Operating Instructions 017186-1000

# Level Probe *multicap DC 16*

# Partially insulated rod probes





















### Applications

The Multicap DC 16 probe is primarily designed for limit detection in liquids. The wide selection of corrosion-resistant materials used ensures that it can also withstand extremely corrosive products. The tried-and tested, rugged construction is gas-tight for pressures from vacuum to 100 bar (1450 psi) gauge.

Seal and insulation materials enable it to be used with operating temperatures in the vessel of -80 °C up to +200 °C (-110 °F to +390 °F).

### Your benefits

- Optimum adaptation to your application thanks to a wide range of process connections and practical variations
  - = reliable function at a cost-effective price
- Protection against condensation in the nozzle
  - = reliable function even with condensation
- Active build-up compensation for limit detection
  - constant and accurate switchpoint even with heavy build-up on the probe, no cleaning or recalibration required



### **Measuring System**

The measuring system consists of:

- Multicap DC 16 probe
- EC... electronic insert in the probe housing
- Nivotester FTC (Z) level limit detector or Silometer FMC (Z) level transmitter.

For limit detection in liquids with heavy build-up or for detecting interface layers, the measuring system consists of:

- Multicap DC 16 probe with active build-up compensation
- EC 16 Z electronic insert
- FTC 520/521 Z or FTC 470/471 Z level limit switch. The limit input of the Silometers FMC 671 Z can also be connected.

Measuring system and application





Level limit detection

Continuous level measurement

Three examples for the use to Multicap DC 16 probes:

- 1) Probe with a combination of screening and active build-up compensation for separation layer detection
- 2) Probe with screening against condensation in the ounting pipe in the tank roof
- Probe with active build-up compensation for reliable limit detection despite extreme build-up



Separate mounting of the electronic insert with an excessively high ambient temperature for the probe head housing



#### **Certified applications**

Please note all specifications in the certificates and appropriate regulations as well as the instructions given in this Technical Information.

## **Operating Principle**

The probe and vessel wall or counter electrode form a capacitor with a defined low capacitance when the probe is in air.

As soon as material covers the probe a parallel circuit is formed consisting of a much larger capacitance and the resistance of the material – the impedance.

In the case of limit detection with partially insulated probes, this means that for materials with conductivities greater than a given, very low threshold, any change in dielectric constant, and thus of conductivity, has no effect on the switchpoint.

On the other hand, this means that it is not possible to use partially insulated probes for continuous level measurement in electrically conducting materials.

Screening on the probe prevents effects caused by build-up of material or condensation in the vicinity of the process connection. Probes with active build-up compensation for limit switching cancel out effects of build-up on the probe.



Simplified circuit diagram showing capacitance measurement with partly insulated probes

### **Probe Selection**

Here are just a few notes on the various designs for the partially insulated Multicap DC 16 probe

#### 1. Probe without ground tube

- for limit detection in conductive liquids
- for high viscosity liquids
- for bulk solids

### 2. Probe with ground tube

for non-conductive liquidsfor use in agitator vessels

### 3. Probe with screening

- Probe with screeni
- for long nozzles
- for condensation on the roof of the vessel
- for build-up on the vessel wall

# 4. Probe with active build-up compensation for limit detection

 with heavy (conductive) build-up on the probe.

The active build-up compensation of the Multicap DC 16 probe is always gas-tight due to the self-adjusting tapered gasket. A wide range of corrosion-resistant materials ensures that they can be used with aggressive products.

### 5. Probe with gas-tight gland

- for liquefied gas tanks (required in Germany)
- to prevent condensation forming in the probe on extreme temperature variations. See also temperature graphs overleaf.

#### 6. Probe with temperature spacer

 for an extended range of operating temperatures in the vessel.
 See also temperature graphs overleaf.

#### 7. Probe without electronic insert

 for high temperatures in the probe housing: Use electronic insert in separate housing. See also temperature graphs overleaf.

#### 8. Probe with protective cover

#### (accessory)

- to prevent condensation forming in the aluminium standard housing.





Further variations outside the product tank

# **Electronic Insert**

Senarate or integrated?			
Separate of integrateu:	Information is provided by the graphs on the right. The horizontal axis is the operating temperature $T_B$ in the vessel. The vertical axis is the ambient temperature $T_U$ of the probe housing (in °C).	A	$\begin{array}{c} 80 \\ 40 \\ 0 \\ -80 \\ -80 \\ -40$
	<ul> <li>Do the temperatures lie in the grey area of graph A? The electronic insert may be mounted in the housing of any probe.</li> </ul>	В	$\begin{array}{c} 80 \\ - \\ 40 \\ - \\ 0 \end{array}$
	<ul> <li>Do the temperatures lie in the grey areas of graph B?</li> <li>The electronic insert may be mounted in the housing of a probe with a temperature spacer or gas-tight gland; or it may be mounted in a separate housing.</li> </ul>	с	- 80 - 40 -
	<ul> <li>Do the temperatures lie in the grey areas of graph C? The electronic insert should be mounted in a separate housing.</li> </ul>		40 - 0 0
	<ul> <li>Do the temperatures lie in the grey area of graph D?</li> <li>Use a probe with a temperature spacer or a gas-tight gland and mount the electronic insert in a separate housing.</li> </ul>	D	$ \begin{array}{c}     T_{U} \\     160 \\     \hline     120 \\     \hline     40 \\     - \\     - 80 \\     - 40 \\     - \\     - 40 \\     - \\     0 \\     - 40 \\     - \\     0 \\     - 40 \\     - \\     0 \\     - 40 \\     - \\     0 \\     0 \\$

 $x \circ C = (x \bullet 1.8 + 32) \circ F$ 

Application range of the various types as a function of operating and ambient temperature

L00-DC21xxxx-05-05-xx-xx-001

**Dimensions** in mm (100 mm = 3.94 in / 1 in = 25.4 mm)



*left: Multicap DC 16 with threaded boss right: Multicap DC 16 with flange* 



left: Multicap DC 16 with threaded boss G 1 ½ A and **ground tube** (Dimensions in brackets for the threaded boss with 1 ½ -11 ½ NPT) right: Multicap DC 16 with flange and **ground tube** 



*left: Multicap DC 16 with threaded boss and active build-up compensation right: Multicap DC 16 with flange and active build-up compensation* 

# Dimensions for Probes with Screening



*left: Multicap DC 16 with threaded boss and screening right: Multicap DC 16 with flange and screening* 



*left: Multicap DC 16 with threaded boss, screening and ground tube right: Multicap DC 16 with flange, screening and ground tube* 



*left: Multicap DC 16 with threaded boss, screening and active build-up-compensation right: Multicap DC 16 with flange, screening and active build-up-compensation* 

#### Dimensions of Other Process Connections and Parts



left: Multicap DC 16 with sanitary thread DN 50 (DIN 11851) right: Multicap DC 16 with 2" Triclamp coupling



*left: Multicap DC 16 with threaded boss and gas-tight gland right: Multicap DC 16 with flange and gas-tight gland* 



*left: Multicap DC 16 with threaded boss and temperature spacer right: Multicap DC 16 with flange and temperature spacer* 

(Dimensions for the DC 16 with screening are shown in brackets)

## Transport, Unpacking

- To avoid damage to the probe, remove the packaging on-site just before mounting. The uninsulated section of probes with active build-up compensation is covered with plastic webbing. This protection should be removed prior to mounting.
- Compare the code on the nameplate of the probe with the product designation on Page 13 to ensure that the correct probe has been delivered.
- Check the probe length. The probes can be shortened easily by sawing. Minimum lengths for the probe rod and insulation are given in the project information.

## Installation

- Probe with parallel thread G 1 ½ A: Use the elastomer/fibre seal provided or any other chemically resistant seal which can withstand temperatures up to 300 °C (570 °F).
- Probe with tapered thread 1 ½ 11 ½ NPT: If required, wrap suitable sealing material around the thread.
- Probe with flange connection: Use a sealing material suitable for the application.
   If the flange is PTFE-clad, then this is generally a suitable seal up to the permitted operating pressure.
- Make sure that the probe insulation is not damaged when sliding the probe through the threaded sleeve or nozzle with counter-flange.
- When tightening, turn the probe with threaded boss at the hex nut only; not at the housing!
- For probes with the G 1 ½ A thread and seal:
   a torque of 300 Nm is sufficient to seal tight against a pressure in the vessel of up to 50 bar (725 psi).
  - a torque of 530 Nm is sufficient to seal tight against a pressure in the vessel of up to 100 bar (1450 psi).

Maximum admissible torque: 600 Nm

• A polypropylene threaded boss with rubber seal may only be tightened using a max. torque of 7 Nm (1 Nm = 0.74 ft lbs).

### **Rotating the Housing**

1) The housing can be rotated after the 3 nuts have been loosened

2) Tighten electronic insert (a) with the central slotted nut (b) leaving space (c) for the connecting cable

The housing can be rotated if the cable gland is pointing in the wrong direction after mounting.

To loosen:

- Unscrew the housing cover
  - Unscrew the central nut (slotted nut) in the electronic housing
  - Remove the electronic insert from the housing
  - Slightly loosen the 3 nuts (7 AF), see Figur.

To rotate:	<ul> <li>The housing can now be rotated in any direction.</li> <li>When mounting the probe from the side, the cable entry should be facing downwards so that no moisture can enter.</li> </ul>
To tighten:	<ul> <li>Securely tighten the 3 nuts in the housing so that the housing is tight against the hex nut.</li> </ul>
	<ul> <li>Insert the electronic insert and securely tighten the central nut so that it does not become loose. Ensure that the cable gland remains free.</li> </ul>

### Connection

Refer to the appropriate Technical Information concerning the electronic insert EC... used in the probe housing.

In the case of the heavy duty housing, the connection diagram corresponds to that of the built-in electronic insert. If is important that no moisture enters the probe housing during storage of the probe, connection of the electronic insert and during operation. Always tighten the housing cover and cable gland securely.

If the probe is installed in a plastic tank, connect the ground terminal of the probe to the counterelectrode using a short cable.

### **Replacing components**

- After the defective electronic insert has been removed and the replacement properly installed. the instrument must be recalibrated and checked for correct function.
- If fully insulated multicap probes are mounted in explosion hazardous areas without the electronic insert, and there is a risk of dangerous electronic discharges, then the probe terminal in the housing must be short-circuited with the ground terminal.

## **Technical Data**

**Operating data** 

Mounting without

electronic insert

electronic inserts

Exchange of

Permitted operating pressures  $p_e$  and temperatures  $T_B$ .

Temperature  $T_B: x \circ C = (x \bullet 1.8 + 32) \circ F$ Pressure  $p_e$ : 1 bar = 14.5 psi

See the following graphs for the relationship between operating pressure and temperature:





Insulation PTFE or PFA



- probes with active build-up compensation - Monel

Insulation PTFE or PFA Applies to probes with active build-up compensation



Insulation PE

• Capacitance values of the probe Ground capacitance: approx. 30 pF

Other capacitance values Gas-tight gland: approx. 20 pF Temperature spacer: approx. 20 pF Active build-up compensation: approx. 10 pF Screening: approx. 3 pF/100 mm

Probe is 250 mm from a conductive vessel wall Insulated probe rod: approx. 1.3 pF/100 mm Uninsulated probe rod: approx. 1.3 pF/100 mm

Probe in ground tube Insulated probe rod: approx. 5.5 pF/100 mm Plain probe rod: approx. 5 pF/100 mm

• Lateral load bearing capacity of the probe see graphs on the right

1 Nm = 0.74 ft lbs







Lateral load bearing capacity for the probe at 20  $^\circ\!C$  (70  $^\circ\!F$ ) and static load

Probe lengths (100 mm = 3.94 in)	<ul> <li>Total length of probe: L max. 6000 mm</li> <li>Length of screening: L3 min. 100 mm. max. 4000 mm.</li> </ul>
	<ul> <li>Length of active probe rod: max. 4000 mm</li> </ul>
	• Length of partial insulation: L2 min. 75 mm, max. probe rod length minus 50 mm
	<ul> <li>Length of active build-up compensation: always 150 mm from where the probe rod leaves the process connection or screening</li> </ul>
	Length tolerances
	up to 1 m: +0 mm, – 5 mm
	up to 3 m: +0 mm, –10 mm
	up to 6 m: +0 mm, -20 mm

Process connection standards	<ul> <li>Parallel thread G 1 ½ A: DIN ISO 228/I, with sealing ring 48 x 55 conf. to DIN 7603</li> <li>Tapered thread 1 ½ - 11 ½ NPT: ANSI B 1.20.1</li> <li>DIN flanges: see flange table</li> <li>ANSI flanges: ANSI B 16.5</li> <li>Sanitary thread: DIN 11851</li> <li>Triclamp coupling: ISO 2852</li> </ul>
Materials	Most material specifications are given in the product structure on Page 13
	<ul> <li>Aluminium housing: cast aluminium AlSi 12, resistant to sea water, EP lacquered</li> <li>Aluminium housing, coated: in fluoropolymer</li> <li>Sealing between housing and process connection: EPDM</li> <li>Sealing for housing cover: O-ring in EPDM</li> <li>Temperature spacer: SS 304 H</li> <li>Gas-tight gland: SS 304 H</li> <li>Sealing ring for process connection G 1 ½ A: elastomer/fibre, non-asbestos, resistant to oils, solvents, steam, weak acids and alkalis up to 300 °C and 100 bar (570 °F and 1450 psi)</li> <li>Cable entrys: standard Pg in nickel-plated brass with NBR seal for cable diameter 710 mm; Protection IP55; ambient temperature up to 100 °C (210 °F)</li> <li>Water-tight Pg in polyamide with neoprene/CR seal for cable diameter 712 mm; Protection IP66; ambient temperature up to 80 °C (180 °F)</li> </ul>

# Certificates

- EC-Type-examination certificate PTB 98 ATEX 2215 X
   C€ ☺ II 1/2 G, EEx ia IIC/B T6 XA 080F/00/a3
- DIBt test report to § 19 WHG, overspill protection with continuous level measurement (for Germany) ZE 210F/00/de
- DIBt test report to § 19 WHG, for overspill protection with level limit switch (for Germany) ZE 211F/00/de

# **Product Structure**

Product structure	Design Basic weight											
Multicap DC 16	DC 16 Partialy insulated rod probe									2,0 kg		
	10		rtificato									
	10			2 G EE	cia IIC T6							
		D	For non-h	azardous	areas	Ove	erspill protection to WH0	G				
		F	ATEX II 1	2 G EE	k ia IIC T6	Ove	erspill protection to WH0	G				
		Н	ATEX II 3	G EE	k nA II T6	Ove	erspill protection to WH0	G				
		R	For non-h	azardous	areas							
		Y	Special ve	ersion								
		2		2G EE	k la IIB T6	$\cap \mathcal{V}$	arspill protection to WH	2				
		5	ATEX II 1/	2 G EE	k ia IIC* T6	Ove	erspill protection to WH	3				
		6	ATEX II 1	2 G EE	k ia IIC* T6							
		7	ATEX II 3	G EE	k nA II* T6							
			*) With no	te: "Avoid	electrostatic o	charge	)"					
			,			0						
	20		Electror	nic inser	t t pot colociad				1	Additional weight		
			B with F	C 61 7	3-wire insert					 0.2 ka		
			C with E	C 11 Z	3-wire Tx 33 k	Hz				0,2 kg 0,2 kg		
			D with E	C 72 Z	3-wire Tx 1 Mł	Ηz				0,2 kg		
			E with E	C 17 Z	2-wire PFM					0,2 kg		
			F with E	C 16 Z	2-wire PFM					0,2 kg		
			G with E	C 27 Z	2-wire PFM					0,2 kg		
			H with E	C 37 Z	2-wire PFM Tx 2 wire DEM Ty	(33 k⊢ (1 м⊔	1z			0,2 kg		
			Y Speci	al version	2-WITE PEIVI TX		IZ			0,2 Kg		
			opeci									
	30	30 Process connection, material										
			AE1	2"	150 lbs	RF	Flange ANSI B16.5	steel		1,6 kg		
			AE2	2"	150 lbs	RF	Flange ANSI B16.5	31611	. 01CT	1,6 kg		
			AE3 AE4	2 2"	150 lbs	RF	Flange ANSI B16.5		>31611 >316Ti	1,6 Kg 1.8 kg		
			AE5	2"	150 lbs	RF	Flange ANSI B16.5	Alloy C	>316Ti	1,8 kg		
			AE6	2"	150 lbs	RF	Flange ANSI B16.5	Monel	>316Ti	1,8 kg		
			AG2	2"	300 lbs	RF	Flange ANSI B16.5	316Ti		3,0 kg		
			AL1	3"	150 lbs	RF	Flange ANSI B16.5	steel		3,2 kg		
			AL2	3"	150 lbs	RF	Flange ANSI B16.5	316Ti	0.407	3,2 kg		
			AL3	3"	150 lbs	RF	Flange ANSI B16.5	216Ti	>31611	3,2 kg		
			ANZ AP1	3 4"	150 lbs	RF	Flange ANSI B16.5	steel		5,0 kg		
			AP2	4"	150 lbs	RF	Flange ANSI B16.5	316Ti		5,4 kg		
			AP3	4"	150 lbs	RF	Flange ANSI B16.5	PTFE	>316Ti	5,4 kg		
			AP4	4"	150 lbs	RF	Flange ANSI B16.5	Alloy B	>316Ti	5,8 kg		
			AP5	4"	150 lbs	RF	Flange ANSI B16.5	Alloy C	>316Ti	5,8 kg		
			AP6	4"	150 lbs	RF	Flange ANSI B16.5	Monel	>316Ti	5,8 kg		
			AR2	4 6"	300 IDS 150 Ibs	RF	Flange ANSI B16.5	31611 316Ti		7,3 Kg		
			AW2	6"	300 lbs	RF	Flange ANSI B16.5	316Ti				
			BG1	DN 50	PN 25/40 B		Flange DIN 2527	steel		3,0 kg		
			BG2	DN 50	PN 25/40 B		Flange DIN 2527	316Ti		3,0 kg		
			BG3	DN 50	PN 25/40		Flange DIN 2527	PTFE	>316Ti	3,0 kg		
			BM1	DN 80	PN 10/16 B		Flange DIN 2527	steel		4,5 kg		
			BM2		PN 10/16 B		Flange DIN 2527	31611 PTEE	S16T	4,5 kg		
			BIVI3	DN 100	PN 10/16 P		Flange DIN 2527	steel	201011	4,0 KY 5 4 ka		
			BQ2	DN 100	PN 10/16 B		Flange DIN 2527	316Ti		5.4 ka		
			BQ3	DN 100	PN 10/16		Flange DIN 2527	PTFE	>316Ti	5,4 kg		
			CG2	DN 50	PN 25/40 C		Flange DIN 2527	316Ti		3,0 kg		
			CG4	DN 50	PN 25/40		Flange DIN 2527	Alloy B	>316Ti	3,2 kg		
			CG5	DN 50	PN 25/40		Flange DIN 2527	Alloy C	>316Ti	3,2 kg		
			CG6	DN 50	PN 25/40		Flange DIN 2527	Monel	>316Ti	3,2 kg		
			CM2	DN 80	PN 10/16 C		Flange DIN 2527	31611		4,5 kg		

30	Proc	ess	coni	nection, ma	ateria	l					
	CM4	DN	80	PN 10/16		Flange DIN 2527	Alloy B	>316Ti	4,8 kg		
	CM5	DN	80	PN 10/16		Flange DIN 2527	Alloy C	>316Ti	4,8 kg		
	CM6	DN	80	PN 10/16		Flange DIN 2527	Monel	>316Ti	4,8 kg		
	CQ2	DN	100	PN 10/16 C		Flange DIN 2527	316Ti		5,4 kg		
	CQ4	DN	100	PN 10/16		Flange DIN 2527	Alloy B	>316Ti	5,8 kg		
	CQ5	DN	100	PN 10/16		Flange DIN 2527	Alloy C	>316Ti	5,8 kg		
	CQ6	DN	100	PN 10/16		Flange DIN 2527	Monel	>316Ti	5,8 kg		
	FG2	DN	50	PN 40 F		Flange DIN 2512	316Ti		3,0 kg		
	FM2	DN	80	PN 16 F		Flange DIN 2512	316Ti		4,5 kg		
	FQ2	DN	100	PN 16 F		Flange DIN 2512	316Ti		5,4 kg		
	GN1	1 1/2		_		Thread ANSI	steel				
	GN2	1 1/2		-		Thread ANSI	31611				
	GN4	1 1/2		-		Thread ANSI	Alloy B				
	GINS	1 1/2	ו NP ו דסוא י	-		Thread ANSI	Alloy C				
	GINO	1 72	14 A			Thread ISO 229					
	GR1	G 1	16 Δ			Thread ISO 228	stool				
	GR2	G 1	1/2 A			Thread ISO 228	316Ti				
	GR4	G 1	1⁄2 A			Thread ISO 228	Allov B				
	GR5	G 1	1/2 A			Thread ISO 228	Alloy C				
	GR6	G 1	1⁄2 A			Thread ISO 228	Monel				
	KF1	20 K	(50)	Ą	RF	Flange JIS B2210	steel		2.6 kg		
	KF2	20 K	50/	4	RF	Flange JIS B2210	316Ti		2,6 kg		
	KF4	20 K	50/	4	RF	Flange JIS B2210	Alloy B	>316Ti	2,8 kg		
	KF5	20 K	50	Ą	RF	Flange JIS B2210	Allov C	>316Ti	2.8 kg		
	KF6	20 k	50	Ą	RF	Flange JIS B2210	Monel	>316Ti	2,8 kg		
	ME2	DN	50	PN 40		DIN 11851	304		0,5 kg		
		Hyg	ienic	connection							
	NG2	DN	50	PN 40 N		Flange DIN 2512	316Ti		3,0 kg		
	NM2	DN	80	PN 16 N		Flange DIN 2512	316Ti		4,5 kg		
	NQ2	DN	100	PN 16 N		Flange DIN 2512	316Ti		5,4 kg		
	TE2	DN	40-5	1 (2")			304		0,5 kg		
	Tri-Clar			p connection							
	119	Spe	ciai v	/ersion							
40		Ina	ctive	e lenath L3	. mate	erial					
		AI	nacti	ive section no	ot seled	cted					
		С.	n	nm (100 mm	400	0 mm)	316Ti		0,2 kg/100 mm		
		D.	n	nm (100 mm	400	0 mm)	Alloy B		0,2 kg/100 mm		
	E			nm (100 mm	400	0 mm)	Alloy C		0,2 kg/100 mm		
		F.	n	nm (100 mm	400	0 mm)	Monel		0,2 kg/100 mm		
		Y	Spec	ial version							
			• • • •								
50				ctive guard b	uiia-u iot sele	p compensation					
			3 1	50 mm			316Ti		0,5 kg		
		4	4 1	50 mm			Alloy B		0,6 kg		
		Ę	5 1	50 mm			Alloy C		0,6 kg		
		6	5 1	50 mm			Monel		0,6 kg		
		ę	9 S	pecial versio	n				-		
60			P	mobe lengt	<b>h L, m</b> 00 mm	6000 mm)	steel		0.1 ka/100 mm		
				without gro	ound tu	be			e,g,		
			В	mm (1 without gro	00 mm ound tu	6000 mm) be	316Ti		0,1 kg/100 mm		
			С	mm (1	00 mm	6000 mm)	Alloy B		0,1 kg/100 mm		
			D	mm (1	00 mm	6000 mm)	Alloy C		0,1 kg/100 mm		
			E	without gro	ound tu 00 mm	be 6000 mm)	Monel		0,1 kg/100 mm		
			н	without gro	ound tu 00 mm	be 6000 mm)	steel		0,3 ka/100 mm		
				with ground	d tube	6000 mm)	304		0.2 ka/100 ~~~		
			J	with ground	d tube	סטטט mm)	31011		0,3 kg/100 mm		
			K	with around	00 mm d tube	6000 mm)	Alloy B		0,3 kg/100 mm		

60				Pr	obe	e len	ngt	h L, material					
				L	with	. mm n gro	n (1 bun	00 mm 6000 m d tube	ım)	Alloy C	0,3 k	g/100 mm	
				Μ	with	. mm n gro	n (1 bun	00 mm 6000 m d tube	ım)	Monel	0,3 k	g/100 mm	
				Υ	Spe	ecial	ve	rsion					
				1	350	) mm	۱ ۵۲	aund tubo		steel			
				2	500	) mm	yıc 1			steel			
				-	with	nout	gro	ound tube		01001			
				3	350	) mm	1			316Ti			
				4	500	) mm	gro 1	ound tube		316Ti			
					with	nout	gro	ound tube		01011			
70					Pa	rtial	l in	sulation I 2					
10					1	i tiai	mr	m(100  mm 400)	0 mm)	PTEE insulated			
					2		mr	n (100 mm 400	0 mm)	PE insulated			
					3		mr	n (100 mm 400	, 0 mm)	PFA insulated			
					4	100	mr	n		PTFE insulated (	standard)		
					9	Spe	cia	l version					
					I								
80						Opt	tio	n					
						1	Ba	sic version					
						2 Temperature spacer							
						3 Gas-tight probe seal							
						9	Shi	ecial version					
90	1	1		1			Но	using, Cable F	Entry				
							С	Aluminium	E-Housing	NPT 1/2"	IP66		
							D	Aluminium	E-Housing	G ½ A	IP66		
							Е	Aluminium	E-Housing	M 20x1,5	IP66		
							F	Aluminium	E-Housing	HNA 24x1,5	IP66		
							J	316Ti	E-Housing	HNA 24x1,5	IP66	0,7 kg	
							L	Polyester	E-Housing	NPT 1/2"	IP66		
							M	Polyester	E-Housing	G ½ A	IP66		
							0	Polyester	E-Housing	M 20x1,5	IP66		
							г т	Ctd. aluminium	E-Housing	HINA 24X1,5	1P66		
								Ctd. aluminium	E-Housing	G 1/2 A	IP66		
							v	Ctd. aluminium	E-Housing	M 20x1 5	IP66		
							w	Ctd. aluminium	E-Housing	HNA 24x1,5	IP66		
						1	9	Special version	0				
DC 16 -								Complete produc	ct designatior	1			



### Note!

Please state lengths for the probe when ordering. See also dimensioned drawings on Pages 6 to 8.

Screening									
L3									
$\downarrow$									



Total length of probe



from the sealing surface of the process connection

### Accessories

see Technical Information TI 229F: "Probe accessories"

- Slip-on sheet for increasing impedance range
- Protective cover for the probe housing

### **Supplementary Documentation**

 

 Technical Information (TI)
 • Electric TI 270

 • Electric
 • Electric

- Electronic Inserts EC 11 Z, EC 72 Z TI 270F/00/en
- Electronic Insert EC 16 Z TI 170F/00/en
- Electronic Insert EC 17 Z TI 268F/00/en
- Electronic Inserts EC 37 Z, EC 47 Z TI 271F/00/en
- Electronic Insert EC 61 Z TI 267F/00/en
- Probe accessories TI 229F/00/en
- Separate housing for electronic insert TI 228F/00/en

Transmitters for limit detection and continuous level measurement on request

#### Endress+Hauser GmbH+Co.

Instruments International P.O. Box 2222 D-79574 Weil am Rhein Germany

Tel. (07621) 975-02 Tx 773926 Fax (07621) 975 345 e-mail: info@ii.endress.com

Internet: http://www.endress.com



