

Technical Information

Weld-in adapter, Process adapter and Flanges

Level and pressure measurement



Application

The adapters and the flanges are used to connect level or pressure sensors to a vessel or a pipe.

Your benefits

- High-quality, corrosion resistant materials for use in aggressive media
- Versions without crevices and dead space of the weld-in adapters and the process adapters according to international hygiene regulations
- A variety of seals for application in diverse processes
- Flanges are specified according to both flange standards DIN/EN

Table of contents

General information	3
Suitable for hygienic processes	3
Weld-in adapter - overview level	4
Weld-in adapter and accessories - level	8
G ¾", d=29 for pipe-mounting	8
G ¾", d=50 for vessel-mounting	9
G ¾", d=55 with flange for flush-mounted installation	10
G 1", d=53 without flange for pipe-mounting	11
G 1", d=60 with flange for flush-mounted installation with sealing surface	12
G 1" sensor can be positioned	13
RD 52 sensor can be positioned	13
UNI D85	14
UNI D65	14
M24 D65	15
DRD DN50 (65 mm (2.56 in)) for flush-mounted installation of devices with DRD-flange ..	16
Weld-in adapter - overview pressure	17
Weld-in adapter and accessories - Pressure	19
UNI D85	19
UNI D65	20
DRD DN50 (65 mm (2.56 in)) for flush-mounted installation of devices with DRD-Flange	21
G 1", d=60 with flange for flush-mounted installation with sealing surface	22
G 1½" flush-mounted	23
G 1" flush-mounted with metallic sealing taper	23
G ½" flush-mounted	23
Process adapter M24 - overview level	24
Process connection M24 - level	25
Varivent F DN32 PN40	25
Varivent N DN50 PN40	25
DIN11851 DN40	26
DIN11851 DN50	26
SMS 1½"	27
Clamp 1½"	27
Clamp 2"	28
APV-Inline	28
Process adapter UNI - overview pressure	29
Process adapter UNI - Pressure	30
Clamp 2"	30
Varivent N	30
DIN11851 DN40	31
DIN11851 DN50	31
DRD DN50	32
Welding hints	33
Weld-in adapter with leakage hole or leakage port	33

Notes for pressure measuring devices	33
Preparation	33
Welding procedure	34
Install measuring device	34
Pressure resistance	35

Flange - Overview	36
Specifications	36
Versions	36
Flange Norm DIN EN 1092-1	36
Height of raised face	37

Mechanical Construction	38
DIN flanges (DIN 2527)	38
PN10	38
PN16	39
PN25	39
PN40	40
PN64	40
PN100	41
EN flanges (DIN EN 1092-1)	42
PN16	42
PN25	42
PN40	43
PN63	43
PN100	44
ASME-Flanges (ASME B 16.5-2013)	45
Class 150	45
Class 300	46
Class 600	46
Class 900	47
Class 1500	47
JIS flanges (B 2220)	48
10 K	48
20 K	48
63 K	49

Adapter flange FAU70	50
FAU70E Version with metrical thread	50
FAU70A Version with conical thread	50

Slip-on flange FAU80	51
FAU80 Version slip-on flange	51

Screw in flange FAX50	52
FAX50 universal flange DIN-ASME-JIS	52
G ¾", NPT ¾"	52
G 1", NPT 1"	52
G 1½", NPT 1½"	53
G 2", NPT 2"	53
Order information FAX50	54

Pressure-temperature dependencies	55
EN flanges	55
ASME flanges	55
JIS flanges	55

General information

Pressure equipment directive PED 2014/68/EU:

The herein listed adapters are not subject to the pressure equipment directive independent of the maximum allowable amount of pressure, because they have no pressurised housing.

NOTICE

Maximum pressure and temperature may be limited by the sensor installed in the adapter.

- ▶ Maximum design pressure and temperature stated is for the adapter only and not for the sensor being installed in the adapter. Consult sensor supplier for sensor pressure-temperature ratings.

Suitable for hygienic processes

3-A und EHEDG



NOTICE

- ▶ Depending of device versions meet the requirements of 3-A sanitary standard no. 74. Endress+Hauser confirms this compliance by affixing the 3-A symbol.
- ▶ For the hygienic design accordingly 3-A, EHEDG and ASME BPE is the use of appropriate fittings for pipings and gaskets should be noted.
- ▶ To avoid the risk of contamination, install the device in accordance with the design principles of EHEDG, Document 37 "Hygienic Design and Application for Sensors" and Document 16 "Hygienic Pipe Connections".
- ▶ Suitable connections and seals must be used in order to guarantee hygiene-compliant design as per 3-A and EHEDG specifications.
- ▶ If installed horizontally, ensure that the leakage hole is pointing downwards. This allows leaks to be detected as quickly as possible, see chapter "Weld-in adapter with leakage hole/leakage port" → 33.
- ▶ The gap-free connections can be cleaned of all residue using sterilization in place (SIP) and cleaning in place (CIP), which are typical cleaning methods within the industry. Attention must be paid to the pressure and temperature specifications of the sensor and process connections for CIP and SIP processes.

Material conformity

Conform materials according to FDA 21 CFR (Code of Federal Regulations)

PART 177 - Indirect Food Additives: Polymers

- Part 177.1550: Perfluorocarbon resins (PTFE)
- Part 177.2600: Rubber articles intended for repeated use (EPDM, Silicone (VMQ), Viton (FKM))







Conform to regulation (EC) No. 1935/2004 on materials and articles intended to come into contact with food (European)

- BfR (Federal Institute for Risk Assessment) Recommendation XV. Commodities based on Silicones: Silicone (VMQ)
- BfR (Federal Institute for Risk Assessment) Recommendation XXI. Commodities based on Natural and Synthetic Rubber: EPDM, Viton (FKM)
- PTFE conform to regulation (EC) No. 10/2011

NOTICE

- ▶ The data concerning suitability for hygienic processes are listed under the relevant device version.







Weld-in adapter - overview level

Weld-in adapter						
	a0008246	a0008251	a0008256	a0011924	a0008248	a0008253
	G ¾", d=29 for pipe- mounting	G ¾", d=50 for vessel- mounting	G ¾", d=55 with flange	G 1", d=53 without flange	G 1", d=60 with flange	G 1" adjustable
Material	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)
Roughness µm (µin) process side	≤ 1.5 (59.1)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)
Order number weld-in adapter	71258357	71258355	52001052	71258358	52001051 ¹⁾	52001221 ²⁾
Order number weld-in adapter with inspection certificate ^{3) 4)}	52028295	52018765	52011897	71093129	52011896 ¹⁾	52011898 ²⁾
Order number for seal replacement (5 pieces) ⁵⁾	Silicone O-ring 52021717	Silicone O-ring 52021717	Silicone O-ring 52014473	Silicone O-ring 52014472	Silicone O-ring 52014472	Silicone profile gasket 52014424
Order number welding dummy ⁶⁾	71174959	71174959	71168889	71166879	71166879	71181945
Order number blind plug ⁶⁾	71167850	71167850	71177193	71173810	71173810	71166366
Order number blind plug with inspection certificate ^{4) 6)}	–	–	71190074	71167291	71167291	71196853
Measuring device	Suitable for process connection option ⁷⁾					
Liquicap						
FMI51	–	GQJ	–	GWJ	GWJ	–
FMI52	–	–	–	GWJ	GWJ	–
FTI51	–	GQJ	–	GWJ	GWJ	–
FTI52	–	–	–	GWJ	GWJ	–
Liquipoint						
FTW23, FTW33	W5J	W5J	–	WSJ	WSJ	–

- 1) Replace the weld-in adapter with order number 917969-1000.
- 2) Replace the weld-in adapter with order number 215159-0000.
- 3) AD2000: The material 316L (in contact with process) corresponds to AD2000 – W0/W2.
- 4) Inspection certificate EN10204-3.1 material
- 5) One seal is included in scope of delivery.
- 6) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.
- 7) The option can be selected in the Product Configurator via the order feature "Process Connection".



Product Configurator: www.endress.com



Weld-in adapter						
	a0008246 G 3/4", d=29 for pipe- mounting	a0008251 G 3/4", d=50 for vessel- mounting	a0008256 G 3/4", d=55 with flange	a0011924 G 1", d=53 without flange	a0008248 G 1", d=60 with flange	a0008253 G 1" adjustable
Measuring device	Suitable for process connection option ¹⁾					
Liquiphant						
FTL33, FTL31	W5J	W5J	–	WSJ	WSJ	WSJ
FTL20	1	1	–	7	7	7
FTL20H	GDJ	GDJ	–	GEJ	GEJ	GEJ
FTL260	–	–	–	0	0	–
FTL330x	–	–	–	G	G	G
FTL50, FTL50H	–	–	GQ2	GW2	GW2	GW2
FTL51, FTL51H	–	–	–	GW2	GW2	GW2
FTL80	–	–	WCJ	WSJ	WSJ	WSJ
FTL81	–	–	–	WSJ	WSJ	WSJ
	Weld-in adapter as an accessory enclosed option ²⁾					
Liquipoint						
FTW23, FTW33	PC/PD	PA/PB	–	PG/PH	PE/PF	–
Liquiphant						
FTL31, FTL33	PC/PD	PA/PB	–	PG/PH	PE/PF	–

1) The option can be selected in the Product Configurator via the order feature "Process Connection".

2) The option can be selected in the Product Configurator via the order feature "Accessory Enclosed".



Product Configurator: www.endress.com

Weld-in adapter					
	a0008252	a0008245	A0017639	a0008552	a0008254
	RD52	UNI D85	UNI D65	M24 D65	DRD DN50 65 mm (2.56 in) (weld-in flange)
Material	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435) 304 (1.4301)
Roughness μm (μin) process side	≤ 0.8 (31.5)	≤ 0.76 (29.9)	≤ 0.76 (29.9)	≤ 0.8 (31.5)	≤ 0.76 (29.9)
Order number weld-in adapter	52001047 ¹⁾	52006262	214880-0002	71041381	52002041/ 916743-0000
Order number weld-in adapter with inspection certificate ²⁾	52006909 ¹⁾	52010173	52010174	71041383	52011899/ -
Order number for seal replacement (5 pieces) ³⁾	Silicone profile gasket 52014424	Silicone profile gasket 52023572	Silicone profile gasket 52023572	EPDM O-ring 52024267	PTFE flat seal 52024228
Order number welding dummy	71181945 ⁴⁾	71114210	71114210	-	71114209
Order number blind plug ⁴⁾	71114210	71181340	71181340	71171418	71181450
Slotted nut	52021715	52021715	52021715	-	-
Measuring device	Suitable for process connection option⁵⁾				
Liquicap					
FMI5x	-	UPJ	UPJ	-	-
FTI5x	-	UPJ	UPJ	-	-
Liquipoint					
FTW23, FTW33	-	-	-	X2J	-
Liquiphant					
FTL33	5ZJ	-	-	X2J	-
FTL20H	UPJ	-	-	-	-
FTL330x	F	-	-	-	-
FTL5xH	EE2	-	-	-	PE2

1) Replace the weld-in adapter with order number 942329-0001.

2) Inspection certificate EN10204-3.1 material; AD2000: The material 316L (in contact with process) corresponds to AD2000 – W0/W2.



3) One seal is included in scope of delivery.

4) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

5) The option can be selected in the Product Configurator via the order feature "Process Connection".



Product Configurator: www.endress.com

Weld-in adapter					
	a0008252	a0008245	A0017639	a0008552	a0008254
	RD52	UNI D85	UNI D65	M24 D65	DRD DN50 65 mm (2.56 in) (weld-in flange)
Measuring device	Suitable for process connection option ¹⁾				
Levelflex					
FMP41C	–	UPK/UQK	UPK/UQK	–	–
FMP43	–	–	–	U1J	–
FMP53	–	–	–	U1J	–
	Weld-in adapter as an accessory enclosed option ²⁾				
Liquipoint					
FTW23, FTW33	–	–	–	PM/PN	–
Liquiphant					
FTL33	PO/PQ	–	–	PM/PN	–

1) The option can be selected in the Product Configurator via the order feature "Process Connection".



2) The option can be selected in the Product Configurator via the order feature "Accessory Enclosed".



Product Configurator: www.endress.com



Weld-in adapter and accessories - level

G 3/4", d=29 for pipe-mounting

Dimensions mm (in)	Version	Order number
 A0008265 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 1.5 µm (59.1 µin)	71258357 52028295
	Silicone O-ring, ø 14.9 x 2.7 mm (0.59 x 0.11 in) Material: VMQ 75 Conform according to FDA, 3-A For this version a simple replacement of the seal is possible.	52021717 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71174959 ¹⁾
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 3.2 µm (126 µin)	71167850 ¹⁾
	Approved by EHEDG	
Alternative seals and pressure ring		Order number
 A0021901	ø 15.08 x 2.62 mm (0.59 x 0.10 in) Material: EPDM Conform according to FDA Approved by EHEDG	71167872 ¹⁾ (5 pieces)
	ø 15.08 x 2.62 mm (0.59 x 0.10 in) Material: FKM Conform according to FDA Approved by EHEDG	71167890 ¹⁾ (5 pieces)
	ø 14.9 x 2.7 mm (0.59 x 0.11 in) Material: Silicone VMQ 80 Conform according to FDA, USP Class VI, 3-A	71086117 (3 pieces)
 A0021902	Pressure ring Material: 316L (1.4435) The seal with pressure ring enables easy exchange of defective sealing rings.	52027421


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

G 3/4", d=50 for vessel-mounting

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	71258355 52018765
	Silicone O-ring, ø 14.9 x 2.7 mm (0.59 x 0.11 in) Material: VMQ 75 Conform according to FDA, 3-A For this version a simple replacement of the seal is possible.	52021717 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71174959 ¹⁾
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 3.2 µm (126 µin)	71167850 ¹⁾
	Approved by EHEDG	
Alternative seals and pressure ring		Order number
	ø 15.08 x 2.62 mm (0.59 x 0.10 in) Material: EPDM Conform according to FDA Approved by EHEDG	71167872 ¹⁾ (5 pieces)
	ø 15.08 x 2.62 mm (0.59 x 0.10 in) Material: FKM Conform according to FDA Approved by EHEDG	71167890 ¹⁾ (5 pieces)
	ø 14.9 x 2.7 mm (0.59 x 0.11 in) Material: Silicone VMQ 80 Conform according to FDA, USP Class VI, 3-A	71086117 (3 pieces)
	Pressure ring Material: 316L (1.4435) The seal with pressure ring enables easy exchange of defective sealing rings.	52027421


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

G ¾", d=55 with flange for flush-mounted installation

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52001052 52011897
	Silicone O-ring, ø 21.89 x 2.62 mm (0.86 x 0.10 in) Material: VMQ 70 Conform according to FDA, 3-A	52014473 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71168889 ¹⁾
	Blind plug for closing weld-in adapter - Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71177193 ¹⁾ 71190074 ¹⁾
	Approved by EHEDG	
	Alternative seals ø 21.89 x 2.62 mm (0.86 x 0.10 in)	Order number
	Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71140670 (3 pieces)
	Material: Kalrez Comp. 2035	71167883 ¹⁾
	Material: FKM	71172153 ¹⁾ (5er Set)
	Material: FKM/FEP-FEK 75 Shore	71167747 ¹⁾
	Material: Silicone VMQ 23-70 Conform according to FDA, USP Class VI	71086100 (3 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

G 1", d=53 without flange for pipe-mounting

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	71258358 71093129
	Silicone O-ring, ø 28.17 x 3.53 mm (1.11 x 0.14 in) Material: VMQ 70 Conform according to FDA, 3-A	52014472 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71166879 ¹⁾
	Blind plug for closing weld-in adapter - Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71173810 ¹⁾ 71167291 ¹⁾
	Approved by EHEDG	
	Alternative seals ø 28.17 x 3.53 mm (1.11 x 0.14 in)	Order number
	Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71140668 (3 pieces)
	Material: FKM665 Conform according to FDA	71182264 ¹⁾ (5 pieces)
	Material: FKM Conform according to FDA, USP Class VI, 3-A	71166227 ¹⁾
	Material: Kalrez comp. 4079	71166292 ¹⁾
	Material: Silicone VMQ 3-70 Conform according to FDA, USP Class VI	71086102 (3 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

**G 1", d=60 with flange for
flush-mounted installation
with sealing surface**

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52001051 52011896
	Silicone O-ring, ø 28.17 x 3.53 mm (1.11 x 0.14 in) Material: VMQ 70 Conform according to FDA, 3-A	52014472 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71166879 ¹⁾
	Blind plug for closing weld-in adapter - Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71173810 ¹⁾ 71167291 ¹⁾
	Approved by EHEDG	
	Alternative seals ø 28.17 x 3.53 mm (1.11 x 0.14 in)	Order number
	Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71140668 (3 pieces)
	Material: FKM665 Conform according to FDA	71182264 ¹⁾ (5 pieces)
	Material: FKM Conform according to FDA, USP Class VI, 3-A	71166227 ¹⁾
	Material: Kalrez comp. 4079	71166292 ¹⁾
	Material: Silicone VMQ 3-70 Conform according to FDA, USP Class VI	71086102 (3 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

G 1" sensor can be positioned

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter ■ max. 25 bar (362 psi) / max. 150 °C (302 °F) ■ max. 40 bar (580 psi) / max. 100 °C (212 °F)	■ Without inspection certificate ■ With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.8 \mu\text{m}$ (31.5 μin)	52001221 52011898
	Silicone profile gasket, $\varnothing 29 \times 36 \times 3.7 \text{ mm}$ (1.14 x 1.42 x 0.15 in) Material: SI-60 Conform according to FDA	52014424 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71181945 ¹⁾
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	71166366 ¹⁾
	Approved by EHEDG	
	Alternative seals $\varnothing 29 \times 36 \times 3.7 \text{ mm}$ (1.14 x 1.42 x 0.15 in)	Order number
	Material: EPDM-60 Conform according to FDA, 3-A	52012805
	Material: Silicone VMQ 60 Conform according to FDA, USP Class VI	71075662 (5 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

RD 52 sensor can be positioned

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52001047 52006909
	Silicone profile gasket, ø 29 x 36 x 3.7 mm (1.14 x 1.42 x 0.15 in) Material: SI-60; Conform according to FDA For this version a simple replacement of the seal is possible.	52014424 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71181945 ¹⁾
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71166366 ¹⁾
	Alternative seals ø 29 x 36 x 3.7 mm (1.14 x 1.42 x 0.15 in)	Order number
	Material: EPDM-60 Conform according to FDA	52012805
	Material: Silicone VMQ 60 Conform according to FDA, USP Class VI, 3-A	71075662 (5 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

UNI D85

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter max. 16 bar (232 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	52006262 52010173
	Silicone profile gasket, ø 34 x 41.5 x 6.4 mm (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71114210
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71181340 ¹⁾
	Approved by EHEDG	
	Alternative seal ø 34 x 41.5 x 6.4 mm (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

UNI D65

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter max. 16 bar (232 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	214880-0002 52010174
	Silicone profile gasket $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71114210
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	71181340 ¹⁾
	Approved by EHEDG	
	Alternative seal $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

M24 D65

Dimensions (mm)	Version	Order number
 Pressure and temperature range of the adapter max. 25 bar (362 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.8 \mu\text{m}$ (31.5 μin)	71041381 71041383
	O-ring, $\varnothing 15.54 \times 2.62 \text{ mm}$ (0.61 x 0.1 in) Material: EPDM Conform according to USP Class VI, 3-A	52024267 (5 pieces)
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	71171418 ¹⁾




1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

**DRD DN50 (65 mm (2.56 in))
for flush-mounted
installation of devices with
DRD-flange**

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter ■ max. 25 bar (362 psi) / max. 150 °C (302 °F) ■ max. 40 bar (580 psi) / max. 100 °C (212 °F)	■ Without inspection certificate ■ With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	52002041 52011899
	Material: AISI 304 (1.4301) Roughness (process side): $R_a \leq 0.8 \mu\text{m}$ (31.5 μin)	916743-0000
	Flat seal, $\varnothing 50 \times 65 \times 1 \text{ mm}$ (1.97 x 2.56 x 0.04 in) Material: PTFE Conform according to FDA	52024228 (5 pieces)
	Welding dummy for welding the weld-in adapter Material: Brass	71114209
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	71181450 ¹⁾

1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

Weld-in adapter - overview pressure

Weld-in adapter							
	a0008245	A0017639	a0008254	a0008248	a0008247	a0008249	a0008250
	UNI D85	UNI D65	DRD DN50 65 mm (2.56 in) (weld-in flange)	G 1" d=60 with flange	G 1½" flush- mounted	G 1" flush- mounted (sealing taper)	G ½" flush- mounted
Material	316L (1.4435)	316L (1.4435)	316L (1.4435) 304 (1.4301)	316L (1.4435)	316L (1.4435)	316L (1.4404)	316L (1.4435)
Roughness μm (μin) process side	≤ 0.76 (29.9)	≤ 0.76 (29.9)	≤ 0.76 (29.9)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)
Order number weld-in adapter	52006262	214880-0002	52002041/ 916743-0000	52001051	52024469	52005087	52002643
Order number weld-in adapter with inspection certificate ^{1) 2)}	52010173	52010174	52011899/ -	52011896	52024470	52010171	52010172
Order number for seal replacement (5 pieces) ³⁾	Silicone profile gasket 52023572	Silicone profile gasket 52023572	PTFE flat seal 52024228	Silicone O-ring 52014472	-	-	-
Order number Welding dummy	71114210	71114210	71114209	71166879 ⁴⁾	52024471	52005272	52005082
Order number blind plug ⁴⁾	71181340	71181340	71181450	71173810	-	71171731	-
Order number blind plug with inspection certificate ^{2) 4)}	-	-	-	71167291	-	-	-
Measuring device	Suitable for process connection option ⁵⁾						
Cerabar T							
PMP135	-	-	-	N	-	M	-
Ceraphant T							
PTP31	-	-	-	-	-	-	AG
PTP35	-	-	-	BB	-	BA	-
Cerabar M							
PMC51	UNJ/UPJ	UNJ/UPJ	TIJ	-	GVJ	-	-
PMP51	-	-	TIJ	GZJ	GVJ	GXJ	GOJ
PMP55	UPJ	UPJ	TIJ	-	GVJ	-	-





1) AD2000: The material 316L (in contact with process) corresponds to AD2000 – W0/W2.

2) Inspection certificate EN10204-3.1 material

3) One seal is included in scope of delivery.

4) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

5) The option can be selected in the Product Configurator via the order feature "Process Connection".

Weld-in adapter							
	a0008245	A0017639	a0008254	a0008248	a0008247	a0008249	a0008250
	UNI D85	UNI D65	DRD DN50 65 mm (2.56 in) (weld-in flange)	G 1" d=60 with flange	G 1½" flush- mounted	G 1" flush- mounted (sealing taper)	G ½" flush- mounted
Measuring device	Suitable for process connection option ¹⁾						
Cerabar S							
PMC71	–	–	TK	–	1G/1H/1J	–	–
PMP71	–	–	–	–	1G/1H	–	–
PMP75	00	00	TK	–	1G/1H	–	–
Deltapilot M							
FMB50	UNJ/UPJ	UNJ/UPJ	TIJ	–	GGJ/GGC	–	–
FMB51	–	–	–	–	GGJ/GGC	–	–
FMB52	–	–	–	–	GGJ/GGC	–	–
Deltapilot S							
FMB70	00/01	00/01	TK	–	1G/1H	–	–
Deltabar S							
FMD78	00/UT	00/UT	TK	–	–	–	–
Deltabar							
FMD71	UNJ/UPJ	UNJ/UPJ	TIJ	–	GVJ	–	–
FMD72	–	–	TIJ	–	GVJ	–	–
	Weld-in adapter as an accessory enclosed option ²⁾						
Cerabar M							
PMC51	Q2/Q3	QT/QU	QP/QR	–	QJ/QK	–	–
PMP51	–	–	QP/QR	–	QJ/QK	QE/QF	QA/QB
PMP55	–	–	QP/QR	–	QJ/QK	–	–
Deltapilot M							
FMB50	Q2/Q3	QT/QU	QP/QR	–	QJ/QK	–	–
FMB51	–	–	–	–	QJ/QK	–	–
FMB52	–	–	–	–	QJ/QK	–	–

1) The option can be selected in the Product Configurator via the order feature "Process Connection".


2) The option can be selected in the Product Configurator via the order feature "Accessory Enclosed".



Product Configurator: www.endress.com


Weld-in adapter and accessories - Pressure

UNI D85

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter max. 16 bar (232 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	52006262 52010173
	Silicone profile gasket, $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Pressure welding dummy for welding the weld-in adapter Material: Brass	71114210
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.76 \mu\text{m}$ (29.9 μin)	71181340 ¹⁾
	Approved by EHEDG	
	Alternative seals $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

UNI D65

Dimensions mm (in)	Version	Order number
 a0008264 Pressure and temperature range of the adapter max. 16 bar (232 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	214880-0002 52010174
	Silicone profile gasket, $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Pressure welding dummy for welding the weld-in adapter Material: Brass	71114210
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	71181340 ¹⁾
	Approved by EHEDG	
	Alternative seal $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

**DRD DN50 (65 mm (2.56 in))
for flush-mounted
installation of devices with
DRD-Flange**

Dimensions mm (in)	Version	Order number
 a0008263 Pressure and temperature range of the adapter ■ max. 25 bar (362 psi) / max. 150 °C (302 °F) ■ max. 40 bar (580 psi) / max. 100 °C (212 °F)	■ Without inspection certificate ■ With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	52002041 52011899
	Material: AISI 304 (1.4301) Roughness (process side): $Ra \leq 0.8 \mu\text{m}$ (31.5 μin)	916743-0000
	Flat seal, $\varnothing 50 \times 65 \times 1 \text{ mm}$ (1.97 x 2.56 x 0.04 in) Material: PTFE Conform according to FDA	52024228 (5 pieces)
	Pressure welding dummy for welding the weld-in adapter Material: Brass	71114209
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	71181450 ¹⁾


1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

**G 1", d=60 with flange for
flush-mounted installation
with sealing surface**


Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52001051 52011896
	Silicone O-ring, ø 28.17 x 3.53 mm (1.11 x 0.14 in) Material: VMQ 70 Conform according to FDA, 3-A	52014472 (5 pieces)
	Pressure welding dummy for welding the weld-in adapter Material: Brass	71166879 ¹⁾
	Blind plug for closing weld-in adapter - Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71173810 ¹⁾ 71167291 ¹⁾
	Approved by EHEDG	
	Alternative seals ø 28.17 x 3.53 mm (1.11 x 0.14 in)	Order number
	Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71140668 (3 pieces)
	Material: FKM665 Conform according to FDA	71182264 ¹⁾ (5 pieces)
	Material: FKM Conform according to FDA, USP Class VI, 3-A	71166227 ¹⁾
	Material: Kalrez comp. 4079	71166292 ¹⁾
	Material: Silicone VMQ 3-70 Conform according to FDA, USP Class VI	71086102 (3 pieces)

1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

G 1½" flush-mounted


Dimensions mm (in)	Version	Order number
	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.8 \mu m$ (31.5 μin)	52024469 52024470
	Pressure welding dummy for welding the weld-in adapter Material: Brass	52024471

G 1" flush-mounted with metallic sealing taper









Dimensions mm (in)	Version	Order number
	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.8 \mu m$ (31.5 μin)	52005087 52010171
	Pressure welding dummy for welding the weld-in adapter Material: Brass	52005272
	Blind plug for closing weld-in adapter Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu m$ (29.9 μin)	71171731 ¹⁾

1) TSP modification number. Can be ordered only FTSP, PTSP or NTSP.

G ½" flush-mounted

Dimensions mm (in)	Version	Order number
	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.8 \mu m$ (31.5 μin) Max. pressure resistance: 100 bar (1500 psi)	52002643 52010172
	Pressure welding dummy for welding the weld-in adapter Material: Brass	52005082

Process adapter M24 - overview level

Process adapter								
	A0023286	A0023419	A0023547	A0023418	A0023420	A0023423	A0023426	A0023422
	Varivent F DN32 PN40	Varivent N DN50 PN40	DIN11851 DN40	DIN11851 DN50	SMS 1½"	Clamp 1½"	Clamp 2"	APV-Inline
Material	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)
Roughness μm (μin) process side	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)	≤ 0.8 (31.5)
Order number weld-in adapter	52023996	52023997	52023999	52023998	52026997	52023994	52023995	52024000
Order number weld-in adapter with inspection certificate ¹⁾	52024003	52024004	52024006	52024005	52026999	52024001	52024002	52024007
Order number for seal replacement (5 pieces) ²⁾	EPDM 52024267	EPDM 52024267	EPDM 52024267	EPDM 52024267	EPDM 52024267	EPDM 52024267	EPDM 52024267	EPDM 52024267
Slotted nut	–	–	71258361	71258361	–	–	–	–
Measuring device	Suitable for process connection option ³⁾							
Liquipoint								
FTW23, FTW33	X2J	X2J	X2J	X2J	X2J	X2J	X2J	X2J
Liquiphant								
FTL33	X2J	X2J	X2J	X2J	X2J	X2J	X2J	X2J
Liquipoint	Weld-in adapter as an accessory enclosed option ⁴⁾							
FTW23								
FTW33	RC/RD	RA/RB	–	RE/RF	RG/RH	RI/RJ	RK/RL	–
FTW33	RC/RD	RA/RB	–	RE/RF	RG/RH	–	–	–
Liquiphant								
FTL33	RC/RD	RA/RB	–	RE/RF	RG/RH	–	–	–

1) Inspection certificate EN10204-3.1 material; AD2000: The material 316L (in contact with process) corresponds to AD2000 – W0/W2.

2) One seal is included in scope of delivery.

3) The option can be selected in the Product Configurator via the order feature "Process Connection".

4) The option can be selected in the Product Configurator via the order feature "Accessory Enclosed".




Product Configurator: www.endress.com

Process connection M24 - level




Pay attention to the temperature and pressure specifications for the seals and clips used at the customer site!


Varivent F DN32 PN40

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52023996 52024003
	Seal, ø 15.54 x 2.62 mm (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)
	Approved by EHEDG	


Varivent N DN50 PN40

Dimensions mm (in)	Version	Order number
 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52023997 52024004
	Seal, ø 15.54 x 2.62 mm (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)
	Approved by EHEDG	


DIN11851 DN40

Dimensions mm (in)	Version	Order number
 A0023548 Pressure and temperature range of the adapter max. 25 bar (362 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.8 \mu\text{m}$ (31.5 μin)	52023999 52024006
	Seal, $\varnothing 15.54 \times 2.62 \text{ mm}$ (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)
	Approved by EHEDG	


DIN11851 DN50

Dimensions in mm (in)	Version	Order number
 A0023273 Pressure and temperature range of the adapter max. 25 bar (362 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $R_a \leq 0.8 \mu\text{m}$ (31.5 μin)	52023998 52024005
	Seal, $\varnothing 15.54 \times 2.62 \text{ mm}$ (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)
	Approved by EHEDG	


SMS 1½"

Dimensions mm (in)	Version	Order number
 A0023278 Pressure and temperature range of the adapter max. 25 bar (362 psi) / max. 150 °C (302 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52026997 52026999
	Seal, ø 15.54 x 2.62 mm (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)


Clamp 1½"

Dimensions mm (in)	Version	Order number
 A0023284 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52023994 52024001
	Seal, ø 15.54 x 2.62 mm (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)
	Approved by EHEDG	

Clamp 2"

Dimensions mm (in)	Version	Order number
 A0023281 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52023995 52024002
	Seal, ø 15.54 x 2.62 mm (0.61 x 0.1 in) Material: EPDM Conform according to FDA, 3-A	52024267 (5 pieces)
	Approved by EHEDG	






APV-Inline

Dimensions mm (in)	Version	Order number
 A0023421 Pressure and temperature range of the adapter - max. 25 bar (362 psi) / max. 150 °C (302 °F) - max. 40 bar (580 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.8 µm (31.5 µin)	52024000 52024007
	Seal, ø 15.54 x 2.62 mm (0.61 x 0.1 in) Material: EPDM Conform according to FDA	52024267 (5 pieces)
	Approved by EHEDG	

Process adapter UNI - overview pressure



The following adapters can be used to create a connection between the customer's process connection and the Endress+Hauser instrument with a universal adapter.

Process adapter					
	A0023532 Clamp 2"	A0023530 Varivent N	A0023413 DIN11851 DN40	A0023417 DIN11851 DN50	A0021898 DRD DN50
Material	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)	316L (1.4435)
Roughness μm (μin) process side	≤ 0.76 (29.9)	≤ 0.76 (29.9)	≤ 0.76 (29.9)	≤ 0.76 (29.9)	≤ 0.76 (29.9)
Order number weld-in adapter	71114176	71114177	71114172	71114173	71114174
Order number weld-in adapter with inspection certificate ¹⁾	71114207	71114208	71114178	71114205	71114206
Order number for seal replacement (5 pieces) ²⁾	Silicone profile gasket 52023572	Silicone profile gasket 52023572	Silicone profile gasket 52023572	Silicone profile gasket 52023572	Silicone profile gasket 52023572
Scope of delivery	–	–	Slotted nut	Slotted nut	DRD-flange
Measuring device	Suitable for process connection option ³⁾				
Cerabar					
PMC51	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ
PMP55	UPJ	UPJ	UPJ	UPJ	
Deltapilot					
FMB50	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ
Deltabar					
FMD71	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ	UNJ/UPJ
Cerabar	Weld-in adapter as an accessory enclosed option ⁴⁾				
PMC51					
	RD / R4	RF/R6	RA/R1	RB/R2	RC/R3
Deltapilot					
FMB50	RD/R4	RF/R6	RA/R1	RB/R2	RC/R3

1) Inspection certificate EN10204-3.1 material; AD2000: The material 316L (in contact with process) corresponds to AD2000 – W0/W2.

2) One seal is included in scope of delivery.

3) The option can be selected in the Product Configurator via the order feature "Process Connection".


4) The option can be selected in the Product Configurator via the order feature "Accessory Enclosed".




Product Configurator: www.endress.com

Process adapter UNI - Pressure


Clamp 2"

Dimensions mm (in)	Version	Order number
 A0023531 Pressure- and temperature range max. 10 bar (150 psi) / max. 100 °C (212 °F)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	71114176 71114207
	Silicone profile gasket, $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Approved by EHEDG	
	Alternative seal $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)
	Approved by EHEDG	


Varivent N

Dimensions mm (in)	Version	Order number
 A0023526 Pressure- and temperature range max. 10 bar (150 psi) / max. 100 °C (212 °F) (max. 135 °C (275 °F) for 30 minutes)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu\text{m}$ (29.9 μin)	71114177 71114208
	Silicone profile gasket, $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Approved by EHEDG	
	Alternative seal $\varnothing 34 \times 41.5 \times 6.4 \text{ mm}$ (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)
	Approved by EHEDG	


DIN11851 DN40

Dimensions mm (in)	Version	Order number
 Pressure- and temperature range max. 10 bar (150 psi) / max. 100 °C (212 °F) (max. 135 °C (275 °F) for 30 minutes)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71114172 71114178
	Material slotted nut: Endress+Hauser supplies these slotted nuts in stainless steel AISI 304 (DIN/EN material number 1.4301) or in AISI 304L (DIN/EN material number 1.4307).	
	Silicone profile gasket, ø 34 x 41.5 x 6.4 mm (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Approved by EHEDG	
	Alternative seal ø 34 x 41.5 x 6.4 mm (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)
	Approved by EHEDG	

DIN11851 DN50

Dimensions mm (in)	Version	Order number
 Pressure- and temperature range max. 10 bar (150 psi) / max. 100 °C (212 °F) (max. 135 °C (275 °F) for 30 minutes)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): Ra ≤ 0.76 µm (29.9 µin)	71114173 71114205
	Material slotted nut: Endress+Hauser supplies these slotted nuts in stainless steel AISI 304 (DIN/EN material number 1.4301) or in AISI 304L (DIN/EN material number 1.4307).	
	Silicone profile gasket, ø 34 x 41.5 x 6.4 mm (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI, 3-A	52023572 (5 pieces)
	Approved by EHEDG	
	Alternative seal ø 34 x 41.5 x 6.4 mm (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI, 3-A	71100719 (5 pieces)
	Approved by EHEDG	

DRD DN50


Dimensions mm (in)	Version	Order number
 Pressure- and temperature range max. 10 bar (150 psi) / max. 100 °C (212 °F) (max. 135 °C (275 °F) for 30 minutes)	- Without inspection certificate - With inspection certificate EN10204-3.1 material Material: AISI 316L (1.4435) Roughness (process side): $Ra \leq 0.76 \mu m$ (29.9 μin)	71114174 71114206
	Material DRD flange: Endress+Hauser supplies these slotted nuts in stainless steel AISI 304 (DIN/EN material number 1.4301).	
	Silicone profile gasket, $\varnothing 34 \times 41.5 \times 6.4$ mm (1.34 x 1.63 x 0.25 in) Material: SI-60 Conform according to FDA, USP Class VI	52023572 (5 pieces)
	Alternative seal $\varnothing 34 \times 41,5 \times 6,4$ mm (1.34 x 1.63 x 0.25 in)	Order number
	Profile gasket Material: EPDM-70 Conform according to FDA, USP Class VI	71100719 (5er-Set)

Welding hints

-  Absolute care must be taken when welding stainless steel. The applied workpieces and tools must be rust-free. Also, no normal steel parts may be present in the vicinity.
-  During the welding, the adapter should be protected against deformations by the welding dummy or by other means of cooling according to usual welding practice (e.g. water cooling). With a suitable seal the welding dummy can also be used to flush-plug the process when starting-up the plant. Before doing so, make sure that the material of the dummy fits the process.

Weld-in adapter with leakage hole or leakage port

If installed horizontally and weld-in adapters with a leakage hole or leakage port are used, ensure that the leakage hole or the leakage port is pointing down. This allows leaks to be detected as quickly as possible.



- A Process adapter with leakage hole
 B Weld-in adapter with leakage hole
 C Process adapter with leakage port
 1 Leakage hole
 2 Mark, e.g. material and/or arrow, 180° across from hole
 3 Leakage port


Notes for pressure measuring devices

Before mounting a weld-in adapter for a pressure measuring device, please note the following:

- The maximum pressure resistance of a sensor is limited. Therefore, the welding must be performed very carefully if a weld-in adapter is applied for screwing-in a pressure measuring cell.
- In order to avoid deformations of the weld-in adapter during the welding it is essential to use the correct welding dummy for heat dissipation. Otherwise the tightness and pressure resistance can not be guaranteed after screwing in the sensor. The welding dummy prevents deformation of the weld-in adapter, which could cause leaks after the mounting of the sensor.

Preparation


- Drill a hole at the required position into the wall of the vessel or pipe
 Hole diameter: The outer diameter of the welding adapter (max. tolerance: +0.2 mm (0.01 in))
- Slide the weld-in adapter with welding dummy into the hole and align it in a way as to ensure that the sensor will be positioned correctly. See the chapter "Install measuring device" from →  34.




Welding procedure

It is recommended to partition the welding seam into several segments (according to common welding practice).

- Pin the weld-in adapter with four or six welding spots to the vessel or tube (see the figures).
- Weld the segments between the spots in order to avoid deformations and leakages. After welding a segment always weld the opposite segment.
- After welding two segments stop the welding procedure until the workpiece is cooled down.
- Let the weld-in adapter cool down after the welding and remove the welding dummy.



Welding of pipes



Welding of vessels



To obtain the desired surface roughness, the range of the welding seam must be polished.


Install measuring device

Notes for level measuring device (e.g. Liquiphant)

The marking indicates the position of the tuning fork. The marking appears either as a material specification (e.g. 316L) or a thread designation (e.g. G 1/2") in the following locations: On the process- or weld-in adapter or on the name plate of the measuring device.


If installed horizontally in vessels

- the marking is face up
- ensure that the leakage hole is pointing down. This allows leaks to be detected as quickly as possible, see chapter "Weld-in adapter with leakage hole/leakage port" → 33.



Orientation in the vessel

When mounted into pipes, the fork must be aligned in the direction of the flow according to the mark.



Orientation in the pipe

Notes for pressure sensor

- Before mounting, all sealing surfaces at the weld-in adapter must be cleaned.
- Remove the protective cap from the pressure sensor.



Do not touch or damage the process isolating diaphragm!

- Screw the pressure sensor firmly at the hexagonal nut. The threaded connection must be fastened fingertight. It is recommended to secure the threaded connection with a torque of 60 Nm (± 20 Nm) to protect it against vibrations and other influences.

Pressure resistance

The material of the weld-in adapter and the quality of the welding are crucial for pressure resistance. The complete length of the thread has to be used in order to ensure maximum pressure resistance.

Flange - Overview

Specifications

The material of the flanges delivered is AISI 316L with the material number 1.4404 or 1.4435. With regard to their stability-temperature property, the materials 1.4404 and 1.4435 are grouped in DIN EN 1092-1 table 18 under 13EO and in JIS B2220:2004 table 5 under 023b. The ASME flanges are dual rated flanges (316/316L) and grouped in table 2-2.2 according to ASME B16.5-2013.



Values in inches are converted to values in millimeters using the factor 2.54.
The mm values are rounded off to the nearest 0 or 5 in the ASME standard.

Versions

DIN flanges	EN flanges	ASME flanges	JIS flanges
German National Standards Institute	European Standards	America Society of Mechanical Engineers	Japanese Industrial Standard
DIN 2527	DIN EN 1092-1:2002-06 and 2007	ASME B16.5-2013	B2220:2004

Flange Norm DIN EN 1092-1

Endress+Hauser usually delivers only flanges with flat face. This type of flange has hardly changed. Thus, a comparison is done only for this sealing surfaces. Due to the change of the designation of the sealing surface mistakes may occur occasionally. The roughness (Rz) of the old raised face form C and the new one B1 have an overlapping between 40 to 50 µm. In this roughness window both standards are fulfilled.

Therefore, at Endress+Hauser the flanges are specified according to both flange standards. This double marking makes it clear that both standards are met.

Flange	Sealing Surface	DIN 2526 ¹⁾		DIN EN 1092-1		
		Form	Rz (µm)	Form	Rz (µm)	Ra (µm)
without raised face		A B	– 40 - 160	A ²⁾	12.5 - 50	3.2 - 12.5
with raised face		C	40 - 160	B1 ³⁾	12.5 - 50	3.2 - 12.5
		D	40	B2	3.2 - 12.5	0.8 - 3.2
		E	16			
tongue		F	–	C	3.2 - 12.5	0.8 - 3.2
groove		N		D		
projection		V 13	–	E	12.5 - 50	3.2 - 12.5
recess		R 13		F		
projection		V 14	for O-rings	H	3.2 - 12.5	3.2 - 12.5
recess		R 14		G		

1) contained in DIN 2527

2) typically of PN2.5 bis PN40

3) typically of PN63



Flange to the old DIN standard are compatible to the new DIN EN 1092-1.
Change in pressure rating: old DIN standards PN64 → DIN EN 1092-1 PN63.


Height of raised face

Dimensions in mm (in).

Standard	Flange	Height of raised face f	Tolerance
DIN EN 1092-1:2002-06	all types	2 (0.08)	0 -1 (-0.04)
DIN EN 1092-1:2007	≤ DN 32	2 (0.08)	0 -1 (-0.04)
	> DN 32 up to DN 250	3 (0.12)	0 -2 (-0.08)
	> DN 250 up to DN 500	4 (0.16)	0 -3 (-0.12)
	> DN 500	5 (0.19)	0 -4 (-0.16)
ASME B16.5-2013	≤ Class 300	1.6 (0.06)	±0.75 (±0.03)
	≥ Class 600	6.4 (0.25)	±0.5 (±0.02)
JIS B2220:2004	< DN 20	1.5 (0.06) 0	-
	> DN 20 up to DN 50	2 (0.08) 0	
	> DN 50	3 (0.12) 0	

Mechanical Construction

DIN flanges (DIN 2527)



A0029176

(Raised face DIN 2526 form C)

- L* Diameter of holes
- d* Raised face diameter
- K* Diameter of hole circle
- D* Flange diameter
- b* Total flange thickness
- f* Raised face height (general 2 mm (0.08 in))

PN10

In following tables, the dimensions are indicated in mm (in) unless otherwise noted.

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	16 (0.63)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.23 (2.71)
32	140 (5.51)	16 (0.63)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	1.80 (3.97)
40	150 (5.91)	16 (0.63)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.09 (4.61)
50	165 (6.50)	18 (0.71)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	2.88 (6.35)
65	185 (7.28)	18 (0.71)	145 (5.71)	122 (4.80)	4xØ18 (0.71)	3.70 (8.16)
80	200 (7.87)	20 (0.79)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	4.83 (10.65)
100	220 (8.66)	20 (0.79)	180 (7.09)	158 (6.22)	8xØ18 (0.71)	5.75 (12.68)
125	250 (9.84)	22 (0.87)	210 (8.27)	188 (7.40)	8xØ18 (0.71)	8.59 (18.94)
150	285 (11.2)	22 (0.87)	240 (9.45)	212 (8.35)	8xØ22 (0.87)	10.6 (23.37)
175	315 (12.4)	24 (0.94)	270 (10.6)	242 (9.53)	8xØ22 (0.87)	14.3 (31.53)
200	340 (13.4)	24 (0.94)	295 (11.6)	268 (10.6)	8xØ22 (0.87)	16.9 (37.26)
250	395 (15.6)	26 (1.02)	350 (13.8)	320 (12.6)	12xØ22 (0.87)	24.7 (54.46)
300	445 (17.5)	26 (1.02)	400 (15.7)	370 (14.6)	12xØ22 (0.87)	31.9 (70.34)

PN16

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	16 (0.63)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.23 (2.71)
32	140 (5.51)	16 (0.63)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	1.80 (3.97)
40	150 (5.91)	16 (0.63)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.09 (4.61)
50	165 (6.50)	18 (0.71)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	2.88 (6.35)
65	185 (7.28)	18 (0.71)	145 (5.71)	122 (4.80)	4xØ18 (0.71)	3.70 (8.16)
80	200 (7.87)	20 (0.79)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	4.83 (10.65)
100	220 (8.66)	20 (0.79)	180 (7.09)	158 (6.22)	8xØ18 (0.71)	5.75 (12.68)
125	250 (9.84)	22 (0.87)	210 (8.27)	188 (7.40)	8xØ18 (0.71)	8.59 (18.94)
150	285 (11.2)	22 (0.87)	240 (9.45)	212 (8.35)	8xØ22 (0.87)	10.6 (23.37)
175	315 (12.4)	24 (0.94)	270 (10.6)	242 (9.53)	8xØ22 (0.87)	14.3 (31.53)
200	340 (13.4)	24 (0.94)	295 (11.6)	268 (10.6)	12xØ22 (0.87)	16.5 (36.38)
250	405 (15.9)	26 (1.02)	355 (14.0)	320 (12.6)	12xØ26 (1.02)	25.6 (56.45)
300	460 (18.1)	28 (1.10)	410 (16.1)	378 (14.9)	12xØ26 (1.02)	36.1 (79.60)

PN25

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.38 (3.04)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.03 (4.48)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.35 (5.18)
50	165 (6.50)	20 (0.79)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.20 (7.06)
65	185 (7.28)	22 (0.87)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	4.33 (9.55)
80	200 (7.87)	24 (0.94)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	5.94 (13.1)
100	235 (9.25)	24 (0.94)	190 (7.48)	162 (6.38)	8xØ22 (0.87)	7.64 (16.85)
125	270 (10.6)	26 (1.02)	220 (8.66)	188 (7.40)	8xØ26 (1.02)	11.0 (24.26)
150	300 (11.8)	28 (1.10)	250 (9.84)	218 (8.58)	8xØ26 (1.02)	14.7 (32.41)
175	330 (13.0)	28 (1.10)	280 (11.0)	248 (9.76)	12xØ26 (1.02)	17.6 (38.81)
200	360 (14.2)	30 (1.18)	310 (12.2)	278 (10.9)	12xØ26 (1.02)	22.7 (50.05)
250	425 (16.7)	32 (1.26)	370 (14.6)	335 (13.2)	12xØ30 (1.18)	34.2 (75.41)
300	485 (19.1)	34 (1.34)	430 (17.0)	395 (15.6)	16xØ30 (1.18)	47.3 (104.3)

PN40

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.38 (3.04)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.03 (4.48)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.35 (5.18)
50	165 (6.50)	20 (0.79)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.20 (7.06)
65	185 (7.28)	22 (0.87)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	4.33 (9.55)
80	200 (7.87)	24 (0.94)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	5.94 (13.1)
100	235 (9.25)	24 (0.94)	190 (7.48)	162 (6.38)	8xØ22 (0.87)	7.64 (16.85)
125	270 (10.6)	26 (1.02)	220 (8.66)	188 (7.40)	8xØ26 (1.02)	11.0 (24.26)
150	300 (11.8)	28 (1.10)	250 (9.84)	218 (8.58)	8xØ26 (1.02)	14.7 (32.41)
175	350 (13.8)	32 (1.26)	295 (11.6)	260 (10.2)	12xØ30 (1.18)	22.4 (49.39)
200	375 (14.8)	34 (1.34)	320 (12.6)	285 (11.2)	12xØ30 (1.18)	27.6 (60.86)
250	450 (17.7)	38 (1.50)	385 (15.2)	345 (13.6)	12xØ33 (1.30)	44.5 (98.12)
300	515 (20.3)	42 (1.65)	450 (17.7)	410 (16.1)	16xØ33 (1.30)	64.3 (141.8)


PN64

DN	D	b	K	d	L	approx. kg (lbs)
25	140 (5.51)	24 (0.94)	100 (3.94)	68 (2.68)	4xØ18 (0.71)	2.65 (5.84)
32	155 (6.10)	24 (0.94)	110 (4.33)	78 (3.07)	4xØ22 (0.87)	3.24 (7.14)
40	170 (6.69)	26 (1.02)	125 (4.92)	88 (3.46)	4xØ22 (0.87)	4.09 (9.02)
50	180 (7.09)	26 (1.02)	135 (5.31)	102 (4.02)	4xØ22 (0.87)	4.51 (9.94)
65	205 (8.07)	26 (1.02)	160 (6.30)	122 (4.80)	8xØ22 (0.87)	5.71 (12.59)
80	215 (8.46)	28 (1.10)	170 (6.69)	138 (5.43)	8xØ22 (0.87)	6.92 (15.26)
100	250 (9.84)	30 (1.18)	200 (7.87)	162 (6.38)	8xØ26 (1.02)	10.1 (22.27)
125	295 (11.6)	34 (1.34)	240 (9.45)	188 (7.40)	8xØ30 (1.18)	16.0 (35.28)
150	345 (13.6)	36 (1.42)	280 (11.0)	218 (8.58)	8xØ33 (1.30)	23.5 (51.82)
175	375 (14.8)	40 (1.57)	310 (12.2)	260 (10.2)	12xØ33 (1.30)	30.8 (67.91)
200	415 (16.3)	42 (1.65)	345 (13.6)	285 (11.2)	12xØ36 (1.42)	39.7 (87.54)
250	470 (18.5)	46 (1.81)	400 (15.7)	345 (13.6)	12xØ36 (1.42)	57.4 (126.6)
300	530 (20.9)	52 (2.05)	460 (18.1)	410 (16.1)	16xØ36 (1.42)	81.0 (178.6)

PN100

DN	D	b	K	d	L	approx. kg (lbs)
25	140 (5.51)	24 (0.94)	100 (3.94)	68 (2.68)	4xØ18 (0.71)	2.65 (5.84)
32	155 (6.10)	24 (0.94)	110 (4.33)	78 (3.07)	4xØ22 (0.87)	3.24 (7.14)
40	170 (6.69)	26 (1.02)	125 (4.92)	88 (3.46)	4xØ22 (0.87)	4.09 (9.02)
50	195 (7.68)	28 (1.10)	145 (5.71)	102 (4.02)	4xØ26 (1.02)	5.84 (12.88)
65	220 (8.66)	30 (1.18)	170 (6.69)	122 (4.80)	8xØ26 (1.02)	8.03 (17.71)
80	230 (9.06)	32 (1.26)	180 (7.09)	138 (5.43)	8xØ26 (1.02)	9.43 (20.79)
100	265 (10.4)	36 (1.42)	210 (8.27)	162 (6.38)	8xØ30 (1.18)	14.3 (31.53)
125	315 (12.4)	40 (1.57)	250 (9.84)	188 (7.40)	8xØ33 (1.30)	22.6 (49.83)
150	355 (14.0)	44 (1.73)	290 (11.4)	218 (8.58)	12xØ33 (1.30)	31.8 (70.12)
175	385 (15.2)	48 (1.89)	320 (12.6)	260 (10.2)	12xØ33 (1.30)	41.3 (91.07)
200	430 (16.9)	52 (2.05)	360 (14.2)	285 (11.2)	12xØ36 (1.42)	56.1 (123.7)
250	505 (19.9)	60 (2.36)	430 (16.9)	345 (13.6)	12xØ39 (1.54)	89.6 (197.6)
300	585 (23.0)	68 (2.68)	500 (19.7)	410 (16.1)	16xØ42 (1.65)	119 (262.4)

EN flanges (DIN EN 1092-1)



A0029176

(Raised face B1)

L Diameter of holes

d Raised face diameter

K Diameter of hole circle

D Flange diameter

b Total flange thickness

f Raised face height (general 2 mm (0.08 in))

PN16

In following tables, the dimensions are indicated in mm (in) unless otherwise noted.

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.00 (4.41)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.50)	18 (0.71)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	2.90 (6.39)
65	185 (7.28)	18 (0.71)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	3.50 (7.72)
80	200 (7.87)	20 (0.79)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	4.50 (9.92)
100	220 (8.66)	20 (0.79)	180 (7.09)	158 (6.22)	8xØ18 (0.71)	5.50 (12.13)
125	250 (9.84)	22 (0.87)	210 (8.27)	188 (7.40)	8xØ18 (0.71)	8.00 (17.64)
150	285 (11.2)	22 (0.87)	240 (9.45)	212 (8.35)	8xØ22 (0.87)	10.5 (23.15)
200	340 (13.4)	24 (0.94)	295 (11.6)	268 (10.6)	12xØ22 (0.87)	16.5 (36.38)
250	405 (15.9)	26 (1.02)	355 (14.0)	320 (12.6)	12xØ26 (1.02)	25.0 (55.13)
300	460 (18.1)	28 (1.10)	410 (16.1)	378 (14.9)	12xØ26 (1.02)	35.0 (77.18)

PN25

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.00 (4.41)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.50)	20 (0.79)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.00 (6.62)
65	185 (7.28)	22 (0.87)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	4.50 (9.92)
80	200 (7.87)	24 (0.94)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	5.50 (12.13)
100	235 (9.25)	24 (0.94)	190 (7.48)	162 (6.38)	8xØ22 (0.87)	7.50 (16.54)
125	270 (10.6)	26 (1.02)	220 (8.66)	188 (7.40)	8xØ26 (1.02)	11.0 (24.26)
150	300 (11.8)	28 (1.10)	250 (9.84)	218 (8.58)	8xØ26 (1.02)	14.5 (31.97)
200	360 (14.2)	30 (1.18)	310 (12.2)	278 (10.9)	12xØ26 (1.02)	22.5 (49.61)
250	425 (16.7)	32 (1.26)	370 (14.6)	335 (13.2)	12xØ30 (1.18)	33.5 (73.9)
300	485 (19.1)	34 (1.34)	430 (16.9)	395 (15.6)	16xØ30 (1.18)	46.5 (102.5)

PN40


DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.00 (4.41)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.50)	20 (0.79)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.00 (6.62)
65	185 (7.28)	22 (0.87)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	4.50 (9.92)
80	200 (7.87)	24 (0.94)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	5.50 (12.13)
100	235 (9.25)	24 (0.94)	190 (7.48)	162 (6.38)	8xØ22 (0.87)	7.50 (16.54)
125	270 (10.6)	26 (1.02)	220 (8.66)	188 (7.40)	8xØ26 (1.02)	11.0 (24.26)
150	300 (11.8)	28 (1.10)	250 (9.84)	218 (8.58)	8xØ26 (1.02)	14.5 (31.97)
200	375 (14.8)	36 (1.42)	320 (12.6)	285 (11.2)	12xØ30 (1.18)	29.0 (63.95)
250	450 (17.7)	38 (1.50)	385 (15.2)	345 (13.6)	12xØ33 (1.30)	44.5 (98.12)
300	515 (20.3)	42 (1.65)	450 (17.7)	410 (16.1)	16xØ33 (1.30)	64.0 (141.1)

PN63

DN	D	b	K	d	L	approx. kg (lbs)
25	140 (5.51)	24 (0.94)	100 (3.94)	68 (2.68)	4xØ18 (0.71)	2.50 (5.51)
32	155 (6.10)	24 (0.94)	110 (4.33)	78 (3.07)	4xØ22 (0.87)	3.50 (7.72)
40	170 (6.69)	26 (1.02)	125 (4.92)	88 (3.46)	4xØ22 (0.87)	4.50 (9.92)
50	180 (7.09)	26 (1.02)	135 (5.31)	102 (4.02)	4xØ22 (0.87)	5.00 (11.03)
65	205 (8.07)	26 (1.02)	160 (6.30)	122 (4.80)	8xØ22 (0.87)	6.00 (13.23)
80	215 (8.46)	28 (1.10)	170 (6.69)	138 (5.43)	8xØ22 (0.87)	7.50 (16.54)
100	250 (9.84)	30 (1.18)	200 (7.87)	162 (6.38)	8xØ26 (1.02)	10.5 (23.15)
125	295 (11.6)	34 (1.34)	240 (9.45)	188 (7.40)	8xØ30 (1.18)	16.5 (36.38)
150	345 (13.6)	36 (1.42)	280 (11.0)	218 (8.58)	8xØ33 (1.30)	24.5 (54.02)
200	415 (16.3)	42 (1.65)	345 (13.6)	285 (11.2)	12xØ36 (1.42)	40.5 (89.3)
250	470 (18.5)	46 (1.81)	400 (15.7)	345 (13.6)	12xØ36 (1.42)	58.0 (127.9)
300	530 (20.9)	52 (2.05)	460 (18.1)	410 (16.1)	16xØ36 (1.42)	83.5 (184.1)

PN100

DN	D	b	K	d	L	approx. kg (lbs)
25	140 (5.51)	24 (0.94)	100 (3.94)	68 (2.68)	4xØ18 (0.71)	2.50 (5.51)
32	155 (6.10)	24 (0.94)	110 (4.33)	78 (3.07)	4xØ22 (0.87)	3.50 (7.72)
40	170 (6.69)	26 (1.02)	125 (4.92)	88 (3.46)	4xØ22 (0.87)	4.50 (9.92)
50	195 (7.68)	28 (1.10)	145 (5.71)	102 (4.02)	4xØ26 (1.02)	6.00 (13.23)
65	220 (8.66)	30 (1.18)	170 (6.69)	122 (4.80)	8xØ26 (1.02)	8.00 (17.64)
80	230 (9.06)	32 (1.26)	180 (7.09)	138 (5.43)	8xØ26 (1.02)	9.50 (20.95)
100	265 (10.4)	36 (1.42)	210 (8.27)	162 (6.38)	8xØ30 (1.18)	14.0 (30.87)
125	315 (12.4)	40 (1.57)	250 (9.84)	188 (7.40)	8xØ33 (1.30)	22.5 (49.61)
150	355 (14.0)	44 (1.73)	290 (11.4)	218 (8.58)	12xØ33 (1.30)	30.5 (67.25)
200	430 (16.9)	52 (2.05)	360 (14.2)	285 (11.2)	12xØ36 (1.42)	54.5 (120.2)
250	505 (19.9)	60 (2.36)	430 (16.9)	345 (13.6)	12xØ39 (1.54)	87.5 (192.9)
300	585 (23.0)	68 (2.68)	500 (19.7)	410 (16.1)	16xØ42 (1.65)	131.5 (289.9)

ASME-Flange (ASME B16.5-2013)

0029175

*(Raised face RF)**L Diameter of holes**d Raised face diameter**K Diameter of hole circle**D Flange diameter**b Total flange thickness**f Raised face height Class 150/300: 1.6 mm (0.06 in) or from Class 600: 6.4 mm (0.25 in)***Note!**Surface finish of the gasket faces $R_a \leq 3.2$ to $6.3 \mu\text{m}$ (126 to 248 μin).**Class 150**

In following tables, the dimensions are indicated in mm (in) unless otherwise noted.

NPS (Nominal pipe size)	D	b	K	d	L	approx. kg (lbs)
1"	108.0 (4.25)	14.2 (0.56)	79.2 (3.12)	50.8 (2.00)	4x $\varnothing$ 15.7 (0.62)	0.86 (1.9)
1¼"	117.3 (4.62)	15.7 (0.62)	88.9 (3.50)	63.5 (2.50)	4x $\varnothing$ 15.7 (0.62)	1.17 (2.58)
1½"	127.0 (5.00)	17.5 (0.69)	98.6 (3.88)	73.2 (2.88)	4x $\varnothing$ 15.7 (0.62)	1.53 (3.37)
2"	152.4 (6.00)	19.1 (0.75)	120.7 (4.75)	91.9 (3.62)	4x $\varnothing$ 19.1 (0.75)	2.42 (5.34)
2½"	177.8 (7.00)	22.4 (0.88)	139.7 (5.50)	104.6 (4.12)	4x $\varnothing$ 19.1 (0.75)	3.94 (8.69)
3"	190.5 (7.50)	23.9 (0.94)	152.4 (6.00)	127.0 (5.00)	4x $\varnothing$ 19.1 (0.75)	4.93 (10.87)
3½"	215.9 (8.50)	23.9 (0.94)	177.8 (7.00)	139.7 (5.50)	8x $\varnothing$ 19.1 (0.75)	6.17 (13.60)
4"	228.6 (9.00)	23.9 (0.94)	190.5 (7.50)	157.2 (6.19)	8x $\varnothing$ 19.1 (0.75)	7.00 (15.44)
5"	254.0 (10.0)	23.9 (0.94)	215.9 (8.50)	185.7 (7.31)	8x $\varnothing$ 22.4 (0.88)	8.63 (19.03)
6"	279.4 (11.0)	25.4 (1.00)	241.3 (9.50)	215.9 (8.50)	8x $\varnothing$ 22.4 (0.88)	11.3 (24.92)
8"	342.9 (13.5)	28.4 (1.12)	298.5 (11.8)	269.7 (10.6)	8x $\varnothing$ 22.4 (0.88)	19.6 (43.22)
10"	406.4 (16.0)	30.2 (1.19)	362.0 (14.3)	323.8 (12.7)	12x $\varnothing$ 25.4 (1.00)	28.8 (63.50)

Class 300

NPS (Nominal pipe size)	D	b	K	d	L	approx. kg (lbs)
1"	124.0 (4.88)	17.5 (0.69)	88.9 (3.50)	50.8 (2.00)	4xØ19.1 (0.75)	1.39 (3.06)
1¼"	133.4 (5.25)	19.1 (0.75)	98.6 (3.88)	63.5 (2.50)	4xØ19.1 (0.75)	1.79 (3.95)
1½"	155.4 (6.12)	20.6 (0.81)	114.3 (4.50)	73.2 (2.88)	4xØ22.4 (0.88)	2.66 (5.87)
2"	165.1 (6.50)	22.4 (0.88)	127.0 (5.00)	91.9 (3.62)	8xØ19.1 (0.75)	3.18 (7.01)
2½"	190.5 (7.50)	25.4 (1.00)	149.4 (5.88)	104.6 (4.12)	8xØ22.4 (0.88)	4.85 (10.69)
3"	209.5 (8.25)	28.4 (1.12)	168.1 (6.62)	127.0 (5.00)	8xØ22.4 (0.88)	6.81 (15.02)
3½"	228.6 (9.00)	30.2 (1.19)	184.2 (7.25)	139.7 (5.50)	8xØ22.4 (0.88)	8.71 (19.21)
4"	254.0 (10.0)	31.8 (1.25)	200.2 (7.88)	157.2 (6.19)	8xØ22.4 (0.88)	11.5 (25.36)
5"	279.4 (11.0)	35.1 (1.38)	235.0 (9.25)	185.7 (7.31)	8xØ22.4 (0.88)	15.6 (34.4)
6"	317.5 (12.5)	36.6 (1.44)	269.7 (10.6)	215.9 (8.50)	12xØ22.4 (0.88)	20.9 (46.08)
8"	381.0 (15.0)	41.1 (1.62)	330.2 (13.0)	269.7 (10.6)	12xØ25.4 (1.00)	34.3 (75.63)
10"	444.5 (17.5)	47.8 (1.88)	387.4 (15.3)	323.8 (12.7)	16xØ28.4 (1.12)	53.3 (117.5)

Class 600

NPS (Nominal pipe size)	D	b	K	d	L	approx. kg (lbs)
1"	124.0 (4.88)	17.5 (0.69)	88.9 (3.50)	50.8 (2.00)	4xØ19.1 (0.75)	1.60 (3.53)
1¼"	133.4 (5.25)	20.6 (0.81)	98.6 (3.88)	63.5 (2.50)	4xØ19.1 (0.75)	2.23 (4.92)
1½"	155.4 (6.12)	22.4 (0.88)	114.3 (4.50)	73.2 (2.88)	4xØ22.4 (0.88)	3.25 (7.17)
2"	165.1 (6.50)	25.4 (1.00)	127.0 (5.00)	91.9 (3.62)	8xØ19.1 (0.75)	4.15 (9.15)
2½"	190.5 (7.50)	28.4 (1.12)	149.4 (5.88)	104.6 (4.12)	8xØ22.4 (0.88)	6.13 (13.52)
3"	209.5 (8.25)	31.8 (1.25)	168.1 (6.62)	127.0 (5.00)	8xØ22.4 (0.88)	8.44 (18.61)
3½"	228.6 (9.00)	35.1 (1.38)	184.2 (7.25)	139.7 (5.50)	8xØ25.4 (1.00)	11.0 (24.26)
4"	273.1 (10.8)	38.1 (1.50)	215.9 (8.50)	157.2 (6.19)	8xØ25.4 (1.00)	17.3 (38.15)
5"	330.2 (13.0)	44.5 (1.75)	266.7 (10.5)	185.7 (7.31)	8xØ28.4 (1.12)	29.4 (64.83)
6"	355.6 (14.0)	47.8 (1.88)	292.1 (11.5)	215.9 (8.50)	12xØ28.4 (1.12)	36.1 (79.6)
8"	419.1 (16.5)	55.6 (2.19)	349.3 (13.8)	269.7 (10.6)	12xØ31.8 (1.25)	58.9 (129.9)
10"	508.0 (20.0)	63.5 (2.50)	431.8 (17.0)	323.8 (12.7)	16xØ35.1 (1.38)	97.5 (214.9)


Class 900

NPS (Nominal pipe size)	D	b	K	d	L	approx. kg (lbs)
1"	149.4 (5.88)	28.4 (1.12)	101.6 (4.00)	50.8 (2.00)	4xØ25.4 (1.00)	3.57 (7.87)
1¼"	158.8 (6.25)	28.4 (1.12)	111.3 (4.38)	63.5 (2.50)	4xØ25.4 (1.00)	4.14 (9.13)
1½"	177.8 (7.00)	31.8 (1.25)	124.0 (4.88)	73.2 (2.88)	4xØ28.4 (1.12)	5.75 (12.68)
2"	215.9 (8.50)	38.1 (1.50)	165.1 (6.50)	91.9 (3.62)	8xØ25.4 (1.00)	10.1 (22.27)
2½"	244.4 (9.62)	41.1 (1.62)	190.5 (7.50)	104.6 (4.12)	8xØ28.4 (1.12)	14.0 (30.87)
3"	241.3 (9.50)	38.1 (1.50)	190.5 (7.50)	127.0 (5.00)	8xØ25.4 (1.00)	13.1 (28.89)
4"	292.1 (11.50)	44.5 (1.75)	235.0 (9.25)	157.2 (6.19)	8xØ31.8 (1.25)	26.9 (59.31)
5"	349.3 (13.8)	50.8 (2.00)	279.4 (11.0)	185.7 (7.31)	8xØ35.1 (1.38)	36.5 (80.48)
6"	381.0 (15.00)	55.6 (2.19)	317.5 (12.5)	215.9 (8.50)	12xØ31.8 (1.25)	47.4 (104.5)
8"	469.9 (18.50)	63.5 (2.50)	393.7 (15.5)	269.7 (10.6)	12xØ38.1 (1.50)	82.5 (181.9)
10"	546.1 (21.50)	69.9 (2.75)	469.9 (18.5)	323.8 (12.7)	16xØ38.1 (1.50)	122 (269.0)

Class 1500

NPS (Nominal pipe size)	D	b	K	d	L	approx. kg (lbs)
1"	149.4 (5.88)	28.4 (1.12)	101.6 (4.00)	50.8 (2.00)	4xØ25.4 (1.00)	3.57 (7.87)
1¼"	158.8 (6.25)	28.4 (1.12)	111.3 (4.38)	63.5 (2.50)	4xØ25.4 (1.00)	4.14 (9.13)
1½"	177.8 (7.00)	31.8 (1.25)	124.0 (4.88)	73.2 (2.88)	4xØ28.4 (1.12)	5.75 (12.68)
2"	215.9 (8.50)	38.1 (1.50)	165.1 (6.50)	91.9 (3.62)	8xØ25.4 (1.00)	10.1 (22.27)
2½"	244.4 (9.62)	41.1 (1.62)	190.5 (7.50)	104.6 (4.12)	8xØ28.4 (1.12)	14.0 (30.87)
3"	266.7 (10.50)	47.8 (1.88)	203.2 (8.00)	127.0 (5.00)	8xØ31.8 (1.25)	19.1 (42.12)
4"	311.2 (12.3)	53.8 (2.12)	241.3 (9.50)	157.2 (6.19)	8xØ35.1 (1.38)	29.9 (65.93)
5"	374.7 (14.8)	73.2 (2.88)	292.1 (11.5)	185.7 (7.31)	8xØ41.1 (1.62)	58.4 (128.8)
6"	393.7 (15.50)	82.6 (3.25)	317.5 (12.5)	215.9 (8.50)	12xØ38.1 (1.50)	71.8 (158.3)
8"	482.6 (19.00)	91.9 (3.62)	393.7 (15.5)	269.7 (10.6)	12xØ44.5 (1.75)	122 (269.0)
10"	584.2 (23.00)	108.0 (4.25)	482.6 (19.0)	323.8 (12.7)	12xØ50.8 (2.00)	210 (463.0)

JIS flanges (B 2220)



A0029174

(Raised face RF)

L Diameter of holes*d* Raised face diameter*K* Diameter of hole circle*D* Flange diameter*b* Total flange thickness*f* Raised face height (general 2 mm (0.08 in))

Note!

Surface finish of the gasket faces $R_a \leq 3.2$ to $6.3 \mu\text{m}$ (126 to $248 \mu\text{in}$).

10 K

In following tables, the dimensions are indicated in mm (in) unless otherwise noted.

DN	D	b	K	d	L
25	125 (4.92)	14 (0.55)	90 (3.54)	67 (2.64)	4xØ19 (0.75)
32	135 (5.31)	16 (0.63)	100 (3.94)	76 (2.99)	4xØ19 (0.75)
40	140 (5.51)	16 (0.63)	105 (4.13)	81 (3.19)	4xØ19 (0.75)
50	155 (6.10)	16 (0.63)	120 (4.72)	96 (3.78)	4xØ19 (0.75)
65	175 (6.89)	18 (0.71)	140 (5.51)	116 (4.57)	4xØ19 (0.75)
80	185 (7.28)	18 (0.71)	150 (5.91)	126 (4.96)	8xØ19 (0.75)
100	210 (8.27)	18 (0.71)	175 (6.89)	151 (5.94)	8xØ19 (0.75)
125	250 (9.84)	20 (0.79)	210 (8.27)	182 (7.17)	8xØ23 (0.91)
150	280 (11.0)	22 (0.87)	240 (9.45)	212 (8.35)	8xØ23 (0.91)
200	330 (13.0)	22 (0.87)	290 (11.4)	262 (10.3)	12xØ23 (0.91)
250	400 (15.7)	24 (0.94)	355 (14.0)	324 (12.8)	12xØ25 (0.98)
300	445 (17.5)	24 (0.94)	400 (15.7)	368 (14.5)	16xØ25 (0.98)

20 K


DN	D	b	K	d	L
25	125 (4.92)	16 (0.63)	90 (3.54)	67 (2.64)	4xØ19 (0.75)
32	135 (5.31)	18 (0.71)	100 (3.94)	76 (2.99)	4xØ19 (0.75)
40	140 (5.51)	18 (0.71)	105 (4.13)	81 (3.19)	4xØ19 (0.75)
50	155 (6.10)	18 (0.71)	120 (4.72)	96 (3.78)	8xØ19 (0.75)
65	175 (6.89)	20 (0.79)	140 (5.51)	116 (4.57)	8xØ19 (0.75)
80	200 (7.87)	22 (0.87)	160 (6.30)	132 (5.20)	8xØ23 (0.91)
100	225 (8.86)	24 (0.94)	185 (7.28)	160 (6.30)	8xØ23 (0.91)
125	270 (10.6)	26 (1.02)	225 (8.86)	195 (7.68)	8xØ25 (0.98)
150	305 (12.0)	28 (1.10)	260 (10.2)	230 (9.06)	12xØ25 (0.98)
200	350 (13.8)	30 (1.18)	305 (12.0)	275 (10.8)	12xØ25 (0.98)
250	430 (16.9)	34 (1.34)	380 (15.0)	345 (13.6)	12xØ27 (1.06)
300	480 (18.9)	36 (1.42)	430 (16.9)	395 (15.6)	16xØ27 (1.06)

63 K

DN	D	b	K	d	L
25	140 (5.51)	27 (1.06)	100 (3.94)	70 (2.76)	4xØ23 (0.91)
32	150 (5.91)	30 (1.18)	110 (4.33)	80 (3.15)	4xØ23 (0.91)
40	175 (6.89)	32 (1.26)	130 (5.12)	90 (3.54)	4xØ25 (0.98)
50	185 (7.28)	34 (1.34)	145 (5.71)	105 (4.13)	8xØ23 (0.91)
65	220 (8.66)	38 (1.50)	175 (6.89)	130 (5.12)	8xØ25 (0.98)
80	230 (9.06)	40 (1.57)	185 (7.28)	140 (5.51)	8xØ25 (0.98)
100	270 (10.6)	44 (1.73)	220 (8.66)	165 (6.50)	8xØ27 (1.06)
125	325 (12.8)	50 (1.97)	265 (10.4)	200 (7.87)	8xØ33 (1.30)
150	365 (14.4)	54 (2.13)	305 (12.0)	240 (9.45)	12xØ33 (1.30)
200	425 (16.7)	60 (2.36)	360 (14.2)	290 (11.4)	12xØ33 (1.30)
250	500 (19.7)	68 (2.68)	430 (16.9)	355 (14.0)	12xØ39 (1.54)
300	560 (22.0)	77 (3.03)	485 (19.1)	410 (16.1)	16xØ39 (1.54)

Adapter flange FAU70

An adapter flange makes it possible to use devices with a threaded connection.



A0029173

- 1 Adapter flange
2 Nozzle
3 Probe

FAU70E Version with metrical thread

Order information

010	Process Connection	
12	DN 50 PN16 A, flange EN 1092-1 (DIN 2527 B)	
14	DN 80 PN16 A, flange EN 1092-1 (DIN 2527 B)	
15	DN 100 PN16 A, flange EN 1092-1 (DIN 2527 B)	
99	Special version, to be specified	
020	Sensor Connection	
3	Thread ISO228 G1-1/2	
4	Thread ISO228 G2	
99	Special version, to be specified	
030	Flange Material	
2	316L	
3	Steel	
7	Polypropylene	
99	Special version, to be specified	

The versions entered make up the order code:

	010	020	030
FAU70E -			

FAU70A Version with conical thread


010	Process Connection	
22	2" 150 lbs FF, flange ANSI B16.5	
24	3" 150 lbs FF, flange ANSI B16.5	
25	4" 150 lbs FF, flange ANSI B16.5	
99	Special version, to be specified	
020	Sensor Connection	
5	Thread NPT1-1/2	
6	Thread NPT2	
99	Special version, to be specified	
030	Flange Material	
2	316L	
3	Steel	
7	Polypropylene	
99	Special version, to be specified	

The versions entered make up the order code:

	010	020	030
FAU70A -			

Slip-on flange FAU80

The sensors (FDU91F, FDU80F, FDU81F) can be flush mounted using a FAU80 slip-on flange. Flanges in polypropylene (PP) should only used with pressures up to 1.5 bar_{abs} (22 psi) flanges in 316L also above.



Details to dimension "Mechanical Construction" → 38

A0029186

FAU80 Version slip-on flange

Order information

010	Process Connection	
	AA	3" 150 lbs FF, flange ANSI B16.5
	AH	4" 150 lbs FF, flange ANSI B16.5
	CA	DN 80 PN16 A, flange EN1092-1 (DIN2527 B)
	CH	DN 100 PN16 A, flange EN1092-1 (DIN2527 B)
	KA	10K 80A FF, flange JIS B2220
	KH	10K 100A FF, flange JIS B2220
	YY	Special version, to be specified
020	Flange Material	
	J	316L
	P	PPs, max. 1.5 bar abs
	Y	Special version, to be specified


The versions entered make up the order code:

	010	020
FAU80 -		

Screw in flange FAX50

The screw in flange is an universal flange. On the basis of dimensions min./max. it can be used for all three standards (DIN - ASME - JIS).

FAX50 universal flange DIN-ASME-JIS



A0029185

L Diameter of holes
K1, K2 Diameter of hole circle
D Flange diameter
b Total flange thickness
B Slotted hole (width)

G ¾", NPT ¾"

In following tables, the dimensions are indicated in mm (in) unless otherwise noted.

DN	D	b	L	K1	K2	approx. kg (lbs)		
						PP	PVDF	316L
50	165 (6.50)	20 (0.79)	4xØ19 (0.75)	120 (4.72)	125 (4.92)	–	–	3.11 (6.86)
80	200 (7.87)		8xØ19 (0.75)	150 (5.91)	160 (6.30)	–	–	4.37 (9.64)
100	228.6 (9.0)		8xØ19 (0.75)	175 (6.89)	190.5 (7.5)	–	–	5.79 (12.77)

G 1", NPT 1"

DN	D	b	L	K1	K2	approx. kg (lbs)		
						PP	PVDF	316L
80	200 (7.87)	20 (0.79)	8xØ19 (0.75)	150 (5.91)	160 (6.30)	0.50 (1.10)	0.97 (2.14)	4.34 (9.57)
100	228.6 (9.0)		8xØ19 (0.75)	175 (6.89)	190.5 (7.5)	0.66 (1.46)	1.29 (2.84)	5.75 (12.68)
150	285 (11.2)		8xØ23 (0.91)	240 (9.45)	241.3 (9.5)	1.09 (2.40)	2.12 (4.67)	9.44 (20.82)
200 ¹⁾	340 (13.4)		12xØ23 (0.91)	290 (11.4)	295 (11.6)	1.53 (3.37)	–	–
250	406.4 (16.0)		12xØ26 (1.02)	355 (14.0)	362 (14.3)	2.20 (4.85)	–	–

1) Only for DIN und JIS!

Exception G 1"

NPS (Nominal pipe size)	D	b	L	K1	K2	approx. kg (lbs)		
ASME						PP	PVDF	316L
8"	342.9 (13.5)	20 (0.79)	8xØ22.5 (0.89)	298.5 (11.8)	298.5 (11.8)	1.61 (3.55)	–	–

G 1½", NPT 1½"

DN	D	b	L	K1	K2	approx. kg (lbs)		
						PP	PVDF	316L
50	165 (6.50)	20 (0.79)	4xØ19 (0.75)	120 (4.72)	125 (4.92)	0.34 (0.75)	0.67 (1.48)	2.97 (6.55)
80	200 (7.87)		8xØ19 (0.75)	150 (5.91)	160 (6.30)	0.49 (1.08)	0.95 (2.09)	4.24 (9.35)
100	228.6 (9.0)		8xØ19 (0.75)	175 (6.89)	190.5 (7.5)	0.65 (1.43)	1.27 (2.80)	5.65 (12.46)
150	285 (11.2)		8xØ23 (0.91)	240 (9.45)	241.3 (9.5)	1.08 (2.38)	2.09 (4.61)	9.34 (20.59)

G 2", NPT 2"

DN	D	b	L	K1	K2	approx. kg (lbs)		
						PP	PVDF	316L
50	165 (6.50)	20 (0.79)	4xØ19 (0.75)	120 (4.72)	125 (4.92)	0.33 (0.73)	0.63 (1.39)	2.83 (6.24)
80	200 (7.87)		8xØ19 (0.75)	150 (5.91)	160 (6.30)	0.47 (1.04)	0.92 (2.03)	4.10 (9.04)
100	228.6 (9.0)		8xØ19 (0.75)	175 (6.89)	190.5 (7.5)	0.64 (1.41)	1.24 (2.73)	5.51 (12.15)
150	285 (11.2)		8xØ23 (0.91)	240 (9.45)	241.3 (9.5)	1.06 (2.34)	2.06 (4.54)	9.20 (20.29)

Order information FAX50

015	Material:	
	BR1	DN50 PN10/16 A, steel flange EN1092-1
	BS1	DN80 PN10/16 A, steel flange EN1092-1
	BT1	DN100 PN10/16 A, steel flange EN1092-1
	JF1	2" 150lbs FF, steel flange ANSI B16.5
	JG1	3" 150lbs FF, steel flange ANSI B16.5
	JH1	4" 150lbs FF, steel flange ANSI B16.5
	JK2	8" 150lbs FF, PP max 3 bar abs/44 psia flange ANSI B16.5
	XIF	UNI flange 2"/DN50/50, PVDF max 4 bar abs/58 psia, suitable for 2" 150 lbs/DN50 PN16/10K 50
	XIG	UNI flange 2"/DN50/50, PP max 4 bar abs/58 psia, suitable for 2" 150 lbs/DN50 PN16/10K 50
	XIJ	UNI flange 2"/DN50/50, 316L max 4 bar abs/58 psia, suitable for 2" 150 lbs/DN50 PN16/10K 50
	XJF	UNI flange 3"/DN80/80, PVDF max 4 bar abs/58 psia, suitable for 3" 150 lbs/DN80 PN16/10K 80
	XJG	UNI flange 3"/DN80/80, PP max 4 bar abs/58 psia, suitable for 3" 150 lbs/DN80 PN16/10K 80
	XJJ	UNI flange 3"/DN80/80, 316L max 4 bar abs/58 psia, suitable for 3" 150 lbs/DN80 PN16/10K 80
	XKF	UNI flange 4"/DN100/100, PVDF max 4 bar abs/58 psia, suitable for 4" 150 lbs/DN100 PN16/10K 100
	XKG	UNI flange 4"/DN100/100, PP max 4 bar abs/58 psia, suitable for 4" 150 lbs/DN100 PN16/10K 100
	XKJ	UNI flange 4"/DN100/100, 316L max 4 bar abs/58 psia, suitable for 4" 150 lbs/DN100 PN16/10K 100
	XLF	UNI flange 6"/DN150/150, PVDF max 4 bar abs/58 psia, suitable for 6" 150 lbs/DN150 PN16/10K 150
	XLG	UNI flange 6"/DN150/150, PP max 4 bar abs/58 psia, suitable for 6" 150 lbs/DN150 PN16/10K 150
	XLJ	UNI flange 6"/DN150/150, 316L max 4 bar abs/58 psia, suitable for 6" 150 lbs/DN150 PN16/10K 150
	XMG	UNI flange DN200/200, PP max 4 bar abs/58 psia, suitable for DN200 PN16/10K 200
	XNG	UNI flange DN250/250, PP max 4 bar abs/58 psia, suitable for DN250 PN16/10K 250
	YYY	Special version
020	Sensor Connection:	
	A	Thread ISO228 G3/4
	B	Thread ISO228 G1
	C	Thread ISO228 G1-1/2
	D	Thread ISO228 G2
	E	Thread ANSI NPT3/4
	F	Thread ANSI NPT1
	G	Thread ANSI NPT1-1/2
	H	Thread ANSI NPT2
	Y	Special version

The versions entered make up the order code:

	15	20
FAX50 -		

Pressure-temperature dependencies

EN flanges¹⁾

Temperature range	Nominal pressure bar (psi)				
	PN16	PN25	PN40	PN63	PN100
−10 °C ... +50 °C (+14 °F ... +122 °F)	16.0 (232)	25.0 (362)	40.0 (580)	63.0 (913)	100.0 (1450)
50 °C (122 °F)	15.5 (225)	24.3 (352)	38.9 (564)	61.3 (889)	97.3 (1411)
100 °C (212 °F)	15.1 (219)	23.6 (342)	37.9 (550)	59.7 (866)	94.7 (1373)
150 °C (302 °F)	13.7 (199)	21.5 (312)	34.4 (499)	54.3 (787)	86.1 (1248)
200 °C (392 °F)	12.7 (184)	19.8 (287)	31.8 (461)	50.1 (726)	79.5 (1153)
250 °C (482 °F)	11.9 (173)	18.6 (270)	29.9 (434)	47.1 (683)	74.7 (1083)
300 °C (572 °F)	11.0 (159)	17.2 (249)	27.6 (400)	43.5 (631)	69.0 (1000)
350 °C (662 °F)	10.5 (152)	16.5 (239)	26.4 (383)	41.7 (605)	66.1 (958)
400 °C (752 °F)	10.2 (148)	16.0 (232)	25.7 (373)	40.1 (580)	64.2 (931)

ASME flanges¹⁾

Temperature range	Nominal pressure bar (psi)				
	Class 150	Class 300	Class 600	Class 900	Class 1500
−29 °C ... +38 °C (−20 °F ... +100 °F)	19.0 (275)	49.6 (719)	99.3 (1440)	148.9 (2159)	248.2 (3599)
50 °C (122 °F)	18.4 (267)	48.1 (697)	96.2 (1395)	144.3 (2092)	240.6 (3489)
100 °C (212 °F)	16.2 (235)	42.2 (612)	84.4 (1224)	126.6 (1836)	211.0 (3059)
150 °C (302 °F)	14.8 (215)	38.5 (558)	77.0 (1116)	115.5 (1675)	192.5 (2791)
200 °C (392 °F)	13.7 (199)	35.7 (518)	71.3 (1034)	107.0 (1551)	178.3 (2588)
250 °C (482 °F)	12.1 (175)	33.4 (484)	66.8 (969)	100.1 (1451)	166.9 (2420)
300 °C (572 °F)	10.2 (148)	31.6 (458)	63.2 (916)	94.9 (1376)	158.1 (2292)
325 °C (617 °F)	9.3 (135)	30.9 (448)	61.8 (896)	92.7 (1344)	154.4 (2239)
350 °C (662 °F)	8.4 (122)	30.3 (439)	60.7 (880)	91.0 (1319)	151.6 (2189)
375 °C (707 °F)	7.4 (107)	29.9 (434)	59.8 (867)	89.6 (1299)	149.4 (2166)
400 °C (752 °F)	6.5 (94)	29.4 (426)	58.9 (854)	88.3 (1280)	147.2 (2134)

JIS flanges¹⁾

Temperature range	Nominal pressure bar (psi)			
	10 K	20 K		
	for all flanges	to DN 125	from DN 150 up to DN 250	DN 300
up to 120 °C (248 °F)	14 (203.0)	34 (493.0)	20 (290.0)	20 (290.0)
220 °C (428 °F)	12 (174.0)	31 (449.5)	20 (290.0)	–
300 °C (572 °F)	10 (145.0)	29 (420.5)	19 (275.5)	–
350 °C (662 °F)	–	26 (377.0)	17 (246.5)	–
400 °C (752 °F)	–	23 (333.5)	17 (246.5)	–
425 °C (797 °F)	–	20 (290.0)	17 (246.5)	–

1) With regard to their stability-temperature property, the materials 1.4435 and 1.4404 are grouped in DIN EN 1092-1 table 18 under 13E0 and in JIS B2220:2004 table 5 under 023b. The ASME flanges are dual rated flanges (316/316L) and grouped in table 2-2.2 according to ASME B16.5-2013.



www.addresses.endress.com
