

N

#### FISCO-Concept

ω

The FISCO Concept allows interconnection of intrinsically safe apparatus to associated apparatus not specifically examined in

The criteria for interconnection is that the voltage (Ui or Vmax), the current (Ii or Imax) and the power (Pi or Pmax) which intrinsically safe apparatus can receive and remain intrinsically safe, considering faults, must be equal or greater than the voltage (Uo or Voc or Vt), the current (Io or Isc or It) and the power (Po or Pmax) levels which can be delivered by the associated apparatus, considering faults and applicable factors. In addition, the maximum unprotected capacitance (Ci) and inductance (Li) of each apparatus (other than the termination) connected to the fieldbus must be less than or equal to 5 nF and 10 uH respectively.

In each segment only one active device, normally the associated apparatus is allowed to provide the necessary energy for the

The voltage Uo (or Voc or Vt) of the associated apparatus has to be limited to the range of 14V to 24V d.c. All other equipment connected to the bus cable has to be passive, meaning that they are not allowed to provide energy to the system, except to a leakage current of 50 µA for each connected device.

Separately powered equipment needs a galvanic isolation to assure that the intrinsically safe fieldbus circuit remains passive. The cable used to interconnect the devices has to meet the following values:

Loop resistance R': 15 ... 150  $\Omega$ /km, inductance L': 0.4 ... 1 mH/km capacitance C': 80 ... 200 nF/km

C' = C' line/line + 0.5 C' line/screen, if both lines are floating or

C'=C' line/line + C' line/screen, if the screen is connected to one line

Length of spur cable: 30 m length of trunk cable: 1 km length of splice: 1 m

At each end of the trunk cable an approved infallible line termination with the following parameters is suitable:

 $R = 90 ... 100 \Omega$   $C = 0 ... 2.2 \mu F$ .

One of the allowed terminations might already be integrated in the associated apparatus.

The number of passive devices connected to the bus segment is not limited due to I.S. reasons. If the above rules are respected, up to a total length of 1000 m (sum of the length of trunk cable and all spur cables), the inductance and capacitance of the cable will not impair the intrinsic safety of the installation.

## INTRINSICALLY SAFE

### Class I / Div. 1 / Groups ABCD

- CSA certified associated apparatus must meet the following requirements:
- Uo or Voc or Vt  $\leq$  Ui (Vmax) and Io or Isc or It  $\leq$  Ii (Imax) and Po or Pmax  $\leq$  Pi (Pmax)
- The maximum non-hazardous area voltage must not exceed 250 V.
- The installation must be in accordance with the Canadian Electrical Code.
- Be aware of multiple earthing of screen. The screen must be connected in accordance with Canadian Electrical Code.
- The polarity for connecting PA+ (1) and PA- (2) is of no importance due to an internal rectifier.

# Class I / Div. 2 / Groups ABCD Ex nA II

- Intrinsic safety barrier not required. Vmax ≤ 35 V DC.
- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous.
- Nonincendive field wiring installation

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or Associated Apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when  $Voc \le Vmax$ ,  $Ca \ge Ci + Ccable$ ,  $La \ge Li + Lcable$ .

Transmitter Nonincendive Field Wiring parameters are as follows: Ui or Vmax  $\leq$  35 V DC Ci  $\leq$  5 nF Li  $\leq$  10 µF For these current controlled circuits, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the Associated Nonincendive Field Wiring Apparatus or Associated Apparatus.

- Warning: Explosion Hazard- Do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous
- The transmitter is suitable to be installed according the FNICO concept.

ו כ		Approved	Date (yyyy-mm-dd)	Drawing No.	Dwg.rev.	Revision no.	Revision date (yyyy-mm-dd)	Name	Material	71540264		_	_
		Pfanzelt	2007-08-06	34 02 00 112	_	-	-	-			Endress+Ha	iuser 4로	<b>.</b>
	Volume (mm³)	Designed	Date (yyyy-mm-dd)	Unit iTEMP TMT85 FF	Scale	Title					]		
		Meroth	2007-03-06	iTEMP TMT84 PA	1:1	CONTRO	DL DRAWING	S CSA	Seri	es			
	Refer to protection notice	Edge of working parts	Geometrical tolerancing	Part No.	Format	IS, NI			Objekt version	Sheet	Endress + Haus		
	ISO 16016	ISO 13715	ISO 2768-mH-E	-	A4					1 of 1	GmbH+Co. KG Nes	selwang / Germany	

w

CD

U

 $\triangleright$ 

B

 $\cap$ 

O