

















Technical Information

Minilog RDL10

Measured value collector with 2 input channels for storing analog and digital values



Application

- Data storage for termperature, humidity, pressure, flow, level, and analysis values
- Temperature monitoring:
 Storage and transport temperature measurement
- Operation time recording
- Access monitoring
- Piece part and quantity monitoring
- Quantity recording by integrating the analog signal
- Where measured values are to be automatically recorded and stored
- Start analog value recording using an external digital control signal
- ON/OFF signals are stored using date and time and displayed in Readwin[®] 2000.

Your benefits

- Variable sensor connections using 0/4 to 20 mA, 0 to 1 V or Pt100 as well as potential free contact for event or count impulses
- \blacksquare Instantaneous value or min-, max-, average value recording
- Measured value storage always includes date and time
- Storage of up to 64,000 measured values
- Presettable storage cycle (1 minute up to 24 hours)
- Stand alone battery powered unit or for external power supply available
- Robust (IP 65 / NEMA 4), small and economical
- User friendly setting up and data analysis using the Readwin[®] 2000 software package
- Selectable display function



Function and system design

Measuring principle

The Minilog B, Version II data-logger records analog and digital measured values. The analog input signals can be 0/4 to 20 mA, 0 to 1 V and Pt100 resistive thermometers. In addition to the analog input there is also a digital input available. A potential free contact (or TTL-signal) can be connected to this input. This input records, for example, count impulses with a max. frequency of 25 Hz and 1 s at events.

Alternatively this input can be used to, for example, calculate the running time of a particular piece of equipment or machine.

The unit reads these values every second. From the values it calculated the instantaneous values or min, max and averages. The memory capacity is a max. 16,000 measured values (optionally max. 64,000 measured values) with a presettable storage cycle of 1 minute up to 24 hours.

Measuring system

analog: Data-logger Minilog B, Version II and separate transmitters in 0/4 to 20 mA, 0 to 1 V and Pt100 technology

digital: Data-logger Minilog B, Version II and potential free contact

Set points

In addition to recording the data the data-logger also monitors two set points. These set points can be set up using the Readwin $^{\otimes}$ 2000 software package. Any infringement of these values is indicated in the display. A choice of whether to record continuously or only in the case of a set point infringement (in the preset storage cycle) is available and can be set up.

Interface / Readwin® 2000 software

Minilog B, Version II data-logger can be simply and easily set up using the RS232 interface. Simple and safe setting up is made possible by using the on-line help text.


The Readwin® 2000 software package is delivered with the unit free of charge. Interface cables for connection to a PC or Modem can be purchased as accessories.

Data visualization

The recorded data can be read out, transmitted and displayed using the Readwin® 2000 software package.

The main features are:

- Common PC operating system
- Saving the unit settings in a database
- Instantaneous value display
- Min-/max-/average value display
- Quantities
- Events
- Read out of the values stored in the unit
- Measured value display in the form of traces, columns and tables
- Data export onto spread sheets (e.g. Excel, Lotus etc.)
- Printout of graphics, tables and unit parameters



Readwin® 2000 PC operating software

R09-RDL10xx-20-01-00-en-000

Input

Measured variable

Universal application

analog: transmitter must have 0/4 to 20 mA, 0 to 1 V output signal or direct Pt100. digital: potential free contact or TTL peak 5 $\rm V_{\rm DC}$



Note!

Minilog B, Version II has no loop power supply.


Power supply minus, GND connection (pin 4) of the interface, analog input minus (terminal 1) and terminal 5 of the digital input are internally connected.

Number of inputs

Analog input: 1 Digital input: 1

Power supply

Terminal assignment



Terminal assignment of the data-logger

Supply voltage

Lithium battery 3.6 V Type AA, optional Type C or external power supply 7 to 30 V_{DC} , approx. 5 mA

Battery life cycle

	Type AA (2.1 Ah)	Type C (7.2 Ah)
Monthly readout	min. 2 years	min. 5 years
Continuous readout	min. 1 month	min. 2 month

Terminals	Termination on 2.5 $\mathrm{mm^2}$ (14 AWG) terminals, 1.5 $\mathrm{mm^2}$ (16 AWG) core with ferrule.
Cable entries	Two-wire connection (three-wire on Pt100); connection access using $2x$ PG9 cable glands (optional $1x$ $\frac{1}{2}$ " NPT instead of $1x$ PG9)

Performance characteristics

Maximum measured error

Analog input	0 to 1 V, $R_i \ge 1$ M Ω Accuracy \pm 0.25 % FSD
	0/4 to 20 mA, via shunt, R_i = 50 Ω Cable open circuit monitor < 2 mA (on 4 to 20 mA) Accuracy \pm 0.25 % FSD
	Pt100, -100 to +400 mA, screened cable Accuracy \pm 0.5 °C (\pm 0.8 °F), cable open circuit monitor
Digital input	1 input using two terminals; $f_{\text{max}} = 25~\text{Hz}$ on pulses, 1 s on events; for potential free contact


Long-term drift	Time drift \pm 50 ppm (\leq 30 min/year)
Influence of ambient temperature	Temperature drift \pm 0.25 % / 10 K (\pm 0.14 % / 10 °F)

Installation

Orientation	The unit should be mounted	vertically, for this a wal	If or stand pipe mounting kit can be ordered.	


Mounting kit

Wall mounting



Dimensions of the wall mounting plate

Stand pipe mounting



Dimensions of the stand pipe mounting plate

Environment

Electromagnetic compatibility	RF protection
Vibration resistance	IEC 654-3, v < 3 mm/s, 1 <f<150 hz<="" th=""></f<150>
Degree of protection	IP 65 / NEMA 4 with closed cover
Climate class	IEC 654 Part 1 Class C1
Storage temperature	-25 to +60 °C (-13 to 140 °F)
Ambient temperature range	-25 to +55 °C (-13 to 131 °F)


To EN 55011 Group 1, Class B

Interference safety

ESD	To EN 61000-4-2, Level 3, 6/8 kV
Electromagnetic fields	To EN 61000-4-3, Level 3, 10 V/m
Burst (supply cicuit)	To EN 61000-4-4, Level 3, 1 kV / 2 kV
Burst (signal circuit)	To EN 61000-4-4, Level 3, 1 kV
Surge HF discharge	To EN 61000-4-6, 10 V additional measurement accuracy \leq 0.5 %
Normal mode noise rejection	26 dB at input range/10, $f = 50/60$ Hz, not on resistance measurement

Mechanical construction

Design, dimensions



Dimensions of the data-logger

Weight

0.5 to 0.7 kg (1.1 to 1.5 lb), dependent on model

Materials

Transmitter housing

Aluminum die cast, surface galvanized

Accessories

Wall / stand pipe adapter: 1.4301 (304 SS)

Strap: 1.4301 (304 SS)

Operability


Operating concept

The device is operated using the Readwin® 2000 operating software.

Local operation

Display

LC display, 7 segment, prefix, decimal point, limit symbol, battery status symbol



Display of the data-logger

1 Limit symbol

Remote operation

 $Readwin^{\circledR}\ 2000\ software\ package\ for\ setting\ up,\ transmission\ and\ display\ of\ measured\ data.\ Download\ under\ www.readwin2000.com$

Certificates and approvals

CE mark

Guide lines 2004/108/EG

	Orderi	ing i	nfo	rm	ati	ion	
Product structure	RDL10 I	RDL10 Data-logger Minilog B, Version II					
		Power S R Bat T 7-3 U Pre	Power Supply: Battery 3.6V 2.1Ah 7-30VDC, (w/o battery) Prepared for battery 3.6V 7.2Ah (w/o battery)				
		Input; Software: 1 0/4-20mA 0-1VDC Pt100; standard 2 W/o E+H label, 0/4-20mA 0-1VDC Pt100, basic software 3 0/4-20mA 0-1VDC Pt100; telealarm + GSM cable, w/o digital input, only 24VDC version 4 W/o E+H label, telealarm + GSM cable, 0/4-20mA 0-1VDC Pt100 w/o digital input, only 24VDC					
		9	vers		ersion	, TSP-no.	to be spec.
			B C F G	32K 128 Wor Wor	K ma: rks cal	16000x x 64000x lib. certif. lib. certif.	
					npera Not Incl.	selected Pt100, -	
					A B C D	Thread Thread	G9 G9 + Lead seal option
						1 Ba 2 Me 3 Me 4 RS 5 Me 6 Me	nal Option: sic version counting bracket, wall counting bracket, pipe 232 cable counting bracket, wall + RS232 cable counting bracket, pipe + RS232 cable counting bracket, pipe + RS232 cable ecial version, TSP-no. to be spec.
						Cu L M Z	Board varnished, mounted in ASP2000 Board varnished Special version, TSP-no. to be spec.
							Marking: A Tagging (TAG), metal B Tagging (TAG), on device C Commissioning label, paper F Tagging (TAG), by customer

Endress+Hauser 7

 \Leftarrow Order code complete

RDL10-

Scope of delivery

The following is included in the delivery:

Built-in lithium battery (only for version with $3.6\,V\,/\,2.1$ Ah battery), operating manual, mounted cable glands, PC software package Readwin® 2000.

Accessories

Device-specific accessories

Description	Order no.
Interface cable without software	50086167
Interface cable for MODEM with adapter	RDL10A-VL
Mounting bracket cpl. for wall mounting	51000946
Mounting bracket/pipe mounting/complete	51000924
Battery (Lithium) Typ AA, 3.6 V / 2.1 Ah	51000981
Battery (Lithium) Typ C, 3.6 V / 7.2 Ah	Can be ordered from: http://www.tadiranbat.com/index.php/ tadiran-international-distributors
Adapter set for connection of two Minilog B to one modem	RDL10A-AA

Documentation

Standard documentation

- Recorder and data acquisition technology brochure: Data managers, paperless recorders and associated software packages: FA014R/09
- Operating instructions Minilog B, RDL10: BA00123R/09

Instruments International

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel.+41 61 715 81 00 Fax+41 61 715 25 00 www.endress.com info@ii.endress.com



People for Process Automation