Technical Information TI 043R/09/en Mat.Nr. 50073427

Process display RIA 450

Multi functional display, with integrated loop power supply, for monitoring and displaying analogue process measurements





















Application areas

- The RIA 450 process display indicates 1 analogue measured value. This can also be monitored for up to 4 individual preset alarm points. A loop power supply is also available.
- The process display can be applied in:
 - Control rooms
 - Control panels
- Stationary or mobile measurement systems
- Manned or unmanned measurement stations.

Features and benefits

- Multi functional:
 All normal measurement signals can be directly connected (bipolar current, voltage; thermocouples; RTD).
- User friendly:
 Measurement range, engineering units
 and alarm set points can be easily set
 up using a simple interactive matrix.
- Clear display:
 Multi coloured display for a clear bargraph display, 4 digit measured value, engineering units and alarms.
- Reliable: Complete alarm set point monitoring function (4 alarm set points).




Function

The pressettable analogue input enables direct connection of different transmitters. These can be current, voltage, RTD and TC. The three colour rear illuminated display shows both the measured value as well as the engineering units. Using the built-in loop power supply the unit can also power the connected sensors and then evaluate the signal returning from the

sensor. Four presettable alarm set points monitor the input for deviation from the predefined conditions. This means that the unit can be used for a number of possibilities for direct process control. A user friendly front end interactive setting up procedure using three push buttons is also available on the unit.

Operation and display



RIA 450 Front view

For special applications the numeric display and the bargraph can be operated inversley to the incoming measurment signal. In this function the displayed value decreases with an

increase in measured signal. This means that a relationship between the measured signal e.g. 4 ... 20 mA and the display 100% ... 0% is possible.

Alarm set point

The switchable alarm set point function monitors the input signal twice per second to check that the preset parameters have been adhered to. The four set points can be allocated to operate in min./max. safety, trend


analysis. The lower and upper set points and hysteresis as well as a time delay can also be defined.

Set point infringement is identified by two arrows and the respective relay is also activated.

Trend analysis

This function enables the unit to monitor and analyse the change in the measured value within a preset time cycle. For this the values m₂-m₁ are compared with each other after a predefined time cycle t_B (10 s, 1 min,

10 min). If the evaluated value is larger than the preset maximum allowable change then the relay is switched. This measured value calculation is repeated every $t_V=0.4$ s (floating time base).



Alternating relay control


Equal use of more than one pump in level applications is done by alternately switching individual pumps.


It is no longer conditional to reach a preset switch point before switching the pump on. It is now more a case of which pump has been inoperative for the

longest time.


The same condition is valid for switching the pump off:


If the switch off point is reached then the pump with the longest operation time is switched off.







Dimensions











Electrical connection





















Note:


* Temperature measurement can only be made when the unit is fitted with the "universal input" option.

S



Note:

** If together with the option "Universal input" the current measurement and the internal loop power supply (terminals 81/82) is used then a link must be added between terminals 14 and 82.



Technical data

General		

Application

Operation and system construction

Input

Output (loop power supply)

Output (relays)

Accuracy (Current/voltage input)

Acuracy (Option "Universal input")

Unit function	Process display for panel mounting.	
Process display, set point contactor	The display receives an analogue signal and shows the corresponding value on the display. Four presettable set points monitor the measured value for any infringement of the preset conditions and control the relays. Transmitters connected can be directly powered by the unit.	
Measurement principle	The analogue signal connected is digitalised, analysed and indicated in the display.	
Measurement system	Microcontroller controlled display with LC display, analogue input, alarm set point relays and loop power supply.	
Input types	Voltage, current, resistive thermometer (RTD), thermocouple (TC)	
Measurement range (current/voltage input)	Voltage: 01/10 V; max. 50 VRi: 1 MOhm Current: 0/420 mA; max.100 mARi: 50 Ohm	
	Voltage: +/-20 mV, +/-50 mA, ±100 mV, ±200 mV, 1 V, ±2 V, ±5 V, ±10 V, 01 V, 010 V; max. ±50 V, Ri: 1 MOhm	
	Current: 0/420 mA; max.100 mA Ri: 50 Ohm	
Measurement range (option "Universal input")	RTD: Pt100, Pt500, Pt1000:	
Integration time	200 ms	
Output signal	24 V +/- 10%, 25 mA (internal limit, short circuit protected) Option: 100 mA, without short circuit protection	
Number	1	
Output signal	Binary, switches on reaching the alarm set point	
Number	4	
Contact type	1 potential free changeover contact	
Contact load	<= 250 VAC, 3 A / 30 VDC, 3 A	
Voltage, current	Accuracy 0.25% of end value (FSD) Temperature drift 0.25% / 10 K ambient temperature	
Current, voltage, RTD, TC	Accuracy 0.5% of end value (FSD) Temperature drift 0.25% / 10 K ambient temperature	
Cold junction TC	Accuracy ±5 K Temperature drift ±1 °C / 10 K ambient temperature	

Technical data

Aplication conditions

Installation conditions		
Installation angle	No limit	
Ambient conditions		
Ambient temp.	0 °C50 °C	
Storage temp.	-20 °C+70 °C	
Climatic class	To EN 60654-1 Class B2	
Ingress protection	Front: IP65; Terminals: IP20	
EMC immunity		
RF protection	To EN 55011 Group1, Class A	
Safety		
Norm	To EN 61010 -1 protection class 1; Overvoltage category II, maximum allowable interference level II; Installation excessive current protection (surge fuse) <=10 A	
Interference safety		
ESD	To EN 61000-4-2, 6 kV/8 kV	
Electromagnetic fields	To EN 61000-4-3, 10 V/m	
Burst (supply)	To EN 61000-4-4, 2 kV	
Burst (signal)	To EN 61000-4-4, 2 kV	
Cable high frequency	To EN 61000-4-6, 10 kV	
Surge (supply)	To EN 61000-4-5, 1 kV symmetrical, 2 kV unsymmetrical	
Surge (signal)	To EN 61000-4-5, 1 kV unsymmetrical with external overvoltage protection (surge)	
Common mode noise rejection	To IEC 770, 60 dB at 60 V 50/60 Hz	
Normal mode noise rejection	To IEC 770, 40 dB at measurement range 1/10, 50/60 Hz	

Mechanical construction

Display

Dimensions	W: 96 mm, H: 96 mm, D: 168 mm
Weight	Approx. 670 g.
Materials	Plastic PC (Polycarbonate)
Electrical connection	Plug on screw terminals 2 x 12 pole 2,5 mm ² solid core, 1,5 mm ² stranded with ferrule
Display	LC display three colour, rear illuminated; 41 element bargraph with 41alarm set point arrows (yellow) 4 x 7 segment, 15 mm, numeric value (orange) 4 x 14 segment, 6 mm, engineering units (orange) 4 x 1 segment alarm set point infringement (red) 4 x exceed, 4 x undercut (arrows, red)
Display range	-999 to +9999 (can be inverted to the input signal)
Offset	-999 to 9999
Operation	3 push button operation (-/+/E)
Mode	Off, minimum, maximum safety, trend analysis, alarm

Technical data

Alarm	set	point	fun	ction
Aidilli	366	POILL	IUII	CULOIL

Number	4
Hysteresis	-999 to 9999
Time delay	0 to 100 s
Display	Two bargraph markings per set point, 1 signal field and 1 exceed/undercut arrow per point
Scan rate	400 ms
Power supply	90253 VAC, 50/60 Hz 1836 VDC, 2028 VAC, 50/60 Hz
Power consumption	8 VA
Fuse	315 mA slow blow (90253 VAC), 1 A slow blow (1836 VDC)
CE mark	Directive 89/336/EWG and 73/23/EWG
System information	SI 006R/09/en/
Operating manual	BA 086R/09/

Power supply


Certification

Additional documentation

Technical alterations reserved

How to order

RIA 450 process display



United Kingdom

Endress+Hauser Ltd. Floats Road Manchester M23 9NF

Tel. (0161) 286 - 5000 Fax. (0161) 998 - 1841 http://www.endress.com

Export division

Endress+Hauser GmbH+Co. Instruments International P.O. Box 2222 D-79574 Weil am Rhein Germany

Tel. (07621) 975-02 Fax (07621) 975-345 http://www.endress.com



