

# Data manager *memo-log*

**Multifunction paperless recorder  
memorizing, monitoring, compressing  
and displaying analog process data**



## Applications

- The Memo-Log data manager records up to 4 analog values. These channels can be mathematically combined, monitored for limit infringement, displayed, and stored on a Memory Card.
- Memo-Log can be universally applied in:
  - manned or unmanned measuring stations
  - continuous and repetitive processes
  - stationary and mobile measurement requirements

## Features and Benefits

- Multifunctional: Direct connection of all nominal measured signals
- Intelligent: Automatic signal analysis, mathematical channel combinations and linearized analog outputs
- System compatible: Normed interfaces and PCMCIA Memory-Card
- User friendly: Easily readable text display and simple dialog operation
- Reliable: Wide range of limit and self-monitoring functions
- Interference security: Complies with NAMUR EMC recommendations


**Endress+Hauser**

Nothing beats know-how



# Function principle

Schematic function diagram



## Analog inputs

The signals connected to the analog inputs are measured 10 times per second, linearized, and calculated to the preset engineering units and amplitudes. Then they are displayed and automatically calculated to the min, max and average values of presettable time cycles. This compressed data form is then stored on exchangeable Memory Cards.

## Limit monitoring

The measured signals are monitored for limit infringement every second. The individual settings (static/dynamic, upper/lower) and allocation to the built-in output relays ensures the highest security.

## Count / control inputs

Count inputs make recording, storing, and display of impulses possible (e.g. for quantity recording). Operation times are calculated using control inputs. Measurement and memory time cycles can also be preset using the control inputs.

## Channel combination

Recorded analog signals can be mathematically combined. These so called "virtual channels" are handled (display, limits, memory, etc.) the same way as all other real channels in the unit.

## Time control

All time dependent functions are precisely controlled by an internal quartz clock. This clock can be synchronized with an external clock or a clock from another unit. The integrated timer enables the unit to record signals within a freely-selectable time interval.

## System integration

A serial interface (standard: RS232 option: RS422/485) is available for quick set up and remote value display. ReadexT software is included with every Memo-Log. The information on the memory card is read out by drives that are connected to a MS-DOS compatible personal computer.

## Display


An easy-to-read fluorescent display shows the measured values—digitally or in the form of a bar graph. Date, time, daily min, max, and average values, limits, unit status, and a large number of additional parameters can be displayed at the touch of a button.

## Unit set up

Parameters can be selected and set up using Memo-Log's eight function keys or remotely using ReadexT software, supplied free-of-charge with every Memo-Log.


## Application example

Memo-Log used for monitoring and storing process sequences in a neutralization system (Submersion armature with pH and temperature sensor, pH transmitter with integrated controller e.g. Mycom)




## Operation and monitoring

Remote configuration and instantaneous value read out using ReadexT system software.




## Additional data evaluation

Transmission of measured data using the memory card for:  
- Read into computer  
- Evaluation using ReadexT or standard software  
- Filling in the system




## Front end operation / display

Menu structured  
operation and  
selection of display  
mode using front-  
mounted keypad.  
Example:  
TREND BAR  
GRAPH on rising  
value.




## Installation

Standard unit  
dimensions




Standard unit with  
front door (IP 54)



# Electrical connections

Rear panel connections



Terminal	Function		
L/L+ N/N- 	Line Neutral Potential earth (housing)		
41	Normally closed (nc)	Relay 1	
42	Common (c)	Relay 1	
43	Normally open (no)	Relay 1	
44	Normally closed (nc)	Relay 2	
45	Common (c)	Relay 2	
46	Normally open (nc)	Relay 2	
51	Normally closed (nc)	Relay 3	
52	Common (c)	Relay 3	
53	Normally open (no)	Relay 3	
54	Normally closed (nc)	Relay 4	
55	Common (c)	Relay 4	
56	Normally open (no)	Relay 4	
+	Auxiliary voltage +24 V		
-	Auxiliary voltage earth		
80 (-)	Common control in/outputs		
81 (+)	Control input 1 (time counter 1)		
82 (+)	Control input 2 (time counter 2)		
83 (+)	Control input 3 (external measuring period)		
84 (+)	Control input 4 (external signal evaluation block, batch)		
85 (+)	Count input A		
86 (+)	Count input B		
87 (+)	Control input 7 (time synchronization)		
88 (+)	Control output 1 (time synchronization)		
90	+control output supply		

Terminal	Channel	V/I/T.C.	Pt 100	Linear output	24 V/24 mA power supply
111	1	+	A	--	+
112	1	-	B	--	-
113	1		Sense	--	
211	2	+	A	20 mA	+
212	2	-	B	0 V, 0/4 mA	-
213	2		Sense	10 V	
311	3	+	A	20 mA	+
312	3	-	B	0 V, 0/4 mA	-
313	3		Sense	10 V	
411	4	+	A	20 mA	+
412	4	-	B	0 V, 0/4 mA	-
413	4		Sense	10 V	

## SUB-D 9 pole socket for DIN 41 652 serial interface

Pin	RS 485	RS 422	RS 232 C
1	Screen	Screen	Screen
2	-	-	TXD
3	RXD/TXD-B	RXD-B	RXD
4	-	TXD-B	-
5	GND	GND	GND
6	-	-	-
7	-	GND	-
8	RXD/TXD-A	RXD-A	-
9	-	TXD-A	-

(Free pins must not be connected !)

# Order Code

RD10- 1 2 3 4 5 6 7 8a 8b 8c 9 0

- 1 Power supply
  - D Multi supply 24 V AC/DC
  - F 115 VAC, 50/60 Hz
  - H 230 VAC, 50/60 Hz
  - Y Special version
- 2 Model
  - A 144x72 mm panel mounted, with bezel
  - B 144x72 mm panel mounted, door and latch
  - C 144x72 mm panel mounted, door and lock
  - Y Special version
- 3 Operating language
  - A German
  - B English
  - C French
  - S English, without operating instructions
  - Y Other versions
- 4 Signal calculation
  - 1 Without signal calculation
  - 2 MM = Mathematic module
  - 3 INT = Integration
  - 4 MM + INT
  - Y Special version
- 5 Count inputs / control inputs
  - A Without count and control inputs
  - B CI = two count inputs
  - C TMC = two time counters
  - D REM = external release/measurement block
  - E SYNC = remote time synchronization
  - O CI + TMC
  - P CI + REM
  - Q CI + SYNC
  - R CI + TMC + REM
  - S CI + TMC + SYNC
  - T CI + TMC + REM + SYNC
  - I TMC + REM
  - J TMC + SYNC
  - K REM + SYNC
  - N TMC + REM + SYNC
- 6 Interface
  - 1 RS 232 C
  - 2 RS 422/485
- 7 Plug-in position 1
  - 1 Standard analog input 0/4...20 mA, 0...1/10 V
  - 2 Multi voltage / thermo couple PCB
  - 3 Pt 100/Ni 100 input
  - 7 Universal input
- 8 Plug-in position for channels 2, 3, and 4
  - 0 Not used
  - 1 Standard analog input 0/4...20 mA, 0...1/10 V
  - 2 Multi voltage / thermo couple PCB
  - 3 Pt 100/Ni 100 input
  - 5 Linear analog output 0/4...20 mA, 0...1/10 V
  - 6 24 VDC, 25 mA power supply output
  - 7 Universal input
- 9 Memory-Card
  - A None
  - B Memory card, 64 kByte
  - C Memory card, 256 kByte
  - D Memory card, 1024 kByte
  - Y Special version
- 0 Internal temperature compensation
  - 0 Without internal temperature compensation
  - 1 With internal temperature compensation

# Technical data

## Models

144x72x210 mm panel mounted  
Protection class front IP 20 D, IEC 529  
Protection class rear IP 00, VDE 0470  
Optional Front door IP 54, IEC529

## Power supply

230/115 VAC +10% -15%, 50/60 Hz  
Option 24 V universal power supply:  
24 VAC +10% -15%, 50/60 Hz  
24 VDC +10% -20%

## Power consumption

max. ca. 15 VA (complete unit)  
min. ca. 8 VA (1 channel unit)

## Fuses

At 230/115 VAC = 630 mA slow blow  
At 24 VAC = 1 A slow blow  
At 24 VDC = 1 A slow blow

## Connections

Spade connectors (DIN 46224),  
6.3 x 0.8 mm

## Display

2 x 20 digit fluorescent display for digital  
measured value display or trend bar  
graph

## Operation

Menu structured matrix operation via 8  
front-mounted keys or serial interface

## Limit monitoring

All channels 1x/second  
5 limit values (statistic/dynamic) per  
channel, presettable value and allocation

## Ambient operational conditions

32...+122°F (0...+50 °C),  
humidity to DIN 40 040

## Storage temperature

-4...158°F (-20...+70 °C)

## EMC/immunity

To NAMUR recommendations AK 4.6  
without functional interference due to:  
IEC 801-2/VDE 0843/2, level 3  
IEC 801-3/VDE 0843/3, level 3  
IEC 801-4/VDE 0843/4, level 3

## Power failure

No functional loss due to main power loss  
up to 20 ms. Automatic start on longer  
power losses.

## Electrical safety

IEC 348/VDE 0411, Protection class I

## RF immunity

EN 55011/VDE 0875 Part 11, Class A

## Standard input ranges

0...1/10 V, 1 MΩ  
0/4...20 mA, via 50 Ω internal shunt  
Basic accuracy: 0.2 % v.E.  
Long term drift: 0.2 % v.E.  
Power up drift up to 4h: 0.1 % v.E.  
Temperature drift: 0.2 % v.E./10 K

## Standard input over range

≤100 mA continuous  
≤50 V continuous

## Normal mode noise rejection

40 dB at input range/10, 50/60 Hz  
±0.5 Hz

## Common mode noise rejection

0.1 % measurement range at 160 V, 50/60  
Hz ±0.5 Hz

## Potential difference

Channel to channel 100 V

## Serial interface

RS 232 C (Option: RS 422/485) incl. PC  
software for setting up, display and  
optional memory card

## Auxiliary voltage

Approx. 24 VDC, 100 mA, for optional  
control inputs.

## Limits / alarm relays

4 Relays, each with 1 x changeover  
contact, 3 A, 250 VAC, insulation group A  
to VDE 0110

## Options

### Multi voltage/thermo couple input

±20 mV...±10 V selectable in 5 ranges  
Thermo couples: L,U,N,B,R,S,K,T

Cold junction compensation incl.  
linearization, galvanic isolation  
Basic accuracy: 0.2 % v.E. + 2 K  
(absolute) using internal reference  
Long term drift: 0.2 % v.E.  
Power up drift up to 4 h: 0.1 % v.E.  
Temperature drift: 0.2 % v.E./10 K  
No cable open circuit monitoring

## RTD

Pt 100, -148...1112°F (-100...+600°C)  
Ni 100, -76...356°F (-60...+180°C)  
Basic accuracy: 0.2 % v.E.  
Long term drift: 0.2 % v.E.  
Power up drift up to 4 h: 0.2 % v.E.  
Temperature drift: 0.1 % v.E./10 K  
No cable open circuit monitoring

## Universal input

Measurement range same as  
Standard/multi voltage/RTD input ranges,  
additional ranges:  
Pt 100 a: -94...338°F (-70...+170°C)  
Pt 100 b: -4...248°F (-20...+120°C)  
Pt 500 : -148...1112°F (-100...+600°C)  
Pt 1000: -148...1112°F (-100...+600°C)  
with cable open circuit monitoring

## Transmitter power supply

24 VDC, ±10 %, 24 mA, short circuit  
protected

## Technical data

### Analog output

0/4...20 mA, load  $\leq$  500  $\Omega$   
 0...10 V, 2 mA  
 Basic accuracy : 0.5 % v.E.  
 Long term drift: 0.5 % v.E.  
 Power up drift up to 4 h: 0.3 % v.E.  
 Temperature drift: 0.3 % v.E.

### Count/control inputs

2 count inputs  
 max. impulse frequency 25 Hz  
 min. impulse length 20 ms  
 2 time counters  
 external release/blocking signal analysis  
 Time synchronization

Control in accordance to DIN 19 240:  
 Logic 0 = -3 V...+5 V  
 Logic 1 = +12 V...+30 V  
 Input current 2-3 mA  
 Bounce time  $\leq$  5 ms, Signal time  $\geq$  100 ms

### Control output

Remote time synchronization  
 375 ms Fleeting contact

### Memory-Card 64/256/1024 kByte

SRAM in accordance with PCMCIA and JEIDA 4.x  
 Card format 85,6x54x3,3 mm  
 Plug in cycles: min. 10.000  
 Storage temp: 14...158°F (-10...70°C)  
 Ambient temp: 32...140°F (0...+60°C)  
 Internal battery BR 2325, 3 V, 165 mAh

Memory capacity is dependent on the number of channels/options used.

The following theoretical values can be used as a guideline:

64 kByte 3 hrs....1.4 years  
 256 kByte 13 hrs....6.7 years  
 1024 kByte 57 hrs...27.6 years

Exact values can be calculated by a help program that can be found on the disks delivered.

### PCMCIA/JEIDA card read out units

Various read out units are offered.  
 Technical data is delivered with the unit ordered.

## Accessories

### External PCMCIA card read unit

for SRAM card  
 Desk top version, parallel interface  
 Order No. 50062456

### Memory card

SRAM 64kByte Order No. 50060834  
 256kByte Order No. 50060833  
 1MByte Order No. 50060832

Trade names:

MS-DOS is a registered trade name for the Microsoft Corporation.

United States	Canada	Mexico
Endress+Hauser 2350 Endress Place Greenwood, IN 46143 Phone: (317) 535-7138 1-800-428-4344 FAX: (317) 535-8498	Regional Office Endress+Hauser 600 Kenrick, Ste. B-14 Houston, TX 77060 Phone: (281) 999-1991 FAX: (281) 999-1891	Endress+Hauser Canada, Ltd. 1440 Graham's Lane Unit 1, Burlington ON, L7S 1W3 Phone: (905) 681-9292 1-800-668-3199 FAX: (905) 681-9444
Fogarty Engineering Sales Company Div. of Endress+Hauser P.O. Box 901 Harvey, LA 70059 Phone: (504) 366-3264 FAX: (504) 366-3816	Sterling IPC Div. of Endress+Hauser 68950 Powell Road P.O. Box 604 Romeo, MI 48065 Phone: (810) 752-0700 FAX: (810) 752-0705	Endress+Hauser Canada Ltée 6800 Côte de Liesse, Ste. 100 St. Laurent, Que H4T 2A7 Téléphone: (514) 733-0254 Télécopieur: (514) 733-2924

