

Technical Information

RIA251

Process display

Digital loop powered display for 4...20 mA current loops



Application

- Plant and machine construction
- Control panels
- Laboratory fittings
- Process display, monitoring
- Suitable for Ex applications

Benefits at a glance

- 5 Digit LC display with 17 mm (0.67 in) character height
- Loop powered display,
- no additional power supply cabling required
- Measurement range 19999 to 99999
 Elevible measurement range set up
- Flexible measurement range set up using 3 push buttons





Function and system design

Measuring principle

The display receives an analog signal and shows the corresponding value on the display. The unit is connected in the 4 ... 20 mA circuit and also receives the required power from this circuit. The analog signal connected is digitalized, analysed and indicated in the LC display.



Example of an application of the process display unit

Measuring system

The RIA251 process display is connected directly into the 4 \dots 20 mA measurement loop. The power required is taken from the current loop. The voltage drop of <2 V has no significant influence on the measurement circuit. Setting up the measurement range, decimal point and offset is easily done using the 3 front mounted push buttons. Setting up can also take place whilst the unit is operational, which means that later changes can be easily made.

The unit can be obtained with Ex certification to ATEX II 1 G EEx ia IIC T6, FM, CSA and NEPSI (option). Therefore special applications where the display is required directly in the hazardous area can now be realized.

	Input		
Measured variable	Current		
Measuring range	420 mA (polarity protected)		
Max. input current	150 mA (short circuit current)		
Voltage drop	< 2 V		
HART [®] protocol	The display is suitable for transmitting the HART [®] protocol.		

Power supply

Electrical connection

Both the terminals and the connection values of the display correspond to the Ex requirements. Connection of an active current source e.g. Transmitter with its own power source and an active current output.



Note!

The display can be placed into the explosion hazardous area if a suitable barrier is used.



Terminal layout of the process display

Voltage supply	From 420 mA current loop
Voltage drop	< 2 V

Performance characteristics

Accuracy	Accuracy < 0.1% of FSD
Temperaturdrift	< 0.01% / 10 K

Installation

Installation instructions	Mounting location	
	Panel cutout 48 x 96 mm (1.9 x 3.78 in)	
	Installation angle	
	No restrictions.	

	Environment			
Ambient temperature range	-20 to +60 °C (-4 to +140 °F)			
Storage temperature	-30 to +70 °C (-22 to +158 °F)			
Climate class	As per IEC 60654-1, Class B2			
Protection degree	Between bezel and panel: NEMA 4x, IP 65 Terminals: NEMA 1, IP 20			
Electromagnetic compatibility (EMC)	RF protection To EN 55011 Group 1, Class A			
	Interferance safety ESD: To IEC 61000-4-2, 6/8 kV Electro magnetic fields: To IEC 61000-4-3, 10 V/m Burst (supply): To IEC 61000-4-4, 2 kV Surge: To IEC 61000-4-5, 1 kV Cable high frequency: To EN 61000-4-6, 10 V			

Mechanical construction



Dimensions of the RIA251 in mm (inch)

Weight

Material	 Housing front: Die cast aluminium Housing casing: Galvanized sheet steel Housing rear panel: Plastic ABS
Electrical connection	Plug on screw terminals (securable), Terminal size 1.5 $\rm mm^2$ (AWG 16) solid, 1.0 $\rm mm^2$ (AWG 17) strands with ferrule

Human interface

Display elements	 Display 5 digit LC display, 17 mm (0.67 in) character height Range 19999 to +999999 Offset 19999 to +32767
Operation	3 push button operation $(-/+/E)$

Certificates and approvals

CE	89/336/EWG guidelines		
Ex-Zulassung	 ATEX II 1 G EEx ia IIC T6 to DIN EN 50014 and DIN EN 50020 FM IS, Class I, Div. 1+2, Group A,B,C,D to FM 3600 and FM 3610 CSA IS, Class I, Div. 1+2, Group A,B,C,D to C22.2 No 157 NEPSI Ex ia IIC T6 		

Ordering information

Product structure	RIA251	1251 Electronical indicator, Depth: 90 mm. Loop powered. 1 1 channel, scalable. Display LC, 5-digit, Character hight 17 mm. Approval: CSA GP.			
		App	proval		
		Α	Non-hazardous area		
		В	ATEX II1G EEx ia IIC T6		
		С	FM IS, Cl.I, Div.1, Gr. ABCD		
		D	CSA Ex ia, Cl.I, Div.1, Gr. ABCD		
		F	NEPSI Ex ia IIC Tó		
			Housing		
			1 Panel mounting, 48 x 96 x 90 mm		
			2 Panel mounting, 48 x 96 x 90 mm + WCC=Works calibration certificate		
	RIA251-		\leftarrow Order code		

Documentation

- System components field and panel installation display unit, energy manager, active barrier, process transmitter and overvoltage protection: FA016K/09
- Operating instructions 'Process display RIA251': BA087R/09
- Ex documentation:
 - ATEX II(1)GD: XA001R/09/a3

Instruments International

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel. +41 61 715 81 00 Fax +41 61 715 25 00 www.endress.com info@ii.endress.com

