



Level



Pressure



Flow



Temperature



Liquid
Analysis



Registration



Systems
Components



Services



Solutions

Safety Instructions

Proline Promass 80

HART

NEPSI Zone 1, Zone 21

This document is an integral part of the following Operating Instructions:

- BA00057D, Proline Promass 80 HART


Contents

General warnings	2
Special conditions	2
Installation instructions	2
COC certificates of conformity	3
Description of measuring system	3
Nameplates.	4
Type code.	5
Temperature table compact version.	6
Temperature table remote version.	8
Gas and dust explosion protection.	9
Design of measuring system	9
Cable entries.	10
Cable specification	10
Potential equalization	10
Connection of remote version connecting cable.	10
Electrical connection.	11
Terminal assignment and connection data, power supply.	11
Terminal assignment and connection data for signal circuits (intrinsically safe circuits)	12
Terminal assignment and connection data for signal circuits (non-intrinsically safe circuits)	13
Service adapter	14
Device fuse.	14
Technical Data	14


General warnings

- For installation, use and maintenance of the flow meter, the instruction manual and the following standards shall be observed:
 - GB50257-2014 "Code for construction and acceptance of electric device for explosive atmospheres and fire hazard electrical equipment installation engineering"
 - GB3836.13-2013 "Explosive atmospheres – Part 13: Equipment repair, overhaul and reclamation"
 - GB3836.15-2000 "Electrical apparatus for explosive gas atmospheres – Part 15: Electrical installations in hazardous area (other than mines)"
 - GB3836.16-2006 "Electrical apparatus for explosive gas atmospheres – Part 16: Inspection and maintenance of electrical installation (other than mines)"
 - GB3836.18-2010 "Explosive atmospheres – Part 18: Intrinsically safe system".
 - GB15577-2007: Safety regulations for dust explosion prevention and protection" (Only if installed in dust hazardous areas.)
 - GB12476.2-2010 "Electrical apparatus for use in the presence of combustible dust – Part 2: Selection and installation". (Only if installed in dust hazardous areas.)
- Any maintenance shall be done after power off or the area known to be non-hazardous.
- The flow meter shall not be modified in order to ensure the explosion protection performance of the equipment. Any change may impair safety.
- Installation, connection to the electricity supply, commissioning and maintenance of the devices must be carried out by qualified specialists trained to work on Ex-rated devices.
- Compliance with all of the technical data of the device (see nameplate) is mandatory.
- Open the device only when it is de-energized (and after a delay of at least 10 minutes following shutdown of the power supply) or in non-hazardous (classified) locations.
- It is not permissible to connect the service adapter whilst the atmosphere is considered to be explosive.
- Opening the transmitter housing and the connection housing of the remote version is only permitted for a brief time. During this time, ensure that no dust or water enters the housing.
- To guarantee resistance to dust and water, the transmitter housing, the connection housing of the remote version and the cable entries must be tightly sealed.
- Use of the devices is restricted to mediums against which the process-wetted materials are adequately resistant.
- The suitability of the device in the event of simultaneous occurrence of gas-air and dust-air mixtures requires an additional assessment.

Special conditions

The device must be integrated into the potential equalization system. Potential must be equalized along the intrinsically safe sensor circuits.
Further information is provided in the "Potential equalization" section: →  10.

Installation instructions

- For terminals No. 20 to No. 27 of the transmitter, only devices with ratings $U_m \leq 260 \text{ V}$ and $I_m \leq 500 \text{ mA}$ are allowed to be connected (does not apply to intrinsically safe circuits).
- The measuring device must only be used in the permitted temperature class.
The values of the individual temperature classes can be found in the temperature tables: →  6.
- The following applies when using the terminal compartment in type of protection "flameproof/Ex d":
Only cable entries and cable glands, which are approved by NEPSI in accordance with GB3836.1-2000 and GB3836.2-2000 and which are suitable for an operating temperature of up to 80 °C, they shall be used.
- The following applies when using the terminal compartment in type of protection "increased safety/Ex e":
Only cable entries, cable glands and blanking plugs, which are approved by NEPSI in accordance with GB3836.1-2010 and GB3836.3-2010 and which are suitable for an operating temperature of up to 80 °C and for an ingress protection of IP 67, they shall be used. The cables must be installed in such a way, that they are fixed in place in order to ensure adequate strain relief.
- Suitable cables and suitable, certified cable glands, cable entries and blanking plugs must be used for measuring devices operated at temperatures below –20 °C.
- The cable entries and openings not used must be sealed tight with suitable components.
- If the active intrinsically safe communication circuits (input/output option S, T; terminals 26/27 resp. 24/25) are fed into areas that require 1D or 2D apparatus, the connected apparatus must be tested and certified accordingly.
- In Zone 0, potentially explosive vapor/air mixtures may only occur under atmospheric conditions. If no potentially explosive mixtures are present, or if additional protective measures have been taken, the devices may be operated under other atmospheric conditions in accordance with the manufacturer's specifications.

Installation instructions (continued)




Caution!

- The explosion group for the measuring device can be IIC. However, it is reduced to IIB if the permitted, external capacitance/inductance for the intrinsically safe communication circuits is increased (→ 12).
- Turning the local display:
the screw cap has to be removed before the local display can be turned, and this must be done with the device de-energized (and after a delay of at least 10 minutes following shutdown of the power supply).

Turning the transmitter housing

1. Unscrew the grub screw.
2. Rotate the transmitter housing cautiously clockwise until the end stop (end of the thread).
3. Rotate the transmitter housing counter-clockwise (max. 360°) in the wanted position.
4. Tighten the grub screw again.



A0006944

Fig. 1: Turning the transmitter housing

COC certificates of conformity

COC certificates of conformity

By affixing the certification number the product conforms with the following standards:

- GB3836.1/2/3/4/20 - 2010
- GB12476.1/5 - 2013, GB12476.4 - 2010

Certification numbers:

- GYJ16.1472X

Inspection body

NEPSI, National Supervision and Inspection Centre for Explosion Protection and Safety of Instrumentation

Description of measuring system


The measuring system consists of transmitters and sensors.

Two versions are available:

- Compact version: transmitters and sensors form a mechanical unit.
- Remote version: transmitters and sensors are installed separately and connected to each other via a connecting cable.

Nameplates

The nameplates, which are mounted in a clearly visible position on the transmitter and sensor, contain all of the relevant information about the measuring system.



A00008199

Fig. 1: Example for nameplates of a transmitter and of a sensor

A Transmitter nameplate

B Sensor nameplate

- 1 Production site
- 2 Transmitter or sensor type
- 3 Order code and serial number
- 3a Extended order code
- 4 Power supply, frequency and power consumption
- 5 Available inputs/outputs
- 6 Space for additional information on special products
- 7 Year of manufacture
- 8 Type of enclosure protection
- 9 Type of protection
- 10 Number of the NEPSI certificate of conformity
- 11 Space for notes, e.g. delays, etc. (only if necessary)
- 12 Ambient temperature range
- 13 C-Tick symbol
- 14 NEPSI symbol
- 15 Associated Ex documentation
- 16 Space for other approval specifications and certificates, e.g. PROFIBUS, etc. (only if present)
- 17 Calibration factor/zero point
- 18 Nominal diameter/nominal pressure
- 19 Materials in contact with the medium
- 20 Fluid temperature range
- 21 Secondary containment pressure range
- 22 Density accuracy
- 23 Additional information, e.g. SP-CAL = 5-point calibration, 3.1B = 3.1 B certificate for wetted material
- 24 Device nominal diameter
- 25 Nominal pressure
- 26 Direction of flow


Cable entry (Pos. no. 15 in type code)

*	Thread form
A	M20 × 1.5
B	NPT 1/2"
C	G 1/2"

Inputs/outputs (Pos. no. 18 in type code)

*	Type of protection
A, D, 8	Non-intrinsically safe outputs
S, T	Ex ia

 Note!

For a detailed explanation of these values, regarding the available outputs and inputs, as well as a description of the associated terminal assignments and connection data: →  11 onwards.

**Temperature table
compact version**

Max. medium temperature [°C] for T1 ~ T6 in relation to the maximum ambient temperature T_a

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*A**-...	1 to 4	+60	60	95	130	150	200	200

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*E**-...	8 to 15	+50	–	100	130	140	140	140
	25 to 50		50	100	130	140	140	140
	8 to 50	+60	–	100	130	140	140	140
	80		60	95	110	140	140	140

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*F**-...	8 to 40	+50	55	95	130	150 (170)	(200)	(200)
	50		60	95	130	150 (170)	(200)	(200)
	80 to 250		60	75	110	150 (170)	(200)	(200)
	8 to 40	+60	55	95	100	100	100	100
	50		60	95	100	100	100	100
	80 to 250		60	75	100	100	100	100

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*F**-1... Promass 8*F**-2... Promass 8*F**-3... Promass 8*F**-4...	25, 50, 80	+60	65	80	(110)	(175)	(265)	(350)

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*H**-...	8	+50	50	65	100	160	200	200
	15 to 50		60	75	115	180	200	200
	8	+60	50	65	100	160	(200)	(200)
	15 to 50		60	75	115	160 (180)	(200)	(200)

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*I**~...	8 to 15	+50	60	95	130	150	150	150
	15 FB, 25							
	25 FB		70	85	120	150	150	150
	40, 40 FB							
	50, 50 FB							
	80							
	8 to 15	+60	60	95	130	(150)	(150)	(150)
	15 FB, 25							
	25 FB		70	85	120	(150)	(150)	(150)
	40, 40 FB							
	50, 50 FB							
	80							

FB = Full bore

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*M**~...	8 to 15	+50	55	95	130	150	150	150
	25 to 40		60	95	130	150	150	150
	50		65	95	130	150	150	150
	80		65	80	110	150	150	150
	8 to 15	+60	55	95	100	100	100	100
	25 to 40		60	95	100	100	100	100
	50		65	95	100	100	100	100
	80		65	80	100	100	100	100

	DN [mm]	T _a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*P**~... Promass 8*S**~...	8	+50	–	65	100	160	200	200
	15 to 25		50	75	115	180	200	200
	40		55	75	115	180	200	200
	50		60	75	110	180	200	200
	8	+60	–	65	100	160	(200)	(200)
	15 to 40		–	75	115	160 (180)	(200)	(200)
	50		60	75	110	160 (180)	(200)	(200)

() = These maximum permissible medium temperatures apply only when the transmitter is installed in such a way that it is not above the sensor and there is free convection on all sides

The minimum **medium temperature** is –50 °C for Promass A/F/H/I/M/P/S, and –40 °C for Promass E.

The minimum **ambient temperature** T_a for Promass A/E/F/H/I/M/P/S is –20 °C.

A version for **ambient temperatures** T_a up to –40 °C is optionally available.

Temperature table remote version**Sensor**Max. medium temperature [°C] for T1 ~ T6 in relation to the maximum ambient temperature T_a

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*A**-...	1 to 4	+60	60	95	130	150	200	200

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*E**-...	8 to 50	+60	–	100	130	140	140	140
	80		60	95	110	140	140	140

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*F**-...	8 to 50	+60	55	95	130	160	200	200
	80 to 250		60	75	110	170	200	200

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*F**-1... Promass 8*F**-2... Promass 8*F**-3... Promass 8*F**-4...	25, 50, 80	+60	65	80	110	175	265	350

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*H**-...	8	+60	50	65	100	160	200	200
	15 to 50		60	75	115	180	200	200

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*I**-...	8 to 15	+60	60	95	130	150	150	150
	15 FB, 25							
	25 FB							
	40, 40 FB		70	85	120	150	150	150
	50, 50 FB							
	80							

FB = Full bore

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*M**-...	8 to 15	+60	55	95	130	150	150	150
	25 to 40		60	95	130	150	150	150
	50		65	95	130	150	150	150
	80		65	80	110	150	150	150

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*P**-... Promass 8*S**-...	8	+50	–	65	100	160	200	200
	15 to 25		50	75	115	180	200	200
	40		55	75	115	180	200	200
	8	+60	–	65	100	160	200	200
	15 to 40		–	75	115	180	200	200
	50		60	75	110	180	200	200

The minimum **medium temperature** is –50 °C for Promass A/F/H/I/M/P/S, and –40 °C for Promass E.**Transmitter**

The remote version transmitter has a T6 temperature class rating when installed in the Ex d housing for operation at ambient temperatures up to $T_a = 60$ °C. The maximum ambient temperature range is –20 to +60 °C. A version for **ambient temperatures** T_a up to –20 °C is optionally available.

Gas and dust explosion protection

Determining the temperature class and surface temperature with the temperature table

- In the case of gas: Determine the temperature class as a function of the ambient temperature T_a and the medium temperature T_m .
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m .

Example of the maximum surface temperature for explosion hazards arising from dust

Device: Promass 80 F, compact version, DN 80

Maximum ambient temperature: $T_a = 60\text{ °C}$

Maximum medium temperature: $T_m = 98\text{ °C}$

	DN [mm]	T_a [°C]	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Promass 8*F**...	8...40	+50	55	95	130	150 (170)	200	200
	50		60	95	130	150 (170)	200	200
	80...250		60	75	110	150 (170)	200	200
	8...40	+60	55	95	100	100	100	100
	50		60	95	100	100	100	100
	80...250		60	95	100	100	100	100


DN 80 $T_a = 60\text{ °C}$ $T_m = 100\text{ °C} (\leq 98\text{ °C})$

A0005219

Fig. 2: Procedure for calculating the max. surface temperature

1. Select the device (Promass 80 F), nominal diameter (DN 80) and ambient temperature T_a (60 °C) in the associated temperature table (compact version).
The row showing the maximum medium temperature is determined.
2. Select the maximum medium temperature T_m (98 °C), which is smaller than or equal to the maximum medium temperature of a cell.
The column with the temperature class for gas is determined ($98\text{ °C} \leq 100\text{ °C} \rightarrow T4$).
3. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature: $T4 = 135\text{ °C} = \text{maximum surface temperature for dust}$.

Design of measuring system



A0005231

Fig. 3: Design of the measuring system, compact/remote version

A Transmitter housing (compact version)

B Transmitter housing on connection housing, remote version

C Sensor connection housing, remote version

a Screw terminal for connecting to the potential equalization

b Connection compartment cover

c Connecting cable remote version

① and ② see following section "Cable entries"

Note!

Connection of remote version connecting cable → 10

Cable entries

- ① for connection compartment (Ex d version): power supply cable and cable of the communication circuit
→ Choice of thread for cable entries M20 × 1.5, ½" NPT or G ½".

Make sure that the Ex d cable glands/entries are secured to prevent working loose and that the seals are installed immediately adjacent to the housing.

- ① for connection compartment (Ex e version): power supply cable and cable of the communication circuit
→ Choice of cable gland M20 × 1.5 or thread for cable entries ½" NPT or G ½".
The cables must be installed such that they are fixed in place. Adequate strain relief must be ensured.
- ② for remote connecting cable:
→ Choice of cable gland M20 × 1.5 or thread for cable entries ½" NPT or G ½"

⚠ Warning!

When using cable glands M20 × 1.5:

- Only approved cable glands may be used (→ 2 "Installation instructions").
- The leak-tight of the cable glands and cable entries is to ensure.

Cable specification

You can find information about the cable specification in the associated Operating Instructions.


Potential equalization

- The transmitter (compact and remote version) is to be securely connected to the potential equalization system using the screw terminal on the outside of the transmitter housing. Alternatively, the transmitter of the compact version as of serial number 4Axxxxxx000 can be connected to the potential equalization system via the pipeline if a ground connection via the pipeline according to regulations can be assured.
- When using the remote version, the connection housing of the sensor must be grounded via the external screw terminal. Alternatively, the sensor can be integrated into the potential equalization via the pipeline as long as the pipeline provides a ground connection conforming to regulations.

📌 Note!

Further information about potential equalization, shielding and grounding can be found in the associated Operating Instructions.

Connection of remote version connecting cable



A0011783

Fig. 4: Connection of remote version connecting cable

a Wall-mount housing: NEPSI Zone 1

b Remote version, flanged version

Terminal No.: 4/5 = gray; 6/7 = green; 8 = yellow; 9/10 = pink; 11/12 = white; 41/42 = brown

Terminal assignment and connection data

The connection of the remote version, between the sensor and the transmitter, has Ex i explosion protection. The maximum cable length between transmitter and sensor must not exceed 120 m.

👉 Caution!

Only preterminated connecting cables supplied by Endress+Hauser may be used.

Electrical connection

Connection compartment

Transmitter housing compact/remote version (terminal assignment, connection data → 11 ff.)




Fig. 5: Electrical connection for 4 to 20 mA HART

- a Power supply cable (terminal assignment and connection data → 11)
- b Signal cable (terminal assignment and connection data → 13)
- c Ground terminal for signal cable shield / fieldbus cable / RS485 line
- d Ground terminal for protective ground
- e Service adapter for connecting service interface FXA 193 (Fieldcheck, FieldCare)


Terminal assignment and connection data, power supply

Terminal assignment and connection data

All transmitters	1 L (+)	2 N (-)	⊕
Designation	Supply voltage		Protective earth
Functional values	AC: U = 85 to 260 V; AC: U = 20 to 55 V DC: U = 16 to 62 V Power consumption: 15 VA / 15 W		Caution! Observe the grounding concepts of the system!
Intrinsically safe circuit	no		
U _m	260 V AC		

Terminal assignment and connection data for signal circuits (intrinsically safe circuits)

 Note!

The following tables contain values/specifications, which are dependent on the type code (type of measuring device). Please compare the following type code to the one shown on the nameplate of your measuring device. For a graphic representation of the electrical connections: →  11.

Terminal assignment of transmitter 80***-*****S+###

Transmitter	Terminal no. (inputs/outputs)							
	20 (+)	21 (-)	22 (+)	23 (-)	24 (+)	25 (-)	26 (+)	27 (-)
Assignment	—	—	—	—	Pulse/frequency output, passive		Current output HART, active	
Electric circuit	—	—	—	—	Ex ia		Ex ia	
Safety-related values	—	—	—	—	U _i	30 V DC	U _o	21.8 V DC
					I _i	500 mA	I _o	90 mA
					P _i	600 mW	P _o	491 mW
					L _i	negligible	L _o IIC/IIB	4.1 mH/15 mH
					C _i	6 nF	C _o IIC/IIB	160 nF/1160 nF
							¹⁾ L _o IIC/IIB	2 mH/10 mH
							¹⁾ C _o IIC/IIB	80 nF/300 nF
							U _i	30 V DC ²⁾
							I _i	10 mA ²⁾
							P _i	0.3 W ²⁾
							L _i	negligible
							C _i	6 nF
Functional values	—	—	—	—	galvanically isolated, passive: 30 V DC / 250 mA Open Collector Full scale frequency 2 to 5000 Hz		galvanically isolated, active: 0/4 to 20 mA R _L < 400 Ω R _L HART ≥ 250 Ω	

¹⁾ Permitted values in the event of simultaneous occurrence of concentrated inductances and capacitances.


²⁾ The interconnection must be assessed according to the valid construction provisions.

Terminal assignment of transmitter 80***-*****T+###

Transmitter	Terminal no. (inputs/outputs)							
	20 (+)	21 (-)	22 (+)	23 (-)	24 (+)	25 (-)	26 (+)	27 (-)
Assignment	—	—	—	—	Pulse/frequency output, passive		Current output HART, passive	
Electric circuit	—	—	—	—	Ex ia		Ex ia	
Safety-related values	—	—	—	—	U _i	30 V DC	U _i	30 V DC
					I _i	500 mA	I _i	100 mA
					P _i	600 mW	P _i	1.25 W
					L _i	negligible	L _i	negligible
					C _i	6 nF	C _i	6 nF
Functional values	—	—	—	—	galvanically isolated, passive: 30 V DC / 250 mA Open Collector Full scale frequency 2 to 5000 Hz		galvanically isolated, passive: 4 to 20 mA voltage drop ≤ 9 V R _L < [(V _{p, supply} - 9 V) ÷ 25 mA]	

Terminal assignment and connection data for signal circuits (non-intrinsically safe circuits)

 Note!

The following tables contain values/specifications, which are dependent on the type code (type of measuring device). Please compare the following type code to the one shown on the nameplate of your measuring device. For a graphic representation of the electrical connections: →  11.

Terminal assignment

Order characteristic "Inputs/outputs"	Terminal no. (inputs/outputs)							
	20 (+)	21 (-)	22 (+)	23 (-)	24 (+)	25 (-)	26 (+)	27 (-)
A	–		–		Pulse/ frequency output		Current output HART	
D	Status input		Relay output		Pulse/ frequency output		Current output HART	
8	Status input		Pulse/ frequency output		Current output 2		Current output 1 HART	

Safety-related and functional values of signal circuits

Signal circuits	Functional values	Safety-related values
Current output HART	galvanically isolated, active/passive can be selected: <ul style="list-style-type: none"> active: 0/4 to 20 mA $R_L < 700 \Omega$, $R_L \text{ HART} \geq 250 \Omega$ passive: 4 to 20 mA $V_s = 18 \text{ to } 30 \text{ V DC}$, $R_i \geq 150 \Omega$ 	intrinsically safe = no $U_m = 260 \text{ V}$ $I_m = 500 \text{ mA}$
Current output	galvanically isolated, active/passive can be selected: <ul style="list-style-type: none"> active: 0/4 to 20 mA $R_L < 700 \Omega$ passive: 4 to 20 mA $V_s = 18 \text{ to } 30 \text{ V DC}$, $R_i \geq 150 \Omega$ 	
Pulse/frequency output	galvanically isolated, active/passive can be selected: <ul style="list-style-type: none"> active: 24 V DC / 25 mA (max. 250 mA during 20 ms) $R_L > 100 \Omega$ passive: 30 V DC / 250 mA Open Collector Full scale frequency 2 to 10000 Hz ($f_{\max} = 12500 \text{ Hz}$)	
Relay output	galvanically isolated, max. 30 V AC / 500 mA max. 60 V DC / 100 mA	
Status input	galvanically isolated, 3 to 30 V DC $R_i = 5 \text{ k}\Omega$	

Service adapter

The service adapter is only used for connecting service interfaces approved by Endress+Hauser.

⚠ Warning!

It is not permissible to connect the service adapter whilst the atmosphere is considered to be explosive.

Device fuse

⚠ Warning!

Use only fuses of the following types; the fuses are installed on the power supply board:

- Voltage 20 to 55 V AC / 16 to 62 V DC:
fuse 2.0 A slow-blow, disconnect capacity 1500 A
(Schurter, 0001.2503 or Wickmann, Standard Type 181 2.0 A)
- Voltage 85 to 260 V AC:
fuse 0.8 A slow-blow, disconnect capacity 1500 A
(Schurter, 0001.2507 or Wickmann, Standard Type 181 0.8 A)

Technical Data**Dimensions**

Please refer to the respective Technical Information for these dimensions:

- Promass 80A, 83A → TI00054D
- Promass 80E, 83E → TI00061D
- Promass 80F, 83F → TI00101D
- Promass 80H, 83H → TI00074D
- Promass 80I, 83I → TI00075D
- Promass 80P, 83P → TI00078D
- Promass 80S, 83S → TI00076D

Weight

- The weight of the Ex d version is approx. 2 kg greater than that of the standard version.
- The weight of the Ex d version in stainless steel is approx. 9 kg greater than that of the standard version.

www.endress.com/worldwide

Endress+Hauser 
People for Process Automation