

















HE/24/09-2m1e

Page 1 of 1

## Manufacturer's Declaration

Endress+Hauser Process Solutions AG, Kägenstrasse 2, CH-4153 Reinach

## Fieldgate FXA320 / FXA520

Endress+Hauser Fieldgates FXA320 and FXA520 can be used in 4...20 mA loops in accordance with the technical specifications to be found in the corresponding Technical Information.

The FXA 520 can be connected as a non-reactive element to protection functions that are classified as SIL 2 as per IEC 61508.

The integrated radio module (wavecom O2686) enables operation in GSM/GPRS networks.

The embedded software of Fieldgates FXA320, FXA520 does not allow the storage or execution of any foreign, possibly harmful, program (viruses etc.)

The configuration of Fieldgates FXA320 and FXA520 is protected by a user identification and password. In addition, the hardware lock can be activated, preventing any unauthorized or accidental remote configuration.

Reinach, 19.11.2009

Endress+Hauser Process Solutions AG

(Dr. Raimund Sommer) Managing Director (Dr. Werner Thoren)
Manager Development Electr. & embedded Software



People for Process Automation