Liquiline[®]: a family you can rely on High-quality transmitters, analyzers and samplers for future-proof plant design and safe operations





They are family

Choose the Liquiline platform and you will spend less money on inventory, save installation time and gain operational safety.

The platform Several devices, all based on the Memosens technology, allowing multiple measurements on the same hardware: The Liquiline platform aligns inventory management and handling of transmitters, analyzers and samplers.

- Unified handling for more operational comfort and safety
- Fast commissioning and automatic sensor recognition thanks to pre-installed settings
- Standardized components for less inventory costs and long-term availability of spare parts
- Based on the Memosens[®] digital sensor technology you gain more efficiency and quality in liquid analysis
- Fieldbus protocols: 0/4..20 mA, HART[®], PROFIBUS[®] DP, Modbus[®] TCP, Modbus[®] RS485, EtherNet/IP[™], Webserver

Liquiline CM44 is the most flexible Liquiline controller: It measures 12 different parameters. Adapt it to connect 1 to 8 sensors, just by adding or removing modules. Liquiline CM44 is available both as field instrument and as DIN-rail device. The robust, corrosion-resistant plastic device is suitable for many applications, for example in the following industries:

- Water / Wastewater
- Chemical
- Life Sciences
- Food & Beverages
- Power plants



Liquiline M CM42 The two-wire transmitter for pH/ORP, conductivity and oxygen parameters stands out through safe data transmission and easy handling. User guidance and menu are equal to the Liquiline CM44. Liquiline CM42 can be connected to field buses like FOUNDATION™ Fieldbus, PROFIBUS PA and HART protocol. It is suitable for all areas of process engineering, especially in the following industries:

- Chemical processes
- Life Sciences
- Food technology
- Renewable energies
- Hazardous applications



Liquiline CM14 The four-wire transmitter for pH/ORP, conductivity and oxygen is an instrument for basic measurement requirements. Handling is easy, though CM14 does not share hard- or software with other Liquiline devices. The compact design of Liquiline CM14 is suitable for installation in panels or cabinets and especially attractive for skid building in:

- Wastewater treatment
- Water treatment and drinking water monitoring
- Ion exchangers
- Surface water monitoring



Liquiline To Go CYM290/CYM291 The multiparameter handhelds measure pH/ORP, conductivity and oxygen. Take them to any measuring point in your plant and you instantly know how your process is running. Both versions have a robust, shock-proof housing – the CYM291 is even suitable for hazardous area use. With Liquiline To Go handhelds you can use the same robust Memosens sensors for grab sample measurement that you use in your process. This guarantees full data consistency between your measurements.

Analyzers Thanks to the built-in Liquiline transmitters, operation of Liquiline System analyzers will be familiar because it is identical to the concept of other online analysis parameters such as pH or oxygen. Adapt them to connect 1 to 4 sensors just by adding modules and thus reduce the number of transmitters in your plant. Connect the sample preparation fast and easily due to Memosens technology.

- Liquiline System CA80AM ammonium
- Liquiline System CA80PH orthophosphate

Samplers Their built-in Liquiline transmitters make them members of the Liquiline family in terms of measurement parameters, handling, maintenance and spare parts. Adapt them to connect 1 to 4 sensors just by adding modules. Robust plastic or stainless steel housings make them suitable for all industries from wastewater to chemicals.

- Stationary sampler Liquistation CSF34
- Portable sampler Liquiport CSP44







Memosens: The cutting-edge sensor technology

Memosens digitizes the measured value within the sensor and provides non-contact interference-free transfer to the transmitter. Since its introduction in 2004, it has become the worldwide leading standard in liquid analysis. Since then, a large portfolio of Memosens products enhances the safety, efficiency, transparency and quality of processes in all industries.

- Safe digital data transmission: inductive, corrosionfree,100% reliable
- Easy-to-handle sensor connection
- Sensor head stores sensor and process specific data for predictive maintenance
- Fast plug & play with pre-calibrated sensors
- International standard



Liquiline CM42 stainless steel ATEX necessary Hygienic application yes yes Liquiline CM42 no plastic housing no Installation and others field Parameters: field device pH/ORP, oxygen

Which transmitter fits best for your application?

Liquiline CM44 and/or conductivity cabinet Liquiline CM44R DIN-rail device only Installation How many sensors cabinet 1 Liquiline CM14 field 1 - 8 Liquiline CM44R DIN-rail device How many sensors 1 - 8 Liquiline CM44 field device 1 Liquiline CM42 plastic housing Trademarks/Copyrights

(PI). Modbus is a trademarks of Schneider Electric. EtherNet/IP is a trademark of ODVA, Inc. FOUNDATION Fieldbus is a trademark of The Fieldbus FOUNDATION. All other trademarks are the properties of their respective owners. All other copyrights are the properties of their respective owners.





USA	Canada	Mexico	Other locations	
Endress+Hauser, Inc. 2350 Endress Place Greenwood, IN 46143 Tel: 317-535-7138 888-ENDRESS (888-363-7377) Fax: 317-535-8498 info@us.endress.com www.us.endress.com	Endress+Hauser Canada 1075 Sutton Drive Burlington, ON L7L 528 Tel: 905-681-9292 800-668-3199 Fax: 905-681-9444 info@ca.endress.com www.ca.endress.com	Endress+Hauser México S.A. de C.V. Fernando Montes de Oca 21 Edificio A Piso 3 Fracc. Industrial San Nicolás 54030 Tlalnepantla de Baz Estado de México México Tel: +52 55 5321 2080 Fax: +52 55 5321 2099 eh.mexico@mx.endress.com www.mx.endress.com	www.addresses.endress.com	СР01050С724/ЕМ/02.15 СР01050С724/ЕМ/02.15 © Endress+Hauser, Inc. 2017

