Safety Instructions **Tankside Monitor NRF81**

II 2 (1) G Ex db [ia Ga] IIC T6 Gb







Tankside Monitor NRF81

Table of contents

Associated documentation 4
Supplementary documentation
Manufacturer's certificates
Manufacturer address 4
Other standards
Extended order code 5
Safety instructions: General
Safety instructions: Special conditions
Safety instructions: Installation
Temperature tables
Connection data

Associated documentation

This document is an integral part of the following Operating Instructions:

BA01465G/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP000217.
- On the CD for devices with CD-based documentation

Manufacturer's certificates

UK Declaration of Conformity

Declaration Number: UK 00016

The UK Declaration of Conformity is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Declaration -> Type: UKCA Declaration -> Product Code: ...

UKCA type-examination certificate

Certificate number: FM21UKEX0002X

List of applied standards: See UK Declaration of Conformity.

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres Explosion prevention and protection - Part 1: Basic concepts and methodology"

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

NRF81	-	******	+	A*B*C*D*E*F*G*.
(Device		(Basic		(Optional
type)		specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Tankside Monitor



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type NRF81

Basic specifications

Position 1	Position 1, 2 (Approval)				
Selected option Descri		Description			
NRF81 UA		UK Ex II 2(1) G Ex db [ia Ga] IIC T6 Gb			

Position 5, 6 (Primary Output)			
Selected option		Description	
NRF81	A1	Modbus RS485	
	B1	V1	
	C1	WM550	
	E1	4-20mA HART Ex d/XP, RTD input	
	H1	4-20mA HART Ex i/IS, RTD input	

Position 7, 8 (Secondary I/O Analogue)				
Selected option		Description		
NRF81	A1	Ex d/XP, 1x 4-20 mA HART, 1x RTD input		
	A2	Ex d/XP, 2x 4-20 mA HART, 2x RTD input		
	B1	Ex i/IS, 1x 4-20 mA HART, 1x RTD input		
	B2	Ex i/IS, 2x 4-20 mA HART, 2x RTD input		
C2		1x Ex i/IS 4-20 mA HART, 2x RTD input + 1x Ex d/XP 4-20 mA HART		
	XO	Not selected		

Position 9, 10 (Secondary I/O Digital Ex d/XP)			
Selected opt	Selected option Description		
NRF81	A1	2x relay + 2x module discrete	
	A2	4x relay + 4x module discrete	
	A3	6x relay + 6x module discrete	
	B1	Modbus RS485	
	B2	Modbus RS485 + 2x relay + 2x module discrete	
	В3	Modbus RS485 + 4x relay + 4x module discrete	
	C1	V1	
	C2	V1 + 2x relay + 2x module discrete	
	C3	V1 + 4x relay + 4x module discrete	
	E1	WM550	
	E2	WM550 + 2x relay + 2x module discrete	
	E3	WM550 + 4x relay + 4x module discrete	
	X0	Not selected	

Position 11	Position 11, 12 (Housing)			
Selected op	otion	Description		
NRF81 AA Transmitter Alu, coated		Transmitter Alu, coated		
	BA	Transmitter 316/316L		

Optional specifications

No options specific to hazardous locations are available.

Safety instructions: General

 Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:


- Be suitably qualified for their role and the tasks they perform
- Be trained in explosion protection
- Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ..)
 - Of isolated capacities (e.g. isolated metallic plates)
- Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

Safety instructions: Special conditions

Permitted ambient temperature range at the electronics enclosure:

- → 🖹 11, "Temperature tables".
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
 - Observe the danger of electrostatic charging and discharge.
 - Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.
- Flamepath joints are not for repair. Contact the manufacturer.
- Use heat resisting cables rated ≥ 85 °C for $T_a > 50$ °C.
- Precautions shall be taken to minimize the risk from electrostatic discharge of non-metallic labels and isolated metal tags applied to the enclosure.
- To maintain the ingress protection ratings (IP66/68), teflon tape or pipe dope is required for blanking plugs.
- Ex d certified seals are required within 50 mm (2 in) on all used enclosure entries.

Safety instructions: Installation



A0035242

₩ 1

- A Zone 1
- 1 Tank; Zone 0, Zone 1
- 2 Observe Safety Instructions of used devices!
- 3 Tankside Monitor
- 4 to inventory management system
- 5 Potential equalization line
- 6 Potential equalization
- Install the device to exclude any mechanical damage or friction during the application.
- In potentially explosive atmospheres:
 - Do not disconnect the electrical connection of the power supply circuit when energized.
 - Do not open the connection compartment cover.
- Only use certified cable entries suitable for the application. Observe national regulations and standards. Accordingly, the connection terminal does not include any ignition sources.
- When operating the transmitter enclosure at an ambient temperature under -20 °C, use appropriate cables and cable entries permitted for this application.

 When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the enclosure.

- Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing clamp on the cover.

Potential equalization

Integrate the device into the local potential equalization.

Overvoltage protection

Overvoltage protection against atmospheric overvoltages.

The following Terminal outputs / configurations need no separate external overvoltage protection measures:

Position	Terminal
Power supply	G
HART interface	E
External display	F

- Device configuration:
 - Basic specification, Position 5, 6 = A1, B1, C1, E1, H1
 - Basic specification, Position 7, 8 = A1, A2, B1, B2, C2, X0
 - Basic specification, Position 9, 10 = B1, C1, E1
- All other configurations must be protected by separate additional measures to comply national regulations and standards.
- Observe the safety instructions of the overvoltage protection.

Temperature tables

Basic specification, Position 11, 12 = AA

Permitted ambient temperature range $T_{\rm a}$ (ambient)

-40 to +60 ℃

Basic specification, Position 11, 12 = BA




For configurations other than listed: use configuration 1.

Configuration of electronics:

	1 (worst case)	2 (best case)	3	4	5
Enclosure	Х	X	X	X	X
Slot A - IOM_D	Х		Х	Х	Х
Slot B - IOM_A (Ex ia)	Х		Х		Х
Slot C - IOM_A (Ex ia)	Х				
Slot D - IOM_D	Х				Х
PS_HV	Х	Х	Х	Х	Х
МВ	Х	Х	Х	Х	Х
	−40 to +50 °C	−40 to +60 °C	−40 to +60 °C	-40 to +60 °C	−40 to +55 °C

Connection data Connection compartment Ex d




A0035243

₽ 2

- 1 Connection for external display Ex i
- 2 Connection for HART interface Ex i
- 3 only when "Analog Ex i" installed

Detailed configuration information located at the display holder. Example for lettering:



A0035244

- ₩ 3
- 1 Area device configuration
- For detailed information see Operating Instructions.
- Assignment of the terminals see designation of front plane.

TRC[01], type Power supply

Terminal	G		CDI
	AC voltage	G1: N G2: not connected G3: L	plug connected
	DC voltage	G1: L+ G2: not connected G3: L-	
Designation	Power / Mains		Local LCD, CDI (internal)
non-Ex (functional)	$\begin{split} &U_{N}=85 \text{ to } 264 \text{ V}_{AC}, 50/60 \text{ Hz} \\ &P_{N}=28.8 \text{ VA} \\ &\text{or} \\ &U_{N}=52 \text{ to } 75 \text{ V}_{AC}, 50/60 \text{ Hz} \\ &P_{N}=21.6 \text{ VA} \\ &U_{N}=19 \text{ to } 64 \text{ V}_{DC} \\ &P_{N}=13.4 \text{ W} \end{split}$		$U_{N} = 3.3 V_{DC}$ $P_{N} = 41 \text{ mW}$

TRC[10], type Main board

Terminal	Е	F
	E1: H+ E2: H-	F1: Vcc F2: A F3: B F4: gnd
Designation	4-20 mA HART	Remote display
Ex [ia]	$\begin{split} &U_{o} = 29 \text{ V} \\ &I_{o} = 110 \text{ mA} \\ &P_{o} = 700 \text{ mW} \\ &C_{o} = 65 \text{ nF} \\ &L_{o} = 2.9 \text{ mH} \end{split}$	$\begin{array}{l} U_o = 3.9 \ V \\ I_o = 500 \ mA \\ P_o = 230 \ mW \\ C_o = 99 \ \mu F \\ L_o = 140 \ \mu H \end{array}$
non-Ex (functional)	$U_{N} = 24 V_{DC}$ $P_{N} \le 426 \text{ mW}$	$U_{N} = 3.3 V_{DC}$ $P_{N} = 41 \text{ mW}$

TRC[32], type "Modbus" module; optional

Terminal	Slot A through slot D		
	1:S Cable shielding; capacitive connected to earth 2: 0V Common reference 3: B- Non-inverting signal line 4: A+ Inverting signal line		
Designation	Modbus-Slave	FOUNDATION Fieldbus	
non-Ex (functional)	$\begin{aligned} &U_N = 12 \ V_{DC} \\ &P_N \leq 12 \ mW \\ &U_M = 250 \ V \end{aligned}$	Currently not supported	

TRC[33], type "V1" module; optional

Terminal	Slot A through slot D		
	1: S Cable shielding; capacitive connected to earth 2: not connected 3: B- Signal - 4: A+ Signal +		
Designation	V1-Slave	WM550	
non-Ex (functional)	$\begin{array}{c} U_{N} = 24 \; V_{DC} \\ P_{N} \leq 414 \; mW \\ U_{M} = 250 \; V \end{array}$	$\begin{split} &U_N = 4 \ V_{DC} \\ &P_N \leq 120 \ mW \\ &U_M = 250 \ V \end{split}$	

TRC[20], type "Analog module" (Ex i); 4-20 mA HART; optional

Terminal	Slot B or slot C		
Operation mode: 4 to 20 mA output or HART slave + 4 to 20 mA output or 4 to 20 mA input or HART master + 4 to 20 mA input or HART master	4-wire RTD connection: Terminal 5 through 8 3-wire RTD connection:	Terminal active use: 2: H- 3: H+ Terminal passive use: 1: H- 2: H+	
	Terminal 5, 6 and 8 2-wire RTD connection: Terminal 5 and 8		
Designation	24 V + RTD	4-20 mA HART	
Ex (ia)	Terminals 4-5 (24 V): $ U_{o} = 29 \text{ V} $ $ I_{o} = 108 \text{ mA} $ $ P_{o} = 776 \text{ mW} $ $ C_{o} = 63 \text{ nF} $ $ L_{o} = 3.0 \text{ mH} $	Terminals 2-3 (Active): $ U_{o} = 29 \text{ V} $ $ I_{o} = 106 \text{ mA} $ $ P_{o} = 760 \text{ mW} $ $ C_{o} = 63 \text{ nF} $ $ L_{o} = 3.1 \text{ mH} $	
	Terminals 5-8 (RTD): $U_{0} = 29 \text{ V}$ $I_{0} = 36 \text{ mA}$ $P_{0} = 263 \text{ mW}$ $C_{0} = 64 \text{ nF}$ $L_{0} = 26 \text{ mH}$	$\begin{split} & \text{Terminals 1-2 (Passive):} \\ & U_i = 29 \text{ V} \\ & I_i = 106 \text{ mA} \\ & P_i = 760 \text{ mW} \\ & C_i = 11 \text{ nF} \\ & L_i = 0 \end{split}$	
non-Ex (functional)	Terminals 4-5 (24 V): $ U_N = 24 \ V_{DC} $ $ P_N \leq 600 \ mW $	Terminals 2-3 (Active): $ U_N = 24 \ V_{DC} $ $ P_N \leq 540 \ mW $	
	Terminals 5-8 (RTD): $I_N = 400 \ \mu A_{DC}$ $P_N \le 160 \ \mu W$	Terminals 1-2 (Passive):	

TRC[21], type "Analog module" (Ex d); 4-20 mA HART; optional

Terminal	Slot B or slot C		
Operation mode: 4 to 20 mA output or HART slave + 4 to 20 mA output or 4 to 20 mA input or HART master + 4 to 20 mA input or HART master	4-wire RTD connection: Terminal 5 through 8 3-wire RTD connection:	Terminal active use: 2: H- 3: H+	
	Terminal 5, 6 and 8 2-wire RTD connection: Terminal 5 and 8	Terminal passive use: 1: H- 2: H+	
Designation	24 V + RTD	4-20 mA HART	
non-Ex (functional)	Terminals 4-5 (24 V): not used	$\begin{split} & \text{Terminals 2-3 (Active):} \\ & U_N = 24 \ V_{DC} \\ & P_N \leq 540 \ mW \\ & U_M = 250 \ V \end{split}$	
	$\begin{split} & \text{Terminals 5-8 (RTD):} \\ & I_N = 400 \; \mu A_{DC} \\ & P_N \leq 160 \; \mu W \\ & U_M = 250 \; V \end{split}$	$\begin{split} & \text{Terminals 1-2 (Passive):} \\ & U_N = 29 \ V_{DC} \\ & P_N \leq 653 \ mW \\ & U_M = 250 \ V \end{split}$	

TRC[31], type "Digital"; optional


Terminal	Slot A through slot D			
Operation mode:	Installed in slot A:			
disabledpassive outputpassive input	1: A1-1 2: A1-2	3: A2-1 4: A2-2		
 active input 	Installed in slot B:			
	1: B1-1 2: B1-2	3: B2-1 4: B2-2		
	Installed in slot C:			
	1: C1-1 2: C1-2	3: C2-1 4: C2-2		
	Installed in slot D:			
	1: D1-1 2: D1-2	3: D2-1 4: D2-2		
Designation	Relay / Digital Input/Output 1	Relay / Digital Input/Output 2		
non-Ex (functional)	$\begin{aligned} & \text{Relay:} \\ & \text{U}_{N} = 250 \text{ V}_{\text{AC/DC}} \\ & \text{I}_{N} \leq 2 \text{ A} \end{aligned}$	Relay: $ U_N = 250 \ V_{AC/DC} $ $ I_N \le 2 \ A $		
	Digital Input: $ U_N = 5 \text{ to } 230 \text{ V}_{AC/DC} $ $ U_M = 250 \text{ V} $	Digital Input: $ U_N = 5 \text{ to } 230 \text{ V}_{AC/DC} $ $ U_M = 250 \text{ V} $		

Tankside Monitor NRF81

Table	of	contents

tto alamant. Namanlata vieve	10
Milacilinelli. Namepiale view	 TO

Attachment: Nameplate view



A0045335

Pos	Position	VGR	Code	Text	Ex- relevant
1	Manufacturer address	-	-	Made in Germany, 79689 Maulburg, Hauptstrasse 1	yes
2	Order code	-	UA	NRF80- 12 digits, mandatory NRF81- 16 digits, mandatory	yes
3	Serial number	-	-	mandatory	yes
4	Extended order code	-	-	optional, digits not limited	no
			В	85264 V AC (50/60 Hz) 28.8 VA	yes
5	Supply voltage	030	D	5275 V AC (50/60 Hz) 21.6 VA	yes
			E	1964 V DC 13.4 W	yes
			Α	Thread M20	yes
8	Thread cable entry	090	В	Thread M25	yes
0	Tillead Cable elitry	090	E	Thread NPT1/2	yes
			F	Thread NPT3/4	yes
			AA	Aluminium	yes
9	Material	070	ВА	316/316L	yes
9	Material	070	Y9	316/316L special coating for e.g. marine applications	yes
10	Device ID	-	-		no
11	Firmware version	-	-		no
12	Device revision	-	-		no
13	PTB certification number	-	-		no
14	Customized parametrization data	-	-		no
15	Permissible ambient temperature	010	all	-40+50°C, -40+55°C or -40+60°C depending on version	yes
16	UKCA mark	010	UR UA	mark without any no. mark with additional approved body no.	UK only
17	Additional information of the device version	-	-	Markings, not relevant for Ex: e.g. C-Tick, SIL, 3A,	no
18	Ingress protection	-	-	IP68 / 66, Type 4X / 6P Encl.	yes
19	Certificate symbol	010	UA	⟨£x⟩ "Ex-Hexagon"	yes
			UA	FM21UKEX0002X	yes
			UA	II 2 (1) G Ex db [ia Ga] IIC T6 Gb	yes
			UA	Entity Parameters per XA02423G	yes
20	Data concerning Ex approvals	010	UA	Warning - do not open when explosive atmosphere is present	
21	General cerficate of approval	010	all	e.g. Overspill protection; optional	no
22	Associated Safety Instruction (XA)	010	UA	XA02423G (actual rev.)	yes
23	Manufacturing date	010	all	YYYY-MM	yes
24	QR code for E+H Operations App	-	-		no

A0045336



www.addresses.endress.com