

# Safety Instructions

## **Deltabar S**

### **PMD75, FMD77, FMD78**

4-20 mA HART, PROFIBUS PA,  
FOUNDATION Fieldbus

II 1 G Ex ia IIC Ga

II 1 D Ex ia IIIC Da



---

# Deltabar S PMD75, FMD77, FMD78

4-20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus

## Table of contents

Associated documentation ..... 4

Supplementary documentation ..... 4

Manufacturer's certificates ..... 4

Manufacturer address ..... 4

Other standards ..... 5

Extended order code ..... 5

Safety instructions: General ..... 9

Safety instructions: Special conditions ..... 9

Safety instructions: Installation ..... 10

Temperature tables ..... 11

Connection data ..... 12

**Associated documentation**

This document is an integral part of the following Operating Instructions:

HART

- BA00270P/00
- BA00274P/00

PROFIBUS PA

- BA00294P/00
- BA00296P/00

FOUNDATION Fieldbus

- BA00301P/00
- BA00303P/00

**Supplementary documentation**

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website:  
[www.endress.com](http://www.endress.com) -> Downloads -> Brochures and Catalogs ->  
Text Search: CP00021Z
- On the CD for devices with CD-based documentation

**Manufacturer's certificates****UK Declaration of Conformity**

Declaration Number:

UK\_00082

The UK Declaration of Conformity is available:

In the download area of the Endress+Hauser website:

[www.endress.com](http://www.endress.com) -> Downloads -> Declaration ->

Type: UKCA Declaration -> Product Code: ...

**UKCA type-examination certificate**

Certificate number:

CML 21UKEX2441X

List of applied standards: See UK Declaration of Conformity.

**Manufacturer address**

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

**Other standards** Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres - Explosion prevention and protection - Part 1: Basic concepts and methodology"

**Extended order code** The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

**Structure of the extended order code**

PMD75,  
FMD7x

–

\*\*\*\*\*

+

A\*B\*C\*D\*E\*F\*G\*..

(Device  
type)

(Basic  
specifications)

(Optional  
specifications)

\* = Placeholder  
At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

*Basic specifications*


The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.  
The selected option of a feature can consist of several positions.

*Optional specifications*

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

**Extended order code: Deltabar S**

-  The following specifications reproduce an extract from the product structure and are used to assign:
- This documentation to the device (using the extended order code on the nameplate).
  - The device options cited in the document.

*Device type*

PMD75

*Basic specifications*

Position 1 (Approval)		
Selected option		Description
PMD75	8	ATEX II 1 G Ex ia IIC T6...T4 Ga ATEX II 1 D Ex ia IIIC T <sub>200</sub> 70°C Da

Position 2 (Output, Operating)		
Selected option		Description
PMD75	A, B, C	4-20 mA HART
	D, E, F	4-20 mA HART, L <sub>1</sub> = 0
	M, N, O	PROFIBUS PA
	P, Q, R	FOUNDATION Fieldbus

Position 3 (Housing, Cover Sealing, Cable Entry)		
Selected option		Description
PMD75	A-E	T14, Alu IP66/67 NEMA6P; EPDM
	G, H	T14, Alu IP66/67 NEMA6P; FVMQ
	J-N	T15, Alu IP66/67 NEMA6P; EPDM
	R-V	T17, 316L hygiene IP66/68 NEMA6P; EPDM
	1-5	T14, 316L IP66/67 NEMA6P; EPDM
	7, 8	T14, 316L IP66/67 NEMA6P; FVMQ

Position 10 (Additional Option 1)		
Selected option		Description
PMD75	M	Overvoltage protection

Position 11 (Additional Option 2)		
Selected option		Description
PMD75	M	Overvoltage protection

Optional specifications

ID Jx (Test, Certificate)		
Selected option		Description
PMD75	JN	Ambient temperature transmitter -50 °C/-58 °F

ID Lx (Additional Approval)		
Selected option		Description
PMD75	LU	UK marking



- The following specifications reproduce an extract from the product structure and are used to assign:
- This documentation to the device (using the extended order code on the nameplate).
  - The device options cited in the document.

Device type

FMD77, FMD78

Basic specifications

Position 1 (Approval)		
Selected option		Description
FMD7x	8	ATEX II 1 G Ex ia IIC T6...T4 Ga ATEX II 1 D Ex ia IIIC T <sub>200</sub> 70°C Da

Position 2 (Output, Operating)		
Selected option		Description
FMD7x	A, B, C	4-20 mA HART
	D, E, F	4-20 mA HART, L <sub>1</sub> = 0
	M, N, O	PROFIBUS PA
	P, Q, R	FOUNDATION Fieldbus

Position 3 (Housing, Cover Sealing, Cable Entry)		
Selected option		Description
FMD7x	A-E	T14, Alu IP66/67 NEMA6P; EPDM
	G, H	T14, Alu IP66/67 NEMA6P; FVMQ
	J-N	T15, Alu IP66/67 NEMA6P; EPDM
	R-V	T17, 316L hygiene IP66/68 NEMA6P; EPDM
	1-5	T14, 316L IP66/67 NEMA6P; EPDM
	7, 8	T14, 316L IP66/67 NEMA6P; FVMQ

Position 11 (Additional Option 1)		
Selected option		Description
FMD7x	M	Overvoltage protection

Position 12 (Additional Option 2)		
Selected option		Description
FMD7x	M	Overvoltage protection

*Optional specifications*

ID Jx (Test, Certificate)		
Selected option		Description
FMD7x	JN	Ambient temperature transmitter -50 °C/-58 °F

ID Lx (Additional Approval)		
Selected option		Description
FMD7x	LU	UK marking




**Safety  
instructions:  
General**

- The device is intended to be used in explosive atmospheres as defined in the scope of EN IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Comply with the installation and safety instructions in the Operating Instructions.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ..)
  - Of isolated capacities (e.g. isolated metallic plates)

**Safety  
instructions:  
Special conditions**

- For light metal flanges or flange faces (e.g. titanium, zirconium), avoid sparks caused by impact and friction.
- Install the device to exclude sparks caused by impact and friction on the aluminium enclosure and/or a light-metal process connection.
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
  - Observe the danger of electrostatic charging and discharge.
  - Do not install in the vicinity of processes ( $\leq 0.5$  m) generating strong electrostatic charges.

## Safety instructions: Installation



A0027673

- A Zone 0, Zone 20, Electronic  
 B Zone 0, Zone 20, Process  
 1 Certified associated apparatus  
 2 PMD75, FMD77, FMD78

- After aligning (rotating) the enclosure, retighten the fixing screw.
- The device is designed for operation in Zone 0 or Zone 20. In the event of potentially explosive gas-air and dust-air mixtures occurring simultaneously: Suitability requires further assessment.

### Intrinsic safety

- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least  $500 V_{\text{rms}}$ .
- When the device is connected to an intrinsically safe circuit Ex ib, the type of protection changes to Ex ib. Do not operate intrinsically safe circuits Ex ib in Zone 0 or Zone 20.
- When the device is connected to an intrinsically safe circuit Ex ic, the type of protection changes to Ex ic. Do not operate intrinsically safe circuits Ex ic in Zone 0, Zone 1 or Zone 20, Zone 21.

### Overvoltage protection

Device type PMD75, Basic specification, Position 10 + 11 = M

Device type FMD77, FMD78, Basic specification, Position 11 + 12 = M

The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least  $290 V_{\text{rms}}$ .

Temperature tables

II 1 G Ex ia IIC T6...T4 Ga

Temperature class	Process temperature T <sub>p</sub> (process)	Ambient temperature range
T6	≤ 80 °C	−40 °C ≤ T <sub>a</sub> ≤ +40 °C
T4	≤ 120 °C <sup>1)</sup>	−40 °C ≤ T <sub>a</sub> ≤ +70 °C

1) Only Device type PMD75

II 1 D Ex ia IIIC T<sub>200</sub> 70°C Da

Max. surface temperature at max. ambient temperature	Basic specification, Position 2 =	Process temperature range	Ambient temperature range
T70 °C	A, B, C, D, E, F	−40 °C ≤ T <sub>p</sub> ≤ +40 °C	−40 °C ≤ T <sub>a</sub> ≤ +40 °C
	M, N, O, P, Q, R	−40 °C ≤ T <sub>p</sub> ≤ +34 °C	−40 °C ≤ T <sub>a</sub> ≤ +34 °C



Do not exceed the max. ambient temperature at the enclosure.

Device type PMD75

The process temperatures refer to the temperature at the separation membrane.

Device type FMD77

Deratings between process temperature and ambient temperature at the enclosure depending on the way of installation as well as functional aspects: See Operating Instructions.

Device type FMD78

The external heat influence depends only on the mountig position of the transmitter itself. Therefore a sufficient capillary length to mount the enclosure at a position with an allowed ambient temperature must be ordered.

Optional specification, ID Jx = JN

Lower limit of the ambient temperature for explosion protection changes to −50 °C.

Connection data

Basic specification, Position 2 = A, B, C, D, E, F

Power supply
<div>U<sub>I</sub> ≤ 30 V<sub>DC</sub> I<sub>I</sub> ≤ 300 mA P<sub>I</sub> ≤ 1 W C<sub>I</sub> ≤ 11.8 nF L<sub>I</sub> ≤ 225 µH<sup>1)</sup> or L<sub>I</sub> = 0<sup>2)</sup></div>

- 1) Basic specification, Position 2 = A, B, C
- 2) Basic specification, Position 2 = D, E, F

Basic specification, Position 2 = M, N, O, P, Q, R

Power supply	
<div>FISCO  U<sub>I</sub> ≤ 17.5 V<sub>DC</sub> I<sub>I</sub> ≤ 500 mA P<sub>I</sub> ≤ 5.5 W C<sub>I</sub> ≤ 5 nF L<sub>I</sub> ≤ 10 µH</div>	<div>Entity  U<sub>I</sub> ≤ 24 V<sub>DC</sub> I<sub>I</sub> ≤ 250 mA P<sub>I</sub> ≤ 1.2 W C<sub>I</sub> ≤ 5 nF L<sub>I</sub> ≤ 10 µH</div>

---

---

---



71549684

[www.addresses.endress.com](http://www.addresses.endress.com)

---