

# Safety Instructions

## Proline Promass 200

Class I, Division 1; Zone 1 for XP  
(Ex d Flameproofed version)



Document: XA00151D  
Safety instructions for electrical apparatus for explosion-hazardous areas → 3

---

# Proline Promass 200

## Table of contents

Associated documentation .....	4
Manufacturer's certificates .....	4
Manufacturer address .....	4
Extended order code .....	5
Safety instructions: General .....	7
Safety instructions: Installation .....	8
Safety instructions: Class II,Class III .....	8
Temperature tables .....	9
Connection values: Signal circuits .....	18

**Associated documentation**

All documentation is available:

- On the CD-ROM supplied (not included in the delivery for all device versions).
- Available for all device versions via:
  - Internet: [www.endress.com/deviceviewer](http://www.endress.com/deviceviewer)
  - Smart phone/tablet: *Endress+Hauser Operations App*
- In the Download Area of the Endress+Hauser web site:  
[www.endress.com](http://www.endress.com) → Download

This document is an integral part of the following Operating Instructions:

<b>Measuring device</b>	<b>Documentation code</b>		
	<b>HART</b>	<b>FOUNDATION Fieldbus</b>	<b>PROFIBUS PA</b>
8A2B**_...	BA01821D	BA01827D	BA01828D
8E2B**_...	BA01027D	BA01314D	BA01133D
8E2C**_...	BA01638D	BA01637D	BA01639D
8F2B**_...	BA01112D	BA01315D	BA01113D

*Additional documentation*

<b>Contents</b>	<b>Document type</b>	<b>Documentation code</b>
Remote display FHX50	Special documentation	SD01007F
	Safety Instructions Division 1	XA01095F
Control drawing		As wanted on the nameplate.

Please note the documentation associated with the device.

**Manufacturer's certificates**
**Certificate number**

160686-2317872

**Notified body**

CSA: Canadian Standards Association

**Manufacturer address**

Endress+Hauser Flowtec AG  
Kägenstrasse 7  
4153 Reinach BL  
Switzerland

## Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

### Structure of the extended order code

*****	-	***** ... *****	+	A*B*C*D*E*F*G*...
<i>(Device type)</i>		<i>(Basic specifications)</i>		<i>(Optional specifications)</i>

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

#### *Device type*

The device and the device design is defined in the "Device type" section (Product root).

#### *Basic specifications*

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.

The selected option of a feature can consist of several positions.

#### *Optional specifications*

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

### Device type

Position	Order code for	Option selected	Description
1	Instrument family	8	Coriolis flowmeter
2	Sensor	A, E, F	Sensor type
3	Transmitter	2	Transmitter type: 2-wire, compact version

<b>Position</b>	<b>Order code for</b>	<b>Option selected</b>	<b>Description</b>
4	Generation index	B, C	Platform generation
5, 6	Nominal diameter	01, 02, 04, 08, 15, 25, 40, 50, 80	Nominal diameter of sensor

### Basic specifications

<b>Position</b>	<b>Order code for</b>	<b>Option selected</b>	<b>Device type</b>	<b>Position 5, 6 Nominal diameter</b>	<b>Description</b>
			Position 2 Sensor		
1, 2	Approval	C3	A, E, F	01, 02, 04, 08, 15, 25, 40, 50	Class I, Division 1 for Group A, B, C, D
			F	80	Class I, Division 1 for Group C, D
			A, E, F	01, 02, 04, 08, 15, 25, 40, 50, 80	Class II, Division 1 for Group E, F, G Class III
			A, E, F	01, 02, 04, 08, 15, 25, 40, 50	Ex d[ia] IIC and AEx d[ia] IIC
			F	80	Ex d[ia] IIB and AEx d[ia] IIB
			A, E, F	01, 02, 04, 08, 15, 25, 40, 50, 80	Class I Zone 1

<b>Position</b>	<b>Order code for</b>	<b>Option selected</b>	<b>Description</b>
3	Output; Input	A	4-20mA HART
		B	4-20mA HART, Pulse/frequency/switch output
		C	4-20mA HART + 4-20mA analog
		E	FOUNDATION Fieldbus, Pulse/frequency/ switch output
		G	PROFIBUS PA, Pulse/frequency/switch output
4	Display; Operation	A	W/o; via communication
		C	SD02 4-line; push buttons + data backup function
		E	SD03 4-line, illum.; touch control + data backup function
		L	Prepared for display FHX50 + M12 connection <sup>1)</sup>

Position	Order code for	Option selected	Description
		M	Prepared for display FHX50 + M12 custom connection <sup>1)</sup>
17, 18 <sup>2)</sup>	Device Model	A1	1

1) FHX50 is approved separately.

2) Order code for "Device model" only for measuring devices with product code 8A2B, 8E2C\*\*,

**Safety instructions:  
General**

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations (e.g. CEC or NEC)
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature classes.
- Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- When using in hybrid mixtures (gas and dust occurring simultaneously), observe additional measures for explosion protection.
- Observe all the technical data of the device (see nameplate).
- Class II Group G: The surface temperature of the apparatus cannot exceed +165 °C.
- Classification of Zones: When installed in Zone 1 the interior of the measuring tube is permissible for use in Zone 0.  
In Zone 0/1 not permitted: Promass A DN1 (order code "Nominal Diameter", Option 01)

**⚠ WARNING**

**Substitution of components is not permitted.**

- ▶ Substitution of components may impair intrinsic safety.

**Safety  
instructions:  
Installation**

- Continuous service temperature of the connecting cable:  
-40 to +80 °C; in accordance with the range of service temperature taking into account additional influences of the process conditions ( $T_{a,min}$  and  $T_{a,max} + 20$  K).
- Only use certified cable entries suitable for the application. Observe selection criteria as per CEC or NEC.  
Accordingly, the connection terminal does not include any ignition sources.
- When the measuring device is connected, attention must be paid to explosion protection at the transmitter.
- In potentially explosive atmospheres:
  - Do not disconnect the electrical connection of the power supply circuit when energized.
  - Do not open the connection compartment cover when energized.
- Install the transmitter circuit wiring according to Canadian Electrical Code (CEC) respective National Electrical Code (NEC) using threaded conduit or other wiring methods in accordance with articles 500 to 510.
- Transmitter enclosure is factory sealed. A conduit seal is not required.
- The sensors Promass E and Promass F is rated as Dual Seal Device in accordance with ANSI/ISA-12.27.01-2003. The sensor Promass E is only rated as Dual Seal Device, if the optional rupture disk is present.

**Intrinsic safety**

- The device can be connected to the Endress+Hauser FXA291 service tool: refer to the Operating Instructions.
- The device can be connected to the remote display FHX50 with IS explosion protection; refer to the Special Documentation and Ex documentation.

**Potential equalization**

- Integrate the device into the local potential equalization .
- If the ground connection has been established via the pipe as specified, it is also possible to integrate the sensor into the potential equalization system via the pipe.

**Safety  
instructions:  
Class II, Class III**

- To ensure dust-tightness, securely seal the transmitter housing, cable entries and sealing plugs.
- Only open the transmitter housing briefly, ensuring that no dust or moisture enters the housing.
- The remote display FHX50 is not suitable for installation in Class II, Class III.

## Temperature tables

### Ambient temperature

#### Minimum ambient temperature

*Basic specification, position 3 (Output; input) = A, B, C, E, G:*

$$T_a = -40 \text{ } ^\circ\text{C}$$

Maximum ambient temperature:

$T_a = +60 \text{ } ^\circ\text{C}$  depending on the medium temperature and temperature class

### Medium temperature

#### Minimum medium temperature

- Promass 8F2B\*\*-..., Promass 8A2B\*\*-...

$$T_m = -50 \text{ } ^\circ\text{C}$$

- Promass 8E2B\*\*-..., Promass 8E2C\*\*-...:

$$T_m = -40 \text{ } ^\circ\text{C}$$

#### Maximum medium temperature

$T_m$  for T6...T1 depending on the maximum ambient temperature  $T_a$

### Compact version

*Basic specification, position 3 (Output; Input) = A*

*Basic specification, position 1, 2 (Approval) = C3*

## Promass A

DN	$T_{m,\max}$ [°C]	$T_a$ [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	40	50	95	130	170	205	205
		60	-	95	130	170	205	205

## Promass E (Promass 8E2B\*\*-...)

DN	$T_{m,\max}$ [°C]	$T_a$ [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	140	50	50	95	130	140	140	140
		60	-	95	130	140	140	140

## Promass E (Promass 8E2C\*\*-...)

DN	$T_{m,\max}$ <sup>1)</sup> [°C]	$T_a$ [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	150	150	150
		60	-	95	130	150	150	150

DN	T <sub>m,max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
	205	40	50	95	130	170	205	205
		60	–	95	130	170	205	205

1) Maximum temperature range, see nameplate

### Promass F

DN	T <sub>m,max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	150	150	150
		60	–	95	130	150	150	150
	205	40	50	95	130	170	205	205
		60	–	95	130	170	205	205
80	150	40	50	85	110	150	150	150
		60	–	85	110	150	150	150
	205	40	50	85	110	170	205	205
		60	–	85	110	170	205	205

1) Maximum temperature range, see nameplate

*Basic specification, position 3 (Output; Input) = B  
Basic specification, position 1, 2 (Approval) = C3*

*Promass A*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	40	50	95	130	170	205	205
		50 <sup>1)</sup>	–	95	130	170	205	205
		55	–	–	130	170	205	205
		60	–	–	130	170	205	200

- 1) T<sub>a</sub> = 55 °C for Impulse/Frequency/Switch output input P<sub>i</sub> ≤ 0,85 W

*Promass E (Promass 8E2B\*\*-... )*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	140	140	140
		50 <sup>1)</sup>	–	95	130	140	140	140
		60	–	–	130	140	140	140

- 1) T<sub>a</sub> = 55 °C for Impulse/Frequency/Switch output input P<sub>i</sub> ≤ 0,85 W

*Promass E (Promass 8E2C\*\*-... )*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	150	150	150
		50 <sup>2)</sup>	–	95	130	150	150	150
		55	–	–	130	150	150	150
		60	–	–	130	150	150	150
	205	40	50	95	130	170	205	205
		50 <sup>2)</sup>	–	95	130	170	205	205
		55	–	–	130	170	205	205
		60	–	–	130	170	205	200

- 1) Maximum temperature range, see nameplate  
2) T<sub>a</sub> = 55 °C for Impulse/Frequency/Switch output input P<sub>i</sub> ≤ 0,85 W

*Promass F*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	150	150	150
		50 <sup>2)</sup>	-	95	130	150	150	150
		55	-	-	130	150	150	150
		60	-	-	130	150	150	150
	205	40	50	95	130	170	205	205
		50 <sup>2)</sup>	-	95	130	170	205	205
		55	-	-	130	170	205	205
		60	-	-	130	170	205	200
80	150	40	50	85	110	150	150	150
		50 <sup>2)</sup>	-	85	110	150	150	150
		55	-	-	110	150	150	150
		60	-	-	110	150	150	150
	205	40	50	85	110	170	205	205
		50 <sup>2)</sup>	-	85	110	170	205	205
		55	-	-	110	170	205	205
		60	-	-	110	170	205	200

1) Maximum temperature range, see nameplate

2) T<sub>a</sub> = 55 °C for Impulse/Frequency/Switch output input P<sub>i</sub> ≤ 0,85 W

*Basic specification, position 3 (Output; Input) = C  
Basic specification, position 1, 2 (Approval) = C3*

*Promass A*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	40	50	95	130	170	205	205
		55	–	95	130	170	205	205
		60	–	–	130	170	205	200

*Promass E (Promass 8E2B\*\*-... )*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	140	140	140
		55	–	95	130	140	140	140
		60	–	–	130	140	140	140

*Promass E (Promass 8E2C\*\*-... )*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	150	150	150
		55	–	95	130	150	150	150
		60	–	–	130	150	150	150
	205	40	50	95	130	170	205	205
		55	–	95	130	170	205	205
		60	–	–	130	170	205	200

1) Maximum temperature range, see nameplate

*Promass F*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40	50	95	130	150	150	150
		55	–	95	130	150	150	150
		60	–	–	130	150	150	150
	205	40	50	95	130	170	205	205
		55	–	95	130	170	205	205

DN	T <sub>m,max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
		60	-	-	130	170	205	200
80	150	40	50	85	110	150	150	150
		55	-	85	110	150	150	150
		60	-	-	110	150	150	150
	205	40	50	85	110	170	205	205
		55	-	-	110	170	205	205
		60	-	-	110	170	205	200

1) Maximum temperature range, see nameplate

*Basic specification, position 3 (Output; Input) = E*  
*Basic specification, position 1, 2 (Approval) = C3*

*Promass A*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	40 <sup>1)</sup>	50	95	130	170	205	205
		55 <sup>2)</sup>	–	95	130	170	205	205
		60	–	–	130	170	205	205

- 1) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output  
 2) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output

*Promass E (Promass 8E2B\*\*-... )*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40 <sup>1)</sup>	50	95	130	140	140	140
		55 <sup>2)</sup>	–	95	130	140	140	140
		60	–	–	130	140	140	140

- 1) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output  
 2) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output

*Promass E (Promass 8E2C\*\*-... )*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40 <sup>2)</sup>	50	95	130	150	150	150
		55 <sup>3)</sup>	–	95	130	150	150	150
		60	–	–	130	150	150	150
	205	40 <sup>2)</sup>	50	95	130	170	205	205
		55 <sup>3)</sup>	–	95	130	170	205	205
		60	–	–	130	170	205	205

- 1) Maximum temperature range, see nameplate  
 2) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output  
 3) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output

*Promass F*

<b>DN</b>	<b>T<sub>m, max</sub><sup>1)</sup> [°C]</b>	<b>T<sub>a</sub> [°C]</b>	<b>T6 [85 °C]</b>	<b>T5 [100 °C]</b>	<b>T4 [135 °C]</b>	<b>T3 [200 °C]</b>	<b>T2 [300 °C]</b>	<b>T1 [450 °C]</b>
8...50	150	40 <sup>2)</sup>	50	95	130	150	150	150
		55 <sup>3)</sup>	–	95	130	150	150	150
		60	–	–	130	150	150	150
	205	40 <sup>2)</sup>	50	95	130	170	205	205
		55 <sup>3)</sup>	–	95	130	170	205	205
		60	–	–	130	170	205	205
80	150	40 <sup>2)</sup>	50	85	110	150	150	150
		55 <sup>3)</sup>	–	85	110	150	150	150
		60	–	–	110	150	150	150
	205	40 <sup>2)</sup>	50	85	110	170	205	205
		55 <sup>3)</sup>	–	85	110	170	205	205
		60	–	–	110	170	205	205

1) Maximum temperature range, see nameplate

2) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output3) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output

*Basic specification, position 3 (Output; Input) = G*  
*Basic specification, position 1, 2 (Approval) = C3*

*Promass A*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	40 <sup>1)</sup>	50	95	130	170	205	205
		55 <sup>2)</sup>	–	95	130	170	205	205
		60	–	–	130	170	205	205

- 1) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output  
 2) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output

*Promass E (Promass 8E2B\*\*-... )*

DN	T <sub>m, max</sub> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40 <sup>1)</sup>	50	95	130	140	140	140
		55 <sup>2)</sup>	–	95	130	140	140	140
		60	–	–	130	140	140	140

- 1) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output  
 2) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output

*Promass E (Promass 8E2C\*\*-... )*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40 <sup>2)</sup>	50	95	130	150	150	150
		55 <sup>3)</sup>	–	95	130	150	150	150
		60	–	–	130	150	150	150
	205	40 <sup>2)</sup>	50	95	130	170	205	205
		55 <sup>3)</sup>	–	95	130	170	205	205
		60	–	–	130	170	205	205

- 1) Maximum temperature range, see nameplate  
 2) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output  
 3) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output


*Promass F*

DN	T <sub>m, max</sub> <sup>1)</sup> [°C]	T <sub>a</sub> [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	150	40 <sup>2)</sup>	50	95	130	150	150	150
		55 <sup>3)</sup>	–	95	130	150	150	150
		60	–	–	130	150	150	150
	205	40 <sup>2)</sup>	50	95	130	170	205	205
		55 <sup>3)</sup>	–	95	130	170	205	205
		60	–	–	130	170	205	205
80	150	40 <sup>2)</sup>	50	85	110	150	150	150
		55 <sup>3)</sup>	–	85	110	150	150	150
		60	–	–	110	150	150	150
	205	40 <sup>2)</sup>	50	85	110	170	205	205
		55 <sup>3)</sup>	–	85	110	170	205	205
		60	–	–	110	170	205	205

1) Maximum temperature range, see nameplate

2) T<sub>a</sub> = 50 °C for use without Impulse/Frequency/Switch output3) T<sub>a</sub> = 60 °C for use without Impulse/Frequency/Switch output**Connection values: Signal circuits**

The following tables contain specifications which are dependent on the transmitter type and its input and output assignment. Compare the following specifications with those on the nameplate of the transmitter.

**Connecting the transmitter**

A0023831

Position		Basic specification, position 1, 2 Approval	Type of protection used for cable entry	Description
1	Cable entry for output 1	C3	XP/Ex d/DIP XP/AEx d/DIP	<p>Plastic sealing plugs act as safeguards during transportation and must be replaced by suitable, individually approved installation material.</p> <p>The metal extensions and dummy plugs supplied are tested and certified as part of the housing for explosion protection XP/Ex d. The various threaded versions are labeled as follows for identification purposes:</p> <ul style="list-style-type: none"> <li>▪ Md: M20 x 1.5</li> <li>▪ NPTd: NPT <math>\frac{1}{2}</math>"</li> <li>▪ Gd: G <math>\frac{1}{2}</math>"</li> </ul>
2	Cable entry for output 2	C3	XP/Ex d/DIP XP/AEx d/DIP	<p>Plastic sealing plugs act as safeguards during transportation and must be replaced by suitable, individually approved installation material.</p> <p>The metal extensions and dummy plugs supplied are tested and certified as part of the housing for explosion protection XP/Ex d. The various threaded versions are labeled as follows for identification purposes:</p> <ul style="list-style-type: none"> <li>▪ Md: M20 x 1.5</li> <li>▪ NPTd: NPT <math>\frac{1}{2}</math>"</li> <li>▪ Gd: G <math>\frac{1}{2}</math>"</li> </ul>
3	Cable entry of the remote display and operating module FHX50	C3	XP/Ex ia/DIP XP/AEx ia/DIP	<p>In the case of device versions with metal extensions and sealing plugs, the latter are part of the device approval and meet the requirements of the explosion protection indicated on the nameplate.</p> <p>In the case of device versions with a cable entry, this entry has a separate component approval and meets the requirements of the explosion protection indicated on the nameplate.</p>
Position		Description		
4	Pressure compensation plug	<p><b>NOTICE</b></p> <p>Housing degree of protection voided due to insufficient sealing of the housing.</p> <ul style="list-style-type: none"> <li>▶ Do not open - not a cable entry.</li> </ul>		
⊕	Potential equalization	<p><b>NOTICE</b></p> <p>Terminal for connection to potential equalization.</p> <ul style="list-style-type: none"> <li>▶ Pay attention to the grounding concept of the facility.</li> </ul>		

## Terminal assignment

### *Transmitter*

 The order code is part of the extended order code. Detailed information on the features of the device and on the structure of the extended order code →  5.

### *Connection versions*

Order code for "Output"	Terminal numbers			
	Output 1		Output 2	
	1 (+)	2 (-)	3 (+)	4 (-)
Option A	4-20mA HART (passive)			-
Option B <sup>1)</sup>	4-20mA HART (passive)			Pulse/frequency/switch output (passive)
Option C	4-20mA HART (passive)			4-20mA analog (passive)
Option E <sup>2)</sup>	FOUNDATION Fieldbus			Pulse/frequency/switch output (passive)
Option G <sup>3)</sup>	PROFIBUS PA			Pulse/frequency/switch output (passive)

- 1) Output 1 must always be used; output 2 is optional.
- 2) FOUNDATION Fieldbus with integrated reverse polarity protection.
- 3) PROFIBUS PA with integrated reverse polarity protection.

## Safety-related values

 The order code is part of the extended order code. Detailed information on the features of the device and on the structure of the extended order code →  5.

### *Type of protection XP*

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	$U_{\text{nom}} = \text{DC } 35 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$
Option B	4-20mA HART	$U_{\text{nom}} = \text{DC } 35 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$
	Pulse/frequency/switch output	$U_{\text{nom}} = \text{DC } 35 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$ $P_{\text{max}} = 1 \text{ W}^1)$
Option C	4-20mA HART	$U_{\text{nom}} = \text{DC } 30 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$
	4-20mA analog	

Order code for "Output"	Output type	Safety-related values
Option E	FOUNDATION Fieldbus	$U_{\text{nom}} = \text{DC } 32 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$ $P_{\text{max}} = 0.88 \text{ W}$
	Pulse/frequency/switch output	$U_{\text{nom}} = \text{DC } 35 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$ $P_{\text{max}} = 1 \text{ W}^1)$
Option G	PROFIBUS PA	$U_{\text{nom}} = \text{DC } 32 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$ $P_{\text{max}} = 0.88 \text{ W}$
	Pulse/frequency/switch output	$U_{\text{nom}} = \text{DC } 35 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$ $P_{\text{max}} = 1 \text{ W}^1)$

1) Internal circuit limited by  $R_i = 760.5 \Omega$

### Remote display FHX50

Basic specification, position 1, 2 Approval	Cable specification	Basic specification, position 4 Display; operation Option L, M
Option C3	Max. cable length: 60 m (196.85 ft)	$U_o = 7.3 \text{ V}$ $I_o = 327 \text{ mA}$ $P_o = 362 \text{ mW}$ $L_o = 149 \mu\text{H}$ $C_o = 388 \text{ nF}$ $C_c \leq 125 \text{ nF}$ $L_c \leq 149 \mu\text{H}$

---

---

[www.addresses.endress.com](http://www.addresses.endress.com)

---