# Safety Instructions

## Memosens ISFET pH sensors

pH measurement

Supplement to BA02154C
Safety instructions for electrical apparatus in explosion-hazardous areas
KOR Ex ia IIC T3/T4/T6 Ga
KOR Ex ia IIC T4/T6 Ga







## Memosens ISFET pH sensors

pH measurement

### Table of contents

Associated documentation	4
Additional documentation	4
Certificates	4
Identification	4
Safety Instructions	5
Temperature tables	5
Connection	6
Installation conditions	7

#### Associated documentation

This document is an integral part of Operating Instructions BA02154C.

### Additional documentation



Competence Brochure CP00021Z

- Explosion Protection: Guidelines and General Principles
- www.endress.com

#### Certificates

The certificates and declarations of conformity are available in the Downloads area of the Endress+Hauser website:

www.endress.com/download

### **Korean Certification of Compliance**

21-KA4BO-0621X

#### IECEx certificate

IECEx BVS 19.0056X

#### Identification

The nameplate provides you with the following information on your device:

- Manufacturer identification
- Order code
- Extended order code
- Serial number
- Safety information and warnings
- Ex marking on hazardous area versions
- ► Compare the information on the nameplate with the order.

### Type code

Item type	Version					
xPS47E xPS77E	KA	*	*	**	*	+*
x = C, OC No Ex relevance	KOR Ex ia IIC T3/T4/T6 Ga	No Ex relevance				

Item type	Version					
xPS97E	KA	*	*	**	*	+*
x = C, OC No Ex relevance	KOR Ex ia IIC T4/T6 Ga	No Ex relevance				

### Certificates and approvals

#### Ex approvals

The product meets the requirements of the "IEC Certification Scheme for Explosive Atmospheres". This is verified by compliance with the standards listed in the IECEx certificate. The IECEx certificate can be viewed on the following website: <a href="https://www.iecex.com">www.iecex.com</a>.

#### CPS47E / CPS77E:

Ex ia IIC T3/T4/T6 Ga

#### CPS97E:

Ex ia IIC T4/T6 Ga

### Safety Instructions

The inductive Memosens ISFET pH sensors CPS47E, CPS97E are suitable for use in hazardous areas in accordance with:

- Korean Certification of Compliance 21-KA4BO-0621X
- IECEx certificate IECEx BVS 19.0056X including amendments
- It is not permitted to operate the sensor under electrostatically critical process conditions. Significant vapor and dust clouds, which have a direct impact on the Memosens sensor head, must be avoided.
- The sensors must not be operated under process conditions where the sensor and the connection system can become electrostatically charged. Sensor operation in liquid media that are in contact with the process and have a minimum conductivity of 10 nS/cm is not considered problematic with regard to electrostatic charge.
- Ex-protected digital sensors with Memosens technology are identified by an orange-red ring on the terminal head.
- The procedures for electrical connection described in the Operating Instructions must be followed.
- This device was developed and manufactured in accordance with Directive 2014/34/EU dated February 26, 2014 and also complies with the following standards:
  - EN IEC 60079-0:2018/IEC 60079-0:2017 Hazardous areas Part 0: General requirements
  - EN 60079-11:2012/IEC 60079-11:2011 + Corrigendum:2012 Electrical apparatus for explosive atmospheres Part 11: Intrinsic safety "i"

## Temperature tables

Sensor	_	Process temp	perature T <sub>p</sub>	Ambient temperature T <sub>a</sub>			
	class	minimum	maximum	minimum	maximum		
CPS47E CPS77E	T3	−15 °C (5 °F)	135 °C (275 °F)	−15 °C (5 °F)	70 °C (158 °F)		
	T4	−15 °C (5 °F)	115 °C (239 °F)	−15 °C (5 °F)	75 °C (167 °F)		

Sensor	Temperature	Process temp	perature T <sub>p</sub>	Ambient temperature T <sub>a</sub>		
	class	minimum	maximum	minimum	maximum	
			110 °C (230 °F)		80°C (176°F)	
			100 °C (212 °F)		85 °C (185 °F)	
			90 ℃ (194 ℉)		90 °C (194 °F)	
	Т6	-15 °C (5 °F)	65 °C (149 °F)	−15 °C (5 °F)	65 °C (149 °F)	
CPS97E	T4	-15 °C (5 °F)	110 °C (230 °F)	−15 °C (5 °F)	80°C (176°F)	
			100 °C (212 °F)		85 °C (185 °F)	
			90 ℃ (194 ℉)		90 °C (194 °F)	
	T6	−15 °C (5 °F)	65 ℃ (149 ℉)	−15 °C (5 °F)	65 °C (149 °F)	

#### Connection

### Ex specification


The approved digital ISFET pH sensors feature an intrinsically safe input with the following parameter set:

Parameters	Value
$P_{i}$	180 mW

The approved CPSx7E-type digital ISFET pH sensors must be connected to a Memosens measuring cable with an intrinsically safe output with the following parameter:

Parameters	Value
Po	Maximum 180 mW

## Installation conditions



A0041281

#### ■ 1 Installation conditions

- 1 Limit
- 2 Distance between plug-in head (lower edge) and process medium, without ring and thrust collar
- 3 Process temperature  $T_p$
- 4 Ambient temperature  $T_a$



www.addresses.endress.com