

Safety Instructions

Deltabar S

PMD75, FMD77, FMD78

4-20 mA HART, PROFIBUS PA,
FOUNDATION Fieldbus

Ex db IIC T6...T4 Gb

Ex db IIC T6...T1 Gb



Deltabar S PMD75, FMD77, FMD78

4-20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus

Table of contents

About this document 4

Associated documentation 4

Supplementary documentation 4

Certificates and declarations 4

Manufacturer address 4

Extended order code 4

Safety instructions: General 7

Safety instructions: Specific conditions of use 7

Safety instructions: Installation 8

Safety instructions: Ex d joints 9

Temperature tables 9

Connection data 10

About this document

This document has been translated into several languages. Legally determined is solely the English source text.

Associated documentation

To commission the device, please observe the Operating Instructions pertaining to the device:

HART

- BA00270P
- BA00274P

PROFIBUS PA

- BA00294P
- BA00296P

FOUNDATION Fieldbus

- BA00301P
- BA00303P

Supplementary documentation

Explosion protection brochure: CP00021Z

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website:
www.endress.com -> Downloads -> Brochures and Catalogs ->
Text Search: CP00021Z
- On the CD for devices with CD-based documentation

Certificates and declarations**NEPSI Declaration of Conformity**

Certificate number:
GYJ24.1013X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- GB/T 3836.1-2021
- GB/T 3836.2-2021

Manufacturer address

Endress+Hauser SE+Co. KG
Hauptstraße 1
79689 Maulburg, Germany
Address of the manufacturing plant: See nameplate.

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional

information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

PMD75, FMD7x	–	*****	+	A*B*C*D*E*F*G*..
(Device type)		(Basic specifications)		(Optional specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Deltabar S



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type
PMD75, FMD77, FMD78

Basic specifications

Position 1 (Approval)		
Selected option		Description
PMD75	G	NEPSI Ex db IIC T6...T4 Gb
FMD7x	G	NEPSI Ex db IIC T6...T1 Gb

Position 2 (Output, Operating)		
Selected option		Description
PMD75 FMD7x	A, B, C	4-20 mA HART
	D, E, F	4-20 mA HART, L ₁ = 0
	M, N, O	PROFIBUS PA
	P, Q, R	FOUNDATION Fieldbus

Position 3 (Housing, Cover Sealing, Cable Entry)		
Selected option		Description
PMD75 FMD7x	A, G, 1, 7	T14 IP66/67 NEMA6P; M20
	B, 2	T14 IP66/67 NEMA6P; G1/2
	C, H, 3, 8	T14 IP66/67 NEMA6P; NPT1/2
	J	T15 IP66/67 NEMA6P; M20
	K	T15 IP66/67 NEMA6P; G1/2
	L	T15 IP66/67 NEMA6P; NPT1/2

Optional specifications

ID Jx (Test, Certificate)		
Selected option		Description
PMD75 FMD7x	JN	Ambient temperature transmitter -50 °C/-58 °F
	JT	Ambient temperature transmitter -54 °C/-65 °F


**Safety
instructions:
General**

- Comply with the installation and safety instructions in the Operating Instructions.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards:
 - GB 50257-2014: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering".
 - GB/T 3836.13-2021: "Explosive atmospheres, Part 13: Equipment repair, overhaul, reclamation and modification".
 - GB/T 3836.15-2017: "Explosive atmospheres, Part 15: Electrical installations design, selection and erection".
 - GB/T 3836.16-2022: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance".
- Install the device according to the manufacturer's instructions and national regulations.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ...)
 - Of isolated capacities (e.g. isolated metallic plates)

**Safety
instructions:
Specific
conditions of use**

- In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces.
- For light metal flanges or flange faces (e.g. titanium, zirconium), avoid sparks caused by impact and friction.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts:
 - Observe the danger of electrostatic charging and discharge.
 - Do not rub surfaces with a dry cloth.

Safety instructions: Installation



- A Zone 1, Electronic
 B Zone 1, Process
 1 Power supply
 2 PMD75, FMD77, FMD78

- After aligning (rotating) the enclosure, retighten the fixing screw.
- In potentially explosive atmospheres: Do not open the connection compartment cover and the electronics compartment cover when energized.
- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing clamp on the cover.
- Connect the device:
 - Using suitable cable and wire entries of protection type "Flameproof Enclosure (Ex db)".
 - Using piping systems of protection type "Flameproof Enclosure (Ex db)".
- When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the enclosure.
- For ambient temperatures higher than +70 °C, use suitable heat resisting cables or wires.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Only use certified cable entries or sealing plugs. The metal sealing plugs supplied meet this requirement.
- Only use genuine spare parts from Endress+Hauser which are specified for the device.

Basic specification, Position 3 = B, 2, K
Flameproof equipment with G threaded holes is not intended for new installations, but only for replacing equipment in existing installations. Use of this equipment shall comply with the local installation requirements.

Safety instructions: Ex d joints

If required or if in doubt: ask manufacturer for specifications.

Temperature tables

Device type PMD75

Option: Process Connection	Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
all	T6	-40 °C ≤ T _p ≤ +75 °C	-40 °C ≤ T _a ≤ +75 °C
	T4	-40 °C ≤ T _p ≤ +100 °C	-40 °C ≤ T _a ≤ +75 °C

 The process temperatures refer to the temperature at the separation membrane.

Device type FMD77, FMD78

Option: Process Connection	Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
FMD77: all FMD78: ¹⁾	T6	-40 °C ≤ T _p ≤ +75 °C	-40 °C ≤ T _a ≤ +75 °C
	T4	-40 °C ≤ T _p ≤ +125 °C	-40 °C ≤ T _a ≤ +75 °C
FMD7x: ¹⁾	T3	-40 °C ≤ T _p ≤ +185 °C ²⁾	-40 °C ≤ T _a ≤ +75 °C
	T2	-40 °C ≤ T _p ≤ +285 °C ²⁾	-40 °C ≤ T _a ≤ +75 °C
	T1	-40 °C ≤ T _p ≤ +400 °C ²⁾	-40 °C ≤ T _a ≤ +75 °C

- 1) Depending on the selected design
- 2) Depending on the selected version; see Operating Instructions



- The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
- Do not exceed the max. ambient temperature at the enclosure.

Device type FMD77

Deratings between process temperature and ambient temperature at the enclosure depending on the way of installation as well as functional aspects: See Operating Instructions.

Device type FMD78

The external heat influence depends only on the mounting position of the transmitter itself. Therefore a sufficient capillary length to mount the enclosure at a position with an allowed ambient temperature must be ordered.

Optional specification, ID Jx = JN

Lower limit of the ambient temperature for explosion protection changes to -50 °C.

Optional specification, ID Jx = JT

Lower limit of the ambient temperature for explosion protection changes to -54 °C.

Connection data

Basic specification, Position 2 = A, B, C, D, E, F

Power supply
U ≤ 45 V _{DC} P ≤ 3 W

Basic specification, Position 2 = M, N, O, P, Q, R

Power supply
U ≤ 32 V _{DC} P ≤ 3 W



71640306

www.addresses.endress.com
