

Safety Instructions

Cerabar PMC71B, PMP71B

Control Drawing XP

Class I, II, III, Div. 1, Groups A-G

Class I, Zone 1, AEx/Ex db ia IIC Gb

Class I, Zone 1, AEx/Ex db IIC Gb

Class I, Div. 2, Groups A-D



Cerabar PMC71B, PMP71B

Table of contents

About this document 4

Associated documentation 4

Certificates and declarations 4

Manufacturer address 4

Extended order code 4

Safety instructions: General 7

Safety instructions: Specific conditions of use 8

Safety instructions: Installation 9

Explosionproof / Flameproof 10

Class II, III, Div. 1, Groups E, F, G 10

Class I, Div. 2, Groups A, B, C, D 11

Process seals 11

Temperature tables 11

Connection data 15

About this document

 The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

All documentation is available on the Internet:
www.endress.com/Deviceviewer
(enter the serial number from the nameplate).
To commission the device, please observe the Operating Instructions pertaining to the device:
PMC71B
BA02010P, TI01507P
PMP71B
BA02012P, TI01509P

Certificates and declarations

CSA C/US certificate

Certificate number:
80066208

Manufacturer address

Endress+Hauser SE+Co. KG
Hauptstraße 1
79689 Maulburg, Germany
Address of the manufacturing plant: See nameplate.

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

PMx71B	–	*****	+	A*B*C*D*E*F*G*..
(Device type)		(Basic specifications)		(Optional specifications)

* = Placeholder
At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Cerabar

-  The following specifications reproduce an extract from the product structure and are used to assign:
- This documentation to the device (using the extended order code on the nameplate).
 - The device options cited in the document.

Device type

PMC71B, PMP71B

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
PMC71B	CD	CSA C/US XP Cl. I, II, III, Div. 1, Gp. A-G; Cl. I, Div. 2, Gp. A-D; Cl. I, Zone 1, AEx/Ex db ia IIC Gb
	CF	CSA C/US XP Cl. I, Div. 1, Gp. A-D; Cl. I, Zone 1, AEx/Ex db ia IIC Gb
	CG	CSA C/US Cl. II, III, Div. 1, Gp. E-G

Position 1, 2 (Approval)		
Selected option		Description
PMP71B	CD	CSA C/US XP Cl. I, II, III, Div. 1, Gp. B-G; Cl. I, Div. 2, Gp. A-D; Cl. I, Zone 1, AEx/Ex db IIC Gb
	CF	CSA C/US XP Cl. I, Div. 1, Gp. B-D; Cl. I, Zone 1, AEx/Ex db IIC Gb
	CG	CSA C/US Cl. II, III, Div. 1, Gp. E-G

Position 3, 4 (Output)		
Selected option		Description
PMC71B PMP71B	BA	2-wire, 4-20 mA HART
	BB	2-wire, 4-20 mA HART, switch output ¹⁾
	BC	2-wire, 4-20 mA HART + 4 to 20 mA analog ¹⁾
	DA	2-wire, PROFIBUS PA
	FA	PROFINET over Ethernet-APL, 10Mbit/s

1) Only in connection with Position 6 = J, K

Position 5 (Display, Operation)		
Selected option		Description
PMC71B PMP71B	N	Prepared for display FHX50B + Thread NPT1/2

Position 6 (Housing, Material)		
Selected option		Description
PMC71B PMP71B	B	Single compartment; Alu, coated
	J	Dual compartment; Alu, coated
	K	Dual compartment; 316L

Position 10 (Diaphragm Seal Type)		
Selected option		Description
PMP71B	G	Temperature isolator
	M	 m capillary, 316L
	N	 m capillary, PVC>316L
	O	 m capillary, PTFE>316L
	R	 ft capillary, 316L
	S	 ft capillary, PVC>316L
	T	 ft capillary, PTFE>316L

Optional specifications

ID Ex (Application Package)		
Selected option		Description
PMC71B	EC	High temperature version, 150°C/302°F process

ID Jx, Kx (Test, Certificate, Declaration)		
Selected option		Description
PMP71B	JL	Ambient temp. transmitter -50°C/-58°F, sensor see specification
	JT	Ambient temp. transmitter -60°C/-76°F, sensor see specification ¹⁾

1) Only in connection with Position 1, 2 = CF

Safety instructions: General


- Comply with the installation and safety instructions in the Operating Instructions.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.

- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ...)
 - Of isolated capacities (e.g. isolated metallic plates)
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

**Safety
instructions:
Specific
conditions of use**

- In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces.
- For light metal flanges or flange faces (e.g. titanium, zirconium), avoid sparks caused by impact and friction.
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
 - Observe the danger of electrostatic charging and discharge.
 - Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.
- Avoid sparks caused by impact and friction.
- Flameproof joints are not intended to be repaired.

Safety instructions: Installation



A0041997

- A Device type PMC71B:
Zone 1 or 2; Class I, II, III, Div. 1, Groups A-G or Class I, Div. 2, Groups A-D
Device type PMP71B:
Zone 1 or 2; Class I, II, III, Div. 1, Groups B-G or Class I, Div. 2, Groups A-D
- B Process;
Device type PMC71B:
Zone 0¹⁾, Zone 1 or 2; Class I, II, III, Div. 1, Groups A-G or Class I, Div. 2, Groups A-D
Device type PMP71B:
Zone 1 or 2; Class I, II, III, Div. 1, Groups B-G or Class I, Div. 2, Groups A-D
- 1 Power supply
2 PMC71B, PMP71B
- ¹⁾ Sensor is intrinsically safe (IS), Ex ia. The National Electrical Code (NFPA70) or Canadian Electrical Code, Part I(C22.1) allows the installation of Class I, Division 1 intrinsically safe equipment in Zone 0 locations.

- After aligning (rotating) the enclosure, retighten the fixing screw.
- In potentially explosive atmospheres: Do not open the connection compartment cover and the electronics compartment cover when energized.
- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing screw on the cover.
- Continuous service temperature of the connecting cable: $\geq T_a + 20 \text{ K}$.
- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.

**Explosionproof /
Flameproof***Device type PMC71B*

Class I, Div. 1, Groups A, B, C, D; Class I, Zone 1, AEx/Ex db ia IIC Gb

Device type PMP71B

Class I, Div. 1, Groups B, C, D; Class I, Zone 1, AEx/Ex db IIC Gb

- Install per National Electrical Code (NFPA70) or Canadian Electrical Code, Part I (C22.1), as applicable.
- XP conduit seal required within 450 mm (18 in) of the enclosure.
- For the maximum supply voltage: See "Connection data" section.
- Seal unused entries with approved plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation. The metal sealing plugs supplied meet this requirement.
- The transmitter enclosure is to be connected to ground via internal or external ground terminals.
- WARNINGS: Keep covers tight when explosive atmosphere is present.

Only Device type PMC71B

- The transmitter enclosure is to be installed as an explosionproof/ flameproof device in Class I, Division 1 / Zone 1 locations. It provides an intrinsically safe circuit to the integral or remote mounted sensor enclosure which may be installed in Class I, Division 1 / Zone 0 locations according to the installation requirements of Canadian Electrical Code, Part I (C22.1) or the National Electrical Code (NFPA70).
- Use wiring and sealing methods for the power supply wiring as appropriate for the location.

Only Device type PMP71B

Use wiring and sealing methods appropriate for the location.

**Class II, III, Div. 1,
Groups E, F, G**

- Install per National Electrical Code (NFPA70) or Canadian Electrical Code, Part I (C22.1), as applicable.
- Use wiring and sealing methods appropriate for the location.
- Use a dust-tight seal for wiring at the conduit/cable entry.
- Seal unused entries with approved plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation. The metal sealing plugs supplied meet this requirement.
- WARNINGS: Keep covers tight when explosive atmosphere is present.

Class I, Div. 2, Groups A, B, C, D

- Install per National Electrical Code (NFPA70) or Canadian Electrical Code, Part I (C22.1), as applicable.
- Use wiring and sealing methods appropriate for the location.
- The device is a nonincendive (NI) electrical equipment per UL121201 and CSA C22.2 No. 213.
- Enclosure is not required to be explosionproof/flameproof when installed in Class I, Division 2 locations.
- WARNINGS: Substitution of components may impair suitability for hazardous locations. Do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous.

Basic specification, Position 5 = N

When prepared for use with an approved remote display FHX50B, remote display is suitable for Class I, Division 2 locations only and connection between transmitter enclosure and remote display is nonincendive field wiring.

Process seals

Device Type PMC71B

- The device is rated Single Seal in accordance with UL122701 and does not require the use of an external secondary process seal.
- The Single Seal rating is valid for a maximum pressure of up to 40 bar and a maximum process temperature (T_p) up to 150 °C.

Device Type PMP71B

- The device is rated Single Seal in accordance with UL122701 and does not require the use of an external secondary process seal.
- The Single Seal rating is valid for a Maximum Working Pressure (MWP) of 0 to 700 bar and a maximum process temperature (T_p) up to 400 °C.



- Limitation of the Maximum Working Pressure (MWP) for each device is marked on the nameplate and must not be exceeded! This value may be less than the Single Seal rating.
- Limitation of the maximum process temperature (T_p) with regards to the device options, temperature code rating and maximum ambient temperature as specified in the "Temperature tables" section of this document must be considered!
- Verify the chemical compatibility of the process fluid with the process seal material (see field "Mat." on the nameplate)!

Temperature tables



Optional specification, ID Jx, Kx = JL

Lower limit of the ambient temperature for explosion protection changes to -50 °C.

Optional specification, ID Jx, Kx = JT

Lower limit of the ambient temperature for explosion protection changes to -60 °C.

Class I, Div. 1 and 2 / Zone 1 and Zone 2

-  The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
- Do not exceed the max. ambient temperature at the enclosure.
- The process temperatures refer to the temperature at the separation membrane.

Device Type PMC71B

Temperature class	Process temperature range	Ambient temperature range	
		Class I, Div. 1/Zone 1	Class I, Div. 2/Zone 2
T6	$-40^{\circ}\text{C} \leq T_p \leq +80^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +55^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +55^{\circ}\text{C}$
T4	$-40^{\circ}\text{C} \leq T_p \leq +55^{\circ}\text{C}$	-	$-40^{\circ}\text{C} \leq T_a \leq +65^{\circ}\text{C}$
	$-40^{\circ}\text{C} \leq T_p \leq +100^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$
	$-40^{\circ}\text{C} \leq T_p \leq +125^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +40^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$

Optional specification, ID Ex = EC

Temperature class	Process temperature range	Ambient temperature range	
		Class I, Div. 1/Zone 1	Class I, Div. 2/Zone 2
T6	$-40^{\circ}\text{C} \leq T_p \leq +80^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +55^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +65^{\circ}\text{C}$
T4	$-40^{\circ}\text{C} \leq T_p \leq +125^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$
T3	$-40^{\circ}\text{C} \leq T_p \leq +150^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +40^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$

Device Type PMP71B

Temperature class	Process temperature range	Ambient temperature range	
		Class I, Div. 1/Zone 1	Class I, Div. 2/Zone 2
T6	$-40^{\circ}\text{C} \leq T_p \leq +80^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$
	$-40^{\circ}\text{C} \leq T_p \leq +70^{\circ}\text{C}$	-	$-40^{\circ}\text{C} \leq T_a \leq +65^{\circ}\text{C}$
T4	$-40^{\circ}\text{C} \leq T_p \leq +100^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$
	$-40^{\circ}\text{C} \leq T_p \leq +125^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$	$-40^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$

Basic specification, Position 10 = G

Temperature class	Process temperature range	Ambient temperature range	
		Class I, Div. 1/Zone 1	Class I, Div. 2/Zone 2
T6	$-40\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T4	$-40\text{ °C} \leq T_p \leq +125\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$	-
	$-40\text{ °C} \leq T_p \leq +130\text{ °C}$	-	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
T3	$-40\text{ °C} \leq T_p \leq +190\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T2	$-40\text{ °C} \leq T_p \leq +290\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T1	$-40\text{ °C} \leq T_p \leq +400\text{ °C}$	$-40\text{ °C} \leq T_a \leq +50\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$

Basic specification, Position 10 = M, N, O, R, S, T

Temperature class	Process temperature range	Ambient temperature range	
		Class I, Div. 1/Zone 1	Class I, Div. 2/Zone 2
T6	$-40\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T4	$-40\text{ °C} \leq T_p \leq +125\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$	-
	$-40\text{ °C} \leq T_p \leq +130\text{ °C}$	-	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
T3	$-40\text{ °C} \leq T_p \leq +190\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
T2	$-40\text{ °C} \leq T_p \leq +290\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
T1	$-40\text{ °C} \leq T_p \leq +400\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$

Class II, III, Div. 1



- The specified surface temperature takes into account all direct heat influences from process heat and self-heating at the enclosure.
- Surface temperatures at the process side maybe higher and must be considered by the user (e.g. at high temperature process connections).
- The T-marking is based on the process temperature of the compact designs.
- The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
- Do not exceed the max. ambient temperature at the enclosure.
- The process temperatures refer to the temperature at the separation membrane.



Basic specification, Position 6 = K
 When using the stainless steel enclosure: Reduce the admissible ambient temperature by 5 K.

Device Type PMC71B

Maximum surface temperature	Process temperature range	Ambient temperature range
T125 °C	$-40\text{ °C} \leq T_p \leq +70\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +100\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +125\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$

Optional specification, ID Ex = EC

Maximum surface temperature	Process temperature range	Ambient temperature range
T150 °C	$-40\text{ °C} \leq T_p \leq +125\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +150\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$

Device Type PMP71B

Maximum surface temperature	Process temperature range	Ambient temperature range
T125 °C	$-40\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +100\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +125\text{ °C}$	$-40\text{ °C} \leq T_a \leq +50\text{ °C}$

Basic specification, Position 10 = G

Maximum surface temperature	Process temperature range	Ambient temperature range
T125 °C	$-40\text{ °C} \leq T_p \leq +190\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +290\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +400\text{ °C}$	$-40\text{ °C} \leq T_a \leq +50\text{ °C}$

Basic specification, Position 10 = M, N, O, R, S, T

Maximum surface temperature	Process temperature range	Ambient temperature range
T125 °C	$-40\text{ °C} \leq T_p \leq +190\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +290\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
	$-40\text{ °C} \leq T_p \leq +400\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$

Connection data

Basic specification, Position 3, 4 = BA, BB, BC

Power supply	
Channel 1 $U \leq 35\text{ V}_{DC}$ $P \leq 1\text{ W}$	Channel 2 (only BB, BC) $U \leq 35\text{ V}_{DC}$ $P \leq 1\text{ W}$

Basic specification, Position 3, 4 = DA

Power supply
$U \leq 32\text{ V}_{DC}$ $U_m = 250\text{ V}_{AC}$ (only PMC71B) $P \leq 0.7\text{ W}$

Basic specification, Position 3, 4 = FA

Power supply
$U \leq 15\text{ V}_{DC}$ $U_m = 250\text{ V}_{AC}$ (only PMC71B) $P \leq 0.7\text{ W}$


In connection with: *Basic specification, Position 5 = N*
Installation according to the specifications of FHX50B.



Only the type of protection suitable for the device shall be connected!

Serial resistance (R_V)

Basic specification, Position 3, 4 = BC (only channel 2)



A0053816

- 1 4 to 20 mA
- 2 Switch output

The power consumption have to be limited for certain applications.

- Recommended: Power consumption ≤ 1 W. This is obtained for a supply voltage up to 27 V_{DC}.
- For higher supply voltages (U_{max}): Insert a serial resistance (R_V) in order to limit the power consumption, see table below.

U _{max} [V]	R _V min
35	199 Ω
34	171 Ω
33	143 Ω
32	115 Ω
31	88 Ω
30	60 Ω
29	32 Ω
28	4 Ω
27	0 Ω



71667771

www.addresses.endress.com
