

Promag W 800

Sustainability, an Endress+Hauser Key Value

As a family-owned business aiming for long-term success, we are aware of the importance of prudent corporate management. For us, economic growth goes hand-in-hand with ecological and social thinking. Our sense of responsibility extends to our customers, partners, employees, and shareholders, as much as it does to the environment and to society at large. Our commitment to sustainability is deeply rooted in the culture of our family business.

This Product Carbon Footprint (PCF) Information Sheet is intended to disclose the climate change impacts to help all the value chain stakeholders make further progress along this common path.

About our calculations

We have created adaptive product models for calculating the Life Cycle Assessment (LCA) focusing on PCF of our products. The PCF reported here considers a Cradle-to-Gate system boundary with a reference unit of one piece of a representative Promag W 500 worldwide produced. Use and End-of-Life are excluded from this report. Calculations are based on product technical specifications collected by us and using secondary data from Managed LCA FE Content version CUP2024.1.

Use References (Representative values)

Product lifetime	Years	15
Use intensity	Hours/year	8760

Further calculation details are included in a background report. The Corporate Sustainability Officer is responsible for the guardianship of this document.

Product carbon footprint results – Cradle to gate						Use References (Representative values)	
Product Size		Materials & intermediates	Manufacturing (In-house & by tier one supplier)	Upstream Logistics	Total	Est. Power consumption	Product weight
DN	in	kg CO2-eq.				Watt	kg
25	1"	51.24	13.83	0.46	65.53	2	10
32	-	56.37	13.85	0.51	70.73	2	11
40	1 ½ "	61.49	13.86	0.56	75.91	2	12
50	2"	66.61	13.88	0.60	81.09	2	13
65	-	66.61	13.88	0.60	81.09	2	13
80	3"	76.86	13.91	0.70	91.47	2	15
100	4"	92.24	13.96	0.84	107.04	2	18
125	-	128.19	14.08	1.16	143.43	2	25
150	6"	158.95	14.18	1.44	174.57	2	31
200	8"	266.55	14.52	2.43	283.50	2	52
250	10"	415.14	14.99	3.78	433.91	2	81
300	12"	486.85	15.22	4.44	506.51	2	95
350	14"	543.27	15.40	4.95	563.62	2	106

375	15"	620.08	15.65	5.65	641.38	2	121
400	16"	620.08	15.65	5.65	641.38	2	121

All values (exclusive of packaging material) refer to devices with flanges of the standard pressure rating.

EN (DIN) PN 40 from DN 25 to DN50, PN 16 from DN 65 to DN 150, PN 10 from DN 200 to DN 300 and PN 6 from DN 350 to DN 400 for the order code for "Design", option C, D, E, H, I with sensor with aluminum connection housing version.

Transmitter

- Proline 500 – digital polycarbonate: + 15.82 kg CO2 eq.
- Proline 500 – digital aluminum: + 51.25 kg CO2 eq.
- Proline 500 aluminum: + 138.81 kg CO2 eq.
- Proline 500 cast, stainless: + 74.00 kg CO2 eq.

Impacts during use

The impact during use is variable depending on the use intensity, location and power emission factor but we contribute to an easier scope 1, 2 and 3 coverage. For example, with a lifetime of 15 years, a power consumption of 2 Watt, an assumed use intensity of 8760 h/y and an average assumed impact of 0,5 kg CO2-eq. per kWh, the carbon footprint during use of one of these products would result in: 118.28 kg CO2-eq..

We highly encourage our clients to calculate their own footprint by substituting the use intensity and the power emission factor for individual data.

Disposal information

Although we have excluded End-of-Life from the Carbon Footprint system boundary, this stage can affect the environmental impact of the product. Proper end-of-life practices reduce waste and enable component/material recovery. Our modular devices are repaired by Endress+Hauser Service or trained customers using logical spare part kits. For repair info, contact Endress+Hauser Service. If needed per Directive 2012/19/EU, products bear a symbol (WEEE) to prevent improper disposal. Please return marked products to the manufacturer for correct disposal.