


Generic, dual label and private label products

Generating additional business for OEMs, industry and commerce



Endress+Hauser – Your reliable business partner

Table of contents

Introductions

- 4 Your market presence - Your advantage
- 5 Your partner Endress+Hauser

Products

- 6 Generic, dual label or private label products
- 7 The three levels of labeling
- 8 Data managers
- 9 Display units
- 10 Temperature transmitters
- 12 Compact devices and switches
- 13 Interface devices and electromechanical paddle switches
- 14 Software and tools
- 15 Modules and accessories

Bluetooth® is a trademark of Bluetooth® SIG, Inc. Profibus is a registered trademark of the PROFIBUS user organization. HART is a registered trademark of the HART communication foundation. FOUNDATION Fieldbus is a registered trademark of the Fieldbus FOUNDATION. All other trademarks are the property of their respective owners. All other copyrights are the property of their respective owners.



To learn more about Endress+Hauser, visit:
www.endress.com

Information on the ISO certification:
[Cyber security certification for Endress+Hauser](#)





Endress+Hauser is a global leader in measurement instrumentation, services and solutions for industrial process engineering

With dedicated sales centers and a strong network of partners, Endress+Hauser guarantees competent support worldwide. Our production centers in twelve countries meet your needs and requirements quickly and effectively. The group is managed and coordinated by a holding company in Reinach, Switzerland. As a successful family-owned business, Endress+Hauser is set to remain independent and self-reliant.

Endress+Hauser provides sensors, instruments, systems and services for level, flow, pressure and temperature measurement as well as analytics and data acquisition. The company supports you with automation engineering, logistics and IT services and solutions. Our products set standards in quality and technology.

The company works closely with the chemical, petrochemical, food & beverage, oil & gas, water & wastewater, power & energy, life science, mining, minerals and metals, renewable energy, pulp & paper and shipbuilding industries. Endress+Hauser helps customers to optimize their processes in terms of reliability, safety, economic efficiency and environmental impact.

Competence center for temperature measurement, temperature engineered solutions and system products

Endress+Hauser Temperature+System Products is one of the leading producers of temperature measurement, temperature engineered solutions and system products worldwide.

The company employs more than 700 associates worldwide. 400 of which are working in our headquarters Nesselwang (Germany), where our products are developed and produced.

Associated product centers in Pessano (Italy), Greenwood (USA), Suzhou (China) and Aurangabad (India) guarantee customer proximity with products and services.



Your market presence - Your advantage

Complete your product offering to expand your business.

Everything you need from a single source.

Your customized version from Endress+Hauser.


We support you with our comprehensive range of products available in a generic design or featuring your individual brand name.

The advantage of our products lies in their functionality and versatility for every customer group, whether OEM, reseller or end user. With our high-quality sensors, transmitters, display units, power supply units, barriers and data managers, we help you achieve added value across the entire measuring chain!

A long-term partnership

From concept to operational support, Endress+Hauser supports you throughout the whole lifecycle of your projects. For us, working with you means more than just supplying you with high-quality products.

Our common goal is the development of a reliable long-term and mutually beneficial relationship through consulting, support and exchange of know-how.



Your benefits

✓ Increase turnover

- Open up new markets, increase market share due to an extended offering
- Increase customer loyalty by strengthening your brand, utilizing follow-up and spare part business
- Offer innovative, state-of-the-art and internationally competitive products

✓ Reduce costs

- Save costs of developing and managing your own products
- Pay only for the services and level of change required

✓ Simplify business

Utilize a complete package - the product, software, approvals and services are customized according to your needs.

Your partner Endress+Hauser

High-quality products from a reliable business partner.



Quality “Made in Germany”

With over 100 years of experience in the field of industrial measurement technology, Endress+Hauser Temperature+System Products develops and produces reliable products in the production center in Nesselwang.

We always attach the greatest importance to quality, customer satisfaction and continuous improvement, right from the start. Our numerous quality awards and ISO 9001 quality management system bear testimony to this.



In the manufacturing process, we attach great importance to:

- Using the latest manufacturing and logistics technologies
- Reliable test and inspection systems
- Ensuring highest product quality
- Delivery of tested assemblies and products
- Fast delivery times from order receipt to shipment
- Certified products for worldwide use
- Traceability along the entire production process



Innovative technologies, marketable products

Benefit from our decades of experience in the development and production of devices and modules for industrial process measurement technology.

Profit from robust, state-of-the-art products, serving a wide range of your customer applications.

Generic, dual label or private label products

Simply neutral or tailored to your needs

Generic products in a standardized design are the smart alternative to developing your own products and marketing other companies' brands. With generic, dual label or private label products you offer your customers everything they need without having to manufacture and stock everything yourself. Thanks to three different levels of labeling available, we offer highest flexibility for your business!

| | Generic | Dual Label | Private Label |
|---|--|--|---|
| Availability | Immediately | At short notice | Depending on the scope of change |
| Nameplate | Generic content | Additional customer-specific content | Customer-specific* |
| Color housing | Light gray RAL 7035 | | Standard: light gray RAL 7035, customer-specific |
| Color design elements | Light gray RAL 7035 or steel blue RAL 5011 (operating fields), signal white (texts and graphics) | | Customer-specific* |
| Approvals | Endress+Hauser | | Approvals transcription |
| Device certificates | Printed, generic certificates with delivery | | Electronic format possible |
| System integration (e. g. HART, IO-Link, ...) | Endress+Hauser | | Customer-specific* |
| Packaging label | Generic | | Customer-specific* |
| Product documentation | Generic | | Customer-specific* |
| Operating software | Generic | | Customer-specific* |
| Data management (Visualization Software) | Generic | | Customer-specific* |
| Configuration kit TXU10L | Generic | | Customer-specific* |
| Your benefits | Fast and easy Generic products with immediate availability, utilizing the Endress+Hauser approvals and system integration. | Best of both worlds A generic product with Endress+Hauser approvals using a name plate containing your additional company and sales information. (possible for selected products) | Full flexibility The complete package: product, software and services are perfectly customized according to your needs. |


*possible


The three levels of labeling

An example to show the differences


The following table explains the three labeling levels and the difference to the originally Endress+Hauser branded products. For illustration purposes, we use the example of a head temperature transmitter to show you the changes to the nameplate and printed elements on the product itself.

Endress+Hauser brand with logo
iTEMP TMT31






Label version
OTMT31



Legally required manufacturer information

Sales/Marketing information


Generic





FW:xx.yy.zz

Ser. No.: XXXXXXXXXXXX
F2058-XXXXXXXXXXNN

Endress+Hauser
D-87484 Nesselwang
Made in Germany 2021








Tag information

4-20mA RTD Transmitter

Manufacturer:
Endress+Hauser

Label:
Generic device description


Dual Label





FW:xx.yy.zz

Ser. No.: XXXXXXXXXXXX
F2058-XXXXXXXXXXNN

Endress+Hauser
D-87484 Nesselwang
Made in Germany 2021








Tag information


Distributed by

 **OEM Dual Label**
Part# 0123456789

Manufacturer:
Endress+Hauser

Label:
Freely definable in given area


Private Label





FW:xx.yy.zz

Ser. No.: XXXXXXXXXXXX
Type - XXXXXXXX


Your company
Address
Made in Germany 2023







Customized text



 **Type - XXXXXX**

Manufacturer:
Your Company

Label:
Freely definable



Data managers

Measure, analyze, visualize, archive, monitor, convert and communicate
- incredibly simple, simply incredible.

| Model | Universal data manager ORSG35 | Advanced data manager ORSG45 |
|--------------------|---|--|
| Design |  |  |
| Brief description | Universal data manager with color graphic display and integrated webserver. Universal analog and digital inputs and outputs/relays. Easy to operate. Ethernet, USB, RS232/485, SD card. Modbus slave. Compact panel or desktop housing. Includes PC reporting software for data archiving and analysis. | High-performance data manager; similar to ORSG35 but with more inputs/outputs, with optional large display or stainless steel front with touchscreen and Ex px approval. Unique HART inputs and gateway functionality. Ethernet/IP, Profinet, Profibus DP, Modbus Master. Tamper-proof documentation in accordance with 21CFR11. |
| Software/functions | <ul style="list-style-type: none"> ■ Versatile signal analysis/display and statistics function ■ Email alarm ■ Mathematics function ■ Encoded or compatible data storage in an open format | <ul style="list-style-type: none"> ■ Similar to ORSG35, but with extra/more powerful mathematics functions, analyses, display and e-mail functions ■ Connection for mouse, printer, keyboard ■ Batch function, application packages, process image display and much more |
| Your benefits | <ul style="list-style-type: none"> ■ Good earning potential due to exceptional price-performance ratio ■ Modular design ■ Easy handling and fulfillment of the most diverse customer requirements ■ Integrated webserver enables remote access to the necessary information for service providers and users ■ Highly compatible thanks to direct connection to all conventional standard signals ■ Modern interfaces and standard formats | <ul style="list-style-type: none"> ■ Compared to the ORSG45, even better solution options and integration capability. ■ Easy to configure instead of difficult to program ■ Ideal for fast and cost-efficient completion of complex tasks ■ Increased earning potential ■ Smart gateway solution for system modernization and integration into modern system architectures ■ New maintenance and service concepts ■ Remote diagnosis, access and maintenance via HART and web server ■ Easily extend your range to include Ex-p applications |
| Levels of labeling | Generic / Private Label | |

Process display units










Accurate information on site — for field and panel.

| Model | ORIA15 | ORIA45 |
|--------------------|---|--|
| Design |  |  |
| Brief description | Universal 5-digit 4-20 mA/HART display unit in compact panel or field housing. | Powerful process display unit and compact system with analog and digital inputs and outputs, as well as control and mathematics functions. |
| Software/functions | <ul style="list-style-type: none"> ■ Scaling and square root extraction of measured value/bar graph ■ Configurable dimensions ■ Optional primary/secondary HART Master | <ul style="list-style-type: none"> ■ Linearization ■ Averaging function ■ Signal conversion ■ Differential pressure ■ Limit functions |
| Your benefits | <ul style="list-style-type: none"> ■ Can be used anywhere thanks to high degree of protection and minimal voltage drop ■ Suitable for HART, Ex and GL applications ■ Extremely compact and universal, with illuminated, large, easy-to-read, digital and bar graph display ■ Status and measured value display (PV, SV, TV, QV) for connected HART measuring points | <ul style="list-style-type: none"> ■ Save time, space and costs thanks to complete measuring chain and signal processing in a single device ■ Supply, separate, convert, calculate, control ■ For cabinet and field ■ For Ex sensors ■ Safety guaranteed through compliance with SIL 2 ■ Easy to adapt via keyboard or DTM |
| Levels of labeling | Generic / Private Label | |

Temperature transmitters

The complete portfolio for all requirements.

| Interface /Configuration | PC/CDI (M12) | PC/CDI |  IO-Link IO-Link |  IO-Link IO-Link |
|--------------------------|---|---|---|--|
| Model | TMT470L | OTMT31 | OTMT36 | OTMT311 |
| Design |  |  |  |  |
| Brief description | Particularly compact transmitter assembly from TMR3x thermometer series. Available as circuit board, with M12 connector or potted. Easy to install and freely configurable. | Accurate and long-term stable 4-20 mA temperature transmitter available as head or DIN rail device with one RTD or one TC sensor. For non-Ex applications. Callendar-van-Dusen sensor-transmitter matching. Diagnostics information as per NAMUR standard NE43. | Digital IO-Link 1.1 head transmitter with digital switch output, compatible with optional plug-on display OTID10. Integrated peakhold and Callendar-van-Dusen sensor-transmitter matching. Diagnostics information as per NAMUR standard NE43. | Particularly compact transmitter with 4-20mA and IO-Link 1.1 with digital switch output. Electronics from iTHERM TM311 thermometer series. Available as circuit board with M12 connector or with stainless steel housing. Diagnostics information as per NAMUR standard NE43. |
| RTD input | Pt100 | Pt100, Pt1000 | | Pt100 |
| TC input | - | A, B, C, D, E, K, L, N, R, S, T | | - |
| Output | 4-20 mA | 4-20 mA | IO-Link | IO-Link/4-20 mA |
| Your benefits | <ul style="list-style-type: none"> ■ Create added value in your thermometer production through the use of well-proven industrial assemblies ■ Marketing of competitive 4-20 mA compact thermometers | <ul style="list-style-type: none"> ■ Market-leading, cost-efficient industry quality ■ Easy configuration thanks to royalty-free PC software | <ul style="list-style-type: none"> ■ Enhance your modular thermometer portfolio and transmitter offering with state of the art IO-Link devices ■ Expand your OEM and skid-builder business ■ Save time and costs due to fast installation using the optional push-in terminals | <ul style="list-style-type: none"> ■ Create added value in your thermometer production through the use of well-proven industrial assemblies ■ Marketing of competitive IO-Link compact thermometers ■ Variant reduction by combining IO-Link and 4-20mA electronics in one module |
| Levels of labeling | Generic / Private Label | Generic / Dual Label / Private Label | | Generic / Private Label |




| | | | |
|--|--|--|--|
|  PC/CDI optional: Bluetooth® |   HART 7, PC/CDI, optional: Bluetooth® |  PROFIBUS PA; DTM |  Foundation Fieldbus; DTM |
| OTMT71 | OTMT72 | OTMT84 | OTMT85 |
|  |  |  |  |
| <p>Highly accurate, universal and fast, available in head, DIN rail and field version. With optional Bluetooth® and plug-in display. Unique CJC for TC measurement, as well as comprehensive diagnostic and self-monitoring functions. For non-Ex and Ex applications.</p> | | <p>Max. performance due to compliance with PA Profile 3.02. 2 universal inputs. Head and field version. Optional plug-in display. Comprehensive diagnostic and self-monitoring functions. Non-Ex and Ex Zones 1+2.</p> | <p>Exceptional due to FF H1/ITK6.0.1. 2 universal inputs. Head and field version. Optional plug-in display. Comprehensive diagnostic and self-monitoring functions. Non-Ex and Ex Zones 1+2.</p> |
| Pt50, Pt100, Pt200, Pt500, Pt1000, Ni100, Ni120, Cu50, Cu100 | | Pt100, Pt200, Pt500, Pt1000, Ni100, Ni120, Ni1000, Cu10, Cu100 (Cu50 for OTMT82) | |
| A, B, C, D, E, J, K, L, N, R, S, T, U | | B, C, D, R, S, E, J, K, L, N, T, U (additionally type A for OTMT82) | |
| 4-20 mA galvanically isolated | 4-20 mA/HART galvanically isolated | PROFIBUS PA galvanically isolated | Foundation Fieldbus galvanically isolated |
| <ul style="list-style-type: none"> Enhance your range with wireless configuration and measured value display via Bluetooth® Expand your project business due to compliance with the latest project specifications and international customer requirements Save time and costs due to fast commissioning, and minimize storage, logistics and production costs | <ul style="list-style-type: none"> Expand your project business due to compliance with the latest project specifications and international customer requirements Comprehensive integration into leading systems Save time and costs due to fast commissioning Minimize storage, logistics and production costs Enhance your range with wireless configuration and measured value display via Bluetooth® | <ul style="list-style-type: none"> Increase market share and expand project business due to compliance with the latest project specifications as well as a wide range of customer, NAMUR and international Ex requirements: intrinsically safe/flameproof, zones 1+2 Reliable integration into all leading systems Reliable measuring point information and redundant monitoring thanks to intelligent transmitter functions Maximum precision due to CvD sensor-/transmitter-matching and digital transmission Time savings due to fast wiring and commissioning | |
| Generic / Dual Label / Private Label | | Generic / Private Label | |

Compact devices and switches

Universal and quick, saving you space, time and money.

OEM applications require fast delivery times and reliable operation. In addition, the measuring technology used must be easy to install and the logistics straightforward. This compact devices meet these requirements to a tee. They are easy to commission, provide reliable measurements, can convert to standard signals and issue an alarm in the event of limit value violations.

- Accurate sensors and long term stable electronics
- Hermetically sealed enclosure made of stainless steel
- Compatible connection technology
- Versatile process adapters, flexible insert lengths
- Easy installation, configuration on site and via PC
- Patented insert concept and fastest response time on the market




| Device type | Compact thermometers | | Temperature and flow switches | |
|--------------------|--|--|--|--|
| Model | TMR31L / OTMR35 / OTM311 | | OTR31 / OTR35 | DTT31L / ODTT35 |
| Design |  | |  |  |
| Brief description | Extremely fast, compact and hermetically sealed temperature measuring point. IP69K; also available in hygienic version. 4-wire Pt100 or 4-20 mA, with fixed settings or freely configurable. | | Similar to TMR3x, but always with integrated display, on-site operation and switch outputs. Intelligent, configurable limit functions and alarm. | |
| Configuration | PC/CDI (M12); OTM311via IO-Link | | PC/CDI (M12) | |
| Input / sensor | Pt100 | | | Patented sensor, operates independently of flow direction, 0.03 to 3m/s |
| Output | 4-20 mA/Pt100 | | 4-20 mA, 1 or 2 switch outputs | |
| Your benefits | <ul style="list-style-type: none">■ Seize opportunities in a fast-growing market segment■ Perfect addition to product range■ Easy to use | | <ul style="list-style-type: none">■ Ideal complement to existing thermometer range and completion of portfolio with compact flow switch■ Available immediately■ Wide range of process connections and versions | |
| Levels of labeling | Generic / Private Label | | | |

Interface devices and electromechanical paddle switches

Reliable devices for guaranteed safety.

Specific features:

- Bidirectional transmission of HART signals
- In accordance with NE43
- Communication jacks for easy configuration of sensors via HART

| Application | Bulk solids detection | Active barrier | |
|----------------------|---|---|--|
| Model | OFTE20 | ORN42 | ORN22 |
| Design |  |  |  |
| Brief description | Electromechanical paddle switch for granular solids. Full-state, empty-state or refill-state indicator, available for non-Ex and Ex locations. | 1-channel and active barrier for safe isolation of 20 mA standard signal circuits, wide range power supply, optional 180° rotated installation | Intrinsically safe 24 VDC compact interface module for use in hazardous areas, SIL systems |
| Configuration | Bulk density can be adjusted via switch | - | |
| Software / functions | Function test, rotation monitoring, integrated alarm lamp, tool-free adjustment to density of bulk solids. | 1-channel | 1-channel 2-channel Signal doubler |
| Input | Bulk solids detection via rotating paddle | 0/4-20 mA / HART feeding/not feeding | |
| Output | Relay | 0/4-20 mA / HART active/passive | |
| Power Supply | 230 VAC 50/60 Hz 115 VAC 50/60 Hz 24 VAC 50/60 Hz 20 to 28 VDC | 24 to 230V AC/DC | 24 V DC |
| Your benefits | <ul style="list-style-type: none"> ■ Savings in terms of logistics, commissioning and inventory management due to spring terminal technology, a laser-marked wiring diagram and a terminal head that can be rotated 360° ■ Maintenance-free operation thanks to robust technology in a compact design ■ Transparent, anti-loss cover enables function checks without opening the device ■ For use in non-Ex and Ex applications thanks to international approvals and tests | <ul style="list-style-type: none"> ■ Compatibility to all standard 4-20 mA measuring points with or w/o HART offers worldwide excellent business opportunities. ■ One device for a variety of applications reduces the number of stockable components. ■ SIL 2 (SC3) as per IEC 61508 expands application and thus sales opportunities into safety-critical areas. | <ul style="list-style-type: none"> ■ Compatibility to all standard 4-20 mA measuring points with or w/o HART in widespread 24V powered networks offers excellent business opportunities. ■ Time and cost saving installation due to push-in terminals, slim housing design, easy HART access and optional 2 channel version. ■ One device for a variety of applications to dramatically reduce the number of stockable components. ■ SIL 2 (SC3) as per IEC 61508 expands application and thus sales opportunities into safety-critical areas. |
| Levels of labeling | Generic / Private Label | Generic / Dual Label / Private Label | |

Software and tools

State-of-the-art tools provide efficiency and a profitable business.

FDC tool Field Device Configurator

- Powerful and easy MS Windows® tool for parameterization of programmable temperature transmitters
- Versatile using the standard TXU10L interface cable (point-to-point)
- Fast, easy and intuitive to use




WFDC app

- Compatible with Android® or iOS® devices.
- Powerful Bluetooth® tool for mobile devices - for device operation and measured value read-out
- Remote parametrization of temperature transmitters with Bluetooth® technology



OMS20 visualization software

- Produce documentation and analyze processes efficiently
- Essential version comes with our data managers (ORSG35 and ORSG45) to archive, visualize and analyze process events
- Multiple display and print options – the perfect complement to our modern data managers.
- Access to fast SQL database either locally or through the network.
- Protection against tampering and unauthorized access or device parameters and measured values.
- Ensures compliance with internal company standards and quality assurance along with fulfillment of legal requirements.



Modules and accessories

Offering added value to complement your product range.


Tested modules, assemblies and spareparts

- For maximum flexibility, we provide tested modules to ensure that you can fulfill your orders quickly and in accordance with your customers' needs.
- Proven device modules reduce risk and allow fast delivery times.



Innovative sensor technologies

- Pick from a wide portfolio for every measurement application
- Thermocouple and RTD technology
- PT100 inserts:
 - Thinfil
 - Wirewound
 - iTHERM QuickSens: fastest response time



OTID10 display unit

- Pluggable display for compatible head transmitters
- Dot-matrix display
- Compatible with: OTMT71, OTMT72, OTMT84, OTMT85



Generic terminal heads


These either will become assembled with insert and thermowell or can be used in conjunction with a head transmitter as remote field transmitters.

- OTA30A - with or without display window
- OTA30D - with cover for installing 2 head transmitters
- OTA30H - with or without display window for explosion proof applications
- All types available in multiple cable entry and sensor connection combinations



TXU10L configuration kit

- USB to CDI adaptor cable
- Providing an universal connection to your PC's USB-port
- With the plug-in adapter it is suitable for analog products with M12 connection



→ Further information

For more information on products from Endress+Hauser, please see the following brochures:

- Temperature measurement technology FA00006T
- System components and data manager FA00016K

 See as download under:
www.endress.com/download

i You are interested in our Dual Label devices?
Check out how easy it is to personalize them:



OTMT31



OTMT71



OTMT72



OTMT36



ORN22



ORN42

www.adresses.endress.com