

# Technical Information

## Field Xpert SMT50

Universal, high-performance tablet PC for device configuration



### Application

The Field Xpert SMT50 tablet PC allows technicians to perform mobile device configuration in non-hazardous areas with its seamless out-of-the-box experience. It manages Endress+Hauser and third-party field devices with a digital, wired and wireless communication interface and documents the progress of the work.

The SMT50 is designed as a complete solution. It comes with a pre-installed driver library of more than 3000 devices and is an easy-to-use, touch-enabled tool for managing field devices throughout their entire life cycle.

The integrated LTE module ensures that the tablet is online even if a WLAN is not available. AT&T is supported in the USA, while Verizon is not.

### Your benefits

- Robust tablet with large 12" display and a battery runtime of up to 8 hours.
- Touch-enabled device configuration software for optimized asset management.
- Direct link to Netilion, Endress+Hauser's IIoT ecosystem.
- Pre-installed device driver libraries for all of the important industrial protocols.
- Fast connection to devices with a single click thanks to automatic hardware detection. Online application software and DTM/driver update service offer new functionality and maximum security.
- Integrated Heartbeat Verification incl. PDF documentation.
- Connection to Endress+Hauser Bluetooth and WLAN devices - perfect for difficult-to-access instruments.

## Table of contents

|                                                      |               |
|------------------------------------------------------|---------------|
| <b>About this document</b> .....                     | <b>3</b>      |
| Symbols .....                                        | 3             |
| <br><b>Function and system design</b> .....          | <br><b>4</b>  |
| Function .....                                       | 4             |
| Overview of supported protocols and interfaces ..... | 4             |
| Application examples .....                           | 6             |
| Communication and data processing .....              | 8             |
| <br><b>Energy supply</b> .....                       | <br><b>9</b>  |
| Battery .....                                        | 9             |
| <br><b>Performance characteristics</b> .....         | <br><b>9</b>  |
| Hardware .....                                       | 9             |
| Software .....                                       | 9             |
| <br><b>Environment</b> .....                         | <br><b>11</b> |
| Ambient temperature range .....                      | 11            |
| Storage temperature .....                            | 11            |
| Humidity .....                                       | 11            |
| Degree of protection .....                           | 11            |
| Vibration resistance .....                           | 11            |
| Shock resistance .....                               | 11            |
| Electromagnetic compatibility (EMC) .....            | 11            |
| <br><b>Mechanical construction</b> .....             | <br><b>12</b> |
| Design, dimensions .....                             | 12            |
| Weight .....                                         | 12            |
| <br><b>Operability</b> .....                         | <br><b>12</b> |
| Operation concept .....                              | 12            |
| Languages .....                                      | 12            |
| <br><b>Certificates and approvals</b> .....          | <br><b>13</b> |
| <br><b>Ordering information</b> .....                | <br><b>13</b> |
| Scope of delivery .....                              | 13            |
| <br><b>Accessories</b> .....                         | <br><b>13</b> |
| Device-specific accessories .....                    | 13            |
| <br><b>Documentation</b> .....                       | <br><b>13</b> |
| Standard documentation .....                         | 13            |
| <br><b>Registered trademarks</b> .....               | <br><b>14</b> |

# About this document

## Symbols

### Safety symbols

- 

This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.
- 

This symbol alerts you to a potentially dangerous situation. Failure to avoid this situation can result in serious or fatal injury.
- 

This symbol alerts you to a potentially dangerous situation. Failure to avoid this situation can result in minor or medium injury.
- 

This symbol alerts you to a potentially harmful situation. Failure to avoid this situation can result in damage to the product or something in its vicinity.

### Symbols for certain types of information

| Symbol                                                                              | Meaning                                                                  |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
|    | <b>Permitted</b><br>Procedures, processes or actions that are permitted. |
|    | <b>Preferred</b><br>Procedures, processes or actions that are preferred. |
|   | <b>Forbidden</b><br>Procedures, processes or actions that are forbidden. |
|  | <b>Tip</b><br>Indicates additional information.                          |
|  | Reference to documentation                                               |
|  | Reference to page                                                        |
|  | Reference to graphic                                                     |
|  | Visual inspection                                                        |

## Function and system design


### Function

The Field Xpert SMT tablet PC for universal device configuration supports a variety of protocols, the Endress+Hauser service protocols, and connection to Endress+Hauser Bluetooth field devices and Endress+Hauser WLAN field devices. You can connect the field devices directly via a suitable interface, such as a modem (point-to-point), a bus system (point-to-bus) or a wireless connection (WLAN/Bluetooth).

The Field Xpert software package is fast, easy and intuitive to use.

The Field Xpert device library already has several thousand pre-installed device and communication drivers. They can be used to operate practically all HART and FOUNDATION Fieldbus devices (FieldComm Group libraries). Furthermore all Endress+Hauser field device drivers are installed. The generic HART DTM and PROFIBUS profile DTMs also enable operation of all the important basic functionalities of the relevant field devices.

In addition, the tablet PC features the FDI Package Manager for the installation of FDIs and the IODD DTM Configurator for installing IODDs. You can install new device drivers (DTMs, FDIs and IODDs) on the Field tablet PC at any time.



A0057124

1 Field Xpert SMT50 applications

### Overview of supported protocols and interfaces

#### Supported field devices and protocols

Endress+Hauser field devices and 3rd-party field devices

- HART
- PROFIBUS DP/PA
- PROFINET
- FOUNDATION Fieldbus
- Modbus
- IO-Link
- Bluetooth: Endress+Hauser field devices with Bluetooth function
- WLAN: Endress+Hauser WLAN field devices

#### Supported Endress+Hauser service protocols


- CDI
- IPC
- ISS
- PCP

| Protocol                          | Interface (interface, modem, gateway)                                                                                                                                                                                                                                                                                        |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| HART                              | <ul style="list-style-type: none"> <li>■ Commubox FXA195</li> <li>■ Viator Bluetooth IS modem</li> <li>■ Viator USB modem with PowerXpress</li> <li>■ FieldPort SFP50</li> <li>■ Fieldgate SFG250</li> <li>■ Memograph RSG45</li> <li>■ Tank Scanner NXA820</li> <li>■ FieldGate SWG50</li> <li>■ Fieldgate SWG70</li> </ul> |
| PROFIBUS                          | <ul style="list-style-type: none"> <li>■ Softing PROFlusb</li> <li>■ Softing PBpro USB</li> <li>■ FieldPort SFP50 with PROFIBUS license</li> <li>■ Fieldgate SFG500</li> </ul>                                                                                                                                               |
| PROFINET                          | PROFINET Comm DTM                                                                                                                                                                                                                                                                                                            |
| FOUNDATION Fieldbus               | <ul style="list-style-type: none"> <li>■ NI USB</li> <li>■ FieldPort SFP50 with FOUNDATION Fieldbus license</li> <li>■ Softing FFusb</li> </ul>                                                                                                                                                                              |
| Modbus                            | Modbus serial                                                                                                                                                                                                                                                                                                                |
| IO-Link                           | FieldPort SFP20                                                                                                                                                                                                                                                                                                              |
| Endress+Hauser service interfaces | <ul style="list-style-type: none"> <li>■ Commubox FXA291 CDI</li> <li>■ Commubox FXA291 IPC, ISS, PCP</li> <li>■ Commubox FXA193 IPC, ISS</li> <li>■ TXU10 V2 CDI</li> <li>■ TXU10 V2 PCP</li> <li>■ TXU10 V1 PCP, CDI</li> <li>■ CDI USB</li> <li>■ CDI TCP/IP</li> </ul>                                                   |
| Bluetooth                         | Endress+Hauser field devices with Bluetooth function                                                                                                                                                                                                                                                                         |
| WLAN                              | Endress+Hauser WLAN field devices                                                                                                                                                                                                                                                                                            |

## Application examples

## HART point-to-point connection via USB/HART modem FXA195

You can use the Endress+Hauser USB/HART modem FXA195 to establish a connection automatically from the tablet PC to a HART field device.



A0056992

 2 Point-to-point connection with a HART field device


- 1 Field Xpert SMT70 tablet PC
- 2 USB/HART modem Commubox FXA195
- 3 HART field device

 To establish communication with the HART field device, a resistor of at least 250  $\Omega$  must be provided in the circuit. The integration of the resistor depends on the system architecture and the power supply used.

For detailed information: Documentation for USB/HART modem Commubox FXA195

## Connecting via WLAN or Bluetooth

You can connect the tablet PC to a WLAN or Bluetooth-enabled Endress+Hauser field device via a WLAN or Bluetooth.




A0056991

 3 Connecting via WLAN or Bluetooth

- 1 Field Xpert SMT70 tablet PC
- 2 WLAN or Bluetooth
- 3 Endress+Hauser field device

### HART point-to-point communication via FieldPort SFP50



A0056990


 4 Point-to-point connection via FieldPort SFP50

- 1 A transmitter power supply unit
- 2 Load resistance 250 to 1 100  $\Omega$
- 3 HART field device
- 4 Field Xpert SMT70 tablet PC
- 5 FieldPort SFP50

### CDI point-to-point connection via Commubox FXA291

You can connect the tablet PC automatically to an Endress+Hauser field device with CDI interface via the Endress+Hauser Commubox FXA291.

 For detailed information, see Commubox FXA291 documentation




A0056989

 5 CDI point-to-point connection with a field device

- 1 Field Xpert SMT70 tablet PC
- 2 Commubox FXA291 for CDI interface
- 3 Field device with CDI interface

### PROFIBUS point-to-bus connection

You can establish a connection from the tablet PC to a PROFIBUS PA field device using a wizard by means of the Endress+Hauser Fieldgate SFG500. The connection from PROFIBUS DP to PROFIBUS PA is established via a segment coupler such as Siemens DP/PA link or Pepperl+Fuchs SK3.



A0056988

6 PROFIBUS point-to-bus connection via Fieldgate SFG500

- 1 Field Xpert SMT70 tablet PC
- 2 Ethernet
- 3 Fieldgate SFG500
- 4 PROFIBUS DP
- 5 Segment coupler
- 6 PROFIBUS PA

## Communication and data processing

### Connections

- Video: 1 x mini HDMI 1.4a
- Serial ports: 1 x RS-232 (COM1) + 1 x RS-485 (COM2)

### Expansion slots

- SIM slot: 1 x micro SIM
- Expansion: 1 x micro SD

### USB

- 2x USB 2.0
- 1x USB 3.0

### Wireless local area network

- IEEE 802.11 a/b/g/n
- Dual Band WiFi 2.4GHz + 5.8G Hz

### Bluetooth

- Bluetooth® 4.0 (BLE), Class 1.5
- Transmission distance: 10 meters

### Wireless WAN + GPS

Integrated 4G module + U-blox NEO-7




## Energy supply


|         |                                                   |
|---------|---------------------------------------------------|
| Battery | Replaceable, rechargeable lithium polymer battery |
|         | <b>Type</b>                                       |
|         | R11AH                                             |
|         | <b>Voltage</b>                                    |
|         | 7.4 V <sub>DC</sub>                               |
|         | <b>Capacity (Energy)</b>                          |
|         | 6 300 mAh (45 Wh)                                 |
|         | <b>Battery life</b>                               |
|         | Up to 8 h                                         |

## Performance characteristics


|          |                                                                     |
|----------|---------------------------------------------------------------------|
| Hardware | <b>CPU</b>                                                          |
|          | Intel® Skylake Core m3-6Y30                                         |
|          | <b>Working memory</b>                                               |
|          | 4 GB DDR3L                                                          |
|          | <b>Storage</b>                                                      |
|          | 128 GB M.2 SSD                                                      |
|          | <b>Display</b>                                                      |
|          | ▪ Screen size: 12.2" (30.98 cm)                                     |
|          | ▪ Resolution: 1920 × 1200                                           |
|          | ▪ Capacitive 10 point touchscreen (Corning Gorilla® Glass 3)        |
| Software | ▪ Luminance (brightness): 280 cd/m <sup>2</sup>                     |
|          | <b>Audio</b>                                                        |
|          | ▪ 2 x loudspeakers (0.8 Watt)                                       |
|          | ▪ 3.5 mm audio out                                                  |
|          | <b>Camera</b>                                                       |
|          | ▪ 2 MP camera at the front                                          |
|          | ▪ 5 MP camera at the back                                           |
|          | <b>Field Xpert SMT50 tablet PC operating system</b>                 |
|          | Windows 10 LTSC                                                     |
|          | <b>Field Xpert software</b>                                         |
|          | Touch-enabled device configuration software developed for tablet PC |



7 Start screen with one-click automatic button



8 Protocol selection for manual selection of connection



9 Example: Device configuration


## Environment

|                                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Ambient temperature range</b>           | –20 to 60 °C (–4 to 140 °F)                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Storage temperature</b>                 | –20 to 60 °C (–4 to 140 °F)                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Humidity</b>                            | 5 to 95%                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Degree of protection</b>                | IP65                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Vibration resistance</b>                | MIL-STD 810G 514.6 Procedure I Cat. 24, Fig. 514.6E-1                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Shock resistance</b>                    | MIL-STD-810G                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Electromagnetic compatibility (EMC)</b> | <div>Interference conformance to:<ul style="list-style-type: none"><li>■ EN 55022: 2010+ AC: 2011</li><li>■ EN 55022 Class B</li><li>■ EN 61000-3-2</li><li>■ EN 61000-3-3</li></ul></div> <div>Interference immunity:<ul style="list-style-type: none"><li>■ EN 55024: 2010</li><li>■ IEC 61000-4-2</li><li>■ IEC 61000-4-3</li><li>■ IEC 61000-4-4</li><li>■ IEC 61000-4-5</li><li>■ IEC 61000-4-6</li><li>■ IEC 61000-4-8</li><li>■ IEC 61000-4-11</li></ul></div> |

## Mechanical construction

### Design, dimensions

Standard version: 319.6 mm · 216 mm · 23.4 mm (12.58 in x 8.50 in x 0.92 in)



10 Front view

### Weight

1.5 kg (3.3 lb)

## Operability

### Operation concept

The Field Xpert software provides three different methods to establish a connection to the field device. The version that is possible depends on the protocol, the interface (modem/gateway) and the field device.

- Automatic: Connection to the interface (modem)/field device is established automatically.
- Wizard: You establish a connection to the interface (modem/gateway) and the field device step by step.
- Wireless: Select this option if you wish to establish a connection to an Endress+Hauser Bluetooth or WLAN field device.

### Languages

#### Field Xpert software

Languages for selection: AR, CS, DE, ES, FI, FR, ID, IT, JA, KO, NL, PL, PT, RU, EN, SV, TH, TR, VI, ZH

#### Driver interface for field devices

Depends on the field device

## Certificates and approvals

Current certificates and approvals for the product are available at [www.endress.com](http://www.endress.com) on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

## Ordering information

Detailed ordering information is available from your nearest sales organization [www.addresses.endress.com](http://www.addresses.endress.com) or in the Product Configurator at [www.endress.com](http://www.endress.com):

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Configuration**.



### Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: direct input of information specific to the measuring point, such as the measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

---

### Scope of delivery

The scope of delivery comprises:

- Field Xpert tablet PC with handle
- AC charger (100 to 240 V<sub>AC</sub>, 1.5 A, 50 to 60 Hz) with connecting cable US, UK, CH, IT, ZA, AU
- Software and interfaces/modem as per order

## Accessories

---

### Device-specific accessories

The accessories currently available for the product can be selected at [www.endress.com](http://www.endress.com):

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Spare parts & Accessories**.

## Documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* ([www.endress.com/deviceviewer](http://www.endress.com/deviceviewer)): Enter the serial number from the nameplate
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

---

### Standard documentation

#### Field Xpert SMT50

- Innovation brochure IN01172S
- Technical Information TI01555S
- Operating Instructions BA02053S

## Registered trademarks

Windows 10 IoT Enterprise® is a registered trademark of Microsoft Corporation, Redmond, Washington, USA.

Intel® Core™ is a registered trademark of Intel Corporation, Santa Clara, USA.

FOUNDATION™ Fieldbus is the trademark of the FieldComm Group, Austin, TX 78759, USA.

HART®, WirelessHART® is the registered trademark of the FieldComm Group, Austin, TX 78759, USA.

PROFIBUS® is a registered trademark of the PROFIBUS User Organization, Karlsruhe/Germany.

PROFINET® is a registered trademark of the PROFIBUS User Organization (PNO), Karlsruhe/Germany

Modbus is the registered trademark of Modicon, Incorporated.

IO-Link® is a registered trademark of the IO-Link Community c/o PROFIBUS User Organization, (PNO) Karlsruhe/Germany - [www.io-link.com](http://www.io-link.com)

All other brand and product names are trademarks or registered trademarks of the companies and organizations in question.

---



71720146

[www.addresses.endress.com](http://www.addresses.endress.com)

---