



Special Documentation

Weather protection cover

Cerabar PMP50, Deltabar PMD50

Accessory

Intended use

The weather protection cover is designed for the following types of housing:

- Dual compartment housing; aluminum, coated
- Dual compartment housing; 316L

Safety instructions

⚠ WARNING

Hazardous area: Risk of injury from explosion! Explosion hazard due to static charging of weather protection cover!

- ▶ Connect the weather protection cover to local potential equalization!


⚠ CAUTION

Risk of injury from mechanical damage!

- ▶ Do not step or climb on the weather protection cover!

Scope of delivery


- 1 × weather protection cover, 316L (1.4404)
- 2 × clamps with recess, 316L (1.4404)
- 4 × screws, 316 L



A0057101

1 Ground terminal for connecting the potential matching line


Dimensions



A0057100

Unit of measurement mm (in)

Installation




A0057129


1 Installation position

1 T = Cover for terminals


2 E = Cover for display and main electronics



A0057130



A0057131



A0057132