

## Technical Information


# RIA141

Digital field loop powered display unit  
with explosion proof enclosure



### Application

- Oil & gas
- Petrochemical industry
- System and apparatus engineering
- Outdoor applications
- Laboratory facilities
- Process data acquisition and monitoring
- Optional: stainless steel housing for EEx d application




### Your benefits

- Loop-powered display unit in single compartment housing
- 5-digit LC display, character height 20.5 mm (0.8")
- Illuminated display, rotatable
- Trend bargraph in increments of 10%
- Background illumination without additional power supply
- Measuring range display from -19999 to 99999
- Digital limit switch
- Freely programmable units
- 3-key operation
- Approvals: ATEX, FM and CSA
- 3 cable entries
- Configuration with ReadWin® 2000 PC software
- Configuration without power supply using setup box

## Function and system design

### Measuring principle



Example of an application of the field display unit

The display unit records an analog measuring signal and shows this on the display with background illumination. The LC display shows the current measured value digitally and as a bargraph with limit value violation signalling. The display unit is looped into the 4 to 20 mA circuit and obtains the required energy from there.

### Measuring system

Microcontroller controlled display unit in single chamber field housing with illuminated LC display. The measuring range, decimal point and offset of the display can be configured comfortably by means of three keys in the device with the housing open or by means of a PC with the ReadWin® 2000 PC software. The background illumination of the display is always activated and does not require additional wiring for the power supply.

## Input

#### Measured variable

Current

#### Measuring range

4 to 20 mA (reverse polarity protection)

#### Input

- Line voltage drop < 4 V at 3 - 22 mA
- Max. line voltage drop < 6 V at max. short-circuit current 200 mA

## Output

#### Output

Digital limit switch  
 Passive, open collector:  
 $I_{\max} = 200 \text{ mA}$   
 $U_{\max} = 35 \text{ V}$   
 $U_{\text{low/max}} = < 2 \text{ V at } 200 \text{ mA}$   
 Max. reaction time to limit value = 250 ms

#### Signal on alarm


No measured value visible on the LC display, no background illumination.

#### Transmission behavior

The display unit allows the HART® transmission protocol to pass unimpeded.

# Power supply

## Electrical connection



Terminal assignment of field display unit

Terminal	Terminal assignment	Input and output
+	Measuring signal (+) 4 to 20 mA	Signal input
-	Measuring signal (-) 4 to 20 mA	Signal input
1	Terminal for further instrumentation	Support terminal
2	Digital limit switch (collector)	Switch output
3	Digital limit switch (emitter)	Switch output

## Supply voltage

Supply by means of the 4 to 20 mA current loop.

## Cable entry

The following cable entries are available:

- 3x thread NPT1 + 1x blind plug
- 3x thread M20 + 1x blind plug
- 2x gland M20 + 1 x blind plug
- 3x thread G1/2 + 1 x blind plug

## Performance characteristics

<b>Reference operating conditions</b>	T= 25 °C (77 °F)
<b>Maximum measured error</b>	< 0.1% of scaled display range
<b>Influence of ambient temperature (temperature drift)</b>	Effect on the accuracy when ambient temperature changes by 1 K (1.8 °F): 0.01%

## Installation

<b>Installation instructions</b>	<b>Mounting location</b>
	Wall or pipe mounting (see 'Accessories')
	<b>Orientation</b>
	No restrictions


## Environment

<b>Ambient temperature limits</b>	-40 to +80 °C (-40 to +176 °F)
	Note! The display can react slowly for temperatures < -20 °C (< -4 °F). Readability of the display cannot be guaranteed at temperatures < -30 °C (-22 °F).
<b>Storage temperature</b>	-40 to +85 °C (-40 to +185 °F)
<b>Electrical safety</b>	As per IEC 61010-1, UL61010-1, CSA C22.2 No. 1010.1-92
<b>Climate class</b>	As per IEC 60 654-1, Class C
<b>Degree of protection</b>	IP 67, NEMA 4X
<b>Shock and vibration resistance</b>	3g / 2 to 150 Hz as per IEC 60 068-2-6
<b>Condensation</b>	Permitted
<b>Installation category</b>	1 to IEC 61010
<b>Pollution degree</b>	2 to IEC 61010
<b>Electromagnetic compatibility (EMC)</b>	<ul style="list-style-type: none"> <li>■ EN 61326 (IEC 61326): Electromagnetic compatibility (EMC requirements)</li> <li>■ NAMUR (NE21): Association for Standards for Control and Regulation in the Chemical Industry</li> </ul>

## Mechanical construction

### Design, dimensions

Die cast aluminum housing for general purpose or as option stainless steel housing



Data in mm (data in inches in brackets)

- Electronics compartment and connection compartment together in the single chamber housing
- Display can be rotated in 90°-stages

### Weight

- Approx. 1.6 kg (3.53 lb) (aluminium housing)
- Approx. 4.2 kg (9.26 lb) (stainless steel housing)

### Material


Housing	Nameplate
Die-cast aluminum housing AISi10Mg with powder coating on polyester basis	Aluminum AlMgI, anodized in black
Stainless steel 1.4435 (AISI 316L)	1.4301 (AISI 304)

### Terminals

Cables / wires up to max. 2.5 mm<sup>2</sup> (AWG 13) plus ferrule

## Human interface

### Display elements



LC display of the field display unit (illuminated, pluggable in 90° stages)

Item 1: bargraph display in increments of 10% with indicators for measuring range undershoot (item 1a)/overshoot (item 1b)

Item 2: warning sign in the case of limit value violation

Item 3: unit indicator K, °F, °C or %

Item 4: measured value display (character height 20.5 mm/0.8")

Item 5: status and information indicator / configuration

Item 6: 'programming disabled' indicator

- Display range  
-19999 to +99999
- Offset  
-19999 to +99999
- Signalling  
Measuring range overshoot/undershoot
- Limit value violation  
Lower/upper limit value exceeded

### Operating elements

3-key operation (-/+/E) integrated in device, access with housing open

### Remote operation

#### Configuration


The device is configured with the ReadWin® 2000 PC operating software.

#### Interface

Configuration interface at device; connection to PC via configuration kit (see "Accessories").

#### Configurable device parameters (selection)

Measuring dimension, measuring ranges (linear/square), setup block using user code, failsafe mode, digital filter (damping), offset, limit value (min/max/alarm), alarm limit values freely adjustable.



Configuration with ReadWin® 2000 PC operating software.

## Certificates and approvals

<b>CE mark</b>	The device complies with the legal requirements of the EC directives. Endress+Hauser confirms that the device has been successfully tested by affixing to it the CE mark.
<b>Hazardous area approvals</b>	Information about currently available Ex versions (ATEX, FM, CSA, etc.) can be supplied by your E+H Sales Center on request. All explosion protection data are given in a separate documentation which is available upon request.
<b>UL</b>	Recognized component to UL 3111-1
<b>Other standards and guidelines</b>	<ul style="list-style-type: none"> <li>■ IEC 60529: Degree of protection provided by housing (IP-Code)</li> <li>■ IEC 61010: Safety requirements for electrical measurement, control and laboratory use.</li> <li>■ IEC 61326: Electromagnetic compatibility (EMC requirements)</li> <li>■ NAMUR Standards working group for measurement and control technology in the chemical industry. (www.namur.de)</li> </ul>
<b>CSA GP</b>	CSA General Purpose

## Ordering information

<b>Product structure</b>	RIA141	1 channel, scalable, for 4-20mA, loop powered, display LC 5 digits, 20.5 mm high, bargraph resolution 10 %, over/underrange, engineering units, 3 key operation, digital limit switch, UL recognized, CSA-GP			
		<b>Approval</b>			
		<b>A</b>	Version for non-hazardous areas		
		<b>B</b>	ATEX II2G EEx d IIC T6		
		<b>C</b>	FM XP, NI, DIP Cl. I, II, III/1+2 Gr. ABCDEFG		
		<b>D</b>	CSA XP, NI, DIP I, II, III/1+2/ Gr. ABCDEFG		
		<b>E</b>	ATEX II3G EEx nA IIC T4/T5/T6		
		<b>F</b>	ATEX II2D		
		<b>Housing</b>			
		<b>1</b>	Field, alu die cast		
		<b>2</b>	Field, 316L		
		<b>Cable entry</b>			
		<b>A</b>	3x thread NPT 1/2 + 1x blind plug		
		<b>B</b>	3x thread M20 + 1x blind plug		
		<b>C</b>	2x gland M20 + 1x blind plug		
		<b>D</b>	3x thread G1/2 + 1x blind plug		
		<b>Mounting bracket</b>			
		<b>1</b>	without		
		<b>2</b>	Pipe 2", 316L		
		<b>Additional option</b>			
		<b>1</b>	Basic version		
		<b>2</b>	Works calibration certificate, 5-point		
		<b>Version</b>			
		<b>A</b>	Standard		
		<b>K</b>	Standard, North American region		
	RIA141-				← order code

## Accessories

Order code	Accessory
51007995	Mounting bracket
51004949	1 x cable entry M20x1.5
51006845	1 x cable gland NPT ½"
51004489	1 x blank (blind) M20x1.5
51004490	1 x blank (blind) NPT ½"
51004916	1 x blank (blind) JIS G½"
51003528	TAG imprint 2x16 characters
TXU10A-xx	<ul style="list-style-type: none"> <li>■ Configuration kit for PC programming (Interface cable for PC with USB port + ReadWin® 2000 PC software)</li> <li>■ ReadWin® 2000 can be downloaded free of charge from the Internet at the following address: <a href="http://www.endress.com/readwin">www.endress.com/readwin</a></li> </ul>

## Documentation

- 'System components' field of activities brochure (FA016K/09/en)
- Operating Instructions for 'RIA141 field display unit' (BA177R/09/a3)
- Supplementary Ex documentation:
  - ATEX II2G EEx d: XA045R/09/a3
  - ATEX II1/2D: XA046R/09/a3
  - ATEX II3G: XA047R/09/a3

### Instruments International

Endress+Hauser  
Instruments International AG  
Kaegenstrasse 2  
4153 Reinach  
Switzerland

Tel. +41 61 715 81 00  
Fax +41 61 715 25 00  
[www.endress.com](http://www.endress.com)  
[info@ii.endress.com](mailto:info@ii.endress.com)

**Endress+Hauser**   
People for Process Automation