

Safety Instructions

iTHERM TM111,

iTHERM TM131, TM151

Ex db IIC T6...T1 Gb

Ex tb IIIC T85 °C...T450 °C Db

Ex db IIC T6...T1 Ga/Gb

Ex ta IIIC T₂₀₀ T85 °C...T₂₀₀ T450 °C Da - Process

Ex tb IIIC T85 °C...T450 °C Db - Enclosure



iTHERM TM111, iTHERM TM131, TM151

Table of contents

About this document 3

Associated documentation 3

Supplementary documentation 3

Certificates and declarations 3

Manufacturer address 3

Safety instructions 4

Safety instructions: Installation of protection flameproof 4

Safety instructions: Installation of Dust ignition protection 5

Safety instructions: Partition wall 6

Safety instructions: Specific conditions of use 7

Temperature tables 10

Electrical connection data 12

About this document

The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

To commission the device, please observe the Operating Instructions pertaining to the device:

www.endress.com/<product code>, e.g. iTHERM TM111

Supplementary documentation

Explosion protection brochure: CP00021Z

The explosion protection brochure is available on the Internet:

www.endress.com/Downloads

Certificates and declarations**NEPSI certificate**

Certificate number: GYJ24.1170X

Affixing the certificate number certifies conformity with the following standards (depending on the device version)

- GB/T 3836.1-2021
- GB/T 3836.2-2021
- GB/T 3836.31-2021



Please refer to NEPSI/CCC certificates for conditions of safe use.


Manufacturer address

Endress+Hauser Wetzer GmbH + Co. KG
Obere Wank 1
87484 Nesselwang, Germany

Endress+Hauser Sicestherm S.r.l
Via Martin Luther King 7/9
Pessano con Bornago (MI) 20042, Italy

Endress+Hauser Wetzer (Suzhou) Co. Ltd.
No.31 JiangTianLilu
Suzhou Industrial Park (SIP) Suzhou 215126, China

Safety instructions



A0056204

Safety instructions: Installation of protection flameproof

- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and any other valid standards and regulations (e.g. EN/IEC 60079-14).
- The housing of the thermometer must be connected to the potential matching line.

- Only the approved wire entries as specified in paragraph 10 of IEC/EN 60079-14, paragraph 16 of IEC/EN 60079-0, paragraph 13 of IEC/EN 60079-1 must be used.
- For connection through a conduit entry approved for this purpose the associated sealing facility shall be mounted directly to the housing.
- Seal the cable entries with certified cable glands and or blanking elements which have at least type of protection Ex db and Ex tb suitable for Group IIC and IIIC (degree of protection IP6X).
- The maximum specified ambient temperature T_a at terminal head not be exceeded.
- For operating the thermometer housing at an ambient temperature under $-20\text{ }^{\circ}\text{C}$ appropriate cables and cable entries permitted for this application must be used.
- For ambient temperatures higher than $+65\text{ }^{\circ}\text{C}$, use suitable heat-resisting cables or wires, cable entries and sealing facilities for $T_a +5\text{ K}$ above surrounding.
- During operation, the cover must be screwed all the way in and the cover's safety catch must be fastened.
- The device must be installed and maintained so, that even in the event of rare incidents, an ignition source due to impact or friction between the enclosure and iron/steel is excluded.

WARNING

Potentially explosive atmospheres

- ▶ Do not open the electrical connection of the supply circuit when energized if there is a potentially explosive atmosphere.

Safety instructions: Installation of Dust ignition protection

- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and any other valid standards and regulations (e.g. EN/IEC 60079-14).
- Seal the cable entries tight with certified cable which have at least type of protection Ex tb suitable for Group IIIC (degree of protection IP6X).
- In case of installation and repair apply a torque for process connection of 50 to 70 Nm for terminal heads suffix code i = A1, A2, D1 (TA30A, TA30D).
- For assure that the temperature assembly has a degree of protection of IP6X the user shall provide a thermowell or equivalent component at the process side
- The housing of the thermometer must be connected to the potential matching line.
- For ambient temperatures higher than $+65\text{ }^{\circ}\text{C}$, use suitable heat-resisting cables or wires, cable entries and sealing facilities for $T_a +5\text{ K}$ above surrounding.



Explosive atmosphere

- ▶ In an explosive atmosphere, do not open the device when voltage is supplied (ensure that the IP6x housing protection is maintained during operation).

**Safety
instructions:
Partition wall**

The provided thermowells to suffix code iTHERM TM131_e, iTHERM TM151_d are made out of material as follows:

iTHERM TM131_e	iTHERM TM151_d	Material
B1, B2, B3, B4	AD, AE, AI	AISI316L/W.1.4404
C1, C2, C3, C4	AF	AISI 316Ti/1.4571
D1, D2	BB	Hastelloy® C-276
E1, E2	BA	Alloy 600
F1, F2	AC, AE, AI	AISI316/W.1.4401
G1		AISI446/W.1.4762
H1		AISI321/ W.1.4541
I1, I2		AISI 316Ti/1.4571 and Tantal
	AG	AISI 347/W.14550
	AH	AISI 310/W.1.4841
	CA	10CrMo9-10/A182 F22/W.1.7380
	CB	13CrMo4-5/A182 F11/W.1.7335
	CC	16Mo3/W.1.5415
	DA	A105/W.1.0402
	DB	C22.8/W.1.0460
	DC	P355NH/W.1.0565
	EA	Duplex S32205/W.1.4470
YY	YY	the thermowell material is listed in the manufacturer's website (CER viewer or Asset Central Viewer)

Instructions for option:

iTHERM TM131-ab...

b

A

iTHERM TM151-ab...

Thermowell:

Thermometer to be assembled into existing thermowell

- | | |
|---|--|
| b | Thermowell: |
| 1 | Thermometer to be assembled into existing thermowell |
- Install the thermometer in a partition wall which is in compliance with IEC/EN 60079-26 in reference to its ultimate application.
 - Use only thermowells out of corrosion resistant materials complying with IEC/EN 60079-0 chapter 8.3 (e.g. AISI316/W.1.4401, AISI316L/W.1.4404, AISI 316Ti/1.4571...) with a wall thickness of at least 1 mm.
 - Use thermowells suitable for the process conditions.
 - Providing a degree of protection of at least IP6X when assembled.

Safety
instructions:
Specific
conditions of use

- The flameproof joints are not intended to be repaired.
- It shall be verified, taking into account the worst case process and ambient temperatures:
 - that the temperature of the enclosure at the process connection point does not exceed the ambient temperature range of the assembly and
 - the temperature of the optionally used RB**1NS union does not exceed the service temperature range as listed in Annex 1.
 - that the temperature of the optionally used Sensor Type iTHERM TS21x with QuickNeck construction does not exceed the service temperature range as listed in Annex 1.
 - that the temperature of optional seal at connection points does not exceed the service temperature range as listed in Annex 1.
 - that the temperature of the thermowells type iTHERM TT151 for iTHERM TM151 does not exceed the service temperature range as listed in Annex 1 for some available materials.
- When provided with special varnishing (type iTHERM TM111 suffix code i = YY, type iTHERM TM131 suffix code m = YY, type iTHERM TM151 suffix code m = YY) refer to the instructions "Safety notes varnish XA01369T" for guidance to minimize the risk from electrostatic discharge.
- Temperature assemblies with flying leads (type iTHERM TM111 suffix code h = 0A, type iTHERM TM131 suffix code l = 0A, type iTHERM TM151 suffix code l = 0A) shall be provided with a round transmitter of max. 2.2 W with a main diameter not exceeding 45 mm and a sensor signal of max 10 V_{DC} and 1 mA.
- The connection fittings, their joints, and their joints with the thermowell and the connection head or field temperature transmitter provide ingress protection of IP6x or, alternatively, IP66/67 (when fitted with at least 5 turns of PTFE tape or Loctite 270 spread on the entire circumference and for at least one thread) in the temperature range of -50 to +130 °C according to IEC 60079-0 and IEC 60529.
- Sensors with Quicksleeve construction shall always be protected by a metallic thermowell.


Type iTHERM TM111

- Sensors with a diameter of 3 mm (suffix code b = A) shall be protected by a thermowell.
- Sensors with other diameters (suffix code b = Y) shall be protected by a thermowell unless excluded by the product information available on the manufacturer's website (CER viewer or Asset Central Viewer) and the safety instructions for optional thermocouples and RTDs (document 10000013456).

These safety instructions show, depending on the sensor details, when protection by a thermowell is required. The viewer on the website shows the sensor details for each serial number of the assembly.

Type iTHERM TM131, TM151

The sensor shall be protected by the thermowell as provided or by a thermowell as specified in the instructions.



A0060699

Sensor

- As the flameproof product suitable certified cable glands or blanking plugs for unused holes approved by ExTL according to GB/T 3836.1-2021 and GB/T 3836.2-2021 with Ex marking “Ex db IIC Gb” shall be used and correctly installed. As the dust product, suitable certified cable glands or blanking plugs for unused holes approved by ExTL according to GB/T 3836.31-2021 with Ex marking “Ex tb IIIC Db” shall be used and correctly installed, after installation, degree of protection of enclosure is at least IP66/IP68 according to GB/T 4208-2017. The cable glands and blanking plugs to be used shall be suitable for the product working conditions.
- Any maintenance shall be performed only when the warning of “Do not open when energized” is observed.
- Clean the surface of this product termly when using in combustible dust atmosphere.
- The user shall not change the configuration in order to maintain/ ensure the explosion protection performance of this product. Any change may impair safety.
- For installation, use and maintenance of this product, the end user shall observe the instruction manual and the following standards:
GB/T 3836.13-2021 “Explosive atmospheres- Part 13: Equipment repair, overhaul, reclamation and modification”.
GB 3836.15-2024 “Explosive atmospheres- Part 15: Electrical installations design, selection and erection”.
GB 3836.16-2024 “Explosive atmospheres- Part 16: Electrical installations inspection and maintenance”.
GB50257-2014 “Code for construction and acceptance of electric equipment on fire and device for explosion hazard electrical installation engineering”.
GB15577-2018 “Safety regulations for dust explosion prevention and protection”

Temperature tables

The relation between the type, electrical connection, temperature class, maximum surface temperature, ambient temperature range and process temperature range is shown in the following table.

Temperature assemblies with RTD temperature sensors				
Electrical connection ¹⁾	Temperature class/ Maximum surface temperature	Ambient temperature range	Process temperature range Insert diameter 3 mm, 6 mm dual	Process temperature range Insert diameter 6 mm
Type iTHERM TM111				
Terminal block (1A) ²⁾	T6/T85 °C	-50 to +70 °C	-50 to +55 °C	-50 to +68 °C
	T5/T100 °C	-50 to +80 °C	-50 to +70 °C	-50 to +83 °C
	T4/T135 °C	-50 to +120 °C	-50 to +105 °C	-50 to +118 °C
	T3/T200 °C	-50 to +120 °C	-50 to +170 °C	-50 to +183 °C
	T2/T300 °C	-50 to +120 °C	-50 to +265 °C	-50 to +278 °C
	T1/T450 °C	-50 to +120 °C	-50 to +415 °C	-50 to +428 °C
Type iTHERM TM111 and iTHERM Type TM131, TM151				
Flying leads (0A) or Transmitter iTEMP TMT31 (2H, 2I) iTEMP TMT36 (6U) iTEMP TMT71 (2C) iTEMP TMT72 (3A) iTEMP TMT82 (3C, 3D, 3F, 3I) iTEMP TMT84 (5A) iTEMP TMT85 (4A) iTEMP TMT86 (6B, 6C) iTEMP TMT180 (2A, 2B)	T6/T85 °C	-40 to +65 °C	-50 to +55 °C	-50 to +68 °C
	T5/T100 °C	-40 to +80 °C	-50 to +70 °C	-50 to +83 °C
	T4/T135 °C	-40 to +85 °C	-50 to +105 °C	-50 to +118 °C
	T3/T200 °C	-40 to +85 °C	-50 to +170 °C	-50 to +183 °C
	T2/T300 °C	-40 to +85 °C	-50 to +265 °C	-50 to +278 °C
	T1/T450 °C	-40 to +85 °C	-50 to +415 °C	-50 to +428 °C
Type iTHERM TM131 and iTHERM TM151				
Terminal block (1A) ²⁾	T6/T85 °C	-50 to +70 °C	-50 to +55 °C	-50 to +68 °C
	T5/T100 °C	-50 to +80 °C	-50 to +70 °C	-50 to +83 °C
	T4/T135 °C	-50 to +90 °C	-50 to +105 °C	-50 to +118 °C
	T3/T200 °C	-50 to +90 °C	-50 to +170 °C	-50 to +183 °C
	T2/T300 °C	-50 to +90 °C	-50 to +265 °C	-50 to +278 °C
	T1/T450 °C	-50 to +90 °C	-50 to +415 °C	-50 to +428 °C

Temperature assemblies with RTD temperature sensors				
Electrical connection ¹⁾	Temperature class/ Maximum surface temperature	Ambient temperature range	Process temperature range Insert diameter 3 mm, 6 mm dual	Process temperature range Insert diameter 6 mm
Transmitter iTEMP TMT142: 7A iTEMP TMT162: 2D, 2E, 2F, 2G, 4B, 4C, 5B, 5C	T6/T85 °C	-40 to +55 °C	-50 to +55 °C	-50 to +68 °C
	T5/T100 °C	-40 to +70 °C	-50 to +70 °C	-50 to +83 °C
	T4/T135 °C	-40 to +80 °C	-50 to +105 °C	-50 to +118 °C
	T3/T200 °C	-40 to +80 °C	-50 to +170 °C	-50 to +183 °C
	T2/T300 °C	-40 to +80 °C	-50 to +265 °C	-50 to +278 °C
	T1/T450 °C	-40 to +80 °C	-50 to +415 °C	-50 to +428 °C

- 1) iTHERM TM111 suffix code h, iTHERM TM131 and iTHERM TM151 suffix code l.
 2) in an enclosure with a blind cover; iTHERM TM111 suffix code i / iTHERM TM131 and iTHERM TM151 suffix code m = A1, D1, H1, H3.

Temperature assemblies with thermocouple temperature sensors			
Electrical connection ¹⁾	Temperature class/ Maximum surface temperature	Ambient temperature range	Process temperature range
Type iTHERM TM111			
Terminal block (1A) ²⁾	T6/T85 °C	-50 to +70 °C	-50 to +85 °C
	T5/T100 °C	-50 to +80 °C	-50 to +100 °C
	T4/T135 °C	-50 to +120 °C	-50 to +135 °C
	T3/T200 °C	-50 to +120 °C	-50 to +200 °C
	T2/T300 °C	-50 to +120 °C	-50 to +300 °C
	T1/T450 °C	-50 to +120 °C	-50 to +450 °C
Type iTHERM TM111 and iTHERM Type TM131, TM151			
Flying leads (0A) or Transmitter iTEMP TMT71 (2C) iTEMP TMT72 (3A) iTEMP TMT82 (3C, 3D, 3F, 3I) iTEMP TMT84 (5A) iTEMP TMT85 (4A) iTEMP TMT86 (6B, 6C)	T6/T85 °C	-40 to +65 °C	-50 to +85 °C
	T5/T100 °C	-40 to +80 °C	-50 to +100 °C
	T4/T135 °C	-40 to +85 °C	-50 to +135 °C
	T3/T200 °C	-40 to +85 °C	-50 to +200 °C
	T2/T300 °C	-40 to +85 °C	-50 to +300 °C
	T1/T450 °C	-40 to +85 °C	-50 to +450 °C
Type iTHERM TM131 and iTHERM TM151			
Terminal block (1A) ²⁾	T6/T85 °C	-50 to +70 °C	-50 to +85 °C
	T5/T100 °C	-50 to +80 °C	-50 to +100 °C
	T4/T135 °C	-50 to +90 °C	-50 to +135 °C

Temperature assemblies with thermocouple temperature sensors			
Electrical connection ¹⁾	Temperature class/ Maximum surface temperature	Ambient temperature range	Process temperature range
	T3/T200 °C	-50 to +90 °C	-50 to +200 °C
	T2/T300 °C	-50 to +90 °C	-50 to +300 °C
	T1/T450 °C	-50 to +90 °C	-50 to +450 °C
Transmitter iTHERM TMT142: 7A iTHERM TMT162: 2D, 2E, 2F, 2G, 4B, 4C, 5B, 5C	T6/T85 °C	-40 to +55 °C	-50 to +85 °C
	T5/T100 °C	-40 to +70 °C	-50 to +100 °C
	T4/T135 °C	-40 to +80 °C	-50 to +135 °C
	T3/T200 °C	-40 to +80 °C	-50 to +200 °C
	T2/T300 °C	-40 to +80 °C	-50 to +300 °C
	T1/T450 °C	-40 to +80 °C	-50 to +450 °C

- 1) iTHERM TM111 suffix code h, iTHERM TM131 and iTHERM TM151 suffix code l.
- 2) in an enclosure with a blind cover; iTHERM TM111 suffix code i / iTHERM TM131 and iTHERM TM151 suffix code m = A1, D1, H1, H3.

Electrical connection data

Type	Electrical data
iTHERM TM111 iTHERM TM131 iTHERM TM151	Power supply U_b Transmitter TMT162: max. 40 V _{DC} , 3 W Transmitter TMT142B: max. 36 V _{DC} , 1 W other Transmitter: max. 42 V _{DC} , 23 mA Sensor: max. 10 V _{DC} , 1 mA

Type of protection	Type
Ex db IIC T6...T1 Gb	iTHERM TM111
Ex tb IIIC T85 °C...T450 °C Db	iTHERM TM111
Ex db IIC T6...T1 Ga/Gb	iTHERM TM131 iTHERM TM151
Ex ta IIIC T ₂₀₀ T85 °C...T ₂₀₀ 450 °C Da/ Ex tb IIIC T85 °C...T450 °C Db	iTHERM TM131 iTHERM TM151



71728009

www.addresses.endress.com
