# Technical Information **Proline Promag E 100**

Electromagnetic flowmeter



# The economical flowmeter with an ultra-compact transmitter

# Application

- The bidirectional measuring principle is virtually independent of pressure, density, temperature and viscosity
- Fully suitable for basic applications in the chemical and process industry

## Device properties

- Nominal diameter: max. DN 600 (24")
- Ex approvals for Zone 2
- Liner made of PTFE
- Robust, ultra-compact transmitter housing
- Local display available

# Your benefits

- Low-cost sensor ideal solution for basic requirements
- Energy-saving flow measurement no pressure loss due to cross-section constriction
- Maintenance-free no moving parts
- Space-saving transmitter full functionality on smallest footprint
- Time-saving local operation without additional software and hardware integrated web server
- Integrated verification Heartbeat Technology



# Table of contents

About this document	<b>3</b>
Function and system design	
Measuring principle	
Measuring system	
Equipment architecture	
Safety	0
Input	. 6
Measured variable	. 6
Measuring range	
Operable flow range	
Input signal	8
Output	8
Output signal	8
Signal on alarm	10
Low flow cut off	12
Protocol-specific data	12
Power supply	20
Terminal assignment	20
Pin assignment, device plug	26
Supply voltage	28
Power consumption	28
Current consumption	29
Power supply failure	29
Electrical connection	29
Potential equalization	33
Terminals	33 34
Cable entries	34 34
	54
Performance characteristics	35
Reference operating conditions	35
Maximum measured error	35
Repeatability	36
Temperature measurement response time	36
Influence of ambient temperature	36
Installation	36
Mounting location	36
Orientation	37
Inlet and outlet runs	38
Adapters	38
Environment	39
Ambient temperature range	39
Storage temperature	39
Degree of protection	39
Vibration resistance	39
Shock resistance	40 40
Impact resistance	40 40
Electromagnetic compatibility (EMC)	40
	10

Process	<b>40</b> 40 40 42 42 43 43 44
Mechanical construction	<b>44</b> 47 49 51 51 53 53 53
Operability	<b>53</b> 54 54 56
Certificates and approvals	<b>58</b> 58 59 59 59 59 59 59 59 59 60
Ordering information	60
Application packages	<b>60</b> 60 61
Accessories Device-specific accessories Communication-specific accessories Service-specific accessories System components	<b>61</b> 61 62 63
Supplementary documentation Standard documentation Supplementary device-dependent documentation	<b>63</b> 63 63
Registered trademarks	64

# About this document

# Symbols used

# Electrical symbols

Symbol	Meaning
	Direct current
$\sim$	Alternating current
$\sim$	Direct current and alternating current
<u>+</u>	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	<b>Protective Earth (PE)</b> A terminal which must be connected to ground prior to establishing any other connections.
	<ul><li>The ground terminals are situated inside and outside the device:</li><li>Inner ground terminal: Connects the protectiv earth to the mains supply.</li><li>Outer ground terminal: Connects the device to the plant grounding system.</li></ul>

## Symbols for certain types of information

Symbol	Meaning
	<b>Permitted</b> Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
×	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
i	<b>Tip</b> Indicates additional information.
<u></u>	Reference to documentation.
	Reference to page.
	Reference to graphic.
	Visual inspection.


## Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
X	Safe area (non-hazardous area)
≈►	Flow direction

# Function and system design

#### Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



- Ue Induced voltage
- B Magnetic induction (magnetic field)
- L Electrode spacing
- I Current
- v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced  $(U_e)$  is proportional to the flow velocity (v) and is supplied to the amplifier by means of two measuring electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The DC magnetic field is created through a switched direct current of alternating polarity.

# Formulae for calculation


- Induced voltage  $U_e = B \cdot L \cdot v$
- Volume flow  $Q = A \cdot v$

#### Measuring system


The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.

#### Transmitter




#### Sensor



1) For flanges made of carbon steel with Al/Zn protective coating (DN 15 to 300 (½ to 12")) or protective varnish (DN 350 to 600 (14 to 24"))

2) With Al/Zn protective coating (DN 15 to 300 (½ to 12")) or protective varnish (DN 350 to 600 (14 to 24"))

# Equipment architecture



- Possibilities for integrating measuring devices into a system
- 1 Control system (e.g. PLC)
- 2 EtherNet/IP
- 3 PROFIBUS DP
- 4 PROFINET
- 5 Modbus RS485
- 6 4-20 mA HART, pulse/frequency/switch output
- 7 Non-hazardous area
- 8 Non-hazardous area and Zone 2/Div. 2

#### Safety

# IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

75

# Input

25

1

Measured variable	Direct measured variables					
	<ul><li>Volum</li><li>Electri</li></ul>		proportional to induced vol activity	tage)		
	Calculat	ed meas	ured variables			
	<ul><li>Mass f</li><li>Correc</li></ul>		ne flow			
Measuring range	Typically $v = 0.01$ to 10 m/s (0.03 to 33 ft/s) with the specified accuracy Electrical conductivity: $\geq 5 \mu$ S/cm for liquids in general Flow characteristic values in SI units					
		ninal neter	Recommended flow	Facto	ry settings	
	value <sup>1</sup>			Low flow cut off (v ~ 0.04 m/s)		
	[mm]	[in]	[dm³/min]	[dm³/min]	[dm <sup>3</sup> ]	[dm³/min]
	15	1/2	4 to 100	25	0.2	0.5

9 to 300

1

0.5

Nom diam		Recommended flow	Factory settings		
	min./max. full scale value (v ~ 0.3/10 m/s)		Current output full scale value <sup>1)</sup> (v ~ 2.5 m/s)	Pulse value <sup>1)</sup> (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s)
[mm]	[in]	[dm <sup>3</sup> /min]	[dm <sup>3</sup> /min]	[dm <sup>3</sup> ]	[dm³/min]
32	-	15 to 500	125	1	2
40	1 ½	25 to 700	200	1.5	3
50	2	35 to 1 100	300	2.5	5
65	-	60 to 2 000	500	5	8
80	3	90 to 3 000	750	5	12
100	4	145 to 4700	1200	10	20
125	-	220 to 7 500	1850	15	30
150	6	20 to 600 m <sup>3</sup> /h	150 m³/h	0.03 m <sup>3</sup>	2.5 m <sup>3</sup> /h
200	8	35 to 1100 m <sup>3</sup> /h	300 m <sup>3</sup> /h	0.05 m <sup>3</sup>	5 m <sup>3</sup> /h
250	10	55 to 1700 m <sup>3</sup> /h	500 m <sup>3</sup> /h	0.05 m <sup>3</sup>	7.5 m <sup>3</sup> /h
300	12	80 to 2 400 m <sup>3</sup> /h	750 m³/h	0.1 m <sup>3</sup>	10 m <sup>3</sup> /h
350	14	110 to 3 300 m <sup>3</sup> /h	1000 m <sup>3</sup> /h	0.1 m <sup>3</sup>	15 m <sup>3</sup> /h
400	16	140 to 4 200 m <sup>3</sup> /h	1200 m <sup>3</sup> /h	0.15 m <sup>3</sup>	20 m <sup>3</sup> /h
450	18	180 to 5 400 m <sup>3</sup> /h	1500 m <sup>3</sup> /h	0.25 m <sup>3</sup>	25 m <sup>3</sup> /h
500	20	220 to 6 600 m <sup>3</sup> /h	2 000 m <sup>3</sup> /h	0.25 m <sup>3</sup>	30 m <sup>3</sup> /h
600	24	310 to 9600 m <sup>3</sup> /h	2 500 m <sup>3</sup> /h	0.3 m <sup>3</sup>	40 m <sup>3</sup> /h

1) HART only

Flow characteristic values in US units

	ninal neter	Recommended flow	Factory settings		
	min./max. full scale value (v ~ 0.3/10 m/s)		Current output full scale value <sup>1)</sup> (v ~ 2.5 m/s)	Pulse value <sup>1)</sup> (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s)
[in]	[mm]	[gal/min]	[gal/min]	[gal]	[gal/min]
1/2	15	1.0 to 27	6	0.1	0.15
1	25	2.5 to 80	18	0.2	0.25
1 1/2	40	7 to 190	50	0.5	0.75
2	50	10 to 300	75	0.5	1.25
3	80	24 to 800	200	2	2.5
4	100	40 to 1250	300	2	4
6	150	90 to 2 650	600	5	12
8	200	155 to 4850	1200	10	15
10	250	250 to 7 500	1500	15	30
12	300	350 to 10600	2400	25	45
14	350	500 to 15000	3600	30	60
16	400	600 to 19000	4800	50	60
18	450	800 to 24000	6000	50	90

Nominal diameter		Recommended flow	Factory settings		
		min./max. full scale value (v ~ 0.3/10 m/s)	Current output full scale value <sup>1)</sup> (v ~ 2.5 m/s)	Pulse value <sup>1)</sup> (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s)
[in]	[mm]	[gal/min]	[gal/min]	[gal]	[gal/min]
20	500	1000 to 30000	7500	75	120
24	600	1400 to 44000	10500	100	180

1) HART only

To calculate the measuring range, use the Applicator sizing tool  $\rightarrow \square 62$ 

# Recommended measuring range

"Flow limit" section  $\rightarrow \square 42$ 

Over 1000 : 1
External measured values
<ul> <li>To increase the accuracy of certain measured variables or to calculate the corrected volume flow, the automation system can continuously write different measured values to the measuring device:</li> <li>Operating pressure to increase accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S)</li> <li>Medium temperature to increase accuracy (e.g. iTEMP)</li> <li>Reference density for calculating the corrected volume flow</li> </ul>
Various pressure transmitters and temperature measuring devices can be ordered from Endress +Hauser: see "Accessories" section → 🗎 63
It is recommended to read in external measured values to calculate the following measured variables Corrected volume flow
HART protocol
The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions: <ul> <li>HART protocol</li> <li>Burst mode</li> </ul>
Digital communication
The measured values can be written from the automation system to the measuring via: PROFIBUS DP Modbus RS485 EtherNet/IP PROFINET

# Output

Output signal

## HART current output

Current output	4-20 mA HART (active)
Maximum output values	<ul> <li>DC 24 V (no flow)</li> <li>22.5 mA</li> </ul>
Load	0 to 700 Ω
Resolution	0.38 μΑ

Damping	Adjustable: 0.07 to 999 s
Assignable measured variables	<ul> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> <li>Flow velocity</li> <li>Conductivity</li> <li>Corrected conductivity</li> <li>Electronic temperature</li> </ul>

# Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	<ul> <li>DC 30 V</li> <li>25 mA</li> </ul>
Voltage drop	For 25 mA: ≤ DC 2 V
Pulse output	
Pulse width	Adjustable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Adjustable
Assignable measured variables	<ul><li>Volume flow</li><li>Mass flow</li><li>Corrected volume flow</li></ul>
Frequency output	
Output frequency	Adjustable: 0 to 10 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	<ul> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> <li>Flow velocity</li> <li>Conductivity</li> <li>Corrected conductivity</li> <li>Temperature</li> <li>Electronic temperature</li> </ul>
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s

Number of switching cycles	Unlimited
Assignable functions	<ul> <li>Off</li> <li>On</li> <li>Diagnostic behavior</li> <li>Limit value: <ul> <li>Off</li> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> <li>Flow velocity</li> <li>Conductivity</li> <li>Corrected conductivity</li> <li>Totalizer 1-3</li> <li>Temperature</li> <li>Electronic temperature</li> </ul> </li> <li>Flow direction monitoring</li> <li>Status <ul> <li>Empty pipe detection</li> <li>Low flow cut off</li> </ul> </li> </ul>

# PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud

# Modbus RS485

Physical interface	In accordance with EIA/TIA-485-A standard
Terminating resistor	Integrated, can be activated via DIP switch on the transmitter electronics module

# EtherNet/IP

Standards In accordance with IEEE 802.3	
---	--

## PROFINET

Standards	In accordance with IEEE 802.3	
-----------	-------------------------------	--

#### Signal on alarm

Depending on the interface, failure information is displayed as follows:

# Current output 4 to 20 mA

# 4 to 20 mA

Failure mode	<ul> <li>Choose from:</li> <li>4 to 20 mA in accordance with NAMUR recommendation NE 43</li> <li>4 to 20 mA in accordance with US</li> <li>Min. value: 3.59 mA</li> <li>Max. value: 22.5 mA</li> <li>Freely definable value between: 3.59 to 22.5 mA</li> <li>Actual value</li> <li>Last valid value</li> </ul>
--------------	---

#### Pulse/frequency/switch output

Pulse output	
Failure mode	Choose from: • Actual value • No pulses
Frequency output	
Failure mode	Choose from: • Actual value • 0 Hz • Defined value: 0 to 12 500 Hz
Switch output	
Failure mode	Choose from: • Current status • Open • Closed

## PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

## Modbus RS485

Failure mode	Choose from: NaN value instead of current value Last valid value
--------------	--

#### EtherNet/IP

<b>Device diagnostics</b> Device condition can be read out in Input Assembly
--

# PROFINET

Device diagnostics	According to "Application Layer protocol for decentralized periphery", Version 2.3
--------------------	--

#### Local display

Plain text display	With information on cause and remedial measures
Backlight	Red backlighting indicates a device error.

Status signal as per NAMUR recommendation NE 107

# Interface/protocol

- Via digital communication:
  - HART protocol
  - PROFIBUS DP
  - Modbus RS485
  - EtherNet/IP
  - PROFINET
- Via service interface CDI-RJ45 service interface

Plain text display         With information on cause and remedial measures
--



HART

Additional information on remote operation  $\rightarrow \square 54$ 

## Web server

Plain text display	With information on cause and remedial measures
--------------------	---

# Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes
	<ul> <li>The following information is displayed depending on the device version:</li> <li>Supply voltage active</li> <li>Data transmission active</li> <li>Device alarm/error has occurred</li> <li>EtherNet/IP network available</li> <li>EtherNet/IP connection established</li> <li>PROFINET network available</li> <li>PROFINET connection established</li> <li>PROFINET connection established</li> <li>PROFINET blinking feature</li> </ul>

The switch points for low flow cut off are user-selectable.

Protocol-specific data

Low flow cut off

Manufacturer ID	0x11
Device type ID	0x3A
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.
	Measured variables for PV (primary dynamic variable) <ul> <li>Off</li> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> <li>Flow velocity</li> <li>Temperature</li> <li>Electronic temperature</li> </ul>
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) Volume flow Mass flow Corrected volume flow Flow velocity Temperature Electronic temperature Totalizer 1 Totalizer 2 Totalizer 3
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned. A maximum of 8 device variables can be transmitted: 0 = volume flow 1 = mass flow 2 = corrected volume flow 3 = flow velocity 4 = conductivity 5 = corrected conductivity 6 = temperature 7 = electronic temperature 8 = totalizer 1 9 = totalizer 2 10 = totalizer 3

#### PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1561
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.org
Output values (from measuring device to automation system)	Analog input 1 to 4 • Volume flow • Mass flow • Corrected volume flow • Flow velocity • Conductivity • Corrected conductivity • Temperature • Electronic temperature Digital input 1 to 2 • Empty pipe detection • Low flow cut off
	<ul> <li>Verification status</li> <li>Totalizer 1 to 3</li> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> </ul>

Input values (from automation system to measuring device)	Analog output 1 to 2 (fixed assignment) <ul> <li>External temperature</li> <li>External density</li> </ul> <li>Digital output 1 to 2 (fixed assignment) <ul> <li>Digital output 1 to 2 (fixed assignment)</li> <li>Digital output 1: switch positive zero return on/off</li> <li>Digital output 2: start verification</li> </ul> </li> <li>Totalizer 1 to 3 <ul> <li>Totalize</li> <li>Reset and hold</li> <li>Preset and hold</li> <li>Stop</li> <li>Operating mode configuration: <ul> <li>Net flow total</li> <li>Forward flow total</li> </ul> </li> </ul></li>
Supported functions	<ul> <li>Forward flow total</li> <li>Reverse flow total</li> <li>Identification &amp; Maintenance Simplest device identification on the part of the control system and nameplate</li> <li>PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download</li> <li>Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur</li> </ul>
Configuration of the device address	<ul><li>DIP switches on the I/O electronics module</li><li>Via operating tools (e.g. FieldCare)</li></ul>

## Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1	
Device type	Slave	
Slave address range	1 to 247	
Broadcast address range	0	
Function codes	<ul> <li>03: Read holding register</li> <li>04: Read input register</li> <li>06: Write single registers</li> <li>08: Diagnostics</li> <li>16: Write multiple registers</li> <li>23: Read/write multiple registers</li> </ul>	
Broadcast messages	Supported by the following function codes: <ul> <li>06: Write single registers</li> <li>16: Write multiple registers</li> <li>23: Read/write multiple registers</li> </ul>	
Supported baud rate	<ul> <li>1200 BAUD</li> <li>2400 BAUD</li> <li>4800 BAUD</li> <li>9600 BAUD</li> <li>19200 BAUD</li> <li>38400 BAUD</li> <li>57 600 BAUD</li> <li>115 200 BAUD</li> </ul>	
Data transfer mode	ASCII     RTU	
Data access	Each device parameter can be accessed via Modbus RS485. For Modbus register information, see "Description of device parameters" documentation	

# EtherNet/IP

Protocol	<ul> <li>The CIP Networks Library Volume 1: Common Industrial Protocol</li> <li>The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP</li> </ul>		
Communication type	<ul><li>10Base-T</li><li>100Base-TX</li></ul>		
Device profile	Generic device (product type: 0x2B)		
Manufacturer ID	0x49E		
Device type ID	0x103A		
Baud rates	Automatic <sup>10</sup> / <sub>100</sub> Mbit with ha	lf-duplex and full-duple	x detection
Polarity	Auto-polarity for automatic of	correction of crossed TxD	and RxD pairs
Supported CIP connections	Max. 3 connections		
Explicit connections	Max. 6 connections		
I/O connections	Max. 6 connections (scanner	)	
Configuration options for measuring device	<ul> <li>DIP switches on the electronics module for IP addressing</li> <li>Manufacturer-specific software (FieldCare)</li> <li>Add-on Profile Level 3 for Rockwell Automation control systems</li> <li>Web browser</li> <li>Electronic Data Sheet (EDS) integrated in the measuring device</li> </ul>		
Configuration of the EtherNet interface	<ul> <li>Speed: 10 MBit, 100 MBit, auto (factory setting)</li> <li>Duplex: half-duplex, full-duplex, auto (factory setting)</li> </ul>		
Configuration of the device address	<ul> <li>DIP switches on the electronics module for IP addressing (last octet)</li> <li>DHCP</li> <li>Manufacturer-specific software (FieldCare)</li> <li>Add-on Profile Level 3 for Rockwell Automation control systems</li> <li>Web browser</li> <li>EtherNet/IP tools, e.g. RSLinx (Rockwell Automation)</li> </ul>		
Device Level Ring (DLR)	No		
Fix Input			
RPI	5 ms to 10 s (factory setting:	20 ms)	
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0x66	56
	$T \rightarrow O$ configuration:	0x64	32
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$0 \rightarrow T$ configuration:	0x66	56
	$T \rightarrow O$ configuration:	0x64	32
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x64	32
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$O \rightarrow T$ configuration:	0xC7	-
	L		

Input Assembly	<ul> <li>Current device diagnostics</li> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> <li>Totalizer 1</li> <li>Totalizer 2</li> <li>Totalizer 3</li> </ul>		
Configurable Input			
RPI	5 ms to 10 s (factory setting: 2	20 ms)	
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0x66	56
	$T \rightarrow O$ configuration:	0x65	88
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$O \rightarrow T$ configuration:	0x66	56
	$T \rightarrow O$ configuration:	0x65	88
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x65	88
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$O \rightarrow T$ configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x65	88
Configurable Input Assembly	I > 0 configuration:     0x65     88       • Volume flow     Corrected volume flow       • Mass flow       • Electronic temperature       • Totalizer 1 to 3       • Flow velocity       • Volume flow unit       • Corrected volume flow unit       • Mass flow unit       • Corrected volume flow unit       • Mass flow unit       • Corrected volume flow unit       • Mass flow unit       • Temperature unit       • Unit totalizer 1-3       • Flow velocity unit       • Verification result       • Verification status       • The range of options increases if the measuring device has one or more application packages.		
Fix Output			
Output Assembly	<ul> <li>Activation of reset totalizer:</li> <li>Activation of reference densi</li> <li>Activation of temperature of Reset totalizers 1-3</li> <li>External density</li> <li>Density unit</li> <li>External temperature</li> <li>Activation verification</li> <li>Start verification</li> </ul>	sity compensation	

Configuration		
Configuration Assembly	Only the most common configurations are listed below.	
	<ul> <li>Software write protection</li> </ul>	
	<ul> <li>Mass flow unit</li> </ul>	
	<ul> <li>Mass unit</li> </ul>	
	<ul> <li>Volume flow unit</li> </ul>	
	<ul> <li>Volume unit</li> </ul>	
	<ul> <li>Corrected volume flow unit</li> </ul>	
	<ul> <li>Corrected volume unit</li> </ul>	
	<ul> <li>Density unit</li> </ul>	
	<ul> <li>Reference density unit</li> </ul>	
	Temperature unit	
	<ul> <li>Pressure unit</li> </ul>	
	<ul> <li>Length</li> </ul>	
	<ul> <li>Totalizer 1-3:</li> </ul>	
	– Assignment	
	– Unit	
	– Operating mode	
	<ul> <li>Failsafe mode</li> </ul>	
	<ul> <li>Alarm delay</li> </ul>	

# PROFINET

Protocol	"Application layer protocol for decentral device periphery and distributed		
Protocol	automation", version 2.3		
Conformity class	В		
Communication type	100 MBit/s		
Device profile	Application interface identifier 0xF600 Generic device		
Manufacturer ID	0x11		
Device type ID	0x843A		
Device description files (GSD, DTM)	Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.org		
Baud rates	Automatic 100 Mbit/s with full-duplex detection		
Cycle times	From 8 ms		
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs		
Supported connections	<ul> <li>1 x AR (Application Relation)</li> <li>1 x Input CR (Communication Relation)</li> <li>1 x Output CR (Communication Relation)</li> <li>1 x Alarm CR (Communication Relation)</li> </ul>		
Configuration options for measuring device	<ul> <li>DIP switches on the electronics module, for device name assignment (last part)</li> <li>Manufacturer-specific software (FieldCare, DeviceCare)</li> <li>Web browser</li> <li>Device master file (GSD), can be read out via the integrated Web server of the measuring device</li> </ul>		
Configuration of the device name	<ul> <li>DIP switches on the electronics module, for device name assignment (last part)</li> <li>DCP protocol</li> </ul>		

<b>Output values</b> (from measuring device to automation system)	<ul> <li>Analog Input module (slot 1 to 10)</li> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> <li>Flow velocity</li> <li>Conductivity</li> <li>Corrected conductivity</li> <li>Temperature</li> <li>Electronic temperature</li> </ul>
	Discrete Input module (slot 1 to 10) <ul> <li>Empty pipe detection</li> <li>Low flow cut off</li> </ul>
	Diagnostics Input module (slot 1 to 10) <ul> <li>Last diagnostics</li> <li>Current diagnosis</li> </ul>
	Totalizer 1 to 3 (slot 11 to 13) <ul> <li>Volume flow</li> <li>Mass flow</li> <li>Corrected volume flow</li> </ul>
	Heartbeat Verification module (fixed assignment) Verification status (slot 17)
Input values (from automation system to measuring device)	<ul> <li>Analog Output module (fixed assignment)</li> <li>External density (slot 14)</li> <li>External temperature (slot 15)</li> </ul>
	<b>Discrete Output module (fixed assignment)</b> Activate/deactivate positive zero return (slot 16)
	Totalizer 1 to 3 (slot 11 to 13) <ul> <li>Totalize</li> <li>Reset and hold</li> <li>Preset and hold</li> <li>Stop</li> <li>Operating mode configuration: <ul> <li>Net flow total</li> <li>Forward flow total</li> <li>Reverse flow total</li> </ul> </li> </ul>
	Heartbeat Verification module (fixed assignment) Start verification (slot 17)
Supported functions	<ul> <li>Identification &amp; Maintenance Simple device identification via:         <ul> <li>Control system</li> <li>Nameplate</li> </ul> </li> <li>Measured value status The process variables are communicated with a measured value status</li> <li>Blinking feature via the local display for simple device identification and assignment</li> </ul>

Input/output value	Process variable	Category	Slot
Output value	Mass flow	Process variable	110
	Volume flow		
	Corrected volume flow		
	Temperature		
	Conductivity		
	Corrected conductivity		
	Electronic temperature		
	Flow velocity		
	Current device diagnostics		
	Previous device diagnostics		

Input/output value	Process variable	Category	Slot
Input/output value	Totalizer	Totalizer	1113
Input value	External density	Process monitoring	14
	External temperature		15
	Flow override		16
	Status verification	Heartbeat Verification <sup>1)</sup>	17

1) Only available with the "Heartbeat" application package.


# Startup configuration

Startup configuration	If startup configuration is enabled, the configuration of the most important
(NSU)	device parameters is taken from the automation system and used.
	The following configuration is taken from the automation system:
	<ul> <li>Management</li> </ul>
	<ul> <li>Software revision</li> </ul>
	<ul> <li>Write protection</li> </ul>
	<ul> <li>System units</li> </ul>
	– Mass flow
	– Mass
	– Volume flow
	– Volume
	<ul> <li>Corrected volume flow</li> </ul>
	<ul> <li>Corrected volume</li> </ul>
	– Density
	– Temperature
	– Conductivity
	<ul> <li>Sensor adjustment</li> </ul>
	<ul> <li>Process parameter</li> </ul>
	<ul> <li>Damping (flow, conductivity, temperature)</li> </ul>
	<ul> <li>Flow override</li> </ul>
	<ul> <li>Filter options</li> </ul>
	<ul> <li>Low flow cut off</li> </ul>
	<ul> <li>Assign process variable</li> </ul>
	<ul> <li>Switch-on/switch-off point</li> </ul>
	<ul> <li>Pressure shock suppression</li> </ul>
	<ul> <li>Empty pipe detection</li> </ul>
	<ul> <li>Assign process variable</li> </ul>
	– Limit values
	<ul> <li>Response time</li> </ul>
	<ul> <li>External compensation</li> </ul>
	<ul> <li>Temperature source</li> </ul>
	<ul> <li>Density source</li> </ul>
	– Density value
	<ul> <li>Diagnostic settings</li> </ul>
	<ul> <li>Diagnostic behavior for diverse diagnostic information</li> </ul>

# Power supply

## Terminal assignment

## Overview: housing version and connection versions



- A Housing version: compact, aluminum coated
- 1 Connection version: 4-20 mA HART, pulse/frequency/switch output
- $1.1 \ \ Signal \ transmission: pulse/frequency/switch \ output$
- 1.2 Signal transmission: 4-20 mA HART
- 1.3 Supply voltage
- 2 Connection version: Modbus RS485, PROFIBUS DP
- 2.1 Signal transmission
- 2.2 Supply voltage
- 3 Connection version: EtherNet/IP and PROFINET
- 3.1 Signal transmission
- 3.2 Supply voltage

#### Transmitter

Connection version 4-20 mA HART with pulse/frequency/switch output


Order code for "Output", option  ${\boldsymbol B}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code	Connection methods avai		Descible options for order sode
"Housing"	Outputs	Power supply	Possible options for order code "Electrical connection"
Option <b>A</b>	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option D: thread NPT <sup>1</sup>/<sub>2</sub>"</li> </ul>
Option <b>A</b>	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>

Order code	Connection me	thods available	Descible entions for order sode	
"Housing"	Outputs	Power supply	Possible options for order code "Electrical connection"	
Option <b>A</b>	Device plugs Device plugs		Option <b>Q</b> : 2 x plug M12x1	
Order code for "Hou	sing":			

Option A: compact, coated aluminum



፼ 2 Terminal assignment 4-20 mA HART with pulse/frequency/switch output

1

2 3

Power supply: DC 24 V Output 1: 4-20 mA HART (active) Output 2: pulse/frequency/switch output (passive)

	Terminal number					
Order code "Output"	Power supply		Power supply Output 1		Output 2	
	2 (L-)	1 (L+)	27 (-)	26 (+)	25 (-)	24 (+)
Option <b>B</b>	DC 2	24 V	4-20 mA H	ART (active)	Pulse/frequ output (	5
Order code for "Output": Option <b>B</b> : 4-20 mA HART with pulse/frequency/switch output						


#### PROFIBUS DP connection version

For use in the non-hazardous area and Zone 2/Div. 2

Order code for "Output", option  ${\boldsymbol L}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Onden es de	Connection methods available		Dessible entires for order and
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Option <b>A</b>	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>
Option <b>A</b>	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>
Option <b>A</b>	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Option <b>Q</b> : 2 x plug M12x1
Order code for "Hou Option <b>A</b> : compact,	5		



## 3 PROFIBUS DP terminal assignment

1 Power supply: DC 24 V

2 PROFIBUS DP

	Terminal number				
Order code	Power	supply	Output		
"Output"	2 (L-) 1 (L+) 26 (RxD/TxD-		26 (RxD/TxD-P)	27 (RxD/TxD- N)	
Option <b>L</b>	DC 24 V B A				
Order code for "Output": Option L: PROFIBUS DP, for use in non-hazardous areas and Zone 2/Div. 2					

#### Modbus RS485 connection version

Order code for "Output", option  ${f M}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Connection methods available		Possible entions for order sode	
Output	Power supply	Possible options for order code "Electrical connection"	
Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option D: thread NPT <sup>1</sup>/<sub>2</sub>"</li> </ul>	
Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>	
Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Option <b>Q</b> : 2 x plug M12x1	
	Output Terminals Terminals Device plugs (Verweisziel existiert nicht, aber @y.link.required=' Device plugs (Verweisziel existiert nicht, aber @y.link.required='	OutputPower supplyTerminalsTerminalsTerminalsTerminalsDevice plugs (Verweisziel existiert nicht, aber (Wilmk.required=true)TerminalsDevice plugs (Verweisziel existiert nicht, aber (Werweisziel existiert nicht, aberDevice plugs (Verweisziel existiert nicht, aberDevice plugs (Verweisziel existiert nicht, aberDevice plugs (Verweisziel existiert nicht, aber	

- 4 Modbus RS485 terminal assignment
- 1 Power supply: DC 24 V
- 2 Modbus RS485

	Terminal number				
Order code "Output"	Power	supply	Output		
o u put	1 (L+)	2 (L-)	26 (B)	27 (A)	
Option <b>M</b>	DC 24 V		Modbus RS485		
Order code for "Output": Option <b>M</b> : Modbus RS485					

Modbus RS485 connection version

For use in the intrinsically safe area. Connection via Safety Barrier Promass 100.

Order code for "Output", option  ${\boldsymbol{M}}$ 

## EtherNet/IP connection version


Order code for "Output", option  ${\bf N}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code	Connection methods available		Possible entions for order code	
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Option <b>A</b>	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT <sup>1</sup>/<sub>2</sub>"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>	
Option <b>A</b>	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Device plugs (Verweisziel existiert nicht, aber @y.link.required=' true')	Option <b>Q</b> : 2 x plug M12x1	

Order code for "Housing":

Option  $\boldsymbol{A}:$  compact, coated aluminum



- ☑ 5 EtherNet/IP terminal assignment
- 1 Power supply: DC 24 V
- 2 EtherNet/IP

	Terminal number			
Order code "Output"	Power supply Outp		Output	
	2 (L-)	1 (L+)	Device plug M12x1	
Option N	DC 24 V		EtherNet/IP	
Order code for "Output": Option <b>N</b> : EtherNet/IP				


#### PROFINET connection version

Order code for "Output", option  ${\bf R}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection methods available		Describle entions for order so de
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Option A	Device plugs → 🗎 26	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT <sup>1</sup>/<sub>2</sub>"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>
Option <b>A</b>	Device plugs → 🗎 26	Device plugs → 🗎 26	Option <b>Q</b> : 2 x plug M12x1
Order code for "Hou	sing":		

Option A: compact, coated aluminum



#### 6 PROFINET terminal assignment

1 Power supply: DC 24 V

2 PROFINET

	Terminal number			
Order code for "Output"	Power supply Output		Output	
	2 (L-)	1 (L+)	Device plug M12x1	
Option <b>R</b>	DC 24 V		PROFINET	
Order code for "Output": Option <b>R</b> : PROFINET	- ·			

Pin assignment, device plug

Order codes for the M12x1 connectors, see the "Order code for **electrical connection**" column: • 4-20 mA HART, pulse/frequency/switch output → 🗎 20

- PROFIBUS DP → 22
- Modbus RS485  $\rightarrow$  🗎 23
- EtherNet/IP  $\rightarrow$  🗎 25
- PROFINET → 🖺 26

# Supply voltage

For all connection versions (device side)

2	Pin		Assignment
	1	L+	DC 24 V
	2		Not assigned
	3		Not assigned
5	4	L-	DC 24 V
4 A0016809	5		Grounding/shielding


Coding	Plug/socket
А	Plug

The following is recommended as a socket:

- Binder, series 763, part no. 79 3440 35 05
   Alternatively: Phase in part no. 1660767 SAC ED M12
- Alternatively: Phoenix part no. 1669767 SAC-5P-M12MS
  - With the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
     With the order code for "Output", option N: EtherNet/IP
- When using the device in a hazardous location: Use a suitably certified socket.

#### 4-20 mA HART with pulse/frequency/switch output

Device plug for signal transmission (device side)




Recommended plug: Binder, series 763, part no. 79 3439 12 05
When using the device in a hazardous location, use a suitably certified plug.

#### PROFIBUS DP

**i** 

For use in the non-hazardous area and Zone 2/Div. 2.

Device plug for signal transmission (device side)




• Recommended plug: Binder, series 763, part no. 79 4449 20 05

When using the device in a hazardous location, use a suitably certified plug.

## MODBUS RS485

Device plug for signal transmission (device side)



Coding	Plug/socket
В	Socket



Recommended plug: Binder, series 763, part no. 79 4449 20 05
When using the device in a hazardous location, use a suitably certified plug.

#### EtherNet/IP

Device plug for signal transmission (device side)

2	Pin		Assignment
$\sim$	1	+	Тх
	2	+	Rx
	3	-	Тх
	4	-	Rx
4 A0016812	Cod	ling	Plug/socket
	Ι	)	Socket

Recommended plug:


Binder, series 763, part no. 99 3729 810 04

Phoenix, part no. 1543223 SACC-M12MSD-4Q

• When using the device in a hazardous location, use a suitably certified plug.

#### PROFINET

Device plug for signal transmission (device side)



Supply voltage

Current consumption	Transmitter						
	Order code for "Output"	Maximum Current consumption	Maximum switch-on current				
	Option <b>B</b> : 4-20mA HART, pul./freq./switch output	145 mA	18 A (< 0.125 ms)				
	Option L: PROFIBUS DP	145 mA	18 A (< 0.125 ms)				
	Option <b>M</b> : Modbus RS485	90 mA	10 A (< 0.8 ms)				
	Option <b>N</b> : EtherNet/IP	145 mA	18 A (< 0.125 ms)				
	Option R: PROFINET	145 mA	18 A (< 0.125 ms)				
Electrical connection	Connecting the transmitter						
Electrical connection		stored.					
	A A 1 2						

- Α Housing version: compact, aluminum coated
- Cable entry or device plug for signal transmission 1

2 Cable entry or device plug for supply voltage


Terminal assignment → <sup>(a)</sup> 20
Pin assignment, device plug → <sup>(a)</sup> 26



In the case of device versions with a connector, the transmitter housing does not need to be opened to connect the signal cable or power supply cable.


#### **Connection examples**

Current output 4 to 20 mA HART




☑ 7 Connection example for 4 to 20 mA HART current output (active)

- 1 Automation system with current input (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications → 🗎 34
- 3 Connection for HART operating devices  $\rightarrow \cong 54$
- 4 Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- 5 Analog display unit: observe maximum load
- 6 Transmitter




- 8 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications  $\rightarrow \square 34$
- 4 Analog display unit: observe maximum load
- 5 Transmitter

Pulse/frequency output



- ☑ 9 Connection example for pulse/frequency output (passive)
- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values


#### Switch output





- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values

#### PROFIBUS DP




- 11 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2
- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Transmitter

F


If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

#### Modbus RS485



I2 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2


- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter
- EtherNet/IP



13 Connection example for EtherNet/IP


- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

#### PROFINET




- 14 Connection example for PROFINET
- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

#### HART input



#### E 15 Connection example for HART input (burst mode) via current output (active)

- 1 Cable shield, observe cable specifications
- 2 Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- *3 Connection for HART operating devices*
- 4 Analog display unit
- 5 Transmitter
- 6 Sensor for external measured variable



■ 16 Connection example for HART input (master mode) via current output (active)

- 1 Automation system with current input (e.g. PLC).
- Prerequisite: automation system with HART version 6, HART commands 113 and 114 can be processed.
- 2 Cable shield, observe cable specifications
- 3 Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- 4 Connection for HART operating devices
- 5 Analog display unit
- 6 Transmitter
- 7 Sensor for external measured variable

Potential equalization Requirements

Please consider the following to ensure correct measurement:

- Same electrical potential for the medium and sensor
- Company-internal grounding concepts
- Pipe material and grounding

For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA).

Terminals

#### Transmitter

Spring terminals for wire cross-sections0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG)

Cable entries	<ul> <li>Cable gland: M20 × 1.5</li> <li>Thread for cable entry:</li> <li>M20</li> <li>G <sup>1</sup>⁄<sub>2</sub>"</li> <li>NPT <sup>1</sup>⁄<sub>2</sub>"</li> </ul>	with cable Ø6 to 12 mm (0.24 to 0.47 in)				
Cable specification	Permitted temperature r	ange				
		tes that apply in the country of installation must be observed. able for the minimum and maximum temperatures to be expected.				
	Power supply cable					
	Standard installation cable	e is sufficient.				
	Signal cable	Signal cable				
	Current output 4 to 20 mA HART					
	A shielded cable is recommended. Observe grounding concept of the plant.					
	Pulse/frequency/switch output					
	Standard installation cable is sufficient.					
	PROFIBUS DP					
	The IEC 61158 standard s	pecifies two types of cable (A and B) for the bus line which can be used fo able type A is recommended.				
	Cable type	А				
	Characteristic impedance	135 to 165 $\Omega$ at a measuring frequency of 3 to 20 MHz				
	Cable capacitance	< 30 pF/m				
	Wire cross-section	> 0.34 mm <sup>2</sup> (22 AWG)				
	Cable type	Twisted pairs				
	Loop resistance	≤110 Ω/km				
	Signal damping	Max. 9 dB over the entire length of the cable cross-section				
	Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.				

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	Α
Characteristic impedance	135 to 165 $\Omega$ at a measuring frequency of 3 to 20 MHz
Cable capacitance	< 30 pF/m
Wire cross-section	> 0.34 mm <sup>2</sup> (22 AWG)
Cable type	Twisted pairs
Loop resistance	$\leq$ 110 $\Omega/km$
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.

#### EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.

For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

#### PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.

For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

# Performance characteristics

Reference operating conditions	<ul> <li>Error limits following DIN EN 29104, in future ISO 20456</li> <li>Water, typically +15 to +45 °C (+59 to +113 °F); 0.5 to 7 bar (73 to 101 psi)</li> <li>Data as indicated in the calibration protocol</li> <li>Accuracy based on accredited calibration rigs according to ISO 17025</li> </ul>		
Maximum measured error	<b>Error limits under reference operating conditions</b> o.r. = of reading		
	<ul> <li>Volume flow</li> <li>±0.5 % o.r. ± 1 mm/s (0.04 in/s)</li> <li>Optional: ±0.2 % o.r. ± 2 mm/s (0.08 in/s)</li> <li>Fluctuations in the supply voltage do not have any effect within the specified range.</li> </ul>		
	[%] 2.5 2.0 1.5 1.0 		

■ 17 Maximum measured error in % o.r.

1

2

5

4

15

10

#### Electrical conductivity

0

0.5 + 0 + 0

Max. measured error not specified.

#### Accuracy of outputs

The output accuracy must be factored into the measured error if analog outputs are used, but can be ignored for fieldbus outputs (e.g. Modbus RS485, EtherNet/IP).

6

20

8

25

10

32

30

[m/s]

[ft/s]

The outputs have the following base accuracy specifications.


#### Current output

Accuracy Max. ±5 µA

	Pulse/frequency output		
	o.r. = of reading		
	Accuracy	Max. ±50 ppm o.r. (over the entire ambient temperature range)	
Repeatability	o.r. = of reading		
	<b>Volume flow</b> Max. ±0.1 % o.r. ± 0.5 mm/s (0.02 in/s)		
	<b>Electrical conductivity</b> Max. ±5 % o.r.		
Temperature measurement response time	T <sub>90</sub> < 15 s		
Influence of ambient temperature	Current output		
	o.r. = of reading		
	Temperature coefficient	Max. ±0.005 % o.r./°C	
	Pulse/frequency output		
	Temperature coefficient	No additional effect. Included in accuracy.	

# Installation


No special measures such as supports etc. are necessary. External forces are absorbed by the construction of the device.



Preferably install the sensor in an ascending pipe, and ensure a sufficient distance to the next pipe elbow: h  $\geq~2\times DN$ 

#### Installation in down pipes

Install a siphon with a vent valve downstream of the sensor in down pipes whose length  $h \ge 5 \text{ m}$  (16.4 ft). This precaution is to avoid low pressure and the consequent risk of damage to the measuring tube. This measure also prevents the system losing prime.




18 Installation in a down pipe

- 1 Vent valve
- 2 Pipe siphon
- h Length of down pipe

## Installation in partially filled pipes

A partially filled pipe with a gradient necessitates a drain-type configuration.



#### Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

	Orientation						
A	Vertical orientation						
В	Horizontal orientation, transmitter at top	E A0015589	<b>V V</b> <sup>1)</sup>				
С	Horizontal orientation, transmitter at bottom	A0015590	✓ 2) 3)				
D	Horizontal orientation, transmitter at side	A0015592	×				


1) Applications with low process temperatures may decrease the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.

2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.

3) To prevent the electronics module from overheating in the case of a sharp rise in temperature (e.g. CIP- or SIP processes), install the device with the transmitter component pointing downwards.

#### Horizontal

- Ideally, the measuring electrode plane should be horizontal. This prevents brief insulation of the two measuring electrodes by entrained air bubbles.
- Empty pipe detection only works if the transmitter housing is pointing upwards as otherwise there is no guarantee that the empty pipe detection function will actually respond to a partially filled or empty measuring tube.




- 1 EPD electrode for empty pipe detection
- 2 Measuring electrodes for signal detection
- 3 Reference electrode for potential equalization


#### Inlet and outlet runs

If possible, install the sensor upstream from fittings such as valves, T-pieces or elbows.

Observe the following inlet and outlet runs to comply with accuracy specifications:



I9 Order code for "Design", option A "Insertion length short, ISO/DVGW until DN400, DN450-2000 1:1" and order code for "Design", option B "Insertion length long, ISO/DVGW until DN400, DN450-2000 1:1.3"



20 Order code for "Design", option C "Insertion length short ISO/DVGW until DN300, w/o inlet and outlet runs, constricted meas.tube"


Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in largerdiameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids.

The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders:

- Calculate the ratio of the diameters d/D.
- From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.

The nomogram only applies to liquids with a viscosity similar to that of water.

Adapters




# Environment

Ambient temperature range	Transmitter	-40 to +60 °C (-40 to +140 °F)				
	Local display	-20 to $+60$ °C ( $-4$ to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range.				
	Sensor	Process connection material, carbon steel: -10 to +60 °C (+14 to +140 °F)				
	Liner	Do not exceed or fall below the permitted temperature range of the liner .				
		device in a shady location. particularly in warm climatic regions. to weather conditions.				
Storage temperature	The storage temperature corresponds to the operating temperature range of the measuring transmitter and the appropriate measuring sensors.→ 🗎 39					
	<ul> <li>Protect the measuring device against direct sunlight during storage in order to avoid unacceptably high surface temperatures.</li> <li>Select a storage location where moisture cannot collect in the measuring device as fungus or bacteria infestation can damage the liner.</li> <li>If protection caps or protective covers are mounted these should never be removed before installing the measuring device.</li> </ul>					
Degree of protection	<ul> <li>Transmitter and sensor</li> <li>As standard: IP66/67, type 4X enclosure</li> <li>When housing is open: IP20, type 1 enclosure</li> <li>Display module: IP20, type 1 enclosure</li> </ul>					
Vibration resistance	<ul> <li>Vibration, sinusoidal according to IEC 60068-2-6 <ul> <li>2 to 8.4 Hz, 3.5 mm peak</li> <li>8.4 to 2 000 Hz, 1 g peak</li> </ul> </li> <li>Vibration broad-band random, according to IEC 60068-2-64 <ul> <li>10 to 200 Hz, 0.003 g<sup>2</sup>/Hz</li> <li>200 to 2 000 Hz, 0.001 g<sup>2</sup>/Hz</li> <li>Total: 1.54 g rms</li> </ul> </li> </ul>					

Shock resistance	Shock, half-sine according to IEC 60068-2-27 6 ms 30 g
Impact resistance	Rough handling shocks according to IEC 60068-2-31
Mechanical load	<ul><li>Protect the transmitter housing against mechanical effects, such as shock or impact.</li><li>Never use the transmitter housing as a ladder or climbing aid.</li></ul>
Electromagnetic compatibility (EMC)	<ul> <li>Depends on the communication protocol: <ul> <li>HART, PROFIBUS DP, EtherNet/IP:</li> <li>As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)</li> <li>Modbus RS485:</li> <li>As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)</li> <li>PROFINET: as per IEC/EN 61326</li> </ul> </li> <li>Complies with emission limits for industry as per EN 55011 (Class A)</li> <li>Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170 Volume 2, IEC 61784</li> </ul>
	The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.
	Details are provided in the Declaration of Conformity.

# Process




- T<sub>A</sub> Ambient temperature
- $T_F \qquad \text{Medium temperature} \qquad \qquad$

 Conductivity
 ≥ 5 μS/cm for liquids in general. Stronger filter damping is required for very low conductivity values.


 Pressure-temperature ratings
 The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure


depending on the specific medium temperature.



Process connection: flange according to EN 1092-1 (DIN 2501)


☑ 21 Process connection material: carbon steel, FE410WB/S235JRG2





22 Process connection material: carbon steel, A105

#### Process connection: flange according to JIS B2220



☑ 23 Process connection material: carbon steel, S235JRG2/HII

Pressure tightness

"-" = no specifications possible

Liner: PTFE

Nominal	diameter	Limit values for	Limit values for absolute pressure in [mbar] ([psi]) for fluid temperature						
[mm]	[in]	+25 °C (+77 °F)	+80 °C (+176 °F)	+100 °C (+212 °F)	+110 °C (+230 °F)				
15	1/2	0 (0)	0 (0)	0 (0)	100 (1.45)				
25	1	0 (0)	0 (0)	0 (0)	100 (1.45)				
32	-	0 (0)	0 (0)	0 (0)	100 (1.45)				
40	1 ½	0 (0)	0 (0)	0 (0)	100 (1.45)				
50	2	0 (0)	0 (0)	0 (0)	100 (1.45)				
65	-	0 (0)	-	40 (0.58)	130 (1.89)				
80	3	0 (0)	-	40 (0.58)	130 (1.89)				
100	4	0 (0)	-	135 (1.96)	170 (2.47)				
125	-	135 (1.96)	-	240 (3.48)	385 (5.58)				
150	6	135 (1.96)	-	240 (3.48)	385 (5.58)				
200	8	200 (2.90)	-	290 (4.21)	410 (5.95)				
250	10	330 (4.79)	-	400 (5.80)	530 (7.69)				
300	12	400 (5.80)	-	500 (7.25)	630 (9.14)				
350	14	470 (6.82)	-	600 (8.70)	730 (10.6)				
400	16	540 (7.83)	-	670 (9.72)	800 (11.6)				
450	18								
500	20		No negative pre	ssure permitted!					
600	24	1							

#### Flow limit

The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum velocity of flow is between 2 to 3 m/s (6.56 to 9.84 ft/s). Also match the velocity of flow (v) to the physical properties of the fluid:

• v < 2 m/s (6.56 ft/s): for abrasive fluids (e.g. potter's clay, lime milk, ore slurry)

- v > 2 m/s (6.56 ft/s): for fluids producing buildup (e.g. wastewater sludge)
- A necessary increase in the flow velocity can be achieved by reducing the sensor nominal diameter.




For an overview of the full scale values for the measuring range, see the "Measuring range" section  $\rightarrow \square 6$ 

#### Pressure loss

• No pressure loss occurs if the sensor is installed in a pipe with the same nominal diameter.

• Pressure losses for configurations incorporating adapters according to DIN EN 545  $\rightarrow$   $\cong$  38



24 Pressure loss DN 50 to 80 (2 to 3") in the case of order code for "Design", option C "Insertion length short ISO/DVGW to DN300, without inlet/outlet runs, constricted meas.tube"






Image: 25 Pressure loss DN 100 to 300 (4 to 12") in the case of order code for "Design", option C "Insertion length short ISO/DVGW to DN300, without inlet/outlet runs, constricted meas.tube"




Never install the sensor on the pump suction side in order to avoid the risk of low pressure, and thus damage to the liner.



- Information on the liner's resistance to partial vacuum  $\rightarrow \textcircled{}{}$  42
- Information on the shock resistance of the measuring system  $\rightarrow ext{ } ex \text{ } ext{ } ex$
- Information on the vibration resistance of the measuring system  $\rightarrow$  🗎 39

Vibrations



• 26 Measures to avoid device vibrations (L > 10 m (33 ft))

In the event of very strong vibrations, the pipe and sensor must be supported and fixed.


- Information on the shock resistance of the measuring system  $\rightarrow \cong 40$
- Information on the vibration resistance of the measuring system ightarrow 🗎 39

# Mechanical construction

## Design, dimensions

#### **Compact version**

Order code for "Housing", option A "Compact, coated aluminum"




DN	L <sup>1)</sup>	А	В	С	D	E <sup>2)</sup>	F	G <sup>2)</sup>	Н	К
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
15	200	136	147.5	93.5	54	197	84	281	120	94
25	200	136	147.5	93.5	54	197	84	281	120	94
32	200	136	147.5	93.5	54	197	84	281	120	94
40	200	136	147.5	93.5	54	197	84	281	120	94

DN	L <sup>1)</sup>	A	В	С	D	E <sup>2)</sup>	F	G <sup>2)</sup>	Н	K
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
50	200	136	147.5	93.5	54	197	84	281	120	94
65	200	136	147.5	93.5	54	222	109	331	180	94
80	200	136	147.5	93.5	54	222	109	331	180	94
100	250	136	147.5	93.5	54	222	109	331	180	94
125	250	136	147.5	93.5	54	262	150	412	260	140
150	300	136	147.5	93.5	54	262	150	412	260	140
200	350	136	147.5	93.5	54	287	180	467	324	156
250	450	136	147.5	93.5	54	312	205	517	400	166
300	500	136	147.5	93.5	54	337	230	567	460	166

1) The length (L) is always the same, irrespective of the selected pressure rating.

2) If using a display, order code for "Display; Operation", option B: values + 28 mm



DN	L <sup>1)</sup>	А	В	С	D	F <sup>2)</sup>	G
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
350	550	136	147.5	93.5	54	399	290
400	600	136	147.5	93.5	54	425	290
450	600	136	147.5	93.5	54	450	290
500	600	136	147.5	93.5	54	476	290
600	600	136	147.5	93.5	54	528	290

1) The length (L) is always the same, irrespective of the selected pressure rating.

2) If using a display, order code for "Display; operation", option B: values + 28 mm


DN	E <sup>1)</sup> for pressure rating					H for pressure rating			
	PN 6	PN 10	PN 16	ASME	PN 6	PN 10	PN 16	ASME	
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
350	644	651	659	665	490	505	520	533	
400	695	707	715	723	540	565	580	597	

DN		E <sup>1)</sup> for pres	sure rating			H for pressure rating			
	PN 6	PN 10	PN 16	ASME	PN 6	PN 10	PN 16	ASME	
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
450	747	757	770	767	595	615	640	635	
500	798	811	833	825	645	670	715	699	
600	905	918	948	934	755	780	840	813	

1) If using a display, order code for "Display; operation", option B: values + 28 mm

# Accessories

Ground disk for flange connection



DN <sup>1)</sup>	A	В	С	D	Е	t
EN (DIN), JIS	PTFE					
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
15	16	43	61.5	73	6.5	2
25	26	62	77.5	87.5	6.5	2
32	35	80	87.5	94.5	6.5	2
40	41	82	101	103	6.5	2
50	52	101	115.5	108	6.5	2
65	68	121	131.5	118	6.5	2
80	80	131	154.5	135	6.5	2
100	104	156	186.5	153	6.5	2
125	130	187	206.5	160	6.5	2
150	158	217	256	184	6.5	2
200	206	267	288	205	6.5	2
250	260	328	359	240	6.5	2
300 <sup>2)</sup>	312	375	413	273	6.5	2
300 <sup>3)</sup>	310	375	404	268	6.5	2
350 <sup>2)</sup>	343	433	479	365	9.0	2
400 <sup>2)</sup>	393	480	542	395	9.0	2
450 <sup>2)</sup>	439	538	583	417	9.0	2

DN <sup>1)</sup>	А	В	С	D	E	t
EN (DIN), JIS	PTFE					
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
500 <sup>2)</sup>	493	592	650	460	9.0	2
600 <sup>2)</sup>	593	693	766	522	9.0	2

1) Ground disks DN 15 to 250 (½ to 10") can be used for all available flange standards/pressure ratings.


2) PN 10/16

3) JIS 10K/20K

Design,	dimensions
---------	------------

#### **Compact version**


Order code for "Housing", option A "Compact, coated aluminum"



DN	L <sup>1)</sup>	A	В	С	D	E <sup>2)</sup>	F	G <sup>2)</sup>	Н	K
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
1/2	7.87	5.35	5.81	3.68	2.13	7.76	3.31	11.1	4.72	3.70
1	7.87	5.35	5.81	3.68	2.13	7.76	3.31	11.1	4.72	3.70
1 1/2	7.87	5.35	5.81	3.68	2.13	7.76	3.31	11.1	4.72	3.70
2	7.87	5.35	5.81	3.68	2.13	7.76	3.31	11.1	4.72	3.70
3	7.87	5.35	5.81	3.68	2.13	8.74	4.29	13.0	7.09	3.70
4	9.84	5.35	5.81	3.68	2.13	8.74	4.29	13.0	7.09	3.70
6	11.8	5.35	5.81	3.68	2.13	10.3	5.91	16.2	10.2	5.51
8	13.8	5.35	5.81	3.68	2.13	11.3	7.09	18.4	12.8	6.14
10	17.7	5.35	5.81	3.68	2.13	12.3	8.07	20.4	15.8	6.54
12	19.7	5.35	5.81	3.68	2.13	13.3	9.06	22.3	18.1	6.54

1) The length (L) is always the same, irrespective of the selected pressure rating.

2) If using a display, order code for "Display; operation", option B: values + 1.1 in



DN	L 1)	А	В	С	D	F <sup>2)</sup>	G
[in]	[in]						
14	21.6	5.35	5.81	3.68	2.13	15.7	11.4
16	23.6	5.35	5.81	3.68	2.13	16.7	11.4
18	23.6	5.35	5.81	3.68	2.13	17.7	11.4
20	23.6	5.35	5.81	3.68	2.13	18.7	11.4
24	23.6	5.35	5.81	3.68	2.13	20.8	11.4


1) 2) The length (L) is always the same, irrespective of the selected pressure rating. If using a display, order code for "Display; operation", option B: values + 1.1 in

DN		E <sup>1)</sup> for pressure rating				H for press	sure rating	
	PN 6	PN 10	PN 16	ASME	PN 6	PN 10	PN 16	ASME
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
14	25.4	25.6	25.9	26.2	19.3	19.9	20.5	21.0
16	27.4	27.8	28.2	28.5	21.3	22.2	22.8	23.5
18	29.4	29.8	30.3	30.2	23.4	24.2	25.2	25.0
20	31.4	31.9	32.8	32.5	25.4	26.4	28.2	27.5
24	35.6	36.1	37.3	36.8	29.7	30.7	33.1	32.0

If using a display, order code for "Display; operation", option B: values + 1.1 in 1)

#### Accessories

Ground disk for flange connection



DN 1)	А	В	С	D	E	t
ASME	PTFE					
[in]	[in]	[in]	[in]	[in]	[in]	[in]
1/2	0.63	1.69	2.42	2.87	0.26	0.08
1	1.02	2.44	3.05	3.44	0.26	0.08
1 1/2	1.61	3.23	3.98	4.06	0.26	0.08
2	2.05	3.98	4.55	4.25	0.26	0.08
3	3.15	5.16	6.08	5.31	0.26	0.08
4	4.09	6.14	7.34	6.02	0.26	0.08
6	6.22	8.54	10.08	7.24	0.26	0.08
8	8.11	10.51	11.34	8.07	0.26	0.08
10	10.24	12.91	14.13	9.45	0.26	0.08
12	12.28	14.76	16.26	10.75	0.26	0.08
14	13.50	17.05	18.86	14.37	0.35	0.08
16	15.47	18.90	21.34	15.55	0.35	0.08
18	17.28	21.18	22.95	16.42	0.35	0.08
20	19.41	23.31	25.59	18.11	0.35	0.08
24	23.35	27.28	30.16	20.55	0.35	0.08

Ground disks can be used for all available pressure ratings. 1)

Weight

## **Compact version**

Including the transmitter (1.8 kg (4.0 lb))Weight specifications excluding packaging material

# Weight in SI units

Nominal d	iameter		EN (		ASME	JIS	
		PN 6	PN 10	PN 16	PN 40	Class 150	10K
[mm]	[in]	[kg]	[kg]	[kg]	[kg]	[kg]	[kg]
15	1/2	-	-	-	4.9	4.9	4.9
25	1	-	-	-	5.7	5.7	5.7
32	-	-	-	-	6.4	-	5.7
40	1 1/2	-	-	-	7.8	7.8	6.7
50	2	-	-	-	9.0	9.0	7.7
65	-	-	-	10.4	-	-	9.5
80	3	-	-	12.4	-	12.4	10.9
100	4	-	-	14.4	-	14.4	13.1
125	-	-	-	19.9	-	-	19.4
150	6	-	-	23.9	-	23.9	22.9
200	8	-	43.4	44.4	-	43.4	40.3
250	10	-	63.4	68.4	-	73.4	67.8
300	12	-	68.4	79.4	-	108.4	70.7
350	14	75.8	86.8	102	-	135.8	79
400	16	87.8	102.8	123.8	-	166.8	100
450	18	101.7	116.7	147.6	-	190.9	128
500	20	113.2	130.8	188.3	-	226.8	142
600	24	153.8	179.4	298.3	_	327.1	188

# Weight in US units

Nominal	diameter	ASME
[mm]	[in]	Class 150
		[lbs]
15	1/2	10.8
25	1	12.6
40	1 1⁄2	17.2
50	2	19.9
80	3	27.3
100	4	31.8
150	6	52.7
200	8	95.7
250	10	161.9
300	12	239.0
350	14	299.4
400	16	367.8
450	18	420.8
500	20	500.1
600	24	721.1


Measuring tube specification	Nominal	diameter		Pressure rating	Process connection internal diameter		
			EN (DIN)	ASME	JIS	РТ	FE
	[mm]	[in]	[bar]	[psi]	[bar]	[mm]	[in]
	15	1/2	PN 40	Class 150	20K	14	0.55
	25	1	PN 40	Class 150	20K	26	1.02
	32	-	PN 40	-	20K	34	1.34
	40	1 1/2	PN 40	Class 150	20K	40	1.57
	50	2	PN 40	Class 150	10K	51	2.01
	65	-	PN 16	-	10K	67	2.64
	80	3	PN 16	Class 150	10K	79	3.11
	100	4	PN 16	Class 150	10K	103	4.06
	125	-	PN 16	-	10K	128	5.04
	150	6	PN 16	Class 150	10K	155	6.10
	200	8	PN 10/16	Class 150	10K	203	7.99
	250	10	PN 10	-	10K	257	10.1
	250	10	PN 16	Class 150	10K	255	10.0
	300	12	PN 16	Class 150	10K	302	11.9
	350	14	PN 6/10	-	10K	338	13.3
	350	14	PN 16	Class 150	10K	334	13.1
	400	16	PN 6/10	-	10K	388	15.3
	400	16	PN 16	_	10K	386	15.2
	400	16	-	Class 150	10K	384	15.1
	450	18	PN 6/10	-	10K	440	17.3
	450	18	PN 16	-	10K	438	17.2
	450	18	-	Class 150	10K	434	17.1
	500	20	PN 6/10	_	10K	491	19.3
	500	20	PN 16	-	10K	487	19.2
	500	20	-	Class 150	10K	485	19.1
	600	24	PN 6	-	10K	592	23.3
	600	24	PN 10	-	10K	590	23.2
	600	24	PN 16	-	10K	588	23.2
	600	24	-	Class 150	10K	582	22.9

Materials

## Transmitter housing

- Order code for "Housing", option A "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
  Window material for optional local display (→ 
  \$\begin{aligned}{l} 54\$): For order code for "Housing", option A: glass

#### Cable entries/cable glands



#### ■ 27 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland M20 × 1.5
- 3 Adapter for cable entry with internal thread G  $\frac{1}{2}$  or NPT  $\frac{1}{2}$ "

#### Order code for "Housing", option A "Compact, coated aluminum"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Nickel-plated brass
Adapter for cable entry with internal thread G $^{1\!\!/}_{2}$	
Adapter for cable entry with internal thread NPT $\frac{1}{2}$ "	

## Device plug

Electrical connection	Material
Plug M12x1	<ul> <li>Socket: Stainless steel, 1.4404 (316L)</li> <li>Contact housing: Polyamide</li> <li>Contacts: Gold-plated brass</li> </ul>

#### Sensor housing

- DN 15 to 300 (1/2 to 12"): coated aluminum AlSi10Mg
- DN 350 to 600 (14 to 24"): carbon steel with protective varnish

#### Measuring tubes

Stainless steel, 1.4301/304/1.4306/304L; for flanges made of carbon with Al/Zn protective coating (DN 15 to 300 (½ to 12")) or protective varnish (DN 350 to 600 (14 to 24"))

Liner

PTFE

#### **Process connections**

EN 1092-1 (DIN 2501) Carbon steel, E250C <sup>1)</sup>/S235JRG2/P245GH ASME B16.5 Carbon steel, A105 JIS B2220 Carbon steel, A105/A350 LF2

<sup>1)</sup> DN 15 to 300 (½ to 12") with Al/Zn-protective coating; DN 350 to 600 (14 to 24") with protective coating

	Electrodes
	Stainless steel, 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); tantalum
	Seals
	As per DIN EN 1514-1, form IBC
	Accessories
	Ground disks
	Stainless steel, 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); tantalum; titanium
Fitted electrodes	Measuring electrodes, reference electrodes and electrodes for empty pipe detection: Standard: stainless steel, 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); tantalum
Process connections	<ul> <li>EN 1092-1 (DIN 2501): DN ≤ 300 (12") Form A, DN ≥ 350 (14") Form B; dimensions DN 65 PN 16 and only as per EN 1092-1</li> <li>ASME B16.5</li> <li>JIS B2220</li> <li>AS 2129 Table E</li> <li>AS 4087 PN 16</li> </ul>
Surface roughness	Stainless steel electrodes, 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); tantalum: ≤ 0.3 to 0.5 μm (11.8 to 19.7 μin) (All data relate to parts in contact with fluid)

# Operability

Operating concept	Operator-oriented menu structure for user-specific tasks <ul> <li>Commissioning</li> <li>Operation</li> <li>Diagnostics</li> <li>Expert level</li> </ul>
	<ul> <li>Quick and safe commissioning</li> <li>Individual menus for applications</li> <li>Menu guidance with brief explanations of the individual parameter functions</li> </ul>
	<ul> <li>Reliable operation <ul> <li>Operation in the following languages:</li> <li>Via "FieldCare", "DeviceCare" operating tool:</li> <li>English, German, French, Spanish, Italian, Chinese, Japanese</li> <li>Via integrated Web browser(only available for device versions with HART, PROFIBUS DP, PROFINET and EtherNet/IP):</li> <li>English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech, Swedish, Korean</li> </ul> </li> <li>Uniform operating philosophy applied to operating tools and Web browser</li> <li>If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure. For devices with Modbus RS485, the data recovery function is implemented without the plug-in memory (HistoROM DAT).</li> </ul>
	<ul> <li>Efficient diagnostics increase measurement availability</li> <li>Troubleshooting measures can be called up via the operating tools and web browser</li> <li>Diverse simulation options</li> <li>Status indicated by several light emitting diodes (LEDs) on the electronic module in the housing compartment</li> </ul>

# Local display

A local display is only available for device versions with the following communication protocols: HART, PROFIBUS-DP, PROFINET, EtherNet/IP

The local display is only available with the following device order code: Order code for "Display; operation", option **B**: 4-line; illuminated, via communication


## Display element

- 4-line liquid crystal display with 16 characters per line.
- White background lighting; switches to red in event of device errors.
- Format for displaying measured variables and status variables can be individually configured.
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F). The readability of the display may be impaired at temperatures outside the temperature range.

#### **Remote operation**

## Via HART protocol

This communication interface is available in device versions with a HART output.




28 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 VIATOR Bluetooth modem with connecting cable
- 7 Transmitter

#### Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




29 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

#### Via EtherNet/IP network

This communication interface is available in device versions with EtherNet/IP.

Star topology




30 Options for remote operation via EtherNet/IP network: star topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Ethernet switch
- 5 Measuring device

#### Via PROFINET network

This communication interface is available in device versions with PROFINET.

#### Star topology



31 Options for remote operation via PROFINET network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

#### Service interface


## Via service interface (CDI-RJ45)

This communication interface is present in the following device version:

- Order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
- Order code for "Output", option L: PROFIBUS DP
- Order code for "Output", option N: EtherNet/IP
- Order code for "Output", option R: PROFINET

#### HART


1



🖻 32 Connection for the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output

- Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


#### PROFIBUS DP



33 Connection for order code for "Output", option L: PROFIBUS DP

- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


#### EtherNet/IP



34 Connection for order code for "Output", option N: EtherNet/IP

- 1 Service interface (CDI -RJ45) and EtherNet/IP interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

## PROFINET




■ 35 Connection for order code for "Output", option R: PROFINET

- 1 Service interface (CDI -RJ45) and PROFINET interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

#### Via service interface (CDI)

This communication interface is present in the following device version: Order code for "Output", option  $\mathbf{M}$ : Modbus RS485

#### Modbus RS485



1 Service interface (CDI) of measuring device

2 Commubox FXA291

3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

# Certificates and approvals

CE mark	The measuring system is in conformity with the statutory requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-Tick symbol	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval	The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate. The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.			
	ATEX, IECEx			
	Currently, the following versions for use in hazard	lous areas are available:		
	Ex nA			
	Category	Type of protection		
	II3G	Ex nA IIC T6-T1 Gc		
HART certification	HART interface			
	The measuring device is certified and registered by meets all the requirements of the following specifi • Certified according to HART 7 • The device can also be operated with certified de	ications:		
Certification PROFIBUS	PROFIBUS interface			
	The measuring device is certified and registered by Organization). The measuring system meets all th • Certified in accordance with PROFIBUS PA Profi • The device can also be operated with certified de	e requirements of the following specifications: ile 3.02		
Modbus RS485 certification	The measuring device meets all the requirements of the MODBUS/TCP conformity test and has the "MODBUS/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out.			
EtherNet/IP certification	<ul> <li>The measuring device is certified and registered by the ODVA (Open Device Vendor Association).</li> <li>The measuring system meets all the requirements of the following specifications:</li> <li>Certified in accordance with the ODVA Conformance Test</li> <li>EtherNet/IP Performance Test</li> <li>EtherNet/IP PlugFest compliance</li> <li>The device can also be operated with certified devices of other manufacturers (interoperability)</li> </ul>			
Certification PROFINET	PROFINET interface			
	The measuring device is certified and registered by the PNO (PROFIBUS User Organization Organization). The measuring system meets all the requirements of the following specification: • Certified according to: – Test specification for PROFINET devices – PROFINET Security Level 1 – Netload Class • The device can also be operated with certified devices of other manufacturers (interoperabilit			
Pressure Equipment Directive	The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary.			
	<ul> <li>With the identification PED/G1/x (x = category) on the sensor nameplate, Endress+Hauser confirms conformity with the "Essential Safety Requirements" specified in Appendix I of the Pressure Equipment Directive 2014/68/EC.</li> <li>Devices bearing this marking (PED) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to0.5 bar (7.3 psi)</li> <li>Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Art. 4, Par. 3 of the Pressure Equipment Directive 2014/68/EU. The range of application is indicated in tables 6 to 9 in Annex II of the Pressure Equipment Directive 2014/68/EC.</li> </ul>			

# Other standards and guidelines

#### EN 60529

Degrees of protection provided by enclosures (IP code)

- EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use -
- general requirements
  IEC/EN 61326
  Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).
- NAMUR NE 21
- Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment • NAMUR NE 32
- Data retention in the event of a power failure in field and control instruments with microprocessors
- NAMUR NE 43 Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.
- NAMUR NE 53
- Software of field devices and signal-processing devices with digital electronics
- NAMUR NE 105
  - Specifications for integrating fieldbus devices in engineering tools for field devices
- NAMUR NE 107
- Self-monitoring and diagnosis of field devices
- NAMUR NE 131

Requirements for field devices for standard applications

# Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
   -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
   Open product page -> The "Configure" button to the right of the product image opens the Product
   Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com
- Product Configurator the tool for individual product configuration
  - Up-to-the-minute configuration data
    - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
    - Automatic verification of exclusion criteria
    - Automatic creation of the order code and its breakdown in PDF or Excel output format
    - Ability to order directly in the Endress+Hauser Online Shop

# **Application packages**

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Cleaning	Package	Description
		The electrode cleaning circuit (ECC) function has been developed to have a solution for applications where magnetite ( $Fe_3O_4$ ) deposits frequently occur (e.g. hot water). Since magnetite is highly conductive this build up leads to measuring errors and ultimately to the loss of signal. The application package is designed to AVOID build up of highly conductive matter and thin layers (typical of magnetite).

Heartbeat Technology	Package	Description
	Heartbeat Verification +Monitoring	<ul> <li>Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. Simple testing process via local operation or other operating interfaces. Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. Extension of calibration intervals according to operator's risk assessment.</li></ul>
		<ul> <li>Heartbeat Monitoring</li> <li>Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to:</li> <li>Draw conclusions - using these data and other information - about the impact process influences (such as corrosion, abrasion, buildup etc.) have on the measuring performance over time.</li> <li>Schedule servicing in time.</li> <li>Monitor the process or product quality, e.g. gas pockets.</li> </ul>

# Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

## Device-specific accessories

#### For the transmitter

Accessories	Description
Ground cable	Set, consisting of two ground cables for potential equalization.

#### For the sensor

Accessories	Description
Ground disks	Are used to ground the medium in lined measuring tubes to ensure proper measurement. For details, see Installation Instructions EA00070D

Communication-specific accessories	Accessories	Description
	Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see the "Technical Information" document TI405C/07
	HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions BA00371F
	Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. For details, see Operating Instructions BA00061S

Fieldgate FXA320	Gateway for the remote monitoring of connected 4 to 20 mA measuring devices a Web browser.	
	For details, see "Technical Information" TI00025S and Operating Instructions BA00053S	
Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser.	
	For details, see "Technical Information" TI00025S and Operating Instructions BA00051S	
Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices and can be used in non-hazardous areas.	
	For details, see Operating Instructions BA01202S	
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices and can be used in the non-hazardous area and in the hazardous area.	
	For details, see Operating Instructions BA01202S	

Applicator	<ul> <li>Software for selecting and sizing Endress+Hauser measuring devices:</li> <li>Choice of measuring devices for industrial requirements</li> <li>Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy.</li> <li>Graphic illustration of the calculation results</li> <li>Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.</li> <li>Applicator is available:</li> <li>Via the Internet: https://wapps.endress.com/applicator</li> <li>As a downloadable DVD for local PC installation.</li> </ul>
W@M	W@M Life Cycle Management Improved productivity with information at your fingertips. Data relevant to a plant and its components is generated from the first stages of planning and during the asset's complete life cycle. W@M Life Cycle Management is an open and flexible information platform with online and on-site tools. Instant access for your staff to current, in-depth data shortens your plant's engineering time, speeds up procurement processes and increases plant uptime. Combined with the right services, W@M Life Cycle Management boosts productivity in every phase. For more information, visit www.endress.com/lifecyclemanagement
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition. For details, see Operating Instructions BA00027S and BA00059S
DeviceCare	Tool for connecting and configuring Endress+Hauser field devices. For details, see Innovation brochure IN01047S

Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser

Common Data Interface) and the USB port of a computer or laptop.

For details, see "Technical Information" TI00405C

Description

Service-specific accessories

Accessories

Commubox FXA291

#### System components

Accessories	Description
Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
	For details, see "Technical Information" TI00133R and Operating Instructions BA00247R

# Supplementary documentation

For an overview of the scope of the associated Technical Documentation, refer to the following: The W@M Device Viewer : Enter the serial number from the nameplate

- (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

#### **Brief Operating Instructions**

Brief Operating Instructions containing all the important information for standard commissioning is enclosed with the device.

#### **Operating Instructions**

Measuring	Documentation code				
device	HART         PROFIBUS DP         Modbus RS485         EtherNet/IP         PROFINET				
Promag E 100	BA01305D	BA01307D	BA01306D	BA01308D	BA01423D

#### Description of device parameters

Measuring device	Documentation code				
	HART PROFIBUS DP Modbus RS485 EtherNet/IP PROFINET				
Promag 100	GP01038D	GP01039D	GP01040D	GP01041D	GP01042D

Supplementary devicedependent documentation

### Safety Instructions

Contents	Documentation code
ATEX/IECEx Ex nA	XA01090D

#### **Special Documentation**

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01056D
Modbus RS485 Register Information	SD01148D
Heartbeat Technology	SD01149D

#### Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory .

# **Registered trademarks**

#### HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

#### **PROFIBUS®**

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

#### Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

## EtherNet/IP™

Trademark of ODVA, Inc.

#### **PROFINET®**

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

#### Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA

# www.addresses.endress.com

