Technical information Soliphant M FTM50, FTM51, FTM52

Vibronic



Universal point level switch for fine-grained bulk solids

Application

Soliphant M is a robust point level switch for silos with fine-grained or dusty bulk solids even with a low bulk weight.

The various designs mean the device has a wide range of applications. Many certificates are available for use in dust or gas incendive hazard areas.

FTM50:

Compact design for installation in any position. A wide range of applications thanks to various variations e.g.

- Polished short fork with stainless steel housing (F15) and Tri-Clamp
- Coated standard fork with aluminum housing (F17) and flange
- Standard fork with 280 °C (536 °F) rating and aluminum housing (F13)

FTM51

With extension pipe up to 4 m (13 ft) for installation in any position

With rope up to 20 m (66 ft) for installation from above

Typical applications:

Cereals, flour, cocoa, sugar, animal feed, detergents, dye powder, chalk, gypsum, cement, plastic granules, fly ash

Your benefits

- Market leader in the area of level detection of bulk solids
- Functional safety up to SIL 2 as per IEC 61508
- No mechanically moving parts
- Insensitive to external vibrations and build-up
- Various electronic inserts
- Configurable density setting (bulk weight setting) and switching delay
- Process temperature up to 280 °C (536 °F)
- Choice of coated or polished sensor
- Warning in the event of impending device failure due to buildup or abrasion



Table of contents


Function and system design
Measuring principle
Measuring system
Cable specifications4
Immunity to temperature change of connecting cable 4
Connecting cables
Cable entry
Cable entry 4
Input
Measured variable
Measuring range (detection range) 4
Input signal
Measuring frequency 4
Output4
Galvanic isolation
Switch-on behavior
Fail-safe mode 4
Switching delay 5
Switch behavior 5
Electronic insert5
FEM51 electronic insert (AC 2-wire) 5
FEM52 electronic insert (DC PNP)
FEM54 electronic insert (DCTM)
FEM55 electronic insert (8/16 mA)
FEM58 electronic insert (NAMUR H-L edge)
FEM57 electronic insert (PFM)
Installation 13
Installation
Installation13Installation instructions13
Installation instructions
Installation instructions 13 Environment 14
Installation instructions
Installation instructions13Environment14Ambient temperature range14Storage temperature14
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15
Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15Limiting medium pressure range16
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15Limiting medium pressure range16State of aggregation16Grain size16
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15Limiting medium pressure range16State of aggregation16Grain size16Bulk weight16
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15Limiting medium pressure range16State of aggregation16Grain size16Bulk weight16
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15Limiting medium pressure range16State of aggregation16Grain size16Bulk weight16Lateral load (static)16
Installation instructions 13 Environment 14 Ambient temperature range 14 Storage temperature 14 Climate class 14 Degree of protection 14 Vibration resistance 14 Shock resistance 14 Electrical safety 14 Electromagnetic compatibility 14 Process 15 Medium temperature limits 15 Thermal shock resistance 15 Limiting medium pressure range 16 State of aggregation 16 Grain size 16 Bulk weight 16 Lateral load (static) 16 Tensile strength rope FTM52 16
Installation instructions13Environment14Ambient temperature range14Storage temperature14Climate class14Degree of protection14Vibration resistance14Shock resistance14Electrical safety14Electromagnetic compatibility14Process15Medium temperature limits15Thermal shock resistance15Limiting medium pressure range16State of aggregation16Grain size16Bulk weight16Lateral load (static)16Tensile strength rope FTM5216Mechanical construction17
Installation instructions 13 Environment 14 Ambient temperature range 14 Storage temperature 14 Climate class 14 Degree of protection 14 Vibration resistance 14 Shock resistance 14 Electrical safety 14 Electromagnetic compatibility 14 Process 15 Medium temperature limits 15 Thermal shock resistance 15 Limiting medium pressure range 16 State of aggregation 16 Grain size 16 Bulk weight 16 Lateral load (static) 16 Tensile strength rope FTM52 16

Versions with extensions2Versions with temperature spacer2Surface refinement2Version with separate housing2Weights2Materials and surfaces2
Operability2Display elements2Operating elements of FEM51, FEM52, FEM54, FEM55,2FEM582Operating elements of FEM572Sediment detection with FTM50 and FTM512
Certificates and approvals
Ordering information
Accessories2Removing tool2Weather protection cover2Sliding sleeve3Rope shortening kit3
Documentation3Operating Instructions3Certificates3Expectational safety3

Function and system design

Measuring principle

A piezoelectric drive excites the tuning fork of Soliphant M to its resonance frequency. If medium covers the tuning fork, the fork's vibrating amplitude changes (the vibration is damped). Soliphant M's electronics compare the actual amplitude with a target value and indicate whether the tuning fork is vibrating freely or whether it is covered by medium.



A: Amplitude t: Time

Measuring system

The measuring system is available either with compact instrumentation or separate instrumentation with a switching unit. The following electronic versions are available:

Compact instrumentation FEM51:


- Two-wire AC version
- Switch the load directly into the power supply circuit via the thyristor

FEM52:

- Three-wire DC version
- Switch the load via the transistor (PNP) and separate connection

FEM54:

- Universal current version with relay output
- Switch the loads via 2 floating change-over contacts (DPDT)



1 Electronic version

Separate instrumentation with switching unit

For connecting to a separate switching unit or isolating amplifier such as Nivotester:

- FTL325N, FTL375N (NAMUR) or
- FTL325P, FTL375P (PFM)

FEM55


Signal transmission 8/16 mA along two-wire cabling:

FEM57:

- PFM signal transmission
- Current pulses superposed on the power supply along the two-wire cabling
- Self-test from the switching unit without changing levels

FEM58

- Signal transmission H-L edge 2.2 to 4.8 / 0.4 to 1.0 mA to EN 50227 (NAMUR) along two-wire cabling
- Checking of connecting cabling and other devices by pressing a key on the electronic insert



- 1 Electronic version
- Switching unit, PLC, isolating amplifier, segment coupler

Cable specifications

Within the indicated standards and guidelines to interference immunity (see also "Electromagnetic compatibility", $\rightarrow \stackrel{\cong}{=} 14$) a normal instrument cable is sufficient. If higher interference levels are present, a shielded cable must be used.

Immunity to temperature change of connecting cable

In non-Ex applications the connecting cables must withstand the ambient temperature +5 K. For Ex applications, the specifications of the respective certificate (XA) must be observed $\rightarrow \stackrel{\text{\tiny le}}{\rightarrow} 30$ Certificates.

Connecting cables

- Electronic inserts: cross-section max. 2.5 mm² (13 AWG); strand in ferrule to DIN 46228
- Protective ground in housing: cross-section max. 2.5 mm² (13 AWG)
- Equipotential bonding connection on housing: cross-section max. 4 mm² (11 AWG)

Cable entry

Housing-specific: screw terminal on electronic insert.

Cable gland M20x1,5 for cable:

- Nickel-plated brass: ø7...10,5 mm (0.28...0.41 in)
- Plastic: ø5...10 mm (0.2...0.38 in)
- Stainless steel: ø7...12 mm (0.28...0.47 in)

Input

Measured variable

Level (according to the mounting location and the overall length)

Measuring range (detection range)

- FTM50: overall length see, \rightarrow 🗎 19
- FTM51: overall length 300 to 4000 mm (11.8 to 157 in)
- FTM52: overall length 750 to 20000 mm (29.5 to 787 in)

The measuring range of Soliphant M depends on the medium, mounting location and fork length. The detection range is located within the length of the fork.

Distinction between the forks:

- For light media:
 - Standard fork with a fork length of 155 mm (6.1 in) (bulk weight of the medium \geq 10 g/l)
- For confined installation conditions, high lateral load or increased buildup: Short fork with a fork length of 100 mm (3.94 in) (bulk weight of the medium \geq 50 g/l)

Input signal

- Probes covered => little to no vibrating amplitude
- Probes not covered => large vibrating amplitude

Selectable frequency monitoring (diagnosis) for detection of abrasion and build-up.

Measuring frequency

- Standard fork: approx. 140 Hz (in air)
- Short fork: approx. 350 Hz (in air)

Output

Galvanic isolation

- FEM51, FEM52, FEM55: Between sensor and power supply
- FEM54: Between sensor, power supply and load
- FEM57, FEM58: See switching unit connected

Switch-on behavior

When the power supply is switched on the switching status of the outputs corresponds to "signal on alarm". The correct switching status is assumed after a maximum of 3 s.

Fail-safe mode

Minimum/maximum residual current safety selectable on electronic insert. (with FEM57 only at Nivotester).

MAX = maximum safety:

The output switches safety-oriented when the fork is covered (signal on alarm)

For use with overfill prevention for example.

MIN = minimum safety:

The output switches safety-oriented when the fork is uncovered (signal on alarm)

For use with dry running protection for example.

Switching delay

0.5 s when the sensor is covered.

Version 150 $^{\circ}$ C (302 $^{\circ}$ F): 1.5 s when the sensor is uncovered (1.0 s for short fork)

Version 230/280 $^{\circ}$ C (446/536 $^{\circ}$ F): 2 s when the sensor is uncovered (1.0 s for short fork)

Can be changed to 5 s for covering and uncovering.

Switch behavior

Binary

Electronic insert

FEM51 electronic insert (AC 2-wire)

Power supply


- Supply voltage AC: 19 to 253 V
- Power consumption: < 1.0 W
- Residual current consumption (I_R): < 4 mA; 5.5 mA for short fork (in switch-off moment < 1 mA for 100 ms)
- Short-circuit protection
- Separation voltage: 3.6 kV
- FEM51 overvoltage protection: overvoltage category II

Two-wire AC connection

Always connect in series with a load!

Check the following:

- the residual current consumption in blocked state.
- that for low voltage
 - the voltage drop across the load is such that the minimum terminal voltage at the electronic insert (19 V) when blocked is not undershot.
 - $\,$ the voltage drop across the electronics when switched through is observed (up to 12 V).
- when selecting the relay, pay attention to the holding power/rated power (see "Connectable load").
- * External load "R" must be connected
- ** AC: U~max. 253 V, 50/60 Hz



LUU-F1M5xxxx-U4-U5-xx-xx-U

Output signal

I_I = load current (switched through)


I_R = residual current (blocked)

_____ = lit

= flashes

 \bullet = unlit

* See also "Operating elements", $\rightarrow \stackrel{\triangle}{=} 25$



L00-FTM5xxxx-04-05-xx-en-00

Signal on alarm

Output signal on power failure or in the event of device failure: I_{R}

Connectable load

- For relays with a minimum holding power/rated power > 2.5 VA at 253 V (10 mA) or > 0.5 VA at 24 V (20 mA)
- ullet For relays with a maximum holding power/rated power < 89 VA at 253 V or 8.4 VA at 24 V
- Voltage drop across FEM51 max. 12 V
- Residual current with blocked thyristor max. 4 mA (5.5 mA for short fork)
- Load current max. 350 mA (short-circuit proof)


FEM52 electronic insert (DC PNP)

Power supply

- DC voltage: 10 to 55 V
- Ripple: max. 1.7 V, 0 to 400 Hz
- Current consumption: max. 16 mA
- Power consumption: max. 0.86 W
- Reverse polarity protection/short-circuit protection
- Separation voltage: 3.6 kV
- FEM52 overvoltage protection: overvoltage category III

Three-wire DC connection with cable entry / M12 plug

- Preferably used with programmable logic controllers (PLC)
- DI modules as per EN 61131-2
- Positive signal at switching output of the electronics (PNP)



L00-FTM5xxxx-04-05-xx-xx-02

DC: U= 10 V...55 V

A: With cable entry wired by customer (Ordering feature 80, options 2, 3, 4, 7) B: With M12 plug wired at the factory (Ordering feature 80, option 1)

Output signal

 I_L = load current (switched through)

 I_R = residual current (blocked)

-\(= lit

= flashes

= unlit

Safety mode	Level	Output signal	LEDs green yellow red
MAX		L+ l _⊥ + 3	-\\(\dagger\)-\\(\dagger\)-
WIAX		1 - 3	-\(\daggregap\)-
MIN		L+ l _L + 3	- \ \(\dagger\)-\(\dagger\)-
		1 - 3	-\(\hat{\psi}\)- • •
Maintenance required *		13	-☆- • - 汝
Instrument failu	ire L	1 	- \ \ • - \ \

L00-FTM5xxxx-04-05-xx-en-007

Signal on alarm

Output signal on power failure or in the event of device failure: < 100 μA

Connectable load

- Load switched via transistor and separate PNP connection, max. 55 V
- Load current max. 350 mA (pulsed overload and short-circuit protection)
- Residual current < 100 µA (with transistor blocked)
- \bullet Capacitance load max. 0.5 μF at 55 V, max. 1.0 μF at 24 V
- Residual voltage < 3 V (with transistor switched through);

FEM54 electronic insert AC/DC with relay output)

Power supply

- Alternating voltage AC: 19 to 253 V, 50/60 Hz DC voltage: 19 to 55 V
- Power consumption: max. 1.5 W
- Reverse polarity protection/short-circuit protection
- Separation voltage: 3.6 kV
- FEM54 overvoltage protection: overvoltage category II


Universal current connection with relay output (DPDT)

Please note the different voltage ranges for AC and DC.

Output:

When connecting a device with high inductance, provide a spark arrester to protect the relay contact. A fine-wire fuse (depending on the load connected) protects the relay contact on short-circuiting. The relay contacts switch simultaneously.

- * When jumpered, the relay output works with NPN logic.
- ** See "Connectable load"
- 1 Relay outputs: normally open/closed (NO, NC)
- 2 AC: U~19 to 253 V, DC: U=19 to 55 V



Output signal

| = relay energized

| / = relay de-energized



= flashes

= unlit

* See also "Operating elements", $\rightarrow \stackrel{\triangle}{1} 25$

Safety mode	Level	Output signal	LEDs green yellow red
MAX		3 4 5 6 7 8	- <u></u>
IVIAA		3 4 5 6 7 8	- <u></u>
		3 4 5 6 7 8	- <u>\</u> \
MIN		3 4 5 6 7 8	-\(\daggregap\)-
Maintenance required *			-\(\d_{-}\)
Instrument failu	ire L	3 4 5 6 7 8	-\\(\dagger^-\) • -\\(\dagger^-\)

L00-FTM5xxxx-04-05-xx-en-008

Signal on alarm

Output signal on power failure or in the event of device failure: relay de-energized

Connectable load

- Loads switched via 2 floating change-over contacts (DPDT)
- AC: I~ max. 6 A (Ex de 4 A), U~ max. 253 V; P~ max. 1500 VA, $\cos \varphi = 1$, P~ max. 750 VA, $\cos \varphi > 0.7$
- DC: I= max. 6 A (Ex de 4 A) to 30 V, I= max. 0.2 A to 125 V
- The following applies when connecting a functional low-voltage circuit with double isolation as per IEC 1010: Sum of voltages of relay output and power supply max. 300 V

FEM55 electronic insert (8/16 mA)

Power supply

DC supply voltage: 11 to 36 VPower consumption: < 600 mW

• Reverse polarity protection/short-circuit protection


■ Separation voltage: 3.6 kV

• FEM55 overvoltage protection: overvoltage category II

Two-wire connection for separate switching unit with cable entry / M12 plug


For connecting to programmable logic controllers (PLC), AI modules 4-20 mA to EN 61131-2. Output signal jump from high to low current on point level.

Use only power supply with safe galvanically isolation (e.g. SELV).



L00-FTM5xxxx-04-05-xx-xx-00

U=11 to 36 e.g. PLC With cable entry wired by customer (Ordering feature 80, options 2, 3, 4, 7)



L00-FTM5xxxx-04-05-xx-xx-000a

With M12 plug wired at the factory (Ordering feature 80, option 1) $\,$

Output signal

 $\sim 16 \text{ mA} = 16 \text{ mA} \pm 5 \%$

 $\sim 8 \text{ mA} = 8 \text{ mA} \pm 6 \%$

= lit

= flashes

= unlit

* See also "Operating elements", \rightarrow $\stackrel{ }{ }$ 25

Safety mode	Level	Output signal	LEDs green yellow red
MAX		⁺ 2 ~16 mA → 1	-\(\dagger\)-\(\dagger\)-
WAX		+ ~8 mA ≥ 1	-\(\hat{\psi}\)- • •
MIN		⁺ 2 ~16 mA 1	-¤́¤́- •
		⁺ 2 ~8 mA → 1	-\\(\dagger^-\) • •
Maintenance required *		+ 8/16 mA → 1	- ⁄ ⁄⁄ - ⁄ ⁄⁄
	4	1.6 mA	- ⁄
Instrument failu	ire L	⁺ 2 3.6 mA → 1	• • -\\.

L00-FTM5xxxx-04-05-xx-en-006

Signal on alarm

Output signal on power failure or in the event of device failure: < 3.6 mA

Connectable load

- \blacksquare R = (U 11 V) / 16.8 mA
- U = connection DC voltage 11 V to 36 V (in wet location DC 11...35 V)

FEM58 electronic insert (NAMUR H-L edge)

Note!

Only in combination with standard fork (fork length 155 mm (6.1 in)).

Power supply

- DC supply voltage: 8.2 V ±20 %
- Power consumption: < 8 mW at I < 1 mA; < 36 mW at I = 2.2 to 4.8 mA
- Separation voltage: 1.9 kV
- Connection data interface: IEC 60947-5-6

Two-wire connection for separate switching unit with cable entry / $M12\ plug$

For connecting to isolating amplifiers acc. to NAMUR (IEC 60947-5-6), z.B. FTL325N or FTL375N from Endress+Hauser.

H-L edge:

Output signal jump from high to low current on point level.


Additional function:

Test key on the electronic insert.

Pressing the key breaks the connection to the isolating amplifier.


Note!

- For Ex d applications, the additional function can only be used if the housing is not exposed to an explosive atmosphere.
- Connecting to multiplexer: Set clock time to min. 5 s.



L00-FTM5xxxx-04-05-xx-xx-005

Isolating amplifier to IEC 60947-5-6 (NAMUR) With cable entry wired by customer (Ordering feature 80, options 2, 3, 4, 7)



L00-FTM5xxxx-04-05-xx-xx-005a

With M12 plug wired at the factory (Ordering feature 80, option 1) $\,$

Output signal

.Ö.-

= flashes

= lit

= unlit

^{*} See also "Operating elements", \rightarrow $\stackrel{ }{ }$ 25

Safety mode	Level	Output signal	LEDs green yellow red
MAX		2.2 + 4.8 mA 2 1	<i>-</i> ≱ -\$- •
IVIAX		0.4 + 1.0 mA 2	• •
MIN		2.2 + 4.8 mA 2 1	- -
		0.4 + 1.0 mA 2	- À • •
Maintenance required *		0.4 + 4.8 mA 2	- À
Instrument failu	ire L	0.4 + 1.0 mA 2 1	• • -

L00-FTM5xxxx-04-05-xx-en-012

Signal on alarm

Output signal

in event of device failure: < 1.0 mA

Connectable load

- See "Technical Data" of the isolating amplifier connected according to IEC 60947-5-6 (NAMUR)
- Connection also to safety isolating amplifiers (I = 3 to 4.8 mA)

FEM57 electronic insert (PFM)

Power supply

■ DC supply voltage: 9.5 to 12.5 V ■ Power consumption: < 150 mW

• Reverse polarity protection/short-circuit protection

• Current consumption: 10 to 13 mA

■ Separation voltage: 2.6 kV

Two-wire connection for separate switching unit / M12 plug

For connecting to Nivotester (see graphic) from Endress+Hauser.

Output signal jump of PFM signal from high to low frequency when sensor is covered. Switching between minimum/maximum safety on the Nivotes-

Additional function "self test":


After interruption of the power supply, a test cycle is activated which checks the sensor and electronics without any change in level.

For this purpose, the operating elements must be configured


as follows:



The test is activated at the switching unit. LEDs indicate the progress of the test.



With cable entry wired by customer (Ordering feature 80, options 2, 3, 4, 7)



With M12 plug wired at the factory (Ordering feature 80, option 1)

12

Output signal

= lit = flashes

= unlit

* See also "Operating elements", $\rightarrow \, \stackrel{\text{\tiny a}}{=} \, 25$

Safety mode	Level	Output signal (PFM)	LEDs green yellow red		
		150 Hz	- <u>`</u> Ċ <u>`</u> Ċ- ●		
		50 Hz	-\'\		
Maintenance required *		150 Hz	-\\(\frac{1}{2}\)-\(\frac{1}{2		
	<u></u>	© ⊿tå %	-\(\)-\(\)-\(\)-		
Instrument failu	ire L	0 Hz —————	-¤- • -¤-		

L00-FTM5xxxx-04-05-xx-en-009

Signal on alarm

Output signal on power failure or in the event of device failure: 0 Hz


Connectable load

- Floating relay contacts in connected switching unit Nivotester (see drawing above)
- For contact load, see the Technical Data of the switching unit

Installation


Installation instructions

Orientation FTM50



1 Protective cover (provided by the customer)

Orientation FTM51, FTM52



- 1 Sliding sleeve
 2 FTM51
 3 FTM52
 4 FTM51 with supporting tube (not included in the delivery)
 A Clearance
 B Maximum nozzle length: = L Sensor length 145 mm (5.71 in) for short fork
 = L Sensor length 200 mm (7.87 in) for standard fork

Environment

Ambient temperature range	−50 °C to +70 °C (-58 °F to +158 °F); With F16 housing: -40 °C to +70 °C (-40 °F to +158 °F)
Storage temperature	-50 °C to +85 °C (-58 °F to +185 °F)
Climate class	Climate protection as per DIN IEC 68, Part 2-38, Fig. 2a
Degree of protection	 Housing F15, F16, F17, separate housing: IP66/IP67, NEMA4X Housing F13, T13, F27: IP66/IP68, NEMA4X/6P
Vibration resistance	To EN 60068-2-64: 0.01 g ² /Hz
Shock resistance	To EN 60068-2-27: 30 g
Electrical safety	IEC 61010, CAN/CSA-C22.2 No. 61010-1-04 US standard UL 61010-1, 2 nd Edition
Electromagnetic compatibility	 Interference emission to EN 61326, Equipment Class B, Interference immunity to EN 61326; Annex A (Industrial) and NAMUR Recommendation NE21 (EMC).

Process


Medium temperature limits

Non-hazardous area and Ex d + DIP certificates

(Ex ia certificates see Seite 30, "Certificates")


NOTICE

Permitted ambient temperature $T_{\rm a}$ at housing depending on the process temperature $T_{\rm p}$ in the



- Restriction to $-40~^{\circ}\mathrm{C}$ with F16 housing
- $Additional\ temperature\ range\ for\ sensors\ (FTM50,\ FTM51)\ with\ temperature\ spacer$

High temperature (only FTM50, FTM51)



- Restriction to $-40\,^{\circ}\mathrm{C}$ with F16 housing Additionally utilizable temperature range when using the temperature spacer outside the insulation "1"
- *** Antistick coating possible up to max. 230 $^{\circ}\mathrm{C}$

Thermal shock resistance

- Maximum 120 K
- At high temperature 260 K

Limiting medium pressure range

-1 to 25 bar (362.5 psi)

Maximum Working Pressure (MWP)

■ FTM50/51: 25 bar (362.5 psi)

■ FTM52: 2 bar (29 psi) (6 bar (87 psi) for Ex d, Ex de and FM/CSA XP)

The specified range may be reduced by the selected process connection.

The pressure rating (PN) specified on the flanges refers to a reference temperature of 20 $^{\circ}$ C (68 $^{\circ}$ F), for ASME flanges to 100 $^{\circ}$ F. Observe pressure-temperature dependency.

The pressure values permitted at higher temperatures can be found in the following standards:

■ EN 1092-1: 2001 Tab.18

With regard to their stability-temperature property, the materials 1.4404 and 1.4435 are grouped together under 13E0 in EN 1092-1, Tab. 18. The chemical composition of the two materials can be identical.

- ASME B 16.5a 1998 Tab. 2-2.2 F316
- ASME B 16.5a 1998 Tab. 2.3.8 N10276
- JIS B 2220

Burst pressure

FTM50/51: 100 bar (1450 psi)

State of aggregation

Solids

Grain size

 $\leq 10 \text{ mm } (0.39 \text{ in})$

Bulk weight


Depends on the density setting on the electronic insert:

- Standard fork: ≥ 10 or 50 g/l (for light media)
- Short fork: ≥ 50 or 200 g/l

(for confined installation conditions, high lateral load or increased buildup)

Lateral load (static)

The following graphic shows the maximum permitted lateral load F in N (lbf) in relation to the length L in mm (in).



A Short fork, sensor Ø36 mm (1.42 in), \rightarrow \triangle 19

- B Short fork, sensor Ø43 mm (1.69 in), $\rightarrow \boxed{2}$ 19;
- C Standard fork, sensor \emptyset 43 mm (1.69 in), $\rightarrow \triangle$ 19.

Tensile strength rope FTM52

3000 N (lbf)


Mechanical construction

Housing and process connection

Polyester housing F16


Process connection:

- R 1½
- 1½ NPT
- 1¼ NPT



Stainless steel housing F15

Process connection: Tri-Clamp



* Cover with glass insert

Aluminum housing F17

Process connection: Flange

max.60 (2.36) max.65 (2.56) ø 80 (3.15) MAD., DAN 19* (4.69*) 22,5 (0.9) mm (in) L00-FTM5xxxx-06-05-xx-xx-050

* Cover with glass insert

Aluminum housing F13 (Ex d)

(Adaption to sensor threaded.)


Process connection

- Flange
- R1½
- 1½ NPT ■ 1¼ NPT
- Stainless steel housing F27 (Ex d)

(Adaption to sensor threaded.)

Process connection

- Flange
- R1½
- 1½ NPT
- 1¼ NPT
- Cover with glass insert (only for aluminum housing F13)
- ** For Tri-Clamp 36 mm (1.42 in)



Aluminum housing T13 (Ex de)


With separate connection compart-

Process connection

- R1½
- 1½ NPT
- 1¼ NPT

With Ex d(e) for FTM51 and FTM52: for flange and thread dimensions see the previous graphic

- R 1½
- 1½ NPT
- 1¼ NPT
- Cover with glass insert
- ** For Tri-Clamp 16 mm (0.63 in)




L00-FTM5xxxx-06-05-xx-xx-052


Dimensions

Compact version FTM50

Dimensions: mm (in)



Rope version FTM52




L00-FTM5xxxx-06-05-xx-xx-015

Process connection:	GJ, GG, A#, B#, K#, TD	GK, GX
ø D1 (mm [in])	43 (1.69)	36 (1.42)
ø D2 (mm [in])	37 (1.46)	37 (1.46)

Versions with extensions

FMI51 (pipe): Dimensions depend on process connection and selected pipe extension **FTM52 (rope):** Dimensions depend on process connection and selected rope extension




L = Length (from lower edge of thread), X = fork length

For further information on the overall length and fork length see "Measuring range (detection range)", $\rightarrow \stackrel{\triangle}{=} 4$. Diameter of pipe extension FTM51: see dimensions of FTM50, $\rightarrow \stackrel{\triangle}{=} 19$.


Versions with temperature spacer

Length and version depend on temperature and certificate:



mm (in)	150 °C	(302 °F)	230 °C (446 °F)	280 °C (536 °F)
L: for housing F15, F16, F17	145 (5.71)		175 (6.89)	215 (8.46)
L: for housing F13, F27, T13	145 (5.71)	165 (6.5)	165 (6.5)	205 (8.07)
Certificate	A, 1, 2, 3, 4, 7, 8, C, D, F, X	5, 6, H, Z	Not relevant	Not relevant


Surface refinement



Version with separate housing

Applications:

For high ambient temperatures and applications with confined installation locations (e.g. filling nozzle applications). The cable between the separate housing and sensor can be shortened at the customer's.




A: Zone 1, Zone 21; B: Length max. 6 m (20 ft); C: Zone 0, Zone 20

	T _{a1}	T _{a2}	T_p
FTM50/51	70 °C (158 °F)	120 °C (248 °F)	Versions: 150 °C (302 °F), 230 °C (446 °F), 280 °C (536 °F)
FTM52	70 °C (158 °F)	80 °C (176 °F)	80 °C (176 °F)

Housing extension heights for wall and pipe mounting

The wall holder unit forms part of the scope of supply for device versions with a separate housing.



- 1) Cover with glass insert;
 2) With optional temperature spacer up to 150 °C (302 °F) → 108 + 145 = 253 mm (4.25 + 5.71 = 9.96 in)
 With high-temperature version 230 °C (446 °F) → 108 + 175 = 283 mm (4.25 + 6.89 = 11.1 in)
 With high-temperature version 280 °C (536 °F) → 108 + 215 = 323 mm (4.25 + 8.46 = 12.7 in)
- **3)** The bending radius is $r \ge 100$ mm (3.94 in); with armored tube $r \ge 75$ mm (2.95 in)

Dimen-	Housing				
sions mm (in)	Polyester (F16)	Stainless steel (F15)	Aluminum (F17)	Aluminum (F13) Stainless steel (F27)	Aluminum (T13) Separate connection compartment
В	76 (2.99)	64 (2.52)	65 (2.56)	65 (2.56)	97 (3.82)
Н1	155 (6.1)	166 (6.54)	160 (6.3)	243 (9.57)	260 (10.2)
H2		185 (7.28)	174 (6.85)	258 (10.2)	273 (10.7)
Н3	41 (1.61)		62 (2.44)	•	

Weights

Depends on type; see last column on "Additional weight" in the ordering information

Materials and surfaces

Material specifications as per AISI and DIN-EN.

Surface roughness

NOTICE

- ▶ In the area of the welding seams, the roughness is not defined due to the production process.
- ▶ In the area of the fork base a deviation of the surface roughness can occur.

Electropolished for simple cleaning and to avoid build-up and corrosion. Choice of surface roughness (version => type): Ra < $0.76 \mu m$

Parts in contact with process

- Process connection and extension pipe: 316L (1.4404, 1.4435)
- Tuning fork: 316L (1.4404, 1.4435)
- Flanges: 316L (1.4435 or 1.4404)
- PTFE coating: prevents buildup, FDA compliant
- ETFE coating: prevents corrosion
- FTM52: PUR/silicone for rope insulation, PBT

Parts with no process contact

- Seal between process connection/housing: EPDM
- Ground terminals outside on housing: 304 (1.4301), 316L (1.4404)
- Polyester housing F16: PBT-FR with PBT-FR cover or with PA12 transparent cover,
 - Cover seal: EPDM
 - Nameplate glued: polyester film (PET)
 - Pressure compensation filter: PBT-GF20
- Stainless steel housing F15: 316L (1.4404)
 - Cover seal: silicone/PTFE
 - Safety claw: 316L (1.4404)
 - Pressure compensation filter: PA, VMQ/VA
 - Nameplate labeling directly on the device
- Aluminum housing F17/F13: EN-AC-AlSi10Mg, plastic-coated,
 - Cover seal: EPDM
 - Safety claw: nickel-plated brass
 - Pressure compensation filter (only F17): silicone
 - Nameplate: 304 (1.4301)
- Stainless steel housing F27: 316L (1.4435)
 - Cover seal: FVMQ (optional: EPDM seal available as spare part)
 - Safety claw: 316L (1.4435)
 - Nameplate: 316L (1.4404)
- Aluminum housing T13: EN-AC-AlSi10Mg, plastic-coated,
 - Cover seal: EPDM
 - Safety claw: nickel-plated brass
 - Nameplate: 304 (1.4301)
- Cable gland versions:
 - Polyamide (PA)
 - Nickel-plated brass
 - 316L (1.4435)
 - M12 connector (nickel-plated brass)

Operability


Display elements

NOTICE

The switch settings in the following graphics are in the as-delivered state.

FEM51


- Green LED lit: Indicates operational status
- Yellow LED lit: Indicates switching status
- Red LED
 - flashing: flashes alternately with green LED if maintenance is required
 - lit: indicates device failure



L00-FTM5xxxx-03-05-xx-xx-001

FEM52


- Green LED lit: Indicates operational status
- Yellow LED lit: Indicates switching status
- Red LED
 - flashing: indicates maintenance is required
 - lit: indicates device failure



L00-FTM5xxxx-03-05-xx-xx-002


FEM54

- Green LED lit: Indicates operational status
- Yellow LED lit: Indicates switching status
- Red LED
 - flashing: indicates maintenance is required
 - lit: indicates device failure



FEM55

- Green LED lit: Indicates operational status
- Yellow LED lit: Indicates switching status
- Red LED
 - flashing: indicates maintenance is required
 - lit: indicates device failure




L00-FTM5xxxx-03-05-xx-xx-005

24

FEM57


- Green LED lit: Indicates operational status
- Yellow LED lit: Indicates covered status
- Red LED
 - flashing: indicates maintenance is required
 - lit: indicates device failure



L00-FTM5xxxx-03-05-xx-xx-007

FEM58

- Green LED flashing: Indicates operational status
- Yellow LED lit: Indicates switching status
- Red LED
 - flashing: flashes alternately with green LED if maintenance is required
 - flashing: indicates device failure



.00-FTM5xxxx-03-05-xx-xx-008

NOTICE

If the test key is pressed this breaks the cable connection.

Operating elements of FEM51, FEM52, FEM54, FEM55, FEM58

Factory setting:




L00-FTM5xxxx-19-05-xx-xx-001

	Switch for safety mode						
	MAX	Overfill prevention					
	MIN	Dry running protection					
	Switch for switching delay						
⊿t	Н	0.5 s when covered 150 °C (302 °F): 1.5 s when uncovered (short fork 1 s) 230/280 °C (446/536 °F): 2 s when uncovered (short fork 1 s)					
	ш	5 s when covered, 5 s when uncovered					
	Switch for bulk weight/density setting						
A.	•	50 g/l standard fork, 200 g/l short fork (high bulk weight)					
	•	10 g/l standard fork, 50 g/l short fork (low bulk weight)					
Ŷ₁	Switch for diagnosis						
	OFF	Diagnosis of abrasion and buildup switched OFF					
	ON	Diagnosis of abrasion and buildup switched ON					
		 For additional density setting to high bulk density: abrasion and build-up are indicated per LED at the electronic insert only For additional density setting to low bulk density: output of "signal on alarm" for abrasion and build-up 					

Operating elements of FEM57

Factory setting:



L00-FTM5xxxx-19-05-xx-xx-002

(I)	Switch for switching the self-test on or off					
	OFF	Self-test switched off				
	ON	At the same time, switching delay 0.5 s when covered, density setting for low bulk weight and diagnostics on (see also Seite 12): Self-test performed when voltage returns.				
⊿t	Switch for switching delay					
	Н	0.5 s when covered 150 °C (302 °F): 1.5 s when uncovered (short fork 1 s) 230/280 °C (446/536 °F): 2 s when uncovered (short fork 1 s)				
	-	5 s when covered, 5 s when uncovered				
A	One switch for bulk weight/density setting					
	•	Standard fork: 50 g/l Short fork: 200 g/l (high bulk weight)				
	•	Standard fork: 10 g/l (low bulk weight) Short fork: 50 g/l				
Ÿ₁	One switch for diagnosis					
	OFF	Diagnosis of abrasion and buildup switched OFF				
	ON	Diagnosis of abrasion and buildup switched ON				
	 For additional density setting to high bulk density: abrasion and build-up are indicated per LED at the electronic insert only For additional density setting to low bulk density: output of "signal on alarm" for abrasion and build-up 					


Sediment detection with FTM50 and FTM51

Detection of solids under water

Only sediment is detected.

Water-like liquids or entrained substances are not detected.

The standard version of FTM52 is not suitable for immersion due to the IP67 rope seal! Version with IP68 available on request.



Certificates and approvals

CE mark

The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied. Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

Ex approval

FEM51, FEM52, FEM54, FEM55:

- Explosion protection for potentially explosive gas/air mixtures:
 Ex d, Ex de, XP, intrinsically safe sensor circuit Ex ia, IS
- Explosion protection for potentially explosive dust/air mixtures:
 Dust ignition-proof as per EN 50281-1-1, DIP as per EN 61241-0

FEM57, FEM58:

- Explosion protection for potentially explosive gas/air mixtures:
 Ex ia, IS (intrinsically safe power supply + intrinsically safe sensor circuit)
- Explosion protection for potentially explosive dust/air mixtures:
 Ex ia D, IS (intrinsically safe power supply + intrinsically safe sensor circuit)

See "Ordering information", $\rightarrow \stackrel{\triangle}{=} 29$ and "Documentation", $\rightarrow \stackrel{\triangle}{=} 30$.

Your Endress+Hauser distributor will supply you with information about hazardous area versions that are currently available.

All explosion protection data are given in a separate documentation (see "Documentation") which is available upon request. Copies of certificates available upon request.

	F16 housing	F15 housing	F17 housing	F13 / F27 housing	T13 housing with separate connection compartment	Separate housing
Dust ignition-proof	X (except II 1/2 D)	X	X	X	X	X
Ex ia	Х	Х	Х	Х	Х	Х
Ex nA/nL/nC	Х	Х	Х	Х	Х	Х
Ex d	_	_	-	Х	Х	Х
Ex de	-	-	-	-	Х	Х
IP66/67	X	Х	Х	-	-	Х
IP66/68	-	-	-	Х	Х	-
Recommended in event of severe external vibrations	-	-	_	X	X	X
Goretex filter	Х	Х	X	-	-	-

Other standards and guidelines

Other standards and guidelines that were taken into consideration in designing and developing Soliphant M FTM50, FTM51, FTM52:

- Low Voltage Directive (73/23/EEC)
- DIN EN 61010 Part 1, 2001

Protection Measures for Electrical Equipment for Measurement, Control, Regulation and Laboratory Procedures

Part 1: General requirements

■ EN 61326

Electrical Equipment for Measurement, Control and Laboratory Use EMC requirements

RCM-Tick marking

The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products are labelled with the RCM- Tick marking on the name plate.



A0029561

Pressure Equipment Directive 2014/68/EU (PED)

Pressure instruments with permitted pressure ≤ 200 bar (2 900 psi)

Pressure instruments with permitted pressure ≤ 200 bar (2 900 psi) Pressure instruments with a flange and threaded boss that do not have a pressure-bearing housing do not fall within the scope of the Pressure Equipment Directive, irrespective of the maximum permitted pressure.

Reason:

According to Article 2, point 5 of EU Directive 2014/68/EU, pressure accessories are defined as "devices with an operational function and having pressure-bearing housings".

If a pressure instrument does not have a pressure-bearing housing (no identifiable pressure chamber of its own), there is no pressure accessory present within the meaning of the Directive.

CRN approval

CRN-approved devices are fitted with a separate plate bearing the registration number No.: 0F10907:5C ADD1.

EAC conformity

The measuring system meets the legal requirements of the applicable EAC guidelines. These are listed in the corresponding EAC Declaration of Conformity together with the standards applied. Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.

RoHS

The measuring system complies with the substance restrictions of the EU Directive on the restriction of the use of certain hazardous substances 2011/65/EU (RoHS 2).

ASME B 31.3

Design and materials in accordance with ASME B31.3. The welding seams are through-penetration welded and comply with ASME Boiler and Pressure Vessel Code Section IX and EN ISO 15614-1.

Process sealing as per ANSI/ ISA 12.27.01

North American practice for the installation of process seals.

Soliphant M instruments are designed by Endress+Hauser according to ANSI/ISA 12.27.01 as single seal devices with annunciation, allowing the user to waive the use and save the cost of installing external secondary process seals in the conduit as required by the process sealing sections of ANSI/NFPA 70 (NEC) and CSA 22.1 (CEC). The instruments comply with the North American installation practice and provide a very safe and cost-saving installation for pressurized applications with hazardous fluids. Please refer to the Safety Instructions (XA) of the relevant device for further information $\rightarrow \square$ 30ff.

Product	Туре	Maximum process pres-	Marking	Approval
		sure		
Soliphant M	FTM50-D/F/H##	25 bar (362.5 psi)	Single Seal	FM, CSA
	FTM51-D/F/H##	25 bar (362.5 psi)	Single Seal	FM, CSA
	FTM52-D/F/H##	2 bar (29 psi)	Single Seal	FM, CSA

Other certificates

- Material certificate as per EN 10204/3.1 for all wetted parts,
- AD2000 on request
- TSE Certificate of Suitability

The following applies to wetted device components:

- They do not contain any materials derived from animals.
- No additives or operating materials derived from animals are used in production or processing.

Functional safety (SIL validation)

Use in safety systems requiring functional safety to SIL2 in accordance with IEC 61508. See "Documentation", $\rightarrow \stackrel{\triangle}{=} 30$.

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Click "Corporate" -> Select country → Click "Products"→ Select product using the filters and search field → Open product page → The "Configuration" button to the right of the product image opens the Product Configurator.
- Endress+Hauser Sales Center: www.addresses.endress.com

NOTICE

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Accessories

Removing tool


For Soliphant M FTM50, FTM51, FTM52.

Order No.: 71026213

Weather protection cover

For Soliphant M FTM50, FTM51, FTM52 with F13, F17 and F27 housing.

Order No.: 71040497



L00-FTM5xxxx-03-05-xx-xx-009

Sliding sleeve

Only for Soliphant M FTM51 with pipe diameter d=43 mm (1,69 in), see ordering information, ordering feature "Process connection", options GG, GJ and ordering feature "Material", options A, 2, 5.

For pressurized containers up to 5 bar (362.5 psi).

Sliding sleeve version:

■ G2

DIN ISO 228/I

Order No.: 52024631


2NPT

ANSI B 1.20.1

Order No.: 52024630

NOTICE


Suitable for switch point configuration!



- G2 (316L) 2NPT (316L) В
- For G2: 24 mm (0.94 in); for 2NPT: 27.5 mm (1.08 in)
- MWP = 25 bar (362.5 psi) $T_p = max. 280 \text{ °C } (536 \text{ °F})$

Rope shortening kit

Only for Soliphant M FTM52. Order No.: 52024632



Documentation

NOTICE

You can find the following supplementary documentation on our product pages at www.endress.com.

Operating Instructions

- Soliphant M FTM50, FTM51 KA00229F Soliphant M FTM52 KA00230F • Soliphant M FTM51, sliding sleeve, pressurized: KA00239F
- Soliphant M FTM52, rope shortening KA00231F
- Soliphant M FTM50, FTM51, FTM52
 - Separate housing; installation and shortening instructions KA00264F (housing side)
 - Separate housing and armored tube; installation and shortening instructions (housing side)
 - Separate housing; removing and installing the sensor

KA00265F KA00273F

Certificates

ATEX

1D, 1/2D, 1G, 1/2G XA00305F ATEX II Ex i ATEX II Ex i (X) 1D, 1G XA00319F

	ATEX II	Ex d/Ex de	1D, 1/2D Ex t, 1/2G	XA00306F
	ATEX II	Ext	1/2D, 1/3D	XA00307F
	ATEX II	Ex t, Ex n	3D, 3G	XA00331F
	NEPSI			
	NEPSI	Ex t		XA00393F
	NEPSI	Ex ia		XA00393F
	NEPSI	Ex d, Ex t		XA00395F
	IECEx			
	IECEx	Ex ia		XA00391F
	IECEx	Ex t		XA00392F
	■ IECEx	Ex d, Ex de, Ex t		XA00633F
	INMETRO			
	■ INMETRO	Ex t		XA01336F
	■ INMETRO	Ex d, Ex de, Ex t		XA01354F
	EAC	, ,		
	■ EAC	Ex d, Ex t	Ga/Gb, Da/Db	XA01590F
		211 0, 211 0	Ga. 65, 2 a. 25	10 10 10 10 10 10 10 10 10 10 10 10 10 1
	FM	IC NII		VA01227E
	■ FM	IS, NI		XA01337F
	CSA			
	■ CSA	IS, NI		XA01248F
	■ CSA	XP, DIP		XA01042F
Functional safety	■ Soliphant M	SD00203F		
i unctional safety	 Soliphant N 	SD00203F SD00204F		
	 Soliphant N 	SD002041 SD00205F		
	 Soliphant N 	SD00203F SD00208F		
	 Soliphant N 	SD00200F SD00207F		
	Soliphant N	SD002071 SD00206F		
	Soliphanen	2202001		



www.addresses.endress.com

