# Safety Instructions Micropilot S FMR532

4-20 mA HART

Ga/Gb Ex ia IIC T6...T4 X 1Ex ia IIC T6...T3 Gb X



Document: XA01407F-A

Safety instructions for electrical apparatus for explosion-hazardous areas  $\rightarrow \square 3$ 



Micropilot S FMR532 XA01407F-A

# Micropilot S FMR532

# 4-20 mA HART

# Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Extended order code	4
Safety instructions: General	5
Safety instructions: Special conditions	5
Safety instructions: Installation	6
Safety instructions: Zone 0	7
Temperature tables	8
Connection data	8

XA01407F-A Micropilot S FMR532

#### Associated documentation

This document is an integral part of the following Operating Instructions:

BA00208F/00

# Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z
- On the CD for devices with CD-based documentation

#### Manufacturer's certificates

#### Certificate of Conformity TP TC 012/2011

Inspection authority:

LLC NANIO CCVE (OOO «HAHIO LCBЭ»)

Certificate number:

EA9C RU C-DE.AA87.B.00370/20

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- GOST 31610.0-2014 (IEC 60079-0:2011)
- GOST 31610.11-2014 (IEC 60079-11:2011)
- GOST 31610.26-2012/IEC 60079-26:2006

#### Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

#### Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

# Structure of the extended order code

FMR532 - \*\*\*\*\*\*\*\*\* + A\*B\*C\*D\*E\*F\*G\*.. (Device type) (Basic specifications) (Optional specifications)

#### \* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

#### Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

#### Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

Micropilot S FMR532 XA01407F-A

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

#### Extended order code: Micropilot S



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

#### Device type

FMR532

Basic specifications

Position 1 (Approval)				
Selected option		Description		
FMR532	Q	EAC Ga/Gb Ex ia IIC T6T4 X, 1Ex ia IIC T6T3 Gb X		

#### Optional specifications

No options specific to hazardous locations are available.

#### Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates, ..)
  - Of isolated capacities (e.g. isolated metallic plates)
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the electronics housing, depending on the range of application and the temperature class.

#### Safety instructions: Special conditions


Permitted ambient temperature range at the electronics housing:

 $-40~^{\circ}\text{C} \le T_a \le +80~^{\circ}\text{C}$ 

- Observe the information in the temperature tables.
- In the event of additional or alternative special varnishing on the housing or other metal parts:
  - Observe the danger of electrostatic charging and discharge.
  - Do not rub surfaces with a dry cloth.
- Avoid electrostatic charging of the antenna (e.g. friction, cleaning, maintenance, strong medium flow).

XA01407F-A Micropilot S FMR532

#### Safety instructions: Installation



- 1 Tank; Hazardous area Zone 0
- 2
- 3 Certified associated apparatus (supply circuit)
- 4 Certified associated apparatus (signal circuit)
- Tank; Hazardous area Zone 1
- Local potential equalization
- After aligning (rotating) the housing, retighten the fixing screw.
- Continuous service temperature of the connecting cable:  $\geq T_a + 5$  K.
- The intrinsically safe input and output power circuits of the device are isolated from ground. The dielectric strength to earth is limited by 600 V electrode arresters.
- The device is equipped with an internal overvoltage protector (600 V electrode arresters). Connect the metallic housing to the tank wall directly with an electrically conductive lead to ensure reliable potential matching.
- Option:
  - Remote display, e.g. FHX40 (Observe Safety Instructions)
  - Overvoltage protector, e.g. HAW56x
- Option (only for service purposes):


Service interface: Commubox with associated ToF cable (Observe Safety Instructions)

#### Intrinsic safety

- When the device is connected to an intrinsically safe circuit Ex ib, the type of protection changes to Ex ib. Do not operate intrinsically safe circuits Ex ib in Zone 0.
- When the device is connected to an intrinsically safe circuit Ex ic, the type of protection changes to Ex ic. Do not operate intrinsically safe circuits Ex ic in Zone 0 or Zone 1.
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.

Micropilot S FMR532 XA01407F-A

#### Overvoltage protection



A0026444

#### **₽** 2

- 1 Tank; Hazardous area Zone 0
- 2 <1000 mm, e.g. armoured hose
- 3 Separate housing with overvoltage protector, e.g. HAW562Z; Metal housing
- 4 Cable with screening or metal sheath
- 5 Certified associated apparatus (supply circuit)
- 6 Certified associated apparatus (signal circuit)
- 7 Potential equalization connection
- 8 Potentiel equalization line
- 9 Potential equalization

If there is a risk of dangerous potential differences within Zone 0 (e.g. through the occurrence of atmospheric electricity), implement suitable measures for intrinsically safe circuits in Zone 0.

#### Overvoltage protector HAW56xZ

- Connect the external overvoltage protector and the device to the local potential equalization.
- Establish potential matching both inside and outside of the explosion-hazardous area.
- The cable connecting the overvoltage protector and the measuring device shall be no longer than 1 m.
- Route cable protected (e.g. in an armoured hose).
- For notes on screening and installation with associated apparatus (Tank Side Monitor NRF590) see associated Operating Instructions.

#### Safety instructions: Zone 0

- In the event of potentially explosive vapor/air mixtures, only operate the device under atmospheric conditions.
  - Temperature: -20 to +60 °C
  - Pressure: 80 to 110 kPa (0.8 to 1.1 bar)
  - Air with normal oxygen content, usually 21 % (V/V)
- If no potentially explosive mixtures are present, or if additional protective measures have been taken, the device may also be operated under non-atmospheric conditions in accordance with the manufacturer's specifications.
- Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred.

XA01407F-A Micropilot S FMR532

## Temperature tables

## Zone 1 - Application

Temperature class	Max. permitted temperature at the antenna (Zone 1)	Max. permitted temperature at the electronics housing (Zone 1) dependent on the medium temperature
Т6	+80 °C +60 °C	+50 °C +55 °C
T5	+95 °C +70 °C	+65 °C +70 °C
T4	+130 °C +80 °C	+70 °C +80 °C
Т3	+150 ℃	+70 °C

# Zone 0 - Application

Temperature class	Max. permitted temperature at the antenna (Zone 0)	Max. permitted temperature at the electronics housing (Zone 1) dependent on the medium temperature
Т6	+60 °C	+55 °C
T5	+60 °C	+65 ℃
T4	+60 °C	+80 °C

#### **Connection data**

Power supply and signal circuit with protection type: intrinsic safety Ex ia IIC, Ex ia IIB. Certified intrinsically safe circuit with the following maximum values

Power supply	
Power circuit	$\begin{split} &U_i = 30 \text{ V} \\ &I_i = 300 \text{ mA} \\ &P_i = 1 \text{ W} \end{split}$
	$\begin{split} L_i &= 13.0 \; \mu H \\ C_i &= 18.5 \; n F \end{split}$
Signal circuit	$\begin{split} &U_i=30~V\\ &I_i=300~mA\\ &P_i=1~W\\ &\text{effective inner inductance}~L_i=0\\ &\text{effective inner capacitance}~C_i=20.7~nF \end{split}$

# Option

Remote display, e.g. FHX40:

Power supply and signal circuit with protection type: intrinsic safety  $\mbox{\rm Ex}$  ia IIC,  $\mbox{\rm Ex}$  ia IIB.

Power supply
$U_0 = 5.4 \text{ V}$ $I_0 = 44 \text{ mA}$ $P_0 = 59.4 \text{ mW}$
effective inner inductance $L_i$ = negligible effective inner capacitance $C_i$ = negligible Characteristic curve: linear

Micropilot S FMR532 XA01407F-A

## Only for service purposes:

Connecting the Commubox service interface with the associated ToF cable  $\,$ 

#### Commubox output + ToF cable

 $U_0 = 3.74 \text{ V}$ 

 $I_0 = 9.9 \text{ mA}$   $P_0 = 9.2 \text{ mW}$ 

effective inner inductance  $L_i = \mbox{negligible}$  effective inner capacitance  $C_i = \mbox{negligible}$ Characteristic curve: linear

For material group IIC:

■ permitted outer inductance  $L_o \le 340 \text{ mH}$ ■ permitted outer capacitance  $C_o \le 100 \text{ µF}$ 

When interconnected to a Micropilot S, the following results apply:

	L <sub>o</sub> =	0.15 mH	0.5 mH	1 mH	2 mH	5 mH
For material group IIC	C <sub>o</sub> =	≤ 5.0 µF	≤ 3.5 µF	≤ 3.0 µF	≤ 2.6 µF	≤ 2.0 µF
For material group IIB	C <sub>o</sub> =	10 μF				





www.addresses.endress.com