Technical Information **Prosonic S FDU95**

Ultrasonic measuring technology



Ultrasonic sensor for level and flow measurement

Application

- Continuous, non-contact level measurement of liquids and bulk solids in silos, on conveyor belts, in material stockpiles and in crushers
- Flow measurement in open flumes and measuring weirs
- Maximum measuring range: 45 m (148 ft)in bulk solids

Your benefits

- Integrated temperature sensor for time-of-flight correction, enabling accurate measurements even if temperatures change
- Hermetically welded PVDF sensor for maximum chemical resistance
- Suitable for harsh ambient conditions thanks to separate transmitter installation (up to 300 m (984 ft))
- Self-cleaning effect ensures minimum deposit build-up
- Weather resistant and flood-proof (IP68)
- International Dust-Ex and Gas-Ex certificates available

Table of contents

Important document information 3 Document conventions 3	
Function and system design	
Blocking distance	
Power supply6Supply voltage6Electrical connection6Connection diagram for sensor \rightarrow FMU907Connection diagram for sensor \rightarrow FMU957Extension cable specifications8Shortening the sensor cable8	
Installation8Installation conditions for level measurement8Installation conditions for flow measurement9Installation options (examples)10Nozzle mounting10Securing the sensor11	
Environment11Degree of protection11Vibration resistance11Storage temperature11Thermal shock resistance11Electromagnetic compatibility11	
Process11Process temperature11Process pressure11	
Mechanical construction12Dimensions12Weight12Materials12Materials of connecting cable12	
Certificates and approvals12CE mark12ROHS12RCM-Tick marking12Ex approval13Other standards and guidelines13	
Ordering information13Ordering information135-point linearity protocol13Scope of delivery14	

Accessories	14
Sensor extension cable	14
Screw-in flange FAX50	14
FAU40 alignment unit	15
P66 protective housing for RNB130 power supply unit	15
Supplementary documentation	16
Documentation for FMU90 transmitter	16
Oocumentation for FMU95 transmitter	16
Other documentation	16

Important document information

Document conventions

Safety symbols

⚠ DANGER
This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.

WARNING

This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in serious or fatal injury.

This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in minor or medium injury.

NOTICE

This symbol contains information on procedures and other facts which do not result in personal injury.

Electrical symbols



Ground connection

A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.

Tool symbols

Ø8

Open-ended wrench

Symbols for certain types of information and graphics

Procedures, processes or actions that are permitted

K Forbidden

Procedures, processes or actions that are forbidden

Indicates additional information

Reference to documentation

1., 2., 3.

Series of steps

1, 2, 3, ...


Item numbers

A, B, C, ...

Views

Function and system design

Level measurement



A0034882


- 1 Prosonic S sensor
- 2 Prosonic S transmitter
- BD Blocking distance
- D Distance between reference point (sensor membrane) and surface of medium
- E Empty distance
- F Span
- L Level

The sensor transmits ultrasonic pulses in the direction of the surface of the medium. There, they are reflected back and received by the sensor. The transmitter measures the time t between the transmission and reception of a pulse. From this time, and using the sonic velocity c, the transmitter calculates the distance D between the reference point (sensor membrane) and the surface of the medium:

 $D = c \cdot t/2$

The level L is derived from D. With linearization, the volume V or the mass M is derived from L.

Flow measurement in flumes or weirs



A0035219

- 1 Prosonic S sensor
- 2 Prosonic S transmitter
- D Distance between sensor membrane and surface of liquid
- Q Flow

The sensor transmits ultrasonic pulses in the direction of the surface of the liquid. There, they are reflected back and received by the sensor. The transmitter measures the time t between the transmission and reception of a pulse. From this time, and using the sonic velocity c, the transmitter calculates the distance D between the (reference point) sensor membrane and the surface of the liquid:

 $D = c \times t/2$

The level L is derived from D. With linearization, the flow Q is derived from L.


Temperature-dependent time-of-flight correction

Temperature-dependent time-of-flight correction via the temperature sensors integrated in the ultrasonic sensors.

Input

Blocking distance

Signals within the blocking distance (BD) range cannot be measured due to the transient response of the sensor.



A003979

- 1 Blocking distance of the ultrasonic sensor. Engineering unit m (ft)
- Reference point (sensor membrane) of measurement

Measuring range

Estimation of the effective sensor range depending on the operating conditions

- 1. Add up all the applicable attenuation values from the following lists.
- 2. From the total calculated attenuation, use the range chart below to calculate the range of the sensor

Attenuation caused by surface of liquid

- Calm surface: 0 dB
- Waves on surface: 5 to 10 dB
- Very turbulent surface: 10 to 20 dB
- Frothy surface: contact Endress+Hauser: http://www.endress.com/contact

Attenuation due to bulk solids surface

- Hard, rough surface (e.g. rubble): 40 dB
- Soft surface (e.g. peat, dust-covered clinker): 40 to 60 dB

Attenuation due to dust


- No dust formation: 0 dB
- Minor dust formation: 5 dB
- Major dust formation: 5 to 20 dB

Attenuation caused by filling curtain in detection range

- No filling curtain: 0 dB
- Small volumes: 5 dB
- Large volumes: 5 to 20 dB

Attenuation caused by temperature difference between sensor and product surface

- Up to 20 °C (68 °F): 0 dB
- Up to 40 °C (104 °F): 5 to 10 dB
- Up to 80 °C (176 °F): 10 to 20 dB



₽ 2 Range chart for ultrasonic sensors

Total attenuation in dB Α

Range in m (ft)

Operating frequency

- FDU95-*1***: 17 kHz
- FDU95-*2***: 18 kHz

Power supply

Supply voltage

Is provided by the transmitter.

Electrical connection

General information

A CAUTION

Inadequate potential equalization can compromise electrical safety

Connect the yellow/green protective conductor (GNYE) of the sensor to local potential equalization after a maximum distance of 30 m (98 ft). This can be done in a terminal box, at the transmitter or in the cabinet.

Interference signals may cause malfunctions


Do not route the sensor cables parallel to high-voltage electric power lines or near frequency converters.

NOTICE

A damaged cable shield may cause malfunctions


- ► For pre-terminated cables: connect the black wire (shield) to the "BK" terminal.
- ► For extension cables: twist the shield and connect to the "BK" terminal.

Connection diagram for sensor → FMU90



- **№** 3 Connection diagram for sensor; YE: yellow, BK: black; RD: red; BU: blue; BN: brown; protective conductor GNYE: green/yellow
- Grounding at terminal box Α
- Grounding at transmitter FMU90 В
- 1 Shielding of sensor cable
- 2 Terminal box
- Shielding of extension cable

Connection diagram for sensor → FMU95



- € 4 Connection diagram for sensor; YE: yellow, BK: black; RD: red; BU: blue; BN: brown; protective conductor GNYE: green/yellow
- Grounding at terminal box Α
- Grounding at transmitter FMU95 В
- Shielding of sensor cable
- Terminal box
- Shielding of extension cable

Extension cable specifications

- Maximum total length (sensor cable + extension cable)
 300 m (984 ft)
- Number of wires

As per connection diagram

Shielding

One shielding braid for the YE wire and one for the RD wire (no foil shield)

Cross-section

0.75 to 2.5 mm² (18 to 14 AWG)

Resistance

Max. 8Ω per wire

Capacitance, wire to shield

Max. 60 nF

• Protective ground

May not be within the shielding.




Suitable extension cables are available from Endress+Hauser.

Shortening the sensor cable

The sensor cable can be shortened if necessary (see the Operating Instructions for the FMU90 or FMU95 transmitter).

Installation

Installation conditions for level measurement



■ 5 Installation conditions for level measurement

- 1 Recommended distance to the vessel wall: 1/6 of the vessel diameter D.
- 2 Do not mount in the center of the vessel.
- *Avoid measurements through the filling curtain.*
- 4 There must be no internal fixtures in the signal beam.
- 5 Symmetrical internal fixtures, in particular, negatively impact the measurement.
- For bulk solids: using the FAU40 alignment unit, align the sensor so that it is perpendicular to the surface of the product.
- BD Blocking distance

Emitting angle/beam

- α (typical) = 5°
- L (max) = 45 m (148 ft)
- r (max) = 1.96 m (6.4 ft)

8

Other conditions

- The lower edge of the sensor should be located inside the vessel
- The maximum level may not enter the blocking distance

Several sensors in one vessel


Sensors that are connected to a common FMU90 or FMU95 transmitter can be used in one vessel.

Installation conditions for flow measurement

Conditions


- \blacksquare Mount the sensor on the upstream side above the maximum upstream level H_{max} plus the blocking distance BD
- Position the sensor in the center of the channel or weir
- Align the sensor so that it is perpendicular to the surface of the water
- Observe the specified mounting distance (clearance) to the flume constriction or weir edge
 See the Operating Instructions for FMU90 / FMU95
- Protect the sensor against sun and precipitation using the weather protection cover

Example: Khafagi-Venturi flume



- Khafagi-Venturi flume
- *b*₀ Width of Khafagi-Venturi flume
- B Upstream side
- C Downstream side
- BD Blocking distance of the sensor
- *E Empty calibration (to be entered during commissioning)*
- H_{max} Maximum upstream level
- V Flow

Example: Triangular weir




Blocking distance of the sensor

Empty calibration (to be entered during commissioning)

 H_{max} Maximum upstream level


Installation options (examples)



№ 6 Installation in systems

- Α On U-rail or bracket
- With FAU40 alignment unit В
- With 1" sleeve welded to a grating

Nozzle mounting



A0039840

- D Nozzle diameter
- Nozzle length

Conditions at the nozzle

- Smooth interior, without edges or welds
- No burr on the inside of the nozzle end on the tank side
- Beveled nozzle end on tank side (ideally: 45°)

Maximum nozzle length


D = DN250/10" to DN300/12": $L_{max} = 630 \text{ mm}$ (24.8 in)

Securing the sensor

NOTICE

Risk of damage to the sensor

- $\,\blacktriangleright\,\,$ Do not use the sensor cable for suspension purposes.
- ▶ Do not damage the sensor membrane when installing.



 \blacksquare 7 Securing the ultrasonic sensor; mounted with counter nut

Environment


Degree of protection	Tested according to IP68/NEMA6P (24 h at 1.83 m (6 ft) under water)
Vibration resistance	DIN EN 600068-2-64; 20 to 2 000 Hz; 1 (m/s ²) ² /Hz; 3x100 min
Storage temperature	Identical to process temperature
Thermal shock resistance	Based on DIN EN 60068-2-14; test according to min./max. process temperature; 0.5 K/min; 1000 h
Electromagnetic compatibility	Electromagnetic compatibility in accordance with all the relevant requirements outlined in the EN 61326 series and NAMUR Recommendation EMC (NE 21). For details, refer to the Declaration of Conformity. With regard to interference emission, the devices meet the requirements of class A, and are only designed for use in an "industrial environment".

Process

	Process
Process temperature	■ FDU95-*1*** -40 to +80 °C (-40 to +176 °F) ■ FDU95-*2*** ■ Non-Ex: -40 to +150 °C (-40 to +302 °F) ■ Dust-Ex: -40 to +130 °C (-40 to +266 °F)
Process pressure	0.7 to 1.5 bar (10.15 to 22 psi)

Mechanical construction

Dimensions




■ 8 Dimensions. Unit of measurement mm (in)

Weight

Weight including cable 5 m (16 ft))

Approx. 4.5 kg (9.92 lb)

Materials



A0038709

9 Materials

- 1 Sensor housing: UP (unsaturated polyester resin)
- 2 Cable gland: CuZn nickel-plated
- 3 Pipe adapter: CuZn nickel-plated
- 4 O-ring: VMQ
- 5 Seal: VMQ
- 6 Screws: V2A
- 7 Nameplate: 304 (1.4301)
- 8 Sensor membrane: FDU95-*1***: 316L (1.4404) with PE coating; FDU95-*2***: 316L (1.4404)

Materials of connecting cable

VMQ

Certificates and approvals

CE mark	The measuring system meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
RoHS	The measuring system complies with the substance restrictions of the Restriction on Hazardous Substances Directive 2011/65/EU (RoHS 2).
RCM-Tick marking	The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well

as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products are labelled with the RCM- Tick marking on the name plate.



A002956

Ex approval

Available Ex approvals: see Product Configurator



Sensors with an Ex approval can be connected to the FMU90 transmitter without an Ex approval.

Other standards and guidelines

EN 60529

Degrees of protection provided by enclosures (IP code)

EN 61326 series

EMC product family standard for electrical equipment for measurement, control and laboratory use

MAMIIR

User association of automation technology in process industries

Ordering information

Ordering information

Detailed ordering information is available for your nearest sales organization www.addresses.endress.comor in the Product Configurator under www.endress.com

- 1. Click Corporate
- 2. Select the country
- 3. Click Products
- 4. Select the product using the filters and search field
- 5. Open the product page

The Configuration button to the right of the product image opens the Product Configurator.

i

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

5-point linearity protocol


Conditions for 5-point linearity protocol

- The 5-point linearity protocol applies for the entire measuring system, consisting of the sensor and transmitter. When ordering, specify the transmitter sensor input where the sensor is to be tested.
- The linearization test is conducted under the reference operating conditions of the transmitter.

Position of the linearization points

- The 5 points of the linearity protocol are evenly distributed over the span S.
- In order to define the span, values for **Empty calibration** (E) and **Full calibration** (F) must be specified when ordering.
- The specified values are only used to create the linearity protocol. Empty calibration and Full calibration are then reset to their factory settings.

Conditions for defining the span



■ 10 Variables to define the span

- *R* Reference point (sensor membrane)
- E "Empty calibration" (distance from sensor membrane to 0%-point)
- *F* "Full calibration" (distance from 0%-point to 100%-point)
- A Distance from sensor membrane to 100%-point
- $E \le 20000 \text{ mm}$ (787 in)
- F = 450 to 18000 mm (17.7 to 709 in)
- $A \ge 2000 \text{ mm} (78.7 \text{ in})$

Scope of delivery

- Ordered version of the sensor
- For certified versions: Safety Instructions (XAs)
- For sensors with Ex-certificate: process seal (VMQ)


Accessories

Sensor extension cable



- Maximum permissible total length (sensor cable + extension cable): 300 m (984 ft)
- The sensor cable and extension cable are the same type of cable.
- Cable type: LiYY 2x(0.75)D+1x0.75
- Material: PVC
- \blacksquare Ambient temperature:–40 to +105 °C (–40 to +221 °F)
- Order number: 71027743
- Cable type: Li2G2G 2x(0.75)D+1x0.75
- Material: silicone
- Ambient temperature:-40 to +150 °C (-40 to +302 °F)
- Order number: 71027745

Screw-in flange FAX50



A004426



- Mounting on the rear thread G1 or NPT1
- Available flange sizes: see Product Configurator
- Minimum nominal diameter: DN80 / NPS 3"


14

FAU40 alignment unit

Use

- To align an ultrasonic sensor with the bulk solids surface
- Swivel range: 15°
- Zone separation for explosion hazardous areas

Dimensions



■ 11 FAU40 alignment unit. Unit of measurement mm (in)

- 1 Cable gland M20x1.5 (if selected in the product structure)
- 2 Seal here
- 3 Two Allen screws for height adjustment (8 Nm (6 lbf ft) \pm 2 Nm (\pm 1.5 lbf ft))
- 4 Grounding screw
- 5 O-ring
- 7 Screw for lateral adjustment (18 Nm (13.5 lbf ft)±2 Nm (±1.5 lbf ft))
- 8 Mounting slots (on version with UNI flange)

Additional information



Technical Information TI00179F

IP66 protective housing for RNB130 power supply unit

■ Order number: 51002468

• Additional information: Technical Information TI00080R

Supplementary documentation

Documentation for FMU90 transmitter

- Technical Information TI00397F
- Operating Instructions:
- BA00288F (HART, level measurement)
- BA00289F (HART, flow measurement)
- BA00292F (Profibus DP, level measurement)
- BA00293F (Profibus DP, flow measurement)
- Description of Device Parameters: GP01151F

Documentation for FMU95 transmitter

- Technical Information TI00398F
- Operating Instructions: BA00344F
- Description of Device Parameters: GP01152F

Other documentation



Further information and the documentation currently available can be found on the Endress+Hauser- website: www.endress.com→ Downloads.



www.addresses.endress.com

