

### **IECEx Certificate** of Conformity

#### INTERNATIONAL ELECTROTECHNICAL COMMISSION **IEC Certification System for Explosive Atmospheres**

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.:

IECEx IBE 20.0030X

Page 1 of 3

Certificate history:

Status:

Current

Issue No: 0

Date of Issue:

2021-06-08

Applicant:

Endress + Hauser Wetzer GmbH & Co. KG

Obere Wank 1 87484 Nesselwang

Germany

Equipment:

NAMUR Switch Isolating Amplifier type RLN42-xx-2\*

Optional accessory:

Type of Protection:

intrinsic safety in combination with increased safety and sealed device

Marking:

[Ex ia Ga] IIC

[Ex ia Da] IIIC Ex ec nC [ia Ga] IIC T4 Gc -40 °C ≤ Tamb ≤ +60 °C

Approved for issue on behalf of the IECEx Certification Body:

Position:

Signature: (for printed version)

Date:

Alexander Henker

Deputy Head of department Certification Body

This certificate and schedule may only be reproduced in full.

This certificate is not transferable and remains the property of the issuing body.
 The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.

Certificate issued by:

IBExU Institut für Sicherheitstechnik GmbH Fuchsmühlenweg 7 09599 Freiberg Germany





## IECEx Certificate of Conformity

Certificate No.: IECEx IBE 20.0030X Page 2 of 3

Date of issue: 2021-06-08 Issue No: 0

Manufacturer: Endress + Hauser Wetzer GmbH & Co. KG

Obere Wank 1 87484 Nesselwang

Germany

Additional manufacturing locations:

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

#### STANDARDS:

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

IEC 60079-0:2017 Explosive atmospheres - Part 0: Equipment - General requirements

Edition:7.0

IEC 60079-11:2011 Explosive atmospheres - Part 11: Equipment protection by intrinsic safety "i"

Edition:6.0

Explosive atmospheres - Part 15: Equipment protection by type of protection "n"

**IEC 60079-15:2017** Edition:5.0

2017 Explosive atmospheres - Part 7: Equipment protection by increased safety "e"

**IEC 60079-7:2017** Edition:5.1

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

#### **TEST & ASSESSMENT REPORTS:**

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

DE/IBE/ExTR21.0024/00

**Quality Assessment Report:** 

DE/TUN/QAR06.0009/09



### IECEx Certificate of Conformity

Certificate No.: IECEx IBE 20.0030X Page 3 of 3

Date of issue: 2021-06-08 Issue No: 0

#### **EQUIPMENT:**

Equipment and systems covered by this Certificate are as follows:

The NAMUR Switch Isolating Amplifiers RLN42-xx-2\* are used for the intrin-sically safe and galvanically isolated operation of proximity switches with NAMUR behaviour or potential-free switches and resistance-connected switches. They are equipped with a wide voltage range supply. The equipment is provided for installation in zone 2 or in the safe area as associated apparatus. The intrinsically safe signal circuits may be routed into areas that require EPL Ga (Zone 0) or Da (Zone 20).

The voltage difference between input and output circuit or supply can be up to 375 V peak. The modules are equipped with a circuit for the detection of line faults.

#### SPECIFIC CONDITIONS OF USE: YES as shown below:

- The NAMUR Switch Isolating Amplifiers RLN42-xx-2\* have to be installed in a certified housing fulfilling the requirements of IEC 60079-7
  or another recognized type of protection. The housing has to maintain a degree of protection of at least IP54 according to IEC 60529 for
  operation in zone 2.
- Connecting and disconnecting of non-intrinsically safe circuits are not allowed in energized state of the NAMUR Switch Isolating Amplifier RLN42-xx-2\*
- The DIP switches may only be used when there is no explosive atmosphere present.

#### Annex:

Annex\_IBE20.0030\_00.pdf



# IECEx Certificate of Conformity - Annex



Certificate No: IECEx IBE 20.0030X Issue No: 0

Date of Issue: 2021-06-08 Page 1 of 1

#### **Technical data:**

Environmental data	
Ambient temperature range	-40 °C up to +60 °C
Degree of protection of the enclosure	≥ IP20

Elect	rical data		
1.	Power Supply (1.1 and 1.2)		
	rated voltage range	$U_N$	24 230 V DC or AC
	supply current	I <sub>N</sub>	< 42 mA (24 V DC); max. < 80 mA (20 V AC)
	power consumption	Pin	< 1.1 W
	maximum r.m.s. or d.c. voltage	U <sub>m</sub>	253 V
	galvanically separated up to a peak voltage	Up	375 V
2.	Intrinsically safe sensor circuit (4.1 and 4.3/5.1 and 5.3)		
	maximum output voltage	Uo	9.56 V
	maximum output current	lo	10.3 mA
	maximum output power	Po	25 mW
	characteristic		linear (928 Ω)
	internal capacitance, inductance	Ci;Li	negligible
3.	Relay output (2.1 2.3 / 3.1 3.3)		
	maximum switching voltage	Us	250 V AC (2 A) /
			120 V DC (0.2 A) /
			30 V DC (2 A)
	maximum switching power	Ps	500 VA

For circuits including inductances and capacitances the following has to be observed:

The values for Lo and Co, mentioned in this certificate are allowed for:

- distributed inductances and capacitances, e.g. as in a cable or
- if the total L<sub>i</sub> of the external circuit (excluding the cable) is < 1 % of the L<sub>O</sub> value or
- if the total Ci of the external circuit (excluding the cable) is < 1 % of the Co value.

	Ex ia IIC	Ex ia IIB/IIIC	Ex ia IIA, Ex ia I
Co	3.6 µF	26 µF	210 µF
Lo	300 mH	1000 mH	1000 mH

The values of L<sub>0</sub> and C<sub>0</sub>, mentioned in this certificate shall be reduced to 50 % or taken from the following table if both of the following conditions are met:

- the total Li of the external circuit (excluding the cable) is ≥ 1 % of the Lo value and
- the total Ci of the external circuit (excluding the cable) is ≥ 1 % of the Co value.

	Ex ia IIC			Ex ia I, Ex ia IIB/IIA, Ex ia					
Co	510 nF	580 nF	600 nF	600 nF	600 nF	1 μF	1μF	1μF	1μF
Lo	100 mH	50 mH	5 mH	1 mH	10 µH	100 mH	5 mH	1 mH	10 µH

The reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F for Groups I, IIA and IIB and 600 nF for Group IIC.