Safety Instructions

Memosens CLS15E, CLS16E, CLS21E, CLS82E

Supplement to: BA02018C, BA02019C, BA02020C and BA02027C

Safety instructions for electrical apparatus in explosion-hazardous areas JPN Ex ia IIC T3/T4/T6 Ga







Memosens CLS15E, CLS16E, CLS21E, CLS82E

Supplement to: BA02018C, BA02019C, BA02020C and BA02027C

Table of contents

Associated documentation	4
Supplementary documentation	4
Certificate	4
Identification	4
Safety instructions	4
Temperature tables	5
Installation conditions	6
Connection	6

Endress+Hauser 3

Associated documentation

This document is an integral part of

Operating Instructions Memosens CLS21E, BA02020C

Operating Instructions Memosens CLS15E, BA02018C

Operating Instructions Memosens CLS16E, BA02019C

Operating Instructions Memosens CLS82E, BA02027C

Supplementary documentation



- Explosion Protection: Guidelines and General Principles
- www.endress.com

Certificate

JPN type-examination certificate, certificate number: CML 20JPN2010X

Identification

The nameplate provides you with the following information on your device:

- Manufacturer identification
- Extended order code
- Serial number
- Safety information and warnings
- Ex marking on hazardous area versions
- ▶ Compare the information on the nameplate with the order.

Type code

Туре	Version					
CLS15E -	JA	**	**	a 1)	***	+*
CLS16E -	JA	**	**	***	+*	
CLS21E -	JA	**	**	***	+*	
CLS82E -	JA	**	**	***	+*	
	JPN Ex ia IIC T3/T4/T6 Ga	No Ex relevance				

1) a = A, B

Certificates and approvals

The product meets the requirements of the Regulation on the Testing of Machinery and other Instruments set down by the Ministry of Health, Labor and Welfare in Japan. CLS15E / CLS16E / CLS21E / CLS82E

JPN Ex ia IIC T3/T4/T6 Ga

Safety instructions

The CLSxxE-type conductivity sensors are suitable for use in explosion-hazardous areas according to JPN type-examination certificate CML 20JPN2010X including appendices.

- CLS15E, CLS16E, CLS21E: Metallic process connection parts have to be mounted electrostatically conductive at the mounting location (< 1 $M\Omega$).
- CLS15E and CLS21E with non-metallic process connection may only be used in liquid media with a conductivity of at least 10 nS/cm.
- CLS15E with non-metallic process connection may not be operated on processing conditions, in which an electrostatic loading of the sensor and in particular of the electrically separated outer electrode, could be expected to occur.


- CLS82E: The sensor may not be operated in electrostatically critical processing conditions. Intense vapour or dust flows directly impacting on the connection system must be avoided. The metallic parts of the sensor have to be mounted at the mounting location electrostatically conductive (< $1 \text{ M}\Omega$).
- The maximum ambient and process temperatures for the temperature classes T3, T4 or T6 are limited according to the tables of this certificate (see "Temperature tables").
- When using devices and sensors, observe the guidelines for interconnecting intrinsically safe circuits (e.g. JNIOSH-TR-NO.44).
- The user shall fit the yellow/black sticker (included in the product package) next to the installed sensor (e.g. on the installed cable).
- This device was developed, manufactured and assessed in accordance with the following standards:
 - JNIOSH-TR-46-1:2015 "Equipment General requirements"
 - JNIOSH-TR-46-6:2015 "Equipment protection by intrinsic safety "i" "

Temperature tables

Sensor type	T-Class	T _p (process)	T _a (ambient)	
		min.	max.	max.
CLS15E-*****A***+*	T3	-20 °C	135 ℃	60 °C
	T4	-20 °C	120°C	60 °C
	Т6	-20 °C	70 ℃	60 °C
CLS15E-*****B***+*	T3	-20 °C	135 ℃	60 °C
	T4	-20 °C	100 °C	60 °C
	Т6	-20 °C	50 ℃	60 °C
CLS16E-*******	T3	-5 ℃	135 °C	60 °C
	T4	-5 ℃	115 °C	60 °C
	Т6	-5 ℃	65 ℃	60 °C
CLS21E-*******+*	T3	-20 °C	135 ℃	60 °C
	T4	-20 °C	115 °C	60 °C
	Т6	-20 °C	65 ℃	60 °C
CLS82E-*******	T3	-20 °C	140 °C	60 °C
	T4	-20 °C	120°C	60 °C
	Т6	-20 °C	70 ℃	60 °C

Endress+Hauser 5

Installation conditions



A004128

■ 1 Installation conditions

- 1 Limit
- 2 Distance between plug-in head (lower edge) and process medium, without ring and thrust collar
- 3 Process temperature T_p
- 4 Ambient temperature T_a

Connection

Ex specification

The CLSxxE-type conductivity sensors are approved according to JPN type-examination certificate CML 20JPN2010X and are suitable for use in hazardous environments.

- The approved CLSxxE-type digital conductivity sensors have an intrinsically safe input with the following parameter set:
 - $P_{i} = 180 \text{ mW}$
- ullet The approved CLSxxE-type digital conductivity sensors may only be connected to a Memosens cable or a compact transmitter with an intrinsically safe output with the following parameter set: P_0 max. 180 mW

6



www.addresses.endress.com