Technical Information Thermophant T TTR31, TTR35

Temperature switch for safe measurement, monitoring and control of process temperatures



Applications

Temperature switch for monitoring, display and control of process temperatures in the range of -50 to 200 °C (-58 to 392 °F):

- Thermophant T TTR31 with threaded connections or compression fitting
- Thermophant T TTR35 for hygienic applications

Applications:

- Versions for use in hygienic applications
- Electronic versions
 - one PNP switch output
 - two PNP switch outputs
 - 2x PNP switch outputs or one PNP switch output and 4 to 20 mA output (active)

Your benefits

The compact temperature switch impresses with state-of-the-art technology:

- Integrated switching electronics for decentralized and cost-effective monitoring and control of processes
- High reproducibility and long-term stability
- Function check and information on site via LEDs and digital display
- Platinum temperature sensor with long-term stability (Pt100, Cl. A as per IEC 60751)
- High accuracy over the entire ambient temperature range and short response time
- Operation and visualization with PC and FieldCare configuration software
- Top housing section can be rotated 310°
- DESINA-compliant
- 3-A mark and EHEDG certification for TTR35



Table of contents

Function and system design	3 3
Input	
Output . Output signal . Signal on alarm . Load . Range of adjustment . Switching capacity . Inductive load .	5 5 5 5 5 5
Power supply	6 6 7 7
Performance characteristics Reference operating conditions Maximum measured error switch point and display Switch point non-reproducibility Long-term drift Sensor response time Long-term reliability Influence of ambient temperature Switch output response time Analog output	7 7 7 7 8 8 8 8 8
Installation	9 9
Storage temperature	10 10 11 11 11 11 11
Process temperature range	11 11 11
Design, dimensions	13 13 13 14 15

Operability	16
Operating concept	
Local operation	
Remote operation with PC	17
Certificates and approvals	18
CE mark	18
Other standards and guidelines	
UL approval	19
Hygiene standard	19
Materials in contact with food/product (FCM)	19
Material certification	19
Ordering information	19
Accessories	20
Device-specific accessories	
Communication-specific accessories	
System components	
Supplementary documentation	22
Technical Information	
Operating Instructions	22


Function and system design

Measuring principle

Electronic recording and conversion of input signals in industrial temperature measurement. A platinum sensor located at the measuring tip changes its resistance value depending on the temperature. This resistance value is recorded electronically. The relationship between resistance and temperature is defined in the international standard IEC 60751.

Measuring system

Overview




DC voltage version (DC)

PNP switch output of electronics.

Power supply e.g. with a power supply unit.

Preferably in connection with programmable logic controllers (PLC) or for controlling a relay.



- 1x PNP switch output
- В 2x PNP switch output
- PNP switch output with additional analog output 4 to 20 mA (active) С
- Transmitter power supply unit, e.g. RNB130 1
- Load (e.g. programmable logic controller, process control system, relay)
- Process indicator, e.g. RIA452 or recorder, e.g. Ecograph T (at 4 to 20 mA analog output)

1 "Easy Analog RNB130" transmitter power supply

Primary switched-mode power supply for sensors. Space-saving DIN rail mounting as per IEC 60715. Wide-range input: 100 to 240 V_{AC} nominal voltage; output: 24 V_{DC} , max. 30 V in the event of a

Nominal current: 1.5 A. Connection to single-phase alternating current networks or to two phase conductors of three-phase supply networks.

2 Process Indicator RIA452

If you would like to read off the instantaneous temperature value not only locally, but also directly from a control room or in the PC network, for example, the RIA452 process indicator is one possible solution: digital process indicator in a 96 x 96 mm (3.78 x 3.78 in) panel-mounted housing for monitoring and displaying analog measured values with pump control and batch functions. Multicolored 7-digit 14-segment LC display with bargraph representation. Configuration and measured value visualization via RS232 interface and PC configuration software.

3 Universal Graphic Data Manager Ecograph T

If you would not only like to read off the instantaneous temperature value, but also record, analyze and display it directly in a control room or in the PC network, for example, then the following options are available:

Universal Graphic Data Manager Ecograph T in a 144 x 144 mm (5.67 x 5.67 in) panel-mounted housing for the electronic capture, display, recording, analysis, remote transmission and archiving of analog and digital input signals. Multichannel data recording system with multicolored TFT display (145 mm (5.7 in) screen size), galvanically isolated universal inputs (U, I, TC, RTD, pulse, frequency),

digital inputs, transmitter power supply, limit relays, communication interfaces (USB, Ethernet, optionally RS232/485), 128 MB internal memory, external SD card and USB stick. The Field Data Manager (FDM) software supports data analysis at the PC, the device can be configured with FieldCare or the integrated Web server.

Input

Measured variable

Temperature (temperature-linear transmission behavior)

Measuring range

Designation	Measuring range limits	Min. Span
Pt100 as per IEC 60751	-50 to +150 °C (-58 to +302 °F) -50 to +200 °C (-58 to +392 °F) with extension neck	20 K (36 °F)
Sensor current: ≤ 0.6 mA		

Output

Output signal

DC voltage version (short-circuit proof version):

- 1x PNP switch output
- 2x PNP switch outputs
- 1x PNP switch output or one PNP switch output and 4 to 20 mA output, active

Signal on alarm

- Analog output: \leq 3.6 mA or \geq 21.0 mA (if setting is \geq 21.0 mA, output is \geq 21.5 mA)
- Switch outputs: in safe state (switch open)

Load

Max. $(V_{power supply}^- 6.5 \text{ V}) / 0.022 \text{ A (current output)}$

Range of adjustment

Switch output	Switch point (SP) and switchback point (RSP) in 0.1 $^{\circ}$ C (0.18 $^{\circ}$ F) increments. Minimum difference between SP and RSP: 0.5 $^{\circ}$ C (0.8 $^{\circ}$ F)	
Analog output (if available)	Lower range value (LRV) and upper range value (URV) can be configured as required within the sensor range Min. Span 20 K (36 °F)	
Damping	Can be configured as required: 0 to 40 s in increments of 0.1 s	
Unit	°C, °F, K	

Switching capacity

DC voltage version:

Switch status ON	Ia ≤ 250 mA
Switch status OFF	Ia ≤ 1 mA
Switching cycles	> 10,000,000
Voltage drop PNP	≤2 V
Overload protection	Switching current checked automatically; switched off in event of overcurrent, switching current checked again every 0.5 s; max. capacitive load: $14~\mu F$ for max. supply voltage (without resistive load); periodic disconnection from a protective circuit in event of overcurrent (f = $2~Hz$) and "Warning" displayed

Inductive load

To prevent electrical interference, only operate an inductive load (relays, contactors, solenoid valves) with a direct protective circuit (free-wheeling diode or capacitor).


Power supply

Electrical connection

Plug connector

i


 $TTR35: According to the 3-A \ Sanitary \ Standard \ and \ EHEDG \ electrical \ connecting \ cables \ must be smooth, corrosion-resistant \ and \ easy \ to \ clean.$



- A M12x1 connector
- B Valve connector M16x1.5 or NPT ½"

Device connection

DC voltage version with M12x1 connector




■ 1 Thermophant T with M12x1 connector

Item no.	Output setting	
A1	1x PNP switch output	
A2	2x PNP switch output R1 and Rx (R2)	
A2'	2xPNP switch output R1 and Rx (diagnostics/NC contact with "DESINA" setting)	
A3	1x PNP switch output and 1x analog output (4 to 20 mA)	
A4	1x analog output (4 to 20 mA) and 1x PNP switch output Rx (R2)	
A4'	1x analog output (4 to 20 mA) and 1x PNP switch output Rx (diagnostics/NC contact with "DESINA" setting)	

DC voltage version with M16x1.5 valve connector or NPT $\mbox{$^{1\!\!/}\!\!2$}"$

6



Item no.	Output setting	
В	1x PNP switch output	

Supply voltage

DC voltage version: 12 to 30 V_{DC} (reverse polarity protection)

Behavior in case of overvoltage (> 30 V)

- ullet The device works continuously up to 34 V_{DC} without any damage
- No damage in the event of transient overvoltage up to 1 kV (according to EN 61000-4-5)
- If the supply voltage is exceeded, the specified characteristics are no longer guaranteed

Behavior in the event of undervoltage

If the supply voltage falls below the minimum value, the device switches off in a defined manner (status is the same as for not supplied with power = switch open).



The device may be powered only by a power supply unit that operates using a limited energy circuit in accordance with UL/EN/IEC 61010-1, Section 9.4 and the requirements in Table 18.

Current consumption

without load < 60 mA with reverse polarity protection

Performance characteristics

The percentages in the "Performance characteristics" section refer to the nominal value of the sensor.

Reference operating conditions

As per DIN IEC 60770 or DIN IEC 61003

T = 25 °C (77 °F)

- Relative humidity 45 to 75%
- Ambient air pressure860 to 1060 kPa (124 to 153 psi), using water as the test medium
- Supply voltage U = 24 V_{DC}

Maximum measured error switch point and display

Electronics

0.2 K (0.36 °F)

Sensor

- Tolerance class A as per IEC 60751, -50 to +200 °C (-58 to +392 °F)
- Maximum measured error in $^{\circ}$ C = $\pm 0.15 + 0.002 \cdot |T|$

|T| = Process temperature in °C without taking the sign into account.

Total error

Total error = electronics error + sensor error, e.g. for process temperatures:

- -50 to +75 °C (-58 to +167 °F) \leq 0.5 K (0.9 °F)
- +75 to +200 °C (+167 to +392 °F) \leq 0.75 K (1.35 °F)

Switch point nonreproducibility

0.1 K (0.18 °F) as per EN 61298-2 (without ambient temperature effect)

Long-term drift


≤ 0.1 K (0.18 °F) per year under reference conditions

Sensor response time	Measured in accordance with IEC 60751 with 0.4 m/s (1.3 ft/s) in flowing water 100 ms		
	t_{50} t_{90}		
	< 1.0 s		< 2.0 s
Long-term reliability	Mean time between failure (MTBF) > 100 years (calculated according to the "British Telecom Handbook of Reliability Data No. 5")		
Influence of ambient temperature	 Switch output and display: ≤ 30 ppm/K Analog output: ≤ 50 ppm/K + influence of switch output and display 		
Switch output response time	100 ms		
Analog output	Maximum measured error Switch point and display deviation + 0.1%		
	Rise time t ₉₀	≤200 ms	
	Settling time t ₉₉	≤500 ms	

Installation

General installation instructions


- Any orientation
- \blacksquare Top housing section can be rotated 310°
- No restrictions. However, self-draining in the process must be guaranteed. If there is an opening to detect leaks at the process connection, this opening must be at the lowest possible point.



₽ 2 Installation options for temperature monitoring in pipelines

- Hexagonal screw of sensor module 1
- TTR31
- 2 3 TTR35 for use in hygienic processes

Installation instructions



A0011673-FN

- 3 Detailed installation instructions for hygiene-compliant installation
- A Milk pipe connection according to DIN 11851 (PL, PG, PH connection), only in conjunction with EHEDG-certified and self-centering sealing ring
- B Varivent® and APV-Inline (LB, LL, HL connection)
- C Clamp as per ISO 2852 (DB, DL connection), EHEDG-certified only in conjunction with seal as per EHEDG position paper
- The requirements of the EHEDG and the 3-A Sanitary Standard must be adhered to. Installation instruction EHEDG/cleanability: $Lt \le (Dt-dt)$ Installation instruction 3-A/cleanability: $Lt \le 2(Dt-dt)$

In the case of weld-in connections, exercise the necessary degree of care when performing the welding work on the process side:

- 1. Use suitable welding material.
- 2. Flush-weld or weld with welding radius \geq 3.2 mm (0.13 in).
- 3. Avoid crevices, folds or gaps.
- 4. Ensure the surface is honed and polished, Ra \leq 0.76 μ m (30 μ in).

Pay attention to the following when installing the thermometer to ensure that the cleanability is not affected:

- 1. The installed sensor is suitable for CIP (cleaning in place). Cleaning is carried out in combination with tubing/piping or tank/vessel. In the case of internal tank fixtures using process connection nozzles, it is important to ensure that the cleaning assembly sprays this area directly so that it is cleaned properly.
- 2. The Varivent® connections enable flush-mounted installation.

NOTICE

The following action must be taken if a sealing ring (O-ring) or seal fails:

- The thermometer must be removed.
- ▶ The thread and the O-ring joint/sealing surface must be cleaned.
- ► The sealing ring or seal must be replaced.
- ► CIP must be performed after installation.

Environment

Ambient temperature range -40 to +85 °C (-40 to +185 °F)

Storage temperature -40 to +85 °C (-40 to +185 °F)

Operating altitude	Up to 4000 m (13123.36 ft) above sea level		
Degree of protection	IP65	M16 x 1.5 or NPT ½", valve connector	
	IP66	M12 x 1 connector	
Shock resistance	50 g as per DIN IEC 68-2-27 (11 ms)		
Vibration resistance	 20 g as per DIN IEC 68-2-6 (10-2000 Hz) 4 g as per marine approval 		
Electromagnetic	CE conformity		
compatibility (EMC)	Electromagnetic compatibility in accordance with all the relevant requirements of the IEC/EN 61326 series and NAMUR Recommendation EMC (NE21). For details refer to the EU Declaration of Conformity.		
	Maximum measured error <1% of measuring range.		
	Interference immunity as per IEC/EN 61326 series, industrial requirements.		
	Interference emission to IEC/EN 61326 - series, electrical equipment Class B.		
Electrical safety	 Protection class III Overvoltage category II Pollution level 2 		

Process

Process temperature range

-50 to +150 °C (-58 to +302 °F)(or -50 to +200 °C (-58 to 392 °F) with extension neck).


Restrictions depending on process connection and ambient temperature:

- No restriction with compression fitting (see Accessories, order no. 51004751, 51004753) and extension neck length min. 20 mm (0.79 in)
- with process connection:

Max. ambient temperature	Max. process temperature
up to 25 °C (77 °F)	No restrictions
up to 40 °C (104 °F)	135 °C (275 °F)
up to 60 °C (140 °F)	120 °C (248 °F)
up to 85 °C (185 °F)	100 °C (212 °F)

Process pressure range

 $\label{lem:maximum permitted process pressure depending on the insertion length$



■ 4 Maximum permitted process pressure


- L Insertion length
- p Process pressure

The diagram takes into consideration not only the overpressure but also the compressive load caused by flow, wherein a safety factor of 1.9 has been applied for operation with flow. Due to the increased bending stress caused by flow, the maximum permitted static operating pressure is lower in the case of longer insertion lengths.

This calculation is based on the maximum permitted flow velocity for the respective insertion length (see diagram below) .

The maximum process pressure for the conical metal-metal process connection for hygienic processes (MB option) for the device is 1.6 MPa = 16 bar (232 psi).

Permitted flow velocity depending on the insertion length




Permitted flow velocity

- A Water
- B Air
- L Insertion length, during flow
- v Flow velocity

The permitted flow velocity is the minimum defined by the resonance velocity (resonance distance 80%) and stress or buckling caused by flow, which would lead to failure of the thermometer tube or to the safety factor (1.9) being exceeded. The calculation was performed for the specified limit operating conditions of 200 °C (392 °F) and \leq 100 bar (1450 psi) process pressure.

Mechanical construction


Design, dimensions



All dimensions in mm (in)

- Temperature switch with extension neck and M12x1 connector according to IEC 60947-5-2
- 2 Temperature switch (hygiene version) with extension neck and M12x1 connector according to IEC 60947-5-2
- 3 Valve connector M16x1.5 or NPT½" as per DIN 43650A/ISO 4400
- Insertion length

Design, dimensions of process connections




№ 6 Process connection versions

Insertion length

Item No.	Version	Thread length L ₁	Screw-in length L ₂
A	Without process connection. Suitable welding bosses and compression fittings. → 20	-	-
В	Threaded process connection: • ANSI NPT ¼" (1 = AF14) • ANSI NPT ½" (1 = AF27)	■ 14.3 mm (0.56 in) ■ 19 mm (0.75 in)	• 5.8 mm (0.23 in) • 8.1 mm (0.32 in)
С	Threaded process connection, inches, cylindrical as per ISO 228: ■ G¼" (2 = AF14) ■ G½" (2 = AF27)	■ 12 mm (0.47 in) ■ 14 mm (0.55 in)	-

Hygienic design, dimensions of process connections



■ 7 Process connection versions

All dimensions in mm (in).

L Insertion length L

Item no.	Process connection versions, hygiene version	Hygiene standard
DB	Clamp 1" to 1½" (ISO 2852) or DN 25 to DN 40 (DIN 32676)	
DL	Clamp 2" (ISO 2852) or DN 50 (DIN 32676) 3-A marked and EHEDG certified (combine Combifit seal).	
DP	Clamp 21/2" (ISO 2852)	,,,,,,
HL	APV Inline, DN50, PN40, 316L, B = bores 6 x Ø8.6 mm (0.34 in) + 2 x M8 thread	
LB	Varivent ¹⁾ F DN25-32, PN 40	With 3-A symbol and EHEDG certification
LL	Varivent ¹⁾ N DN40-162, PN 40	
MB	Metal sealing system for hygienic processes, $G^{1/2}$ " thread, thread length L1 = 14 mm (0.55 in). Suitable welding boss available as an accessory.	-

Item no.	Process connection versions, hygiene version	Hygiene standard		
PG	DIN 11851, DN25, PN40 (including coupling nut)	3-A marked and EHEDG certified (only in combination		
PH	DIN 11851, DN40, PN40 (including coupling nut)	with self-centering seal according to EHEDG position		
PL	DIN 11851, DN50, PN40 (including coupling nut)	paper)		

1) Varivent® process connections are suitable for installation in VARINLINE® housing connection flanges.



The VARINLINE® housing connection flange is suitable for welding into the conical or torispherical head in tanks or vessels with a small diameter (≤ 1.6 m (5.25 ft)) and up to a wall thickness of 8 mm (0.31 in). The Varivent type F cannot be used for installations in pipes in combination with the VARINLINE housing connection flange.

Weight

approx. 300 g (10.58 oz), depends on process connection and sensor length


Materials

- Process connection AISI 316L
 - Surfaces in contact with the process in hygienic version with surface quality Ra $\leq 0.76~\mu m$ (30 $\mu in)$
- Coupling nut AISI 304
- AISI 316L housing, with surface quality $R_a \le 0.76 \ \mu m$ (30 μ in) O-ring between housing and sensor module: EPDM
- Electrical connection
 - M12 connector, exterior AISI 316L, interior polyamide (PA)
 - Valve connector, polyamide (PA)
 - M12 connector, exterior 316L
 - Cable sheath polyurethane (PUR)
 - O-ring between electrical connection and housing: FKM
- Display, polycarbonate PC-FR (Lexan®)
 Seal between display and housing: SEBS THERMOPLAST K®
 Keys, polycarbonate PC-FR (Lexan®)

Operability

Operating concept

Position of the display and operating elements



To prevent damage to the keys, do not operate them with a pointed object!

Local operation

Menu-guided operation using operating keys.

Function group	Operating options		
BASE	Selection of unit: °C, °F, K		
(basic functions)	Zero point, offset (automatic and manual)		
	Damping display value, output signal: from 0 to 40 s (in 0.1 s increments), as required		
	Display		
	 Display measured value or set switch point Rotate display by 180° Switch off display 		
	Behavior in accordance with DESINA (with 2 outputs only): The PIN assignment of the M12 connector is in accordance with DESINA guidelines (DESINA = distributed and standardized installation technology for machine tools and manufacturing systems)		
OUT (configuration of 1st output) and	Switch output function:		
OUT2 (configuration of 2nd output, only for corresponding electronics version)	 Hysteresis or window function NC contact or NO contact (see the following diagram) Analog output 4 to 20 mA 		
	Switch point:		
	Input valueAccept present value		
	Switch point from 0.5 to 100% URL (in 0.1 % increments), as required		
	Switchback point:		
	Input valueAccept present value		
	Switchback point from 0.5 to 99.5% URL (in 0.1 % increments), as required		
	Switch output delay: can be configured as required from 0 to 99 s (in 0.1 s increments)		

Function group	Operating options				
4-20 (configuration of analog output, only	Lower range value (LRV) and upper range value (URV) of analog output:				
for corresponding electronic version)	Input valueAccept present value				
	Setting of failure current: choice of \leq 3.6 mA / \geq 21 mA / last current value				
SERV (service functions)	Reset all settings to factory setting				
	Preset locking code				
	Locking				
	Static revision counter, incremented each time the configuration is changed				
	Display of last error to occur				
	Simulation of switch output 1, switch output 2 and analog output				
	Display of max. measured temperature value				
	Display of min. measured temperature value				

Functions of the switch point

• Hysteresis function:

The hysteresis function enables two-point control via a hysteresis. Depending on the temperature, the hysteresis can be set via the switch point SP and the switchback point RSP.


Window function:

The window function allows a process window to be defined.

• NO contact or NC contact:

This switch function can be selected as required.


 Delay times for switch point SP and switchback point RSP can be configured in increments of 1 s. This makes it possible to filter out undesired temperature peaks of short duration or of high frequency



- Hysteresis NC contact
- 3 Window - NO contact
- SP Switch point
- RSP Switchback point

Remote operation with PC

Operation, visualization and maintenance with PC and PC configuration software ReadWIN 2000 or FieldCare.



Operation, visualization and maintenance with PC and configuration software

- 1 PC with ReadWin 2000 or FieldCare configuration software
- 3 Temperature switch

In addition to the operating options listed in the previous "Local operation" section, further information regarding the Thermophant T is available via the ReadWin 2000 or FieldCare configuration software:

Function group	Description		
SERV	Number of switch changes, output 1		
	Number of switch changes, output 2		
	Device status		
INFO	Tagging, 18-digit		
	Order code		
	Device serial number		
	Sensor serial number		
	Electronics serial number		
	Displays overall version		
	Hardware version		
	Software version		

Certificates and approvals

CE mark

The product meets the requirements of the harmonized European standards. As such, it complies with the legal specifications of the EC directives. The manufacturer confirms successful testing of the product by affixing to it the CE-mark.

Other standards and guidelines

- IEC 60529:
- Degrees of protection provided by enclosures (IP code)
- IEC/EN 61010-1:

Protection Measures for Electrical Equipment for Measurement, Control, Regulation and Laboratory Procedures

- IEC/EN 61326 series:
 - Electromagnetic compatibility (EMC requirements)
- NAMUR:
 - International user association of automation technology in process industries (www.namur.de)
- NEMA:

United States National Electrical Manufacturers Association.

18

UL approval	More information under UL Product iq [™] , search for keyword "E225237") ■ EHEDG certification, type EL CLASS I. EHEDG certified/tested process connections → 🖺 13 ■ 3-A Authorization No. 1144, 3-A Sanitary Standard 74-07. Listed process connections → 🖺 13 ■ FDA-compliant				
Hygiene standard					
Materials in contact with food/product (FCM)	 The materials of the thermometer in contact with food/product (FCM) comply with the following European regulations: (EC) No. 1935/2004, Article 3, Paragraph 1, Articles 5 and 17 on materials and articles intended to come into contact with food. (EC) No. 2023/2006 on good manufacturing practice (GMP) for materials and articles intended to come into contact with food. (EC) No. 10/2011 on plastic materials and articles intended to come into contact with food. All surfaces in contact with the medium are free from materials derived from bovine animals or other livestock (ADI/TSE) 				
Material certification	The material certificate 3.1 (according to standard EN 10204) can be requested separately. The "short form" certificate includes a simplified declaration with no enclosures of documents related to the materials used in the construction of the single sensor and guarantees the traceability of the				

the materials can subsequently be requested by the client if necessary.

Ordering information

Detailed ordering information is available for your nearest sales organization www.addresses.endress.com or in the Product Configurator under www.endress.com:

materials through the identification number of the thermometer. The data related to the origin of

- 1. Click Corporate
- 2. Select the country
- 3. Click Products
- 4. Select the product using the filters and search field
- 5. Open the product page

The Configuration button to the right of the product image opens the Product Configurator.

Product Configurator - the tool for individual product configuration


- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- $\, \blacksquare \,$ Ability to order directly in the Endress+Hauser Online Shop

Accessories

Device-specific accessories


Welding boss with sealing taper

- Collar welding boss movable with sealing taper, washer and pressure screw G¹/₂"
- Material of parts in contact with the process: 316L, PEEK,
- Max. process pressure 10 bar (145 psi)
- Order number with pressure screw 51004751
- Order number without pressure screw 51004752




Collar welding boss

- Collar welding boss movable with sealing taper and washer
- Material of parts in contact with the process: 316L, PEEK
- Max. process pressure 10 bar (145 psi)
- Order number without pressure screw: 51004752



Compression fitting

- Movable clamping ring, various process connections
- Material of compression fitting and parts in contact with the process: 316L
- Order number: TA50-..... (depending on the process connection)



20


Version	F in mm (in)		L ~ in mm (in)	C in mm (in)	B in mm (in)	Clamping ring material	Max. process temperature	Max. process pressure
TA50	G ¹ /2"	SW/AF 27	47 (1.85)	-	15 (0.6)	SS316 ¹⁾	800 °C (1472 °F)	40 bar at 20 °C (580 psi at 68 °F)
						PTFE 2)	200 °C (392 °F)	5 bar at 20 °C (72.5 psi at 68 °F)
	G ³ / ₄ "	SW/AF 32	63 (2.48)	-	20 (0.8)	SS316 1)	800 °C (1472 °F)	40 bar at 20 °C (580 psi at 68 °F)
						PTFE 2)	200 °C (392 °F)	5 bar at 20 °C (72.5 psi at 68 °F)
	G1"	SW/AF 41	65 (2.56)	-	25 (0.98)	SS316 1)	800 °C (1472 °F)	40 bar at 20 °C (580 psi at 68 °F)
						PTFE 2)	200 °C (392 °F)	5 bar at 20 °C (72.5 psi at 68 °F)
	NPT½"	SW/AF 22	50 (1.97)	-	20 (0.8)	SS316 1)	800 °C (1472 °F)	40 bar at 20 °C (580 psi at 68 °F)
	R½"	SW/AF 22	52 (2.05)	-	20 (0.8)	PTFE 2)	200 °C (392 °F)	5 bar at 20 °C (72.5 psi at 68 °F)
	R3/4"	SW/AF 27	52 (2.05)	-	20 (0.8)	PTFE 2)	200 °C (392 °F)	5 bar at 20 °C (72.5 psi at 68 °F)

- 1) SS316 clamping ring: can only be used once. Once released the compression fitting cannot be repositioned on the thermowell. Fully adjustable immersion length on initial installation
- 2) PTFE/Elastosil® clamping ring: reusable; once loosened, the compression fitting can be moved up or down on the thermowell. Fully adjustable immersion length


Communication-specific accessories

Coupling; connecting cable

- Coupling M12x1; straight
- Connection to M12x1 housing connector
- Materials: body PA, coupling nut CuZn, nickelplated
- Degree of protection (connected): IP 67
- Order number: 52006263



- M12x1 coupling; elbowed, for termination of connecting cable by user
- Connection to M12x1 housing connector
- Materials: body PBT/PA,
- Cap-nut GD-Zn, nickel-plated
- Degree of protection (connected): IP 67
- Order number: 51006327




- PVC cable (terminated), 4 x 0.34 mm² with M12x1 coupling, elbowed, screw plug, length 5 m (16.4 ft)
- Degree of protection: IP67

• Order number: 51005148

Core colors:

- 1 = BN brown
- 2 = WH white
- 3 = BU blue
- 4 = BK black




- PVC cable, 4x 0.34 mm²with M12x1 coupling, with LED, elbowed,
- 316L screw plug, length5 m (16.4 ft), specially for hygiene applications,
- Degree of protection (connected): IP69K
- Order number: 52018763

Display:

- gn: device is operational
- ye1: switch status 1
- ye2: switch status 2



Not suitable for 4 to 20 mA analog output!



Configuration kit

- Configuration kit for PC-programmable transmitters;
 Configuration software and interface cable for PC with USB port and 4-pin post connector Order code: TXU10-AA
- "Commubox FXA291" configuration kit with interface cable for PC with USB port. Intrinsically safe CDI interface (Endress+Hauser Common Data Interface) for transmitters with 4-pin post connector. Suitable configuration software is FieldCare for example.
 Order code: FXA291

Configuration software

The ReadWin 2000 and FieldCare 'Device Setup' configuration programs can be downloaded free of charge directly from the Internet at the following addresses:

- www.produkte.endress.com/readwin
- www.produkte.endress.com/fieldcare

FieldCare 'Device Setup' can also be ordered from an Endress+Hauser sales office.

System components

- Easy Analog RNB130 power supply from Endress+Hauser with nominal output current IN = 1.5 A. For details, see Technical Information TI120R/09/en.
- Process indicator RIA452 from Endress+Hauser with transmitter power supply, max. output current I = 250 mA.

For details, see Technical Information TI113R/09/en.

Supplementary documentation

Technical Information

- Easy Analog RNB130: TI120R
- Process indicator RIA452: TI113R
- Universal Data Manager Ecograph T: TI01079R

Operating Instructions

- Thermophant T temperature switch TTR31, TTR35: BA00229R
- FieldCare configuration software: BA027S

22





www.addresses.endress.com