Safety Instructions Liquicap M FMI51, FMI52, FTI51, FTI52

II 3 G Ex ec IIC T6 Gc II 3 G Ex ec nC IIC T5 Gc II 3 D Ex tc IIIC T100°C Dc







Liquicap M FMI51, FMI52, FTI51, FTI52

Table of contents

About this document	4
Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	5
Other standards	5
Extended order code	5
Safety instructions: General	10
Safety instructions: Special conditions	11
Safety instructions: Installation	12
Temperature tables	13
Connection data	16

About this document	This document has been translated into several languages. Legally determined is solely the English source text.
	 The document translated into EU languages is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Manuals and Datasheets -> Type: Ex Safety Instruction (XA) -> Text Search: In the Device Viewer: www.endress.com -> Product tools -> Access device specific information -> Check device features
	If not yet available, the document can be ordered.
Associated documentation	This document is an integral part of the following Operating Instructions:
	 BA00297F/00, BA00298F/00 (FMI51, FMI52) BA00299F/00 (FTI51, FTI52)
Supplementary	Explosion-protection brochure: CP00021Z/11
documentation	 The Explosion-protection brochure is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z On the CD for devices with CD-based documentation
Manufacturer's certificates	EU Declaration of Conformity
certificates	Declaration Number: EU_00957
	The EU Declaration of Conformity is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Declaration -> Type: EU Declaration -> Product Code:
	EU type-examination certificate
	Certificate number: EU 00957 X
	List of applied standards: See EU Declaration of Conformity.

Manufacturer address	Endress+Hause Hauptstraße 1 79689 Maulbur Address of the p	rg, Geri		namepl	ate.
Other standards	 current version IEC/EN 6007 installations EN 1127-1: " 	for pro '9-14: " design, Explosi	he following stand oper installation: Explosive atmosph selection and erec ve atmospheres - E Basic concepts and	eres - Pa tion" Explosion	n prevention and
Extended order code	to the device in	such a out the	way that it is clear nameplate is provi	ly visibl	
	Structure of th	e exter	nded order code		
	FMI5x, FTI5x	_ ;	*****	+	A*B*C*D*E*F*G*
	(Device type)		(Basic specifications)		(Optional specifications)
	-	osition,	an option (numbei lisplayed instead of		er) selected from the ceholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Liquicap M

The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type FMI51, FMI52

Basic specifications

Position 1 (Approval)			
Selected option		Description	
FMI5x	М	ATEX II 3 G Ex ec IIC T6 Gc ATEX II 3 D Ex tc IIIC T 100 °C Dc	

Position 2 (Inactive Length L3)			
Selected op	otion	Description	
FMI51	1	Not selected	
	2, 5	mm/in, 316L	
	3, 6	mm/in, fully insulated PTFE > 316L	
FMI52	1	Not selected	
	2, 5	mm/in, 316L	
	3, 6	mm/in, fully insulated PFA > 316L	

Position 3	Position 3 (Active Probe length L1, Insulation)		
Selected op	otion	Description	
FMI51	A, B, C, D, H, K, M, N	mm/in, rod, 316L	
	E, F, G, P, R, S	mm/in, rod, 316L + ground tube	
FMI52	A, B, C, D	mm/in, 316	

Position 7 (Electronics, Output)			
Selected option		Description	
FMI5x	А	FEI50H; 4-20mA HART + display	
	В	FEI50H; 4-20mA HART	
	С	FEI57C; 2-wire PFM	

Position 8 (Housing)			
Selected option		Description	
FMI5x	1	F15 316L hygiene IP66/67 NEMA Type 4X	
	3	F17 Alu IP66/67 NEMA Type 4X	
	4	F13 Alu IP66 NEMA Type 4X + gas-tight probe seal	
	5	T13 Alu IP66 NEMA Type 4X + gas-tight probe seal + separate conn. compartment	
	6	F27 316L IP66/67 NEMA Type 6P + gas-tight probe seal	

Position 9 (Cable Entry)		
Selected option		Description
FMI5x	А	Gland M20
	В	Thread G1/2
	С	Thread NPT1/2
	D	Thread NPT3/4
	Е	Plug M12

Position 10 (Type of Probe)		
Selected option		Description
FMI5x	1	Compact
	2, 3, 4, 5	mm/in, L4 cable > separate enclosure

Optional specifications

No options specific to hazardous locations are available.

The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type FTI51, FTI52

Basic specifications

Position 1 (Approval)		
Selected option		Description
FTI5x	М	ATEX II 3 G Ex ec IIC T6 Gc ATEX II 3 G Ex ec nC IIC T5 Gc ATEX II 3 D Ex tc IIIC T 100 °C Dc

Position 2 (Inactive Length L3)		
Selected option		Description
FTI51	А	Not selected
	В	Not selected + active build-up protection 125mm/5in, 316L
	С	Not selected + fully insulated, active build-up protection 125mm/ 5in, PFA > 316L
	1, 5	mm/in, 316L
	2,6	mm/in, fully insulated PTFE > 316L
	3, 7	mm/in (≤ 500mm/20in), 316L + active build-up protection 125mm/5in, 316L
	4, 8	mm/in (> 500mm/20in), 316L + active build-up protection 125mm/5in, 316L

Position 2 (Inactive Length L3)		
Selected option		Description
FTI52	А	Not selected
1, 5 mm/in, 316L 3, 6 mm/in, fully insulated PFA > 316L		mm/in, 316L
		mm/in, fully insulated PFA > 316L

Position 3 (A	Position 3 (Active Probe length L1; Insulation)	
Selected opt	ion	Description
FTI51	A, B, C, D, H, K, M, N, T, 1	mm/in, rod, 316L
	E, F, G, P, R, S	mm/in, rod, 316L + ground tube
FTI52	A, B, C, D	mm/in, 316

Position 8 (Electronics, Output)		
Selected option		Description
FTI5x	1	FEI51; 2-wire 19-253 VAC
2 FEI52; 3-wire PNP 10-55 VDC 4 FEI54; relay DPDT, 19-253 VAC, 19-55 VDC 5 FEI55; 8/16 mA, 11-35 VDC 7 FEI57S; 2-wire PFM 8 FEI58; NAMUR + test button (H-L signal)		FEI52; 3-wire PNP 10-55 VDC
		FEI54; relay DPDT, 19-253 VAC, 19-55 VDC
		FEI55; 8/16 mA, 11-35 VDC
		FEI57S; 2-wire PFM
		FEI58; NAMUR + test button (H-L signal)

Position 9 (Housing)			
Selected option		Description	
FTI5x	1	F15 316L hygiene IP66/67 NEMA Type 4X	
4 F 5 T se		F17 Alu IP66/67 NEMA Type 4X	
		F13 Alu IP66 NEMA Type 4X + gas-tight probe seal	
		T13 Alu IP66 NEMA Type 4X + gas-tight probe seal + separate conn. compartment	
		F27 316L IP66/67 NEMA Type 6P + gas-tight probe seal	

Position 10 (Cable Entry)		
Selected option		Description
FTI5x	А	Gland M20
	В	Thread G1/2
	С	Thread NPT1/2
	D	Thread NPT3/4
	Е	Plug M12

Position 11 (Type of probe)		
Selected opti	ion	Description
FTI5x	1	Compact
	2, 3, 4, 5	mm/in, L4 cable > separate enclosure

Optional specifications


No options specific to hazardous locations are available.

Safety instructions: General

- The device is intended to be used in explosive atmospheres as defined in the scope of EN IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.

	 Avoid electrostatic charging: Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates,) Of isolated capacities (e.g. isolated metallic plates) Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application and the temperature class. Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser. 		
Safety instructions: Special conditions	 To avoid electrostatic charging: Do not rub surfaces with a dry cloth. In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates: Observe the danger of electrostatic charging and discharge. Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges. 		
	Basic specification, Position $3 = E, F, G, P, R, S$ Probes can be used in gases of Group IIC, IIB and IIA.		
	<i>Basic specification, Position 3 = A, B, C, D, H, K, M, N, T, 1</i> Probes can be used in gases of Group IIC and IIB if avoiding electrostatic charging (e.g. through friction, cleaning, maintenance, strong medium flow). These probes are marked by the warning sign "Avoid Electrostatic Charge".		
	 Device type FTI5x, Basic specification, Position 8 = 1, 4 In a condensing atmosphere: The device must not be serviced or installed. The device must be externally protected against transient overvoltage up to 140 % of the maximum voltage. 		

Safety instructions: Installation



• 1

- A Zone 2, Zone 22
- B Zone 2, Zone 22
- 1 Rope or rod probes
- 2 Electronic insert
- 3 Enclosure
- 4 Associated power supply
- Mechanically fix probes which are more than 3 m (e.g. using guy ropes).
- Do not open in a potentially explosive dust atmosphere.
- To maintain the ingress protection of the enclosure:
 - Screw the cover tight.
 - Mount the cable entry correctly.
- Cable glands with ATEX-Ex e approval and metallic glands: Only use with an ingress protection of at least IP65. Lay connecting cable and secure.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection.

Basic specification, Position 8 (FMI5x), 9 (FTI5x) = 1

- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing clamp on the cover.
- Tightening torque of the securing screw: max. 1 Nm.

Basic specification, Position 8 (FMI5x), 9 (FTI5x) = 3, 4, 5 Tighten the cover with torque 12 Nm.

Potential equalization

Integrate the device into the local potential equalization.

Temperature tables


Application in gas

II 3 G Ex ec IIC T6 Gc

Basic specification, Position 7 (FMI5x), Position 8 (FTI5x)	Temperature class	Ambient temperature T _a (ambient): electronics	Process temperature T _p (process)
A, B, C, 1, 2	Т6	$-50 \text{ °C} \le T_a \le +60 \text{ °C}$	$\rightarrow \blacksquare 2, \blacksquare 14,$
	T3T5	$-50 \text{ °C} \le \text{T}_{a} \le +70 \text{ °C}$	→ 🖻 3, 🖺 15
5, 7, 8	Т6	-50 °C ≤ T _a ≤ +55 °C	→ 🖸 2, 🗎 14,
	T3T5	$-50 \text{ °C} \le T_a \le +70 \text{ °C}$	→ 🖻 3, 🖺 15

II 3 G Ex ec nC IIC T5 Gc

Basic specification, Position 8 (FTI5x)	Temperature class	Ambient temperature T _a (ambient): electronics	Process temperature T_p (process)
4	T5	$-50 \text{ °C} \le T_a \le +50 \text{ °C}$	→ 2, 14,
	T3T4	$-50 \text{ °C} \le T_a \le +70 \text{ °C}$	→ ■ 3, ■ 15





Basic specification, Position 10 (FMI5x), 11 (FTI5x) = 1

₽ 2

- T_a Ambient temperature in °C
- T_p Process temperature in °C

A0032139





- 🛃 3
- T_a Ambient temperature in °C
- T_p Process temperature in °C
- 1 Temperature at the separate enclosure ≤ 70 °C

Application in dust

II 3 D Ex tc IIIC T 100 °C Dc

1	· · ·	Ambient temperature T _a (ambient): electronics	Max. surface temperature (T _{a,max})	Protection type of enclosure
2	all	$-50 \ ^\circ C \le T_a \le +60 \ ^\circ C$	+100 °C	IP65

Connection data

Application in dust: Connetion to non-intrinsically safe circuits.

Basic specification, Position 7 (FMI5x), Position 8 (FTI5x)	Power supply	Output
А, В	12 to 35 V_{DC}	4 to 20 mA
С	\leq 19.2 V _{DC}	PFM
1	19 to 253 V _{AC}	-
2	10 to 55 V _{DC}	PNP transistor, max. 350 mA
4	19 to 253 V _{AC}	$\begin{array}{l} 253 \ V_{AC} \ / \ 6 \ A^{\ 1)} \\ 1 \ 500 \ VA \ / \ \cos \phi = 1 \\ 750 \ VA \ / \ \cos \phi > 0.7 \end{array}$
	19 to 55 V _{DC}	30 V _{DC} / 6 A ¹⁾ 125 V _{DC} / 0.2 A
5	11 to 35 V _{DC}	8 mA / 16 mA
7	9 to 12.5 V_{DC}	PFM
8	4 to 12.5 V_{DC}	NAMUR

Basic specification, Position 8 (FMI5x), 9 (FTI5x) = 5:4 A 1)



71546168

www.addresses.endress.com

