

# Safety Instructions

## Liquiphant FTL51B

4-20 mA HART

II 1/2 G Ex db IIC T6...T1 Ga/Gb

II 2 G Ex db IIC T6...T1 Gb

**UK  
CA**





# Liquiphant FTL51B

4-20 mA HART

## Table of contents

|   |    |
|---|----|
| Associated documentation .....                            | 4  |
| Supplementary documentation .....                         | 4  |
| Manufacturer's certificates .....                         | 4  |
| Manufacturer address .....                                | 4  |
| Other standards .....                                     | 4  |
| Extended order code .....                                 | 5  |
| Safety instructions: General .....                        | 7  |
| Safety instructions: Special conditions .....             | 8  |
| Safety instructions: Installation .....                   | 9  |
| Safety instructions: Ex d joints .....                    | 10 |
| Safety instructions: Zone 0 .....                         | 11 |
| Safety instructions: Zone separation Zone 0, Zone 1 ..... | 11 |
| Temperature tables .....                                  | 11 |
| Connection data .....                                     | 12 |

|                                    |   |
|------------------------------------|---|
| <b>Associated documentation</b>    | <p>This document is an integral part of the following Operating Instructions:<br/>BA02213F</p>  |
| <b>Supplementary documentation</b> | <p>Explosion protection brochure: CP00021Z<br/>The Explosion-protection brochure is available:</p> <ul style="list-style-type: none"><li>■ In the download area of the Endress+Hauser website:<br/><a href="http://www.endress.com">www.endress.com</a> -&gt; Downloads -&gt; Brochures and Catalogs -&gt; Text Search: CP00021Z</li><li>■ On the CD for devices with CD-based documentation</li></ul>  |
| <b>Manufacturer's certificates</b> | <p><b>UK Declaration of Conformity</b></p> <p>Declaration Number:<br/>UK_00529</p> <p>The UK Declaration of Conformity is available:<br/>In the download area of the Endress+Hauser website:<br/><a href="http://www.endress.com">www.endress.com</a> -&gt; Downloads -&gt; Declaration -&gt; Type: UKCA Declaration -&gt; Product Code: ...</p> <p><b>UKCA type-examination certificate</b></p> <p>Certificate number:<br/>CML 22UKEX1611X</p> <p>List of applied standards: See UK Declaration of Conformity.</p> |
| <b>Manufacturer address</b>        | <p>Endress+Hauser SE+Co. KG<br/>Hauptstraße 1<br/>79689 Maulburg, Germany<br/>Address of the manufacturing plant: See nameplate.</p>  |
| <b>Other standards</b>             | <p>Among other things, the following standards shall be observed in their current version for proper installation:</p> <ul style="list-style-type: none"><li>■ IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection"</li><li>■ EN 1127-1: "Explosive atmospheres - Explosion prevention and protection - Part 1: Basic concepts and methodology"</li></ul>  |

## Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

### Structure of the extended order code

|                      |   |                               |   |                                  |
|----------------------|---|-------------------------------|---|----------------------------------|
| FTL51B               | - | *****                         | + | A*B*C*D*E*F*G*..                 |
| <i>(Device type)</i> |   | <i>(Basic specifications)</i> |   | <i>(Optional specifications)</i> |

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

#### *Basic specifications*

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.

The selected option of a feature can consist of several positions.

#### *Optional specifications*

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

### Extended order code: Liquiphant



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

#### *Device type*

FTL51B

*Basic specifications*

| Position 1, 2 (Approval) |             |   |
|--------------------------|-------------|---|
| Selected option          | Description |   |
| FTL51B                   | UC          | UK Ex II 1/2 G Ex db IIC T6...T1 Ga/Gb<br>UK Ex II 2 G Ex db IIC T6...T1 Gb |

| Position 3, 4 (Output) |             |   |
|------------------------|-------------|---|
| Selected option        | Description |   |
| FTL51B                 | BA          | FEL60H, 2-wire 4...20 mA HART+test button |

| Position 6 (Housing, Material) |             |                                       |
|--------------------------------|-------------|---------------------------------------|
| Selected option                | Description |                                       |
| FTL51B                         | B           | Single compartment; Alu, coated       |
|                                | M           | Dual compartment L-shape; Alu, coated |
|                                | N           | Dual compartment L-shape; 316L        |

| Position 7 (Electrical Connection) |             |   |
|------------------------------------|-------------|---|
| Selected option                    | Description |   |
| FTL51B                             | F           | Thread M20, IP66/68 NEMA Type 4X/6P                 |
|                                    | G           | Thread G1/2 <sup>1)</sup> , IP66/68 NEMA Type 4X/6P |
|                                    | H           | Thread NPT1/2, IP66/68 NEMA Type 4X/6P              |

- 1) Reduction M20x1.5 to G1/2 enclosed

| Position 10 (Type of Probe) |             |                    |
|-----------------------------|-------------|--------------------|
| Selected option             | Description |                    |
| FTL51B                      | 1           | Compact version    |
|                             | 2           | Extension tube     |
|                             | 3           | Short tube version |

*Optional specifications*

| ID Jx, Kx (Test, Certificate, Declaration) |    |                                 |
|--|----|---------------------------------|
| Selected option                            |    | Description                     |
| FTL51B                                     | JL | Ambient temperature -50°C/-58°F |
|  | JN | Ambient temperature -52°C/-62°F |
|  | JT | Ambient temperature -60°C/-76°F |

| ID Px, Rx (Accessory Enclosed) |                  |                                |
|--------------------------------|------------------|--------------------------------|
| Selected option                |                  | Description                    |
| FTL51B                         | PA <sup>1)</sup> | Weather protection cover, 316L |

1) Only in connection with Position 6 = M, N

**Safety instructions:**  
**General**


- The device is intended to be used in explosive atmospheres as defined in the scope of EN IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Devices suitable for zone separation (marked Ga/Gb or Da/Db) are always suitable for installation in the less critical zone (Gb or Db). Due to space limitations the corresponding marking maybe not indicated on the nameplate.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.

- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ..)
  - Of isolated capacities (e.g. isolated metallic plates)
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application and the temperature class.
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

**Safety instructions:**

**Special conditions**

Permitted ambient temperature range at the electronics enclosure:  
 $-40\text{ °C} \leq T_a \leq +70\text{ °C}$


- Limitations of the maximum ambient temperature at the electronics enclosure may be required dependent on device configuration, process temperatures and temperature classification.
- Details of limitations: →  11, "Temperature tables".
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
  - Observe the danger of electrostatic charging and discharge.
  - Do not install in the vicinity of processes ( $\leq 0.5\text{ m}$ ) generating strong electrostatic charges.
- Avoid sparks caused by impact and friction.
- Covers with glass window only permitted for the following ambient temperatures:  
 $-50\text{ °C} \leq T_a \leq +70\text{ °C}$

*Optional specification, ID Px, Rx = PA*

Connect the weather protection cover to the local potential equalization.



## Safety instructions: Installation



A0025536

### 1

- A Zone 1  
 1 Tank; Zone 0, Zone 1  
 2 Electronic insert  
 3 Enclosure  
 4 Power supply unit  
 5 Potential equalization line  
 6 Local potential equalization

- After aligning (rotating) the enclosure, retighten the fixing screw.
- Before operation:
  - Screw in the cover all the way.
  - Tighten the securing screw on the cover.
- In potentially explosive atmospheres:
  - Do not disconnect the electrical connection of the power supply circuit when energized.
  - Do not open the connection compartment cover and the electronics compartment cover.
- Continuous service temperature of the connecting cable / cable gland / cable entry:  $\geq T_a + 20 \text{ K}$ .
- Perform the following to achieve the degree of protection IP66/68:
  - Screw the cover tight.
  - Mount the cable entry correctly.
- Connect the device:
  - Using suitable cable and wire entries of protection type "Flameproof Enclosure (Ex db)".
  - Using piping systems of protection type "Flameproof Enclosure (Ex db)".

- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- At high medium temperatures, note flange pressure load capacity as a factor of temperature.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.
- Support extension tube of the device if a dynamic load is expected.
- Only use genuine spare parts from Endress+Hauser which are specified for the device.
- Only use certified cable entries suitable for the application. Observe national regulations and standards.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- The built-in metallic sealing plug is examined and approved for explosion protection type Ex d with the device.
- When operating the transmitter enclosure at an ambient temperature under  $-20\text{ }^{\circ}\text{C}$ , use appropriate cables and cable entries permitted for this application.
- When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the enclosure.

*Basic specification, Position 7 = G*

Flameproof equipment with G threaded entry holes is not intended for new installations but only for replacement of equipment in existing installations. Application of this equipment shall comply with the local installation requirements.

### **Accessory high pressure sliding sleeve**

The high pressure sliding sleeve can be used for a continuous setting of the switch point and is suited for zone separation if mounted properly (see Operating Instructions).

### **Potential equalization**

Integrate the device into the local potential equalization.

*Optional specification, ID Px, Rx = PA*

Connect the weather protection cover to the local potential equalization.

## **Safety instructions: Ex d joints**

- If required or if in doubt: ask manufacturer for specifications.
- Flameproof joints are not intended to be repaired.

**Safety instructions:**  
**Zone 0**

When using under non-atmospheric pressures and non-atmospheric temperatures: The sensor part of the device approved for Zone 0 does not cause any ignition hazards.

**Safety instructions:**  
**Zone separation**  
**Zone 0, Zone 1**

The zone separation wall of the device is made of stainless steel or high corrosion-resistant alloy of thickness  $\geq 1$  mm.

**Temperature tables**



- The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
- Do not exceed the max. ambient temperature at the enclosure.



*Optional specification, ID Jx, Kx = JL*

Lower limit of the ambient temperature for explosion protection changes to  $-50$  °C.

*Optional specification, ID Jx, Kx = JN*

Lower limit of the ambient temperature for explosion protection changes to  $-52$  °C.

*Optional specification, ID Jx, Kx = JT*

Lower limit of the ambient temperature for explosion protection changes to  $-60$  °C.

*Basic specification, Position 10 = 1*

| Temperature class | Process temperature range  | Ambient temperature range  |
|-------------------|--|--|
| T6                | $-40\text{ °C} \leq T_p \leq +80\text{ °C}$<br>$-40\text{ °C} \leq T_p \leq +60\text{ °C}$   | $-40\text{ °C} \leq T_a \leq +55\text{ °C}$<br>$-40\text{ °C} \leq T_a \leq +60\text{ °C}$ |
| T5                | $-40\text{ °C} \leq T_p \leq +95\text{ °C}$  | $-40\text{ °C} \leq T_a \leq +60\text{ °C}$  |
| T4                | $-40\text{ °C} \leq T_p \leq +100\text{ °C}$<br>$-40\text{ °C} \leq T_p \leq +130\text{ °C}$ | $-40\text{ °C} \leq T_a \leq +60\text{ °C}$<br>$-40\text{ °C} \leq T_a \leq +50\text{ °C}$ |
| T3...T1           | $-40\text{ °C} \leq T_p \leq +150\text{ °C}$   | $-40\text{ °C} \leq T_a \leq +45\text{ °C}$  |

*Basic specification, Position 10 = 2, 3*

| Temperature class | Process temperature range  | Ambient temperature range  |
|-------------------|--|--|
| T6                | $-40\text{ °C} \leq T_p \leq +80\text{ °C}$<br>$-40\text{ °C} \leq T_p \leq +60\text{ °C}$   | $-40\text{ °C} \leq T_a \leq +65\text{ °C}$<br>$-40\text{ °C} \leq T_a \leq +70\text{ °C}$ |
| T5                | $-40\text{ °C} \leq T_p \leq +95\text{ °C}$  | $-40\text{ °C} \leq T_a \leq +70\text{ °C}$  |
| T4                | $-40\text{ °C} \leq T_p \leq +100\text{ °C}$<br>$-40\text{ °C} \leq T_p \leq +130\text{ °C}$ | $-40\text{ °C} \leq T_a \leq +70\text{ °C}$<br>$-40\text{ °C} \leq T_a \leq +70\text{ °C}$ |
| T3...T1           | $-40\text{ °C} \leq T_p \leq +150\text{ °C}$   | $-40\text{ °C} \leq T_a \leq +65\text{ °C}$  |

**Connection data**

| Power supply                                     |
|--|
| $U \leq 35\text{ V}_{DC}$<br>$P \leq 1\text{ W}$ |









71588155

[www.addresses.endress.com](http://www.addresses.endress.com)

---