# Technical Information Fieldgate FXA42

System Products



# Gateway for data transmission via Ethernet, WLAN or mobile telecommunications

#### Application

Fieldgates make it possible to remotely interrogate connected 4 to 20 mAModbus RS485 and Modbus TCP devices, either via Ethernet TCP/IP, WLAN or mobile telecommunications (UMTS, LTE Cat M1 and Cat NB1). The measured data are processed accordingly and forwarded to SupplyCare. In SupplyCare, the data are visualized, compiled into reports and used for other inventory management tasks. However, it is also possible to access the data transmitted by Fieldgate FXA42 without any additional software using the Web browser. Comprehensive configuration and automation capabilities are available for the Fieldgate FXA42 thanks to the integrated Web PLC.

### Your benefits

- Communication via Ethernet, WLAN, UMTS or LTE Cat M1 and Cat NB1
- Easy configuration without any additional software using Web browser
- Four 4 to 20 mA current inputs with integrated loop power supply
- Active/passive current input for 2-wire and 4-wire devices
- 4 digital inputs can also be used as pulse counters for flow applications
- Advanced logic functions thanks to integrated Web-PLC and communication with external systems via Modbus interface



### Table of contents

About this document	
Application          Vendor Managed Inventory	
Function and system design	<b>5</b> 5 5
Input Terminal assignment Weight Materials Terminals 4 to 20 mA analog input Digital input	12 12 12 12 12 12 12 13
Output	<b>14</b> 14 15
FF-3 · · · · · · · · · · · · · · · · · · ·	15 15 15 15
Installation  Mounting location Orientation Dimensions Antenna	16 16 16 16 16
Ambient temperature range	17 17 17 17 17 17 17 17 17
Display elements (device status indicator / LED)	18 18 18 19 20
CE mark	20 21 21 21

external standards and guidelines	21
Telecommunications approval         Gurope         JSA and Canada         Other certificates	21 21
Ordering information	23
Accessories	24
Supplementary documentation	
Registered trademarks	2.5

### About this document

### Symbols

### Safety symbols

⚠ DANGER
This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.

### **▲** WARNING

This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in serious or fatal injury.

This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in minor or medium injury.

#### **NOTICE**

This symbol contains information on procedures and other facts which do not result in personal injury.

### **Electrical symbols**

Grounded clamp, which is grounded via a grounding system.

A terminal that can be used as a ground contact for the digital input.

### Communication-specific symbols

Wireless Local Area Network (WLAN)

Communication via a wireless, local area network

- LED is off
- LED is on
- LED is flashing

### Symbols for certain types of Information

Indicates additional information

- Reference to documentation
- Reference to another section
- 1., 2., 3. Series of steps

### Symbols in graphics

1, 2, 3 ... Item numbers


★ Hazardous area

X Safe area (non-hazardous area)

### **Application**

### Vendor Managed Inventory

Thanks to the remote interrogation of tank or silo levels via Fieldgates, raw material suppliers can access information about current inventory levels at their regular customers' plants 24/7 and factor this information into their own production planning, for example. The Fieldgates monitor the configured level limits and automatically trigger the next delivery of product as required. The possibilities here range from simple refill requisitioning by e-mail through to fully automated order processing by incorporating XML data into the planning systems on both sides.



- 1 Application of a Vendor Managed Inventory
- A Supplier
- B Customer 1
- C Customer 2
- D Customer 3
- 1 SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- 2 Internet / LAN
- 3 Fieldgate FXA42
- 4 Analog 4 to 20 mA
- 5 Limit switch

### Function and system design

### IT security

Our warranty is valid only if the product is installed and used as described in the Operating Instructions. The product is equipped with security mechanisms to protect it against any inadvertent changes to the settings.


IT security measures, which provide additional protection for the product and associated data transfer, must be implemented by the operators themselves in line with their security standards.

### System requirements

Internet browser	Mobile device
<ul> <li>Mozilla Firefox version 31 or higher</li> <li>Google Chrome version 31 or higher</li> <li>Microsoft Edge</li> <li>Internet Explorer 10 or higher</li> </ul>	<ul> <li>Device with iOS: iOS Safari 7.1 or higher</li> <li>Device with Android: Android Firefox or Chrome from version 31</li> </ul>

### System design


### Configuration with 4 to 20 mA analog input (2-wire/4-wire)



A0030920


- 2 System architecture of a Fieldgate FXA42 with 4 to 20 mA analog input
- 1 SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- 2 Internet / LAN
- 3 SupplyCare Enterprise / SupplyCare Hosting on mobile devices (via Web browser)
- 4 Ethernet / WLAN / UMTS / LTE-M / LTE Cat NB1
- 5 Fieldgate FXA42
- 6 Power supply 24 V<sub>DC</sub>
- 7 4 x 4 to 20 mA analog input (passive), 4-wire
- 8 4 x 4 to 20 mA analog input (active), 2-wire (loop-powered)
- 9 Measuring device power supply

### Configuration with a digital input



- **₽** 3 System architecture of a Fieldgate FXA42 with a digital input
- SupplyCare Enterprise / SupplyCare Hosting (via Web browser) 1
- 2 Internet / LAN
- SupplyCare Enterprise / SupplyCare Hosting on mobile devices (via Web browser)
  Ethernet / WLAN / UMTS / LTE-M / LTE Cat NB1
  Fieldgate FXA42 3
- 4
- 5
- Power supply 24  $V_{DC}$
- 4 x digital input and auxiliary voltage output 24  $V_{DC}$


### Configuration with a pulse counter



A0030922

- € 4 System architecture of a Fieldgate FXA42 with a pulse counter
- SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- Internet / LAN
- 2 3 SupplyCare Enterprise / SupplyCare Hosting on mobile devices (via Web browser)
- Ethernet / WLAN / UMTS / LTE-M / LTE Cat NB1
- Fieldgate FXA42
- Power supply 24 V<sub>DC</sub>
- 4 x digital input with pulse counter


### Configuration with Modbus TCP



A0034272


- 5 System architecture of a Fieldgate FXA42 with a HART point-to-point multiplexer
- 1 SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- 2 Internet / LAN
- 3 SupplyCare Enterprise / SupplyCare Hosting on mobile devices (via Web browser)
- 4 Ethernet / WLAN / UMTS / LTE-M / LTE Cat NB1
- 5 Fieldgate FXA42
- 6 Power supply 24  $V_{DC}$
- 7 Modbus TCP via Ethernet as server/client
- 8 Phoenix Contact multiplexer from Modbus TCP to HART point-to-point. 1 head module and up to 5 extension modules are possible. Extension modules for 4 or 8 HART channels are possible
- 9 External power supply
- 10 FieldCare tunneling via Phoenix Contact multiplexer
- Modbus TCP can be operated as a server and as a client at the Ethernet connection of the Fieldgate FXA42.
- When operated as a Modbus client, up to 32 devices and 256 values can be defined. As values can become arrays when reading and writing several registers or coils, the following limit applies: The number of all scalar (non-array) values plus the size of all arrays must not exceed 512.

### Configuration with Modbus TCP



- **№** 6 System architecture of a Fieldgate FXA42 with Modbus TCP
- SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- 2 Internet / LAN
- $Supply Care\ Enterprise\ /\ Supply Care\ Hosting\ on\ mobile\ devices\ (via\ Web\ browser)$   $Ethernet\ /\ WLAN\ /\ UMTS\ /\ LTE\ Cat\ M1\ /\ LTE\ Cat\ NB1$ 3
- Fieldgate FXA42
- Power supply 24 V<sub>DC</sub>
- Modbus TCP via Ethernet as server/client
- 8 HG1 Plus converter from Modbus to HART Multidrop
- HART Multidrop (maximum 7 devices, depending on the power demand)
- 10 4 x analog input 4 to 20 mA (2-wire / 4-wire)
- FieldCare tunneling via HG1 Plus
- 12 Measuring device power supply
  - Modbus TCP can be operated as a server or client at the Ethernet connection of the Fieldgate FXA42.

### Configuration with HART Multidrop via Modbus TCP




 $\blacksquare$  7 System architecture of a Fieldgate FXA42 with HART Multidrop

- 1 SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- 2 Internet / LAN
- 3 SupplyCare Enterprise / SupplyCare Hosting on mobile devices (via Web browser)
- 4 Ethernet / WLAN / UMTS / LTE Cat M1 / LTE Cat NB1
- 5 Fieldgate FXA42
- 6 Power supply 24 V<sub>DC</sub>
- 7 4 x analog input 4 to 20 mA (2-wire / 4-wire)
- 8 HG1 Plus converter from Modbus to HART Multidrop
- 9 Converter from Modbus to HART Multidrop
- 10 Barrier
- 11 HART Multidrop

Modbus TCP can be operated as a server or client at the Ethernet connection of the Fieldgate FXA42.

If an appropriate communication barrier is used ( $\rightarrow \blacksquare 7$ ), then the measuring devices can also be operated in the hazardous area.

### Configuration with Modbus RS485




A0030923

- 8 System architecture of a Fieldgate FXA42 with Modbus RS485
- 1 SupplyCare Enterprise / SupplyCare Hosting (via Web browser)
- 2 Internet / LAN
- 3 SupplyCare Enterprise / SupplyCare Hosting on mobile devices (via Web browser)
- 4 Ethernet / WLAN / UMTS / LTE-M / LTE Cat NB1
- 5 Fieldgate FXA42
- 6 Power supply 24 V<sub>DC</sub>
- 7 1 x Modbus RS485 as master or slave
- 8 4 x analog input 4 to 20 mA (2-wire / 4-wire)
- The Modbus RS485 connection can be used as either a master or a slave, but cannot act as both simultaneously.
  - When operated as a master, up to 32 devices and 256 values can be defined. As values can become arrays when reading and writing several registers or coils, the following limit applies: The number of all scalar (non-array) values plus the size of all arrays must not exceed 512.
  - When operated as a slave, up to 128 values can be defined. As values can become arrays when reading and writing several registers or coils, the following limit applies: The number of all scalar (non-array) values plus the size of all arrays must not exceed 512.

### **Input**

### Terminal assignment



 $\blacksquare$  9 Labeling on the housing for terminal assignment


Weight Approx.300 g (10.6 oz)

Materials Housing: plastic PC-GF10

Terminals Plug-in screw terminals, 2.5 mm² (14 AWG), 0.1 to 4 mm² (30 to 12 AWG), torque 0.5 to 0.6 Nm (0.37 to 0.44 lbf ft)


### $4\ to\ 20\ mA$ analog input

### 4 to 20 mA analog input (2-wire) with auxiliary voltage output




	Te	erminal block			Function	Dyonoutica		
	A	В	С	D	runction	Properties		
X1 =	11	21	31	41	4 x GND			
X3 =	13	23	33	43	4 x 4 to 20 mA analog input	Maximum input voltage: 35 V Maximum input current: 22 mA Internal resistance: 250 $\Omega$ (suitable for HART communication) Measuring range: 3.8 to 20.5 mA Resolution: 16 bit Accuracy: 0.1% of measuring range		
X4 =	14	24	34	44	4 x auxiliary voltage output for transmitter loop power supply	Output voltage: $28~V_{DC}$ (no-load) $26~V_{DC}$ @ $3~mA$ $20~V_{DC}$ @ $30~mA$ Output current: max. $160~mA$		

### 4 to 20 mA analog input (4-wire)




### Digital input

### Digital input (2-wire) with auxiliary voltage output




### Digital input (3-wire)



### **Output**


### Digital output



You may only use power units that ensure safe electrical isolation according to DIN VDE 0570-2-6 and EN61558-2-6 (SELV / PELV or NEC Class 2) and that are designed as limited-energy circuits.

### RS485 serial interface (Modbus)

- Internal resistance: 96 kΩ
- Protocol: Modbus RTU
- External termination required (  $120 \Omega$ )




### **Power supply**

### Supply voltage



The supply voltage is 24 V DC ( $\pm 20\%$ ). You may only use power units that ensure safe electrical isolation according to DIN VDE 0570-2-6 and EN61558-2-6 (SELV / PELV or NEC Class 2) and that are designed as limited-energy circuits.



You may only use power units that ensure safe electrical isolation according to DIN VDE 0570-2-6 and EN61558-2-6 (SELV / PELV or NEC Class 2) and that are designed as limited-energy circuits.

Power consumption	< 9 W
Voltage interruption (IEC 61000-4-29)	20 ms

### Installation


### Mounting location

The Fieldgate must be housed in a cabinet outside the hazardous area. A protective housing (IP65) must be used if the unit is mounted outdoors.

### Orientation

Vertical or horizontal on DIN rail (HT 35 as per EN 60715).

#### **Dimensions**




■ 10 Dimensions in mm (in)

### Antenna

The devices require an external antenna for wireless communication via UMTS (2G/3G), LTE Cat M1 and Cat NB1 (2G/4G) and WLAN. The antenna can be purchased as an accessory from Endress +Hauser. The antenna cable is screwed onto the connection on the front of the device. The antenna must be mounted outside the cabinet or field housing. In areas with weak reception, it is advisable to first check the communication before securing the antenna permanently.


Connection: SMA connection.



A003111

- 1 Mobile communications networks
- 2 Antenna for Fieldgate FXA42
- 3 SMA connection
- 4 Fieldgate FXA42 Ethernet and 2G/3G/4G
- 5 Control cabinet

16



WLAN receivers


- Uplink to Internet or LAN via router Antenna for Fieldgate FXA42 SMA connection
- 2 3 4 5 6
- Fieldgate FXA42 Ethernet and WLAN Control cabinet

### **Environment**

Ambient temperature range	Normal operation (EN 60068-2-14; Nb; 0.5 K/min): -20 to 60 °C (-4 to 140 °F)				
	Side by side installation: $-20$ to $50$ °C ( $-4$ to $122$ °F)				
Transportation and storage temperature	EN 60068-2-1; Ab; 0.5K/min / EN 60068-2-2; Bb; 0.5K/min: -25 to 85 °C (-13 to 185 °F)				
Humidity	EN 60068-2-30; Db; 0.5 K/min: 5 to 85%; non-condensing				
Condensation	Not permitted				
Climate class	To IEC 60654-1, Class B2				
Installation height as per IEC61010-1 Ed.3	Generally up to 2000 m (6560 ft) above sea level				
Degree of protection	IP20, NEMA1				
Shock resistance	DIN EN 60068-2-27: ±15 g; 11 ms				
Vibration resistance	EN 60068-2-64 / IEC60068-2-64: 202000 Hz 0.01 g <sup>2</sup> /Hz				
Electromagnetic compatibility	<ul> <li>Interference immunity: as per IEC 61326, industrial environment</li> <li>Interference emissions: as per IEC 61326, Class B</li> </ul>				

### Operability

### Display elements (device status indicator / LED)



- 1 Power
- 2 Modem (mobile communications versions) / WLAN / Ethernet
- 3 Network
- 4 Web-PLC


Description	State	Color	Meaning	Note
Power	->-	Green (GN)	Power supply on	
Modem	-\$-	Green (GN)	Power supply for modem on Only mobile communications version	
WLAN	-\$-	Green (GN)	Power supply for WLAN module on	Only WLAN version
Ethernet	-\$-	Green (GN)	Power supply for Ethernet interface on	Only Ethernet version
Network	- C	Green (GN)	Data connection established	Ethernet version: valid fixed IP address configured or DHCP completed successfully
Network	•		Data connection interrupted	Ethernet version: no valid fixed IP address configured or DHCP not completed successfully
Web-PLC		Green (GN)	Editor program for Web-PLC is enabled	
	2 x	Green (GN)	Manual firmware update completed successfully	
	2 x	Green (GN)	Reset to factory settings (factory reset) confirmed	

### Operating elements

### Reset button

The reset button can be accessed through a small hole in the front ( $\rightarrow \blacksquare 14$ ,  $\trianglerighteq 23$ ).


### Card slot




- 1 SIM card
- 2 microSD card

### Integrated Web server

The integrated Web server enables the full control and operation of the Fieldgate and allows users to visualize the current measured values of the connected devices using standard Web browsers. Examples of a few Web pages are provided in the following section.



- 11 Home page in the Web browser
- Select the language
- Opening the online help




■ 12 Grid view in the Web browser

### **Integrated Web-PLC**

The Web-PLC is a Web-based graphic editor solution for basic PLC control functions.

AND, OR, XOR, FF, TIMER and COUNTER operations are provided for implementing simple PLC functions.



■ 13 Graphic editor for PLC control functions

### Certificates and approvals

Current certificates and approvals for the product are available at <a href="https://www.endress.com">www.endress.com</a> on the relevant product page:

- 1. Select the product using the filters and search field.
- 2. Open the product page.

20 Endress+Hauser

A00310

### 3. Select **Downloads**.

#### CE mark

The device meets the legal requirements of the applicable EC directives. These are listed in the corresponding EC declaration of conformity together with the standards applied.

#### **UKCA** marking

The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark.

Contact address Endress+Hauser UK: Endress+Hauser Ltd. Floats Road Manchester M23 9NF United Kingdom www.uk.endress.com

#### **RoHS**

The measuring system meets the substance restrictions of the Directive on the Restriction of the Use of Certain Hazardous Substances 2011/65/EU (RoHS 2) and the Delegated Directive (EU) 2015/863 (RoHS 3).

### External standards and quidelines

Other standards and guidelines that have been considered in the design and development of the

- EN 60529
  - Degrees of protection provided by enclosure (IP code)
- EN 61010-1
  - Safety requirements for electrical equipment for measurement, control and laboratory use
- IEC/EN 61326
  - "Emission in accordance with Class A requirements" Electromagnetic compatibility (EMC requirements)

### Telecommunications approval

### Europe

This device meets the requirements of the Radio Equipment Directive (RED) 2014/53/EU.

### **USA** and Canada

This device complies with Part 15 of the FCC rules.

#### **Federal Communications Commission Notice**

If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the device off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- 1. Reorient or relocate the receiving antenna.
- 2. Increase the separation between the equipment and receiver.
- 3. Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

To ensure that the unit complies with current FCC regulations and safety requirements limiting both maximum RF output power and human exposure to radio frequency radiation, use an antenna with a maximum gain of 2 dBi and a separation distance of at least 20 cm must be maintained between the unit's antenna and the body of the user and any nearby persons at all times and in all applications and uses.

#### Modifications

The FCC requires the user to be notified that any changes or modifications made to this device that are not expressly approved by Endress+Hauser may void the user's authority to operate the equipment.

### **Federal Communications Commission Statement**

This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) This device must accept any interference received, including interference that may cause undesired operation.

### **Wireless Notices**

In some situations or environments, the use of wireless devices may be restricted. Such restrictions may apply aboard airplanes, in vehicles, in hospitals, near explosives, in hazardous locations, etc. If you are uncertain of the policy that applies to the use of this device, please ask for authorization to use it prior to turning it on.

### Other certificates

Other national approvals are available on request.

### Bulgaria

General authorization required for use outdoors and in public.

### Italy

General authorization is required for use outside of own premises.

### Norway

Use can be limited within a 20-km radius of the center of Ny-Alesund.

#### Romania

Use as a secondary device; special license required.


#### Latvia

A national permit is required for outdoor use of the 2.4 GHz frequency.

### **Ordering information**

#### Product design

Four versions of the Fieldgate FXA42 are available. These versions differ in terms of the device features and data transmission technology.



A0030516

■ 14 Fieldgate FXA42 versions and design

- A FXA42-A Ethernet
- B FXA42-B Ethernet and WLAN
- C FXA42-C Ethernet and 2G/3G
- D FXA42-D Ethernet and LTE Cat M1 and Cat NB1 (2G/4G)
- 1 Slot for memory card, card type: microSD
- 2 Status LED for modem / WLAN / Ethernet
- 3 Status LED for supply voltage
- 4, 5 Input modules with analog input, digital input, current source and reference potential
- 6 Status LED for network
- 7 Status LED for Web PLC
- 8, 9 Ethernet connections
- 10 Reset button
- 11 Power supply for Fieldgate FXA42, power supply for digital outputs, digital outputs
- 12 RS-485 serial interface
- 13 Connection for antenna (only WLAN and mobile telecommunications versions)
- 14 Slot for SIM card (only mobile telecommunications versions)

### Supported frequency bands for mobile telecommunications

FXA42-C: supported frequency bands UMTS (2G/3G)

2G

Band 2 (1900 MHz), Band 3 (1800 MHz), Band 5 (850 MHz), Band 8 (900 MHz)

3G

Band 1 (2100 MHz), Band 2 (1900 MHz), Band 4 (1700 MHz), Band 5 (850 MHz), Band 6 (800 MHz), Band 8 (900 MHz)

FXA42-D: supported frequency bands LTE Cat M1 and Cat NB1 (2G/4G)

2G

Band 2 (1900 MHz), Band 3 (1800 MHz), Band 5 (850 MHz), Band 8 (900 MHz)

4G

Band 1 (2100 MHz), Band 2 (1900 MHz), Band 3 (1800 MHz), Band 4 (AWS 1700 MHz), Band 5 (850 MHz), Band 8 (900 MHz), Band 12 (700 MHz), Band 13 (700 MHz), Band 18 (800 MHz), Band 19 (800 MHz), Band 20 (800 MHz), Band 26 (850 MHz), Band 28 (700 MHz)

### Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com-> Click "Corporate"
   -> Select your country -> Click "Products" -> Select the product using the filters and search field -> Open product page -> The "Configure" button to the right of the product image opens the Product Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com
  - Product Configurator the tool for individual product configuration

     Up-to-the-minute configuration data
    - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
    - Automatic verification of exclusion criteria
    - Automatic creation of the order code and its breakdown in PDF or Excel output format
    - Ability to order directly in the Endress+Hauser Online Shop
- Note that when choosing the contract, the SMS function must be agreed to allow use of this function. The mobile telecommunications contract for the device must support this function.

### Accessories

### Device-specific accessories

Power unit

Power unit for power supply Material number: 71327426

Antenna

Antenna with SMA connection for mobile telecommunications or WLAN operation

Material number: 71327395 SD card (card type: microSD)

On request

Communication modules

 Datexel DAT8017-I server unit: analog to Modbus TCP converter Material number: 71375710

 Rapsystems HG1 Plus: HART to Modbus gateway Material number: 71327424

Phoenix Contact: HART Ethernet multiplexer head module

Material number: 71363548

Phoenix Contact: 4-channel HART extension module

Material number: 71363561

• Phoenix Contact: 8-channel HART extension module

Material number: 71363582

### Communication-specific accessories

### SupplyCare Enterprise SCE30B

Inventory management software that displays the level, volume, mass, temperature, pressure, density or other parameters of tanks. The parameters are recorded and transmitted by means of gateways like Fieldgate FXA42, Connect Sensor FXA30B or other gateway types.

This Web-based software is installed on a local server and can also be visualized and operated with mobile terminals such as a smartphone or tablet.



For details, see Technical Information TI01228S and Operating Instructions BA00055S

#### SupplyCare Hosting SCH30

Inventory management software that displays the level, volume, mass, temperature, pressure, density or other parameters of tanks. The parameters are recorded and transmitted by means of gateways like Fieldgate FXA42, Connect Sensor FXA30B or other gateway types. SupplyCare Hosting is offered as a hosting service (Software as a Service, SaaS). In the Endress +Hauser portal, the user is provided with the data over the Internet.



For details, see Technical Information TI01229S and Operating Instructions BA00050S  $\,$ 

24

### Supplementary documentation

The following document types are available in the Download Area of the Endress+Hauser website: www.endress.com  $\rightarrow$  Download:

### Standard documentation

The following documentation is available for the Fieldgate FXA42:

Brief Operating Instructions
 Document code: KA01246S

 Operating Instructions
 Document code: BA01778S

## Registered trademarks

### Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

#### Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA





www.addresses.endress.com