

EU - Type Examination Certificate

(1)

(2) Equipment and protective systems intended for use in potentially explosive atmospheres – **Directive 2014/34/EU**

(3) EU - Type Examination Certificate Number

EPS 18 ATEX 1 152 X

Revision 5

(4) Equipment: Insert iTHERM type TS111, TS211, TS212
Thermometer iTHERM type TM111, TM131, TM112, TM151, TM152

(5) Manufacturer: Endress+Hauser Wetzler GmbH + Co. KG

(6) Address: Obere Wank 1
87484 Nesselwang
Germany

(7) This equipment and any acceptable variation thereto are specified in the annex to this certificate and the documentation therein referred to.

(8) Bureau Veritas Consumer Products Services Germany GmbH, notified body No. 2004 in accordance with Article 21 given in the Directive 2014/34/EU of the European Parliament and of the Council of 26 February 2014, certifies that this equipment has been found to comply with the essential health and safety requirements relating to the design and construction of equipment and protective systems intended for use in potentially explosive atmospheres, given in Annex II of the Directive. The examination and test results are recorded in the confidential documentation under the reference number 18TH0259.

(9) Compliance with the essential health and safety requirements has been assured by compliance with:

EN IEC 60079-0:2018

EN 60079-11:2012

EN 60079-26:2015

IEC TS 60079-40:2015

(10) If the sign "X" is placed after the certificate number, it indicates that the equipment is subject to special conditions for safe use specified in the annex to this certificate.

(11) This EU - Type Examination Certificate relates only to the design and construction of the specified equipment in accordance with Directive 2014/34/EU. Further requirements of this Directive apply to the manufacture of this equipment and its placing on the market. Those requirements are not covered by this certificate.

(12) The marking of the equipment shall include the following:

II 1G Ex ia IIC T6...T1 Ga

II 1/2G Ex ia IIC T6...T1 Ga/Gb

II 1/2D Ex ia IIIC T₂₀₀85°C... T₂₀₀450°C Da/Db



Certification department of explosion protection

Ulrich Feike

Tuerkheim, 2023-11-03

Certificates without signature and seal are void. This certificate is allowed to be distributed only if not modified. Extracts or modifications must be authorized by Bureau Veritas Consumer Products Services Germany GmbH.

(13)

Annex

(14) **EU - Type Examination Certificate EPS 18 ATEX 1 152 X**

Revision 5

(15) Description of equipment:

The Insert for Thermometers iTHERM, type TS111-..., TS211-... and TS212-..., are used to convert the temperature of a process medium into an electrical signal.

The insert is used with a terminal head or field transmitter, made of aluminum, stainless steel or conductive plastic. The terminal head contains either a temperature transmitter or connection terminals for connection of the TRD or TC sensor to an external temperature transmitter.

The Thermometers iTHERM type TM111, TM112, TM131, TM151 and TM152 consist of RTD or Thermocouple insert iTHERM, type TS111-..., TS211-... and TS212-... and a terminal head or field transmitter with a thermowell.

The sensor is a single or dual Pt100 resistance element (wire wound or thin film) or a thermocouple element, mounted in a stem with a diameter of 3 mm or 6 mm and a length depending on the application.

The sensor can be used in a 3- or a 4-wire measurement system or in a dual 2- or 3-wire measurement system if a dual temperature sensor element is mounted.

The terminal head or field transmitter, including the cable entry devices provides a degree of protection of at least IP2X in accordance with EN 60529 for application in explosive gas atmospheres.

The terminal head or field transmitter, including the cable entry devices provides a degree of protection of at least IP6X in accordance with EN IEC 60079-0 and EN 60529 for application in explosive dust atmospheres.

The equipment is intended for the application inside the explosive hazardous area.

EU - Type Examination Certificate EPS 18 ATEX 1 152 X

Revision 5

Electrical data:

In type of protection intrinsic safety Ex ia IIC and Ex ia IIIC, only for connection to a certified intrinsically safe circuit with the following maximum values:

Transmitter	Ui	Ii	Pi	Ci	Li
TMT71/TMT72	30 V	100 mA	800 mW	0	0
TMT82	30 V	130 mA	800 mW	0	0
TMT142 HART	30V	300 mA	1000 mW	5 nF	0
TMT162 HART	30 V	300 mA	1000 mW	0	0
TMT162 PA/FF	FISCO field device				
TMT84, TMT85	FISCO field device				
TMT86	FISCO field device				
Terminal block	30 V	140 mA	1000 mW	See tables below	
Flying leads	30 V	140 mA	1000 mW	See tables below	

Ci and Li, for types TS111/ TS211 and TS212:

Sensor type	Insertion Length IL		Flying leads		Terminal block	
	Ci/m	Li/m	Ci	Li	Ci	Li
Single	200 pF	1 µH	56.4 pF	282 nH	4.6 pF	23 nH
Dual	400 pF	2 µH	113 pF	564 nH	9.2 pF	46 nH

Calculation formula for options with flying leads and terminal block only:

$$C_i = C_{i \text{ Insertion length IL}} \times IL + C_{i \text{ Flying leads}}$$

$$L_i = L_{i \text{ Insertion length IL}} \times IL + L_{i \text{ Flying leads}}$$

$$C_i = C_{i \text{ Insertion length IL}} \times IL + C_{i \text{ Terminal block}}$$

$$L_i = L_{i \text{ Insertion length IL}} \times IL + L_{i \text{ Terminal block}}$$

EU - Type Examination Certificate EPS 18 ATEX 1 152 X

Revision 5

Thermal data:

The dependency of the ambient and process temperatures upon the temperature class for assembly with transmitters:

Type	Assembled transmitter	Temperature class	Ambient temperature range housing Ta	Maximum surface temperature housing
TM111, TM112, TM131,	TMT84, TMT85 TMT162 PA/FF	T6	-40 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-40 °C ≤ Ta ≤ +70 °C	T100 °C
		T4	-40 °C ≤ Ta ≤ +85 °C	T135 °C
TM151, TM152, TS111,	TMT71, TMT72, TMT86 ¹ TMT162 HART TMT142 HART	T6	-50 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-50 °C ≤ Ta ≤ +70 °C	T100 °C
		T4	-50 °C ≤ Ta ≤ +85 °C	T135 °C
TS211, TS212	TMT82 ¹	T6	-50 °C ≤ Ta ≤ +58 °C	T85 °C
		T5	-50 °C ≤ Ta ≤ +75 °C	T100 °C
		T4	-50 °C ≤ Ta ≤ +85 °C	T135 °C
	TMT8x, TMT7x with display	T6	-40 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-40 °C ≤ Ta ≤ +70 °C	T100 °C
		T4	-40 °C ≤ Ta ≤ +85 °C	T135 °C

¹ Lower temperature of -52 °C for TMT82 only with gas Ex ia IIC Ga/Gb and only without display.

Type	Assembled transmitter	Insert diameter	Process temperature range Tp	Temperature class/ Maximum surface temperature sensor
TM111, TM112, TM131,	TMT8x, TMT7x TMT142	3mm (1/8"), 3mm (1/8") dual,	-50 °C ≤ Tp ≤ +66 °C -50 °C ≤ Tp ≤ +81 °C -50 °C ≤ Tp ≤ +116 °C	T6 / T85 °C T5 / T100 °C T4 / T135 °C
TM151, TM152, TS111, TS211, TS212		6mm (1/4"), dual	-50 °C ≤ Tp ≤ +181 °C -50 °C ≤ Tp ≤ +276 °C -50 °C ≤ Tp ≤ +426 °C	T3 / T200 °C T2 / T300 °C T1 / T450 °C
		6mm (1/4")	-50 °C ≤ Tp ≤ +73 °C -50 °C ≤ Tp ≤ +88 °C -50 °C ≤ Tp ≤ +123 °C -50 °C ≤ Tp ≤ +188 °C -50 °C ≤ Tp ≤ +283 °C -50 °C ≤ Tp ≤ +433 °C	T6 / T85 °C T5 / T100 °C T4 / T135 °C T3 / T200 °C T2 / T300 °C T1 / T450 °C

EU - Type Examination Certificate EPS 18 ATEX 1 152 X

Revision 5

Type	Assembled transmitter	Insert diameter	Process temperature range T_p	Temperature class/ Maximum surface temperature sensor
TM131, TM151, TM152, TS211, TS212	TMT162	3mm (1/8"), 3mm (1/8") dual, 6mm (1/4"), dual	$-50\text{ °C} \leq T_p \leq +64\text{ °C}$	T6 / T85 °C
			$-50\text{ °C} \leq T_p \leq +79\text{ °C}$	T5 / T100 °C
			$-50\text{ °C} \leq T_p \leq +114\text{ °C}$	T4 / T135 °C
			$-50\text{ °C} \leq T_p \leq +179\text{ °C}$	T3 / T200 °C
			$-50\text{ °C} \leq T_p \leq +279\text{ °C}$	T2 / T300 °C
			$-50\text{ °C} \leq T_p \leq +424\text{ °C}$	T1 / T450 °C
		6mm (1/4")	$-50\text{ °C} \leq T_p \leq +71\text{ °C}$	T6 / T85 °C
			$-50\text{ °C} \leq T_p \leq +86\text{ °C}$	T5 / T100 °C
			$-50\text{ °C} \leq T_p \leq +121\text{ °C}$	T4 / T135 °C
			$-50\text{ °C} \leq T_p \leq +186\text{ °C}$	T3 / T200 °C
			$-50\text{ °C} \leq T_p \leq +286\text{ °C}$	T2 / T300 °C
			$-50\text{ °C} \leq T_p \leq +431\text{ °C}$	T1 / T450 °C

The dependency of the ambient and process temperatures upon the temperature class for assembly without transmitter (terminal block or flying leads):

Type	Insert diameter	Temperature class/ Maximum surface temperature	Maximum allowed process temperature (sensor)				
			T_p (process)				
			$P_i \leq 50\text{ mW}$	$P_i \leq 100\text{ mW}$	$P_i \leq 200\text{ mW}$	$P_i \leq 500\text{ mW}$	$P_i \leq 650\text{ mW}$
TS111, TS211, TS212	3mm (1/8"), 3mm (1/8") dual or 6mm (1/4") dual	T1 / T450 °C	426 °C	415 °C	396 °C	343 °C	333 °C
		T2 / T300 °C	276 °C	265 °C	246 °C	193 °C	183 °C
		T3 / T200 °C	181 °C	170 °C	151 °C	98 °C	88 °C
		T4 / T135 °C	116 °C	105 °C	86 °C	33 °C	23 °C
		T5 / T100 °C	81 °C	70 °C	51 °C	-2 °C	-12 °C
		T6 / T85 °C	66 °C	55 °C	36 °C	-17 °C	-27 °C
	6mm (1/4")	T1 / T450 °C	433 °C	428 °C	420 °C	398 °C	388 °C
		T2 / T300 °C	283 °C	278 °C	270 °C	248 °C	238 °C
		T3 / T200 °C	188 °C	183 °C	175 °C	153 °C	143 °C
		T4 / T135 °C	123 °C	118 °C	110 °C	88 °C	78 °C
		T5 / T100 °C	88 °C	83 °C	75 °C	53 °C	43 °C
		T6 / T85 °C	73 °C	68 °C	60 °C	38 °C	28 °C

EU - Type Examination Certificate EPS 18 ATEX 1 152 X

Revision 5

Type	Insert diameter	Temperature class/ Maximum surface temperature	Maximum allowed process temperature (sensor) Tp (process)			Ambient temperature (housing), Ta (ambient)*
			Pi ≤ 750 mW	Pi ≤ 800 mW	Pi ≤ 1000 mW	
TS111, TS211, TS212	3mm (1/8"), 3mm (1/8") (dual) or 6mm (1/4") dual	T1 / T450 °C	320 °C	312 °C	280 °C	-40 °C ≤ Ta ≤ +130 °C
		T2 / T300 °C	170 °C	162 °C	130 °C	-40 °C ≤ Ta ≤ +130 °C
		T3 / T200 °C	75 °C	62 °C	30 °C	-40 °C ≤ Ta ≤ +130 °C
		T4 / T135 °C	10 °C	2 °C	-30 °C	-40 °C ≤ Ta ≤ +116 °C
		T5 / T100 °C	-25 °C	-33 °C	---	-40 °C ≤ Ta ≤ +81 °C
		T6 / T85 °C	-40 °C	---	---	-40 °C ≤ Ta ≤ +66 °C
	6mm (1/4")	T1 / T450 °C	381 °C	377 °C	361 °C	-40 °C ≤ Ta ≤ +130 °C
		T2 / T300 °C	231 °C	227 °C	211 °C	-40 °C ≤ Ta ≤ +130 °C
		T3 / T200 °C	136 °C	127 °C	111 °C	-40 °C ≤ Ta ≤ +130 °C
		T4 / T135 °C	71 °C	67 °C	51 °C	-40 °C ≤ Ta ≤ +123 °C
		T5 / T100 °C	36 °C	32 °C	16 °C	-40 °C ≤ Ta ≤ +88 °C
		T6 / T85 °C	21 °C	17 °C	1 °C	-40 °C ≤ Ta ≤ +73 °C

* The ambient temperature at the terminal head may be directly influenced by the process temperature, but is restricted to the range -40 °C ... +130 °C besides for types TA30A, TA30D and TA30H and sensor type TS111, TS211 or TS212, with a restricted range of -50 °C ... +130 °C.

The lower temperature of -60 °C is only possible with the marking Ex ia IIC Ga/Gb.

For thermometers with two mounted head transmitters the allowed ambient temperature is up to 12K lower than each head transmitter's certified ambient temperature.

For thermocouple inserts, the temperature class T6...T1 and the maximum surface temperature T85 °C ... T450 °C are equal to the process temperature.

EU - Type Examination Certificate EPS 18 ATEX 1 152 X

Revision 5

(16) Reference number: 18TH0259

(17) Special conditions for safe use:

From the safety point of view, the circuit of versions of the following temperature sensors and inserts shall be considered to be connected to ground (for details, the instruction manual, provided with the equipment, shall be observed):

- Type TS111, TS211 and TS212 with diameter 3mm or 1/8", single or dual
- Type TS111, TS211 and TS212 with diameter 6mm or 1/4" dual

The thermometer must be installed so, that even in the event of rare incidents, an ignition source due to impact friction between the enclosure and iron/steel is excluded.

Avoid electrostatic charging of the plastic housing according to EN 60079-0 7.4.2 e) (do not rub dry).

(18) Essential health and safety requirements:

Met by compliance with standards.

Certification department of explosion protection

Tuerkheim, 2023-11-03



(1) **EU - Baumusterprüfbescheinigung**

(2) Geräte und Schutzsysteme zur bestimmungsgemäßen Verwendung in explosionsgefährdeten Bereichen –
Richtlinie 2014/34/EU

(3) EU - Baumusterprüfbescheinigungsnummer

EPS 18 ATEX 1 152 X

Revision 5

(4) Gerät: Einsatz iTHERM Typ TS111, TS211, TS212
Thermometer iTHERM Typ TM111, TM131, TM112, TM151, TM152

(5) Hersteller: Endress+Hauser Wetzer GmbH + Co. KG

(6) Anschrift: Obere Wank 1
87484 Nesselwang
Deutschland

(7) Die Bauart dieses Gerätes sowie die verschiedenen zulässigen Ausführungen sind in der Anlage zu dieser EU - Baumusterprüfbescheinigung festgelegt.

(8) Bureau Veritas Consumer Products Services Germany GmbH bescheinigt als benannte Stelle Nr. 2004 nach Artikel 21 der Richtlinie 2014/34/EU des Europäischen Parlaments und des Rates vom 26. Februar 2014 die Erfüllung der grundlegenden Sicherheits- und Gesundheitsanforderungen für die Konzeption und den Bau von Geräten und Schutzsystemen zur bestimmungsgemäßen Verwendung in explosionsgefährdeten Bereichen gemäß Anhang II der Richtlinie. Die Ergebnisse der Prüfung sind in der vertraulichen Dokumentation unter der Referenznummer 18TH0259 festgelegt.

(9) Die grundlegenden Sicherheits- und Gesundheitsanforderungen werden erfüllt durch Übereinstimmung mit:

EN IEC 60079-0:2018

EN 60079-11:2012

EN 60079-26:2015

IEC TS 60079-40:2015

(10) Falls das Zeichen „X“ hinter der Bescheinigungsnummer steht, wird auf besondere Bedingungen für die sichere Anwendung des Gerätes in der Anlage zu dieser Bescheinigung hingewiesen.

(11) Diese EU - Baumusterprüfbescheinigung bezieht sich nur auf Konzeption und Prüfung des festgelegten Gerätes gemäß Richtlinie 2014/34/EU. Weitere Anforderungen dieser Richtlinie gelten für die Herstellung und das Inverkehrbringen dieses Gerätes. Diese Anforderungen werden nicht durch diese Bescheinigung abgedeckt.

(12) Die Kennzeichnung des Gerätes muss die folgenden Angaben enthalten:

II 1G Ex ia IIC T6...T1 Ga



II 1/2G Ex ia IIC T6...T1 Ga/Gb

II 1/2D Ex ia IIC T₂₀₀85°C... T₂₀₀450°C Da/Db

Zertifizierungsstelle Explosionsschutz

Türkheim, 03.11.2023

Ulrich Feike

Bescheinigungen ohne Unterschrift und Siegel haben keine Gültigkeit. Diese Bescheinigung darf nur unverändert weiterverbreitet werden. Auszüge oder Änderungen bedürfen der Genehmigung von Bureau Veritas Consumer Products Services Germany GmbH.

(13)

Anlage

(14) **EU – Baumusterprüfbescheinigung EPS 18 ATEX 1 152 X**

Revision 5

(15) Beschreibung des Gerätes:

Die Einsätze iTHERM Typ TS111-..., TS211-... und TS212-..., für Thermometer, dienen der Umwandlung von Temperaturen eines Prozessmediums in ein elektrisches Signal.

Der Einsatz wird mit einem Anschlusskopf oder Feldtransmitter aus Aluminium, Edelstahl oder leitfähigem Kunststoff verwendet. Der Anschlusskopf enthält entweder einen Temperaturtransmitter oder Anschlussklemmen für den Anschluss des RTD- oder TC-Sensors an einen externen Temperaturtransmitter.

Die Thermometer iTHERM Typ TM111, TM112, TM131, TM151 und TM152 bestehen aus RTD oder Thermoelementeinsatz iTHERM, Typ TS111-..., TS211-... und TS212-... und einem Anschlusskopf- oder Feldtransmitter mit Schutzrohr.

Der Sensor ist ein Widerstandselement aus einem bis zwei Pt100-Elementen (Draht oder dünne Folie) oder ein Thermoelement. Diese sind in einem Schaft mit einem Durchmesser von 3 mm oder 6 mm und einer Länge je nach Anwendung montiert.

Der Sensor kann in einem 3- oder 4-Leiter-Messsystem und in einem 2- oder 3-Leiter-Messsystem verwendet werden. Dazu muss ein Doppeltemperatursensorelement montiert sein.

Der Anschlusskopf- oder Feldtransmitter einschließlich der Kabeleinführungsvorrichtung bietet einen Schutzgrad von mindestens IP2X gemäß EN 60529 für den Einsatz in explosionsgefährdeten Gasatmosphären.

Der Anschlusskopf- oder Feldtransmitter einschließlich der Kabeleinführung bietet eine Schutzart von mindestens IP6X gemäß EN IEC 60079-0 und EN 60529 für den Einsatz in explosionsgefährdeten Bereichen.

Das Gerät ist für den Einsatz im explosionsgefährdeten Bereich gemäß Kennzeichnung vorgesehen.

EU – Baumusterprüfbescheinigung EPS 18 ATEX 1 152 X

Revision 5

Elektrische Daten:

In Zündschutzart Eigensicherheit Ex ia IIC und Ex ia IIIC. Die gilt nur für den Anschluss an einen bescheinigten eigensicheren Stromkreis mit folgenden Höchstwerten:

Sensor/ Transmitter	Ui	Ii	Pi	Ci	Li
TMT71/TMT72	30 V	100 mA	800 mW	0	0
TMT82	30 V	130 mA	800 mW	0	0
TMT142 HART	30 V	300 mA	1000 mW	5 nF	0
TMT162 HART	30 V	300 mA	1000 mW	0	0
TMT162 PA/FF	FISCO Feldgerät				
TMT84, TMT85	FISCO Feldgerät				
TMT86	FISCO Feldgerät				
Klemmen	30 V	140 mA	1000 mW	Siehe Tabellen unten	
Freie Kabelenden	30 V	140 mA	1000 mW	Siehe Tabellen unten	

C_i and L_i für Typen TS111/ TS211 und TS212:

Sensortyp	Einsatzlänge IL		Freie Kabelenden		Klemmen	
	Ci/m	Li/m	Ci	Li	Ci	Li
Single	200 pF	1 µH	56,4 pF	282 nH	4,6 pF	23 nH
Dual	400 pF	2 µH	113 pF	564 nH	9,2 pF	46 nH

Berechnungsformel für die Optionen mit freien Kabelenden und Klemmen:

$$C_i = C_i \text{ Einsatzlänge IL} \times IL + C_i \text{ freie Kabelenden}$$

$$L_i = L_i \text{ Einsatzlänge IL} \times IL + L_i \text{ freie Kabelenden}$$

$$C_i = C_i \text{ Einsatzlänge IL} \times IL + C_i \text{ Klemmen}$$

$$L_i = L_i \text{ Einsatzlänge IL} \times IL + L_i \text{ Klemmen}$$

EU – Baumusterprüfbescheinigung EPS 18 ATEX 1 152 X
Revision 5
Thermische Daten:

Abhängigkeit der Umgebungstemperatur und Prozesstemperatur in Verbindung mit der Temperaturklasse und den verwendeten Transmittern:

Typ	Sensor/ Transmitter	Temperatur- klasse	Umgebungs- temperaturbereich Ta	Maximale Oberflächen- temperatur
TM111, TM112, TM131,	TMT84, TMT85	T6	-40 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-40 °C ≤ Ta ≤ +70 °C	T100 °C
		T4	-40 °C ≤ Ta ≤ +85 °C	T135 °C
TM151, TM152, TS111,	TMT71, TMT72, TMT86 ¹	T6	-50 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-50 °C ≤ Ta ≤ +70 °C	T100 °C
	TMT162 PA/FF	T4	-50 °C ≤ Ta ≤ +85 °C	T135 °C
TS211, TS212	TMT142 HART	T6	-50 °C ≤ Ta ≤ +58 °C	T85 °C
		T5	-50 °C ≤ Ta ≤ +75 °C	T100 °C
		T4	-50 °C ≤ Ta ≤ +85 °C	T135 °C
	TMT82 ¹	T6	-40 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-40 °C ≤ Ta ≤ +70 °C	T100 °C
		T4	-40 °C ≤ Ta ≤ +85 °C	T135 °C
	TMT8x, TMT7x mit Anzeige	T6	-40 °C ≤ Ta ≤ +55 °C	T85 °C
		T5	-40 °C ≤ Ta ≤ +70 °C	T100 °C
		T4	-40 °C ≤ Ta ≤ +85 °C	T135 °C

¹ Niedrigere Temperatur von -52°C bei TMT82 nur bei Gas Ex ia IIC Ga/Gb und nur ohne Display.

Typ	Sensor/ Transmitter	Durchmesser Einsatz	Prozesstemperatur Tp	Temperaturklasse/ Maximale Oberflächen- temperatur
TM111, TM112, TM131,	TMT8x,	3mm (1/8"),	-50 °C ≤ Tp ≤ +66 °C	T6 / T85 °C
		3mm (1/8")	-50 °C ≤ Tp ≤ +81 °C	T5 / T100 °C
		dual,	-50 °C ≤ Tp ≤ +116 °C	T4 / T135 °C
TM151, TM152, TS111,	TMT7x	6mm (1/4")	-50 °C ≤ Tp ≤ +181 °C	T3 / T200 °C
		dual	-50 °C ≤ Tp ≤ +276 °C	T2 / T300 °C
			-50 °C ≤ Tp ≤ +426 °C	T1 / T450 °C
TS211, TS212	TMT142	6mm (1/4")	-50 °C ≤ Tp ≤ +73 °C	T6 / T85 °C
			-50 °C ≤ Tp ≤ +88 °C	T5 / T100 °C
			-50 °C ≤ Tp ≤ +123 °C	T4 / T135 °C
			-50 °C ≤ Tp ≤ +188 °C	T3 / T200 °C
			-50 °C ≤ Tp ≤ +283 °C	T2 / T300 °C
			-50 °C ≤ Tp ≤ +433 °C	T1 / T450 °C

EU – Baumusterprüfbescheinigung EPS 18 ATEX 1 152 X

Revision 5

Typ	Sensor/ Transmitter	Durchmesser Einsatz	Prozesstemperatur Tp	Temperaturklasse/ Maximale Oberflächen- temperatur
TM131, TM151, TM152, TS211, TS212	TMT162	3mm (1/8"),	-50 °C ≤ Tp ≤ +64 °C	T6 / T85 °C
		3mm (1/8")	-50 °C ≤ Tp ≤ +79 °C	T5 / T100 °C
		dual,	-50 °C ≤ Tp ≤ +114 °C	T4 / T135 °C
		6mm (1/4")	-50 °C ≤ Tp ≤ +179 °C	T3 / T200 °C
		dual	-50 °C ≤ Tp ≤ +279 °C	T2 / T300 °C
			-50 °C ≤ Tp ≤ +424 °C	T1 / T450 °C
			-50 °C ≤ Tp ≤ +71 °C	T6 / T85 °C
			-50 °C ≤ Tp ≤ +86 °C	T5 / T100 °C
			-50 °C ≤ Tp ≤ +121 °C	T4 / T135 °C
			-50 °C ≤ Tp ≤ +186 °C	T3 / T200 °C
			-50 °C ≤ Tp ≤ +286 °C	T2 / T300 °C
			-50 °C ≤ Tp ≤ +431 °C	T1 / T450 °C

Abhängigkeit der Umgebungstemperatur und Prozesstemperatur in Verbindung mit der Temperaturklasse bei Bestückung ohne Transmitter/ Sensor (freie Kabelenden bzw. Klemmen):

Typ	Durch- messer Einsatz	Temperatur- klasse/ Maximale Oberflächen- temperatur	Maximal erlaubte Prozesstemperatur (Sensor)				
			Tp (Prozess)				
			Pi ≤ 50 mW	Pi ≤ 100 mW	Pi ≤ 200 mW	Pi ≤ 500 mW	Pi ≤ 650 mW
TS111, TS211, TS212	3mm (1/8"), 3mm (1/8") dual oder 6mm (1/4") dual	T1 / T450 °C	426 °C	415 °C	396 °C	343 °C	333 °C
		T2 / T300 °C	276 °C	265 °C	246 °C	193 °C	183 °C
		T3 / T200 °C	181 °C	170 °C	151 °C	98 °C	88 °C
		T4 / T135 °C	116 °C	105 °C	86 °C	33 °C	23 °C
		T5 / T100 °C	81 °C	70 °C	51 °C	-2 °C	-12 °C
		T6 / T85 °C	66 °C	55 °C	36 °C	-17 °C	-27 °C
	6mm (1/4")	T1 / T450 °C	433 °C	428 °C	420 °C	398 °C	388 °C
		T2 / T300 °C	283 °C	278 °C	270 °C	248 °C	238 °C
		T3 / T200 °C	188 °C	183 °C	175 °C	153 °C	143 °C
		T4 / T135 °C	123 °C	118 °C	110 °C	88 °C	78 °C
		T5 / T100 °C	88 °C	83 °C	75 °C	53 °C	43 °C
		T6 / T85 °C	73 °C	68 °C	60 °C	38 °C	28 °C

EU – Baumusterprüfbescheinigung EPS 18 ATEX 1 152 X

Revision 5

Typ	Durch- messer Einsatz	Temperatur- klasse/ Maximale Oberflächen- temperatur	Maximal erlaubte Prozesstemperatur			Umgebungs- temperatur (Gehäuse) Ta (Umgebung) *
			Pi ≤ 750 mW	Pi ≤ 800 mW	Pi ≤ 1000 mW	
TS111, TS211, TS212	3mm (1/8"), 3mm (1/8") (dual) oder 6mm (1/4") dual	T1 / T450 °C	320 °C	312 °C	280 °C	-40 °C ≤ Ta ≤ +130 °C
		T2 / T300 °C	170 °C	162 °C	130 °C	-40 °C ≤ Ta ≤ +130 °C
		T3 / T200 °C	75 °C	62 °C	30 °C	-40 °C ≤ Ta ≤ +130 °C
		T4 / T135 °C	10 °C	2 °C	-30 °C	-40 °C ≤ Ta ≤ +116 °C
		T5 / T100 °C	-25 °C	-33 °C	---	-40 °C ≤ Ta ≤ +81 °C
		T6 / T85 °C	-40 °C	---	---	-40 °C ≤ Ta ≤ +66 °C
	6mm (1/4")	T1 / T450 °C	381 °C	377 °C	361 °C	-40 °C ≤ Ta ≤ +130 °C
		T2 / T300 °C	231 °C	227 °C	211 °C	-40 °C ≤ Ta ≤ +130 °C
		T3 / T200 °C	136 °C	127 °C	111 °C	-40 °C ≤ Ta ≤ +130 °C
		T4 / T135 °C	71 °C	67 °C	51 °C	-40 °C ≤ Ta ≤ +123 °C
		T5 / T100 °C	36 °C	32 °C	16 °C	-40 °C ≤ Ta ≤ +88 °C
		T6 / T85 °C	21 °C	17 °C	1 °C	-40 °C ≤ Ta ≤ +73 °C

*Die Umgebungstemperatur des Kopftransmitters wird durch die Prozesstemperatur direkt beeinflusst und ist eingeschränkt auf -40 °C ... +130 °C außer für die Typen TA30A, TA30D und TA30H sowie Sensortyp TS111, TS211 oder TS212, die im Bereich -50 °C ... +130 °C eingesetzt werden können.
Die niedrigere Temperatur von -60 °C ist nur mit der Kennzeichnung Ex ia IIC Ga/Gb möglich.

Für Thermometer mit zwei bestückten Kopftransmittern ist der erlaubte Umgebungstemperaturbereich um 12K niedriger als beim Einzeltransmitter.

Für Thermoelement-Einsätze ist die Temperaturklasse T6...T1 und die maximale Oberflächentemperatur T85 °C ... T450 °C gleich der Prozesstemperatur.

EU – Baumusterprüfbescheinigung EPS 18 ATEX 1 152 X

Revision 5

(16) Referenznummer: 18TH0259

(17) Besondere Bedingungen:

Aus sicherheitstechnischer Sicht ist der Stromkreis der Versionen der folgenden Temperatursensoren und -einsätze als mit der Erde verbunden zu betrachten (für Einzelheiten ist die mit dem Gerät mitgelieferte Betriebsanleitung zu beachten):

- Typ TS111, TS211 und TS212 mit 3mm oder 1/8" Durchmesser, einzeln oder dual
- Typ TS111, TS211 und TS212 mit 6mm oder 1/4" Durchmesser, dual

Das Thermometer muss so installiert werden, dass auch in selten auftretenden Fällen eine Zündquelle durch Stoß oder Reibung zwischen Metall/Stahl und dem Anschlusskopf ausgeschlossen ist.

Die elektrostatische Aufladung des Kunststoffgehäuses gemäß EN 60079-0 7.4.2 e) ist zu vermeiden (nur mit feuchtem Tuch reinigen).

(18) Grundlegende Sicherheits- und Gesundheitsanforderungen:

Durch Übereinstimmung mit Normen abgedeckt.

Zertifizierungsstelle Explosionsschutz

Türkheim, 03.11.2023

