



Certificate of Compliance

Certificate:	2551823	Master Contract:	160686
Project:	80224103	Date Issued:	2024-11-13
Issued to:	Endress+Hauser Flowtec AG Kagenstrasse 7 Reinach, Basel-Country 4153 Switzerland		
	Attention: Daniel Bosshard		

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.



Issued by: Anil Sodhi
Anil Sodhi, P. Eng.

PRODUCTS

Class 2258 03 PROCESS CONTROL EQUIPMENT - Intrinsically Safe and Non - Incendive Systems - For Hazardous Locations
Class 2258 83 PROCESS CONTROL EQUIPMENT - Intrinsically Safe and Non-Incendive Systems-For Hazardous Locations-
Certified to U.S. Standards

Class I, Division 2, Groups A, B, C and D:



Certificate: 2551823

Project: 80224103

Master Contract: 160686

Date Issued: 2024-11-13

Product	Proline Promag 400 Magnetic-inductive flow measuring system; compact version providing exciter coil circuits and non-incendive electrode circuits to Integral Sensor Model Promag W, L, D. Proline Promag W 400, Model 5W4Cbb-ccdLfA/M/Q/Rhiklllmn+#### and O5W4Cbb-ccdLfA/M/Q/Rhiklllmnp + #### Proline Promag L 400, Model 5L4Cbb-ccLfA/M/Q/Rhiklllmn+#### and O5L4Cbb-ccLfA/M/Q/Rhiklllmnp + #### Proline Promag D 400, Model 5D4Cbb-ccLfA/M/Q/Rhiklllmn+#### and O5D4Cbb-ccLfA/M/Q/Rhiklllmnp + #### Note: Must be installed as per control drawing FES0196*
Electrical Rating	Rated input: 100-240 V AC, 50/60Hz (+/- 4Hz), 30VA 24 V AC, 50/60Hz (+/- 4Hz), 10VA 24 V DC, 8.0W
Enclosure rating	Type 4X, IP 66/67
Temp. code and ambient temperature	T4 (-40°C to + 60°C)
Process temperature and MWP	Max process temperature: +90°C Maximum Working Pressure (MWP): 160bar (Sensors W, L), 25bar (sensor D)

Product	Proline Promag 400 Magnetic-inductive flow measuring system; remote version providing exciter coil circuits and non-incendive electrode circuits to Remote Sensor, Model Promag W, L, D. Proline Promag W 400, Model 5W4Cbb-ccdLfN/Phiklllmn+#### and O5W4Cbb-ccdLfN/Phiklllmnp + #### Proline Promag L 400, Model 5L4Cbb-ccLfN/Phiklllmn+#### and O5L4Cbb-ccLfN/Phiklllmnp + #### Proline Promag D 400, Model 5D4Cbb-ccLfN/Phiklllmn+#### and O5D4Cbb-ccLfN/Phiklllmnp + #### Note: Must be installed as per control drawing FES0196*
Electrical Rating	Rated input: 100-240 V AC, 50/60Hz (+/- 4Hz), 30VA 24 V AC, 50/60Hz (+/- 4Hz), 10VA 24 V DC, 8.0W
Enclosure rating	Transmitter Housing: Type 4X, IP 66/67 Sensor Housing: Type 4X, 6P, IP 66/68
Temp. code and ambient temperature	Transmitter Housing: T4 (-40°C to + 60°C) Sensor Housing: T6 or T5 (-40°C to + 60°C)



Certificate: 2551823

Project: 80224103

Master Contract: 160686

Date Issued: 2024-11-13

Process temperature and MWP	Max process temperature: +90°C Maximum Working Pressure (MWP): 160bar (Sensors W, L), 25bar (sensor D)
-----------------------------	--

Order Code Structure:

<u>Proline Promag W 400</u>	<u>Proline Promag L 400, Proline Promag D 400</u>
5a4obb-ccdefghikllmn + ### O5a4obb-ccdefghikllmnpp + ### <u>Proline Promag 400 - replacement transmitter</u> 5X4oXX-ccdefghi + ### O5X4oXX-ccdefghipp + ### a = Type of sensor W = Promag W o = Generation Index C = modular version bb = Size (nominal tube diameter) any double number or letter cc = Approval C6 = CSA C/US NI CL.I Div.2 Gr. ABCD d = Design (options for length of tube) any single number or letter e = Power Supply (and sensor only option) L = 24-240V AC/DC (modular version only) X = sensor only (For customers ordering a replacement sensor.) f = Output/Input H,I,J = 4-20mA HART + configurable ports L = PROFIBUS DP M = Modbus RS485 N = Ethernet/IP O, P = Modbus/PFS/IOUT X = sensor only (For customers ordering a replacement sensor.) g = Housing of Transmitter A = Compact, Alu M = Compact, Polymeric N = Remote, Polymeric P = Remote, Alu Q = Compact, Polymeric, 22.5° angle R = Compact, Alu, 22.5° angle h = Cable, Remote Version (options for	5a4obb-ccdefghikllmn + ### O5a4obb-ccdefghikllmnpp + ### - a = Type of sensor L = Promag L D = Promag D o = Generation Index C = modular version bb = Size (nominal tube diameter) any double number or letter cc = Approval C6 = CSA C/US NI CL.I Div.2 Gr. ABCD e = Power Supply (and sensor only option) L = 24-240V AC/DC (modular version only) X = sensor only (For customers ordering a replacement sensor.) f = Output/Input H,I,J = 4-20mA HART + configurable ports L = PROFIBUS DP M = Modbus RS485 N = Ethernet/IP O, P = Modbus/PFS/IOUT X = sensor only (For customers ordering a replacement sensor.) g = Housing of Transmitter A = Compact, Alu M = Compact, Polymeric N = Remote, Polymeric P = Remote, Alu Q = Compact, Polymeric, 22.5° angle R = Compact, Alu, 22.5° angle h = Cable, Remote Version (options for length and quality of cable) any single number or letter i = Cable Glands D = Thread NPT1/2" L = Thread NPT1/2" + M12x1 receptacle



Certificate: 2551823

Master Contract: 160686

Project: 80224103

Date Issued: 2024-11-13

length and quality of cable) any single number or letter i = Cable Glands D = Thread NPT1/2" L = Thread NPT1/2" + M12x1 receptacle for ethernet k = Liner Material (covers the inside of measurement tube) any single number or letter III = Process Connection (= flange) any triple number or letter m = Electrodes (shape and material of electrodes contacting the fluid) any single number or letter n = Calibration Flow any single number or letter pp = Customer version any double number or letter ** = Option in two digits (none, two or multiple of two digits); any combination of number or letter +, # = Signs used as indicator for optional abbreviation of extended order code	for ethernet k = Liner Material (covers the inside of measurement tube) any single number or letter III = Process Connection (= flange) any triple number or letter m = Electrodes (shape and material of electrodes contacting the fluid) any single number or letter n = Calibration Flow any single number or letter pp = Customer version any double number or letter ** = Option in two digits (none, two or multiple of two digits); any combination of number or letter +, # = Signs used as indicator for optional abbreviation of extended order code
---	---

Product	Proline Prosonic Flow ultrasonic flow measuring system; remote version providing non incensive circuits to sensors Prosonic Flow W and Prosonic Flow I. Proline Prosonic W 400, Model 9W4Bcc-ddefghikkmmnnpp + ### and O9W4Bcc-ddefghikkmmnnppq + ### Proline Prosonic I 400, Model 9I4Bcc-ddefghikkmmnnopp + ### and O9I4Bcc-ddefghikkmmnnoppq + ### Note: Must be installed as per control drawing FES0233*
Electrical Rating	Rated input: 100-240 V AC, 50/60Hz (+/- 4Hz), 30VA 24 V AC, 50/60Hz (+/- 4Hz), 10VA 24 V DC, 8.0W
Enclosure rating	Transmitter Housing: Type 4X, IP 66/67 Sensor: Type 4X/ 6P/ IP 66/68
Temp. code and ambient temperature	Transmitter Housing: T4 (-40°C to + 60°C) Sensor Housing: T6-T1, see control drawing FES0233*
Process temperature and MWP	See control drawing FES0233*



Certificate: 2551823

Project: 80224103

Master Contract: 160686

Date Issued: 2024-11-13

Order Code Structure:

Proline Prosonic Flow W 400 9W4Bcc-ddefghikkmmnnpp + ### 09W4Bcc-ddefghikkmmnnppqq + ###	
Proline Prosonic Flow I 400 9I4Bcc-ddefghikkmmnnnoopp + ### 09I4Bcc-ddefghikkmmnnnooppqq + ###	
Proline Prosonic Flow 400 - replacement transmitter 9X4BXX-ddefghipp + ### 09X4BXX-ddefghippqq + ###	
cc	Number of Sensorsets any double number or letter
dd	Approval C6 = CSA C/US NI CL.I Div.2 Gr. ABCD
e	Power Supply L = 100..240 VAC or 24V AC/DC X = Sensor only (Not for replacement transmitter)
f	Output/Input H,I = 4-20mA HART + configurable ports L = Profibus DP M = Modbus RS485 N = Ethernet/IP O,P = Modbus/PFS/IOOUT X = Sensor only (Not for replacement transmitter)
g	Display/Operation F = Display module G = Display module with WLAN X = Sensor only (Not for replacement transmitter)
h	Housing of Transmitter N = Remote, Polymeric enclosure P = Remote, Aluminum enclosure X = Sensor only (Not for replacement transmitter)
i	Cable Entries D = Thread NPT1/2" L = Thread NPT1/2" + M12x1 receptacle for Ethernet X = Sensor only (Not for replacement transmitter)
kk	Sensor Version any double number or letter
l	Process Temperature any single number or letter
mm	Cable any double number or letter
nn	Installation Set any double number or letter



Certificate: 2551823

Master Contract: 160686

Project: 80224103

Date Issued: 2024-11-13

oo	Sensor Holder any double number or letter
pp	Device Model any double number or letter
qq	Customer Version any double number or letter
+, #	Signs used as indicator for optional abbreviation of extended order code
**	Option in two digits (none, two or multiple of two digits); any combination of number or letter

Proline Prosonic Flow 400 sensor set

DK9018-ddkk100

dd	Approval C6 = CSA C/US NI CL.I Div.2 Gr. ABCD
kk	Sensor Version any double number or letter
l	Process Temperature any single number or letter
00	Reserved for future use

Note:

Optionally an antenna bushing is available for the connection of an external antenna.

Conditions of Acceptability:

1. Final installation shall be as per Canadian Electrical Code (CEC) or National Electrical Code (NEC). Refer to control drawing FES0196 and FES0233 for safe instructions.
2. For polymeric enclosures: Do not remove the reinforcement plate. This ensures grounding and mechanical stability of the conduit entries and the optional antenna bushing.
3. Antenna supplied by Endress+Hauser shall be used only. As an alternate, any passive omni-directional RF antenna with or without cable is permitted to be connected when meeting the following parameters:
 - a. The antenna shall have an impedance of at least 50Ω.
 - b. The rated frequency range of the antenna shall not exceed 1710MHz ... 6000MHz.
 - c. The RF antenna or the RF antenna cable shall be fitted with a Type N connector plug (male).
4. The antenna bushing type H337 shall be mounted wrench tight to the transmitter enclosure to maintain the ingress protection of the enclosure.
5. The coupling nut of the Type N plug connector shall be hand tightened only.
6. The metal enclosure of the Antenna Bushing H337 shall be securely connected to local earth, typically via the enclosure to which it is connected.



Certificate: 2551823

Master Contract: 160686

Project: 80224103

Date Issued: 2024-11-13

APPLICABLE REQUIREMENTS

CSA C22.2 No. 213-17+Upd.1+Upd.2+Upd.3(Third Edition) - Nonincendive electrical equipment for use in Class I and II, Division 2 and Class III, Divisions 1 and 2 hazardous (classified) locations - Third Edition; Update No. 1: August 2018; Update No. 2: August 2019; Update No. 3: April 2021

CSA C22.2 No. 61010-1-12, UPD1:2015, UPD2:2016 AMD1:2018 - Safety requirements for electrical equipment for measurement, control, and laboratory use — Part 1: General requirements...

CSA C22.2 No. 94.2:15 - Second Edition - Enclosures for electrical equipment, environmental considerations

ANSI/UL 121201-2021 Ninth Edition - Nonincendive Electrical Equipment for Use in Class I and II, Division 2 and Class III, Divisions 1 and 2 Hazardous (Classified) Locations

ANSI/UL 61010-1:2012 - Third Edition - Including revisions through June 6, 2023 - Safety Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General Requirements

UL 50E:2015 - Second Edition - UL Standard for Safety Enclosures for Electrical Equipment, Environmental Considerations

FM 3600:2022 - Electrical Equipment for Use in Hazardous (Classified) Locations - General Requirements

FM 3611:2021 - Nonincendive Electrical Equipment for Use in Class I and II, Division 2 and Class III, Divisions 1 and 2 Hazardous (Classified) Locations



Certificate: 2551823


Project: 80224103

Master Contract: 160686

Date Issued: 2024-11-13

Notes:

Products certified under Class(es) C225803, C225883 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). www.scc.ca



7. Specified temperatures

Transmitter:

- Temperature class for transmitter is T4
- Range of ambient temperature: -40°C to 60°C

Sensor:

- Temperature class and range of ambient/fluid temperature:

Order Code	kk	l	Type of Sensor	Ambient temp. (°C)		Fluid temp. min (°C)	Fluid temp. max (°C)			
				min	max		T6	T5	T4	T3-T1
Prosonic Flow W 400: 9W4B**-C6*****kk1*****+##*# 09W4B**-C6*****kk1*****+##*# DK9018-C6kk1**	AA	A	C-030-A	-20	80	-20	80	80	80	80
	AA	B	C-030-A	-40	80	-40	80	80	80	80
	AB	A	C-050-A	-20	75	-20	75	80	80	80
	AC	A	C-100-A		80	-20	-	80	80	80
	AD	A	C-200-A							
	AE	A	C-500-A	-20	75	-20	75	80	80	80
					80	-20	-	80	80	80
	AE	B	C-500-A	-40	75	-40	75	80	80	80
					80	-40	-	80	80	80
	AE	F	C-500-A	0	75	0	75	95	130	130
80					0	-	95	130	130	
Prosonic Flow I 400: 9I4B**-C6*****kk1*****+##*# 09I4B**-C6*****kk1*****+##*# DK9018-C6kk1**	AC	B	C-100-B	-40	70	-40	70	80	80	80
					80	-40	-	80	80	80
	AD	B	C-200-B	-40	75	-40	75	80	80	80
					80	-40	-	80	80	80
	AC	F	C-100-C	0	70	0	70	95	130	130
					80	0	-	95	130	130
	AD	F	C-200-C	0	75	0	75	95	130	130
					80	0	-	95	130	130
	AF	A	I-100-A	-20	75	-20	75	80	80	80
					80	-20	-	80	80	80
AF	B	I-100-A	-40	75	-40	75	80	80	80	
				80	-40	-	80	80	80	

8. WARNING - EXPLOSION HAZARD - SUBSTITUTION OF COMPONENTS MAY IMPAIR SUITABILITY FOR CLASS I, DIVISION 2;

AVERTISSEMENT – RISQUE D'EXPLOSION – LA SUBSTITUTION DE COMPOSANTS PEUT RENDRE CE MATÉRIEL INACCEPTABLE POUR LES EMBLEMENTS DE CLASSE I, DIVISION 2;

9. WARNING - EXPLOSION HAZARD – DO NOT DISCONNECT EQUIPMENT UNLESS POWER HAS BEEN SWITCHED OFF OR THE AREA IS KNOWN TO BE NON-HAZARDOUS;
AVERTISSEMENT – RISQUE D'EXPLOSION – AVANT DE DÉCONNECTER L'EQUIPMENT, COUPER LE COURANT OU S'ASSURER QUE L'EMPLACEMENT EST DÉSIGNÉ NON DANGEREUX;

10. Replacement of transmitter or sensor: Do not re-use the replaced transmitter / sensor in any other application.

Aenderungen:	A	03.12.2014 / BDA	F		Ersteller: FES / BDA FILE: M:\ZEICHNG\FES0233\C\FES0233C.doc		
	B	08.03.2019 / BDA	G				
	C	28.06.2021 / BDA	H				
	D	21.11.2023 / BDA	J				
	E		K				
cCSA _{US} Control Drawing Class I Division 2 Prosonic Flow I/W 400 Endress+Hauser 					Gezeichnet	03.12.2014	BDA
					Geprüft		
					Ex-geprüft	21.11.2023	BDA
					Gesehen		
Flowtec AG, Kaegenstrasse 7, CH-4153 Reinach BL1, Postfach					FES0233D		
					2/3		

Prosonic Flow I/W 400 - Wiring Options

1) Cl. I. Div. 2, Gps A,B,C,D

a) Threaded Cable Entries NPT1/2":

- Install per Canadian Electrical Code (CEC) or National Electrical Code (NEC) ANSI/NFPA 70 and use supply wires suitable for 20 °C above ambient temperature.

b) Receptacle (plug-in connector) with thread M12x1, approved for Cl. I. Div.2:

- Install per Canadian Electrical Code (CEC) or National Electrical Code (NEC) ANSI/NFPA 70.
- The M12 mating connector which is sourced by the customer must also be approved for Cl. I. Div.2 and must be suitable for Type 4X, IP66/67. It must provide additional mechanical security to prevent accidental disconnection.

c) Sensor Circuits (NIFW):

- Install per Canadian Electrical Code (CEC) or National Electrical Code (NEC) ANSI/NFPA 70.

2) Non-hazardous classified areas

a) Threaded Cable Entries (e.g. NPT1/2" or M20x1.5):

- Install per Canadian Electrical Code (CEC) or National Electrical Code (NEC) ANSI/NFPA 70 and use supply wires suitable for 20 °C above ambient temperature.

b) Receptacle (plug-in connector) with thread M12 x 1:

- Install per Canadian Electrical Code (CEC) or National Electrical Code (NEC) ANSI/NFPA 70.
- The M12 mating connector which is sourced by the customer must be suitable for Type 4X, IP66/67.

c) Sensor Circuits:

- Install per Canadian Electrical Code (CEC) or National Electrical Code (NEC) ANSI/NFPA 70.

3) Notes for External Antenna

- a) Antenna supplied by Endress+Hauser shall be used only. As an alternate, any passive omni-directional RF antenna with or without cable is permitted to be connected when meeting the following parameters:
- i) The antenna shall have an impedance of at least 50Ω
 - ii) The rated frequency range of the antenna shall not exceed 1710MHz ... 6000MHz
 - iii) The RF antenna or the RF antenna cable shall be fitted with a Type N connector plug (male)
- b) The antenna bushing type H337 shall be mounted wrench tight to the transmitter enclosure to maintain the ingress protection of the enclosure.
- c) The coupling nut of the Series N plug connector shall be hand tightened only.
- d) The metal enclosure of the Antenna Bushing H337 shall be securely connected to local earth, typically via the enclosure to which it is connected

Änderungen:	A	03.12.2014 / BDA	F		Ersteller: FES / BDA FILE: M:\ZEICHN\GFES0233\C\GFES0233C.doc
	B	08.03.2019 / BDA	G		
	C	28.06.2021 / BDA	H		
	D	21.11.2023 / BDA	J		
	E		K		

cCSA _{US} Control Drawing Class I Division 2 Prosonic Flow I/W 400	Gezeichnet	03.12.2014	BDA
	Geprüft		
	Ex-geprüft	21.11.2023	BDA
	Gesehen		

Endress+Hauser 	FES0233D	3/3
Flowtec AG, Kaegenstrasse 7, CH-4153 Reinach BL1, Postfach		