Technical Information Proline Prosonic Flow B 200

Ultrasonic transit time flowmeter



The device for accurate, reliable biogas measurement with loop-powered technology

Application

- The measuring principle is unaffected by gas composition
- Inline flowmeter for wet biogas and digester gas under fluctuating process conditions

Device properties

- Multivariable device: flow, temperature and methane
- Medium temperature: 0 to 80 °C (32 to 176 °F)
- Process pressure: 0.7 to 11 bar a (10.2 to 159 psi a)
- Loop-powered technology
- Robust dual-compartment housing
- Plant safety: worldwide approvals

Your benefits

- Integrated real-time methane fraction measurement
- Optimized for low pressure gas specialized sensor design
- No additional pressure loss full bore design
- Process transparency diagnostic capability
- Convenient device wiring separate connection compartment
- Safe operation no need to open the device due to display with touch control, background lighting
- Integrated verification Heartbeat Technology



Table of contents

| Document information | 3 |
|-------------------------------------|----------|
| Symbols used | 3 |
| | |
| Function and system design | 3 |
| Measuring principle | |
| Measuring system | |
| | |
| Input | 5 |
| Measured variable | |
| Measuring range | |
| Operable flow range | |
| Input signal | 6 |
| r 5 | - |
| Output | 7 |
| Output signal | |
| Signal on alarm | |
| Load | |
| Ex connection data | 10 |
| Low flow cut off | 13 |
| Galvanic isolation | 13 |
| Protocol-specific data | 13 |
| • | |
| Power supply | 15 |
| Terminal assignment | 15 |
| Supply voltage | 15 |
| Power consumption | 16 |
| Current consumption | 16 |
| Power supply failure | 16 |
| Electrical connection | 17 |
| Potential equalization | 19 |
| Terminals | 19 |
| Cable entries | 19 |
| Cable specification | 19 |
| Overvoltage protection | 20 |
| | |
| Performance characteristics | 20 |
| Reference operating conditions | 20 |
| Maximum measured error | 20 |
| Repeatability | |
| Response time | 21 |
| Influence of ambient temperature | 21 |
| | |
| Installation | 22 |
| Mounting location | 22 |
| Orientation | 22 |
| Inlet and outlet runs | 23 |
| Special mounting instructions | 24 |
| - . | <u> </u> |
| Environment | 25 |
| Ambient temperature range | 25 |
| Storage temperature | 27 |
| Degree of protection | 27 27 |
| Shock resistance | 27 |
| Electromagnetic compatibility (EMC) | 27 |
| Licenomagnetic compationity (ENG) | 47 |

| Process | 27 27 28 29 29 29 |
|---|---|
| Mechanical construction | 29 33 37 38 40 |
| Operability | 41 41 42 43 |
| Certificates and approvals CE mark . C-Tick symbol . Ex approval . HART certification . Pressure Equipment Directive . Other standards and guidelines . | 43 43 43 43 44 44 44 |
| Ordering information | 45 |
| Application packages | 45 45 46 |
| Accessories | 46 47 48 48 |
| Documentation Standard documentation Supplementary device-dependent documentation | 49 49 49 |
| Registered trademarks | 50 |

Document information

Symbols used

Electrical symbols

| Symbol | Meaning | Symbol | Meaning |
|--------|--|----------|---|
| | Direct current | \sim | Alternating current |
| R | Direct current and alternating current | <u> </u> | Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system. |
| Ð | Protective ground connection A terminal which must be connected to ground prior to establishing any other connections. | Ą | Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice. |

Symbols for certain types of information

| Symbol | Meaning |
|--------|--|
| | Permitted Procedures, processes or actions that are permitted. |
| | Preferred Procedures, processes or actions that are preferred. |
| | Forbidden Procedures, processes or actions that are forbidden. |
| i | Tip Indicates additional information. |
| Ĩ | Reference to documentation |
| | Reference to page |
| | Reference to graphic |
| | Visual inspection |

Symbols in graphics

| Symbol | Meaning | Symbol | Meaning |
|------------|----------------|----------------|--------------------------------|
| 1, 2, 3, | Item numbers | 1. , 2. , 3 | Series of steps |
| A, B, C, | Views | A-A, B-B, C-C, | Sections |
| EX | Hazardous area | × | Safe area (non-hazardous area) |
| ≈ → | Flow direction | | |

Function and system design

Measuring principle


A Proline Prosonic Flow ultrasonic flowmeter measures the flow rate of the passing fluid by using sensor pairs located on opposite sides of the meter body and at an angle so that one of the sensors in

the pair is slightly mounted downstream. The design is non-invasive and does not have any moving parts.

The flow signal is established by alternating an acoustic signal between the sensor pairs and measuring the transit time of each transmission. Then utilizing the fact that sound travels faster with the flow versus against the flow, this differential time (D T) can be used to determine the fluids velocity between the sensors.

The volume flow rate is established by combining all the flow velocities determined by the sensor pairs with the cross sectional area of the meter body and extensive knowledge about fluid flow dynamics. The design of the sensors and their position ensures that only a short straight run of pipe upstream of the meter is required after typical flow obstructions such as bends in one or two planes.

Advance digital signal processing facilitates constant validation of the flow measurement reducing susceptibility to multiphase flow conditions and increases the reliability of the measurement.




Direct measurement of the methane fraction (CH₄)

The sound velocity, temperature and chemical composition of a gas are directly dependant on each other. If two of these characteristic quantities are known, the third can be calculated. The higher the gas temperature or the methane fraction, the higher the sound velocity in biogas.

Since the measuring device accurately measures both the sound velocity and the current gas temperature, the methane fraction can be calculated directly and displayed on site without the need for an additional measuring instrument $\rightarrow \blacksquare 1$, $\boxdot 4$.

The relative humidity of biogas is usually 100%. Thus, the water content can be determined by the temperature measurement and can be compensated for.

The measuring device is unique in its ability to measure the methane fraction directly, making it possible to monitor the gas flow and gas quality 24/7. In this way, operators of a biogas plant, for example, can react swiftly and specifically to problems in the digestion process.



I Calculation of the methane fraction [%] based on the sound velocity [m/s (ft/s)] and a temperature T of 40 °C (104 °F), for example.

Measuring system


The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.

Transmitter

| Prosonic Flow 200 | Device versions and materials: |
|-------------------|--|
| | Compact, aluminum coated: Aluminum, AlSi10Mg, coated Compact, stainless: For maximum corrosion resistance: stainless steel 1.4404 (316L) |
| | Configuration: External operation via four-line, illuminated local display with touch control and guided menus ("Make-it-run" wizards) for applications Via operating tools (e.g. FieldCare) |

Sensor



Input

Measured variable

Direct measured variables

Volume flow

Calculated measured variables

- Corrected volume flow
- Mass flow

Optional measured variables (can be ordered)

Order code for "Sensor version", option 2 "Volume flow + Biogas analysis"

- Corrected methane volume flow
- Energy flow
- Methane fraction
- Gross calorific value
- Wobbe index
- Temperature

Measuring range

Standard (order code for "Calibration flow", option 1 "Operable flow range 30 : 1")

| Nominal | Nominal diameter Velocity | | Effective volume flow | | |
|---------|---------------------------|---------|-----------------------|---------------------|----------------------|
| [mm] | [in] | [m/s] | [ft/s] | [m ³ /h] | [ft ³ /h] |
| 50 | 2 | 1 to 30 | 3.28 to 98.4 | 9 to 269 | 316 to 9495 |
| 80 | 3 | 1 to 30 | 3.28 to 98.4 | 20 to 611 | 720 to 21592 |
| 100 | 4 | 1 to 30 | 3.28 to 98.4 | 34 to 1032 | 1215 to 36443 |
| 150 | 6 | 1 to 30 | 3.28 to 98.4 | 76 to 2 290 | 2 695 to 80 862 |
| 200 | 8 | 1 to 30 | 3.28 to 98.4 | 131 to 3925 | 4620 to 138596 |

Optional (order code for "Calibration flow", option 2 "Operable flow range 100 : 1")

| Nominal | diameter | Velocity | | Effective volume flow | |
|---------|----------|-----------|--------------|-----------------------|----------------------|
| [mm] | [in] | [m/s] | [ft/s] | [m ³ /h] | [ft ³ /h] |
| 50 | 2 | 0.3 to 30 | 0.98 to 98.4 | 3 to 269 | 95 to 9495 |
| 80 | 3 | 0.3 to 30 | 0.98 to 98.4 | 6 to 611 | 215 to 21592 |
| 100 | 4 | 0.3 to 30 | 0.98 to 98.4 | 11 to 1032 | 363 to 36443 |
| 150 | 6 | 0.3 to 30 | 0.98 to 98.4 | 25 to 2290 | 805 to 80862 |
| 200 | 8 | 0.3 to 30 | 0.98 to 98.4 | 43 to 3925 | 1365 to 138596 |

The values in the table should be regarded as reference values.

To calculate the measuring range, use the Applicator sizing tool $\rightarrow \square 48$

Recommended measuring range

"Flow limit" section $\rightarrow \square 28$

30:1 (standard; order code for "Calibration Flow", option 1 "Operable flow range 30:1")
 100:1 (optional; order code for "Calibration Flow", option 2 "Operable flow range 100:1")

Flow rates above the preset full scale value do not overload the amplifier so the totalized values are registered correctly.

Input signal

Operable flow range

Current input

| Current input | 4-20 mA (passive) |
|--------------------------|--|
| Resolution | 1 μΑ |
| Voltage drop | Typically: 2.2 to 3 V for 3.6 to 22 mA |
| Maximum voltage | <35 V |
| Possible input variables | Pressure |

External measured values

To increase the accuracy of certain measured variables, the automation system can continuously write the operating pressure to the measuring device. Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S

Various pressure transmitters can be ordered from Endress+Hauser: see "Accessories" section $\rightarrow \cong 48$

It is recommended to read in external measured values to calculate the following measured variables:

- Energy flow
- Mass flow
- Corrected volume flow
- Corrected methane volume flow

Current input

The measured values are written from the automation system to the measuring device via the current input $\rightarrow \cong 6$.

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Output

Output signal

Current output

| Current output 1 | 4-20 mA HART (passive) |
|----------------------------------|--|
| Current output 2 | 4-20 mA (passive) |
| Resolution | < 1 µA |
| Damping | Adjustable: 0.0 to 999.9 s |
| Assignable measured variables | Volume flow Corrected volume flow Corrected methane volume flow Mass flow Energy flow Methane fraction Calorific value Wobbe index Temperature |

Pulse/frequency/switch output

| n | |
|----------------------------------|---|
| Function | Can be set to pulse, frequency or switch output |
| Version | Passive, open collector |
| Maximum input values | DC 35 V 50 mA for information on the Ex connection values → ■ 10 |
| Voltage drop | For ≤ 2 mA: 2 V For 10 mA: 8 V |
| Residual current | ≤ 0.05 mA |
| Pulse output | |
| Pulse width | Adjustable: 5 to 2 000 ms |
| Maximum pulse rate | 100 Impulse/s |
| Pulse value | Adjustable |
| Assignable measured variables | Volume flow Corrected volume flow Corrected methane volume flow Mass flow Energy flow |
| Frequency output | |
| Output frequency | Adjustable: 0 to 1 000 Hz |
| Damping | Adjustable: 0 to 999 s |
| Pulse/pause ratio | 1:1 |

| Assignable measured variables | Volume flow Corrected volume flow Corrected methane volume flow Mass flow Energy flow Methane fraction Calorific value Wobbe index Temperature |
|----------------------------------|--|
| Switch output | |
| Switching behavior | Binary, conductive or non-conductive |
| Switching delay | Adjustable: 0 to 100 s |
| Number of switching cycles | Unlimited |
| Assignable functions | Off On Diagnostic behavior Limit value Volume flow Corrected volume flow Corrected methane volume flow Mass flow Energy flow Methane fraction Calorific value Wobbe index Temperature Totalizer 1 to 3 Flow direction monitoring Status Low flow cut off |

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output

4-20 mA

| Failure mode Selectable (as per NAMUR recommendation NE 43): • Minimum value: 3.6 mA • Maximum value: 22 mA • Defined value: 3.59 to 22.5 mA • Actual value • Last valid value | |
|--|--|
|--|--|

HART

Pulse/frequency/switch output

Pulse output

| Failure mode | Choose from: • Actual value • No pulses |
|--------------|---|
|--------------|---|

Frequency output

| Failure mode | Choose from: • Actual value |
|--------------|---|
| | 0 HzDefined value: 0 to 1 250 Hz |

Switch output

| OpenClosed | Failure mode | 1 |
|---------------------------------------|--------------|---|
|---------------------------------------|--------------|---|

Local display

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
| Backlight | Additionally for device version with SD03 local display: red lighting indicates a device error. |

Status signal as per NAMUR recommendation NE 107

Operating tool

- Via digital communication:
- HART protocol
- Via service interface

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
|--------------------|---|

Additional information on remote operation $\rightarrow \square 42$


Load

Load for current output: 0 to 500 Ω , depending on the external supply voltage of the power supply unit

Calculation of the maximum load

Depending on the supply voltage of the power supply unit (U_S), the maximum load (R_B) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage

- For $U_S = 16.0$ to 16.8 V: $R_B \le (U_S 16.0$ V): 0.0036 A For $U_S = 16.8$ to 23.0 V: $R_B \le (U_S 12.0$ V): 0.022 A
- For $U_{\rm S} = 23.0$ to 30.0 V: $R_{\rm B} \le 500$ Ω



- Operating range 1
- 1.1 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with Ex i and option C "4-20 mA HART + 4-20 mA analog"
- 1.2 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with non-Ex and Ex d

Sample calculation

Supply voltage of the power supply unit: $U_S = 17.5 \text{ V}$ Maximum load: $R_B \le (17.5 \text{ V} - 12.0 \text{ V})$: 0.022 A = 250 Ω

Ex connection data

Safety-related values

Type of protection Ex d

| Order code for "Output" | Output type | Safety-related values |
|-------------------------|-------------------------------|---|
| Option A | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| Option B | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| Option C | 4-20mA HART | $U_{nom} = DC 30 V$ $U_{max} = 250 V$ |
| | 4-20mA analog | |
| Option D | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| | 4 to 20 mA current input | U _{nom} = DC 35 V U _{max} = 250 V |

1) Internal circuit limited by R_i = 760.5 Ω

Type of protection XP

| Order code for "Output" | Output type | Safety-related values |
|-------------------------|-------------------------------|---|
| Option A | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| Option B | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| | Pulse/frequency/switch output | $\begin{array}{l} U_{nom} = DC \ 35 \ V \\ U_{max} = 250 \ V \\ P_{max} = 1 \ W^{1)} \end{array}$ |
| Option C | 4-20mA HART | U _{nom} = DC 30 V |
| | 4-20mA analog | U _{max} = 250 V |
| Option D | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| | 4 to 20 mA current input | U _{nom} = DC 35 V U _{max} = 250 V |

1) Internal circuit limited by $R_i = 760.5 \Omega$

Type of protection NI

| Order code for "Output" | Output type | Safety-related values |
|-------------------------|-------------------------------|---|
| Option A | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| Option B | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| Option C | 4-20mA HART | U _{nom} = DC 30 V |
| | 4-20mA analog | U _{max} = 250 V |
| Option D | 4-20mA HART | U _{nom} = DC 35 V U _{max} = 250 V |
| | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| | 4 to 20 mA current input | U _{nom} = DC 35 V U _{max} = 250 V |

1) Internal circuit limited by $R_i = 760.5 \ \Omega$

Type of protection NIFW

| Order code for "Output" | Output type | Safety-related values |
|-------------------------|-------------------------------|--|
| Option A | 4-20mA HART | $\begin{array}{l} U_{i} = DC \ 35 \ V \\ I_{i} = n.a. \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 5 \ nF \end{array}$ |
| Option B | 4-20mA HART | $\begin{array}{l} U_i = DC \ 35 \ V \\ I_i = n.a. \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 5 \ nF \end{array}$ |
| | Pulse/frequency/switch output | $ \begin{array}{l} U_{i} = DC \ 35 \ V \\ I_{i} = n.a. \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array} $ |
| | 4-20mA HART | $U_i = DC 30 V$ |
| Option C | 4-20mA analog | $ \begin{array}{l} I_i = n.a. \\ P_i = 1 W \\ L_i = 0 \ \mu H \\ C_i = 30 \ nF \end{array} $ |
| Option D | 4-20mA HART | $\begin{array}{l} U_i = DC \ 35 \ V \\ I_i = n.a. \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 5 \ nF \end{array}$ |

| Order code for "Output" | Output type | Safety-related values |
|-------------------------|-------------------------------|--|
| | Pulse/frequency/switch output | $\begin{array}{l} U_i = DC \; 35 \; V \\ I_i = n.a. \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 6 \; nF \end{array}$ |
| | 4 to 20 mA current input | $\begin{array}{l} U_{i} = DC \ 35 \ V \\ I_{i} = n.a. \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 5 \ nF \end{array}$ |

Intrinsically safe values

Type of protection Ex ia

| Order code for "Output" | Output type | Intrinsically safe values |
|-------------------------|-------------------------------|--|
| Option A | 4-20mA HART | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array}$ |
| Option B | 4-20mA HART | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array}$ |
| | Pulse/frequency/switch output | $ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 6 \; nF \end{array} $ |
| Option C | 4-20mA HART | $U_i = DC 30 V$ |
| | 4-20mA analog | $ I_i = 300 \text{ mA} P_i = 1 W L_i = 0 \mu H C_i = 30 \text{ nF} $ |
| Option D | 4-20mA HART | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array}$ |
| | Pulse/frequency/switch output | $ \begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 6 \; nF \end{array} $ |
| | 4 to 20 mA current input | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array}$ |

Type of protection IS

| Order code for "Output" | Output type | Intrinsically safe values |
|-------------------------|-------------------------------|--|
| Option A | 4-20mA HART | $ \begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array} $ |
| Option B | 4-20mA HART | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array}$ |
| | Pulse/frequency/switch output | $ \begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 6 \; nF \end{array} $ |
| Option C | 4-20mA HART | $U_i = DC 30 V$ $I_i = 300 mA$ |
| | 4-20mA analog | $P_i = 1 W$ $L_i = 0 \mu H$ $C_i = 30 nF$ |
| Option D | 4-20mA HART | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 5 \; nF \end{array}$ |
| | Pulse/frequency/switch output | $ \begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = \; 300 \; mA \\ P_{i} = \; 1 \; W \\ L_{i} = \; 0 \; \mu H \\ C_{i} = \; 6 \; nF \end{array} $ |
| | 4 to 20 mA current input | $ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array} $ |

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

All outputs are galvanically isolated from one another.

HART

Protocol-specific data

| Manufacturer ID | 0x11 |
|---------------------------------------|--|
| Device type ID | 0x5A |
| HART protocol revision | 7 |
| Device description files (DTM, DD) | Information and files under: www.endress.com |
| HART load | Min. 250 Ω Max. 500 Ω |


| Dynamic variables | Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables. |
|-------------------|---|
| | Measured variables for PV (primary dynamic variable) Volume flow Corrected volume flow Corrected methane volume flow Energy flow Methane fraction in % Calorific value Wobbe index Temperature Mass flow Sound velocity Flow velocity Flow velocity Acceptance rate Signal asymmetry Turbulence Signal to noise ratio Signal strength |
| | Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) Volume flow Corrected volume flow Corrected methane volume flow Energy flow Methane fraction in % Calorific value Wobbe index Temperature Totalizer 1 Totalizer 2 Totalizer 3 Mass flow Sound velocity Flow velocity Flow velocity Acceptance rate Signal asymmetry Turbulence Signal strength |
| Device variables | Read out the device variables: HART command 9 The device variables are permanently assigned. A maximum of 8 device variables can be transmitted: 0 = volume flow 1 = corrected volume flow 2 = methane corrected volume flow 3 = energy flow 4 = methane fraction in % 5 = calorific value 6 = Wobbe index 7 = temperature 8 = totalizer 1 9 = totalizer 2 10 = totalizer 3 11 = mass flow 12 = sound velocity 13 = flow velocity 14 = acceptance rate 15 = signal asymmetry 16 = turbulence 17 = signal to noise ratio 18 = signal strength |

Power supply

Terminal assignment

Transmitter

Connection versions



| Order code for "Output" | Terminal numbers | | | | | |
|----------------------------------|------------------------|---------------|-------------------------|-------------------------|--------------------|-------|
| | Output 1 | | Output 2 | | Input | |
| | 1 (+) | 2 (-) | 3 (+) | 4 (-) | 5 (+) | 6 (-) |
| Option A | 4-20 mA HA | ART (passive) | - | - | - | - |
| Option B ¹⁾ | 4-20 mA HART (passive) | | Pulse/frequ output (| ency/switch passive) | - | - |
| Option C ¹⁾ | 4-20 mA HART (passive) | | 4-20 mA ana | alog (passive) | | - |
| Option D ^{1) 2)} | 4-20 mA HART (passive) | | · · | ency/switch passive) | 4-20 mA cu (pas | 1 |

1) Output 1 must always be used; output 2 is optional.

2) The integrated overvoltage protection is not used with option D: Terminals 5 and 6 (current input) are not protected against overvoltage.

Supply voltage

Transmitter

An external power supply is required for each output.

| Order code for "Output" | Minimum terminal voltage | Maximum terminal voltage |
|---|---|-----------------------------|
| Option A ^{1) 2)} : 4-20 mA HART | For 4 mA: ≥ DC 16 V For 20 mA: ≥ DC 12 V | DC 35 V |
| Option B : 4-20 mA HART, pulse/frequency/switch output | For 4 mA: ≥ DC 16 V For 20 mA: ≥ DC 12 V | DC 35 V |

| Order code for "Output" | Minimum terminal voltage | Maximum terminal voltage |
|--|---|-----------------------------|
| Option C : 4-20 mA HART + 4-20 mA analog | For 4 mA: ≥ DC 16 V For 20 mA: ≥ DC 12 V | DC 30 V |
| Option D : 4-20 mA HART, pulse/frequency/switch output, 4-20 mA current input ³⁾ | ≥ DC 12 V | DC 35 V |

1) External supply voltage of the power supply unit with load.

2) For device versions with SD03 local display: The terminal voltage must be increased by DC 2 V if backlighting is used.

- 3) Voltage drop 2.2 to 3 V for 3.59 to 22 mA
- For information about the load see $\rightarrow \cong 9$
- Various power supply units can be ordered from Endress+Hauser: see "Accessories" section $\rightarrow \cong 48$
- For information on the Ex connection values $\rightarrow \cong 10$

Power consumption

Transmitter

| Order code for "Output" | Maximum power consumption |
|---|---|
| Option A : 4-20 mA HART | 770 mW |
| Option B : 4-20 mA HART, pulse/ frequency/switch output | Operation with output 1: 770 mWOperation with output 1 and 2: 2 770 mW |
| Option C : 4-20 mA HART + 4-20 mA analog | Operation with output 1: 660 mWOperation with output 1 and 2: 1320 mW |
| Option D : 4-20 mA HART, pulse/ frequency/switch output, 4-20 mA current input | Operation with output 1: 770 mW Operation with output 1 and 2: 2770 mW Operation with output 1 and input: 840 mW Operation with output 1, 2 and input: 2840 mW |




| Current consumption | Current output | | |
|----------------------|---|--|--|
| | For every 4-20 mA or 4-20 mA HART current output: 3.6 to 22.5 mA | | |
| | If the option Defined value is selected in the Failure mode parameter : 3.59 to 22.5 mA | | |
| | Current input | | |
| | 3.59 to 22.5 mA | | |
| | Internal current limiting: max. 26 mA | | |
| Power supply failure | Totalizers stop at the last value measured. | | |
| | Configuration is retained in the device memory (HistoROM). Error messages (incl. total operated hours) are stored. | | |

Error messages (incl. total operated hours) are stored.

Electrical connection


Connecting the transmitter



- 1 Cable entry for output 1
- 2 Cable entry for output 2


Connection examples

Current output 4-20 mA HART



- ☑ 2 Connection example for 4-20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- Active barrier for power supply with integrated resistor for HART communication (≥ 250 Ω)(e.g. RN221N)
 Connection for HART operating devices →
 ¹ 42
 Observe the maximum load →
 ¹ 9
- 3 Cable shield, observe cable specifications
- 4 Analog display unit: observe maximum load $\rightarrow \square 9$
- 5 Transmitter


Current output 4-20 mA



■ 3 Connection example for 4-20 mA current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Analog display unit: observe maximum load $\rightarrow \square 9$
- 4 Transmitter


Pulse/frequency output



Connection example for pulse/frequency output (passive)

- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values

Switch output




☑ 5 Connection example for switch output (passive)

- Automation system with switch input (e.g. PLC)
- 2 Power supply

1

3 Transmitter: observe input values

Current input



■ 6 Connection example for 4-20 mA current input

- 1 Power supply
- 2 External measuring device (for capturing the pressure)
- 3 Transmitter: observe input values $\rightarrow \square 6$

HART input

| | $\begin{bmatrix} 1 & 2 & 3 & 4 & 5 \\ 4 & 20 & mA \\ \hline & 4 & 20 & mA \\ \hline & & 4 & 20 & mA \\ \hline & & & & & & & & & & \\ \hline & & & & & &$ |
|------------------------|---|
| | I Connection example for HART input with a common negative Automation system with HART output (e.g. PLC) Resistor for HART communication (≥ 250 Ω): observe maximum load → 9 Active barrier for power supply (e.g. RN221N) Cable shield, observe cable specifications Analog display unit: observe maximum load → 9 Pressure transmitter (e.g. Cerabar M, Cerabar S): see requirements Transmitter |
| Potential equalization | Requirements |
| | No special measures for potential equalization are required. |
| | For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA). |
| Terminals | For device version without integrated overvoltage protection: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG) For device version with integrated overvoltage protection: screw terminals for wire cross-sections 0.2 to 2.5 mm² (24 to 14 AWG) |
| Cable entries | Cable gland (not for Ex d): M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in) Thread for cable entry: For non-Ex and Ex: NPT ½" For non-Ex and Ex (not for CSA Ex d/XP): G ½" For Ex d: M20 × 1.5 |
| Cable specification | Permitted temperature range |
| | -40 °C (-40 °F) to +80 °C (+176 °F) Minimum requirement: cable temperature range ≥ ambient temperature +20 K |
| | Signal cable |
| | Current output |
| | For 4-20 mA: standard installation cable is sufficient. For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant. |
| | |
| | Pulse/frequency/switch output |
| | |
| | Pulse/frequency/switch output |

Overvoltage protection

The device can be ordered with integrated overvoltage protection for diverse approvals: *Order code for "Accessory mounted", option NA "Overvoltage protection"*

| Input voltage range | Values correspond to supply voltage specifications ¹⁾ |
|--|--|
| Resistance per channel | 2 · 0.5 Ω max |
| DC sparkover voltage | 400 to 700 V |
| Trip surge voltage | < 800 V |
| Capacitance at 1 MHz | < 1.5 pF |
| Nominal discharge current (8/20 μs) | 10 kA |
| Temperature range | -40 to +85 °C (-40 to +185 °F) |

1) The voltage is reduced by the amount of the internal resistance $I_{\text{min}} \cdot R_i$

Depending on the temperature class, restrictions apply to the ambient temperature for device versions with overvoltage protection $\rightarrow \cong 25$

Performance characteristics


| Reference operating conditions | Error limits following ISO/DIS 11631 Calibration gas: air Temperature regulated to 24 ± 0.5 °C (75.2 ± 0.9 °F) under atmospheric pressure Humidity regulated to <40% RH Accuracy based on accredited calibration rigs that are traced to ISO 17025. | | |
|-----------------------------------|--|---|--|
| | To calculate the measuring range, use | e the <i>Applicator</i> sizing tool $\rightarrow \square 48$ | |
| Maximum measured error | o.r. = of reading; o.f.s. = of full scale value; abs. = absolute; T = medium temperature Volume flow | | |
| | Standard Order code for "Calibration flow", option 1 "Operable flow range 30 : 1" | ±1.5 % o.r. for 3 to 30 m/s (9.84 to 98.4 ft/s) ±3 % o.r. for 1 to 3 m/s (3.28 to 9.84 ft/s) | |
| | Optional | ■ ±0.1 % o.f.s. for 0.3 to 1 m/s (0.98 to 3.28 ft/s) | |

Methane ± 2 % o.f.s. = ± 2 % abs.

Temperature

 $\pm 0.6^{\circ}\% \pm 0.005 \cdot T^{\circ}C (\pm 0.9^{\circ}F \pm 0.005 \cdot (T - 32)^{\circ}F)$





🛃 8 Example for max. measured error (volume flow) in % o.r.

Standard (order code for "Calibration flow", option 1 "Operable flow range 30 : 1") Optional (order code for "Calibration flow", option 2 "Operable flow range 100 : 1") 1

2

Accuracy of outputs

o.r. = of reading

The outputs have the following base accuracy specifications.

Current output

| Accuracy | ±10 µA |
|----------|--------|
|----------|--------|

Pulse/frequency output

| | Accuracy | Max. ±100 ppm o.r. | | | | | | | |
|-------------------------------------|---|---|--|--|--|--|--|--|--|
| | | | | | | | | | |
| Repeatability | o.r. = of reading; o.f.s. = of | o.r. = of reading; o.f.s. = of full scale value; abs. = absolute; T = medium temperature | | | | | | | |
| | Volume flow $\pm 0.5 \% \text{ o.r.}$ | | | | | | | | |
| | Methane $\pm 0.5 \% \text{ o.f.s.} = \pm 0.5 \% \text{ abs.}$ | | | | | | | | |
| | Temperature ±0.3 °C ± 0.0025 × T °C (±0.45 °F ± 0.0025 × (T − 32) °F) | | | | | | | | |
| Response time | | The response time depends on the configuration (damping). Response time in the event of erratic changes in the flow: after 1 000 ms 95% of the full scale value. | | | | | | | |
| Influence of ambient temperature | t o.r. = of reading | | | | | | | | |
| | Current output | | | | | | | | |
| | Additional error, in relation to the span of 16 mA: | | | | | | | | |


| Temperature coefficient at zero point (4 mA) | 0.02 %/10 K |
|--|-------------|
| Temperature coefficient with span (20 mA) | 0.05 %/10 K |

Pulse/frequency output

| Temperature coefficient | Max. ±100 ppm o.r. |
|-------------------------|--------------------|
| • | |


Installation

No special measures such as supports are necessary. External forces are absorbed by the construction of the device.



Orientation

The direction of the arrow on the sensor helps you to install the sensor according to the flow direction (direction of medium flow through the piping).



 Orientation
 Compact version


 A
 Vertical orientation
 Image: Compact version

 B
 Horizontal orientation, transmitter head up *
 Image: Compact version

A0015895

| | Orientation | | | | | | |
|---|--|----------|---|--|--|--|--|
| С | Horizontal orientation, transmitter head down * | A0015590 | | | | | |
| D | Horizontal orientation, transmitter head at side | A0015592 | × | | | | |


A maximum deviation of only ±3° is permitted for the horizontal alignment of the converters.



Inlet and outlet runs

If possible, the sensor should be installed upstream from valves, T-pieces, elbows etc. To attain the specified level of accuracy of the measuring device, the below mentioned inlet and outlet runs must be maintained at minimum. If there are several flow disturbances present, the longest specified inlet run must be maintained.

Single-path version: DN 50 (2"), DN 80 (3")




Single-path version: minimum inlet and outlet runs with various flow obstructions

- 1 90 °elbow or T-section
- 2 Pump
- 3 $2 \times 90^{\circ}$ elbow, 3-dimensional

4 Control valve

Two-path version: DN 100 to 200 (4 to 8")




🖻 10 Two-path version: minimum inlet and outlet runs with various flow obstructions

- 1 90 °elbow or T-section
- 2 Pump
- 3 $2 \times 90^{\circ}$ elbow, 3-dimensional
- 4 Control valve

Outlet runs when installing external devices

If installing an external device, observe the specified distance.



PT Pressure transmitter


Special mounting instructions

Flow conditioner

If the inlet runs cannot be observed, the use of a flow conditioner is recommended. This makes the following shorter inlet runs possible:

| Single-path version | Two-path version | | |
|---------------------|------------------|--|--|
| 10 × DN | 5 × DN | | |

The flow conditioner should divide the inlet run available into a ratio of around 20 : 80. Example of an inlet run of $10 \times DN$:



1 Flow conditioner

Pressure loss

The pressure loss for flow conditioners is calculated as follows: $\Delta p \ [mbar] = 0.0085 \cdot \rho \ [kg/m^3] \cdot v^2 \ [m/s]$

| Example for biogas |
|---|
| p = 1040 mbar abs. |
| $\rho = 1.0432 \text{ kg/m}^3$ with t = 54 °C (129 °F) |
| v = 7 m/s |
| $\Delta p = 0.0085 \cdot 1.0432 \text{ kg/m}^3 \cdot 49 \text{ m/s} = 0.434 \text{ mbar}$ |
| |
| |
| abs.: absolute |
| ρ : density of the process medium |
| v: average flow velocity |


Environment

Ambient temperature range

| Transmitter | -40 to +60 °C (-40 to +140 °F) |
|---------------|---|
| Local display | -20 to $+60$ °C (-4 to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range. |
| Sensor | Flange material carbon steel: -10 to +60 °C (+14 to +140 °F) Flange material stainless steel: -40 to +60 °C (-40 to +140 °F) Version without flange: -40 to +60 °C (-40 to +140 °F) |

► If operating outdoors:

Avoid direct sunlight, particularly in warm climatic regions.



Temperature tables

The following interdependencies between the permitted ambient and fluid temperatures apply when operating the device in hazardous areas:

The following applies for installations with overvoltage protection in conjunction with approval code BJ or IJ: $T_a = T_a - 2$ °C ($T_a = T_a - 3.6$ °F)

Order code for "Output", option A "4-20mA HART"

Ex ia, Ex d, $_{\text{C}}\text{CSA}_{\text{US}}$ IS, $_{\text{C}}\text{CSA}_{\text{US}}$ XP, $_{\text{C}}\text{CSA}_{\text{US}}$ NI

SI units

| Nominal diameter [mm] | T _a [°C] | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 ℃] |
|--------------------------|------------------------|---------------|----------------|----------------|----------------|----------------|---------------|
| 50 to 200 | 40 | 60 | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 50 | - | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 60 | - | 80 | 80 | 80 | 80 | 80 |

US units

| Nominal diameter [in] | T _a [°F] | T6 [185 °F] | T5 [212 °F] | T4 [275 °F] | T3 [392 °F] | T2 [572 °F] | T1 [842 °F] |
|--------------------------|------------------------|----------------|----------------|----------------|----------------|----------------|----------------|
| 2 to 8 | 104 | 140 | 176 | 176 | 176 | 176 | 176 |
| 2 to 8 | 122 | - | 176 | 176 | 176 | 176 | 176 |
| 2 to 8 | 140 | _ | 176 | 176 | 176 | 176 | 176 |

Order code for "Output", option B "4-20mA HART, pulse/frequency/switch output"

Ex ia, Ex d, $_{\rm C}{\rm CSA}_{\rm US}$ IS, $_{\rm C}{\rm CSA}_{\rm US}$ XP, $_{\rm C}{\rm CSA}_{\rm US}$ NI

SI units

| Nominal diameter [mm] | Т _а [°С] | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
|--------------------------|------------------------|---------------|------------------|----------------|----------------|----------------|----------------|
| 50 to 200 | 40 | _ 1) | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 50 | - | 60 ²⁾ | 80 | 80 | 80 | 80 |
| 50 to 200 | 60 | - | _ | 80 | 80 | 80 | 80 |

1) $T_a = 60 \text{ °C}$ for pulse/frequency/switch output $P_i \le 0.85 \text{ W}$

2) $T_a = 80 \text{ °C for pulse/frequency/switch output } P_i \le 0.85 \text{ W}$

US units

| Nominal diameter [in] | T _a [°F] | T6 [185 °F] | T5 [212 °F] | T4 [275 °F] | T3 [392 °F] | T2 [572 °F] | T1 [842 °F] |
|--------------------------|------------------------|----------------|-------------------|----------------|----------------|----------------|----------------|
| 2 to 8 | 104 | _ 1) | 176 | 176 | 176 | 176 | 176 |
| 2 to 8 | 122 | _ | 140 ²⁾ | 176 | 176 | 176 | 176 |
| 2 to 8 | 140 | _ | _ | 176 | 176 | 176 | 176 |

1) $T_a = 140$ °F for pulse/frequency/switch output $P_i \le 0.85$ W

2) $T_a = 176$ °F for pulse/frequency/switch output $P_i \le 0.85$ W

Order code for "Output", option C "4-20mA HART, 4-20mA analog"

Ex ia, Ex d, $_{C}CSA_{US}$ IS, $_{C}CSA_{US}$ XP, $_{C}CSA_{US}$ NI

SI units

| Nominal diameter [mm] | Т _а [°С] | T6 [85 ℃] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
|--------------------------|------------------------|--------------|----------------|----------------|----------------|----------------|----------------|
| 50 to 200 | 40 | 60 | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 50 | - | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 60 | - | 55 | 80 | 80 | 80 | 80 |

US units

| Nominal diameter [in] | T _a [°F] | T6 [185 °F] | T5 [212 °F] | T4 [275 °F] | T3 [392 °F] | T2 [572 °F] | T1 [842 °F] |
|--------------------------|------------------------|----------------|----------------|----------------|----------------|----------------|----------------|
| 2 to 8 | 104 | 140 | 176 | 176 | 176 | 176 | 176 |
| 2 to 8 | 122 | - | 176 | 176 | 176 | 176 | 176 |
| 2 to 8 | 140 | _ | 131 | 176 | 176 | 176 | 176 |

Order code for "Output", option D "4-20mA HART, PFS output; 4-20 mA input"

Ex ia, Ex d, $_{\rm C}{\rm CSA}_{\rm US}$ IS, $_{\rm C}{\rm CSA}_{\rm US}$ XP, $_{\rm C}{\rm CSA}_{\rm US}$ NI

SI units

| Nominal diameter [mm] | T _a ¹⁾ [°C] | T6 [85 °C] | T5 [100 °C] | T4 [135 ℃] | T3 [200 °C] | T2 [300 °C] | T1 [450 ℃] |
|--------------------------|--------------------------------------|---------------|----------------|---------------|----------------|----------------|---------------|
| 50 to 200 | 35 | 60 | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 50 | _ | 80 | 80 | 80 | 80 | 80 |
| 50 to 200 | 60 | _ | - | 80 | 80 | 80 | 80 |

1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C


US units


| | Nominal diameter [in] | T _a ¹⁾ [°F] | T6 [185 °F] | T5 [212 °F] | T4 [275 °F] | T3 [392 °F] | T2 [572 °F] | T1 [842 °F] | | |
|--|--|--------------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|--|--|
| | 2 to 8 | 95 | 140 | 176 | 176 | 176 | 176 | 176 | | |
| | 2 to 8 | 122 | _ | 176 | 176 | 176 | 176 | 176 | | |
| | 2 to 8 | 140 | _ | _ | 176 | 176 | 176 | 176 | | |
| | The following applies for installations with overvoltage protection in conjunction with temperature or T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: T_a = T_a - 35.6 °F | | | | | | | | | |
| Storage temperature | All components apart from the display modules: -40 to $+80$ °C (-40 to $+176$ °F), preferably at $+20$ °C ($+68$ °F) | | | | | | | | | |
| | Display modules | | | | | | | | | |
| | -40 to +80 °C (-40 to + | 176 °F) | | | | | | | | |
| Degree of protection | Transmitter • As standard: IP66/67, type 4X enclosure • When housing is open: IP20, type 1 enclosure • Display module: IP20, type 1 enclosure | | | | | | | | | |
| | Sensor IP66/67, type 4X enclosure | | | | | | | | | |
| Shock resistance | In accordance with EN 6 | 50721- | 3-4 | | | | | | | |
| Vibration resistance | Class 4M4, in accordan | ce with | EN 60721- | 3-4 | | | | | | |
| Electromagnetic compatibility (EMC) | As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) Complies with emission limits for industry as per EN 55011 | | | | | | | | | |
| | For details, refer to the Declaration of Conformity. | | | | | | | | | |

Process


| Medium temperature range | Sensor 0 to +80 °C (+32 to +176 °F) |
|---------------------------------|--|
| Pressure-temperature ratings | The following pressure-temperature ratings refer to the entire device and not just the process connection. |

Flange connection according to EN 1092-1 (DIN 2501)






Flange connection according to EN 1092-1 (DIN 2501)




☑ 12 With lap joint flange PN 10, material 1.4306 (304L) (DN 200 / 8")

Flange connection according to EN 1092-1 (DIN 2501)



I 3 With lap joint flange PN 10/16, materials S235JR (DN 50 to 200 / 2 to 8") and 1.4306 (304L) (DN 50 to 150 / 2 to 6"); With lap joint flange, stamped plate PN 10, material S235JR (DN 50 to 200 / 2 to 8")

Flange connection according to ASME B16.5



I4 With lap joint flange Class 150, materials 1.4404 (316L) and A105 (DN 50 to 200 / 2 to 8")

Flow limit

Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.

For an overview of the measuring range full scale values, see the "Measuring range" section $\rightarrow \cong 6$

The minimum recommended full scale value is approx. 1/20 of the maximum full scale value.
In most applications, 10 to 50 % of the maximum full scale value can be considered ideal.

| Pressure loss | There is no pressure loss. | | | | | |
|--------------------|--|--|--|--|--|--|
| System pressure | Sensor Max. 10 bar (145 psi) | | | | | |
| Thermal insulation | For optimum temperature and methane fraction measurement (order characteristic for "Sensor version", option 2 "Volume flow + Biogas analysis"), make sure that heat is neither lost nor applied to the sensor. Thermal insulation can ensure that such heat transfer does not take place. | | | | | |
| | Thermal insulation is particularly recommended in situations where there is a large difference between the process temperature and the ambient temperature. This can result in heat convection errors during temperature measurement. A further factor which can lead to measurement errors du to heat convection is a low flow velocity. | | | | | |


Mechanical construction

Dimensions in SI units

Compact version

Order code for "Housing", options C "GT20 two-chamber, aluminum coated" , S "GT18 two-chamber, stainless steel"

Lap joint flange; lap joint flange, stamped plate



| DN [mm] | A [mm] | B ¹⁾ [mm] | C [mm] | D ²⁾ [mm] | E [mm] | F ²⁾ [mm] | G ³⁾ [mm] | ØH [mm] | L [mm] |
|------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|------------|-----------|
| 50 | 162 | 102 | 60 | 165 | 75 | 90 | 254 | 56.3 | 250 |
| 80 | 162 | 102 | 60 | 165 | 75 | 90 | 268 | 84.9 | 300 |
| 100 | 162 | 102 | 60 | 165 | 75 | 90 | 281 | 110.3 | 300 |


| DN [mm] | A [mm] | B ¹⁾ [mm] | C [mm] | D ²⁾ [mm] | E [mm] | F ²⁾ [mm] | G ³⁾ [mm] | ØH [mm] | L [mm] |
|------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|------------|-----------|
| 150 | 162 | 102 | 60 | 165 | 75 | 90 | 308 | 164.3 | 350 |
| 200 | 162 | 102 | 60 | 165 | 75 | 90 | 334 | 213.9 | 400 |

1)

For version without local display: values - 7 mm For version with overvoltage protection (OVP): values + 8 mm For version without local display: values - 10 mm 2)

3)

Without flange




| DN [mm] | A [mm] | B ¹⁾ [mm] | C [mm] | D ²⁾ [mm] | E [mm] | F ²⁾ [mm] | G ³⁾ [mm] | ØH [mm] | L [mm] |
|------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|------------|-----------|
| 50 | 162 | 102 | 60 | 165 | 75 | 90 | 254 | 56.3 | 282.5 |
| 80 | 162 | 102 | 60 | 165 | 75 | 90 | 268 | 84.9 | 336.5 |
| 100 | 162 | 102 | 60 | 165 | 75 | 90 | 281 | 110.3 | 338.0 |
| 150 | 162 | 102 | 60 | 165 | 75 | 90 | 308 | 164.3 | 394.0 |
| 200 | 162 | 102 | 60 | 165 | 75 | 90 | 334 | 213.9 | 447.0 |

1)

For version without local display: values - 7 mm For version with overvoltage protection (OVP): values + 8 mm Version without local display: values - 10 mm

2) 3)

Lap joint flange



🖻 15 mm (in)

Lap joint flange according to EN 1092-1 (DIN 2501): PN 10 1.4301 (304L): order code for "Process connection", option D23 S235JR: order code for "Process connection", option D21

Lap joint flange according to EN 1092-1 (DIN 2501): PN 16 1.4306 (304L): order code for "Process connection", option D34 S235JR: order code for "Process connection", option D32

| DN [mm] | A [mm] | B [mm] | C [mm] | Ø D [mm] | L [mm] |
|------------|-----------|-----------|-----------|-------------|-----------|
| 50 | 165 | 125 | 22 | 4 × 18 | 250 |
| 80 | 200 | 160 | 22 | 8 × 18 | 300 |
| 100 | 220 | 180 | 24 | 8 × 18 | 300 |
| 150 | 285 | 240 | 26 | 8 × 22 | 350 |


Lap joint flange according to EN 1092-1 (DIN 2501): PN 10 1.4306 (304L): order code for "Process connection", option D24 S235JR: order code for "Process connection", option D22

| DN | A | B | C | Ø D | L |
|------|------|------|------|--------|------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 200 | 340 | 295 | 27 | 8 × 22 | 400 |

Lap joint flange according to ASME B16.5: Class 150 1.4404 (316L): order code for "Process connection", option A14 A105: order code for "Process connection", option A12

| DN [mm] | A [mm] | B [mm] | C [mm] | Ø D [mm] | L [mm] |
|------------|-----------|-----------|-----------|-------------|-----------|
| 50 | 152.4 | 120.7 | 21.1 | 4 × 19.1 | 250 |
| 80 | 190.5 | 152.4 | 25.9 | 4 × 19.1 | 300 |
| 100 | 228.6 | 190.5 | 25.9 | 8 × 19.1 | 300 |
| 150 | 279.4 | 241.3 | 27.4 | 8×22.4 | 350 |
| 200 | 342.9 | 298.5 | 31.0 | 8×22.4 | 400 |

Lap joint flange, stamped plate




🖻 16 mm (in)

| Lap joint flange, stamped plate according to EN 1092-1 (DIN 2501): PN 10 1.4301 (304): order code for "Process connection", option D23 S235JR: order code for "Process connection", option D21 | | | | | | | |
|--|-----|-----|----|----------|-----|--|--|
| DN A B C Ø D L [mm] [mm] [mm] [mm] [mm] | | | | | | | |
| 50 | 165 | 125 | 22 | 4 × 17.5 | 250 | | |
| 80 | 200 | 160 | 25 | 8 × 17.5 | 300 | | |
| 100 | 220 | 180 | 26 | 8 × 17.5 | 300 | | |
| 150 | 285 | 240 | 29 | 8 × 21.5 | 350 | | |
| 200 | 340 | 295 | 34 | 8 × 21.5 | 400 | | |


Accessories

Replacement tool



| Replacement tool Order code for "Accessory enclosed", option PS | | | | | | |
|--|-------------|-----------|-----------|------------|--|--|
| A [mm] | Φ B [mm] | C [mm] | D [mm] | E [mm] | | |
| 108 | 67 | 131 | 159 | 330 to 430 | | |

Flow conditioner



Flow conditioner according to EN 1092-1 (DIN 2501): PN 10/16 Order code for "Accessory enclosed", option PF

| , | | | | | | | | | |
|------------|-----------------|----------------------------|-------------------------------------|-----------|--|--|--|--|--|
| DN [mm] | Pressure rating | Centering diameter [mm] | D1 ¹⁾ / D2 ²⁾ | s [mm] | | | | | |
| 50 | PN 10/16 | 110.0 | D2 | 6.80 | | | | | |
| 80 | PN 10/16 | 145.3 | D2 | 10.1 | | | | | |
| 100 | PN 10/16 | 165.3 | D2 | 13.3 | | | | | |
| 150 | PN 10/16 | 221.0 | D2 | 20.0 | | | | | |
| 200 | PN 10 | 274.0 | D1 | 26.3 | | | | | |

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

| Flow conditioner according to ASME B16.5: Class 150 Order code for "Accessory enclosed", option PF | | | | | | | | |
|---|-----------------|----------------------------|-------------------------------------|-----------|--|--|--|--|
| DN [mm] | Pressure rating | Centering diameter [mm] | D1 ¹⁾ / D2 ²⁾ | s [mm] | | | | |
| 50 | Class 150 | 104.0 | D2 | 6.80 | | | | |
| 80 | Class 150 | 138.4 | D1 | 10.1 | | | | |
| 100 | Class 150 | 176.5 | D2 | 13.3 | | | | |
| 150 | Class 150 | 223.5 | D1 | 20.0 | | | | |
| 200 | Class 150 | 274.0 | D2 | 26.3 | | | | |


1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Dimensions in US units

Compact version

Order code for "Housing", options C "GT20 two-chamber, aluminum coated" , S "GT18 two-chamber, stainless steel"



Lap joint flange; lap joint flange, stamped plate


| DN [in] | A [in] | B ¹⁾ [in] | C [in] | D ²⁾ [in] | E [in] | F ²⁾ [in] | G ³⁾ [in] | Ø H [in] | L [in] |
|------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|-------------|-----------|
| 2 | 6.38 | 4.02 | 2.36 | 6.50 | 2.95 | 3.54 | 10.0 | 2.22 | 9.84 |
| 3 | 6.38 | 4.02 | 2.36 | 6.50 | 2.95 | 3.54 | 10.6 | 3.34 | 11.81 |
| 4 | 6.38 | 4.02 | 2.36 | 6.50 | 2.95 | 3.54 | 11.1 | 4.34 | 11.81 |
| 6 | 6.38 | 4.02 | 2.36 | 6.50 | 2.95 | 3.54 | 12.1 | 6.47 | 13.78 |
| 8 | 6.38 | 4.02 | 2.36 | 6.50 | 2.95 | 3.54 | 13.2 | 8.42 | 15.75 |

1)

For version without local display: values - 0.28 in For version with overvoltage protection (OVP): values + 0.31 in 2)

3) For version without local display: values - 0.39 in

Without flange



| DN [in] | A [in] | B ¹⁾ [in] | C [in] | D ²⁾ [in] | E [in] | F ²⁾ [in] | G ³⁾ [in] | Ø H [in] | L [in] |
|------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|-------------|-----------|
| 2 | 6.38 | 4.02 | 2.36 | 6.5 | 2.95 | 3.54 | 10.0 | 2.22 | 11.1 |
| 3 | 6.38 | 4.02 | 2.36 | 6.5 | 2.95 | 3.54 | 10.6 | 3.34 | 13.2 |
| 4 | 6.38 | 4.02 | 2.36 | 6.5 | 2.95 | 3.54 | 11.1 | 4.34 | 13.3 |
| 6 | 6.38 | 4.02 | 2.36 | 6.5 | 2.95 | 3.54 | 12.1 | 6.47 | 15.5 |
| 8 | 6.38 | 4.02 | 2.36 | 6.5 | 2.95 | 3.54 | 13.1 | 8.42 | 17.6 |


Dimensions in US units for version without overvoltage protection

1)

For version without local display: values - 0.28 in For version with overvoltage protection (OVP): values + 0.31 in Version without local display: values - 0.39 in 2)

3)

Lap joint flange




17 mm (in)

| Lap joint flange according to ASME B16.5: Class 150 1.4404 (316L): order code for "Process connection", option A14 A105: order code for "Process connection", option A12 | | | | | | | | |
|--|-------|-------|------|----------|-------|--|--|--|
| DN A B C ØD L [in] [in] [in] [in] [in] | | | | | | | | |
| 2 | 6.00 | 4.75 | 0.83 | 4 × 0.75 | 9.84 | | | |
| 3 | 7.50 | 6.00 | 1.02 | 4 × 0.75 | 11.81 | | | |
| 4 | 9.00 | 7.50 | 1.02 | 8 × 0.75 | 11.81 | | | |
| 6 | 11.00 | 9.50 | 1.08 | 8 × 0.88 | 13.78 | | | |
| 8 | 13.50 | 11.75 | 1.22 | 8 × 0.88 | 15.75 | | | |

Accessories


Replacement tool



| Replacement tool Order code for "Accessory enclosed", option PS | | | | | | |
|--|-------------|-----------|-----------|-----------|--|--|
| A [in] | Ø B [in] | C [in] | D [in] | E [in] | | |
| 4.25 | 2.64 | 5.16 | 6.26 | 13 to 17 | | |

Flow conditioner

(according to EN 1092-1 (DIN 2501))



| Flow conditioner according to ASME B16.5: Class 150 Order code for "Accessory enclosed", option PF | | | | | | | | |
|---|-----------------|----------------------------|-------------------------------------|-----------|--|--|--|--|
| DN [in] | Pressure rating | Centering diameter [in] | D1 ¹⁾ / D2 ²⁾ | s [in] | | | | |
| 2 | Class 150 | 4.09 | D2 | 0.27 | | | | |
| 3 | Class 150 | 5.45 | D1 | 0.40 | | | | |
| 4 | Class 150 | 6.95 | D2 | 0.52 | | | | |
| 6 | Class 150 | 8.81 | D1 | 0.79 | | | | |
| 8 | Class 150 | 10.8 | D2 | 1.04 | | | | |

1) 2) The flow conditioner is fitted at the outer diameter between the bolts. The flow conditioner is fitted at the indentations between the bolts.

Weight

Weight in SI units

Compact version

All values (weight) refer to devices with EN (DIN) PN 10/16 flanges. Weight information in [kg].

Order code for "Housing", option C "GT20 two-chamber, aluminum coated"

| Nominal diameter | Lap joint flange 1.4306 S235JR | | lange Lap joint flange, stamped plat | |
|------------------|--------------------------------|-----------------|--------------------------------------|--------|
| [mm] | | | 1.4301 | S235JR |
| 50 | 9 | .5 | 5. | .9 |
| 80 | 11 | 8 | 7. | .5 |
| 100 | 14.0 | | 9. | .1 |
| 150 | 20.9 | | 12.3 | |
| 200 | 27 | ⁷ .9 | 19 | 9.1 |

Order code for "Housing", option S, "GT18 two-chamber, stainless steel"

| Nominal diameter | Lap joint flange 1.4306 S235JR | | Lap joint flange Lap joint flange, stamped plate | |
|------------------|--------------------------------|-----|--|--------|
| [mm] | | | 1.4301 | S235JR |
| 50 | 12 | .4 | 8. | .7 |
| 80 | 14 | .7 | 10 |).3 |
| 100 | 16.9 | | 12 | 0 |
| 150 | 23.7 | | 15 | 5.2 |
| 200 | 30 |).7 | 22 | 0 |

Weight in US units

Compact version

All values (weight) refer to devices with ASME B16.5, Class 150 flanges. Weight information in [lbs].

Order code for "Housing", option C "GT20 two-chamber, aluminum coated"

| Nominal diameter | Lap joint flange | |
|------------------|------------------|------|
| [in] | 316L | A105 |
| 2 | 18.8 | |
| 3 | 28.6 | |
| 4 | 38.0 | |
| 6 | 49.8 | |
| 8 | 7 | 7.4 |

Order code for "Housing", option S "GT18 two-chamber, stainless steel"

| Nominal diameter | Lap joint flange | |
|------------------|------------------|------|
| [in] | 316L | A105 |
| 2 | 25.1 | |
| 3 | 34.9 | |
| 4 | 44.3 | |
| 6 | 56.1 | |
| 8 | 83.7 | |

Accessories

Replacement tool

| Weight [kg] | Weight [lbs] |
|-------------|--------------|
| 3.66 | 8.07 |

Flow conditioner

Weight in SI units

| DN [mm] | Pressure rating | Weight [kg] |
|------------|-----------------|----------------|
| 50 | PN 10/16 | 0.5 |
| 00 | Class 150 | 0.5 |
| 80 | PN 10/16 | 1.4 |
| | Class 150 | 1.2 |
| 100 | PN 10/16 | 2.4 |
| | Class 150 | 2.7 |
| 150 | PN 10/16 | 6.3 |
| 150 | Class 150 | 6.3 |
| 200 | PN 10 | 11.5 |
| 200 | Class 150 | 12.3 |

Weight in US units


| DN [in] | Pressure rating | Weight [lbs] |
|------------|-----------------|-----------------|
| 2 | Class 150 | 1.1 |
| 3 | Class 150 | 2.6 |
| 4 | Class 150 | 6.0 |
| 6 | Class 150 | 14.0 |
| 8 | Class 150 | 27.0 |

Materials

Transmitter housing

- Order code for "Housing", option C "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Order code for "Housing", option **S**: stainless steel 1.4404 (316L)
- Window material: glass

Cable entries/cable glands



🖻 18 Possible cable entries/cable glands

- 1 Cable entry in transmitter housing or connection housing with internal thread M20 x 1.5
- Cable gland M20 x 1.5
 Adapter for cable entry
- 3 Adapter for cable entry with internal thread G ¹/₂" or NPT ¹/₂"

Order code for "Housing", option C "GT20 two-chamber, aluminum coated"

| Transmitter | | | | |
|--|---|---------------------|--|--|
| Cable entry/cable gland | Type of protection | Material | | |
| Cable gland M20 × 1.5 | Non-ExEx ia | Plastic | | |
| Adapter for cable entry with internal thread G ½" | For non-Ex and Ex (except for CSA Ex d/XP) | Nickel-plated brass | | |
| Adapter for cable entry with internal thread NPT ½" | For non-Ex and Ex | | | |

| Transmitter neck | | | | |
|-----------------------|----------------|---------------------|--|--|
| Cable gland | Measuring path | Material | | |
| Cable gland M20 × 1.5 | Two-path | Nickel-plated brass | | |
| Cable gland M12 × 1.5 | Single-path | | | |

| Sensor | | |
|-----------------------|---------------------|--|
| Cable gland Material | | |
| Cable gland M12 × 1.5 | Nickel-plated brass | |

Order code for "Housing", option S, "GT18 two-chamber, stainless steel"

| Transmitter | | | | |
|---|---|--------------------------------|--|--|
| Cable entry/cable gland | Type of protection | Material | | |
| Cable gland M20 × 1.5 | Non-ExEx ia | Stainless steel ,1.4404 | | |
| Adapter for cable entry with internal thread G ½" | For non-Ex and Ex (except for CSA Ex d/XP) | Stainless steel, 1.4404 (316L) | | |
| Adapter for cable entry with internal thread NPT ½" | For non-Ex and Ex | | | |

| Transmitter neck | | | | |
|-----------------------|----------------|-------------------------|--|--|
| Cable gland | Sensor version | Material | | |
| Cable gland M20 × 1.5 | Two-path | Stainless steel ,1.4305 | | |
| Cable gland M12 × 1.5 | Single-path | | | |

| Sensor | | |
|-----------------------|----------------|-------------------------|
| Cable gland | Sensor version | Material |
| Cable gland M20 × 1.5 | Two-path | Stainless steel ,1.4305 |
| Cable gland M12 × 1.5 | Single-path | |

Sensor housing

Stainless steel (cold worked):

- 1.4404 (316L)
- 1.4435 (316L)

Process connections

- Stainless steel:
 - 1.4301 (304) 1.4306 (304L)
- 1.4404 (316L)
- Steel S235JR
- Carbon steel A105

List of all available process connections $\rightarrow \implies 40$ F

Seals

- Converter: HNBR
- Temperature sensor: AFM 34

Accessories

Replacement tool

- Knurled handle: aluminum
- Stop cock: nickel-plated brass
- Shaft: brass
- Tensioning element: tempered steel

Flow conditioner

Stainless steel 1.4404 (316L) (in compliance with NACE MR0175-2003 and MR0103-2003)

Weather protection cover

Stainless steel 1.4404 (316L)

Process connections

– EN 1092-1 (DIN 2501)

- ASME B16.5

Flanges:


For information on the materials of the process connections $\rightarrow \ \bigspace{1.5}{10}$ 40 -

Operability

| Operating concept | Operator-oriented menu structure for user-specific tasks Commissioning Operation Diagnostics Expert level |
|-------------------|---|
| | Quick and safe commissioning Guided menus ("Make-it-run" wizards) for applications Menu guidance with brief explanations of the individual parameter functions |
| | Reliable operation Operation in the following languages: Via local display: English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Korean, Bahasa (Indonesian), Vietnamese, Czech, Swedish Via "FieldCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese Uniform operating philosophy applied to device and operating tools If replacing the electronic module, transfer the device configuration via the integrated memory (integrated HistoROM) which contains the process and measuring device data and the event logbook. No need to reconfigure. |
| | Efficient diagnostics increase measurement availability Troubleshooting measures can be called up via the device and in the operating tools Diverse simulation options, logbook for events that occur and optional line recorder functions |

Local operation

Via display module



Display elements

- 4-line display
- With order code for "Display; operation", option **E**:
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: –20 to +60 $^\circ$ C (–4 to +140 $^\circ$ F)
- The readability of the display may be impaired at temperatures outside the temperature range.


Operating elements

- With order code for "Display; operation", option **C**:
- Local operation with 3 push buttons: 🔄, 🔄, 🕥
- With order code for "Display; operation", option E:
- External operation via touch control; 3 optical keys: 🕞, 🕞, 🖲
- Operating elements also accessible in various hazardous areas

Additional functionality

- Data backup function
- The device configuration can be saved in the display module.
- Data comparison function
 - The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function
 The transmitter configuration can be transmitted to another device using the display module.

Via remote display and operating module FHX50




I9 Operating options via FHX50

- 1 Housing of remote display and operating module FHX50
- 2 SD02 display and operating module, push buttons: cover must be opened for operation
- 3 SD03 display and operating module, optical buttons: operation possible through cover glass

Remote operation

Via HART protocol

This communication interface is available in device versions with a HART output.




20 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 VIATOR Bluetooth modem with connecting cable
- 9 Transmitter

Service interface

Via service interface (CDI)



- 1 Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring device
- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

Certificates and approvals

| CE mark | The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied. | | |
|---------------|--|--|--|
| | Endress+Hauser confirms successful testing of t | he device by affixing to it the CE mark. | |
| C-Tick symbol | The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)". | | |
| Ex approval | The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate. | | |
| | The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center. | | |
| | ATEX/IECEx | | |
| | Currently, the following versions for use in hazardous areas are available: | | |
| | Ex d | | |
| | Category | Type of protection | |
| | II2G / Zone 1 | Ex d[ia] IIC T6-T1 Gb | |

Ex ia

| Category | Type of protection |
|---------------|--------------------|
| II2G / Zone 1 | Ex ia IIC T6-T1 Gb |

CCSA{US}

Currently, the following versions for use in hazardous areas are available:

XP

| Category | Type of protection |
|--------------------------------|------------------------------|
| Class I Division 1 Groups ABCD | XP (Ex d Flameproof version) |

IS

| Category | Type of protection |
|--------------------------------|---|
| Class I Division 1 Groups ABCD | IS (Ex i Intrinsically safe version), Entity-Parameter* |

NI

| Category | Type of protection |
|--------------------------------|---|
| Class I Division 2 Groups ABCD | NI (Non-incendive version), NIFW-Parameter* |

 $\star=$ Entity and NIFW parameters according to control drawings

NEPSI

Currently, the following versions for use in hazardous areas are available:

Ex d

| Category | Type of protection |
|----------|-----------------------|
| Zone 1 | Ex d[ia] IIC T6-T1 Gb |

| | Ex ia | | |
|---|--|---|--|
| | Category | Type of protection | |
| | Zone 1 | Ex ia IIC T6-T1 Gb | |
| HART certification | HART interface | | |
| | The measuring device is certified and registered by the HCF (HART Communication Foundation). The measuring system meets all the requirements of the following specifications: Certified according to HART 7 The device can also be operated with certified devices of other manufacturers (interoperability) | | |
| Pressure Equipment Directive | The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order. | | |
| | With the PED/G1/x (x = category) marking on the compliance with the "Essential Safety Requirement Equipment Directive 97/23/EC. Devices bearing this marking (PED) are suitable Media in Group 1 and 2 with a vapor pressure gr to 0.5 bar (7.3 psi) Devices not bearing this marking (PED) are designed engineering practice. They meet the requirement Directive 97/23/EC. The range of application is a Pressure Equipment Directive. | ents" specified in Annex I of the Pressure for the following types of medium: reater than, or smaller and equal gned and manufactured according to good ts of Art.3 Section 3 of the Pressure Equipment | |
| EN 60529 Degrees of protection provided by enclosures (IP code) EN 61010-1 Safety requirements for electrical equipment for measurement, control a IEC/EN 61326 Emission in accordance with Class A requirements. Electromagnetic con requirements). NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laborator | | measurement, control and laboratory use its. Electromagnetic compatibility (EMC | |

NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

- NAMUR NE 43
 - Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.
- NAMUR NE 53
- Software of field devices and signal-processing devices with digital electronics
- NAMUR NE 80
- The application of the pressure equipment directive to process control devices

 NAMUR NE 105
- Specifications for integrating fieldbus devices in engineering tools for field devices • NAMUR NE 107
- Self-monitoring and diagnosis of field devices
- NAMUR NE 131 Requirements for field devices for standard applications

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country → Products → Select measuring technology, software or components → Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com
- Product Configurator the tool for individual product configuration
 - Up-to-the-minute configuration data
 - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
 - Automatic verification of exclusion criteria
 - Automatic creation of the order code and its breakdown in PDF or Excel output format
 - Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

| Diagnostics functions | Package | Description |
|-----------------------|----------------------------|---|
| | HistoROM extended function | Comprises extended functions concerning the event log and the activation of the measured value memory. |
| | | Event log: Memory volume is extended from 20 message entries (basic version) to up to 100 entries. |
| | | Data logging (line recorder): Memory capacity for up to 1000 measured values is activated. 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Data logging is visualized via the local display or FieldCare. |

| ogy | Package | Description |
|-----|---------------------------------------|--|
| | Heartbeat Verification +Monitoring | Heartbeat Monitoring: Continuously supplies monitoring data, which are characteristic of the measuring principle, for an external condition monitoring system. This makes it possible to: Draw conclusions - using these data and other information - about the impact the measuring application has on the measuring performance over time. Schedule servicing in time. Monitor the product quality, e.g. gas pockets. |
| | | Heartbeat Verification: Makes it possible to check the device functionality on demand when the device is installed, without having to interrupt the process. Access via local operation or other operating interfaces, such as FieldCare for instance. Documentation of device functionality within the framework of manufacturer specifications, for proof testing for instance. End-to-end, traceable documentation of the verification results, including report. Makes it possible to extend calibration intervals in accordance with operator's risk assessment. |

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

 Device-specific accessories
 For the transmitter

 Accessories
 Description

 Prosonic Flow 200
transmitter
 Transmitter for replacement or storage. Use the order code to define the following
specifications:
• Approvals
• Output
• Display / operation
• Housing
• Software
• For details, see Installation Instructions EA00104D

| FHX50 housing to accommodate a display module → |
|--|
| SD02 display module (push buttons) SD03 display module (touch control) Housing material: |
| SD03 display module (touch control)Housing material: |
| Housing material: |
| 5 |
| |
| - Stainless steel CF-3M (316L, 1.4404) |
| Length of connecting cable: up to max. 60 m (196 ft) |
| (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft)) |
| The measuring device can be ordered with the FHX50 housing and a display |
| module. The following options must be selected in the separate order codes: Order code for measuring device, feature 030: |
| Option L or M "Prepared for FHX50 display" |
| Order code for FHX50 housing, feature 050 (device version): |
| Option A "Prepared for FHX50 display" |
| • Order code for FHX50 housing, depends on the desired display module in feature 020 (display, operation): |
| Option C: for an SD02 display module (push buttons) |
| – Option E: for an SD03 display module (touch control) |
| The FHX50 housing can also be ordered as a retrofit kit. The measuring device display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing: • Feature 050 (measuring device version): option B "Not prepared for FHX50 |
| display" • Feature 020 (display, operation): option A "None, existing displayed used" |
| For details, see Special Documentation SD01007F |
| deally, the overvoltage protection module should be ordered directly with the levice. See product structure, characteristic 610 "Accessory mounted", option NA Overvoltage protection". Separate order necessary only if retrofitting. |
| OVP10: For 1-channel devices (characteristic 020, option A): OVP20: For 2-channel devices (characteristic 020, options B, C, E or G) |
| For details, see Special Documentation SD01090F. |
| is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight or extreme cold in winter. |
| For details, see Special Documentation SD00333F |
| |

For the sensor

| Accessories | Description |
|------------------|--|
| Replacement tool | Is used to remove the converters on the fly for cleaning or replacement purposes. For details, see Installation Instructions EA00108D |
| Flow conditioner | Is used to shorten the necessary inlet run. |

| Communication-specific | Accessories | Description |
|------------------------|------------------------------|---|
| accessories | Commubox FXA195 HART | For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F |
| | Commubox FXA291 | Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see the "Technical Information" document TI405C/07 |
| | HART Loop Converter HMX50 | Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions BA00371F |

| Wireless HART adapter SWA70 | Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. For details, see Operating Instructions BA00061S |
|--------------------------------|--|
| | For details, see Operating Instructions BA00061S |
| Fieldgate FXA320 | Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. |
| | For details, see "Technical Information" TI00025S and Operating Instructions BA00053S |
| Fieldgate FXA520 | Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser. |
| | For details, see "Technical Information" TI00025S and Operating Instructions BA00051S |
| Field Xpert SFX350 | Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area . |
| | For details, see Operating Instructions BA01202S |
| Field Xpert SFX370 | Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area and the Ex area . |
| | For details, see Operating Instructions BA01202S |

| Service-specific accessories | Accessories | Description |
|------------------------------|-------------|--|
| | Applicator | Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections. Graphic illustration of the calculation results |
| | | Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project. |
| | | Applicator is available:Via the Internet: https://wapps.endress.com/applicatorOn CD-ROM for local PC installation. |
| | W@M | Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records. |
| | | W@M is available:Via the Internet: www.endress.com/lifecyclemanagementOn CD-ROM for local PC installation. |
| | FieldCare | FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition. |
| | | For details, see Operating Instructions BA00027S and BA00059S |
| System components | Accessories | Description |

| System components | Accessories | Description |
|-------------------|---|--|
| | Memograph M graphic display recorder | The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick. For details, see "Technical Information" TI00133R and Operating Instructions BA00247R |

-

| r | |
|-----------|---|
| RN221N | Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission. |
| | For details, see "Technical Information" TI00073R and Operating Instructions BA00202R |
| RNS221 | Supply unit for powering two 2-wire measuring devices solely in the non-Ex area. Bidirectional communication is possible via the HART communication jacks. |
| | For details, see "Technical Information" TI00081R and Brief Operating Instructions KA00110R |
| Cerabar M | The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value. |
| | For details, see "Technical Information" TI00426P, TI00436P and Operating Instructions BA00200P, BA00382P |
| Cerabar S | The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value. |
| | For details, see "Technical Information" TI00383P and Operating Instructions BA00271P |

Documentation

- For an overview of the scope of the associated Technical Documentation, refer to the following:
 The W@M Device Viewer : Enter the serial number from the nameplate (www.endress.com/deviceviewer)
 - The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

Brief Operating Instructions

| Measuring device | Documentation code |
|---------------------|--------------------|
| Prosonic Flow B 200 | KA01096D |

Operating Instructions

Safety Instructions

| Measuring device | Documentation code |
|---------------------|--------------------|
| | HART |
| Prosonic Flow B 200 | BA01031D |

Description of Device Parameters

| Measuring device | Documentation code HART |
|---------------------|----------------------------|
| Prosonic Flow B 200 | GP01012D |

Supplementary devicedependent documentation

| Contents | Documentation code |
|-----------------------------------|--------------------|
| ATEX/IECEx Ex d | XA01008D |
| ATEX/IECEx Ex i | XA01009D |
| _C CSA _{US} XP | XA01010D |
| _C CSA _{US} IS | XA01011D |
| INMETRO Ex d | XA01307D |
| INMETRO Ex i | XA01308D |

| Contents | Documentation code |
|------------|--------------------|
| NEPSI Ex d | XA01068D |
| NEPSI Ex i | XA01069D |

Special Documentation

| Contents | Documentation code |
|---|--------------------|
| Information on the Pressure Equipment Directive | SD00152D |
| Heartbeat Technology | SD01470D |

Installation Instructions

| Contents | Documentation code |
|---|---|
| Installation Instructions for spare part sets | Specified for each individual accessory |

Registered trademarks

HART®

Registered trademark of the HART Communication Foundation, Austin, USA

Applicator[®], **FieldCare[®]**, **Field XpertTM**, **HistoROM[®]**, **Heartbeat TechnologyTM** Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

