Safety Instructions **Display FHX50**

EAC: OEx ia IIC T6 Ga X

Ex ia IIIC T100°C Db X Ex ia IIIC T105°C Db X



Document: XA01601F-C

Safety instructions for electrical apparatus for explosion-hazardous areas $\rightarrow \square 3$



Display FHX50

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Extended order code	4
Safety instructions: General	5
Safety instructions: Special conditions	5
Safety instructions: Installation	7
Safety instructions: Zone 0	7
Temperature tables	7
Connection data	2

XA01601F-C Display FHX50

Associated documentation

This document is an integral part of the following Operating Instructions:

SD01007F/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Media Type: Documentation -> Documentation Type: Brochures and catalogs -> Text Search: CP00021Z
- On the CD for devices with CD-based documentation

Manufacturer's certificates

Certificate of Conformity TP TC 012/2011

Inspection authority:

LLC NANIO CCVE (OOO «HAHNO LICBЭ»)

Certificate number:

EA3C RU C-DE.AA87.B.00087/19

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- GOST 31610.0-2014 (IEC 60079-0:2011)
- GOST 31610.11-2014 (IEC 60079-11:2011)
- GOST 31610.26-2012 (IEC 60079-26:2006)

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FHX50 - ********* + A*B*C*D*E*F*G*..

(Device type) (Basic specifications) (Optional specifications)

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

^{* =} Placeholder

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Display FHX50



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FHX50

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
FHX50	GA	EAC OEx ia IIC T6 Ga X
	GM	EAC Ex ia IIIC T100°C Db X EAC Ex ia IIIC T105°C Db X

Position 3 (Display; Operation)			
Selected option	n	Description	
FHX50	А	None, use existing device display	
	С	C SD02 4-line, push buttons + data backup function	
	E	SD03 4-line, illum., touch control + data backup function	

Position 4 (Housing)		
Selected option	on	Description
FHX50	В	Single compartment, 316L
	С	Single compartment, alu, coated
	D	Single compartment, plastics PBT

Position 5 (Cable)		
Option sélectionnée		Description
FHX50	A	5m + M12 plug
	В	10m + M12 plug
	D	20m + M12 plug
	Е	30m + M12 plug
	1	Provided by customer, M16, max 60m
	2	Provided by customer, NPT1/2, max 60m ¹⁾

1) Only in connection with Position 4 (Housing) = B, C

XA01601F-C Display FHX50

Position 6 (Option Measurement Device)		
Selected option		Description
FHX50	A	Prepared for remote display FHX50
B Not prepared for display FHX50 + retrofit kit		

Optional specifications

ID Jx (Test, Cert	tificate)	
Selected option		Description
FHX50	JN	Ambient temperature transmitter −50 °C

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates, ..)
 - Of isolated capacities (e.g. isolated metallic plates)
- Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

Safety instructions: Special conditions

Permitted ambient temperature range at the electronics housing:

 $-40 \,^{\circ}\text{C} \le T_a \le +80 \,^{\circ}\text{C}$

Optional specification, ID Jx (Test, Certificate) = JN

Permitted ambient temperature range at the electronics housing:

 $-50 \, ^{\circ}\text{C} \le T_a \le +80 \, ^{\circ}\text{C}$

- Observe the information in the temperature tables.
- In the event of additional or alternative special varnishing on the housing or other metal parts:
 - Observe the danger of electrostatic charging and discharge.
 - Do not rub surfaces with a dry cloth.


Basic specification, Position 4 (Housing) = C

In Zone 0, avoid sparks caused by impact and friction.

Basic specification, Position 4 (Housing) = D

Avoid electrostatic charging of the housing (e.g. friction, cleaning, maintenance, strong medium flow).

Safety instructions: Installation



A0032629

■ 1

- Power supply or certified associated apparatus (dependent on Endress+Hauser measuring device)
- 2 Display FHX50 in Zone 0/1/2, Zone 21 or 22
- 3 Endress+Hauser measuring device
- 4 Local potential equalization

Continuous service temperature of the connecting cable: $-40\,^{\circ}\text{C}$ to $\geq +85\,^{\circ}\text{C}$; in accordance with the range of service temperature taking into account additional influences of the process conditions $(T_{a,min})$, $(T_{a,max} + 20\,\text{K})$.

Optional specification, ID Jx (Test, Certificate) = JN

Continuous service temperature of the connecting cable: -50 °C to $\geq +85$ °C; in accordance with the range of service temperature taking into account additional influences of the process conditions ($T_{a,min}$), ($T_{a,max}$ +20 K).

Intrinsic safety

- When the device is connected to an intrinsically safe circuit Ex ib, the type of protection changes to Ex ib. Do not operate intrinsically safe circuits Ex ib in Zone 0 or Zone 20.
- When the device is connected to an intrinsically safe circuit Ex ic, the type of protection changes to Ex ic. Do not operate intrinsically safe circuits Ex ic in Zone 0, Zone 1 or Zone 20, Zone 21.

Potential equalization

Integrate the device into the local potential equalization.

Safety instructions: Zone 0

- In the event of potentially explosive vapor/air mixtures, only operate the device under atmospheric conditions.
 - Temperature: -20 to +60 °C
 - Pressure: 80 to 110 kPa (0.8 to 1.1 bar)
 - \blacksquare Air with normal oxygen content, usually 21 % (V/V)
- If no potentially explosive mixtures are present, or if additional protective measures have been taken, the device may also be operated under non-atmospheric conditions in accordance with the manufacturer's specifications.

Temperature tables

Basic specification, Position 4 (Housing) = B, C

Zone 0, Zone 1, Zone 2	
Temperature class T6	$T_a \le +60 ^{\circ}\text{C}$

Zone 21, Zone 22	
Max. surface temperature at T_a +80 $^{\circ}C$	+100 ℃

XA01601F-C Display FHX50

Basic specification, Position 4 (Housing) = D

Zone 0, Zone 1, Zone 2	
Temperature class T6	$T_a \le +55 ^{\circ}\text{C}$

Zone 21, Zone 22	
Max. surface temperature at T_a +80 $^{\circ}\text{C}$	+105 ℃

Connection data

FHX50

Power supply and signal circuit

$$\begin{split} &U_i = 7.3 \ V \\ &l_i = 157 \ mA \\ &P_i = 362 \ mW \end{split}$$
 effective inner inductance $L_i = 0$

effective inner capacitance $C_i = 263 \text{ nF}$

The device can be connected to a measuring device which has an intrinsically safe display circuit. For more information see "Connectable transmitters" section.

Connectable transmitters

- To connect the device to a measuring device, such as a measuring device from Endress+Hauser, it must meet the following conditions:
 - The device has an intrinsically safe display circuit
 - The device specifically bears the information "Prepared for display FHX50"
 - The device is prepared for display FHX50 using the retrofit kit
- Please note the "Connectable transmitters" section in the Special Documentation SD01007F provided!

Basic specification, Position 6 (Option Measurement Device) = A, B

All transmitters for which the device structure provides the "Prepared for display FHX50" (A) option can be converted using the retrofit kit (B).

Please note the "Extended order code" section in the Safety Instructions (XA) included with the transmitter.

The measuring device which has already been prepared for the FHX50 or converted using the retrofit kit has an intrinsically safe display circuit with the following characteristic values:

Power supply and signal circuit

 $U_0 = 7.3 \text{ V}$ $I_0 = 157 \text{ mA}$ $P_0 = 362 \text{ mW}$

effective outer inductance L_o = 149 μH effective outer capacitance C_o = 388 nF

Connectable cables

- Cables which are optionally available from Endress+Hauser: can be ordered up to a total length of 30 m.
- Maximum cable length: 60 m.
- The customer's own cable can be used if the total effective inductance and capacitance of the cable do not exceed the following values respectively:
 - \blacksquare Total inductance of cable L_c = 149 μH
 - Total capacitance of cable $C_c = 125 \text{ nF}$

Display module

• Display module present in the measuring device: The display module removed during conversion using the retrofit kit can be installed in the FHX50.

- Display module present in the FHX50: No action necessary.
- Display module not present: Display module must be ordered.

Basic specification, Position 6 (Option Measurement Device) = B

- For information on the suitability of the display module for conversion, see the "Connectable transmitters" section.
- Identification marking to identify the suitability of the display module: [AA], [AB] or [AC].





www.addresses.endress.com