TI00036D/06/EN/07.20

71463744 2020-02-03

# Technical Information **Magphant**

Electromagnetic flowmeter

# Cost-effective limit switch for reliable and repeatable flow monitoring

## Application

- The bidirectional measuring principle is virtually independent of pressure, density, temperature and viscosity
- Universal usability for all water applications in utilities
- Device properties
- Compact, space-saving design
- Nominal diameter: DN 15 to 2000 ( $\frac{1}{2}$  to 80")
- Can be used with steel or plastic pipes
- Switch point setting via rotary switch
- Current output and relay output
- ATEX, FM, CSA

## Your benefits

- High plant availability reliable flow information
- Energy-saving flow measurement no pressure loss due to cross-section constriction
- Maintenance-free no moving parts
- Process safety device self-monitoring and reliable display even with empty pipes
- Product safety integrated testing to check correct functioning of the electronics
- Easy operation full-scale value adjustment via potentiometer



# Table of contents

About this document         3           Symbols         3
Function and system design4Measuring principle4Measuring system4
Input         5           Measured variable         5           Measuring range         5
Output         6           Output signal         6
Power supply6Terminal assignment6Supply voltage6Power consumption6Electrical connection7Potential equalization7Terminals7Cable specification7
Performance characteristics8Maximum measured error8Reproducibility8
Installation8Mounting location8Installation position8Inlet and outlet runs9Mounting conditions for welding socket10Installation conditions for T-fitting12
Environment12Ambient temperature range12Degree of protection12Electromagnetic compatibility (EMC)12
Process13Medium temperature range13Conductivity13Pressure-temperature ratings13
Mechanical construction13Dimensions13Weight14Materials14
Human interface14Local operation14Communication14
Certificates and approvals14Ex approval15

Other standards and guidelines	15
Ordering information	15
Accessories	15
Supplementary documentation	<b>16</b> 16 16

# About this document

# Symbols

# Electrical symbols

Symbol	Meaning
	Direct current
$\sim$	Alternating current
$\sim$	Direct current and alternating current
÷	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	<b>Protective Earth (PE)</b> A terminal which must be connected to ground prior to establishing any other connections.
	<ul><li>The ground terminals are situated inside and outside the device:</li><li>Inner ground terminal: Connects the protectiv earth to the mains supply.</li><li>Outer ground terminal: Connects the device to the plant grounding system.</li></ul>

# Symbols for certain types of information

Symbol	Meaning
	<b>Permitted</b> Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
×	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
1	<b>Tip</b> Indicates additional information.
Ĩ	Reference to documentation.
	Reference to page.
	Reference to graphic.
	Visual inspection.

## Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
X	Safe area (non-hazardous area)
≈ <b>→</b>	Flow direction

# Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



#### Formulae for calculation

- Induced voltage  $U_e = B \cdot L \cdot v$
- Volume flow  $Q = A \cdot v$

#### Measuring system

The device consists of a transmitter and a sensor.

The device is available as a compact version:

The transmitter and sensor form a mechanical unit.

Magphant	Transmitter
	<ul> <li>Materials: Transmitter housing: powder-coated die-cast aluminum</li> <li>Configuration: Via operating and display elements on the transmitter</li> <li>Cable entry: M20 × 1.5 cable gland or M20 × 1.5 thread or <sup>1</sup>/<sub>2</sub>" NPT thread or G <sup>1</sup>/<sub>2</sub>" thread</li> <li>Sensor</li> <li>Materials:</li> <li>Sensor tip: PVDF; Viton O-ring</li> <li>Electrodes: stainless steel, 1.4435 (316L)</li> <li>Sensor sleeve: Stainless steel, 1.4435 (316L) with clamping ring 1.4571 (316Ti) for welding socket 1.4435 (316L); Stainless steel, 1.4435 (316L)</li> <li>With clamping ring and NBR seal for welding socket 1.4435 (316L)</li> </ul>
Welding socket for steel pipes DN	Materials: stainless steel. 1.4435 (316L) or steel St.37/A570
25	
A0040147	
Welding socket for steel pipes ≥DN 40	Materials: stainless steel, 1.4435 (316L) or steel St.37/A570
Plastic union nut (1) and adapter	Materials:
piece (2) for plastic pipes	Plastic union nut: PVC
1 2 A0040149	<ul> <li>Adapter piece: stainless steel, 1.4435 (316L), Viton O-rings</li> </ul>

# Input

Measured variable	Volume flow
Measuring range	0.1 to 5 m/s (0.33 to 16.41 ft/s)

# Output



#### Current output 4 to 20 mA



## **Relay output**

Floating changeover contact

- 60 V AC/0.4 A
- 75 V DC/0.5 A

# Power supply

Terminal assignment	Supply voltage			Relay output			Current output 4 to 20 mA	
	1 (+)	2 (-)	23	24	25	26 (+)	27 (-)	
Supply voltage	24 $V_{DC}$ (20 to 30 $V_{DC}$ ) The power unit must be tested to ensure it meets safety requirements (e.g. PELV, SELV).							
Power consumption	<2.5 W							



## E 1 Electrical connection

- 1 Power supply cable
- 2 Signal cable
- 3 Ground terminals for cable shield
- 4 160 mA fuse, slow-blow

## Potential equalization

## Connection example, standard scenario

In order to ensure electromagnetic compatibility (EMC), we recommend connecting the measuring device to ground via the ground terminal on the housing.



Connection example, potential equalization

1 Copper wire,  $\leq 2.08 \text{ mm}^2$  (14 AWG)

Terminals	Terminal type	Screw terminals
	Conductor cross- section	0.2 to 1.5 mm <sup>2</sup> (24 to 16 AWG)

## Cable specification

#### Permitted temperature range

• The installation guidelines that apply in the country of installation must be observed.

• The cables must be suitable for the minimum and maximum temperatures to be expected.

# **Power supply cable** Standard installation cable is sufficient.

## Protective ground cable

Cable  ${\leq}2.08~mm^2$  (14 AWG) The grounding impedance must be less than 1  $\Omega.$ 

## Signal cable

*Current output* Standard installation cable is sufficient.

Relay output Standard installation cable is sufficient.

# **Performance characteristics**

Maximum measured error	o.r. = of reading			
	$\pm 2$ % o.r. at the measuring electrode with local adjustment at flow velocities >1 m/s			
Reproducibility	o.r. = of reading			
	±2 % o.r.			

# Installation



Preferably install the sensor in an ascending pipe, and ensure a sufficient distance to the next pipe elbow:  $h \geq \ 5 \times DN$ 

Installation position	Installatio	Recommendation	
	Vertical orientation	A0017337	
	Horizontal orientation, transmitter head up	A0015589	× <sup>1)</sup>

Installatio	Recommendation	
Horizontal orientation, transmitter head down	A0015590	<b>X</b> <sup>2)</sup>
Horizontal orientation, transmitter head at side	45° 45°	<b>3</b> )

- 1) Risk of air pockets.
- 2) Risk of build-up of solids.
- 3) This installation method in horizontal pipes ensures that the electrodes are always immersed in the flowing medium.

#### Alignment with flow direction

The sensor must be installed in such a way that the electrode axis is always at a 90° angle to the flow direction. The cable glands, which are located on the same axis, serve as a visual aid.



- 3 Position of electrode axis
- 1 Axis of electrodes
- 2 Axis of cable glands

Inlet and outlet runs

If possible, install the sensor upstream from fittings such as valves, T-pieces or elbows. Observe the following inlet and outlet runs to comply with accuracy specifications:





For information on the dimensions and installed lengths of the device  $\rightarrow$  🗎 13

Mounting conditions for welding socket

## Installation in steel pipes

The measuring device is mounted in steel pipes using the welding socket supplied. Two different types of welding socket are available, depending on the nominal diameter:

- Welding socket for pipes DN 25
- Welding socket for pipes ≥DN 40

# NOTICE

## Damage to the measuring device

- Only weld the welding socket when the measuring device is not installed.
- Pipe DN 25: Weld the welding socket at right angles to the axis of the piping.



Welding socket for pipes DN 25. Engineering unit mm (in)

▶ Pipe ≥DN 40: With the marking (according to the nominal diameter) flush against the outer wall of the pipe, weld the welding socket at right angles to the axis of the piping. The DN 300 marking must be used for nominal diameters >DN 300.



E 5 Welding socket for piping ≥DN 40. Engineering unit mm (in)

#### Installation in plastic pipe

For pipe sizes  $\geq$ DN 65, the measuring device is mounted in plastic pipes using a plastic welding socket. The plastic welding socket can be purchased from the Georg Fischer company. PVC, PP and PE sockets are available. Depending on the outer diameter of the pipe, the dimension L must be adjusted accordingly by the client onsite. Perform the following steps when installing a plastic welding socket:

# NOTICE

## Damage to the measuring device

- Only weld the welding socket when the measuring device is not installed.
- **1**. Determine dimension L: L = 40 S E.
- 2. Determine the welding socket taking dimension L into account.
- **3.** Taking immersion depth E into account, weld the welding socket at right angles to the axis of the piping.



Installation conditions for plastic welding socket. Engineering unit mm (in)

1 Plastic welding socket

L To be determined

S Pipe wall thickness

*E* Immersion depth of plastic welding socket (please refer to the table below for dimension *E*)

Immersion depth depending on the pipe outer diameter

Pipe outer diameter mm (in)	Immersion depth E mm (in)
65 (2.6)	6.9 (0.27)
75 (3.0)	8.3 (0.33)
110 (4.33)	11.4 (0.45)
125 (4.92)	14.4 (0.57)
140 (5.51)	17.7 (0.70)
160 (6.30)	17.7 (0.70)
200 (7.87)	12.0 (0.47)
225 (8.86)	10.0 (0.39)

Pipe outer diameter mm (in)	Immersion depth E mm (in)
250 (9.84)	10.0 (0.39)
280 (11,.0)	10.0 (0.39)
315 (12.4)	10.0 (0.39)
355 (14.0)	10.0 (0.39)
400 (17.8)	10.0 (0.39)
450 (17.7)	5.0 (0.20)
500 (19.7)	5.0 (0.20)
630 (24.8)	5.0 (0.20)

## Installation conditions for Tfitting

For pipe sizes DN 15 to 50, the measuring device is mounted in plastic pipes using a standard T-fitting. The T-fitting can be purchased from the Georg Fischer company. PVC, PP and PE T-fittings are available.

1 Only use the Magphant version for device installation in plastic pipes (order code for "Process connection", option 5 "Adapter, plastic pipe, 316L, NBR").



☑ 7 Installation conditions for T-fitting. Engineering unit mm (in)

1 Standard T-fitting

# Environment

Ambient temperature range	-20 to +60 °C (-4 to +140 °F)
	<ul><li>If operating outdoors:</li><li>Install the measuring device in a shady location.</li><li>Avoid direct sunlight, particularly in warm climatic regions.</li><li>Avoid direct exposure to weather conditions.</li></ul>
Degree of protection	IP66, Type 4X
Electromagnetic compatibility (EMC)	Details are provided in the Declaration of Conformity. As per EN 61326-1 and EN 61326-2-3

	Process	
Medium temperature range	<ul> <li>-20 to +120 °C (+4 to +248 °F) for welding socket made of 1.4435 (316L) with clamping ring</li> <li>-20 to +100 °C (+4 to +212 °F) for welding socket made of St.37/A570 with clamping ring and NBR seal</li> </ul>	
Conductivity	$\geq$ 20 µS/cm for liquids in general.	
Pressure-temperature ratings	• 16 bar (230 psi) at 25 °C (77 °F) • 10 bar (145 psi) at 120 °C (250 °F) $\begin{bmatrix} psi \\ 290 \\ 218 \\ 15 \\ 145 \\ 16 \\ 72 \\ 5 \\ 0 \\ 0 \\ 20 \\ 40 \\ 60 \\ 80 \\ 100 \\ 120 \end{bmatrix} [°C]$	
	68 104 140 176 212 248	

# Mechanical construction



# Dimension H

Pipe nominal diameter mm (in)	H for installation in steel pipes mm (in)	H for installation in plastic pipes
25 (0.98)	237.0 (9.331)	→ 🗎 11
40 (1.57)	234.0 (9.212)	

Pipe nominal diameter mm (in)	H for installation in steel pipes mm (in)	H for installation in plastic pipes
50 (1.97)	234.0 (9.212)	
80 (3.15)	230.0 (9.055)	
100 (3.94)	227.0 (8.937)	
150 (5.91)	220.5 (8.681)	
200 (7.87)	214.5 (8.445)	
250 (9.84)	207.5 (8.169)	
≥300 (11.81)	201.5 (7.933)	



# $\blacksquare Dimensions of welding sockets \rightarrow \blacksquare 10$

Weight

Materials

# Sensor

Sensor tip:

1.2 kg (2.6 lb)

- PVDF
- Viton O-ring
- Electrodes:
- Stainless steel, 1.4435 (316L)
- Sensor sleeve:
  - Stainless steel, 1.4435 (316L) with clamping ring 1.4571 (316Ti) for welding socket 1.4435 (316L)
  - Stainless steel, 1.4435 (316L) with clamping ring and NBR seal for welding socket ST.37/A570

## Welding socket (for steel pipes)

- Stainless steel, 1.4435 (316L)
- Steel St.37/A570

#### Adapter piece (for plastic pipes)

- Stainless steel, 1.4435 (316L)
- Viton O-rings

## Plastic union nut (for plastic pipes)

PVC

## **Transmitter housing**

Powder coated die-cast aluminum

# Human interface

Local operation	The device is operated and configured via operating and display elements on the transmitter .
Communication	The measured values are communicated to a higher-level system via the current output.

# **Certificates and approvals**

Currently available certificates and approvals can be called up via the product configurator. A

Ex approval	The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.
	The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.
	ATEX, IECEx
	Zone 2
	FM
	<ul> <li>NI Class I Division 2 Groups A-D</li> <li>DIP/II, III/1/EFG</li> <li>Type 4X</li> </ul>
	CSA
	<ul> <li>Class I, Division 2 Groups A-D</li> <li>Class II Groups E-G</li> <li>Class III</li> <li>Type 4X</li> </ul>
Other standards and guidelines	<ul> <li>EN 60529 Degrees of protection provided by enclosures (IP code) </li> <li>EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements </li> <li>IEC/EN 61326 Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).</li></ul>
	Ordering information
	Detailed ordering information is available for your nearest sales organization www.addresses.endress.com or in the Product Configurator under www.endress.com :
	1. Click Corporate
	2. Select the country
	3. Click Products
	4. Select the product using the filters and search field
	5. Open the product page
	The Configuration button to the right of the product image opens the Product Configurator.
	Due due to Configuration, the tool for individual and due to configuration.

# Product Configurator - the tool for individual product configuration • Up-to-the-minute configuration data

- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

# Accessories

Various accessories are available for the device, and can be ordered with the device or at a later stage from Endress+Hauser. An up-to-date overview of accessories is available from your local Endress +Hauser sales organization or on the product page of the Endress+Hauser website: www.endress.com.

#### Cover set

Order number	Description
50093653	Cover set, MAGPHANT

## Connection set (process)

Order number	Description
50093656	Welding socket set, DN 40 to 2000; 1.4435/316L
50093657	Welding socket set, DN 40 to 2000; St37/A570
50093658	Welding socket set, DN 25; 1.4435/316L
50093659	Welding socket set, DN 25; St37/A570
50093662	Socket set for connection, PVC

## *Connection set (electrical)*

Order number	Description
50093671	Set, 2 extensions PG16 /NPT1/2"
50093672	Set, 2 extensions PG16 /G 1/2"
50093673	Set, 2 extensions PG16 /M20x1.5

## Seal set

Order number	Description
50093631	Set, NBR seal, connection St37/A570

#### Set, electronics

Order number	Description
50093564	Set, electronics module, MAGPHANT
50093522	Set, 10 fuses T 0A16/250

# Supplementary documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- *W@M Device Viewer* (www.endress.com/deviceviewer): Enter the serial number from nameplate
- *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2D matrix code (QR code) on the nameplate

Standard documentation	Document type	Documentation code
	Brief Operating Instructions	KA01451D
	Operating Instructions	BA00025D
Device-dependent additional documentation	Document type	Documentation code
	Safety Instructions	XA00025D

www.addresses.endress.com

