

# Technical Information

## Micropilot FMR20

### HART

Free space radar

## Level measurement for liquids



#### Application

- Ingress protection: IP66/68 / NEMA 4X/6P
- Measuring range: up to 20 m (66 ft)
- Process temperature: -40 to 80 °C (-40 to 176 °F)
- Process pressure: -1 to 3 bar (-14 to 43 psi)
- Accuracy: up to  $\pm 2$  mm (0.08 in)
- International explosion protection certificates

#### Your benefits

- Level measurement for liquids in storage tanks, open basins, pump shafts and canal systems
- Radar measuring device with *Bluetooth*® wireless technology and HART communication
- Simple, safe and secure wireless remote access – ideal for installation in hazardous areas or places difficult to reach
- Commissioning, operation and maintenance via free iOS / Android app SmartBlue – saves time and reduces costs
- Full PVDF body - for a long sensor lifetime
- Hermetically sealed wiring and fully potted electronics – eliminates water ingress and allows operation under harsh environmental conditions
- Most compact radar due to unique radar chip design – fits in limited space installations
- Best price-performance-ratio radar



## Table of contents

<b>Important document information</b> . . . . .	<b>3</b>	Storage temperature . . . . .	20
Symbols used . . . . .	3	Climate class . . . . .	20
<b>Terms and abbreviations</b> . . . . .	<b>4</b>	Operating altitude as per IEC 61010-1 Ed.3 . . . . .	20
<b>Product life cycle</b> . . . . .	<b>5</b>	Degree of protection . . . . .	20
Engineering . . . . .	5	Vibration resistance . . . . .	20
Procurement . . . . .	5	Electromagnetic compatibility (EMC) . . . . .	21
Installation . . . . .	5	<b>Process</b> . . . . .	<b>22</b>
Commissioning . . . . .	5	Process temperature, process pressure . . . . .	22
Operation . . . . .	5	Dielectric constant . . . . .	22
Maintenance . . . . .	5	<b>Mechanical construction</b> . . . . .	<b>23</b>
Retirement . . . . .	5	Dimensions . . . . .	23
<b>Measuring principle</b> . . . . .	<b>6</b>	Weight . . . . .	27
Input . . . . .	6	Materials . . . . .	28
Output . . . . .	6	Connecting cable . . . . .	28
<b>Input</b> . . . . .	<b>7</b>	<b>Operability</b> . . . . .	<b>28</b>
Measured variable . . . . .	7	Operating concept . . . . .	28
Measuring range . . . . .	7	Operation via Bluetooth® wireless technology . . . . .	28
Operating frequency . . . . .	7	Via HART protocol . . . . .	29
Transmission power . . . . .	7	<b>Certificates and approvals</b> . . . . .	<b>30</b>
<b>Output</b> . . . . .	<b>7</b>	CE mark . . . . .	30
Output signal . . . . .	7	RoHS . . . . .	30
Digital output . . . . .	7	EAC conformity . . . . .	30
Signal on alarm . . . . .	8	RCM-Tick marking . . . . .	30
Linearization . . . . .	8	Approvals . . . . .	30
<b>Protocol-specific data, HART</b> . . . . .	<b>8</b>	Explosion-protected smartphones and tablets . . . . .	30
<b>Electrical connection</b> . . . . .	<b>9</b>	Pressure equipment with allowable pressure	
Cable assignment . . . . .	9	≤ 200 bar (2 900 psi) . . . . .	30
Supply voltage . . . . .	9	EN 302729-1/2 radio standard . . . . .	31
Power consumption . . . . .	9	FCC / Industry Canada . . . . .	31
Current consumption . . . . .	9	Japanese Radio Law and Japanese Telecommunications	
Starting time . . . . .	9	Business Law Compliance . . . . .	32
Power supply failure . . . . .	10	Mexico . . . . .	33
Connecting the device . . . . .	10	Other standards and guidelines . . . . .	33
Cable specification . . . . .	12	<b>Ordering information</b> . . . . .	<b>34</b>
Overvoltage protection . . . . .	12	<b>Accessories</b> . . . . .	<b>34</b>
<b>Performance characteristics</b> . . . . .	<b>13</b>	Device-specific accessories . . . . .	34
Reference operating conditions . . . . .	13	Communication-specific accessories . . . . .	55
Maximum measured error . . . . .	13	Service-specific accessories . . . . .	55
Measured value resolution . . . . .	13	System components . . . . .	56
Response time . . . . .	13	<b>Supplementary documentation</b> . . . . .	<b>56</b>
Influence of ambient temperature . . . . .	14	Brief Operating Instructions (KA) . . . . .	56
<b>Installation</b> . . . . .	<b>14</b>	Operating Instructions (BA) . . . . .	56
Installation conditions . . . . .	14	Safety Instructions (XA) . . . . .	56
<b>Environment</b> . . . . .	<b>20</b>	<b>Registered trademarks</b> . . . . .	<b>57</b>
Ambient temperature range . . . . .	20		













## Important document information

---

**Symbols used**

**Symbols for certain types of information and graphics**

-  **Permitted**  
Procedures, processes or actions that are permitted
-  **Forbidden**  
Procedures, processes or actions that are forbidden
-  **Tip**  
Indicates additional information
-  **Reference to documentation**
-  **Reference to graphic**
-  **Notice or individual step to be observed**
-  **Series of steps**
-  **Result of a step**
-  **Item numbers**
-  **Views**



## Terms and abbreviations

**BA**

Document type "Operating Instructions"

**KA**

Document type "Brief Operating Instructions"

**TI**

Document type "Technical Information"

**SD**

Document type "Special Documentation"

**XA**

Document type "Safety Instructions"

**PN**

Nominal pressure

**MWP**

MWP (Maximum working pressure/max. process pressure)

The MWP can also be found on the nameplate.

**ToF**

Time of Flight

**FieldCare**

Scalable software tool for device configuration and integrated plant asset management solutions

**DeviceCare**

Universal configuration software for Endress+Hauser HART, PROFIBUS, FOUNDATION Fieldbus and Ethernet field devices

**DTM**

Device Type Manager

 **$\epsilon_r$  (Dk value)**

Relative dielectric constant

**Operating tool**

The term "operating tool" is used in place of the following operating software:

- FieldCare / DeviceCare, for operation via HART communication and PC
- SmartBlue (app), for operation using an Android or iOS smartphone or tablet

**BD**


Blocking Distance; no signals are analyzed within the BD.

**PLC**

Programmable logic controller (PLC)




## Product life cycle

<b>Engineering</b>	<ul style="list-style-type: none"> <li>■ Proven radar measuring technology</li> <li>■ Level measurement and open channel flow measurement for Ex and non-Ex areas</li> <li>■ Flooding detection</li> <li>■ Wide range of installation possibilities and accessories</li> <li>■ Highest degree of ingress protection</li> <li>■ 2D/3D drawings</li> <li>■ Spec Sheet Producer</li> <li>■ Applicator Selection tool for selecting the perfect measurement solution</li> </ul> <p> Device not compatible with transmitters and sensors that use ultrasonic measurement technology (e.g. Prosonic FMU9x, FDU9x)</p>
<b>Procurement</b>	<ul style="list-style-type: none"> <li>■ Best price-performance-ratio radar</li> <li>■ Global availability</li> <li>■ Order code includes variety of mounting accessories and decentralized RIA15 process indicator for HART</li> </ul>
<b>Installation</b>	<ul style="list-style-type: none"> <li>■ Rear and front thread for flexible installation</li> <li>■ Slip-on flange for nozzle installation</li> <li>■ Complete measuring point: including mounting accessory, RIA15 and flooding protection tube</li> </ul>
<b>Commissioning</b>	<ul style="list-style-type: none"> <li>■ Quick and easy setup with the SmartBlue app and DeviceCare / FieldCare or RIA15</li> <li>■ No additional tools or adapters required</li> <li>■ Local languages (up to 15)</li> </ul>
<b>Operation</b>	<ul style="list-style-type: none"> <li>■ Continuous self-monitoring</li> <li>■ Diagnostics information according to NAMUR NE107 with remedial measures in the form of plain text messages</li> <li>■ Signal curve via SmartBlue (app) and DeviceCare / FieldCare</li> <li>■ Encrypted single point-to-point data transmission (tested by Fraunhofer Institute) and password-protected communication via <i>Bluetooth®</i> wireless technology</li> </ul>
<b>Maintenance</b>	<ul style="list-style-type: none"> <li>■ No maintenance required</li> <li>■ Technical experts on-call around the world</li> </ul>
<b>Retirement</b>	<ul style="list-style-type: none"> <li>■ Environmentally responsible recycling concepts</li> <li>■ RoHS compliance (restriction of certain hazardous substances), lead-free soldering of electronic components</li> </ul>



## Measuring principle

The Micropilot is a "downward-looking" measuring system, which functions according to the time-of-flight (ToF) method. It measures the distance from the reference point **R** to the product surface. Radar pulses are emitted by an antenna, reflected off the product surface and received again by the radar system.



1 Level / flow calibration parameter

*E* Empty calibration (= zero)

*F* Full calibration (= span)

*D* Measured distance

*L* Level ( $L = E - D$ )

*Q* Flow rate at measuring weirs or channels (calculated from the level using linearization)

*R* Reference point

### Input

The reflected radar pulses are received by the antenna and transmitted to the electronics. A microprocessor evaluates the signals and identifies the level echo caused by the reflection of the radar pulses at the product surface. This clear signal detection system benefits from over 30 years' experience with time-of-flight procedures.

The distance **D** to the product surface is proportional to the time of flight **t** of the pulse:

$$D = c \cdot t / 2,$$

where **c** is the speed of light.

Based on the known empty distance **E**, the level **L** is calculated:

$$L = E - D$$

### Output

The Micropilot is calibrated by entering the empty distance **E** (= zero point) and the full distance **F** (= span).

- Current output: 4 to 20 mA
- Digital output (HART, SmartBlue): 0 to 15 m (0 to 49 ft)<sup>1)</sup> or 0 to 20 m (0 to 66 ft) depending on antenna version

1) order code 010 (approval) "GA", "GB", "GR": 0 to 10 m (0 to 32.8 ft)



## Input

<b>Measured variable</b>	<p>The measured variable is the distance between the reference point and the product surface.</p> <p>The level is calculated based on <b>E</b>, the empty distance entered.</p>
<b>Measuring range</b>	<p><b>Maximum measuring range</b></p> <ul style="list-style-type: none"> <li>■ Device with 40 mm (1.5 in) antenna: 15 m (49 ft) <sup>2)</sup></li> <li>■ Device with 80 mm (3 in) antenna: 20 m (66 ft)</li> </ul> <p><b>Installation requirements</b></p> <ul style="list-style-type: none"> <li>■ Recommended tank height &gt; 1.5 m (5 ft) for media with low <math>\epsilon_r</math> value</li> <li>■ Open channel minimum width 0.5 m (1.6 ft)</li> <li>■ Calm surfaces</li> <li>■ No agitators</li> <li>■ No buildup</li> <li>■ Relative dielectric constant <math>\epsilon_r &gt; 4</math> Contact Endress+Hauser for lower <math>\epsilon_r</math> values</li> </ul> <p><b>Usable measuring range</b></p> <p>The usable measuring range depends on the antenna size, the medium's reflective properties, the installation position and any possible interference reflections.</p> <p><b>Media groups</b></p> <ul style="list-style-type: none"> <li>■ <math>\epsilon_r = 4</math> to 10 e.g. concentrated acid, organic solvents, ester, aniline, alcohol, acetone.</li> <li>■ <math>\epsilon_r &gt; 10</math> e.g. conductive liquids, aqueous solutions, diluted acids and bases</li> </ul> <p>Reduction of the maximum possible measuring range by:</p> <ul style="list-style-type: none"> <li>■ Media with bad reflective properties (= low <math>\epsilon_r</math> value)</li> <li>■ Formation of buildup, particularly of moist products</li> <li>■ Strong condensation</li> <li>■ Foam generation</li> <li>■ Freezing of sensor</li> </ul>
<b>Operating frequency</b>	K-band (~ 26 GHz)
<b>Transmission power</b>	<p><b>Mean power density in the direction of the beam</b></p> <ul style="list-style-type: none"> <li>■ At a distance of 1 m (3.3 ft): &lt; 12 nW/cm<sup>2</sup></li> <li>■ At a distance of 5 m (16 ft): &lt; 0.4 nW/cm<sup>2</sup></li> </ul>

## Output

<b>Output signal</b>	<p><b>4 to 20 mA</b></p> <p>An 4 to 20 mA interface is used for measured value output and to power to the device.</p>
<b>Digital output</b>	<p><b>HART®</b></p> <ul style="list-style-type: none"> <li>■ Signal encoding; FSK <math>\pm 0.5</math> mA over current signal</li> <li>■ Data transmission rate; 1 200 Bit/s</li> </ul> <p><b>Bluetooth® wireless technology (available as an optional extra)</b></p> <p>The device has a <i>Bluetooth®</i> wireless technology interface and can be operated and configured via this interface using the SmartBlue app.</p>

2) order code 010 (approval) "GA", "GB", "GR": 10 m (32.8 ft)



- The range under reference conditions is 25 m (82 ft)
- Incorrect operation by unauthorized persons is prevented by means of encrypted communication and password encryption
- The *Bluetooth*® wireless technology interface can be deactivated

**Signal on alarm**

Depending on the interface, failure information is displayed as follows:

- Current output  
Alarm current: 22.5 mA (in accordance with NAMUR recommendation NE 43)
- Operating tool via digital communication (HART) or SmartBlue (app)
  - Status signal (as per NAMUR Recommendation NE 107)
  - Plain text display with remedial action

**Linearization**

The linearization function of the device allows the conversion of the measured value into any unit of length, weight, flow or volume. In DeviceCare and FieldCare, there are preprogrammed linearization tables for volume calculation in vessels.

**Pre-programmed linearization curves**

- Horizontal cylindrical tank
- Sphere
- Tank with pyramid bottom
- Tank with conical bottom
- Tank with flat bottom

Other linearization tables of up to 32 value pairs can be entered manually.

## Protocol-specific data, HART

**Manufacturer ID**

17 (0x11)

**Device type ID**

44 (0x112c)

**HART specification**

7.0

**Device description files (DTM)**

Information and files under:

- [www.endress.com](http://www.endress.com)
- [www.hartcomm.org](http://www.hartcomm.org)

**HART load**

Min. 250 Ω

**HART device variables**

Assignment of HART device variables is fixed and cannot be changed.

- **Measured values for PV (primary variable)**  
Level linearized
- **Advanced diag. measured values for SV (secondary variable)**  
Distance
- **Advanced diag. measured values for TV (tertiary variable)**  
Relative echo amplitude
- **Advanced diag. measured values for QV (quarternary variable)**  
Temperature

**Supported functions**

Additional transmitter status

**Multidrop current**

4 mA


**Time for connection setup**

< 1 s



## Electrical connection

Cable assignment




A0028954

- 2 Cable assignment
- 1 Plus, brown wire
  - 2 Minus, blue wire

Supply voltage

10.5 to 30 V<sub>DC</sub>  
An external power supply is necessary.



A0029226

- 3 Maximum load R, depending on supply voltage U<sub>0</sub> of power supply unit

**Battery operation**

The sensor's *Bluetooth*® wireless technology communication can be disabled to increase the operating life of the battery.

**Potential equalization**

No special measures for potential equalization are required.



Various power supply units can be ordered as an accessory from Endress+Hauser.

Power consumption

Maximum input power: 675 mW

Current consumption

- Maximum input current: <25 mA
- Maximum start-up current: 3.6 mA

Starting time

First stable measured value after 20 s (with supply voltage = 24 V<sub>DC</sub>)




**Power supply failure**


The configuration remains stored in the sensor.

**Connecting the device****4 to 20 mA HART block diagram**

Connection of the device with HART communication, power source and 4 to 20 mA display



A0028908

 4 Block diagram of HART connection

- 1 Device with HART communication
- 2 HART resistor
- 3 Power supply



The HART communication resistor of  $250\ \Omega$  in the signal line is always necessary in the case of a low-impedance power supply.


**The voltage drop to be taken into account is:**

Max. 6 V for  $250\ \Omega$  communication resistor




**HART device block diagram, connection with RIA15**

FMR20 with RIA15 (incl. option for FMR20 basic configuration)

 The RIA15 remote indicator can be ordered together with the device.


**Product structure, feature 620 "Accessory enclosed":**

- Option R4 "Remote indicator RIA15 non-hazardous area, field housing"
- Option R5 "Remote indicator RIA15 with explosion protection approval, field housing"

 Alternatively available as an accessory, for details see Technical Information TI01043K and Operating Instructions BA01170K


**Terminal assignment RIA15**

- **+**  
Positive connection, current measurement
- **-**  
Negative connection, current measurement (without backlighting)
- **LED**  
Negative connection, current measurement (with backlighting)
- $\perp$   
Functional grounding: Terminal in housing


 The RIA15 process indicator is loop-powered and does not require any external power supply.

**The voltage drop to be taken into account is:**


- $\leq 1$  V in the standard version with 4 to 20 mA communication
- $\leq 1.9$  V with HART communication
- and an additional 2.9 V if display light is used

*Connection of the HART device and RIA15 without backlighting*


A0019567

 5 Block diagram of HART device with RIA15 process indicator without light

- 1 Device with HART communication
- 2 Power supply
- 3 HART resistor

*Connection of the HART device and RIA15 with backlighting*

A0019568

 6 Block diagram of HART device with RIA15 process indicator with light

- 1 Device with HART communication
- 2 Power supply
- 3 HART resistor



**Block diagram of HART device, RIA15 with installed HART communication resistor module**


 The HART communication module for installation in the RIA15 can be ordered together with the device.


**Product structure, feature 620 "Accessory enclosed":**

Option R6 "HART communication resistor hazardous / non-hazardous area"


**The voltage drop to be taken into account is:**

Max. 7 V


 Alternatively available as an accessory, for details see Technical Information TI01043K and Operating Instructions BA01170K

*Connection of the HART communication resistor module, RIA15 without backlighting*


A0020839

 7 Block diagram of HART device, RIA15 without light, HART communication resistor module

- 1 HART communication resistor module
- 2 Device with HART communication
- 3 Power supply

*Connection of the HART communication resistor module, RIA15 with backlighting*

A0020840

 8 Block diagram of HART device, RIA15 with light, HART communication resistor module

- 1 HART communication resistor module
- 2 Device with HART communication
- 3 Power supply

**Cable specification**

Unshielded cable, wire cross-section 0.75 mm<sup>2</sup>

- Resistant to UV and weather conditions as per ISO 4892-2
- Flame resistance according to IEC 60332-1-2

As per IEC/EN 60079-11 section 10.9, the cable is designed for a tensile strength of 30 N (6.74 lbf) (over a period of 1 h).

The device is supplied with 5 m (16 ft) cable length as standard. Cable lengths 10 m (33 ft) and 20 m (66 ft) are optionally available.


Lengths can be selected by the user up to an overall length of 300 m (980 ft) and are available by the meter (order option "8") or foot (order option "A").

**Overvoltage protection**

The device is equipped with integrated overvoltage protection.



Performance characteristics

Reference operating conditions	<ul style="list-style-type: none"><li>Temperature = +24 °C (+75 °F) ±5 °C (±9 °F)</li><li>Pressure = 960 mbar abs. (14 psia) ±100 mbar (±1.45 psi)</li><li>Humidity = 60 % ±15 %</li><li>Reflector: metal plate with diameter ≥ 1 m (40 in)</li><li>No major interference reflections inside the signal beam</li></ul>
Maximum measured error	<p>Typical data under reference operating conditions: DIN EN 61298-2, percentage values in relation to the span.</p> <p><b>Output, digital</b> (HART, SmartBlue (app))</p> <ul style="list-style-type: none"><li>Sum of non-linearity, non-repeatability and hysteresis: ±2 mm (±0.08 in)</li><li>Offset/zero point: ±4 mm (±0.16 in)</li></ul> <p><b>Output, analog</b> Only relevant for 4-20mA current output; add error of the analog value to the digital value</p> <ul style="list-style-type: none"><li>Sum of non-linearity, non-repeatability and hysteresis: ±0.02 %</li><li>Offset/zero point: ±0.03 %</li></ul> <p><b>Differing values in near-range applications</b></p> <div></div> <p>9 Maximum measured error in near-range applications; values for standard version</p> <p>Δ Maximum measured error R Reference point of the distance measurement D Distance from reference point of antenna</p>
Measured value resolution	<p>Dead band as per EN61298-2:</p> <ul style="list-style-type: none"><li>Digital: 1 mm (0.04 in)</li><li>Analog: 4 μA</li></ul>
Response time	<p>The response time can be configured. The following step response times apply (in accordance with DIN EN 61298-2) when damping is switched off:</p> <p><b>Tank height</b> &lt;20 m (66 ft)</p> <p><b>Sampling rate</b> 1 s<sup>-1</sup></p>



**Response time**


&lt;3 s

**i** In accordance with DIN EN 61298-2, the step response time is the time following an abrupt change in the input signal up until the changed output signal has adopted 90% of the steady-state value for the first time.

**Influence of ambient temperature****The measurements are carried out in accordance with EN 61298-3**

- Digital (HART, *Bluetooth*® wireless technology):  
Standard version: average  $T_C = \pm 3 \text{ mm } (\pm 0.12 \text{ in})/10 \text{ K}$
- Analog (current output):
  - Zero point (4 mA): average  $T_K = 0.02 \text{ } \%/10 \text{ K}$
  - Span (20 mA): average  $T_K = 0.05 \text{ } \%/10 \text{ K}$

## Installation

**Installation conditions****Installation types**

A0030605

**10 Wall, ceiling or nozzle installation**


- A Wall or ceiling mount, adjustable
- B Mounted at front thread
- C Mounted at rear thread
- D Ceiling installation with counter nut (included in delivery)
- E Horizontal installation in cramped spaces (wastewater shaft), 40 mm (1.5 in) antenna with flooding protection tube (accessory) or 80 mm (3 in) antenna recommended
- F Shaft wall mounting

**i Caution!**

- The sensor cables are not designed as supporting cables. Do not use them for suspension purposes.
- Always operate the device in a vertical position in free-space applications.



## Position for installation on a vessel



11 Installation position on a vessel

- If possible install the sensor so that its lower edge projects into the vessel.
  - Recommended distance **A** wall - nozzle outer edge:  $\sim \frac{1}{6}$  of the vessel diameter **D**. Under no circumstances should the device be mounted closer than 15 cm (5.91 in) to the vessel wall.
  - Do not install the sensor in the middle of the vessel.
  - Avoid measurements through the filling curtain.
  - Avoid equipment such as limit switches, temperature sensors, baffles, heating coils etc.
  - No signals are evaluated within the Blocking distance (BD). It can therefore be used to suppress interference signals (e.g. the effects of condensate) in the vicinity of the antenna.
- An automatic Blocking distance of at least 0.1 m (0.33 ft) is configured as standard. However, this can be overwritten manually (0 m (0 ft) is also permitted).

Automatic calculation:


Blocking distance = Empty calibration - Full calibration - 0.2 m (0.656 ft).

Each time a new entry is made in the **Empty calibration** parameter or **Full calibration** parameter, the **Blocking distance** parameter is recalculated automatically using this formula.

If the result of the calculation is a value  $< 0.1$  m (0.33 ft), the Blocking distance of 0.1 m (0.33 ft) will continue to be used.

## Nozzle installation

The antenna should be located out of the nozzle for optimum measurement. The interior of the nozzle must be smooth and may not contain any edges or welded joints. The edge of the nozzle should be rounded if possible.



12 Nozzle installation

A 80 mm (3 in) antenna

B 40 mm (1.5 in) antenna

The maximum length of the nozzle **L** depends on the nozzle diameter **D**.



Please note the limits for the diameter and length of the nozzle.

**80 mm (3 in) antenna, installation inside nozzle**

- D: min. 120 mm (4.72 in)
- L: max. 205 mm (8.07 in) + D × 4.5

**80 mm (3 in) antenna, installation outside nozzle**

- D: min. 80 mm (3 in)
- L: max. D × 4.5

**40 mm (1.5 in) antenna, installation outside nozzle**


- D: min. 40 mm (1.5 in)
- L: max. D × 1.5

**40 mm (1.5 in) antenna, installation inside nozzle**

- D: min. 80 mm (3 in)
- L: max. 140 mm (5.5 in) + D × 1.5

**Device alignment for installation on a vessel**


- Align the antenna vertically to the product surface.
- Align the eyelet with lug towards the vessel wall as well as possible.



A0028927

13 Device alignment for installation on a vessel

**Beam angle**



A0033201

14 Relationship between beam angle  $\alpha$ , distance  $D$  and beamwidth diameter  $W$

The beam angle is defined as the angle  $\alpha$ , at which the power density of the radar waves reaches half the value of the maximum power density (3 dB width). Microwaves are also emitted outside the signal beam and can be reflected off interfering installations.



Beam diameter  $W$  as a function of beam angle  $\alpha$  and distance  $D$ .

**40 mm (1.5 in) antenna,  $\alpha 30^\circ$**

$$W = D \times 0.54$$


**40 mm (1.5 in) antenna with flooding protection tube,  $\alpha 12^\circ$**

$$W = D \times 0.21$$

**80 mm (3 in) antenna with or without flooding protection tube,  $\alpha 12^\circ$**

$$W = D \times 0.21$$

### Measurement in plastic vessels



**15** Measurement in a plastic vessel with a metallic, interfering installation outside of the vessel

- 1 Pipe, tubing
- 2 Ladder
- 3 Grate, railing

If the outer wall of the vessel is made of a non-conductive material (e.g. GFR), microwaves can also be reflected by interfering installations outside of the vessel.

Please ensure there are no interfering installations made of a conductive material in the signal beam (see the beam angle section for information on calculating the beamwidth diameter).


Please contact the manufacturer for further information.

### Protective hood

For outdoor use, a protective hood is recommended.

The protective hood can be ordered as an accessory or together with the device via the product structure "Accessory enclosed".





A0031277

16 Protective hood, e.g. with 40 mm (1.5") antenna




The sensor is not completely covered by the protective hood.

### Free-field measurement with flooding protection tube

The flooding protection tube ensures the sensor measures the maximum level even if it is completely flooded.

In free-field installations and/or in applications where there is a risk of flooding, the flooding protection tube must be used.

The flooding protection tube can be ordered as an accessory or together with the device via the product structure "Accessory enclosed".



A0031093

17 Function of flooding protection tube


- 1 Air pocket
- 2 O-ring (EPDM) seal
- 3 Blocking distance
- 4 Max. level

The tube is screwed directly onto the sensor and seals off the system by means of an O-ring making it air-tight. In the event of flooding, the air pocket that formed in the tube ensures the measurement of the maximum level at the end of the tube. Due to the fact that the Blocking distance is inside the tube, multiple echoes are not analyzed.



### Installation with mounting bracket, adjustable

The mounting bracket can be ordered as an accessory or together with the device via the product structure "Accessory enclosed".



18 Installation with mounting bracket, adjustable

A0030606

- Wall or ceiling installation is possible.
- Using the mounting bracket, position the antenna so that it is perpendicular to the product surface.


#### NOTICE

**There is no conductive connection between the mounting bracket and transmitter housing.**  
Electrostatic charging possible.

- Integrate the mounting bracket in the local potential equalization system.

### Cantilever installation, with pivot

The cantilever, wall bracket and mounting frame are available as accessories.



19 Cantilever installation, with pivot


A0028412

- A Cantilever with wall bracket
- B Cantilever with mounting frame
- C Cantilever can be turned (e.g., in order to position the device over the center of the flume)

### Installation of horizontal mounting bracket for sewer shafts

The horizontal mounting bracket for sewer shafts is available as an accessory.






20 Installation of horizontal mounting bracket for sewer shafts  
A 40 mm (1.5 in) Antenna, with flooding protection tube (accessory)  
B 80 mm (3 in) Antenna, without flooding protection tube


Mounting in a shaft

The pivoted mounting bracket is available as an accessory.



21 Mounting in a shaft, pivotable and adjustable  
A Arm with wall bracket  
B Pivotable and adjustable arm (e.g. to align the device with the center of a channel)

Environment

Ambient temperature range	Measuring device: -40 to +80 °C (-40 to +176 °F) <div> It may not be possible to use the Bluetooth connection at ambient temperatures &gt; 60 °C (140 °F).</div> <div>Outdoor operation in strong sunlight:<ul style="list-style-type: none"><li>Mount the device in the shade.</li><li>Avoid direct sunlight, particularly in warm climatic regions.</li><li>Use a weather protection cover.</li></ul></div>
Storage temperature	-40 to +80 °C (-40 to +176 °F)
Climate class	DIN EN 60068-2-38 (test Z/AD)
Operating altitude as per IEC 61010-1 Ed.3	Generally up to 2 000 m (6 600 ft) above sea level.
Degree of protection	Tested acc. to: <ul style="list-style-type: none"><li>IP66, NEMA 4X</li><li>IP68, NEMA 6P (24 h at 1.83 m (6.00 ft) 1.83 m under water)</li></ul>
Vibration resistance	DIN EN 60068-2-64/IEC 60068-2-64: 20 to 2 000 Hz, 1 (m/s <sup>2</sup> ) <sup>2</sup> /Hz




---

<b>Electromagnetic compatibility (EMC)</b>	Electromagnetic compatibility in accordance with all of the relevant requirements outlined in the EN 61000 series and NAMUR Recommendation EMC (NE 21). Details are provided in the Declaration of Conformity ( <a href="http://www.endress.com/downloads">www.endress.com/downloads</a> ).
--	---



## Process

Process temperature, process pressure



A0029007-EN

22 FMR20: Permitted range for process temperature and process pressure

### Process temperature range

-40 to +80 °C (-40 to +176 °F)

### Process pressure range, threaded process connection

- $p_{rel} = -1$  to 3 bar (-14.5 to 43.5 psi)
- $p_{abs} < 4$  bar (58 psi)

### Process pressure range, UNI flange process connection

- $p_{rel} = -1$  to 1 bar (-14.5 to 14.5 psi)
- $p_{abs} < 2$  bar (29 psi)



The pressure range may be further restricted in the event of a CRN approval.

Dielectric constant

### For liquids

- $\epsilon_r \geq 4$
- Contact Endress+Hauser for lower  $\epsilon_r$  values



For dielectric constants (DC values) of many media commonly used in various industries refer to:


- the Endress+Hauser DC manual (CP01076F)
- the Endress+Hauser "DC Values App" (available for Android and iOS)



## Mechanical construction

Dimensions


40 mm (1.5 in) Antenna with G 1-½" or MNPT 1-½" thread



23 Dimensions of G 1-½" or MNPT 1-½" process connection thread, engineering unit: mm (in)

- A Cable gland
- B FNPT ½" conduit

40 mm (1.5 in) Antenna with G 2" or MNPT 2" thread




24 Dimensions of G 2" or MNPT 2" process connection thread, engineering unit: mm (in)

- A Cable gland
- B FNPT ½" conduit




40 mm (1.5 in) antenna with flooding protection tube



25 Dimensions of 40 mm (1.5 in) antenna mounted with flooding protection tube, engineering unit: mm (in)

The flooding protection tube, metalized PBT-PC, can be ordered together with the device via the product structure "Accessory enclosed".

80 mm (3 in)Antenna




26 Dimensions of 80 mm (3 in) antenna; engineering unit: mm (in)

- A Cable gland
- B FNPT 1/2" conduit



80 mm (3 in) antenna with flooding protection tube




27 Dimensions of 80 mm (3 in) antenna mounted with flooding protection tube, engineering unit: mm (in)

- A Cable gland  
B FNPT 1/2" conduit

The flooding protection tube, metalized PBT-PC, can be ordered together with the device via the product structure "Accessory enclosed".




**80 mm (3 in) antenna with slip-on flange 3"/DN80**

A0028813

28 Dimensions of 80 mm (3 in) antenna with slip-on flange 3"/DN80, engineering unit: mm (in)

The slip-on flange 3"/DN80, PVDF, can be ordered together with the device via the product structure "Accessory enclosed".


**80 mm (3 in) antenna with slip-on flange 4"/DN100**

A0028816

29 Dimensions of 80 mm (3 in) antenna with slip-on flange 4"/DN100, engineering unit: mm (in)

The slip-on flange 4"/DN100, PVDF, can be ordered together with the device via the product structure "Accessory enclosed".




**80 mm (3 in) antenna with slip-on flange 6"/DN150**

A0028818

30 Dimensions of 80 mm (3 in) antenna with slip-on flange 6"/DN150, engineering unit: mm (in)

The slip-on flange 6"/DN150, PVDF, can be ordered together with the device via the product structure "Accessory enclosed".

**Counter nut for process connection, rear side**

A0028419

31 Dimensions of counter nut for process connection, rear side, engineering unit: mm (in)

1 Seal


- The counter nut with seal (EPDM) is included in the scope of supply.
- Material: PA66

**Weight****Weight (incl. 5 m (16.4 ft) cable)**

- Device with 40 mm (1.5 in) antenna: approx. 2.5 kg (5.5 lb)
- Device with 80 mm (3 in) antenna: approx. 2.8 kg (6.2 lb)



Materials



A0028416

32 Overview of materials

- A 40 mm (1.5 in) Antenna
- B 80 mm (3 in) Antenna
- 1 Sensor housing; PVDF
- 2 Seal; EPDM
- 3 Process connection, rear side; PVDF
- 4 Cable gland; PA
- 5 Conduit adapter; CuZn nickel-plated
- 6 O-ring; EPDM
- 7 Counter nut; PA6.6
- 8 Design ring; PBT-PC
- 9 Process connection, front side; PVDF

Connecting cable


Available cable length: 5 to 300 m (16 to 980 ft)  
Material : PVC

Operability

Operating concept

- 4 to 20 mA, HART
- Menu guidance with brief explanations of the individual parameter functions in the operating tool
- Optional: SmartBlue (app) via Bluetooth® wireless technology

Operation via Bluetooth® wireless technology




A0028895

33 Possibilities for remote operation via Bluetooth® wireless technology

- 1 Transmitter power supply unit
- 2 Smartphone/tablet with SmartBlue (app)
- 3 Transmitter with Bluetooth® wireless technology



Via HART protocol



A0028894

34 Options for remote operation via HART protocol

- 1 PLC (programmable logic controller)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195
- 4 Loop-powered RIA15 process indicator
- 5 Commubox FXA195 (USB)
- 6 Computer with operating tool (FieldCare, DeviceCare)
- 7 Smartphone / tablet with SmartBlue (app)
- 8 Transmitter with Bluetooth® wireless technology



## Certificates and approvals



The availability of approvals and certificates can be called up daily via the Product Configurator.

<b>CE mark</b>	The measuring system meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied. Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
<b>RoHS</b>	The measuring system complies with the substance restrictions of the Restriction on Hazardous Substances Directive 2011/65/EU (RoHS 2).
<b>EAC conformity</b>	The measuring system meets the legal requirements of the applicable EAC guidelines. These are listed in the corresponding EAC Declaration of Conformity together with the standards applied. Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.
<b>RCM-Tick marking</b>	The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products are labelled with the RCM- Tick marking on the name plate.



A0029561

<b>Approvals</b>	<ul style="list-style-type: none"> <li>■ Non-hazardous area</li> <li>■ ATEX II 1 G Ex ia IIC T4 Ga</li> <li>■ ATEX II 1/2 G Ex ia IIC T4 Ga/Gb</li> <li>■ CSA C/US General Purpose</li> <li>■ CSA C/US IS Cl.I Div.1 Gr.A-D, AEx ia / Ex ia T4</li> <li>■ CSA C/US Cl.I Div.2 Gr.A-D, T4</li> <li>■ EAC Ex ia IIC T4 Ga/Gb</li> <li>■ IEC Ex ia IIC T4 Ga/Gb</li> <li>■ KC Ex ia IIC T4 Ga/Gb <sup>3)</sup></li> <li>■ INMETRO Ex ia IIC T4 Ga/Gb</li> <li>■ NEPSI Ex ia IIC T4 Ga/Gb</li> <li>■ TIIS Ex ia IIC T4 <sup>3)</sup></li> </ul> <p>Additional safety instructions must be followed for use in hazardous areas. Please refer to the separate "Safety Instructions" (XA) document included in the delivery. Reference to the applicable XA can be found on the nameplate.</p>
------------------	---

<b>Explosion-protected smartphones and tablets</b>	Only mobile end devices with Ex approval may be used in hazardous areas.
--	--

<b>Pressure equipment with allowable pressure ≤ 200 bar (2 900 psi)</b>	<p>Pressure instruments with a flange and threaded boss that do not have a pressurized housing do not fall within the scope of the Pressure Equipment Directive, irrespective of the maximum allowable pressure.</p> <p><b>Reasons:</b></p> <p>According to Article 2, point 5 of EU Directive 2014/68/EU, pressure accessories are defined as "devices with an operational function and having pressure-bearing housings".</p> <p>If a pressure instrument does not have a pressure-bearing housing (no identifiable pressure chamber of its own), there is no pressure accessory present within the meaning of the Directive.</p>
---	---

<sup>3)</sup> Under development at time of going to press



**EN 302729-1/2 radio standard**

The devices comply with the LPR (Level Probing Radar) radio standard EN 302729-1/2 and are approved for unrestricted use inside and outside of closed vessels in countries of the EU and EFTA. As a prerequisite, the countries in question must have already implemented this standard.

The following countries are those that have currently implemented the standard:

Belgium, Bulgaria, Germany, Denmark, Estonia, France, Greece, UK, Ireland, Iceland, Italy, Liechtenstein, Lithuania, Latvia, Malta, The Netherlands, Norway, Austria, Poland, Portugal, Romania, Sweden, Switzerland, Slovakia, Spain, Czech Republic and Cyprus.

Implementation is still underway in all of the countries not listed.

Please note the following for operation of the devices outside of closed vessels:

1. The device must be mounted in accordance with the instructions in the "Installation" section.
2. Installation must be carried out by properly trained, expert staff.
3. The device antenna must be installed in a fixed location pointing vertically downwards.
4. The installation site must be located at a distance of 4 km from the astronomy stations listed below or otherwise approval must be provided by the relevant authority. If the device is installed at a distance of 4 to 40 km from one of the listed stations, it must not be installed at a height of more than 15 m (49 ft) above the ground.

*Astronomy stations*

Country	Name of the station	Latitude	Longitude
Germany	Effelsberg	50°31'32" North	06°53'00" East
Finland	Metsähovi	60°13'04" North	24°23'37" East
	Tuorla	60°24'56" North	24°26'31" East
France	Plateau de Bure	44°38'01" North	05°54'26" East
	Floirac	44°50'10" North	00°31'37" West
Great Britain	Cambridge	52°09'59" North	00°02'20" East
	Damhall	53°09'22" North	02°32'03" West
	Jodrell Bank	53°14'10" North	02°18'26" West
	Knockin	52°47'24" North	02°59'45" West
	Pickmere	53°17'18" North	02°26'38" West
Italy	Medicina	44°31'14" North	11°38'49" East
	Noto	36°52'34" North	14°59'21" East
	Sardinia	39°29'50" North	09°14'40" East
Poland	Fort Skala Krakow	50°03'18" North	19°49'36" East
Russia	Dmitrov	56°26'00" North	37°27'00" East
	Kalyazin	57°13'22" North	37°54'01" East
	Pushchino	54°49'00" North	37°40'00" East
	Zelenchukskaya	43°49'53" North	41°35'32" East
Sweden	Onsala	57°23'45" North	11°55'35" East
Switzerland	Bleien	47°20'26" North	08°06'44" East
Spain	Yebes	40°31'27" North	03°05'22" West
	Robledo	40°25'38" North	04°14'57" West
Hungary	Penc	47°47'22" North	19°16'53" East



As a general rule, the requirements outlined in EN 302729-1/2 must be observed.



harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

*Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes: (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.*

[Any] Changes or modifications made to this equipment not expressly approved by Endress+Hauser may void the FCC authorization to operate this equipment.

**i** This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna
- Increase the separation between the equipment and receiver
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected
- Consult the dealer or an experienced radio/TV technician for help

**i**

- The installation of the LPR/TLPR device shall be done by trained installers, in strict compliance with the manufacturer's instructions.
- The use of this device is on a "no-interference, no-protection" basis. That is, the user shall accept operations of high-powered radar in the same frequency band which may interfere with or damage this device. However, devices found to interfere with primary licensing operations will be required to be removed at the user's expense.
- Only for usage without the accessory "flooding protection tube", i.e. NOT in the free-field: This device shall be installed and operated in a completely enclosed container to prevent RF emissions, which can otherwise interfere with aeronautical navigation.

#### FCC / Industry Canada IDs

##### Tank level-probing radar

- **HVIN: FMR20**
  - FCC ID: LCGFMR2XK
  - Industry Canada ID: 2519A-2K
- **HVIN: FMR20X**
  - FCC ID: LCGFMR2XKT
  - Industry Canada ID: 2519A-2KT

##### Level-probing radar:

- **HVIN: FMR20+R7; FMR20+R8**
  - FCC ID: LCGFMR2XKF
  - Industry Canada ID: 2519A-2KF
- **HVIN: FMR20+R7X; FMR20+R8X**
  - FCC ID: LCGFMR2XKL
  - Industry Canada ID: 2519A-2KL

#### Japanese Radio Law and Japanese Telecommunications Business Law Compliance

This device is granted pursuant to the Japanese Radio Law (電波法) and the Japanese Telecommunications Business Law (電気通信事業法). This device should not be modified (otherwise the granted designation number will become invalid).

Certified No.: 202-LSF004

The products are labelled with the Technical Conformity Mark (GITEKI) from Japanese Ministry of Internal Affairs and Communications (MIC) on the name plate.



**R** 202-LSF004

A0032960



## Mexico

El funcionamiento de este equipo está sujeto a las dos condiciones siguientes:

- (1) Este equipo o aparato no puede causar interferencias perjudiciales.
- (2) Este equipo o aparato debe aceptar todas las interferencias, incluyendo las que puedan causar un funcionamiento indeseado del equipo o aparato.

Este producto contiene un módulo inalámbrico

Marca: Endress+Hauser

Modelo: FMR20



A0034100

## Other standards and guidelines

- IEC/EN 61010-1  
Protection Measures for Electrical Equipment for Measurement, Control, Regulation and Laboratory Procedures
- IEC/EN 55011  
"EMC Emission, RF Emission for Class B". Industrial, scientific and medical equipment – Electromagnetic disturbance characteristics - Limits and methods of measurement
- IEC/EN 61000-4-2  
EMC Immunity, ESD (Performance Criteria A). Electromagnetic compatibility (EMC): Testing and measurement techniques - Electrostatic discharge immunity test (ESD)
- IEC/EN 61000-4-3  
EMC Immunity, RF field susceptibility (Performance Criteria A). Electromagnetic compatibility (EMC): Testing and measurement techniques - Radiated, radio-frequency, electromagnetic field immunity test
- IEC/EN 61000-4-4  
EMC Immunity, bursts (Performance Criteria B). Electromagnetic compatibility (EMC): Testing and measurement techniques - Electrical fast transient/burst immunity test
- IEC/EN 61000-4-5  
EMC Immunity, surge (Performance Criteria B). Electromagnetic compatibility (EMC): Testing and measurement techniques - Surge immunity test
- IEC/EN 61000-4-6  
EMC Immunity, conducted RF (Performance Criteria A). Electromagnetic compatibility (EMC): Testing and measurement techniques - Immunity to conducted disturbances induced by radio-frequency fields
- IEC/EN 61000-4-8  
EMC Immunity, magnetic fields 50 Hz. Electromagnetic compatibility (EMC): Testing and measurement techniques - Power frequency magnetic field immunity test
- EN 61000-6-3  
EMC Emission, conducted RF. EMC: Radiated interference - Residential, commercial and light industry environment
- NAMUR NE 21  
Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment
- NAMUR NE 43  
Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.
- NAMUR NE 107  
Status classification as per NE107
- NAMUR NE 131  
Requirements for field devices for standard applications
- IEEE 802.15.1  
Requirements for the *Bluetooth*® wireless technology interface



## Ordering information

Detailed ordering information is available for your nearest sales organization [www.addresses.endress.com](http://www.addresses.endress.com) or in the Product Configurator under [www.endress.com](http://www.endress.com) :

1. Click Corporate
2. Select the country
3. Click Products
4. Select the product using the filters and search field
5. Open the product page

The Configuration button to the right of the product image opens the Product Configurator.

### Product Configurator - the tool for individual product configuration


- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop


## Accessories

### Device-specific accessories

#### Protective cover

The protective cover can be ordered together with the device via the product structure "Accessory enclosed".



 35 Dimensions of protective cover, engineering unit: mm (in)

A0028841

**Material**  
PVDF



**Order number**


52025686



The sensor is not completely covered in the case of the 40 mm (1.5 in) antenna or the 80 mm (3 in) antenna.

**Securing nut G 1-1/2"**

Suitable for devices with G 1-1/2" and MNPT 1-1/2" process connection.



A0028849

36 Dimensions of securing nut, engineering unit: mm (in)

**Material**


PC

**Order number**

52014146

**Securing nut G 2"**

Suitable for devices with G 2" and MNPT 2" process connection on front.



A0029101

37 Dimensions of securing nut, engineering unit: mm (in)

**Material**

PC

**Order number**


52000598



**Flooding protection tube 40 mm (1.5 in)**

Suitable for use with devices with a 40 mm (1.5 in) antenna and G 1-1/2" process connection on front.

The flooding protection tube can be ordered together with the device via the product structure "Accessory enclosed".



A0028418

38 Dimensions of 40 mm (1.5 in) flooding protection tube, engineering unit: mm (in)

**Material**

PBT-PC, metalized

**Order number**


71325090



### Flooding protection tube 80 mm (3 in)

Suitable for use with devices with a 80 mm (3 in) antenna and "Mounting customer side w/o flange" process connection.

The flooding protection tube can be ordered together with the device via the product structure "Accessory enclosed".



39 Dimensions of 80 mm (3 in) flooding protection tube, engineering unit: mm (in)

### Material

PBT-PC, metalized


### Order number

71327051



**Mounting bracket, adjustable**

The mounting bracket can be ordered together with the device via the product structure "Accessory enclosed".



A0028861

40 Dimensions of mounting bracket, engineering unit: mm (in)

Consists of:

- 1 × mounting bracket, 316L (1.4404)
- 1 × mounting bracket, 316L (1.4404)
- 3 × screws, A4
- 3 × securing disks, A4


**Order number**

71325079



**UNI flange 2"/DN50/50, PP**

The UNI flange 2"/DN50/50 can be ordered together with the device via the product structure "Accessory enclosed".



41 Dimensions of UNI flange 2"/DN50/50, engineering unit: mm (in)

A Sensor connection in accordance with product structure "Process connection on front" or "Process connection on rear"

**Material**

PP


**Order number**

FAX50-####



**UNI flange 3"/DN80/80, PP**

The UNI flange 3"/DN80/80 can be ordered together with the device via the product structure "Accessory enclosed".



A0037947

42 Dimensions of UNI flange 3"/DN80/80, engineering unit: mm (in)

A Sensor connection in accordance with product structure "Process connection on front" or "Process connection on rear"

**Material**

PP


**Order number**

FAX50-####



**UNI flange 4"/DN100/100, PP**

The UNI flange 4"/DN100/100 can be ordered together with the device via the product structure "Accessory enclosed".



A0037948

43 Dimensions of UNI flange 4"/DN100/100, engineering unit: mm (in)

A Sensor connection in accordance with product structure "Process connection on front" or "Process connection on rear"


**Material**

PP

**Order number**

FAX50-####



**Angle bracket for wall mounting**

A0019346

44 Dimensions of angle bracket. Unit of measurement mm (in)

G Sensor connection in accordance with product structure "Process connection on front"

**Weight**

3.4 kg (7.5 lb)

**Material**

316L (1.4404)

**Order number for G 1-1/2" process connection**

71452324


Also suitable for MNPT 1-1/2"

**Order number for G 2" process connection**

71452325

Also suitable for MNPT 2"




**Cantilever with pivot***Installation type sensor process connection rear side*

A0028885

45 *Installation type sensor process connection rear side*

- A *Installation with cantilever and wall bracket*  
 B *Installation with cantilever and mounting frame*  
 1 *Cantilever*  
 2 *Wall bracket*  
 3 *Mounting frame*

*Cantilever (short) with pivot, sensor process connection on rear*

A0037806

46 *Dimensions of cantilever (short) with pivot for sensor process connection on rear. Unit of measurement mm (in)*

**Weight:**

2.1 kg (4.63 lb)

**Material**

316L (1.4404)

**Order number**


71452315



- 35 mm (1.38 in) openings for all G 1" or MNPT 1" connections on rear
- 22 mm (0.87 in) opening can be used for an additional sensor
- Retaining screws are included in delivery



## Endress+Hauser



**Order number**  
71452316


- Installation type sensor process connection front side



- 44



*Cantilever (short) with pivot, G 1-½" sensor process connection on front*



49 Dimensions of cantilever (short) with pivot for G 1-½" sensor process connection on front. Unit of measurement mm (in)

Weight:

1.9 kg (4.19 lb)

## Material


316L (1.4404)

## Order number

71452318

- 50 mm (2.17 in) openings for all G 1-1/2" (MNPT 1-1/2") connections on front
- 22 mm (0.87 in) opening can be used for an additional sensor
- Retaining screws are included in delivery

*Cantilever (long) with pivot, G 1-1/2" sensor process connection on front*



50 Dimensions of cantilever (long) with pivot for G 1-½" sensor process connection on front. Unit of measurement mm (in)



**Weight:**

4.4 kg (9.7 lb)

**Material**

316L (1.4404)


**Order number**

571452319



- 50 mm (2.17 in) openings for all G 1-½" (MNPT 1-½") connections on front
- 22 mm (0.87 in) opening can be used for an additional sensor
- Retaining screws are included in delivery

*Cantilever (short) with pivot, G 2" sensor process connection on front*



A0037804

51 Dimensions of cantilever (short) with pivot for G 2" sensor process connection on front. Unit of measurement mm (in)

**Weight:**

1.9 kg (4.19 lb)

**Material**

316L (1.4404)

**Order number**


71452321



- 62 mm (2.44 in) openings for all G 2" (MNPT 2") connections on front
- 22 mm (0.87 in) opening can be used for an additional sensor
- Retaining screws are included in delivery



Cantilever (long) with pivot, G 2" sensor process connection on front



A0037805

52 Dimensions of cantilever (long) with pivot for G 2" sensor process connection on front. Unit of measurement mm (in)

**Weight:**

4.4 kg (9.7 lb)

**Material**

316L (1.4404)


**Order number**

71452322



- 62 mm (2.44 in) openings for all G 2" (MNPT 2") connections on front
- 22 mm (0.87 in) opening can be used for an additional sensor
- Retaining screws are included in delivery

Mounting frame (short) for cantilever with pivot



A0037799

53 Dimensions of mounting frame (short). Unit of measurement mm (in)




**Weight:**  
3.2 kg (7.06 lb)

**Material**  
316L (1.4404)

**Order number**  
71452327

*Mounting frame (long) for cantilever with pivot*



A0037800


54 Dimensions of mounting frame (long). Unit of measurement mm (in)

**Weight:**  
4.9 kg (10.08 lb)

**Material**  
316L (1.4404)

**Order number**  
71452326

*Wall bracket for cantilever with pivot*



A0019350

55 Dimensions of the wall bracket. Unit of measurement mm (in)



**Weight**

1.4 kg (3.09 lb)

**Material**

316L (1.4404)

**Order number**

71452323








**Pivoted mounting bracket for sewer channel**

The pivotable mounting bracket is used to install the device in a manhole over a sewer channel.

The mounting bracket can be ordered together with the device via the "Accessory enclosed" section of the product order structure.



A0038143

57 Dimensions of pivotable mounting bracket. Unit of measurement mm (in)

**Material**

316L (1.4404)

**Order number**


71429910



**Horizontal mounting bracket for sewer shafts**

The horizontal mounting bracket for sewer shafts is used to install the device in confined spaces.

The mounting bracket can be ordered together with the device via the "Accessory enclosed" section of the product order structure.



A0038142

58 Dimensions of horizontal mounting bracket for sewer shafts. Unit of measurement mm (in)


**Material**

316L (1.4404)

**Order number**

71429905



**RIA15 in the field housing**

A0017722

59 Dimensions of RIA15 in field housing, engineering unit: mm (in)



The RIA15 remote indicator can be ordered together with the device. Product structure, feature 620 "Accessories enclosed":


- Option R4 "Remote indicator RIA15 non-hazardous area, field housing"
- Option R5 "Remote indicator RIA15 Ex= explosion protection approval, field housing"

Field housing material: Plastic (PBT with steel fibers, antistatic)

Other housing versions are available via the RIA15 product structure.



Alternatively available as an accessory, for details see Technical Information TI01043K and Operating Instructions BA01170K

**HART communication resistor**

A0020858

60 Dimensions of HART communication resistor, engineering unit: mm (in)



A communication resistor is required for HART communication. If this is not already present (e.g. in the power supply RMA, RN221N, RNS221, ...), it can be ordered with the device via the product structure, feature 620 "Accessories enclosed": option R6 "HART communication resistor hazardous / non-hazardous area".


Alternatively, it is available as an accessory; order number "RK01-BC"



Alternatively available as an accessory, for details see Technical Information TI01043K and Operating Instructions BA01170K

The HART communication resistor is specially designed for use with the RIA15 and can be attached easily.





A0020844

1. Disconnect plug-in terminal block.
2. Insert the terminal block into the slot provided on the HART communication resistor module.
3. Insert the HART communication resistor in the slot in the housing.



**Communication-specific accessories****Commubox FXA195 HART**

For intrinsically safe HART communication with FieldCare / DeviceCare via the USB interface.



For details, see Technical Information TI00404F

**HART Loop Converter HMX50**

Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.

Order number: 71063562



For details, see Technical Information TI00429F and Operating Instructions BA00371F

**WirelessHART adapter SWA70**

Is used for the wireless connection of field devices.

The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks.



For details, see Operating Instructions BA00061S

---

**Service-specific accessories****Applicator**

Software for selecting and sizing Endress+Hauser measuring devices:

- Calculation of all the necessary data for identifying the optimum measuring device: e.g. pressure loss, accuracy or process connections.
- Graphic illustration of the calculation results

Administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.

Applicator is available:

<https://portal.endress.com/webapp/applicator>

**Configurator**

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

The Configurator is available on the Endress+Hauser website: [www.endress.com](http://www.endress.com) -> Click "Corporate" -> Select your country -> Click "Products" -> Select the product using the filters and the search field -> Open the product page -> The "Configure" button to the right of the product image opens the Product Configurator.

**DeviceCare SFE100**

Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices

DeviceCare is available for download at [www.software-products.endress.com](http://www.software-products.endress.com). You need to register in the Endress+Hauser software portal to download the application.



Technical Information TI01134S

**FieldCare SFE500**

FDT-based plant asset management tool

It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.



Technical Information TI00028S

**W@M**

Life cycle management for your plant

W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle.

The application already contains the data of your Endress+Hauser device. Endress+Hauser also takes care of maintaining and updating the data records.



W@M is available:  
[www.endress.com/lifecyclemanagement](http://www.endress.com/lifecyclemanagement)

## System components

### Memograph M graphic data manager

The Memograph M graphic data manager provides information on all the relevant process variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on an SD card or USB stick.



For details, see Technical Information TI01180R and Operating Instructions BA01338R

### RNS221

Supply unit for powering two 2-wire measuring devices. Bidirectional communication is possible via the HART communication jacks.



For details, see Technical Information TI00081R and Brief Operating Instructions KA00110R

### RN221N

Active barrier with power supply for safe separation of 4 to 20 mA standard signal circuits. Bidirectional HART communication is possible via integrated communication jacks ( $R=250\ \Omega$ ).



For details, see Technical Information TI073R and Operating Instructions BA202R

### RMA42

Digital process transmitter for monitoring and displaying analog measured values



For details, see Technical Information TI00150R and Operating Instructions BA00287R

### RIA452

RIA452 digital process indicator, panel mounted housing for monitoring and displaying analog measured values with batch and pump control functions and flow calculation



For details, see Technical Information TI113R and Operating Instructions BA00254R

### HAW562

Overvoltage protection device for DIN rail as per IEC 60715, suitable for protecting electronics against destruction as a result of overvoltage.



For details, see Technical Information TI01012K

## Supplementary documentation

The following documentation types are available in the Downloads section of the Endress+Hauser website ([www.endress.com/downloads](http://www.endress.com/downloads)):



For an overview of the scope of the associated Technical Documentation, refer to the following:

- *W@M Device Viewer* ([www.endress.com/deviceviewer](http://www.endress.com/deviceviewer)): Enter the serial number from nameplate
- *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2D matrix code (QR code) on the nameplate

## Brief Operating Instructions (KA)

### Guide that takes you quickly to the 1st measured value

The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.

## Operating Instructions (BA)

### Your reference guide

These Operating Instructions contain all the information that is required in various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal.

## Safety Instructions (XA)

Depending on the approval, the following Safety Instructions (XA) are supplied with the device. They are an integral part of the Operating Instructions.



The nameplate indicates the Safety Instructions (XA) that are relevant to the device.



## Registered trademarks

### **HART®**

Registered trademark of the FieldComm Group, Austin, Texas, USA

### **Apple®**

Apple, the Apple logo, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

### **Android®**

Android, Google Play and the Google Play logo are trademarks of Google Inc.

### **Bluetooth®**

The *Bluetooth*® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Endress+Hauser is under license. Other trademarks and trade names are those of their respective owners.



---



---





71492916

[www.addresses.endress.com](http://www.addresses.endress.com)

---