

Manufacturer Declaration

Company: Endress+Hauser Flowtec AG, Kägenstrasse 7, CH-4153 Reinach

Products: WRAS Material Approval for Promag Electromagnetic Flowmeters

Statement: This is to confirm that the hard rubber lining material used in the Endress+Hauser Promag electromagnetic flowmeters, is certified according the Water Regulations Advisory Scheme (WRAS).


The hard rubber material used, Wagunit H 1005, is produced by WAGU-Gummitechnik GmbH. As the manufacturer of the hard rubber material, WAGU Gummitechnik GmbH is the holder of the WRAS approval with the approval number 1807555.

Endress + Hauser Flowtec AG herewith declares, that only WRAS approved Wagunit H1005 from WAGU-Gummitechnik GmbH is used in the production of our Promag electromagnetic flowmeters with WRAS drinking water approval.

Approval 1807555 is valid between July 2018 and July 2023

Reinach, 2021.04.08
Endress+Hauser Flowtec AG

i.V.


Winfried Amann
Senior Expert Customer Care

i.V.


Michael Fuchs
Head of Main Department RDA FE Sensoric A