Safety Instructions Proline Prowirl 200

UKEX: II2G, II1/2G, II1G Ex ia IIC T6 ... T1 II2D Ex tb IIIC Txx °C







Proline Prowirl 200

Table of contents

Associated documentation	4
Manufacturer's certificates	4
Manufacturer address	5
Extended order code	5
Safety instructions: General	8
Safety instructions: Installation	8
Safety instructions: Zone 0	10
Safety instructions: Zone 21	10
Temperature tables	11
Explosion hazards arising from gas and dust	19
Connection values: Signal circuits	20

Associated documentation

All documentation is available:

- On the CD-ROM supplied (not included in the delivery for all device versions).
- Available for all device versions via:
 - Internet: www.endress.com/deviceviewer
 - Smart phone/tablet: *Endress+Hauser Operations App*
- In the Download Area of the Endress+Hauser web site: www.endress.com → Download.

This document is an integral part of the following Operating Instructions:

Measuring				
device	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFINET-APL
Prowirl D 200	BA01685D	BA01693D	BA01689D	BA02133D
Prowirl F 200	BA01686D	BA01694D	BA01690D	BA02132D
Prowirl O 200	BA01687D	BA01695D	BA01691D	BA02134D
Prowirl R 200	BA01688D	BA01696D	BA01692D	BA02135D

Additional documentation

Contents	Document type	Documentation code
Remote display FHX50	Special documentation	SD01007F
	Safety Instructions II2G, II2D Ex ia	XA01053F
Overvoltage Protection (OVP)	Special documentation	SD01090F
Explosion Protection	Brochure	CP00021Z/11

Please note the documentation associated with the device.

Manufacturer's certificates

UK Declaration of Conformity

Documentation code: UK_00356

UKCA type-examination certificate

Certificate number: CML 21UKEX11112X

Manufacturer address


Endress+Hauser Flowtec AG

Kägenstrasse 7 4153 Reinach BL Switzerland

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code



specification is displayed instead of the placeholders.

Device type

The device and the device design is defined in the "Device type" section (Product root).

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Device type

Position	Order code for	Option selected	Description
1	Instrument family	7	Vortex flowmeter
2	Sensor	D, F, O, R	Sensor type
3	Transmitter	2	Transmitter type: 2-wire, compact version Remote version
4	Generation index	С	Platform generation
5, 6	Nominal diameter	D: DN 15150 F: DN 15300 O: DN 15300 R: Reducer DN 25200 Super reducer DN 40250	Nominal diameter of sensor

Basic specifications

Position	Order code for	Selected option	Description
1, 2	Approval	UA	Ex ia IIC T6T1 Ga
		UB	Ex ia IIC T6T1 Ga/Gb
		UJ	Ex ia IIC T6T1 Gb
		U2	Ex ia IIC T6T1 Ga/Gb
	Ex tb IIIC T		Ex tb IIIC Txx °C Db 1)
3	В 4-2		4-20mA HART
			4-20 mA HART, pulse/frequency/switch output
		С	4-20mA HART + 4-20mA analog
		D	4-20mA HART, pulse/frequency/switch output, 4-20mA input
		Е	FOUNDATION Fieldbus, Pulse/ frequency/switch output
		G	PROFIBUS PA, Pulse/frequency/switch output

Position	Order code for	Selected option	Description
4	Display; operation	A	W/o; via communication
		С	SD02 4-line; push buttons + data backup function
		Е	SD03 4-line, illum.; touch control + data backup function
		L	Prepared for display FHX50 + M12 connection ²⁾
		М	Prepared for display FHX50 + custom connection ²⁾
8, 9	Sensor version; DSC sensor; measuring tube Only available for sensors F, O, R with the HART communication protocol.	DA	Mass steam; 316L; 316L (integrated pressure/temperature measurement), -200 to +400 °C (-328 to +750 °F)
	-	DB	Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement), -40 to +260 °C (-40 to +500 °F)
		DC	Mass steam; Alloy 718; 316L (integrated pressure/temperature measurement), -200 to +400 °C (-328 to +750 °F)
		DD	Mass gas/liquid; Alloy 718; 316L (integrated pressure/temperature measurement), -40 to +100 °C (-40 to +212 °F)
11	Pressure component	A	Not used
	Only available for sensors F, O, R with the HART communication protocol.	В	Pressure measuring cell 2bar/29psi abs
	TANT communication protocol.	С	Pressure measuring cell 4bar/58psi abs
			Pressure measuring cell 10bar/145psi abs
		Е	Pressure measuring cell 40bar/580psi abs
		F	Pressure measuring cell 100bar/1450psi abs
		G	Pressure measuring cell 160bar/2320psi abs
16, 17	Device model	A1	1

The labeling changes according to whether "Display; operation" = "L" or "M": Ex tb[ia Da] IIIC Txx $^{\circ}$ C Db. FHX50 is separately approved.

1) 2)

Optional specifications

1	ID Order code for Option selected		Option selected	Description
J	X	Test, certificate	JN	Ambient temperature transmitter −50 °C
I	Vх	Accessory mounted	NA	Overvoltage Protection (OVP)

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations or guidelines (e.g. EN 60079-14)
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature classes.
- Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- When using in hybrid mixtures (gas and dust occurring simultaneously), observe additional measures for explosion protection.
- Observe all the technical data of the device (see nameplate).

Safety instructions: Installation

- Continuous service temperature of the connecting cable: -40 to +80 °C (-50 to +80 °C for optional specifications, ID Jx (Test, Certificate) = JN); in accordance with the range of service temperature taking into account additional influences of the process conditions ($T_{a,min}$ and $T_{a,max} + 20$ K).
- Only use certified cable entries suitable for the application. Observe selection criteria as per EN 60079-14.
- When the measuring device is connected, attention must be paid to explosion protection at the transmitter.

Basic specification, position 8, 9 (sensor version; DSC sensor; measuring tube) = DA, DB, DC, DD and position 11 (pressure component) = B, C, D, E, F, G

- The maximum medium temperature is limited for device versions with a pressure component that is installed directly on the sensor F, O. R:
 - To 40 °C for T6 and T5
 - To 90 °C for T4 and T1
- In the case of T4 ... T1 and medium temperatures > 90 °C the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R.
 - The spacer tube must have a minimum length of 50 cm (1.97 in).
 - The spacer tube supplied meets this requirement.

Intrinsic safety

- Observe the guidelines for interconnecting intrinsically safe circuits (e.g. EN 60079-14, Proof of Intrinsic Safety).
- The intrinsically safe input power circuit of the device is isolated from ground. If the device is only equipped with one input, the dielectric strength of the input is at least $500 \, V_{rms}$. If the device is equipped with more than one input, the dielectric strength of each individual input to ground is at least $500 \, V_{rms}$, and the dielectric strength of the inputs vis-à-vis one another is also at least $500 \, V_{rms}$.
- The device can be connected to the Endress+Hauser FXA291 service tool: refer to the Operating Instructions.
- The device can be connected to the remote display FHX50 with explosion protection; refer to the Special Documentation and Ex documentation.

Basic specification, position 3 (Output; input) = A, B, C, D, E, G:

- When the intrinsically safe Ex ia circuits of the device are connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC or IIB, the type of protection changes to Ex ib IIC or Ex ib IIB.
- When the intrinsically safe Ex ic circuits of the device are connected to certified intrinsically safe circuits of Category Ex ic for Equipment Groups IIB, the type of protection changes from Ex ic IIC to Ex ic IIB.

Potential equalization

- Integrate the device into the local potential equalization .
- If the ground connection has been established via the pipe as specified, it is also possible to integrate the sensor into the potential equalization system via the pipe.

Overvoltage protection

Optional specification, ID Nx (Accessory Mounted) = NA

- Minimum ambient temperature when using Overvoltage Protection (OVP): -40 °C
- When using the internal overvoltage protection: Reduce the admissible ambient temperature at the housing by 2 K.
- For installations which require overvoltage protection to comply with national regulations or standards, install the device using overvoltage protection (e.q. HAW56x from Endress+Hauser).
- Observe the safety instructions of the overvoltage protection.
- If an overvoltage protection against atmospheric over voltages is required: no other circuits may leave the enclosure during normal operation without additional measures.
- The intrinsically safe input power circuit of the device is isolated from ground. If the device is only equipped with one input, the dielectric strength of the input is at least 290 V_{rms} . If the device is equipped with more than one input, the dielectric strength of each individual input to ground is at least 290 V_{rms} , and the dielectric strength of the inputs vis-à-vis one another is also at least 290 V_{rms} .

Safety instructions: Zone 0

Basic specification, position 1, 2 (Approval) = UB, U2

The intrinsically safe version of the device can be used in the measuring pipe in Zone 0.

Basic specification, position 1, 2 (Approval) = UA

The sensor's coated aluminum AlSi10Mg transmitter or connector housing installed in Zone 0: Mechanical shock-proof installation.

Safety instructions: Zone 21

- To ensure dust-tightness, securely seal all housing openings, cable entries and sealing plugs.
- Only open all housing briefly, ensuring that no dust or moisture enters the housing.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Only use certified cable entries and sealing plugs. The metal cable entries, extensions and sealing plugs supplied meet this requirement.
- If the transmitter is connected to the remote display FHX50, the circuit has type of protection Ex ia IIIC.
 Connection values

Temperature tables

Ambient temperature

Minimum ambient temperature

Basic specification, position 3 (Output; Input) = A, B, D in conjunction with optional specification, ID Jx (Test, Certificate) = JN

$$T_a = -50 \,^{\circ}\text{C}$$

(Not permitted in conjunction with optional specification, ID Nx (Accessory Mounted) = $NA \rightarrow \bigcirc$ 9)

Basic specification, position 3 (Output; input) = A, B, C, D, E, G:

$$T_a = -40 \,^{\circ}\text{C}$$

Maximum ambient temperature:

- Compact version
 - $T_{\text{a}} = +70\,\,^{\circ}\text{C}$ depending on the medium temperature and temperature class
- Transmitter remote version
 - $T_{\text{a}} = +75\ ^{\circ}\text{C}$ depending on the medium temperature and temperature class
- Sensor remote version

 $T_{a} = +85\ ^{\circ}\text{C}$ depending on the medium temperature and temperature class

Medium temperature

The following relationship of ambient temperature to medium temperature applies when $T_{\rm m} < -50~{\rm ^{\circ}C}:$

T _m [°C]	-50	-100	-150	-200
T _a [°C]	-50	-47	-44	-39

Compact version

Basic specification, position 3 (output; input) = A

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

$$T_a = T_a - 2 K$$

Version	Version with max. $T_m = 280 ^{\circ}\text{C}$						
T _a [°C]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200°C]	T2 [300°C]	T1 [450 ℃]	
40	80 1)	95 ¹⁾	130 ¹⁾	195 ¹⁾	280 1)	-	
60	-	95 ^{2) 1)}	130 ¹⁾	195 ¹⁾	280 1)	-	

Version with max. T_m = 280 °C							
T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300 ℃]	T1 [450 ℃]	
65	-	-	130 ¹⁾	195 ¹⁾	280 1)	-	
70	-	-	130 ¹⁾	-	-	-	

- For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ...T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- T_a = 55 °C for device versions with pressure component option DA, DB, DC, DD.

Basic specification, position 3 (output; input) = B

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

►
$$T_a = T_a - 2 \text{ K}$$

Version	Version with max. $T_m = 280$ °C							
T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300°C]	T1 [450°C]		
35 ¹⁾	80 ²⁾	95 ²⁾	130 ²⁾	195 ²⁾	280 ²⁾	-		
50 ³⁾	-	95 ²⁾	130 ²⁾	195 ²⁾	280 ²⁾	-		
60	_	_	130 ²⁾	195 ²⁾	280 ²⁾	-		
65	-	_	130 ²⁾	195 ²⁾	280 4) 2)	_		
70	_	_	130 ²⁾	195 ^{5) 2)}	280 ⁵⁾	_		

- 1) $T_a = 40$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 2) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ... T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- 3) $T_a = 55$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0.7$ W
- 5) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.7$ W

Basic specification, position 3 (output; input) = C

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

 $ightharpoonup T_a = T_a - 2 K$

Version	Version with max. T_m = 280 °C							
T _a [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200°C]	T2 [300 °C]	T1 [450 ℃]		
40	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	280 1)	-		
55	-	95 ¹⁾	130 ¹⁾	195 ¹⁾	280 1)	_		
60	-	_	130 ¹⁾	195 ¹⁾	280 1)	-		
65	_	_	130 ¹⁾	195 ¹⁾	280 2) 1)	_		
70	-	-	130 ¹⁾	-	-	-		

- 1) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ...T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- 2) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0$ W

Basic specification, position 3 (output; input) = D

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

$$T_a = T_a - 2 K$$

Version	Version with max. T_m = 280 °C							
T _a [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 ℃]	T3 [200°C]	T2 [300°C]	T1 [450 ℃]		
35	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	280 1)	-		
50	-	95 ¹⁾	130 ¹⁾	195 ¹⁾	280 1)	-		
55	-	-	-	195 ¹⁾	280 1)	-		
60	-	-	-	195 ¹⁾	-	-		

1) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 $^{\circ}\text{C}$ for T6 ...T5 and to

 $90\,^{\circ}\text{C}$ for T4 ... T1. In the case of T4 ... T1 and medium temperatures > $90\,^{\circ}\text{C}$, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).

Basic specification, position 3 (output; input) = E, G

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

►
$$T_a = T_a - 2 \text{ K}$$

Version with max. $T_m = 280$ °C							
T _a [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]	
40	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	280 ¹⁾	-	
50	-	95 ¹⁾	130 ^{1) 2)}	195 ^{1) 2)}	280 1) 2)	-	
60	-	-	130 ¹⁾	195 ¹⁾	280 1)	-	
65	-	_	130 ¹⁾	195 ¹⁾	280 3) 1)	-	
70	-	-	130 ¹⁾	195 ^{4) 1)}	280 4) 1)	_	

- 1) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ... T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- 2) $T_a = 60$ °C for pulse/frequency/switch output $P_i = 0$ W
- T_a = 65 °C for pulse/frequency/switch output $P_i = 0 \text{ W}$
- 4) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0$ W

High-temperature version

Basic specification, position 3 (output; input) = A

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

$$ightharpoonup T_a = T_a - 2 K$$

Version	Version with max. T_m = 440 °C							
T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200°C]	T2 [300 °C]	T1 [450 ℃]		
40	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	290 1)	440 1)		
60	-	95 ^{2) 1)}	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 1)		
70	-	-	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 1)		

- For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ...T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- 2) $T_a = 55$ °C for device versions with pressure component option DA, DB, DC, DD.

Basic specification, position 3 (output; input) = B

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

 $ightharpoonup T_a = T_a - 2 K$

Version	Version with max. T_m = 440 °C							
T _a [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 ℃]	T1 [450°C]		
35 ¹⁾	80 ²⁾	95 ²⁾	130 ²⁾	195 ²⁾	290 ²⁾	440 ²⁾		
50 ³⁾	-	95 ²⁾	130 ²⁾	195 ²⁾	290 ²⁾	440 ²⁾		
65	-	-	130 ²⁾	195 ²⁾	290 ²⁾	440 ²⁾		
70	-	-	130 ²⁾	195 ^{4) 2)}	290 ²⁾	440 4) 2)		

- 1) $T_a = 40$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 2) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ... T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- 3) $T_a = 55$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.85$ W

Basic specification, position 3 (output; input) = C

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

► $T_a = T_a - 2 \text{ K}$

Version with max. T_m = 440 °C							
T _a [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 ℃]	T1 [450 ℃]	
40	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 1)	
55	-	95 ¹⁾	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 1)	
65	-	-	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 ¹⁾	
70	-	-	130 ¹⁾	195 ^{2) 1)}	290 ²⁾¹⁾	440 2) 1)	

- For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ...T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- 2) $T_a = 70 \,^{\circ}\text{C}$ for pulse/frequency/switch output $P_i = 0 \,^{\circ}\text{W}$

Basic specification, position 3 (output; input) = D

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

► $T_a = T_a - 2 \text{ K}$

Version	Version with max. T_m = 440 °C							
T _a [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]		
35	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 1)		
50	-	95 ¹⁾	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 1)		
55	-	_	-	195 ¹⁾	290 ¹⁾	440 1)		
60	-	-	-	195 ¹⁾	290 ¹⁾	440 1)		
65	-	_	_	_	290 ¹⁾	_		

1) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 $^{\circ}\text{C}$ for T6 ...T5 and to

90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).

Basic specification, position 3 (output; input) = E, G

NOTICE

The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for the basic specification, position 1, 2 (approval) = UA, UB, UJ, U2:

►
$$T_a = T_a - 2 \text{ K}$$

Version with max. $T_m = 440$ °C							
T _a [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200°C]	T2 [300°C]	T1 [450 ℃]	
40	80 ¹⁾	95 ¹⁾	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 ¹⁾	
50	-	95 ¹⁾	130 ^{1) 2)}	195 ^{1) 2)}	290 1) 2)	440 1) 2)	
65	-	-	130 ¹⁾	195 ¹⁾	290 ¹⁾	440 ¹⁾	
70	-	-	130 ¹⁾	195 ^{3) 1)}	290 ^{3) 1)}	440 3) 1)	

- For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ...T5 and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- T_a = 60 °C for pulse/frequency/switch output $P_i = 0 W$
- T_a = 70 °C for pulse/frequency/switch output $P_i = 0 \text{ W}$

Remote version

Transmitter

Basic specification, Position 3 Output; input ¹⁾	Basic specification, position 1, 2 Approval	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]
A	All	40	60	75
В	All	35 ²⁾	50 ³⁾	70 ⁴⁾
С	All	40	55	70 ⁵⁾

Basic specification, Position 3 Output; input ¹⁾	Basic specification, position 1, 2 Approval	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]
D	All	35	50	65
E G	All	40	55	70 ⁵⁾

- 1) The following applies for installations with overvoltage protection in conjunction with basic specification, position 1, 2 (approval) = UA, UB, UJ, U2: $T_a = T_a 2$ K
- 2) $T_a = 40$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 60 \,^{\circ}\text{C}$ for pulse/frequency/switch output $P_i = 0.85 \,^{\circ}\text{W}$
- 4) $T_a = 75$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- T_a = 75 °C for pulse/frequency/switch output $P_i = 0 W$

Sensor

Version with max. $T_m = 280 ^{\circ}\text{C}$							
T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300°C]	T1 [450 °C]	
55	80 1) 2)	95 ²⁾	130 ²⁾	195 ²⁾	280 ²⁾	-	
70	-	95 ^{3) 2)}	130 ²⁾	195 ²⁾	280 ²⁾	-	
85	-	-	130 ²⁾	195 ²⁾	280 ²⁾	-	

- 1) $T_a = 40$ °C For device versions with pressure component option DA, DB, DC, DD.
- 2) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to 40 °C for T6 ...T5 and to and to 90 °C for T4 ... T1. In the case of T4 ... T1 and medium temperatures > 90 °C, the pressure component DPC21 must be installed using a spacer tube between the pressure component and the sensor F, O, R. The length of the spacer tube must be at least 50 cm (1.97 in).
- T_a = 55 °C for device versions with pressure component option DA, DB, DC, DD.

High-temperature version

Version	Version with max. T_m = 440 °C							
T _a [°C]	T6 [85 ℃]	T5 [100 °C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]		
55	80 1) 2)	95 ²⁾	130 ²⁾	195 ²⁾	290 ²⁾	440 ²⁾		
70	-	95 ^{3) 2)}	130 ²⁾	195 ²⁾	290 ²⁾	440 ²⁾		
85	-	_	130 ²⁾	195 ²⁾	290 ²⁾	440 ²⁾		

- T_a = 40 °C For device versions with pressure component option DA, DB, DC, DD.
- 2) For device versions with a pressure component that is installed directly on the sensor F, O, R, the maximum medium temperature is limited to $40\,^{\circ}\text{C}$ for T6 ...T5 and to and to $90\,^{\circ}\text{C}$ for T4 ... T1. In the case of T4 ... T1 and medium temperatures $> 90\,^{\circ}\text{C}$, the pressure component DPC21 must be installed using a spacer tube between the

pressure component and the sensor F, O, R. The length of the spacer tube must be at least $50\ cm\ (1.97\ in)$.

3) $T_a = 55$ °C for device versions with pressure component option DA, DB, DC, DD.


Explosion hazards arising from gas and dust

Determining the temperature class and surface temperature with the temperature table

- In the case of gas: Determine the temperature class as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m.
- ullet In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m .

Example

- Measured maximum ambient temperature: $T_{ma} = 63 \, ^{\circ}\text{C}$
- Measured maximum medium temperature: $T_{mm} = 108 \, ^{\circ}\text{C}$



A0031266

- 1 Procedure for determining the temperature class and surface temperature
- 1. In the column for the maximum ambient temperature T_a select the temperature that is immediately greater than or equal to the maximum ambient temperature T_{ma} that is present.
 - $T_a = 65$ °C. The row showing the maximum medium temperature is determined.
- 2. Select the maximum medium temperature T_m of this row, which is immediately greater than or equal to the maximum medium temperature T_{mm} that is present.
 - The column with the temperature class for gas is determined: 108 °C \leq 130 °C \rightarrow T4.
- 3. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature for dust: $T4 = 135 \,^{\circ}\text{C}$.

Connection values: Signal circuits

The following tables contain specifications which are dependent on the transmitter type and its input and output assignment. Compare the following specifications with those on the nameplate of the transmitter.


Cable specification: Connecting cable for remote version

The sensor cable connection between the sensor and the transmitter has Ex ia type of protection.

Cable parameter: $L/R \le 38.2 \mu H/\Omega$

The cable supplied by Endress+Hauser complies with this value.

Connecting the transmitter



A0034702

Position		Basic specification, position 1, 2: Approval	Type of protection used for cable entry	Description		
1	Cable entry for output 1	UA, UB, UJ U2	Ex ia Ex ia/Ex tb	The following applies for devices with basic specification, position 1, 2 (approval) = U2: In the case of device versions with a plastic transport sealing plug, this plug does not meet the explosion protection requirements and must be replaced during installation by a suitable entry that meets the approval specifications. In the case of device versions with a cable entry, this entry has a separate component approval and meets the requirements of the explosion protection indicated on the nameplate.		
2	Cable entry for output 2	UA, UB, UJ U2	Ex ia Ex ia/Ex tb	The following applies for devices with basic specification, position 1, 2 (approval) = U2: In the case of device versions with metal extensions and sealing plugs, the latter are part of the device approval and meet the requirements of the explosion protection indicated on the nameplate. In the case of device versions with a cable entry, this entry has a separate component approval and meets the requirements of the explosion protection indicated on the nameplate.		
3	Optional order code ¹⁾ : Cable entry of the remote display and operating module FHX50	UA, UB, UJ U2	Ex ia Ex ia/Ex tb ²⁾	The following applies for devices with basic specification, position 1, 2 (approval) = U2: In the case of device versions with metal extensions and sealing plugs, the latter are part of the device approval and meet the requirements of the explosion protection indicated on the nameplate. In the case of device versions with a cable entry, this entry has a separate component approval and meets the requirements of the explosion protection indicated on the nameplate.		

Pos	sition	Basic specification, position 1, 2: Approval	Type of protection used for cable entry	Description		
4	Optional order code ³¹ : Cable entry of pressure measuring cell	UA, UB, UJ	Exia	-		
Pos	Position		Description			
5 Pressure compensation plug		NOTICE Housing degree of protection voided due to insufficient sealing of the housing. ▶ Do not open - not a cable entry.				
Potential equalization		NOTICE Terminal for connection to potential equalization. Pay attention to the grounding concept of the facility.				

- 1)
- 2)
- Basic specification, position 4 (display; operation) = L, M The labeling changes according to whether "Display; operation" = "L" or "M": Ex tb[ia Da] IIIC Txx $^{\circ}$ C Db. Basic specification, position 8, 9 (sensor version; DSC sensor; measuring tube) = DA, DA, DC, DD and position 11 (pressure component) = B, C, D, E, F, G 3)

Terminal assignment

Transmitter



Connection versions

Order code for	Terminal numbers					
"Output"	Output 1		Output 2		Input	
	1 (+)	2 (-)	3 (+)	4 (-)	5 (+)	6 (-)
Option A		20mA HART (passive)		-		
Option B ¹⁾	4-20mA HART (passive)		Pulse/frequency/ switch output (passive)		-	
Option C 1)	4-20mA HART (passive)		4-20mA analog (passive)		-	
Option D ^{1) 2)}		A HART sive)	Pulse/frequency/ switch output (passive)		4-20mA current input (passive)	
Option E ^{1) 3)}		OATION dbus	Pulse/frequency/ switch output (passive)		-	
Option G ^{1) 4)}	PROFII	BUS PA	Pulse/frequency/ switch output (passive)		-	

- 1) Output 1 must always be used; output 2 is optional.
- The integrated overvoltage protection is not used with option D: Terminals 5 and 6 (current input) are not protected against overvoltage.
- 3) FOUNDATION Fieldbus with integrated reverse polarity protection.
- 4) PROFIBUS PA with integrated reverse polarity protection.

Intrinsically safe values



The order code is part of the extended order code. Detailed information on the features of the device and on the structure of the extended order code $\rightarrow \blacksquare 5$.

Type of protection Ex ia

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$\begin{split} &U_{i} = DC \; 30 \; V \\ &I_{i} = 300 \; mA \\ &P_{i} = 1 \; W \\ &L_{i} = 0 \; \mu H \\ &C_{i} = 5 \; nF \end{split}$
Option B	4-20mA HART	$ \begin{aligned} &U_i = DC \; 30 \; V \\ &I_i = 300 \; mA \\ &P_i = 1 \; W \\ &L_i = 0 \; \mu H \\ &C_i = 5 \; nF \end{aligned} $
	Pulse/frequency/switch output	$\label{eq:controller} \begin{array}{l} U_i = DC~30~V\\ I_i = 300~mA\\ P_i = 1~W\\ L_i = 0~\mu H\\ C_i = 6~nF \end{array}$
Option C	4-20mA HART	U _i = DC 30 V
	4-20mA analog	$ \begin{aligned} & & I_i = 300 \text{ mA} \\ & & P_i = 1 \text{ W} \\ & & L_i = 0 \mu\text{H} \\ & & C_i = 30 n\text{F} \end{aligned} $
Option D	4-20mA HART	$ \begin{aligned} &U_i = DC \ 30 \ V \\ &I_i = 300 \ mA \\ &P_i = 1 \ W \\ &L_i = 0 \ \mu H \\ &C_i = 5 \ nF \end{aligned} $
	Pulse/frequency/switch output	$ \begin{aligned} &U_i = DC \; 30 \; V \\ &I_i = 300 \; mA \\ &P_i = 1 \; W \\ &L_i = 0 \; \mu H \\ &C_i = 6 \; nF \end{aligned} $
	4 to 20 mA current input	$ \begin{aligned} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{aligned} $
Option E	FOUNDATION Fieldbus	$STANDARD \\ U_i = 30 \text{ V} \\ l_i = 300 \text{ mA} \\ P_i = 1.2 \text{ W} \\ L_i = 10 \mu\text{H} \\ C_i = 5 \text{ nF} \\ \\$
	Pulse/frequency/switch output	$\label{eq:controller} \begin{split} U_i &= 30 \text{ V} \\ l_i &= 300 \text{ mA} \\ P_i &= 1 \text{ W} \\ L_i &= 0 \mu\text{H} \\ C_i &= 6 \text{ nF} \end{split}$

Order code for "Output"	Output type	Intrinsically safe values	
Option G	PROFIBUS PA	$\begin{split} & STANDARD \\ & U_i = 30 \ V \\ & I_i = 300 \ mA \\ & P_i = 1.2 \ W \\ & L_i = 10 \ \mu H \\ & C_i = 5 \ nF \end{split}$	
	Pulse/frequency/switch output	$\begin{split} &U_{l} = 30 \text{ V} \\ &l_{l} = 300 \text{ mA} \\ &P_{l} = 1 \text{ W} \\ &L_{l} = 0 \mu\text{H} \\ &C_{l} = 6 \text{ nF} \end{split}$	

Remote display FHX50

Basic specification, position 1, 2 Approval	Cable specification	Basic specification, position 4 Display; operation Option L, M	
	Max. cable length: 60 m (196.85 ft)	$U_0 = 7.3 \text{ V}$	
		I _o = 327 mA	
		P _o = 362 mW	
Option UA, UB, UJ, U2		L _o = 149 μH	
		C _o = 388 nF	
		C _c ≤ 125 nF	
		L _c ≤ 149 μH	





www.addresses.endress.com