

Safety Instructions

Nivotester FTL325P

II (1) G [Ex ia Ga] IIC

II (1) D [Ex ia Da] IIIC



Nivotester FTL325P

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Other standards	4
Extended order code	5
Safety instructions: General	6
Safety instructions: Installation	7
Temperature tables	10
Connection data	10

Associated documentation

This document is an integral part of the following Operating Instructions:

BA01970F/00, BA01971F/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website:
www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z
- On the CD for devices with CD-based documentation

Manufacturer's certificates**UK Declaration of Conformity**

Declaration Number:

UK_00076

The UK Declaration of Conformity is available:

In the download area of the Endress+Hauser website:

www.endress.com -> Downloads -> Declaration ->

Type: UKCA Declaration -> Product Code: ...

UKCA type-examination certificate

Certificate number:

CML 21UKEX2467X

List of applied standards: See UK Declaration of Conformity.

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres - Explosion prevention and protection - Part 1: Basic concepts and methodology"

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FTL325P	–	*****	+	A*B*C*D*E*F*G*..
<i>(Device type)</i>		<i>(Basic specifications)</i>		<i>(Optional specifications)</i>

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Nivotester



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FTL325P

Basic specifications

Position 1 (Approval)		
Selected option		Description
FTL325P	B	UK Ex II (1) G Ex ia Ga IIC, WHG UK Ex II (1) D Ex ia Da IIIC
	E	UK Ex II (1) G Ex ia Ga IIC, WHG, SIL UK Ex II (1) D Ex ia Da IIIC

Position 2 (Housing)		
Selected option		Description
FTL325P	1	Rail mounting, 22.5 mm, 1-channel
	3	Rail mounting, 45 mm, 3-channel

Position 3 (Power Supply)		
Selected option		Description
FTL325P	A	85-253 V AC
	E	20-30 V AC / 20-60 V DC

Position 4 (Switch Output)		
Selected option		Description
FTL325P	1	1x SPDT level + 1x SPST alarm
	3	3x SPDT level + 1x SPST alarm

Optional specifications


No options specific to hazardous locations are available.

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging.

Safety instructions:
Installation

One channel version




A0034562

 1

- 1 PFM sensor, Limit level
- 2 PFM sensor
- 3 Level relay
- 4 Fault signal relay
- 5 Power supply

Three channel version



A0034563

2

CH1 Channel 1

CH2 Channel 2

CH3 Channel 3


1 PFM sensor, Limit level

2 PFM sensor

3 Level relay

4 Fault signal relay

5 Power supply



A0027418

3

- A *Min. 6 mm*
 1 *Intrinsically safe contacts*
 2 *Nivotester FTL325P*
 3 *Other type, other product*

- To achieve an ingress protection of at least IP55: Protect the device from dust and humidity, e.g. in control rooms, or located in a suitable protective enclosure.
- The device is an associated apparatus: Only use the device outside explosion hazardous areas.
- If an intrinsically safe circuit is connected to the device passes through dust explosion-hazardous areas of Zones 20 or Zone 21, make sure that the devices connected to this circuit meet the requirements of categories 1 D or 2 D and are certified accordingly.
- There must be a distance (thread measure) of at least 50 mm between intrinsically safe and nonintrinsically safe terminals.
- When combining the device with other types and products on the same top-hat rail: Keep the distances comply to the relevant standards and rules.
- When combining with devices from other manufacturers: Observe ingress protection of the enclosure.

Intrinsic safety

- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- The intrinsically-safe input circuits are galvanically isolated from other circuits up to a peak value of the nominal voltage of 375 V.

Temperature tables

Ambient temperature range	
Individual installation	$-20\text{ °C} \leq T_a \leq +60\text{ °C}$
Series installation	$-20\text{ °C} \leq T_a \leq +50\text{ °C}$

Connection data

Power supply circuit		
Terminal connections: 1, 2	AC voltage	$U = 85 \text{ to } 253\text{ V}_{AC}$, 50/60 Hz $P \leq 2.0\text{ W}$ (one channel version) $P \leq 4.2\text{ W}$ (three channel version)
	DC voltage	$U = 20 \text{ to } 60\text{ V}_{DC}$ $U = 20 \text{ to } 30\text{ V}_{AC}$, 50/60 Hz $P \leq 1.7\text{ W}$ (one channel version) $P \leq 4.0\text{ W}$ (three channel version)

Contact circuit	
Level relay Terminal connections: Channel 1 (CH1): 4, 5, 6 Channel 2 (CH2): 22, 23, 24 ¹⁾ Channel 3 (CH3): 26, 27, 28 ¹⁾	$U \leq 250\text{ V}_{AC}$, $I \leq 2\text{ A}$, $P \leq 500\text{ VA}$ at $\cos \varphi \geq 0.7$ $U \leq 40\text{ V}_{DC}$, $I \leq 2\text{ A}$, $P \leq 80\text{ W}$
Fault signal relay Terminal connections: 15, 16	

1) not available in one channel version

Sensor circuit						
Terminal connections: Channel 1 (CH1): 7, 8 Channel 2 (CH2): 33, 34 ¹⁾ Channel 3 (CH3): 37, 38 ¹⁾	Connection data:		$U_0 \leq 14.6 \text{ V}$ $I_0 \leq 97 \text{ mA}$ $P_0 \leq 633 \text{ mW}$	$R_i \geq 273 \Omega$ $C_i \leq 19 \text{ nF}$ $L_i = 0$	Trapezium-shaped characteristic	
		[Ex ia Ga] IIC		[Ex ia Ga] IIB [Ex ia Da] IIIC		
		L_o	C_o	L_o	C_o	
	Max. external capacitance at max. external inductance	0.5 mH	300 nF	1.0 mH	1.0 μF	
		1.0 mH	200 nF	5.0 mH	500 nF	
	Max. external capacitance or max. external inductance	3.0 mH	640 nF	15 mH	3.9 μF	
If using explosion protection group [Ex ib Gb] IIC/IIB the application is limited to II (2) G		[Ex ib Gb] IIC		[Ex ib Gb] IIB		
		L_o	C_o	L_o	C_o	
	Max. external capacitance or max. external inductance	3.0 mH	640 nF	15 mH	3.9 μF	

1) not available in one channel version



71553734

www.addresses.endress.com
