Thermal mass flowmeter



Insertion flowmeter with long-term stability and a compact, easily accessible transmitter

Application

- Measuring principle is characterized by a high operable flow range and direct mass flow measurement
- Measurement of utility and process gases as well as gas mixtures in circular piping or rectangular ducts

Device properties

- Insertion version for DN 80 to 1500 (3 to 60")
- Bidirectional measurement; high measuring performance
- Patented drift-free sensor with SIL 2
- Compact dual-compartment housing with up to 3 I/Os
- Backlit display with touch control and WLAN access
- Remote display available

Your benefits

- Flexible, convenient programming based on 21 standard gases or freely definable gas mixtures thereof
- High level of process control premium measurement accuracy and repeatability
- Reliable monitoring detection of process disturbances and reverse flow
- Flexible installation suitable for large dimensional range and circular pipes or rectangular ducts
- Full access to process and diagnostic information numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety freely configurable I/O functionality
- Integrated verification Heartbeat Technology



Table of contents

About this document	4 . 4
Function and system design Measuring principle Measuring system Equipment architecture Reliability	. 6 . 7 . 8
Input . Measured variable	11 11 13 13
OutputOutput and input variantsOutput signalSignal on alarmLoadLoadLow flow cut offGalvanic isolationProtocol-specific data	15 17 21 22 23 23 24
Power supply	25 25 25 25 25 25 25 26 26 26 31 31 31 31 33
Performance characteristics . Reference operating conditions . Maximum measured error . Repeatability . Response time . Influence of ambient temperature . Influence of medium temperature . Influence of medium pressure .	34 34 35 35 35 35 35
Mounting Orientation Installation instructions Pipes Insertion depth Installation conditions for nipples Aligning to the flow direction	36 36 36 36 36 38 38

Inlet and outlet runs	. 38
Environment	. 43
Ambient temperature range	. 43
Storage temperature	
Atmosphere	
Degree of protection	
Vibration- and shock-resistance	
Interior cleaning	
Electromagnetic compatibility (EMC)	
Process	
Medium temperature range	
Medium pressure range	
Pressure/temperature ratings	
Flow limit	. 45
Pressure loss	. 46
Thermal insulation	. 46
Heating	. 46
Hot tap, process pressure	. 47
Cold tap, ambient pressure	
Mounting boss	
Mechanical construction	48
Dimensions in SI units	. 48
Dimensions in US units	
Materials	
Weight	
Process connections	
Display and user interface	. 65
Display and user interface	
	. 65
Operation concept	. 65 . 65
Operation concept	. 65 . 65 . 65
Operation concept	. 65 . 65 . 65 . 66
Operation concept	 65 65 65 65 66 68
Operation concept	 . 65 . 65 . 65 . 66 . 68 . 69
Operation concept	. 65 . 65 . 65 . 66 . 68 . 69 . 70
Operation concept	. 65 . 65 . 65 . 66 . 68 . 69 . 70
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark	 65 65 65 66 68 69 70
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking	 65 65 65 66 68 69 70
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark	 65 65 65 66 68 69 70 72 72 72 72 72 72 72 72
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking	 65 65 65 66 68 69 70 72 72 72 72 72 72
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking RCM marking	 . 65 . 65 . 66 . 68 . 69 . 70 . 72
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking RCM marking Ex approval	 65 65 66 68 69 70 72 73
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking RCM marking Ex approval Functional safety HART certification	 65 65 66 68 69 70 72 72 72 72 72 72 72 72 72 73 73
Operation conceptLanguagesLocal operationRemote operationService interfaceSupported operating toolsHistoROM data managementCertificates and approvalsCE markUKCA markingRCM markingEx approvalFunctional safety	 65 65 66 68 69 70 72 72 72 72 72 72 72 72 72 73 73 73
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking RCM marking Ex approval Functional safety HART certification Radio approval	 65 65 66 68 69 70 72 72 72 72 72 72 72 72 73 73 73 73 73
Operation conceptLanguagesLocal operationRemote operationService interfaceSupported operating toolsHistoROM data managementCertificates and approvalsCE markUKCA markingRCM markingEx approvalFunctional safetyHART certificationRadio approvalAdditional certificationExternal standards and guidelines	 65 65 66 68 69 70 72 72 72 72 72 72 72 72 73 73 73 73 73
Operation conceptLanguagesLocal operationRemote operationService interfaceSupported operating toolsHistoROM data managementCertificates and approvalsCE markUKCA markingRCM markingEx approvalFunctional safetyHART certificationRadio approvalAdditional certification	 65 65 66 68 69 70 72 72 72 72 72 72 72 72 73 73 73 73 73
Operation conceptLanguagesLocal operationRemote operationService interfaceSupported operating toolsHistoROM data managementCertificates and approvalsCE markUKCA markingRCM markingEx approvalFunctional safetyHART certificationRadio approvalAdditional certificationExternal standards and guidelinesClassification of process sealing between electrical	 65 65 65 66 68 69 70 72 72 72 72 72 72 72 73 73 73 73 73
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking RCM marking Ex approval Functional safety HART certification Radio approval Additional certification External standards and guidelines Classification of process sealing between electrical systems and (flammable or combustible) process fluids in accordance with ANSI/ISA 12.27.01	 65 65 65 66 68 69 70 72 72 72 72 72 72 72 73 73 73 73 73 74
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management CE mark UKCA marking RCM marking Ex approval Functional safety HART certification Radio approval Additional certification External standards and guidelines Classification of process sealing between electrical systems and (flammable or combustible) process fluids in	 65 65 65 66 68 69 70 72 72 72 72 72 72 72 73 73 73 73 73 74
Operation conceptLanguagesLocal operationRemote operationService interfaceSupported operating toolsHistoROM data managementCertificates and approvalsCE markUKCA markingRCM markingEx approvalFunctional safetyHART certificationRadio approvalAdditional certificationExternal standards and guidelinesClassification of process sealing between electricalsystems and (flammable or combustible) process fluids inaccordance with ANSI/ISA 12.27.01	 65 65 65 66 68 69 70 72 72 72 72 72 72 72 72 73 73 73 73 73 73 74
Operation concept Languages Local operation Remote operation Service interface Supported operating tools HistoROM data management Certificates and approvals CE mark UKCA marking RCM marking Ex approval Functional safety HART certification Radio approval Additional certification External standards and guidelines Classification of process sealing between electrical systems and (flammable or combustible) process fluids in accordance with ANSI/ISA 12.27.01	 65 65 65 66 68 69 70 72 72 72 72 72 72 72 72 73 73 73 73 73 73 74 76

Heartbeat Technology	76 76
Accessories Device-specific accessories Communication-specific accessories Service-specific accessories System components	77 77 78 79 80
Documentation	81
Registered trademarks	82

About this document

Symbols

Electrical symbols

Symbol	Meaning
	Direct current
\sim	Alternating current
8	Direct current and alternating current
<u> </u>	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Potential equalization connection (PE: protective earth) Ground terminals that must be connected to ground prior to establishing any other connections.
	The ground terminals are located on the interior and exterior of the device:Interior ground terminal: potential equalization is connected to the supply network.Exterior ground terminal: device is connected to the plant grounding system.

Communication-specific symbols

Symbol	Meaning
((:-	Wireless Local Area Network (WLAN) Communication via a wireless, local network.
	LED Light emitting diode is off.
-×-	LED Light emitting diode is on.
	LED Light emitting diode is flashing.

Symbols for certain types of information

Symbol	Meaning
	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
×	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection


Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
X	Safe area (non-hazardous area)
≈➡	Flow direction

Function and system design

Measuring principle

The thermal measuring principle is based on the cooling of a heated resistance thermometer (PT100) from which heat is extracted by the passing medium.



The medium passes two PT100 resistance thermometers in the measurement section. One of these is used in the conventional way as a temperature sensor, while the other serves as a heating element. The temperature sensor monitors and records the effective process temperature while the heated resistance thermometer is kept at a constant differential temperature (compared to the measured process temperature) by controlling the electrical current used by the heating element. The greater the mass flow passing over the heated resistance thermometer, the greater the extent to which cooling takes place and therefore the stronger the current required to maintain a constant differential temperature. This means that the heat current measured is an indicator of the mass flow rate of the medium.

Gas Engine

The integrated Gas Engine functionality ensures maximum measuring performance for flow measurement. The Gas Engine developed by Endress+Hauser is a software-based database of typical standard gases and their specific properties. The Gas Engine calculates the properties of gas mixtures based on the percentage shares of up to 8 gas components.

The Gas Engine functionality enables:

- Calibration with air; no need for expensive and complex calibration with real gas
- Precise conversion of air to other gases; no recalibration required
- Exact measurement of single gases and also of gas mixtures
- Dynamic correction of pressure and temperature changes

The device can be configured for 21 freely selectable gases and water vapor.

Gases available for selection:

- Ammonia
- Argon
- Butane
- Chlorine
- Hydrogen chloride
- Ethane
- Ethylene

 Carbon monoxide Krypton

Carbon dioxide

Helium

- Air
- Methane
- Neon

- Ozone¹⁾
- Propane
- Oxygen

- Xenon

1) Can only be selected as an individual gas or as a gas mixture with oxygen.

Mixtures of these gases, e.g. natural gas, can be programmed easily and quickly on the basis of the percentage shares.

For other gases, contact the Endress+Hauser sales organization responsible for your area.

- Hydrogen sulfide Nitrogen
- Hydrogen

Bidirectional measurement and reverse flow detection

Conventional thermal mass flowmeters cannot distinguish between forward and reverse flows. They always record flow in both directions with the same algebraic sign. Endress+Hauser's thermal flowmeter is available in this conventional unidirectional design, or as a bidirectional flowmeter. Both versions feature sensors that are protected in stainless steel. The bidirectional version can distinguish between the two flow directions and measure and totalize the flow in both directions with the same degree of accuracy.

The version to detect reverse flow only measures flow in the positive direction. The reverse flow is detected by the device but is not totalized.

Measuring system


The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.


Transmitter

Proline 300	Device versions and materials: Transmitter housing
	 Aluminum, coated: aluminum, AlSi10Mg, coated Material of window in transmitter housing: Aluminum, coated: glass
	 Configuration: External operation via 4-line, illuminated graphic local display (LCD) with touch control and guided menus ("Make-it-run" wizards) for application-specific commissioning. Via exprise interface or VII AN interface.
	 Via service interface or WLAN interface: Operating tools (e.g. FieldCare, DeviceCare) Web server (access via Web browser, e.g. Microsoft Internet Explorer, Microsoft Edge)

Sensor



Equipment architecture



Possibilities for integrating measuring devices into a system

- 1 Control system (e.g. PLC)
- 2 Connecting cable (0/4 to 20 mA HART etc.)
- 3 Fieldbus
- 4 Coupler
- 5 Non-hazardous area
- 6 Hazardous area: Zone 2; Class I, Division 2
- 7 Hazardous area: Zone 1; Class I, Division 1

Reliability

IT security

Our warranty is valid only if the product is installed and used as described in the Operating Instructions. The product is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the product and associated data transfer, must be implemented by the operators themselves in line with their security standards.

Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. The following list provides an overview of the most important functions:

Function/interface	Factory setting	Recommendation
Write protection via hardware write protection switch $\rightarrow \square 9$	Not enabled	On an individual basis following risk assessment
Access code (also applies to web server login or FieldCare connection) $\rightarrow \bigcirc 9$	Not enabled (0000)	Assign a customized access code during commissioning
WLAN (order option in display module)	Enabled	On an individual basis following risk assessment
WLAN security mode	Enabled (WPA2- PSK)	Do not change
WLAN passphrase (Password) → 🗎 9	Serial number	Assign an individual WLAN passphrase during commissioning
WLAN mode	Access point	On an individual basis following risk assessment
Web server $\rightarrow \textcircled{B} 9$	Enabled	On an individual basis following risk assessment
CDI-RJ45 service interface→ 🗎 9	-	On an individual basis following risk assessment

Protecting access via hardware write protection

Write access to the parameters of the device via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the main electronics module). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

Protecting access via a password

Different passwords are available to protect write access to the device parameters or access to the device via the WLAN interface.

User-specific access code

Protect write access to the device parameters via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare). Access authorization is clearly regulated through the use of a user-specific access code.

WLAN passphrase

The network key protects a connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface which can be ordered as an option.

Infrastructure mode
 When the device is operated in infrastructure mode, the WLAN passphrase corresponds to the
 WLAN passphrase configured on the operator side.

User-specific access code

Write access to the device parameters via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

WLAN passphrase: Operation as WLAN access point

A connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface, which can be ordered as an optional extra, is protected by the network key. The WLAN authentication of the network key complies with the IEEE 802.11 standard.

When the device is delivered, the network key is pre-defined depending on the device. It can be changed via the **WLAN settings** submenu in the **WLAN passphrase** parameter.

Infrastructure mode

A connection between the device and WLAN access point is protected by means of an SSID and passphrase on the system side. Please contact the relevant system administrator for access.

General notes on the use of passwords


- The access code and network key supplied with the device should be changed during commissioning for safety reasons.
- Follow the general rules for generating a secure password when defining and managing the access code and network key.
- The user is responsible for the management and careful handling of the access code and network key.

Access via web server

The device can be operated and configured via a web browser using the integrated web server. The connection is established via the service interface (CDI-RJ45) or the WLAN interface.

The web server is enabled when the device is delivered. The web server can be disabled via the **Web server functionality** parameter if necessary (e.g. after commissioning).

The device and status information can be hidden on the login page. This prevents unauthorized access to the information.



Access via service interface (CDI-RJ45)

The device can be connected to a network via the service interface (CDI-RJ45). Device-specific functions guarantee the secure operation of the device in a network.

The use of relevant industrial standards and guidelines that have been defined by national and international safety committees, such as IEC/ISA62443 or the IEEE, is recommended. This includes organizational security measures such as the assignment of access authorization as well as technical measures such as network segmentation.



Transmitters with an Ex de approval may not be connected via the service interface (CDI-RJ45)! Order code for "Approval", options (Ex de): BB, C2, GB, MB, NB

Input

Measured variable	Measured process variables					
	 Mass flow 					
	 Tempera 	ture				
	Calculated	process variables				
	 Corrected volume flow Volume flow FAD volume flow Flow velocity Calorific value 2nd temperature heat difference Heat flow Energy flow Density 					
	Process va	Process variables available for order				
	 Order code for "Sensor version": Option SB "Bidirectional" measures the flow in both directions (»positive« and »negative« flow) and totalizes the flow in both directions. The device is calibrated in both directions. Option SC "Reverse flow detection" only measures the flow in the positive direction. The reverse flow is detected by the device but is not totalized. The device is only calibrated in the positive forward flow direction. 					
	Order code for "Application package": Option EV "Second gas group" enables the configuration of two different standard gases/gas mixtures in the device and allows the user to switch from one gas group to another using the status input or (if available) via bus communication.					
Measuring range	device is ca required in	The available measuring range depends on the choice of gas and size of the pipe. Each measuring device is calibrated individually with air under reference operating conditions. No recalibration is required in the case of customer-specific gases, as the device's Gas Engine $\rightarrow \textcircled{B}$ 6 functionality converts from air to these gases.				
	The measuring ranges calibrated for air are indicated in the following section. For information on other gases and process conditions, contact your sales organization or use the Applicator selection software.					
	SI units					
	 Order code for "Sensor version; sensor; insertion tube", option SA "Unidirectional; stainless steel; stainless steel" Order code for "Sensor version; sensor; insertion tube", option HA "Unidirectional; Alloy; stainless steel" 					
	DN		alue [kg/h]		lue [Nm3/h]	
	[mm]	(Air, 20 C, . Minimum	1.013 bar a) Maximum	(Air, U C, 1) Minimum	.013 bar a) Maximum	
		Iviiiiiiiuiii	Iviaxilliulli	Iviiiiiiiuiii		

22 689 40 337

DN [mm]	Full scale value [kg/h] (Air, 20°C, 1.013 bar a)		Full scale value [Nm3/h] (Air, 0°C, 1.013 bar a)	
	Minimum	Maximum	Minimum	Maximum
1000	3260	326000	2 5 2 1	252 105
1500	7335	733 501	5672	567236

 Order code for "Sensor version; sensor; insertion tube:", option SB "Bidirectional; stainless steel; stainless steel"

 Order code for "Sensor version; sensor; insertion tube:", option SC "Reverse flow detection; stainless steel; stainless steel"

DN [mm]	Full scale value [kg/h] (Air, 20°C, 1.013 bar a)		Full scale va (Air, 0°C, 1	lue [Nm3/h] .013 bar a)
	Minimum	Maximum	Minimum	Maximum
80	13	1310	10	1012
100	23	2 3 1 0	17	1786
150	47	4750	36	3 673
200	84	8475	65	6553
250	132	13250	102	10246
300	190	19000	146	14692
400	337	33750	260	26099
500	530	53000	409	40986
600	762	76250	589	58966
700	1038	103820	802	80286
1000	2119	211900	1638	163868
1500	4767	476750	3 686	368683

US units

- Order code for "Sensor version; sensor; insertion tube", option SA "Unidirectional; stainless steel; stainless steel"
- Order code for "Sensor version; sensor; insertion tube", option HA "Unidirectional; Alloy; stainless steel"

DN [in]	Full scale v (Air, 68°F,	alue [lb/h] 14.7 psi a)	Full scale va (Air, 59°F,	alue [SCFM] 14.7 psi a)
	Minimum	Maximum	Minimum	Maximum
3	42	4173	9	909
4	74	7419	16	1616
6	167	16693	36	3 6 3 6
8	297	29677	65	6464
10	464	46371	101	10100
12	668	66774	145	14544
16	1 187	118709	259	25856
20	1855	185 482	404	40400
24	2671	267094	582	58176
28	3635	363 545	792	79184
40	7419	741929	1616	161600
60	16693	1669340	3636	363600

- Order code for "Sensor version; sensor; insertion tube:", option SB "Bidirectional; stainless steel; stainless steel"
- Order code for "Sensor version; sensor; insertion tube:", option SC "Reverse flow detection; stainless steel; stainless steel"

DN [in]	Full scale v (Air, 68°F,	alue [lb/h] 14.7 psi a)	Full scale va (Air, 59°F,	alue [SCFM] 14.7 psi a)
	Minimum	Maximum	Minimum	Maximum
3	29	2981	6	648
4	52	5257	11	1144
6	108	10810	23	2 3 5 4
8	192	19287	42	4200
10	301	30155	65	6567
12	432	43241	94	9417
16	768	76810	167	16729
20	1206	120620	262	26272
24	1735	173533	377	37 797
28	2362	236279	514	51463
40	4822	482253	1050	105 039
60	10850	1085012	2 363	236326

The flow rates listed are only representative for the calibrated conditions and do not necessarily reflect the measuring capacity of the measuring device under operating conditions and the actual pipe internal diameters present on site. To make sure that the correct device version and sizing is selected to suit the application, contact the sales organization or use the Applicator selection software.

Special applications

High gas flow velocities (>70 m/s)

In the case of high gas flow velocities, it is advisable to read in the process pressure dynamically or to enter the pressure as accurately as possible, as a velocity-dependent correction is performed.

Light gases (hydrogen, helium)

- The reliable measurement of light gases can be difficult due to their very high thermal conductivity. Depending on the application, the flow rates of light gases are often particularly slow and the flow profiles are not sufficiently developed. The flows are frequently in the laminar flow range, while turbulent flow would actually be needed for optimum measurement.
 Despite loss of accuracy and linearity in applications with light gases and low flow rates, the device
 - measures with a good degree of repeatability and is therefore suitable for monitoring flow conditions (e.g. leak detection).
 - The recommended inlet runs must be doubled for light gases. \rightarrow \cong 38

Operable flow range

- 200:1 with factory calibration
 - Up to 1000:1 with application-specific adjustment

Input signal

Output and input variants $\rightarrow \cong 15$

External values

The measuring device provides interfaces which allow values measured externally $\rightarrow \cong 14$ to be transmitted to the measuring device:

- Analog inputs 4-20 mA
- Digital inputs

Pressure values can be transmitted as absolute or gauge pressure. For gauge pressure, the atmospheric pressure must be known or specified by the customer.

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Current input

The measured values are written from the automation system to the measuring device via the current input $\rightarrow \cong 14$.

Digital communication

The measured values can be written by the automation system via: Modbus $\mathsf{RS485}$

Current input 0/4 to 20 mA

Current input	0/4 to 20 mA (active/passive)
Current span	 4 to 20 mA (active) 0/4 to 20 mA (passive)
Resolution	1 μΑ
Voltage drop	Typically: 0.6 to 2 V for 3.6 to 22 mA (passive)
Maximum input voltage	≤ 30 V (passive)
Open-circuit voltage	< 28.8 V (active)
Possible input variables	 Pressure Temperature Mol-% (gas analyzer) External reference flow rate (in-situ adjustment)

Status input

Maximum input values	 DC -3 to 30 V If status input is active (ON): R_i >3 kΩ
Response time	Configurable: 5 to 200 ms
Input signal level	 Low signal: DC -3 to +5 V High signal: DC 12 to 30 V
Assignable functions	 Off Reset the individual totalizers separately Reset all totalizers Flow override Second gas group Zero point adjustment

Output

Output and input variants Depending on the option selected for output/input 1, different options are available for the other outputs and inputs. Only one option can be selected for each output/input 1 to 3. The following tables must be read vertically (\downarrow). Example: If the option BA "4–20 mA HART" was selected for output/input 1, one of the options A, B, D, E, , H, I or J is available for output 2 and one of the options A, B, D, E, , H, I or J is available for output 3.

Output/input 1 and options for output/input 2

Options for output/input $3 \rightarrow \square 16$ -

Order code for "Output; input 1" (020) →						Possi	ble o	ption	S				
Current output 4 to 20 mA HART	BA												
Current output 4 to 20 mA HART Ex i passive	\downarrow	CA											
Current output 4 to 20 mA HART Ex i active		\downarrow	сс										
Modbus RS485								\downarrow	MA				
Order code for "Output; input 2" (021) \rightarrow	\downarrow	\rightarrow	\downarrow	\downarrow	\downarrow								
Not used	A	Α	Α	Α	A	A	Α	Α	A	Α	Α	Α	Α
Current output 4 to 20 mA	В			В		В	В		В	В	В	В	
User-configurable input/output ¹⁾	D			D		D	D		D	D	D	D	
Pulse/frequency/switch output	E			Е		E	Е		E	Ε	Е	Е	
Relay output	н			н		н	н		н	Н	Н	Н	
Current input 0/4 to 20 mA	I			I		I	I		Ι	Ι	Ι	Ι	
Status input	J			J		J	J		J	J	J	J	

1) A specific input or output can be assigned $\rightarrow \cong 20$ to a user-configurable input/output.

Output/input 1 and options for output/input 3

Options for output/input $2 \rightarrow \cong 15$

Order code for "Output; input 1" (020) →						Possi	ble o	ption	S				
Current output 4 to 20 mA HART	BA												
Current output 4 to 20 mA HART Ex i passive	\downarrow	CA											
Current output 4 to 20 mA HART Ex i active		\downarrow	СС										
Modbus RS485								\downarrow	MA				
Order code for "Output; input 3" (022) →	\downarrow	\rightarrow	\downarrow										
Not used	A	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α
Current output 4 to 20 mA	В					В			В	В	В	В	
User-configurable input/output	D					D			D	D	D	D	
Pulse/frequency/switch output	E					Е			E	Е	Е	Е	
Relay output	Н					н			н	н	Н	н	
Current input 0/4 to 20 mA	I					I			I	Ι	Ι	I	
Status input	J					J			J	J	J	J	

Output signal

Current output 4 to 20 mA HART

Order code	"Output; input 1" (20): Option BA: current output 4 to 20 mA HART
Signal mode	Can be set to: • Active • Passive
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	250 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow FAD volume flow FAD volume flow Flow velocity Temperature Energy flow Pressure Density Heat flow Electronics temperature 2nd temperature heat difference For SIL (application package), only mass flow

Current output 4 to 20 mA HART Ex i

Order code	 "Output; input 1" (20) choose from: Option CA: current output 4 to 20 mA HART Ex i passive Option CC: current output 4 to 20 mA HART Ex i active
Signal mode	Depends on the selected order version.
Current range	Can be set to: • 4 to 20 mA NAMUR • 4 to 20 mA US • 4 to 20 mA • 0 to 20 mA (only if the signal mode is active) • Fixed current
Open-circuit voltage	DC 21.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	 250 to 400 Ω (active) 250 to 700 Ω (passive)
Resolution	0.38 μΑ

Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow FAD volume flow Flow velocity Temperature Energy flow Pressure Density Heat flow Electronics temperature 2nd temperature heat difference For SIL (application package), only mass flow

Modbus RS485

Physical interface	RS485 in accordance with EIA/TIA-485 standard
Terminating resistor	Integrated, can be activated via DIP switches

Current output 4 to 20 mA

Order code	"Output; input 2" (21), "Output; input 3" (022): Option B: current output 4 to 20 mA
Signal mode	Can be set to: • Active • Passive
Current span	Can be set to: • 4 to 20 mA NAMUR • 4 to 20 mA US • 4 to 20 mA • 0 to 20 mA (only if the signal mode is active) • Fixed current
Maximum output values	22.5 mA
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow FAD volume flow Flow velocity Temperature Energy flow Pressure Density Heat flow Electronics temperature 2nd temperature heat difference For SIL (application package), only mass flow

Pulse/frequency/switch output

Function	Can be configured as pulse, frequency or switch output
Version	Open collector Can be set to: • Active • Passive • Passive NAMUR
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V
Pulse output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Pulse width	Configurable: 0.05 to 2 000 ms
Maximum pulse rate	10000 Impulse/s
Pulse value	Configurable
Assignable measured variables	 Mass flow Volume flow Corrected volume flow FAD volume flow Energy flow Heat flow
	For SIL (application package), only mass flow
Frequency output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Output frequency	Configurable: end value frequency 2 to 10000 Hz(f _{max} = 12 500 Hz)
Damping	Configurable: 0 to 999.9 s
Pulse/pause ratio	1:1
Assignable measured variables	 Mass flow Volume flow Corrected volume flow FAD volume flow Flow velocity Temperature Energy flow Pressure Density Heat flow Electronic temperature 2nd temperature heat difference
	For SIL (application package), only mass flow
Switch output	
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Switching behavior	Binary, conductive or non-conductive
Switching delay	Configurable: 0 to 100 s

Number of switching cycles	Unlimited
Assignable functions	 Off On Diagnostic behavior Limit value Off Mass flow Volume flow Corrected volume flow FAD volume flow Heat flow Heat flow Energy flow Flow velocity Density Calorific value Temperature 2nd temperature heat difference Totalizer 1-3 Electronic temperature Flow direction monitoring Status Low flow cut off

Relay output

Function	Switch output
Version	Relay output, galvanically isolated
Switching behavior	Can be set to: • NO (normally open), factory setting • NC (normally closed)
Maximum switching capacity (passive)	 DC 30 V, 0.1 A AC 30 V, 0.5 A
Assignable functions	 Off On Diagnostic behavior Limit value Off Mass flow Volume flow Corrected volume flow FAD volume flow Heat flow Energy flow Flow velocity Density Temperature 2nd temperature heat difference Totalizer 1-3 Electronics temperature Flow direction monitoring Status Low flow cut off

User-configurable input/output

One specific input or output is assigned to a user-configurable input/output (configurable I/O) during device commissioning.

- The following inputs and outputs are available for assignment: Choice of current output: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Pulse/frequency/switch output
- Choice of current input: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Status input

The technical values correspond to those of the inputs and outputs described in this section.

Depending on the interface, failure information is displayed as follows:

Signal on alarm

HART current output

Device diagnostics	Device condition can be read out via HART Command 48

Modbus RS485

Failure mode	Choose from:
	NaN value instead of current valueLast valid value

Current output 0/4 to 20 mA

4 to 20 mA

Failure mode	 Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Definable value between: 3.59 to 22.5 mA Actual value
	Last valid value

0 to 20 mA

Failure mode	Choose from:
	Maximum alarm: 22 mADefinable value between: 0 to 20.5 mA

Pulse/frequency/switch output

Pulse output	
Fault mode	Choose from: • Actual value • No pulses
Frequency output	
Fault mode	Choose from: • Actual value • 0 Hz • Definable value between: 2 to 12 500 Hz
Switch output	
Fault mode	Choose from: • Current status • Open • Closed

Relay output

Failure mode	Choose from:
	 Current status
	 Open
	Closed
	- closed

Local display

Plain text display	With information on cause and remedial measures
Backlight	Red lighting indicates a device error.

Status signal as per NAMUR recommendation NE 107 H

Interface/protocol

- Via digital communication:HART protocol

 - Modbus RS485
- Via service interface
 - CDI-RJ45 service interface
 - WLAN interface

Plain text display	With information on cause and remedial measures
--------------------	---

Additional information on remote operation \rightarrow 🗎 66 H

Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes
	 The following information is displayed depending on the device version: Supply voltage active Data transmission active Device alarm/error has occurred

Output signal $\rightarrow \square 17$

Ex connection data

Load

Safety-related values

Order code "Output; input 1"	Output type	Safety-related values "Output; input 1"	
		26 (+)	27 (-)
Option BA	Current output 4 to 20 mA HART	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option MA	Modbus RS485	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	

Order code	Output type	Safety-related values					
"Output; input 2"; "Output; input 3"		Output;	Output; input 2		Output; input 2		input 3
• • •		24 (+)	25 (-)	22 (+)	23 (-)		
Option B	Current output 4 to 20 mA	$U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$	2				
Option D	User-configurable input/ output	$U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$	2				
Option E	Pulse/frequency/switch output	$U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$:				

Order code	Output type	Safety-related values			
"Output; input 2"; "Output; input 3"		Output;	input 2	Output;	input 3
		24 (+)	25 (-)	22 (+)	23 (-)
Option H	Relay output	$ \begin{array}{l} U_{N} = 30 \ V_{DC} \\ I_{N} = 100 \ mA_{DC} / 500 \ mA_{AC} \\ U_{M} = 250 \ V_{AC} \end{array} $			
Option I	Current input 4 to 20 mA	$U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$			
Option J	Status input	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$			

Intrinsically safe values

Order code "Output; input 1"	Output type	Intrinsically safe values "Output; input 1"		
		26 (+)	27 (-)	
Option CA	Current output 4 to 20 mA HART Ex i passive	$\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 100 \ mA \\ P_{i} = 1.25 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$		
Option CC	Current output 4 to 20 mA HART Ex i active	Ex ia $U_0 = 21.8 V$ $l_0 = 90 mA$ $P_0 = 491 mW$ $L_0 = 4.1 mH(IIC) / 15 mH(IIB)$ $C_0 = 160 nF(IIC) / 1160 nF(IIB)$ $U_i = 30 V$	39 mH(IIB)	
		$ l_i = 10 \text{ mA} $ $ P_i = 0.3 \text{ W} $ $ L_i = 5 \mu H $ $ C_i = 6 \text{ nF} $		

1) Only available for transmitter Zone 2; Class I, Division 2.

Order code for	Output type	Intrinsically safe values or NIFW values			
"Output; input 2"; "Output; input 3"		Output;	input 2	Output;	input 3
• • •		24 (+)	25 (-)	22 (+)	23 (-)
Option C	Current output 4 to 20 mA Ex i passive	$\begin{array}{l} U_i = 30 \ V \\ l_i = 100 \ mA \\ P_i = 1.25 \ W \\ L_i = 0 \\ C_i = 0 \end{array}$			
Option G	Pulse/frequency/switch output Ex i passive	$\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 100 \ mA \\ P_{i} = 1.25 \ W \\ L_{i} = 0 \\ C_{i} = 0 \end{array}$			

Low flow cut off	The switch points for low flow cut off are user-selectable.
Galvanic isolation	The outputs are galvanically isolated: from the power supply from one another from the potential equalization (PE) terminal

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x1160
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω
System integration	Information on system integration: Operating Instructions .Measured variables via HART protocolBurst Mode functionality

Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1
Response times	 Direct data access: typically 25 to 50 ms Auto-scan buffer (data range): typically 3 to 5 ms
Device type	Slave
Slave address range	1 to 247
Broadcast address range	0
Function codes	 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers
Broadcast messages	Supported by the following function codes: • 06: Write single registers • 16: Write multiple registers • 23: Read/write multiple registers
Supported baud rate	 1 200 BAUD 2 400 BAUD 4 800 BAUD 9 600 BAUD 19 200 BAUD 38 400 BAUD 57 600 BAUD 115 200 BAUD
Data transmission mode	ASCIIRTU
Data access	Each device parameter can be accessed via Modbus RS485.
System integration	Information regarding system integration: Operating Instructions . Modbus RS485 information Function codes Register information Response time Modbus data map

Power supply

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

Supply	voltage	Input/o	utput 1	Input/c	output 2	Input/c	output 3
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \cong 15$.					

Modbus RS485

Supply	voltage	Input/o	output 1	Input/o	output 2	Input/o	output 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \cong 15$.					



Terminal assignment of the remote display and operating module $\rightarrow \square$ 26.

Available device plugs



Device plugs may not be used in hazardous areas!

Device plug for connecting to the service interface:

Order code for "Accessory mounted"

Option **NB**, RJ45 M12 adapter (service interface) $\rightarrow \implies 31$

Order code for "Accessory mounted", option NB "Adapter RJ45 M12 (service interface)"

Order code	Cable entry/coupling $\rightarrow \square 26$	
"Accessory mounted"	Cable entry 2	Cable entry 3
NB	Plug M12 × 1	-

Supply voltage	Order code "Power supply"	Terminal voltage	2	Frequency range
	Option D	DC 24 V	±20%	-
	Option E	AC 100 to 240 V	-15+10%	50/60 Hz, ±4 Hz
	Option I	DC 24 V	±20%	-
		AC 100 to 240 V	-15+10%	50/60 Hz, ±4 Hz

Power consumption

Transmitter

Max. 10 W (active power)

switch-on curre	ent	Max. 36 A (<5 ms) as per NAMUR Recommendation NE 21
-----------------	-----	---

Current consumption Transmitter • Max. 400 mA (24 V) • Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)

Power supply failure Totalizers stop at the last value measured. Depending on the device version, the configuration is retained in the device memory or in the pluggable data memory (HistoROM DAT). Error messages (incl. total operated hours) are stored.


Overcurrent protection
elementThe device must be operated with a dedicated circuit breaker, as it does not have an ON/OFF switch
of its own.

- The circuit breaker must be easy to reach and labeled accordingly.
- Permitted nominal current of the circuit breaker: 2 A up to maximum 10 A.

Electrical connection

Transmitter connection

- [Terminal assignment→ 🗎 25
- Device plugs available → 🖺 25



- 1 Terminal connection for supply voltage
- 2 Terminal connection for signal transmission, input/output
- 3 Terminal connection for signal transmission, input/output or terminal for network connection via service interface (CDI-RJ45); Optional: terminal connection for external WLAN antenna or connection for remote display and operating module DKX001
- 4 Terminal connection for potential equalization (PE)

An adapter for the RJ45 to the M12 plug is optionally available:

Order code for "Accessories", option NB: "Adapter RJ45 M12 (service interface)"


The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can therefore be established via an M12 plug without opening the device.

Network connection via service interface (CDI-RJ45) $\rightarrow \triangleq 68$

Connecting the remote display and operating module DKX001

The remote display and operating module DKX001 is available as an optional extra $\rightarrow \square$ 77.


- The measuring device is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring device. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring device display module. Only one display or operation unit may be connected to the transmitter at any one time.



- *1 Remote display and operating module DKX001*
- 2 Terminal connection for potential equalization (PE)
- 3 Connecting cable
- 4 Measuring device
- 5 Terminal connection for potential equalization (PE)


Connection examples

Current output 4 to 20 mA HART



☑ 2 Connection example for 4 to 20 mA HART current output (active)


- 1 Automation system with current input (e.g. PLC)
- 2 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC
- requirements; observe cable specifications \rightarrow 🖺 31
- 3 Connection for HART operating devices $\rightarrow \square 66$
- 4 Resistor for HART communication ($\geq 250 \Omega$): observe maximum load $\rightarrow \square 17$
- 5 Analog display unit: observe maximum load $\rightarrow \square 17$
- 6 Transmitter



3 Connection example for 4 to 20 mA HART current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications $\rightarrow \cong 31$
- 4 Analog display unit: observe maximum load $\rightarrow \square 17$
- 5 Transmitter


HART input



Connection example for HART input with a common negative (passive)

- 1 Automation system with HART output (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 Analog display unit: observe maximum load $\rightarrow \square 17$
- 5 Pressure measuring device (e.g. Cerabar M, Cerabar S): observe requirements
- 6 Transmitter


Modbus RS485



Connection example for Modbus RS485, non-hazardous area and Zone 2; Class I, Division 2


- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter

Current output 4-20 mA



■ 6 Connection example for 4-20 mA current output (active)


- 1 Automation system with current input (e.g. PLC)
- 2 Analog display unit: observe maximum load $\rightarrow \square 17$
- 3 Transmitter



☑ 7 Connection example for 4-20 mA current output (passive)


- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Analog display unit: observe maximum load $\rightarrow \square 17$
- 4 Transmitter

Pulse/frequency output



- *Connection example for pulse/frequency output (passive)*
- 1 Automation system with pulse/frequency input (e.g. PLC with 10 k Ω pull-up or pull-down resistor)
- Power supply
 Transmitter: c
- 3 Transmitter: observe input values $\rightarrow \square 19$


Switch output



Connection example for switch output (passive)

- 1 Automation system with switch input (e.g. PLC with a 10 k Ω pull-up or pull-down resistor)
- 2 Power supply
- *3* Transmitter: observe input values $\rightarrow \implies 19$


Relay output



10 Connection example for relay output (passive)

- 1 Automation system with relay input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \square 20$

Current input



■ 11 Connection example for 4 to 20 mA current input

- 1 Power supply
- 2 Terminal box
- 3 External measuring device (to read in pressure or temperature, for instance)
- 4 Transmitter

Status input

	 I2 Connection example for status inplant Automation system with status output Power supply 			
	2 Power supply3 Transmitter			
Potential equalization	 Requirements For potential equalization: Pay attention to in-house grounding concepts Take account of operating conditions like the pipe material and grounding Connect the medium, sensor and transmitter to the same electrical potential Use a ground cable with a minimum cross-section of 6 mm² (0.0093 in²) and a cable lug for potential equalization connections 			
Terminals	Spring-loaded terminals: Suitable for strands and strands with ferrules. Conductor cross-section 0.2 to 2.5 mm ² (24 to 12 AWG).			
Cable entries	 Cable gland: M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in) Thread for cable entry: NPT ¹/₂" G ¹/₂" M20 			
Pin assignment, device plug	Service interface Order code for "Accessories mounted"	, option NB: Adapter RJ45 M12 (service interface)		
	2. Pin	Assignment		
	1 +	Тх		
		Rx		
		Тх		
	4 -	Rx		
	4 Coding	Plug/socket		
	D	Socket		
	 Recommended plug: Binder, series 763, part no. 99 3 Phoenix, part no. 1543223 SACC 			
Cable specification	 Permitted temperature range The installation guidelines that apply in the country of installation must be observed. The cables must be suitable for the minimum and maximum temperatures to be expected. 			

Protective grounding cable for the outer ground terminal

Conductor cross-section < 2.1 mm^2 (14 AWG)

The use of a cable lug enables the connection of larger cross-sections.

The grounding impedance must be less than 2 Ω .

Signal cable

Current output 4 to 20 mA HART

A shielded cable is recommended. Observe grounding concept of the plant.

Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A	
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz	
Cable capacitance	< 30 pF/m	
Wire cross-section	> 0.34 mm ² (22 AWG)	
Cable type	Twisted pairs	
Loop resistance	\leq 110 Ω/km	
Signal damping	Max. 9 dB over the entire length of the cable cross-section	
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.	

Current output 0/4 to 20 mA

Standard installation cable is sufficient

Pulse /frequency /switch output Standard installation cable is sufficient

Relay output

Standard installation cable is sufficient.

Current input 0/4 to 20 mA Standard installation cable is sufficient

Status input

Standard installation cable is sufficient

Connecting cable for transmitter - remote display and operating module DKX001

Standard cable

A standard cable can be used as the connecting cable.

Standard cable	4 cores (2 pairs); pair-stranded with common shield	
Shielding	Tin-plated copper-braid, optical cover \geq 85 %	
Capacitance: core/shield	Maximum 1000 nF for Zone 1; Class I, Division 1	
L/R	Maximum 24 $\mu H/\Omega$ for Zone 1; Class I, Division 1	
Cable length	Maximum 300 m (1000 ft), see the following table	

Cross-section	Cable length for use in: Non-hazardous area Hazardous area: Zone 2; Class I, Division 2 Hazardous area: Zone 1; Class I, Division 1	
0.34 mm ² (22 AWG)	80 m (270 ft)	
0.50 mm ² (20 AWG)	120 m (400 ft)	
0.75 mm ² (18 AWG)	180 m (600 ft)	
1.00 mm ² (17 AWG)	240 m (800 ft)	
1.50 mm ² (15 AWG)	300 m (1000 ft)	

Optionally available connecting cable

Standard cable	$2\times2\times0.34~mm^2$ (22 AWG) PVC cable $^{1)}$ with common shield (2 pairs, pair-stranded)	
Flame resistance	According to DIN EN 60332-1-2	
Oil-resistance According to DIN EN 60811-2-1		
Shielding Tin-plated copper-braid, optical cover ≥ 85 %		
Capacitance: core/shield	≤200 pF/m	
L/R $\leq 24 \ \mu H/\Omega$		
Available cable length	10 m (35 ft)	
Operating temperature	When mounted in a fixed position: –50 to +105 $^\circ$ C (–58 to +221 $^\circ$ F); when cable can move freely: –25 to +105 $^\circ$ C (–13 to +221 $^\circ$ F)	

1) UV radiation can impair the cable outer sheath. Protect the cable from direct sunshine where possible.

Overvoltage protection

Mains voltage fluctuations	→ 🗎 25	
Overvoltage category	Overvoltage category II	
Short-term, temporary overvoltage	Up to 1200 V between cable and ground, for max. 5 s	
Long-term, temporary overvoltage	Up to 500 V between cable and ground	


Performance characteristics

Reference operating conditions

- Error limits based on ISO 11631
- Dry air with +20 to +30 °C (+68 to +86 °F) at 0.8 to 1.5 bar (12 to 22 psi)
- Specifications as per calibration protocol
- Accuracy based on accredited calibration rigs that are traced to ISO 17025.

To obtain measured errors, use the Applicator sizing tool $\rightarrow \square 79$

Maximum measured error



Calibrated measuring range

The measuring accuracy is specified in relation to the mass flow and divided into two ranges:

- ±1.0 % of the current measured value for 100% to 10% of the calibrated measuring range (under reference operating conditions)
- ±0.10 % of the calibrated full scale value for 10% to 1% of the calibrated measuring range (under reference operating conditions)

The measuring device is calibrated and adjusted on an accredited and traceable calibration rig and its accuracy is certified in a calibration report $^{1)}$ (5 control points).

Order code for "Calibration flow":

- Option G "Factory calibration": calibration report (5 control points)
- Option K "Traceable ISO/IEC17025": Swiss Calibration Services (SCS) calibration report (5 control points) which confirms traceability to the national calibration standard

For information on calibrated measuring ranges and maximum full scale values \rightarrow 🗎 11

Extended measuring range

The device has an extended measuring range that goes beyond the maximum calibrated value (100%). Here, the last measured values in the calibrated range are taken and then extrapolated. The end of the extrapolated range is only reached once the productive energy of the sensor is exceeded and/or the Mach number is greater than listed below.

Mach number	Order code
0.2	 Order code for "Sensor version; sensor; insertion tube:", option SB "Bidirectional; stainless steel; stainless steel" Order code for "Sensor version; sensor; insertion tube:", option SC "Reverse flow detection; stainless steel; stainless steel"
0.4	 Order code for "Sensor version; sensor; insertion tube:", option SA "Unidirectional; stainless steel; stainless steel" Order code for "Sensor version; sensor; insertion tube:", option HA "Unidirectional; Alloy; stainless steel"

The accuracy is specified in relation to the mass flow.

 $\pm 1.0\% \pm (current measured value in \% -100\%) \times 0.07$ for 100% to 200% of the calibrated measuring range (under reference operating conditions)

¹⁾ Two calibration reports for the order code for "Sensor version; sensor; insertion tube,", option SB "Bidirectional; stainless steel; stainless steel"

Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

	Accuracy	±5 μA	
	Pulse/frequency output		
	o.r. = of reading		
	Accuracy	Max. ±50 ppm o.r. (over the entire ambient temperature range)	
Repeatability	± 0.25 % of the display value for velocities above 1.0 m/s (3.3 ft/s)		
Response time	Typically < 3 s for 63 % of a step change (in both directions)		
Influence of ambient Current output temperature			
	Temperature coefficient	Max. 1 µA/°C	
	Pulse/frequency output		
	Temperature coefficient	No additional effect. Included in accuracy.	
Influence of medium temperature	Air: 0.02 % per °C (0.036 % per °F) of the process temperature change in relation to the reference temperature		
Influence of medium pressure	Air: 0.3 % per bar (0.02 % per psi) of the process pressure change (from the set process pressure)		

Mounting

As a prerequisite for correct flow measurement, thermal measuring devices require a fully developed flow profile. For this reason, please pay attention to the following points and document sections when installing the device:

- Avoid flow disturbances, as the thermal measuring principle reacts sensitively to them.
- Give priority to dry gases.
- Take measures to avoid or remove condensation (e.g. condensation trap, thermal insulation etc.).

Orientation

The direction of flow must match the direction of the arrow on the sensor. In the case of the bidirectional sensor, the arrow points in the positive direction. When performing bidirectional measurement, the sensing element must be installed with an accuracy of 3°.


	Orien	Orientation		
	Vertical orientation		✓ ¹⁾	
	Horizontal orientation, transmitter head up	2 A0015589	V V	
	Horizontal orientation, transmitter head down	A0015590	2 ²⁾	
	Horizontal orientation, transmitter head at side	A0015592		
	Inclined orientation, transmitter head down	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	√ ²⁾	
Installation instructions	 In the case of saturated or impure gases, vertical orientation is preferred in order to minimize condensation or contamination. For bidirectional sensors, select horizontal orientation. Select inclined orientation (α = approx. 135°) for very wet or water-saturated gas (e.g. digester gas, undried compressed air), or if deposits or condensate are constantly present. For mechanical reasons and to protect the pipe, support is recommended for heavy sensors (e.g. 			
	when installing a hot tap).		,	
Pipes	 The measuring device must be professionally installed, and the following points must be observed: Weld pipes professionally. Use seals of the correct size. Align flanges and seals correctly. Remove protection cap from sensing element. 			
	 Following installation, the pipe must be free from dirt and particles in order to avoid damage to the sensors. For further information → ISO standard 14511. 			
Insertion depth	The minimum length of the insertion version can be determined using the Endress+Hauser Applicator program or with the calculation formula below. The calculated necessary insertion depth must be within the adjusting range of the selected insertion version.			

NOTICE

Metal ferrules undergo plastic deformation during the initial installation.

As a result the insertion depth is fixed after initial installation and the ferrules can no longer be replaced.

- > Pay attention to information on preconditions and on determining the insertion depth.
- Check the insertion depth closely before tightening the ferrules.



- 13 Determine the dimensions A, B, C1 and C2
- A In the case of a circular pipe: the pipe internal diameter (DN); in the case of a duct: the inner dimension
- B Thickness of pipe wall or of duct wall
- C1 Mounting kit
- C2 Sensor's compression fitting

Calculating the insertion depth

Insertion depth = $(0.3 \cdot A) + B + (C1 + C2)$

The insertion depth must be at least 100mm.

Determining dimensions C1 and C2

If only Endress+Hauser mounting bosses are used

Mounting boss 1" NPT	C1 + C2 = 112 mm (4.409 in)
Mounting boss G1"	C1 + C2 = 106 mm (4.173 in)
Mounting boss ³ / ₄ " NPT	C1 + C2 = 108 mm (4.252 in)
Mounting boss G¾"	C1 + C2 = 105 mm (4.134 in)



If a cold/hot tap is used, use dimension "L" \rightarrow 🖺 51 instead of "C1".



Use Applicator to determine dimensions C1 and C2 if using other E+H mounting kits (e.g. cold/hot taps).

If not exclusively using Endress+Hauser mounting bosses

C1	Length of pipe connection used
C2 (compression fitting with 1" NPT thread)52 mm (2.047 in)	
C2 (compression fitting with G1" thread)	46 mm (1.811 in)
C2 (compression fitting with ¾" NPT thread)	48 mm (1.889 in)
C2 (compression fitting with G¾" thread)	45 mm (1.772 in)


Selecting the length of the insertion version

Select the length of the insertion version using the calculated insertion depth and the following table. The insertion depth must be within the adjusting range of the insertion version.

Length of insertion tube		Adjusting range (insertion depth)		
[mm]	[in]	[mm]	[in]	
235	9	100 to 235	3.9 to 9.3	
335	13	100 to 335	3.9 to 13.2	
435	17	100 to 435	3.9 to 17.1	
608	24	100 to 608	3.9 to 23.9	

Installation conditions for nipples


Suitable support brackets must be used if installing in rectangular air ducts (or pipes with thin walls).



$D = \emptyset 31.0 \pm 0.5 \text{ mm} (1.22 \pm 0.019 \text{ in})$

Aligning to the flow direction The following criteria must be met for optimum flow measurement:

- The sensor is aligned at a 90° angle to the flow direction.
- The arrow engraved on the sensor shaft matches the positive flow direction.
- The scale on the sensor shaft is aligned with the pipe axis.








Inlet and outlet runs

A fully developed flow profile is a requirement for optimal thermal flow measurement. To achieve the best possible measuring performance, observe the following inlet and outlet runs at the very minimum.

- In the case of bidirectional sensors, also observe the recommended inlet run in the opposite direction.
- If several flow disturbances are present, use flow conditioners.
- Use flow conditioners if it is not possible to observe the required inlet runs.
 - In the case of control valves, the amount of disturbance depends on the valve type and opening degree. The recommended inlet run for control valves is 50 × DN.
 - In the case of very light gases (helium, hydrogen), the recommended inlet run must be doubled.







- A Additional measured error (%)
- B Inlet run (DN)
- 1 2 × 90 ° elbow, 3-dimensional
- 2 Expansion
- 3 2 × 90° elbow
- 4 Reduction or 90° elbow


Flow conditioner

Use flow conditioners if it is not possible to observe the required inlet runs. Flow conditioners improve the flow profile and therefore reduce the necessary inlet runs.


Mount the flow conditioner in flow direction in front of the measuring device.

Available in the following flange standards:


- ASME B16.5 Cl. 150/Cl. 300
- EN 1092-1 PN10/PN16/PN25/PN40
- JIS B2220 10K/20K
- Available in the following line sizes:
- DN 80 (3")
- DN 100 (4")
- DN 150 (6")
- DN 200 (8")
- DN 250 (10")
- DN 300 (12")




- 1 Flow conditioner
- 2 Seal



- 🖻 22 Recommended inlet and outlet runs when using a flow conditioner
- 1 Flow conditioner





- 23 The additional measured error to be expected with flow conditioners depending on the disturbance type and inlet run
- A Additional measured error (%)
- *B* Inlet runs upstream of the flow conditioner (DN)
- 1 2 × 90 ° elbow, 3-dimensional
- 2 Expansion
- 3 $2 \times 90^{\circ}$ elbow
- 4 Reduction or 90° elbow

The pressure loss for flow conditioners is calculated as follows: $\Delta~p~[mbar]$ = 0.0085 $\cdot~\rho~[kg/m^3] \cdot v^2~[m/s]$

Example of air

p = 10 bar abs.

 $t=25~^\circ\!C \rightarrow \rho=11.71~kg/m^3$


v = 10 m/s

 Δ p = 0.0085 \cdot 11.71 \cdot 10 2 = 9.95 mbar

 ρ : density of the process medium v: average flow velocity abs. = absolute

Outlet runs with pressure measuring points

Install the pressure measuring point downstream of the measuring system. This prevents the pressure transmitter from potentially affecting the flow in the measuring point.



☑ 24 Installation of a pressure measuring point (P = pressure transmitter)

Environment

Ambient temperature range	80 °C (176 °F). ► Ensure that sufficien	 -40 to +60 °C (-40 to +140 °F) Order code for "Test, certificate", option JP: -50 to +60 °C (-58 to +140 °F) -20 to +60 °C (-4 to +140 °F) The readability of the display may be impaired at temperatures outside the temperature range. 				
	 display NOTICE Danger of overheating ► Ensure that the temp 80 °C (176 °F). ► Ensure that sufficient 	The readability of the display may be impaired at temperatures outside the temperature range.				
	 Danger of overheating Ensure that the temp 80 °C (176 °F). Ensure that sufficient 					
	 Danger of overheating ► Ensure that the temperature at the lower end of the transmitter housing does not exceed 					
	You can order a weather protection cover from Endress+Hauser→ 🗎 77.					
Storage temperature	−50 to +80 °C (−58 to +176 °F), preferably at +20 °C (+68 °F)					
Atmosphere	If a plastic transmitter housing is permanently exposed to certain steam and air mixtures, this can damage the housing.					
	In cases of doubt, please contact the Sales Center.					
Degree of protection	Transmitter					
	 IP66/67, Type 4X enclosure, suitable for pollution degree 4 When the housing is open: IP20, Type 1 enclosure, suitable for pollution degree 2 Display module: IP20, Type 1 enclosure, suitable for pollution degree 2 					
	Optional					
	Order code for "Sensor options", option CC "IP68, Type 6P, Cust-potted"					
	External WLAN antenna					
	IP67					
Vibration- and shock-	Vibration sinusoidal, in accordance with IEC 60068-2-6					
resistance	 2 to 8.4 Hz, 3.5 mm peak 8.4 to 2 000 Hz, 1 g peak 					
	Vibration broad-band r	andom, according to IEC 60068-2-64				
	 10 to 200 Hz, 0.003 g²/Hz 200 to 2 000 Hz, 0.001 g²/Hz Total: 1.54 g rms 					
	Shock half-sine, according to IEC 60068-2-27					
	6 ms 30 g					
	Rough handling shocks according to IEC 60068-2-31					
Interior cleaning	Suitable for cleaning-in-	place (CIP) and sterilization-in-place (SIP).				

	 Manufacturer options for delivery of parts Oil- and grease-free wetted parts, no declaration. Order code for "Service", option HA. Oil- and grease-free wetted parts as per IEC/TR 60877-2.0 and BOC 50000810-4, with declaration. Order code for "Service", option HB. The plant operator must ensure that the measuring device meets the requirements of the operator's oxygen application.
Electromagnetic compatibility (EMC)	As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) Details are provided in the Declaration of Conformity.
	This unit is not intended for use in residential environments and cannot guarantee adequate protection of the radio reception in such environments.


Process

Medium temperature range	Sensor -40 to +180 °C (-40 to +356 °F) Seals • Sealing rings: • EPDM -40 to +140 °C (-40 to +284 °F) • FKM -40 to +180 °C (-40 to +356 °F) • Ferrule: • PEEK -40 to +140 °C (-40 to +284 °F) • PVDF -20 to +110 °C (-4 to +230 °F) = 1 (400 to (40 to +120 °C (*0 to +256 °F))
	 1.4404 – 40 to +180 °C (–40 to +356 °F) Ferrule in 1.4404: ferrule has a fixed position on the shaft. Restriction for repeat calibrations
Medium pressure range	 Lagrandian (observe minimum insertion depth → 🗎 36) Minimum 0.5 bar absolute. Maximum permitted medium pressure → 🖺 45


Pressure/temperature ratings

The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.

Ferrule



■ 25 With compression fitting material 1.4404/F316L/F316



☑ 26 With compression fitting material 1.4404/F316L/F316

Flow limit

Measuring range $\rightarrow \square 11$

	Mach number	Order code				
	0.2	 Order code for "Sensor version; sensor; insertion tube:", option SB "Bidirectional; stainless steel; stainless steel" Order code for "Sensor version; sensor; insertion tube:", option SC "Reverse flow detection; stainless steel; stainless steel" 				
	0.4	 Order code for "Sensor version; sensor; insertion tube:", option SA "Unidirectional; stainless steel; stainless steel" Order code for "Sensor version; sensor; insertion tube:", option HA "Unidirectional; Alloy; stainless steel" 				
	1 Use the	e Applicator to size the device.				
Pressure loss	Use the Applicator for precise calculations.					
Thermal insulation	In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.					
	If the gas is very wet or saturated with water (e.g. digester gas), the pipe and the sensor housing should be insulated, and heated where necessary, to prevent water droplets condensing on the sensing element.					
	 NOTICE Electronics overheating on account of thermal insulation! Recommended orientation: horizontal orientation, transmitter housing pointing downwards. Do not insulate the transmitter housing . Maximum permissible temperature at the lower end of the transmitter housing: 80 °C (176 °F) Thermal insulation with not isolated extended neck: We recommend that you do not insulate the extended neck in order to ensure optimum dissipation of heat. 					

The maximum flow depends on the gas type and the pipe nominal diameter used. The end of the measuring range is reached when the Mach number listed below is reached.

Heating

Some fluids require suitable measures to avoid loss of heat at the sensor.

Heating options

- Electrical heating, e.g. with electric band heaters
- Via pipes carrying hot water or steam


NOTICE

Electronics overheating on account of thermal insulation!


- Recommended orientation: horizontal orientation, transmitter housing pointing downwards.
- Do not insulate the transmitter housing .
- ► Maximum permissible temperature at the lower end of the transmitter housing: 80 °C (176 °F)
- ► Thermal insulation with extended neck free: We recommend that you do not insulate the extended neck in order to ensure optimum dissipation of heat.

	 NOTICE Danger of overheating when heating Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F). Ensure that sufficient convection takes place at the transmitter neck. When using in potentially explosive atmospheres, observe the information in the device-specific Ex documentation. For detailed information on the temperature tables, see the separate document entitled "Safety Instructions" (XA) for the device. Ensure that a sufficiently large area of the transmitter neck remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.
Hot tap, process pressure	Only use the hot tap for mounting and removal at process pressure for non-toxic, innocuous gases.
	 Medium pressure version Max. process pressure: 20 bar (290 psi) Max. extraction pressure: 16 bar (230 psi) Max. extraction temperature: +50 °C (+122 °F) Min. insertion sensor length: 435mm (17")
	Low pressure version Max. process pressure: 20 bar (290 psi) Max. extraction pressure: 4.5 bar (65 psi) Max. extraction temperature: +50 °C (+122 °F) Min. insertion sensor length: 335mm (13")
Cold tap, ambient pressure	Cold tap for mounting and removal at ambient pressure.
	 Max. process pressure: 20 bar (290 psi) Max. extraction pressure: 1 bar (14.5 psi) Max. extraction temperature: +50 °C (+122 °F) Min. insertion sensor length: 335mm (13")
Mounting boss	To mount the device directly on the process pipe.
	Max. process pressure: 40 bar (580 psi)

Mechanical construction



Compact version



Order code for "Housing", option A "Aluminum, coated"

A 1)	B ¹⁾	С	G ²⁾	Н	I ²⁾
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
169	68	101	200	59	141

1) Depending on the cable gland used: values up to + 30 mm

2) For version without local display: values – 30 mm

A 1)	В	С	G ²⁾	Н	I
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
188	85	103	217	58	148

1) Depending on the cable gland used: values up to + 30 mm

2) For version without local display: values - 49 mm


Installed length	D	E	F	L ¹⁾
[mm]	[mm]	[mm]	[mm]	[mm]
235	281	298	22.4	483
335	381	398	22.4	583
435	481	498	22.4	683
608	652	669	22.4	854

Sensor with order code for "Housing", option A "Aluminum, coated"

1) For Ex d or XP versions: values + 4 mm

Accessories

Welding socket




- Α 45 mm
- Order code for "Accessory enclosed", option "Welding socket" В
- С 60 mm

Order code for "Accessory enclosed":

- Option PC "Welding socket G 1""
 Option PD "Welding socket 1" NPT"
- Option PE "Welding socket G 3/4""
- Option PF "Welding socket ¾" NPT"

Cold tap, ambient pressure



E 28 Dimensions: mm (in)

Α Order code for "Accessory enclosed", option "Welding socket"

Order code for "Accessory enclosed":

- Option PR "Cold tap G 1", ambient pressure"
- Option PS "Cold tap 1" NPT, ambient pressure"
- Option PT "Cold tap G 3/4", ambient pressure"
- Option PU "Cold tap ¾" NPT, ambient pressure"


Cold/hot tap, process pressure

Low-pressure version

- Available for order as:
 - Order code for "Accessory enclosed"
 - Option PG "Cold/hot tap G 1", low pressure = 4.5 bar/65 psig"
 - Option PH "Cold/hot tap 1" NPT, low pressure = 4.5 bar/65 psig"
 - Option PK "Cold/hot tap G ¾", low pressure = 4.5 bar/65 psig"
 - Option PL "Cold/hot tap ¾" NPT, low pressure = 4.5 bar/65 psig"
 - The low-pressure version as "Accessory enclosed" comprises: V2 \rightarrow \blacksquare 29, \blacksquare 50
 - Can be ordered separately as "Accessories": DK6003 →
 ⁽¹⁾
 ⁽²⁾
 ⁽²⁾

• Can only be used with the following installed lengths:

- Order code for "Installed length", option L2 "335mm (13")"
- Order code for "Installed length", option L3 "435mm (17")"
- Order code for "Installed length", option L4 "608mm (24")"
- Cannot be used with 1.4404 clamping ring. Maximum temperature is limited (140°C for PEEK and 110°C for PVDF)



■ 29 Versions available for order

- 1 Safety chain for low-pressure version
- 2 Sensor connection
- 3 Ball valve
- 4 Retrofit adapter (for subsequent installation with existing welding socket (DK6MB))
- 5 Welding socket (DK6MB) only G1"/1" NPT
- 6 Process connection welding socket
- 7 Flange adapter
- 8 Process connection flange
- V1 Version with retrofit adapter
- V2 Version with welding socket
- V3 Version with flange

A	B	C	D	E	F	G	H	I	L	R	Y ¹⁾
[mm]	[mm]	[mm]	[mm]								
41.4	~85	88	~30	95	33.4	33.4	54	108 to 125	~268	165	

1) Safety chain (for $p \le 4.5$ bar) only in conjunction with low-pressure version

Weight [kg]		
V1	V2	V3
2.8	2.4	4.9

Medium-pressure version

Available for order as:

- Order code for "Accessory enclosed"
 - Option PI "Cold/hot tap G 1", medium pressure = 16 bar/230 psig"
 - Option PJ "Cold/hot tap 1" NPT, medium pressure = 16 bar/230 psig"
 - Option PM "Cold/hot tap G ¾", medium pressure = 16 bar/230 psig"
 - Option PN "Cold/hot tap 3/4" NPT, medium pressure = 16 bar/230 psig"


• Can only be used with the following installed lengths:

- Order code for "Installed length", option L3 "435mm (17")"
- Order code for "Installed length", option L4 "608mm (24")"
- Cannot be used with 1.4404 clamping ring. Maximum temperature is limited (140°C for PEEK and 110°C for PVDF)

Extractor assembly for medium-pressure version

Order code for "Accessory enclosed":


- Option PI "Cold/hot tap G 1", medium pressure maximum 16 bar/230 psig"
- Option PJ "Cold/hot tap 1" NPT, medium pressure maximum 16 bar/230 psig"
- Option PM "Cold/hot tap G ¾", medium pressure maximum 16 bar/230 psig"
- Option PN "Cold/hot tap 3/4" NPT, medium pressure maximum 16 bar/230 psig"



■ 30 Extractor assembly

L	A	B	C	D	E	Weight
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg]
930	740	40	700	120	180	

Flow conditioner



Used in combination with flanges according to DIN EN 1092-1: PN 10 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004 $D1^{1)}/D2^{2)}$ DN Centering diameter s [mm] [mm] [mm] 145.3 80 D2 10.1 165.3 D2 13.3 100 150 221.0 D2 20.0 200 274.0 D1 26.3 250 330.0 D2 33.0 300 380.0 D2 39.6

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to DIN EN 1092-1: PN 16 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004				
DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]	
80	145.3	D2	10.1	
100	165.3	D2	13.3	
150	221.0	D2	20.0	
200	274.0	D2	26.3	
250	330.0	D2	33.0	
300	380.0	D2	39.6	

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to DIN EN 1092-1: PN 25 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004					
DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]		
80	145.3	D2	10.1		
100	171.3	D1	13.3		
150	227.0	D2	20.0		

Used in combination with flanges according to DIN EN 1092-1: PN 25 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004					
DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]		
200	280.0	D1	26.3		
250	340.0	D1	33.0		
300	404.0	D1	39.6		

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to DIN EN 1092-1: PN 40 1.4404 (316, 316L)

Can be ordered separately as "Accessories": DK6004		Can be orde	ed separately as	"Accessories": DK6004
--	--	-------------	------------------	-----------------------

DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]
80	145.3	D2	10.1
100	171.3	D1	13.3
150	227.0	D2	20.0
200	294.0	D2	26.3
250	355.0	D2	33.0
300	420.0	D1	39.6

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to ASME B16.5: Class 150 1.4404 (316, 316L)

Can be ordered separately as "Accessories": DK6004

DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]			
80	138.4	D1	10.1			
100	176.5	D2	13.3			
150	223.5	D1	20.0			
200	274.0	D2	26.3			
250	340.0	D1	33.0			
300	404.0	D1	39.6			

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to ASME B16.5: Class 300 1.4404 (316, 316L)

Can be ordered separately as "Accessories": DK6004

DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]
80	151.3	D1	10.1
100	182.6	D1	13.3
150	252.0	D1	20.0
200	309.0	D1	26.3

Used in combination with flanges according to ASME B16.5: Class 300 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004				
DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]	
250	363.0	D1	33.0	
300	402.0	D1	39.6	

1) 2) The flow conditioner is fitted at the outer diameter between the bolts.

The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to JIS B2220: 10K 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004				
DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]	
80	136.3	D2	10.1	
100	161.3	D2	13.3	
150	221.0	D2	20.0	
200	271.0	D2	26.3	
250	330.0	D2	33.0	
300	380.0	D2	39.6	


The flow conditioner is fitted at the outer diameter between the bolts. 1)

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to JIS B2220: 20K 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004						
DN [mm]	Centering diameter [mm]	D1 ¹⁾ /D2 ²⁾	s [mm]			
80	142.3	D1	10.1			
100	167.3	D1	13.3			
150	240.0	D1	20.0			
200	284.0	D1	26.3			
250	355.0	D2	33.0			
300	404.0	D1	39.6			


The flow conditioner is fitted at the outer diameter between the bolts. 1)

2) The flow conditioner is fitted at the indentations between the bolts. Weather protection cover



☑ 31 Engineering unit mm (in)


Remote display and operating module DKX001




☑ 32 Engineering unit mm (in)

External WLAN antenna


External WLAN antenna mounted on device





External WLAN antenna mounted with cable


The external WLAN antenna can be mounted separately from the transmitter if the transmission/ reception conditions at the transmitter mounting location are poor.





Dimensions in US units

Compact version



Order code for "Housing", option A "Aluminum, coated"

A ¹⁾	B ¹⁾	С	G ²⁾	Н	I ²⁾
[in]	[in]	[in]	[in]	[in]	[in]
6.65	2.68	3.98	7.87	2.32	5.55

1) Depending on the cable gland used: values up to + 1.18 in

2) For version without local display: values – 1.18 in

Order code for "Housing", option A "Aluminum, coated"; Ex d or XP

A ¹⁾	B ¹⁾	С	G ²⁾	Н	I ²⁾
[in]	[in]	[in]	[in]	[in]	[in]
7.4	3.35	4.06	8.54	2.28	5.83

1) Depending on the cable gland used: values up to + 1.18 in

2) For version without local display: values – 1.93 in


Installed length	D	Е	F	L ¹⁾
[in]	[in]	[in]	[in]	[in]
9	11.06	11.73	0.88	19.02
13	15	15.67	0.88	22.95
17	18.94	19.61	0.88	26.89
24	25.67	26.34	0.88	33.62

Sensor with order code for "Housing", option A "Aluminum, coated"

1) For Ex d or XP versions: values + 0.16 in

Accessories

Welding socket




A 1.77 in

- *B* Order code for "Accessory enclosed", option "Welding socket"
- C 2.36 in

Order code for "Accessory enclosed":

- Option PC "Welding socket G 1""
- Option PD "Welding socket 1" NPT"
- Option PE "Welding socket G 3/4""
- Option PF "Welding socket ¾" NPT"

Cold tap, ambient pressure



- ☑ 35 Dimensions: mm (in)
- A Order code for "Accessory enclosed", option "Welding socket"

Order code for "Accessory enclosed":

- Option PR "Cold tap G 1", ambient pressure"
- Option PS "Cold tap 1" NPT, ambient pressure"
- Option PT "Cold tap G 3/4", ambient pressure"
- Option PU "Cold tap ¾" NPT, ambient pressure"


Cold/hot tap, process pressure

Low-pressure version

- Available for order as:
 - Order code for "Accessory enclosed"
 - Option PG "Cold/hot tap G 1", low pressure = 4.5 bar/65 psig"
 - Option PH "Cold/hot tap 1" NPT, low pressure = 4.5 bar/65 psig"
 - Option PK "Cold/hot tap G ³/₄", low pressure = 4.5 bar/65 psig"
 - Option PL "Cold/hot tap 3/4" NPT, low pressure = 4.5 bar/65 psig"
 - The low-pressure version as "Accessory enclosed" comprises: V2 \rightarrow 🗷 36, 🗎 58
 - Can be ordered separately as "Accessories": DK6003 →
 ⁽¹⁾
 ⁽²⁾
 ⁽²⁾

• Can only be used with the following installed lengths:

- Order code for "Installed length", option L2 "335mm (13")"
- Order code for "Installed length", option L3 "435mm (17")"
- Order code for "Installed length", option L4 "608mm (24")"
- Cannot be used with 1.4404 clamping ring. Maximum temperature is limited (284°F for PEEK and 230°F for PVDF)



■ 36 Versions available for order

- 1 Safety chain for low-pressure version
- 2 Sensor connection
- 3 Ball valve
- 4 Retrofit adapter (for subsequent installation with existing welding socket (DK6MB))
- 5 Welding socket (DK6MB) only G1"/1" NPT
- 6 Process connection welding socket
- 7 Flange adapter
- 8 Process connection flange
- V1 Version with retrofit adapter
- V2 Version with welding socket
- V3 Version with flange

A	B	C	D	E	F	G	H	I	L	R	Y ¹⁾
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
1.67	~3.35	3.46	~1.18	3.74	1.31	1.31	2.13	4.25 to 4.92	~10.6	6.50	

1) Safety chain (for $p \le 65$ psi g) only in conjunction with low-pressure version

Weight [lbs]				
	V1	V2	V3	
	6	5	11	

Medium-pressure version

Available for order as:

- Order code for "Accessory enclosed"
 - Option PI "Cold/hot tap G 1", medium pressure = 16 bar/230 psig"
 - Option PJ "Cold/hot tap 1" NPT, medium pressure = 16 bar/230 psig"
 - Option PM "Cold/hot tap G ¾", medium pressure = 16 bar/230 psig"
 - Option PN "Cold/hot tap 3/4" NPT, medium pressure = 16 bar/230 psig"

 - Can be ordered separately as "Accessories": DK6003 →
 ¹ 78
 Versions V1, V2 and V3 →
 ¹ 36,
 ¹ 58 can be ordered via DK6003


• Can only be used with the following installed lengths:

- Order code for "Installed length", option L3 "435mm (17")"
- Order code for "Installed length", option L4 "608mm (24")"
- Cannot be used with 1.4404 clamping ring. Maximum temperature is limited (140°C for PEEK and 110°C for PVDF)

Extractor assembly for medium-pressure version

Order code for "Accessory enclosed":


- Option PI "Cold/hot tap G 1", medium pressure maximum 16 bar/230 psig"
- Option PJ "Cold/hot tap 1" NPT, medium pressure maximum 16 bar/230 psig"
- Option PM "Cold/hot tap G ¾", medium pressure maximum 16 bar/230 psig"
- Option PN "Cold/hot tap 3/4" NPT, medium pressure maximum 16 bar/230 psig"



■ 37 Extractor assembly

L	A	B	C	D	E	Weight
[in]	[in]	[in]	[in]	[in]	[in]	[lbs]
36.61	29.13	1.57	27.56	4.72	7.09	18.5

Flow conditioner



Used in combination with flanges according to ASME B16.5: Class 150 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004						
DN [in]	Centering diameter [in]	D1 ¹⁾ /D2 ²⁾	s [in]			
3	5.45	D1	0.40			
4	6.95	D2	0.52			
6	8.81	D1	0.79			
8	10.80	D2	1.04			
10	13.40	D1	1.30			
12	15.90	D1	1.56			

1) The flow conditioner is fitted at the outer diameter between the bolts.


2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges according to ASME B16.5: Class 300 1.4404 (316, 316L) Can be ordered separately as "Accessories": DK6004					
DN [in]	Centering diameter [in]	D1 ¹⁾ /D2 ²⁾	s [in]		
3	5.96	D1	0.40		
4	7.19	D1	0.52		
6	9.92	D1	0.79		
8	12.20	D1	1.04		
10	14.30	D1	1.30		
12	15.80	D1	1.56		

1) The flow conditioner is fitted at the outer diameter between the bolts.


2) The flow conditioner is fitted at the indentations between the bolts.

Weather protection cover






Remote display and operating module DKX001



☑ 39 Engineering unit mm (in)

External WLAN antenna


External WLAN antenna mounted on device





External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/ reception conditions at the transmitter mounting location are poor.



■ 41 Engineering unit mm (in)

Materials


Transmitter housing

Order code for "Housing": Option **A** "Aluminum, coated": aluminum, AlSi10Mg, coated

Window material

Order code for "Housing": Option **A** "Aluminum, coated": glass

Cable entries/cable glands



☑ 42 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland M20 × 1.5
- 3 Adapter for cable entry with female thread $G \frac{1}{2}$ or NPT $\frac{1}{2}$ "

Order code for "Housing", option A "Aluminum, coated"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Compression fitting M20 × 1.5	Non-Ex: plastic
Compression fitting M20 ~ 1.5	Z2, D2, Ex d/de: brass with plastic
Adapter for cable entry with female thread G $\frac{1}{2}$ "	Nickel-plated brass
Adapter for cable entry with female thread NPT $\frac{1}{2}$ "	

Materials for insertion tube

Stainless steel, 1.4404 (316/316L)

Process connections, process coupling

Stainless steel, 1.4404 (316/316L)

Sensing element

Unidirectional

Stainless steel, 1.4404 (316/316L)Alloy C22, 2.4602 (UNS N06022);

Bidirectional Stainless steel, 1.4404 (316/316L)

Reverse flow detection

Stainless steel, 1.4404 (316/316L)

Ferrules

- PEEK
- PVDF
- 1.4404 (316/316L)

Flat ring seal

- EPDM
- FKM

For aggressive media (e.g. chlorine or ozone), we recommend special materials (Alloy for sensing element, PVDF or 1.4404 for ferrules and FKM for flat seal). For any requests, please contact the Endress+Hauser sales organization responsible for your area.

Sensor guard

Stainless steel, 1.4404 (316/316L)

Accessories

Protective cover

Stainless steel, 1.4404 (316L)

External WLAN antenna

- Antenna: ASA plastic (acrylonitrile styrene acrylate) and nickel-plated brass
- Adapter: Stainless steel and nickel-plated brass
- Cable: Polyethylene
- Plug: Nickel-plated brass
- Angle bracket: Stainless steel

Mounting boss (DK6MB)

Stainless steel, 1.4404 (316/316L)

Cold/hot tap, low pressure and medium pressure

Welding socket

Stainless steel 1.4404 (316L)

Ball valve

- Stainless cast steel CF3M or CF8M
- Seal: PTFE

Sensor connection

Stainless steel, 1.4404 (316/316L)

Cold tap, atmospheric pressure

- Stainless steel, 1.4404 (316/316L)
- Stainless cast steel CF3M or CF8M
- Seal: PTFE

Weight

All values (weight exclusive of packaging material) refer to devices with EN/DIN PN 40 flanges. Weight specifications including transmitter as per order code for "Housing", option A "Aluminum, coated".

Different values due to different transmitter versions: Transmitter version for the hazardous area (Order code for "Housing", option A "Aluminum, coated"; Ex d): +2 kg (+4.4 lbs)

Weight in SI units

Installed length [mm]	Weight [kg]
235	4.8
335	4.9
435	5
608	5.1

Weight in US units

Installed length [in]	Weight [lbs]
9	10.6
13	10.8
17	11
24	11.2

Process connections

• G¾", ISO 228/1 compression fitting

• G1", ISO 228/1, compression fitting

• ³/₄" NPT, compression fitting

1" NPT, compression fitting

For information on the different materials used in the process connections $\rightarrow \square 63$

Display and user interface

Operation concept	Operator-oriented menu structure for user-specific tasks Commissioning Operation Diagnostics Expert level 			
	 Fast and safe commissioning Guided menus ("Make-it-run" wizards) for applications Menu guidance with short explanations of the individual parameter functions Access to the device via Web server WLAN access to the device via mobile handheld terminal, tablet or smart phone 			
	 Reliable operation Operation in local language Uniform operating philosophy applied to device and operating tools If replacing electronic modules, transfer the device configuration via the integrated memory (HistoROM backup) which contains the process and measuring device data and the event logbook. No need to reconfigure. 			
	 Efficient diagnostics increase measurement availability Troubleshooting measures can be called up via the device and in the operating tools Diverse simulation options, logbook for events that occur and optional line recorder functions 			
Languages	 Can be operated in the following languages: Via local operation English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Korean, Vietnamese, Czech, Swedish Via Web browser English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Vietnamese, Czech, Swedish Via "FieldCare", "DeviceCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese 			
Local operation	Via display module			
	 Equipment: Order code for "Display; operation", option F "4-line, illuminated, graphic display; touch control" Order code for "Display; operation", option G "4-line, illuminated, graphic display; touch control + WLAN" Information about WLAN interface → 68 			
	A00267			
	Display elements			
	• (Line illuminated graphic display			

- 4-line, illuminated, graphic display White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured


Operating elements

- External operation via touch control (3 optical keys) without opening the housing: 🗄, 🖃, 🗉
- Operating elements also accessible in the various zones of the hazardous area

Via remote display and operating module DKX001

The remote display and operating module DKX001 is available as an optional extra $\rightarrow \square$ 77.

- The measuring device is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring device. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring device display module. Only one display or operation unit may be connected to the transmitter at any one time.



44 Operation via remote display and operating module DKX001

Display and operating elements

The display and operating elements correspond to those of the display module $\rightarrow \bigoplus 65$.

Housing material

-

Transmitter housing	Remote display and operating module	
Order code for "Housing"	Material	Material
Option A "Aluminum, coated"	AlSi10Mg, coated	AlSi10Mg, coated

Cable entry

Corresponds to the choice of transmitter housing, order code for "Electrical connection".

Connecting cable

→ 🗎 32


Dimensions

→ 🖺 55

Remote operation


Via HART protocol

This communication interface is available in device versions with a HART output.



45 Options for remote operation via HART protocol (active)

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 Field Xpert SMT70
- 7 VIATOR Bluetooth modem with connecting cable
- 8 Transmitter




46 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 Field Xpert SMT70
- 9 VIATOR Bluetooth modem with connecting cable
- 10 Transmitter

Via Modbus RS485 protocol

This communication interface is available in device versions with a Modbus RS485 output.



☑ 47 Options for remote operation via Modbus RS485 protocol (active)

- 1 Control system (e.g. PLC)
- 2 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or with operating
- tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP" or Modbus DTM

3 Transmitter


Service interface

Via service interface (CDI-RJ45)

A point-to-point connection can be established to configure the device on site. With the housing open, the connection is established directly via the service interface (CDI-RJ45) of the device.

An adapter for the RJ45 to the M12 plug is optionally available for the non-hazardous area: Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can be established via an M12 plug without opening the device.




☑ 48 Connection via service interface (CDI-RJ45)

- 1 Computer with web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) to access the integrated web server or with an operating tool "FieldCare", "DeviceCare" with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI-RJ45) of the measuring device with access to the integrated web server

Via WLAN interface

The optional WLAN interface is available on the following device version: Order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN"



- 1 Transmitter with integrated WLAN antenna
- 2 Transmitter with external WLAN antenna
- 3 LED lit constantly: WLAN reception is enabled on measuring device
- 4 LED flashing: WLAN connection established between operating unit and measuring device
- 5 Computer with WLAN interface and web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device web server or with operating tool (e.g. FieldCare, DeviceCare)
- 6 Mobile handheld terminal with WLAN interface and web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device web server or operating tool (e.g. FieldCare, DeviceCare)
- 7 Smart phone or tablet (e.g. Field Xpert SMT70)

Function	WLAN: IEEE 802.11 b/g (2.4 GHz) • Access Point with DHCP server (factory setting) • Network	
Encryption	WPA2-PSK AES-128 (in accordance with IEEE 802.11i)	
Configurable WLAN channels	1 to 11	
Degree of protection	IP67	
Available antennas	 Internal antenna External antenna (optional) In the event of poor transmission/reception conditions at the place of installation. Available as an accessory . Only 1 antenna is active at any one time! 	
Range	 Internal antenna: typically 10 m (32 ft) External antenna: typically 50 m (164 ft) 	
Materials (external antenna)	 Antenna: ASA plastic (acrylonitrile styrene acrylate) and nickel-plated brass Adapter: Stainless steel and nickel-plated brass Cable: Polyethylene Plug: Nickel-plated brass Angle bracket: Stainless steel 	

Supported operating tools

Different operating tools can be used for local or remote access to the measuring device. Depending on the operating tool used, access is possible with different operating units and via a variety of interfaces.

Supported operating tools	Operating unit	Interface	Additional information
Web browser	Notebook, PC or tablet with web browser	CDI-RJ45 service interfaceWLAN interface	Special Documentation for device
DeviceCare SFE100	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🗎 79

Supported operating tools	Operating unit	Interface	Additional information
FieldCare SFE500	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🗎 79
Field Xpert	SMT70/77/50	 All Fieldbus protocols WLAN interface Bluetooth CDI-RJ45 service interface 	Operating Instructions BA01202S Device description files: Use update function of handheld terminal
SmartBlue app	Smart phone or tablet with iOs or Android	WLAN	→ 🗎 79

Other operating tools based on FDT technology with a device driver such as DTM/iDTM or DD/EDD can be used for device operation. These operating tools are available from the individual manufacturers. Integration into the following operating tools, among others, is supported:

- FactoryTalk AssetCentre (FTAC) from Rockwell Automation → www.rockwellautomation.com
- Process Device Manager (PDM) from Siemens → www.siemens.com
- Asset Management Solutions (AMS) from Emerson → www.emersonprocess.com
- FieldCommunicator 375/475 from Emerson → www.emersonprocess.com
- Field Device Manager (FDM) from Honeywell → www.process.honeywell.com
- FieldMate from Yokogawa → www.yokogawa.com
- PACTWare → www.pactware.com

The related device description files are available: www.endress.com \rightarrow Download Area

Web server

With the integrated web server, the device can be operated and configured via a web browser service interface (CDI-RJ45) or WLAN interface. The structure of the operating menu is the same as for the local display. In addition to the measured values, status information on the device is displayed and can be used to monitor device health. Furthermore the device data can be managed and the network parameters can be configured.

A device that has a WLAN interface (can be ordered as an option) is required for the WLAN connection: order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN". The device acts as an Access Point and enables communication by computer or a mobile handheld terminal.

Supported functions

Data exchange between the operating unit (such as a notebook, for example,) and measuring device:Upload the configuration from the measuring device (XML format, configuration backup)

- Save the configuration to the measuring device (XML format, restore configuration)
- Export event list (.csv file)
- Export parameter settings (.csv file or PDF file, document the measuring point configuration)
- Export the Heartbeat verification log (PDF file, only available with the **Heartbeat Verification** $\rightarrow \bigoplus$ 76 application package)
- Flash firmware version for device firmware upgrade, for example
- Download driver for system integration

Special Documentation for web server

HistoROM data management

The measuring device features HistoROM data management. HistoROM data management comprises both the storage and import/export of key device and process data, making operation and servicing far more reliable, secure and efficient.

When the device is delivered, the factory settings of the configuration data are stored as a backup in the device memory. This memory can be overwritten with an updated data record, for example after commissioning.

Additional information on the data storage concept

There are different types of data storage units in which device data are stored and used by the device:

	HistoROM backup	T-DAT	S-DAT
Available data	 Event logbook, e.g. diagnostic events Parameter data record backup Device firmware package 	 Measured value logging ("Extended HistoROM" order option) Current parameter data record (used by firmware at run time) Indicator (minimum/maximum values) Totalizer value 	 Sensor data: e.g. nominal diameter Serial number Calibration data Device configuration (e.g. SW options, fixed I/O or multi I/O)
Storage location	Fixed on the user interface PC board in the connection compartment	Can be plugged into the user interface PC board in the connection compartment	In the sensor plug in the transmitter neck part

Data backup

Automatic

- The most important device data (sensor and transmitter) are automatically saved in the DAT modules
- If the transmitter or measuring device is replaced: once the T-DAT containing the previous device data has been exchanged, the new measuring device is ready for operation again immediately without any errors
- If exchanging the electronics module (e.g. I/O electronics module): Once the electronics module has been replaced, the software of the module is compared against the current device firmware. The module software is upgraded or downgraded where necessary. The electronics module is available for use immediately afterwards and no compatibility problems occur.

Manual

Additional parameter data record (complete parameter settings) in the integrated device memory HistoROM backup for:

- Data backup function
- Backup and subsequent restoration of a device configuration in the device memory HistoROM backup
- Data comparison function

Comparison of the current device configuration with the device configuration saved in the device memory HistoROM backup

Data transmission

Manual

Transfer of a device configuration to another device using the export function of the specific operating tool, e.g. with FieldCare, DeviceCare or Web server: to duplicate the configuration or to store in an archive (e.g. for backup purposes)

Event list

Automatic

- Chronological display of up to 20 event messages in the events list
- If the **Extended HistoROM** application package (order option) is enabled: up to 100 event messages are displayed in the events list along with a time stamp, plain text description and remedial measures
- The events list can be exported and displayed via a variety of interfaces and operating tools e.g. DeviceCare, FieldCare or Web server

Data logging

Manual

If the **Extended HistoROM** application package (order option) is enabled:

- Recording of 1 to 4 channels of up to 1000 measured values (up to 250 measured values per channel)
- User configurable recording interval
- Export the measured value log via a variety of interfaces and operating tools e.g. FieldCare, DeviceCare or web server

	Certificates and approvals			
	Current certificates and approvals for the product a product page:	re available at www.endress.com on the relevant		
	1. Select the product using the filters and search	n field.		
	2. Open the product page.			
	3. Select Downloads .			
CE mark	The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.			
	Endress+Hauser confirms successful testing of the	device by affixing to it the CE mark.		
UKCA marking	The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark.			
	Contact address Endress+Hauser UK: Endress+Hauser Ltd. Floats Road Manchester M23 9NF United Kingdom www.uk.endress.com			
RCM marking	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".			
Ex approval	The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.			
	Devices with the order code for "Approval", option BB or BD have equipment protection level (EPL) Ga/Gb (Zone 0 in the measuring tube).			
	The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.			
	ATEX, IECEx			
	Currently, the following versions for use in hazardous areas are available:			
	Ex db eb			
	Category	Type of protection		
	II1/2G	Ex db eb ia IIC T4T1 Ga/Gb		
	II2G	Ex db eb ia IIC T4T1 Gb		
	Ex db			
	Category	Type of protection		
	II1/2G	Ex db ia IIC T4T1 Ga/Gb		
	II2G	Ex db ia IIC T4T1 Gb		

Ех ес

Category	Type of protection
II3G	Ex ec IIC T4T1 Gc

	Category	Type of protection
	II2D	Ex tb IIIC T** °C Db
	CE A	
	cCSA _{US}	
	Currently, the following versions for use in hazardo XP (Ex d) Class I, II, III Division 1 Groups A-G	ous areas are available:
	NI (Ex ec) Class I Division 2 Groups A - D	
	Ex de Class I, Zone 1 AEx/ Ex de ia IIC T4T1 Ga/Gb Class I, Zone 1 AEx/ Ex de ia IIC T4T1 Gb	
	Ex db Class I, Zone 1 AEx/ Ex db ia IIC T4T1 Ga/Gb Class I, Zone 1 AEx/ Ex db ia IIC T4T1 Gb	
	Ex ec Class I, Zone 2 AEx/ Ex ec IIC T4T1 Gc	
	Ex tb Zone 21 AEx/ Ex tb IIIC T** °C Db	
Functional safety	The measuring device can be used for flow monitor (single-channel architecture; order code for "Addition channel architecture with homogeneous redundance accordance with IEC 61508.	onal approval", option LA) and SIL 3 (multi-
	The following types of monitoring in safety equipm Mass flow	nent are possible:
	Functional safety manual with information ar	nd restrictions for the SIL device $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $
ART certification	HART interface	
	The measuring device is certified and registered by meets all the requirements of the following specific Certified according to HART 7	cations:
	 The device can also be operated with certified de 	vices of other manufacturers (interoperability)
adio approval	The measuring device has radio approval.	
	For detailed information on the radio approva	l, see the Special Documentation $ ightarrow extsf{B1}$ 81
dditional certification	CRN approval	
	Some device versions have CRN approval. A CRN-ap must be ordered for a CRN-approved device.	pproved process connection with a CSA approval
cternal standards and iidelines	 EN 60529 Degrees of protection provided by enclosure (IP c EN 61010-1 	
	Safety requirements for electrical equipment for general requirements IEC/EN 61326-2-3	measurement, control and laboratory use -
	Emission in accordance with Class A requirement requirements). • NAMUR NE 21	ts. Electromagnetic compatibility (EMC
	Electromagnetic compatibility (EMC) of industria NAMUR NE 32	
	Data retention in the event of a power failure in a microprocessors	field and control instruments with

	 NAMUR NE 43 Standardization of the signal level for the breakdown information of digital transmitters with analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronics NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications ETSI EN 300 328 Guidelines for 2.4 GHz radio components. EN 301489 Electromagnetic compatibility and radio spectrum matters (ERM).
Classification of process sealing between electrical systems and (flammable or combustible) process fluids in accordance with ANSI/ISA 12.27.01	Endress+Hauser devices are designed in accordance with ANSI/ISA 12.27.01. allowing the user to waive the use and save the cost of installing external secondary process seals in the conduit as required by the process sealing sections of ANSI/NFPA 70 (NEC) and CSA 22.1 (CEC). These devices comply with the North American installation practice and provide a very safe and cost-saving installation for pressurized applications with hazardous fluids. Further information can be found in the control drawings of the relevant devices.

Ordering information

Detailed ordering information is available as follows:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
 -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
 Open product page -> The "Configure" button to the right of the product image opens the Product
 Configurator.
- From your Endress+Hauser Sales Center:www.addresses.endress.com
- Product Configurator the tool for individual product configuration
 - Up-to-the-minute configuration data
 - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
 - Automatic verification of exclusion criteria
 - Automatic creation of the order code and its breakdown in PDF or Excel output format
 - Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com. Detailed information on the application packages: Special Documentation $\rightarrow \cong 81$ **Diagnostic functionality** Order code for "Application package", option EA "Extended HistoROM" Comprises extended functions concerning the event log and the activation of the measured value memory. Event log: Memory volume is extended from 20 message entries (standard version) to up to 100 entries. Data logging (line recorder): • Memory capacity for up to 1000 measured values is activated. • 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server. For detailed information, see the Operating Instructions for the device. 1 Heartbeat Technology Order code for "Application package", option EB "Heartbeat Verification + Monitoring" **Heartbeat Verification** Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". • Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. • Simple testing process via local operation or other operating interfaces. - Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. Extension of calibration intervals according to operator's risk assessment. Heartbeat Monitoring Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to: • Draw conclusions - using these data and other information - about the impact on the measuring performance over time. Schedule servicing in time.

• Monitor the process or product quality , e.g. process stability.

Special Documentation SD02712D

Second gas group	Package	Description
	Second gas group	This application package enables the configuration of two different standard gases/gas mixtures in the device and allows the user to switch from one gas group to another using the status input or (if available) via bus communication.

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Accessories	Description
Proline 300 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: • Approvals • Output • Input • Display/operation • Housing • Software • Order code: 6X3BXX • Installation Instructions EA01286D
Remote display and operating module DKX001	 If ordered directly with the measuring device: Order code for "Display; operation", option O "Remote display 4-line, illuminated; 10 m (30 ft) cable; touch control" If ordered separately: Measuring device: order code for "Display; operation", option M "W/o, prepare for remote display" DKX001: Via the separate product structure DKX001 If ordered subsequently: DKX001: Via the separate product structure DKX001 If ordered subsequently: DKX001: Via the separate product structure DKX001 If ordered directly: order code for "Accessory enclosed", option RA "Mounting bracket, pipe 1/2" If ordered subsequently: order number: 71340960 Connecting cable (replacement cable) Via the separate product structure: DKX002
	 Further information on display and operating module DKX001→ Special Documentation SD01763D
External WLAN antenna	 External WLAN antenna with 1.5 m (59.1 in) connecting cable and two angle brackets. Order code for "Accessory enclosed", option P8 "Wireless antenna wide area". Inte external WLAN antenna is not suitable for use in hygienic applications. Additional information regarding the WLAN interface → B 68. Order number: 71351317 Installation Instructions EA01238D
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight. Order number: 71343505 Installation Instructions EA01160D

Device-specific accessories For the transmitter

For the sensor

Accessories	Description	
Mounting boss	Order code for "Accessory enclosed" • Option PC "Mounting boss, G1" • Option PD "Mounting boss, 1" NPT" • Option PE "Mounting boss, G34" • Option PF "Mounting boss, 34" NPT" • Option PF "Mounting boss, 34" NPT" • Option PF "Mounting boss, 1" NPT" • Option PF "Mounting boss, 54" • Option PF "Mounting boss, 54" • Option PF "Mounting boss, 54"	
Cold tap (ambient pressure)	 Order code for "Accessory enclosed" Option PR "Cold tap G1", ambient pressure" Option PS "Cold tap 1" NPT, ambient pressure" Option PT "Cold tap G¾", ambient pressure" Option PU "Cold tap ¾" NPT, ambient pressure" Option PU "Cold tap ¾" NPT, ambient pressure" Can be ordered separately: order code DK6ML 	
Hot tap (low pressure)	 Order code for "Accessory enclosed" Option PG "Hot tap G1", low pressure max. 4.5 bar/65 psig" Option PH "Hot tap 1" NPT, low pressure max. 4.5 bar/65 psig" Option PK "Hot tap G¾", low pressure max. 4.5 bar/65 psig" Option PL "Hot tap ¾" NPT, low pressure max. 4.5 bar/65 psig" 	
	Mounting set contains mounting boss (process connection), sensor connection with safety chain and ball valve. To insert or remove the sensor a process pressures up to max. 4.5 barg (65 psi).	
	If the accessory is ordered separately, individual combinations can be selected. Order code DK6003	
Hot tap (medium pressure)	Order code for "Accessory enclosed" • Option PI "Hot tap G1", medium pressure max. 16 bar/230 psig" • Option PJ "Hot tap 1" NPT, medium pressure max. 16 bar/230 psig" • Option PM "Hot tap G¾", medium pressure max. 16 bar/230 psig" • Option PN "Hot tap ¾", medium pressure max. 16 bar/230 psig" • Option PN "Hot tap ¾", medium pressure max. 16 bar/230 psig"	
	Mounting set contains mounting boss (process connection), sensor connection, ball valve and extractor assembly. To insert or remove the sensor at process pressures up to max. 16 barg (230 psi).	
	If the accessory is ordered separately, individual combinations can be selected. Order code DK6003	
Flow conditioner	Can be ordered separately: order code DK6004	
	Available for the following pipe diameters: • DN 80 (3") • DN 100 (4") • DN 150 (6") • DN 200 (8") • DN 250 (10") • DN 300 (12")	
	Available for the following process connections: PN10, EN1092-1 PN16, EN1092-1 PN25, EN1092-1 PN40, EN1092-1 Cl.150, ASME B16.5 Cl.300, ASME B16.5 10K, JIS B2220 20K, JIS B2220 	
	Screws and seals are not included in the delivery.	

Communication-specific accessories	Accessories	Description
	Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB port.

HART Loop Converter	Is used to evaluate and convert dynamic HART process variables to analog current	
НМХ50	signals or limit values.	
	 Technical Information TI00429F Operating Instructions BA00371F 	
Fieldgate FXA42	Transmission of the measured values of connected 4 to 20 mA analog measuring devices, as well as digital measuring devices	
	 Technical Information TI01297S Operating Instructions BA01778S Product page: www.endress.com/fxa42 	
Field Xpert SMT50	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.	
	 Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt50 	
Field Xpert SMT70	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.	
	 Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt70 	
Field Xpert SMT77	The Field Xpert SMT77 tablet PC for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1.	
	 Technical Information TI01418S Operating Instructions BA01923S Product page: www.endress.com/smt77 	

Service-specific accessories	Accessories	Description
	Applicator	 Software for selecting and sizing Endress+Hauser measuring devices: Choice of measuring devices for industrial requirements Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy. Graphic illustration of the calculation results Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.
		 Applicator is available: Via the Internet: https://portal.endress.com/webapp/applicator As a downloadable DVD for local PC installation.
	W@M	W@M Life Cycle Management Improved productivity with information at your fingertips. Data relevant to a plant and its components is generated from the first stages of planning and during the asset's complete life cycle. W@M Life Cycle Management is an open and flexible information platform with online and on-site tools. Instant access for your staff to current, in-depth data shortens your plant's engineering time, speeds up procurement processes and increases plant uptime. Combined with the right services, W@M Life Cycle Management boosts productivity in every phase. For more information, see: www.endress.com/lifecyclemanagement

Accessories	Description	
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.	
DeviceCare	Tool to connect and configure Endress+Hauser field devices.	

System components	Accessories	Description
	Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
		 Technical Information TI00133R Operating Instructions BA00247R
	Ceraphant PTC31B	The pressure transmitter for measuring the absolute and gauge pressure in gases, steam, liquids and dusts. It can be used to read in the operating pressure value. Technical Information TI01130P
		Operating Instructions BA01270P
	Cerabar PMC21	The pressure transmitter for measuring the absolute and gauge pressure in gases, steam, liquids and dusts. It can be used to read in the operating pressure value.
		 Technical Information TI01133P Operating Instructions BA01271P
	Cerabar S PMC71	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.
		 Technical Information TI00383P Operating Instructions BA00271P

Documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

 Device Viewer (www.endress.com/deviceviewer): Enter the serial number from the nameplate

• *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

Standard	documentation
----------	---------------

Supplementary information on the semi-standard options is available in the relevant Special Documentation in the TSP database.

Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring device	Documentation code
Proline t-mass I	KA01443D

Brief Operating Instructions for the transmitter

	Documentation code	
Measuring device	HART	Modbus RS485
Proline 300	KA01444D	KA01445D

Operating Instructions

Measuring device	Documentation code	
	HART	Modbus RS485
t-mass I 300	BA01993D	BA01995D

Description of Device Parameters

	Documentation code	
Measuring device	HART	Modbus RS485
t-mass 300	GP01143D	GP01144D

Supplementary device- Safety instructions

dependent documentation

Safety instructions for electrical equipment for hazardous areas.

Contents	Documentation code
ATEX/IECEx Ex d/Ex de	XA01965D
ATEX/IECEx Ex ec	XA01966D
cCSAus XP	XA01969D
cCSAus Ex d/ Ex de	XA01967D
cCSAus Ex nA	XA01968D

Remote display and operating module DKX001

Contents	Documentation code
ATEX/IECEx Ex i	XA01494D
ATEX/IECEx Ex ec	XA01498D
cCSAus IS	XA01499D

Contents	Documentation code
cCSAus Ex nA	XA01513D
INMETRO Ex i	XA01500D
INMETRO Ex ec	XA01501D
NEPSI Ex i	XA01502D
NEPSI Ex nA	XA01503D

Functional safety manual

Contents	Documentation code
Proline t-mass 300	SD02483D

Special documentation

Contents	Documentation code	
	HART	Modbus RS485
Functional Safety Manual	SD02483D	-
Heartbeat Technology	SD02478D	SD02478D
Web server	SD02485D	SD02486D

Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory .

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.



www.addresses.endress.com

