

CERTIFICATE OF CONFORMITY

1. ELECTRICAL EQUIPMENT PER CANADIAN REQUIREMENTS

2. Certificate No: FM24CA0048
3. Equipment:
(Type Reference and Name) CERABAR PMP50, DELTABAR PMD50 Pressure Transmitter
4. Name of Listing Company: Endress+Hauser SE+Co. KG
5. Address of Listing Company: Hauptstrasse 1, Maulburg D-79689, Germany

6. The examination and test results are recorded in confidential report number:

PR464557 dated 4 September 2024

7. FM Approvals LLC, certifies that the equipment described has been found to comply with the following Approval standards and other documents:

CSA C22.2 No. 94.2:2020, CSA C22.2 No. 60529:R2021, CSA C22.2 No. 61010-1:2019

8. This certificate relates to the design, examination and testing of the products specified herein. The FM Approvals surveillance audit program has further determined that the manufacturing processes and quality control procedures in place are satisfactory to manufacture the product as examined, tested and Approved.

9. Equipment Ratings:

IP66/68; Type 4X/6P

10. Description of Equipment:

The Cerabar PMP50 and Deltabar PMD50 Pressure Transmitters are electrical instruments used to measure pressure (Absolute, Gauge, Differential, Remote, Flange types). The measured pressure is communicated via 4...20mA signal, HART protocol.

The Cerabar PMP50 and Deltabar PMD50 Pressure Transmitters housing is constructed of aluminium alloy or stainless steel. The enclosure is a two-compartment enclosure with thread-on covers (blank or windowed if ordered). One compartment for terminals (field wiring connection), and the other compartment for electronics (housing the electronics and optional display). The compartments are interconnected together with various feedthrough designs to route signal and power from the terminal compartment into the electronics compartment. The sensor module, used for measuring the pressure, is threaded to the base of

Certificate issued by:



J.E. Marquedant
VP, Manager - Electrical Systems

4 September 2024

Date

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

F 333 (Jul 24)



SCHEDULE

to Canadian Certificate of Conformity No: FM24CA0048

the enclosure entering the electronics compartment. There are 2 main sensor modules (SP12B and SP11B types).

The enclosure field wiring entries are provided with two M20 or two ½ inch NPT openings. The overall dimensions of the Cerabar PMP50 and Deltabar PMD50 Pressure Transmitter housing without cover is 72 mm long, 106 mm wide, 117 mm height. The free internal volume, both compartments total, is less than 500 cm³.

The Cerabar PMP50 and Deltabar PMD50 Pressure Transmitter process connection (wet end) is constructed of 316/316L/EN 1.4404 Stainless Steel, Alloy 625, Alloy C-246 (austenitic nickel-molybdenum-chromium alloy), Alloy 400, each containing less than 6% magnesium by weight. Further material type process connection versions, for example with plastic coatings or titanium are possible.

The following table below defines the Sensor Module Types and their corresponding maximum working pressure ratings (MWPR).

Code	Type	Maximum Working Pressure Rating and Process Temperature Range
SP11B	Cerabar product (Absolute or Relative Pressure)	-1...400 bar; -40°C...+125°C...+400°C (depending on process connection)
SP12B	Deltabar product (Differential)	-1...40 bar differential -1...420 bar static pressure -40°C...+100°C

Operation Temperature Ranges:

The ambient operating temperature range of the Cerabar PMP50 and Deltabar PMD50 Pressure Transmitter is -40°C...85°C. For Cerabar PMP50 the process temperature range is -40°C...400°C depending on process connection type. For Deltabar PMD50 the process temperature range is -40°C...100°C.

Electrical data:

The Cerabar PMP50 and Deltabar PMD50 Pressure Transmitter require 10.5 Vdc minimum to 35 Vdc maximum input voltage (±10%) for operation. The transmitters use 900mW of power. Electrical signal is digital HART communication over 4...20mA signal.

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

F 333 (Jul 24)



SCHEDULE

to Canadian Certificate of Conformity No: FM24CA0048

11. Specific Conditions of Use:

None

12. Test and Assessment Procedure and Conditions:

This Certificate has been issued in accordance with FM Approvals Canadian Certification Requirements.

13. Schedule Drawings

A copy of the technical documentation has been kept by FM Approvals.

14. Certificate History

Details of the supplements to this certificate are described below:

Date	Description
4 September 2024	Original Issue.

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

F 333 (Jul 24)



SCHEDULE

to Canadian Certificate of Conformity No: FM24CA0048

ANNEX

CERABAR PMP50-FAbbcdefghijklmmno+(options) Pressure Transmitter

Equipment Ratings:

IP 66/68; Type 4X, 6P

Description of Equipment:

CERABAR PMP50-FAbbcdefghijklmmno+(options) Pressure Transmitter

Model Code Options:

bb	Output: BA: 2-wire 4-20 mA HART
c	Display; Operation: A: Blind cover C: Color display w/o buttons
d	Housing; Material: J: Dual compartment; Alu, coated K: Dual compartment; 316L Y: Modifications of one of the above options; changes not relevant for explosion protection
e	Electrical Connection: A: Gland M20, plastic, IP66/68, NEMA Type 4X/6P B: Gland M20, brass nickel plated, IP66/68 NEMA Type 4X/6P C: Gland M20, 316L, IP66/68, NEMA Type 4X/6P F: Thread M20, IP66/68 NEMA Type 4X/6P G: Thread G1/2, IP66/68 NEMA Type 4X/6P H: Thread NPT1/2, IP66/68 NEMA Type 4X/6P J: Gland M20, plastic, blue color, IP66/68, NEMA Type 4X/6P Y: Modification of one of the above mentioned options: Assembled with third party certified cable gland or blanking element, plug connector for Ex i; changes not relevant for explosion protection
f	Pressure Type: 6: Gauge 8: Absolute
g	Application: A: Standard B: Diaphragm seal


To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

F 333 (Jul 24)



SCHEDULE

to Canadian Certificate of Conformity No: FM24CA0048

h	Diaphragm Seal: A: W/o D: Compact G: Temperature isolator Y: Special version, e.g. capillary PE coat., capillary made of other materials (e.g. alloy)
ii	Sensor Range: 3x: pressure ranges up to 400 bar 9Y: Modification of one of the above mentioned options: customer specific pressure range; not relevant for safety
k	Calibration; Unit: Any single character or number not relevant for safety
ll	Process connection, Sealing Surface: AA to ZZ: Standard industrial process connection: threaded, flange 99: Modification of one of the above mentioned options: not relevant for explosion protection
mmm	Process Connection: AAA to ZZZ: Standard industrial process connection: flanges, threaded , flushmount diaphragm seal, 316L, Alloy C , plastic coated 9YY: Modification of one of the above mentioned options: customer specific connections, not relevant for explosion protection
n	Membrane Material: Any single character not relevant for safety
o	Fill fluid: Any single character or number not relevant for safety
(options)	Options: Not relevant for safety

DELTABAR PMD50-FAbbcdefgghikkklnn+(options) Pressure Transmitter

Equipment Ratings:

IP 66/68; Type 4X, 6P

Description of Equipment:

DELTABAR PMD50-FAbbcdefgghikkklnn+(options) Pressure Transmitter

Model Code Options:

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

F 333 (Jul 24)



SCHEDULE

to Canadian Certificate of Conformity No: FM24CA0048

bb	Output: BA: 2-wire 4-20 mA HART
c	Display; Operation: A: Blind cover C: Color display w/o buttons
d	Housing; Material: J: Dual compartment; Alu, coated K: Dual compartment; 316L Y: Modifications of one of the above options; changes not relevant for explosion protection
e	Electrical Connection: A: Gland M20, plastic, IP66/68, NEMA Type 4X/6P B: Gland M20, brass nickel plated, IP66/68 NEMA Type 4X/6P C: Gland M20, 316L, IP66/68, NEMA Type 4X/6P F: Thread M20, IP66/68 NEMA Type 4X/6P G: Thread G1/2, IP66/68 NEMA Type 4X/6P H: Thread NPT1/2, IP66/68 NEMA Type 4X/6P J: Gland M20, plastic, blue color, IP66/68, NEMA Type 4X/6P Y: Modification of one of the above mentioned options: Assembled with third party certified cable gland or blanking element, plug connector for Ex i; changes not relevant for explosion protection
f	Pressure Type: 3: Differential 6: Gauge
gg	Sensor Range: 7x: Dp pressure ranges up to 40 bar 9Y: Modification of one of the above mentioned options: customer specific pressure range; not relevant for safety
h	Calibration; Unit: Any single character or number not relevant for safety
i	Installation: Any single character or number not relevant for safety
kkk	Process Connection: AAA to ZZZ: Standard industrial process connection: e.g. Oval flange NPT1/4", coplanar compatible, 316L, Alloy C, plastic coated 9YY: Modification of one of the above mentioned options: customer specific connections, e.g. PVDF inlay, not relevant for explosion protection
l	Membrane Material: Any single character not relevant for safety

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com


F 333 (Jul 24)



SCHEDULE

to Canadian Certificate of Conformity No: FM24CA0048

m	Fill Fluid: Any single character or number not relevant for safety
n	Seal: Any single character or number not relevant for safety
(options)	Options: Not relevant for safety



To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. One Technology Way, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

F 333 (Jul 24)

