

# Certificate



**No.: 968/FSP 2813.00/25**

<b>Product tested</b>	Pressure Transmitter	<b>Certificate holder</b>	Endress+Hauser SE + Co. KG Hauptstraße 1 79689 Maulburg Germany
-----------------------	----------------------	---------------------------	--

<b>Type designation</b>	Cerabar PMP50 Deltabar PMD50
-------------------------	---------------------------------

<b>Codes and standards</b>	IEC 61508 Parts 1-7:2010	IEC 61326-3-1:2017
----------------------------	--------------------------	--------------------

<b>Intended application</b>	The devices fulfil the requirements of SIL 2 / SC 3 in accordance with IEC 61508 and can be used in applications according to IEC 61508 and IEC 61511-1:2016 + Corr.1:2016 + AMD1:2017 up to SIL 2 (HFT=0) resp. SIL 3 (HFT=1) for the safety function pressure monitoring (MIN, MAX, RANGE).
-----------------------------	---

<b>Specific requirements</b>	The instructions of the associated Operating Manual and Safety Manual shall be considered.
------------------------------	--


Valid until 2030-03-13

The issue of this certificate is based upon an examination, whose results are documented in Report No. 968/FSP 2813.00/25 dated 2025-03-03.  
This certificate is valid only for products which are identical with the product tested.

**TÜV Rheinland Industrie Service GmbH**  
Bereich Automation  
Funktionale Sicherheit  
Am Grauen Stein, 51105 Köln

Köln, 2025-03-13

Certification Body Safety & Security for Automation & Grid

  
Dipl.-Ing. Gebhard Bouwer