

Manufacturer Declaration

WRAS Material Approval for Promag Electromagnetic Flowmeters

This is to confirm that the hard rubber lining material used in the Endress+Hauser Promag electromagnetic flowmeters, is certified according the Water Regulations Advisory Scheme (WRAS).


The hard rubber material used, Wagunit H 1005, is produced by WAGU-Gummitechnik GmbH. As the manufacturer of the hard rubber material, WAGU Gummitechnik GmbH is the holder of the WRAS approval with the approval number 1312510.

Endress + Hauser Flowtec AG herewith declares, that only WRAS approved Wagunit H1005 from WAGU-Gummitechnik GmbH is used in the production of our Promag electromagnetic flowmeters with WRAS drinking water approval.

Reinach, 2014-08-28

Endress+Hauser Flowtec AG

ppa.



Dr.-Ing. Christian Jarms
Head of Quality Management

i.V.



Dipl.-Ing. Michael Karolzak
Project Manager Functional Safety