Technical Information Proline Prowirl C 200

Vortex flowmeter

Products



Sensor enabling primary element corrosion inspection, available as compact or remote device version

Application

- Preferred measuring principle for wet/saturated/ superheated steam, gases & liquids (also cryogenic)
- For steam applications with high chloride content (SAGD) aligned with AER Directive 017 Guidelines

Device properties

- Sensor made of carbon steel
- Material for low medium temperatures
- Display module with data transfer function
- Robust two-chamber housing
- Plant safety: CSA C/US and SIL approvals

Your benefits

- Compliance to AER enables customer to fullfil inspection requirements
- Higher process control unique inspection concept allows visual assessment of primary element
- High process safety resistant to inter-granular stress corrosion cracking
- Convenient device wiring separate connection
- Safe operation no need to open the device due to display with touch control, background lighting
- Integrated verification Heartbeat Technology™



Table of contents

Document information3Symbols used3	Electromag
	Process
Function and system design	Medium ter
Measuring principle	Pressure-te
Measuring system	Pressure los
	Thermal in
Input	Vibrations
Measured variable	
Measuring range	Mechanic
Operable flow range	Design, dim
Input signal	Weight
input signal	Materials .
	Process con
Output	1 100033 0011
Output signal	
Signal on alarm	Operabilit
Load	Operating of
Ex connection data	Local opera
Low flow cut off	Remote ope
Galvanic isolation	Service inte
Protocol-specific data	
	Certificate
Power supply	C-Tick syml
	Ex approval
	Functional
	FOUNDATI
	Certification
Power consumption	Experience
	Other stand
The state of the s	Other stand
Electrical connection	
	Ordering
Terminals	
Cable entries	Application
Cable specification	Diagnostics
Overvoltage protection	Heartbeat 7
	Air and ind
Performance characteristics	Natural gas
Reference operating conditions	Tractarar gas
Maximum measured error	
Repeatability	Accessori
Response time	Device-spec
Influence of ambient temperature	Communica
	Service-spe
Installation	System com
Mounting location	
Orientation	Document
Inlet and outlet runs	Standard do
Length of connecting cable	Supplemen
Installing the wall-mount housing	Supplemen
Special mounting instructions	Registere
Environment	
Ambient temperature range	
Storage temperature	
Climate class	
Degree of protection	
Vibration resistance	

Electromagnetic compatibility (EMC)	44
Process	44
Medium temperature range	44
Pressure-temperature ratings	44
Pressure loss	45
Γhermal insulation	45
Jibrations	45
Mechanical construction	45
Design, dimensions	45
Weight	54
Materials	55
Process connections	56
Operability	57
Operating concept	57
Local operation	57
Remote operation	58
Service interface	60
Certificates and approvals	60
	60
C-Tick symbol	
Ex approval	60
Functional safety	61
FOUNDATION Fieldbus certification	61
Certification PROFIBUS	61
Experience	61
Other standards and guidelines	61
Ordering information	62
Application packages	62
Application packages	
Diagnostics functions	62
Heartbeat Technology	62
Air and industrial gases	63
Natural gas	63
Accessories	63
Device-specific accessories	63
Communication-specific accessories	65
Service-specific accessories	65
System components	66
ystem components	00
Documentation	66
Standard documentation	66
Supplementary device-dependent documentation	67
Registered trademarks	67

2

Document information

Symbols used

Electrical symbols

Symbol	Meaning	Symbol	Meaning
	Direct current	~	Alternating current
≂	Direct current and alternating current	-	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective ground connection A terminal which must be connected to ground prior to establishing any other connections.	♦	Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice.

Symbols for certain types of information

Symbol	Meaning
	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ţ i	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection

Symbols in graphics


Symbol	Meaning	Symbol	Meaning
1, 2, 3,	Item numbers	1. , 2. , 3	Series of steps
A, B, C,	Views	A-A, B-B, C-C,	Sections
EX	Hazardous area	×	Safe area (non-hazardous area)
≋ →	Flow direction		

Function and system design

Measuring principle

Vortex meters work on the principle of the *Karman vortex street*. When fluid flows past a bluff body, vortices are alternately formed on both sides with opposite directions of rotation. These vortices each generate a local low pressure. The pressure fluctuations are recorded by the sensor and converted to

electrical pulses. The vortices develop very regularly within the permitted application limits of the device. Therefore, the frequency of vortex shedding is proportional to the volume flow.



A0019373

The calibration factor (K-factor) is used as the proportional constant:

A0003939-EN

Within the application limits of the device, the K-factor only depends on the geometry of the device. For Re > 20000 it is:

- Independent of the flow velocity and the fluid properties viscosity and density
- Independent of the type of substance under measurement: steam, gas or liquid

The primary measuring signal is linear to the flow. After production, the K-factor is determined in the factory by means of calibration. It is not subject to long-time drift or zero-point drift.

The device does not contain any moving parts and does not require any maintenance.

The capacitance sensor

The sensor of a vortex flowmeter has a major influence on the performance, robustness and reliability of the entire measuring system.

The robust DSC sensor is:

- burst-tested
- tested against vibrations
- tested against thermal shock (thermal shocks of 150 K/s)

The Prowirl uses the tried-and-tested capacitance measuring technology of Endress+Hauser applied in over 300 000 measuring points worldwide.


The DSC (differential switched capacitance) sensor patented by Endress+Hauser has complete mechanical balancing. It only reacts to the measured variable (vortex) and does not react to vibrations. Even in the event of pipe vibrations, the smallest of flows can be reliably measured at low density thanks to the unimpaired sensitivity of the sensor. Thus, the wide turndown is also maintained even in the event of harsh operating conditions. Vibrations up to 1 g at least, at frequencies up to 500 Hz in every axis (X, Y, Z), do not affect the flow measurement. Thanks to its design, the capacitance sensor is also particularly mechanically resistant to temperature shocks and pressure shocks in steam pipelines.

Temperature measurement

The temperature is measured via Pt 1000 temperature sensors. These sensors are located in the paddle of the DSC sensor and are therefore in the direct vicinity of the fluid.

Order code for "Sensor version":

- Option 4 "Volume flow, Alloy 718"
- Option 6 "Mass flow, Alloy 718"



A0010721

■ 1 Sample graphic

- 1 Sensor
- 2 Seal
- 3 Order code for "Sensor version", option 4 "Volume flow, Alloy 718"
- 4 Order code for "Sensor version", option 6 "Mass flow, Alloy 718"

Lifelong calibration

Experience has shown that recalibrated Prowirl devices demonstrate a very high degree of stability compared to their original calibration: The recalibration values were all within the original measuring accuracy specifications of the devices.

Various tests and simulation procedures carried out on devices by filing away the edges of Prowirl's bluff body found that there was no negative impact on the accuracy up to a rounding diameter of 1 mm (0.04 in).

If the meter's edges do not show rounding at the edges that exceeds 1 mm (0.04 in), the following general statements apply (for non-abrasive and non-corrosive media, such as in most water and steam applications):

- The measuring device does not display an offset in the calibration and the accuracy is still quaranteed.
- All the edges on the bluff body have a radius that is typically smaller in size. As the measuring devices are naturally also calibrated with these radii, the measuring device remains within the specified accuracy rating provided that the additional radius that is produced as a result of wear and tear does not exceed 1 mm (0.04 in).

Consequently it can be said that the Prowirl product line offers lifelong calibration if the measuring device is used in non-abrasive and non-corrosive media.

Diagnostic functions

In addition, the device offers extensive diagnostic options, such as tracking fluid and ambient temperatures, extreme flows etc.

The following minimum and maximum values are tracked in the measuring device and saved for diagnostic purposes:

- Frequency
- Temperature
- Velocity
- Pressure

Inspection concept


According to the requirements of the ERCB (Canada), in certain applications the owner-operator of a plant is required to maintain a servicing interval of 12 months.

The condition of the primary measurement element must be checked during these servicing activities. The aim is to be able to ensure a repeatable measurement. Maintenance can be either by way of visual inspection or in line with the recommendations of the equipment manufacturer.

With its unique inspection concept for Prowirl C 200 Endress+Hauser has developed a solution that makes it possible to:

- meet these requirements
- perform maintenance on the installed device
- perform a visual inspection
- deliver an opinion about the measurement quality by measuring the edges of the bluff body.

This inspection concept is available via the *order code "Sensor option"*, *option CR "ERCB Dir. 017 inspection ports"*.



Measuring system

The device consists of a transmitter and a sensor.

Two device versions are available:

• Compact version - the transmitter and sensor form a mechanical unit.

A0013471

• Remote version – the transmitter and sensor are mounted separately from one another.

Device versions and materials:

Transmitter





Configuration:


Compact or remote version, aluminum coated: Aluminum, AlSi10Mg, coated

 Via four-line local display with key operation or via four-line, illuminated local display with touch control and guided menus ("Makeit-run" wizards) for applications

Via operating tools (e.g. FieldCare)

Sensor

Prowirl C



Carbon steel flanged version for use with process pressures, Class 600/ Sch. 80, Cl. 900/Sch. 160:

- Nominal diameter range: DN 50 to 150 (2 to 6")
- Materials
 - Measuring tubes: carbon steel, multiple certifications, SA-106 Grade B, SA-333 Grade 6
 - Process connections: carbon steel, multiple certifications, SA-105, SA-350 LF2 (1)
- Order code for "Sensor option":
 ERCB Dir. 017, version with inspection ports
- Also available as butt-weld version

Input

Measured variable

Direct measured variables

Order code for "Sensor version": Option 4 "Volume flow, Alloy 718": Volume flow

Order code for "Sensor version": Option 6 "Mass flow, Alloy 718":

- Volume flow
- Temperature

Calculated measured variables

Order code for "Sensor version": Option 4 "Volume flow, Alloy 718":

- $\,$ In the case of constant process conditions: Mass flow $^{\rm 1)}$ or Corrected volume flow
- The totalized values for Volume flow, Mass flow, or Corrected volume flow

Order code for "Sensor version":

Option 6 "Mass flow, Alloy 718":

- Corrected volume flow
- Mass flow
- Calculated saturated steam pressure
- Energy flow
- Heat flow difference
- Specific volume
- Degrees of superheat

¹⁾ A fixed density must be entered for calculating the mass flow (Setup menu → Advanced setup submenu → External compensation submenu → Fixed density parameter).

Measuring range

The measuring range depends on the fluid and nominal diameter.

Lower range value

Depends on the density and the Reynolds number ($Re_{min} = 5\,000$, $Re_{linear} = 20\,000$). The Reynolds number is dimensionless and indicates the ratio of the inertia force of a fluid to its viscous force. It is used to characterize the flow. The Reynolds number is calculated as follows:

$$Re = \frac{4 \cdot Q \; [m^3/s] \cdot \rho \; [kg/m^3]}{\pi \cdot di \; [m] \cdot \mu \; [Pa \cdot s]} \qquad \qquad Re = \frac{4 \cdot Q \; [ft^3/s] \cdot \rho \; [lb/ft^3]}{\pi \cdot di \; [ft] \cdot \mu \; [0.001 \; cP]}$$

A000379

Re = Reynolds number; Q = flow; di = internal diameter; μ = dynamic viscosity, ρ = density

DN 50...150
$$\rightarrow v_{min.} = \frac{6}{\sqrt{\rho [kg/m^3]}} [m/s]$$

DN 2...6" $\rightarrow v_{min.} = \frac{4.92}{\sqrt{\rho [lb/ft^3]}} [ft/s]$

A0020558

Upper range value

Liquids:

The upper range value must be calculated as follows:

 v_{max} = 9 m/s (30 ft/s) and v_{max} = 350/ $\sqrt{\rho}$ m/s (130/ $\sqrt{\rho}$ ft/s)

► Use the lower value.

Gas/steam:

Nominal diameter	v_{max}
Standard device: DN 50 to 150 (2 to 6")	120 m/s (394 ft/s) and 350/ $\sqrt{\rho}$ m/s (130/ $\sqrt{\rho}$ ft/s) (Use the lower value.) Calibrated range: up to 75 m/s (246 ft/s)



For information about the Applicator ($\rightarrow \triangleq 65$)

Operable flow range


Up to 45: 1 (ratio between lower and upper range value)

Input signal

External measured values

To increase the accuracy of certain measured variables or to calculate the corrected volume flow, the automation system can continuously write different measured values to the measuring device:

- Operating pressure to increase accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S)
- Medium temperature to increase accuracy (e.g. iTEMP)
- Reference density for calculating the corrected volume flow



It is recommended to read in external measured values to calculate the following measured variables:

- Energy flow
- Mass flow
- Corrected volume flow

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Current input

The measured values are written from the automation system to the measuring device via the current input.

Fieldbuses

The measured values can be written from the automation system to the measuring via:

- PROFIBUS PA
- FOUNDATION Fieldbus

Current input

Current input	4 to 20 mA (passive)
Resolution	1 μΑ
Voltage drop	Typically: 2.2 to 3 V for 3.6 to 22 mA
Maximum voltage	≤ 35 V
Possible input variables	PressureTemperatureDensity

Output

Output signal

Current output

Current output 1	4-20 mA HART (passive)
Current output 2	4-20 mA (passive)
Resolution	<1 μΑ
Damping	Adjustable: 0.0 to 999.9 s
Assignable measured variables	 Volume flow Corrected volume flow Mass flow Flow velocity Temperature Calculated saturated steam pressure Total mass flow Energy flow Heat flow difference

Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	 DC 35 V 50 mA For information on the Ex connection values (→ 12)
Voltage drop	■ For ≤2 mA: 2 V ■ For 10 mA: 8 V

Residual current	≤0.05 mA
Pulse output	
Pulse width	Adjustable: 5 to 2 000 ms
Maximum pulse rate	100 Impulse/s
Pulse value	Adjustable
Assignable measured variables	 Total volume flow Total corrected volume flow Total mass flow Total energy flow Total heat flow difference
Frequency output	
Output frequency	Adjustable: 0 to 1000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Volume flow Corrected volume flow Mass flow Flow velocity Temperature Calculated saturated steam pressure Steam quality Total mass flow Energy flow Heat flow difference
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	Off On Diagnostic behavior Limit value Volume flow Corrected volume flow Mass flow Flow velocity Temperature Calculated saturated steam pressure Steam quality Total mass flow Energy flow Heat flow difference Reynolds number Totalizer 1-3 Status Status of low flow cut off

FOUNDATION Fieldbus

Signal encoding	Manchester Bus Powered (MBP)
Data transfer	31.25 KBit/s, Voltage mode

10

PROFIBUS PA

Signal encoding	Manchester Bus Powered (MBP)
Data transfer	31.25 KBit/s, Voltage mode

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output

HART

Device diagnostics	Device condition can be read out via HART Command 48

Pulse/frequency/switch output

Pulse output	
Failure mode	No pulses
Frequency output	
Failure mode	Choose from: Actual value Defined value: 0 to 1250 Hz O Hz
Switch output	
Failure mode	Choose from: Current status Open Closed

FOUNDATION Fieldbus

Status and alarm messages	Diagnostics in accordance with FF-912
Error current FDE (Fault Disconnection Electronic)	0 mA

PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Error current FDE (Fault Disconnection Electronic)	0 mA

Local display

Plain text display	With information on cause and remedial measures
Backlight	Additionally for device version with SD03 local display: red lighting indicates a device error.

Status signal as per NAMUR recommendation NE 107

Operating tool

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
- Via service interface

Plain text display	With information on cause and remedial measures
--------------------	---



Additional information on remote operation ($\rightarrow \triangleq 58$)


Load

Load for current output: 0 to 500 Ω , depending on the external supply voltage of the power supply unit

Calculation of the maximum load

Depending on the supply voltage of the power supply unit (U_S), the maximum load (R_B) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage ($\rightarrow \boxtimes 22$)

- $R_B \le (U_S U_{term. min}) : 0.022 A$
- $R_B \le 500 \Omega$



A002041

- Load for a compact version without local operation
- 1 Operating range
- 1.1 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with Ex i and option C "4-20 mA HART, 4-20 mA"
- 1.2 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with non-Ex and Ex d

Sample calculation

Supply voltage of the supply unit:

- $U_S = 19 V$
- $U_{term.\,min}$ = 12 V (measuring device) + 1 V (local operation without lighting) = 13 V

Maximum load: R_B ≤ (19 V - 13 V) :0.022 A = 273 Ω

i

The minimum terminal voltage (U $_{term.\,min}$) increases if local operation is used ($\rightarrow~\cong~23$).

Ex connection data

Safety-related values

Type of protection XP

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
Option B	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option C	4-20mA HART	U _{nom} = DC 30 V
	4-20mA	$U_{\text{max}} = 250 \text{ V}$
Option D	4-20mA HART	$U_{\text{nom}} = DC 35 V$ $U_{\text{max}} = 250 V$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W$
	4 to 20 mA current input	U _{nom} = DC 35 V U _{max} = 250 V
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W$

¹⁾ Internal circuit limited by R_i = 760.5 Ω

Intrinsically safe values

IS type of protection

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$\begin{split} &U_{i} = DC \; 30 \; V \\ &I_{i} = 300 \; mA \\ &P_{i} = 1 \; W \\ &L_{i} = 0 \; \mu H \\ &C_{i} = 5 \; nF \end{split}$
Option B	4-20mA HART	$\begin{split} &U_i = DC \ 30 \ V \\ &I_i = 300 \ mA \\ &P_i = 1 \ W \\ &L_i = 0 \ \mu H \\ &C_i = 5 \ nF \end{split}$
	Pulse/frequency/switch output	$\begin{split} &U_i = DC~30~V\\ &I_i = 300~mA\\ &P_i = 1~W\\ &L_i = 0~\mu H\\ &C_i = 6~nF \end{split}$
Option C	4-20mA HART	$\begin{split} &U_i = DC~30~V\\ &I_i = 300~mA\\ &P_i = 1~W\\ &L_i = 0~\mu H \end{split}$

Order code for "Output"	Output type	Intrinsically safe values
	4-20mA	$C_i = 30 \text{ nF}$
Option D	4-20mA HART	$\begin{split} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{split}$
	Pulse/frequency/switch output	$\begin{split} &U_{i} = DC \; 30 \; V \\ &I_{i} = 300 \; mA \\ &P_{i} = 1 \; W \\ &L_{i} = 0 \; \mu H \\ &C_{i} = 6 \; nF \end{split}$
	4 to 20 mA current input	$\begin{split} &U_{i} = DC \; 30 \; V \\ &I_{i} = 300 \; mA \\ &P_{i} = 1 \; W \\ &L_{i} = 0 \; \mu H \\ &C_{i} = 5 \; nF \end{split}$
Option E	FOUNDATION Fieldbus	$\begin{array}{llllllllllllllllllllllllllllllllllll$
	Pulse/frequency/switch output	$\label{eq:U_i = 30 V} \begin{split} U_i &= 30 \ V \\ l_i &= 300 \ mA \\ P_i &= 1 \ W \\ L_i &= 0 \ \mu H \\ C_i &= 6 \ nF \end{split}$
Option G	PROFIBUS PA	$\begin{array}{llllllllllllllllllllllllllllllllllll$
	Pulse/frequency/switch output	$\label{eq:U_i = 30 V} \begin{split} &U_i = 30 \ V \\ &l_i = 300 \ mA \\ &P_i = 1 \ W \\ &L_i = 0 \ \mu H \\ &C_i = 6 \ nF \end{split}$

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

All outputs are galvanically isolated from one another.

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x38
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	 Min. 250 Ω Max. 500 Ω

14

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.
	Measured variables for PV (primary dynamic variable) • Volume flow
	Corrected volume flow
	Mass flow
	 Flow velocity
	 Temperature
	 Calculated saturated steam pressure
	 Steam quality
	 Total mass flow
	Energy flow
	Heat flow difference
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary
	dynamic variable)
	Volume flow Compared and leave flows
	Corrected volume flowMass flow
	Mass nowFlow velocity
	Temperature
	 Calculated saturated steam pressure
	Steam quality
	Total mass flow
	■ Energy flow
	 Heat flow difference
	 Condensate mass flow
	 Reynolds number
	■ Totalizer 1
	■ Totalizer 2
	 Totalizer 3
	 HART input
	Density
	• Pressure
	Specific volume
	Degree of overheating
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned.
	A maximum of 8 device variables can be transmitted:
	0 = volume flow
	• 1 = corrected volume flow
	■ 2 = Mass flow
	■ 3 = flow velocity
	■ 4 = temperature
	 5 = calculated saturated steam pressure
	■ 6 = steam quality
	■ 7 = total mass flow
	■ 8 = energy flow
	9 = heat flow difference
	• 10 = condensate mass flow
	■ 11 = Reynolds number
	• 12 = totalizer 1
	■ 13 = totalizer 2
	• 14 = totalizer 3
	• 15 = HART input
	• 16 = density
	17 = pressure18 = specific volume
	 10 - Specific volume 19 = degree of overheating
	- 17 degree of overheading

FOUNDATION Fieldbus

Manufacturer ID	0x452B48
Ident number	0x1038
Device revision	1

DD revision	Information and files under:				
CFF revision	www.endress.comwww.fieldbus.org				
Device Tester Version (ITK version)	6.1.1				
ITK Test Campaign Number	IT094200				
Link Master capability (LAS)	Yes				
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device				
Node address	Factory setting: 247 (0xF7)				
Supported functions	The following methods are supported: Restart ENP Restart Diagnostic				
Virtual Communication Relation	onships (VCRs)				
Number of VCRs	44				
Number of link objects in VFD	50				
Permanent entries	1				
Client VCRs	0				
Server VCRs	10				
Source VCRs	43				
Sink VCRs	0				
Subscriber VCRs	43				
Publisher VCRs	43				
Device Link Capabilities					
Slot time	4				
Min. delay between PDU	8				
Max. response delay	Min. 5				

Transducer Blocks

Block	Contents	Output values
Setup Transducer Block (TRDSUP)	All parameters for standard commissioning.	No output values
Advanced Setup Transducer Block (TRDASUP)	All parameters for more accurate measurement configuration.	No output values
Display Transducer Block (TRDDISP)	Parameters for configuring the local display.	No output values
HistoROM Transducer Block (TRDHROM)	Parameters for using the HistoROM function.	No output values

Block	Contents	Output values
Diagnostic Transducer Block (TRDDIAG)	Diagnostics information.	Process variables (AI Channel) Mass flow (11) Flow velocity (37) Condensate mass flow (47) Total mass flow (46) Volume flow (9) Corrected volume flow (13) Temperature (7) Calculated saturated steam pressure (45) Steam quality (48) Energy flow (38) Heat flow difference (49) Reynolds number (50)
Expert Configuration Transducer Block (TRDEXP)	Parameters that require the user to have indepth knowledge of the operation of the device in order to configure the parameters appropriately.	No output values
Expert Information Transducer Block (TRDEXPIN)	Parameters that provide information about the state of the device.	No output values
Service Sensor Transducer Block (TRDSRVS)	Parameters that can only be accessed by Endress +Hauser Service.	No output values
Service Information Transducer Block (TRDSRVIF)	Parameters that provide Endress+Hauser Service with information about the state of the device.	No output values
Total Inventory Counter Transducer Block (TRDTIC)	Parameters for configuring all the totalizers and the inventory counter.	Process variables (AI Channel) Totalizer 1 (16) Totalizer 2 (17) Totalizer 3 (18)
Heartbeat Technology Transducer Block (TRDHBT)	Parameters for the configuration and comprehensive information about the results of the verification.	No output values
Heartbeat Results 1 Transducer Block (TRDHBTR1)	Information about the results of the verification.	No output values
Heartbeat Results 2 Transducer Block (TRDHBTR2)	Information about the results of the verification.	No output values
Heartbeat Results 3 Transducer Block (TRDHBTR3)	Information about the results of the verification.	No output values
Heartbeat Results 4 Transducer Block (TRDHBTR4)	Information about the results of the verification.	No output values

Function blocks

Block	Number of blocks	Contents	Process variables (Channel)
Resource Block (RB)	1	This Block (extended functionality) contains all the data that uniquely identify the device; it is the equivalent of an electronic nameplate for the device.	_
Analog Input Block (AI)	4	This Block (extended functionality) receives the measurement data provided by the Sensor Block (can be selected via a channel number) and makes the data available for other blocks at the output. Execution time: 13 ms	 Temperature (7) Mass flow (11) Volume flow (9) Corrected volume flow (13) Flow velocity (37) Energy flow (38) Calculated saturated steam pressure (45) Total mass flow (46) Condensate mass flow (47) Steam quality (48) Heat flow difference (49) Reynolds number (50)
Discrete Input Block (DI)	1	This Block (standard functionality) receives a discrete value (e.g. indicator that measuring range has been exceeded) and makes the value available for other blocks at the output. Execution time: 12 ms	 Status switch output (101) Low flow cutoff (103) Status verification (105)
PID Block (PID)	1	This Block (standard functionality) acts as a proportional-integral-differential controller and can be used universally for control in the field. It enables cascading and feedforward control. Execution time: 13 ms	-
Multiple Analog Output Block (MAO)	1	This Block (standard functionality) receives several analog values and makes them available for other blocks at the output. Execution time: 11 ms	Channel_0 (121) Value 1: External compensation variables (pressure, gage pressure, density, temperature or second temperature) Value 2 to 8: Not assigned The compensation variables must be transmitted to the device in the SI basic unit.

Block	Number of blocks	Contents	Process variables (Channel)
Multiple Digital Output Block (MDO)	1	This Block (standard functionality) receives several discrete values and makes them available for other blocks at the output. Execution time: 14 ms	Channel_DO (122) Value 1: Reset totalizer 1 Value 2: Reset totalizer 2 Value 3: Reset totalizer 3 Value 4: Flow override Value 5: Start heartbeat verification Value 6: Status switch output Value 7: Not assigned Value 8: Not assigned
Integrator Block (IT)	1	This Block (standard functionality) integrates a measured variable over time or totalizes the pulses from a Pulse Input Block. The Block can be used as a totalizer that totalizes until a reset, or as a batch totalizer whereby the integrated value is compared against a target value generated before or during the control routine and generates a binary signal when the target value is reached. Execution time: 16 ms	-

PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x1564
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: www.endress.com www.profibus.org
Output values (from measuring device to automation system)	Analog input 1 to 4 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Pressure Specific volume Degree of overheating
	Digital input 1 to 2 Status Low flow cut off Switch output Totalizer 1 to 3 Mass flow Volume flow
	Corrected volume flow
Input values (from automation system to measuring device)	Analog output External pressure, gage pressure, density, temperature or second temperature (for delta heat measurement)
	Digital output 1 to 3 (fixed assignment) Digital output 1: switch positive zero return on/off Digital output 2: switch switch output on/off Digital output 3: Start verification
	Totalizer 1 to 3 Totalize Reset and hold Preset and hold


Supported functions	 Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Local display Via operating tools (e.g. FieldCare)

Power supply

Terminal assignment

Transmitter

Connection versions



- Output 1 (passive): supply voltage and signal transmission
- Output 2 (passive): supply voltage and signal transmission
- Input (passive): supply voltage and signal transmission
- Ground terminal for cable shield

Order code for "Output"	Terminal numbers						
	Output 1		Output 2		Input		
	1 (+) 2 (-)		3 (+)	4 (-)	5 (+)	6 (-)	
Option A	4-20 mA HART (passive)		-		-		
Option B ¹⁾	4-20 mA HART (passive)		Pulse/freque output (ency/switch passive)	-		
Option C 1)	4-20 mA HART (passive)		4-20 mA (passive)		-		
Option D ^{1) 2)}	4-20 mA HART (passive)		Pulse/frequo output (,	4-20 mA cu (pass	*	

Order code for "Output"	Terminal numbers						
	Out	out 1	Outp	out 2	Inp	out	
	1 (+) 2 (-)		3 (+)	4 (-)	5 (+)	6 (-)	
Option E ^{1) 3)}	FOUNDATION Fieldbus		Pulse/frequency/switch output (passive)		-	-	
Option G ^{1) 4)}	PROFIBUS PA		Pulse/frequ output (ency/switch passive)	-	-	

- 1) Output 1 must always be used; output 2 is optional.
- 2) The integrated overvoltage protection is not used with option D: Terminals 5 and 6 (current input) are not protected against overvoltage.
- 3) FOUNDATION Fieldbus with integrated reverse polarity protection.
- 4) PROFIBUS PA with integrated reverse polarity protection.

Remote version

In the case of the remote version, the sensor and transmitter are mounted separately from one another and connected by a connecting cable. The sensor is connected via the connection housing while the transmitter is connected via the connection compartment of the wall holder unit.

i

The way the transmitter wall holder is connected depends on the measuring device approval and the version of the connecting cable used.


Connection is only possible via terminals:

- For approvals Ex n, Ex tb and cCSAus Div. 1
- If a reinforced connecting cable is used

The connection is via an M12 connector:

- For all other approvals
- ullet If the standard connecting cable is used

Connection to the connection housing of the sensor is always via terminals.



A0019335

- 🗷 3 Terminals for connection compartment in the transmitter wall holder and the sensor connection housing
- 1 Terminals for connecting cable
- 2 Grounding via the cable strain relief

Terminal number	Assignment	Cable color Connecting cable
1	Supply voltage	Brown
2	Grounding	White
3	RS485 (+)	Yellow
4	RS485 (-)	Green

Pin assignment, device plug

PROFIBUS PA

Device plug for signal transmission (device side)

	Pin		Assignment	Coding	Plug/socket
2 3	1	+	PROFIBUS PA +	А	Plug
1 4	2		Grounding		
A0019021	3	-	PROFIBUS PA -		
	4		Not assigned		

FOUNDATION Fieldbus

Device plug for signal transmission (device side)

	Pin		Assignment	Coding	Plug/socket
2 3	1	+	Signal +	А	Plug
1 4	2	-	Signal –		
A0019021	3		Not assigned		
	4		Grounding		

Supply voltage

Transmitter

An external power supply is required for each output.

Supply voltage for a compact version without a local display $^{1)}$

Order code for "Output"	Minimum terminal voltage ²⁾	Maximum terminal voltage
Option A : 4-20 mA HART	≥DC 12 V	DC 35 V
Option B : 4-20 mA HART, pulse/ frequency/switch output	≥DC 12 V	DC 35 V
Option C : 4-20 mA HART, 4-20 mA	≥DC 12 V	DC 30 V
Option D : 4-20 mA HART, pulse/ frequency/switch output, 4-20 mA current input ³⁾	≥DC 12 V	DC 35 V
Option E : FOUNDATION Fieldbus, pulse/frequency/switch output	≥DC 9 V	DC 32 V
Option G : PROFIBUS PA, pulse/frequency/switch output	≥DC 9 V	DC 32 V

- 1) In event of external supply voltage of the power supply unit with load, the PROFIBUS DP/PA coupler or FOUNDATION Fieldbus power conditioners
- 2) The minimum terminal voltage increases if local operation is used: see the following table
- 3) Voltage drop 2.2 to 3 V for 3.59 to 22 mA

Increase in minimum terminal voltage

Local operation	Increase in minimum terminal voltage
Order code for "Display; Operation", option C : Local operation SD02	+ DC 1 V
Order code for "Display; Operation", option E : Local operation SD03 with lighting (backlighting not used)	+ DC 1 V
Order code for "Display; Operation", option E : Local operation SD03 with lighting (backlighting used)	+ DC 3 V

- For information about the load see ($\rightarrow \triangleq 12$)
- For information on the Ex connection values ($\rightarrow = 12$)

Power consumption

Transmitter

Order code for "Output"	Maximum power consumption
Option A: 4-20 mA HART	770 mW
Option B : 4-20 mA HART, pulse/ frequency/switch output	Operation with output 1: 770 mWOperation with output 1 and 2: 2 770 mW
Option C : 4-20 mA HART, 4-20 mA	 Operation with output 1: 660 mW Operation with output 1 and 2: 1320 mW
Option D : 4-20 mA HART, pulse/ frequency/switch output, 4-20 mA current input	 Operation with output 1: 770 mW Operation with output 1 and 2: 2770 mW Operation with output 1 and input: 840 mW Operation with output 1, 2 and input: 2840 mW
Option E: FOUNDATION Fieldbus, pulse/frequency/switch output	 Operation with output 1: 512 mW Operation with output 1 and 2: 2512 mW
Option G : PROFIBUS PA, pulse/frequency/switch output	 Operation with output 1: 512 mW Operation with output 1 and 2: 2512 mW

Current consumption

Current output

For every 4-20 mA or 4-20 mA HART current output: 3.6 to 22.5 mA

If the option **Defined value** is selected in the **Failure mode** parameter ($\rightarrow \implies 11$): 3.59 to 22.5 mA

Current input

3.59 to 22.5 mA

Internal current limiting: max. 26 mA

PROFIBUS PA

15 mA

FOUNDATION Fieldbus


15 mA

Power supply failure

- Totalizers stop at the last value measured.
- Configuration is retained in the device memory (HistoROM).
- Error messages (incl. total operated hours) are stored.

Electrical connection


Connecting the transmitter



1 Cable entries for inputs/outputs

Remote version connection

Connecting cable



A001972

- 4 Connecting cable connection
- 1 Wall holder with connection compartment (transmitter)
- 2 Connecting cable
- 3 Sensor connection housing

The way the transmitter wall holder is connected depends on the measuring device approval and the version of the connecting cable used.

Connection is only possible via terminals:

- For approvals Ex n, Ex tb and cCSAus Div. 1
- If a reinforced connecting cable is used

The connection is via an M12 connector:


- For all other approvals
- If the standard connecting cable is used

Connection to the connection housing of the sensor is always via terminals.

24

Connection examples


Current output 4-20 mA HART



■ 5 Connection example for 4-20 mA HART current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N) ($\rightarrow \square$ 29)
- *3 Cable shield, observe cable specifications* ($\rightarrow \stackrel{\triangle}{=} 29$)
- 5 Connection for HART operating devices (→ 🖺 58)
- 6 Analog display unit: observe maximum load ($\rightarrow \square$ 12)
- 7 Transmitter


Current output 4-20 mA



A0015512


- 6 Connection example for 4-20 mA current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 3 Analog display unit: observe maximum load ($\rightarrow \square$ 12)
- 4 Transmitter

Pulse/frequency output




- **₽** 7 Connection example for pulse/frequency output (passive)
- Automation system with pulse/frequency input (e.g. PLC) 1
- 2
- Power supply $Transmitter: observe input values \ (\rightarrow \ \ \ \, \bigcirc \ \, 9)$ 3

Switch output



- ₽8 Connection example for switch output (passive)
- 1 Automation system with switch input (e.g. PLC)
- Power supply
- 2 3 *Transmitter: observe input values* ($\rightarrow \implies 9$)


PROFIBUS-PA



₽ 9 Connection example for PROFIBUS-PA

- 1
- Control system (e.g. PLC) Segment coupler PROFIBUS DP/PA Cable shield T-box
- 2 3 4 5
- Measuring device
- Local grounding Bus terminator
- Potential matching line


FOUNDATION Fieldbus



■ 10 Connection example for FOUNDATION Fieldbus


- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus) 2
- 3 Cable shield
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- Bus terminator
- Potential matching line

Current input



- **■** 11 Connection example for 4-20 mA current input
- External measuring device (for reading in pressure or temperature, for instance) Transmitter: observe input values $(\rightarrow \bigcirc \bigcirc \bigcirc \bigcirc \bigcirc \bigcirc$ 2

HART input



■ 12 Connection example for HART input with a common negative


- 1 Automation system with HART output (e.g. PLC)
- 2 Resistor for HART communication (≥ 250 Ω): observe maximum load (\rightarrow $\stackrel{\triangle}{=}$ 12)
- 3 Active barrier for power supply (e.g. RN221N) ($\rightarrow \triangleq 22$)
- 4 Cable shield, observe cable specifications ($\rightarrow \stackrel{\triangle}{=} 29$)
- 5 Analog display unit: observe maximum load ($\rightarrow \square$ 12)
- 6 Pressure transmitter (e.g. Cerabar M, Cerabar S): see requirements (→ 🖺 8)
- 7 Transmitter

Potential equalization

Requirements

Please consider the following to ensure correct measurement:

- Same electrical potential for the fluid and sensor
- Remote version: same electrical potential for the sensor and transmitter
- Company-internal grounding concepts
- Pipe material and grounding



Terminals

- For device version without integrated overvoltage protection: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)
- For device version with integrated overvoltage protection: screw terminals for wire cross-sections 0.2 to 2.5 mm² (24 to 14 AWG)

Cable entries

- Cable gland (not for Ex d): M20 \times 1.5 with cable ϕ 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - For non-Ex and Ex: NPT 1/2"
 - For non-Ex and Ex (not for CSA Ex d/XP): G $\frac{1}{2}$ "
 - For Ex d: M20 × 1.5

Cable specification

Permitted temperature range

- -40 °C (-40 °F) to +80 °C (+176 °F)
- \blacksquare Minimum requirement: cable temperature range \ge ambient temperature +20 K

Signal cable

Current output

For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant.

Pulse/frequency/switch output

Standard installation cable is sufficient.

Current input

Standard installation cable is sufficient.

FOUNDATION Fieldbus

Twisted, shielded two-wire cable.



- - Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)
 - FOUNDATION Fieldbus Guideline
 - IEC 61158-2 (MBP)

PROFIBUS PA

Twisted, shielded two-wire cable. Cable type A is recommended.



For further information on planning and installing PROFIBUS PA networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

Connecting cable for remote version

Connecting cable (standard)

Standard cable	$4\times2\times0.34~\text{mm}^2$ (22 AWG) PVC cable with common shield (4 pairs, pair-stranded)
Flame resistance	According to DIN EN 60332-1-2
Oil-resistance	According to DIN EN 60811-2-1
Shielding	Galvanized copper-braid, opt. density approx. 85%
Cable length	5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft)
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)

Connecting cable (reinforced)

Cable, reinforced	$4\times2\times0.34$ mm² (22 AWG) PVC cable with common shield (4 pairs, pair-stranded) and additional steel-wire braided sheath
Flame resistance	According to DIN EN 60332-1-2
Oil-resistance	According to DIN EN 60811-2-1
Shielding	Galvanized copper-braid, opt. density approx. 85%
Strain relief and reinforcement	Steel-wire braid, galvanized
Cable length	5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft)
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)

Overvoltage protection

The device can be ordered with integrated overvoltage protection for diverse approvals: Order code for "Accessory mounted", option NA "Overvoltage protection"

Input voltage range	Values correspond to supply voltage specifications ($\rightarrow riangleq riangleq 22$) $^1)$
Resistance per channel	2·0.5 Ω max
DC sparkover voltage	400 to 700 V
Trip surge voltage	<800 V
Capacitance at 1 MHz	<1.5 pF

Nominal discharge current (8/20 μs)	10 kA
Temperature range	-40 to +85 °C (-40 to +185 °F)

1) The voltage is reduced by the amount of the internal resistance $I_{\text{min}}\cdotp R_i$

Depending on the temperature class, restrictions apply to the ambient temperature for device versions with overvoltage protection $(\rightarrow \triangleq 38)$

Performance characteristics

Reference operating conditions

- Error limits following ISO/DIN 11631
- +20 to +30 °C (+68 to +86 °F)
- 2 to 4 bar (29 to 58 psi)
- Calibration system traceable to national standards
- Calibration with the process connection corresponding to the particular standard
- To obtain measured errors, use the Applicator sizing tool (ightarrow 🖺 65)


Maximum measured error

Base accuracy

o.r. = of reading, Re = Reynolds number

Volume flow

The measured error for the volume flow is as follows depending on the Reynolds number and the compressibility of the medium under measurement:



Deviation of volume flow value (absolute) from the reading			
Medium type		Incompressible	Compressible 1)
Re range	Measured value deviation	Standard	Standard
R1 to R2	A2	< 10 %	< 10 %
R2 to Re _{max}	A1	< 0.75 %	< 1.0 %

1) Accuracy specifications valid up to 75 m/s (246 ft/s)

Endress+Hauser 31

A0019703

Reynolds numbers	Incompressible	Compressible
Reynolus numbers	Standard	Standard
R1	5 000	
R2	20 000	

Temperature

- Saturated steam and liquids at room temperature if T > 100 °C (212 °F) applies: < 1 °C (1.8 °F)
- Gas: < 1 % o.r. [K]

Rise time 50 % (stirred under water, following IEC 60751): 8 s

Mass flow (saturated steam)

- Flow velocities 20 to 50 m/s (66 to 164 ft/s), T > 150 °C (302 °F) or (423 K)
 - Re > 20000: < 1.7 % o.r.
 - Re between 5 000 to 20 000: < 10 % o.r.
- Flow velocities 10 to 70 m/s (33 to 210 ft/s), T > 140 °C (284 °F) or (413 K)
 - Re > 20000: < 2 % o.r.
 - Re between 5 000 to 20 000: < 10 % o.r.
- The use of a Cerabar S is required for the measured errors listed in the following section. The measured error used to calculate the error in the measured pressure is 0.15%.

Mass flow of superheated steam and gas (single gas, gas mixture, air: NEL40; natural gas: ISO 12213-2 contains AGA8-DC92, AGA NX-19, ISO 12213-3 contains SGERG-88 and AGA8 Gross Method 1)

- Re > 20000 and process pressure < 40 bar abs. (580 psi abs.): 1.7 % o.r.
- Re between 5000 to 20000 and process pressure < 40 bar abs. (580 psi abs.): 10 % o.r.
- Re > 20 000 and process pressure < 120 bar abs. (1740 psi abs.): 2.6 % o.r.
- Re between 5 000 to 20 000 and process pressure < 120 bar abs. (1740 psi abs.): 10 % o.r.

abs. = absolute

Mass flow (water)

- Re 20000: < 0.85 % o.r.
- Re between 5000 to 20000: < 10 % o.r.

Mass flow (user-defined liquids)

To specify the system accuracy, Endress+Hauser requires information about the type of liquid and its operating temperature or information in table form about the dependency between the liquid density and the temperature.

Example

- Acetone is to be measured at fluid temperatures between +70 to +90 °C (+158 to +194 °F).
- For this purpose the **Reference temperature** parameter (7703) (here 80 °C (176 °F)), **Reference density** parameter (7700) (here 720.00 kg/m³) and **Linear expansion coefficient** parameter (7621) (here 18.0298 × 10⁻⁴ 1/°C) must be entered in the transmitter.
- The overall system uncertainty, which is smaller than 0.9 % for the example above, is comprised of the following uncertainties of measurement: uncertainty of volume flow measurement, uncertainty of temperature measurement, uncertainty of the density-temperature correlation used (incl. the resulting uncertainty of density).

Mass flow (other media)

Depends on the selected fluid and the pressure value, which is specified in the parameters. Individual error analysis must be performed.

Accuracy of outputs

o.r. = of reading

Current output

Accuracy	±10 μΑ
----------	--------

Pulse/frequency output

Accuracy	Max. ±100 ppm o.r.
Accuracy	Max. ±100 ppm o.r.

Repeatability

o.r. = of reading

±0.2 % o.r.

Response time

If all the configurable functions for filter times (flow damping, display damping, current output time constant, frequency output time constant, status output time constant) are set to 0, in the event of vortex frequencies of 10 Hz and higher a response time of $max(T_v, 100 \text{ ms})$ can be expected.

In the event of measuring frequencies < 10 Hz, the response time is > 100 ms and can be up to 10 s. T_v is the average vortex period duration of the flowing fluid.

Influence of ambient temperature

o.r. = of reading

Current output

Additional error, in relation to the span of 16 mA:


Temperature coefficient at zero point (4 mA)	0.02 %/10 K
Temperature coefficient with span (20 mA)	0.05 %/10 K

Pulse/frequency output

Temperature coefficient	Max. ±100 ppm o.r.
Temperature coefficient	Max. ±100 ppm o.r.

Installation

Mounting location



Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).


Vortex meters require a fully developed flow profile as a prerequisite for correct volume flow measurement. Therefore, please note the following:

Orientation			Compact version	Remote version
A	Vertical orientation	A0015545	∨∨ 1)	ζ.
В	Horizontal orientation, transmitter head up	A0015589	νν ²⁾³⁾	V

Orientation			Compact version	Remote version
С	Horizontal orientation, transmitter head down	A0015590	√√ 4) 5)	VV
D	Horizontal orientation, transmitter head at side	A0015592	√ √ ⁴⁾	VV

- In the case of liquids, there should be upward flow in vertical pipes to avoid partial pipe filling (Fig. A).
 Disruption in flow measurement! In the case of vertical orientation and downward flowing liquid, the pipe always needs to be completely filled to ensure correct liquid flow measurement.
- Danger of electronics overheating! If the fluid temperature is \geq 200 °C (392 °F) orientation B is not permitted for the wafer version (Prowirl D) with nominal diameters DN 100 (4") and DN 150 (6").
- In the case of hot media (e.g. steam or fluid temperature (TM) \geq 200 °C (392 °F): orientation C or D
- 4) In the case of very cold media (e.g. liquid nitrogen): orientation B or D
- 5) For "wet steam detection/measurement" option: orientation C

Minimum spacing and cable length



A00192

- A Minimum spacing in all directions
- L Required cable length

The following dimensions must be observed to guarantee problem-free access to the device for service purposes:


- A =100 mm (3.94 in)
- \blacksquare L = L + 150 mm (5.91 in)

Rotating the electronics housing and the display

The electronics housing can be rotated continuously by 360 $^{\circ}$ on the housing support. The display unit can be rotated in 45 $^{\circ}$ stages. This means you can read the display comfortably from all directions.

Inlet and outlet runs

To attain the specified level of accuracy of the measuring device, the inlet and outlet runs mentioned below must be maintained at the very minimum.




■ 13 Minimum inlet and outlet runs with various flow obstructions

- h Difference in expansion
- 1 Reduction by one nominal diameter size
- 2 Single elbow (90° elbow)
- 3 Double elbow $(2 \times 90^{\circ} \text{ elbows, opposite})$
- 4 Double elbow 3D ($2 \times 90^{\circ}$ elbows, opposite, not on one plane)
- 5 T-piece
- 6 Expansion
- 7 Control valve
- 8 Two measuring devices in a row where DN \leq 25 (1"): directly flange on flange
- Two measuring devices in a row where DN \geq 40 (1½"): for spacing, see graphic

Outlet runs when installing external devices

If installing an external device, observe the specified distance.



A001920

- PT Pressure transmitter
- TT Temperature transmitter

Length of connecting cable


To ensure correct measuring results when using the remote version,

- $\mbox{--}$ observe the maximum permitted cable length $L_{\mbox{\scriptsize max}}.$
- The value for the cable length must be calculated if the cable cross-section differs from the specification.

For detailed information about calculating the length of the connecting cable, refer to the Operating Instructions for the device on the CD-ROM provided


Installing the wall-mount housing

Wall mounting



■ 14 Engineering unit mm (in)

Post mounting



■ 15 Engineering unit mm (in)

1 Post retainer kit for post mounting

Special mounting instructions

Inspection kit

The inspection kit contains the necessary parts for the annual visual inspection of the primary measurement element (bluff body) in accordance with ERCB Dir. 017.

- 2 inspection centering sleeves
- 8 screws
- 2 inspection seals
- 2 inspection covers

The centering sleeve supports the user by centering the calipers in the inspection ports. This makes it easier to measure the distance from the sealing surface to the bluff body. In addition, the kit also contains screws, seals and covers for the inspection ports.




An inspection kit can be ordered separately (see the "Accessories" section ($\rightarrow \triangleq 64$)).

Installation for delta heat measurements

Order code for "Sensor version", option 3 "Mass flow (integrated temperature measurement)"

The second temperature measurement is taken using a separate temperature sensor. The measuring device reads in this value via a communication interface.

- In the case of saturated steam delta heat measurements, the Prowirl 200 must be installed on the steam side.
- In the case of water delta heat measurements, the Prowirl 200 can be installed on the cold or warm side.



 \blacksquare 16 Layout for delta heat measurement of saturated steam and water

- Prowirl
- Temperature sensor
- Heat exchanger
- Heat flow

Weather protection cover

Observe the following minimum head clearance: 222 mm (8.74 in)



For information the weather protection cover, see ($\rightarrow \triangleq 63$)

Environment

Ambient temperature range

Compact version

Measuring device	Non-Ex:	-40 to +80 °C (-40 to +176 °F) 1)
	Ex i:	-40 to +70 °C (-40 to +158 °F) 1)
	EEx d/XP version:	-40 to +60 °C (-40 to +140 °F) 1)
	ATEX II1/2G Ex d, Ex ia:	-40 to +60 °C (-40 to +140 °F) 1)
Local display		-20 to +60 °C (-4 to +140 °F)

1) Additionally available as order code for "Test, certificate", option JN "Transmitter ambient temperature -50 °C (-58 °F)".

Remote version

Transmitter	Non-Ex:	-40 to +80 °C (-40 to +176 °F) ¹⁾
	Ex i:	-40 to +80 °C (-40 to +176 °F) ¹⁾
	Ex d:	-40 to +60 °C (-40 to +140 °F) ¹⁾
	ATEX II1/2G Ex d, Ex ia:	-40 to +60 °C (-40 to +140 °F) ¹⁾
Sensor	Non-Ex:	-40 to +85 °C (-40 to +185 °F) ¹⁾
	Ex i:	-40 to +85 °C (-40 to +185 °F) ¹⁾
	Ex d:	-40 to +85 °C (-40 to +185 °F) ¹⁾
	ATEX II1/2G Ex d, Ex ia:	-40 to +85 °C (-40 to +185 °F) ¹⁾
Local display		-20 to +60 °C (-4 to +140 °F)

- 1) Additionally available as order code for "Test, certificate", option JN "Transmitter ambient temperature -50 °C (-58 °F)".
- ► If operating outdoors:

Avoid direct sunlight, particularly in warm climatic regions.

Weather protection covers can be ordered from Endress+Hauser: see "Accessories" section $(\rightarrow \triangleq 63)$

Temperature tables

 $T_{\rm m}$ = fluid temperature, $T_{\rm a}$ = ambient temperature

The following interdependencies between the permitted ambient and fluid temperatures apply when operating the device in hazardous areas:

$Compact\ version$

Order code for "Sensor version", option 4 "Volume flow Alloy 718"; option 6 "Mass flow Alloy 718" option 6 "Mass flow Alloy 718" option 6 "Mass flow Alloy 718".

Order code for "Output", option A "4-20mA HART"

Order code for "Approval", all options cCSA_{US} IS, cCSA_{US} XP, cCSA_{US} NI

SI units

Version with max. T_m = 280 °C								
T _a 1) [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 °C]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]		
40	80	95	130	195	280	_		
60	-	95	130	195	280	_		

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a 1) [°C]	T6 [85 ℃]	T5 [100 °C]	T4 [135 ℃]	T3 [200 °C]	T2 [300°C]	T1 [450 ℃]			
65	-	-	130	195	280	-			
70	-	-	130	_	_	-			

1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C

US units

Version with max. T_m = 536 $^{\circ}F$									
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
104	176	203	266	383	536	-			
140	_	203	266	383	536	-			
149	_	-	266	383	536	-			
158	-	-	266	-	-	-			

The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 35.6$ °F

Order code for "Output", option B "4-20mA HART, pulse/frequency/switch output" Order code for "Approval", options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2 $_{\rm CCSA_{\rm US}}$ IS

SI units

Version w	Version with max. $T_m = 280 ^{\circ}\text{C}$									
T _a 1) [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]				
35 ²⁾	80	95	130	195	280	-				
50 ³⁾	-	95	130	195	280	_				
60	_	-	130	195	280	1				
65	_	-	130	195	280 ⁴⁾	_				
70	-	-	130	195 ⁵⁾	280 ⁵⁾	-				

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 40$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 55$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0.7$ W
- 5) $T_a = 70 \,^{\circ}\text{C}$ for pulse/frequency/switch output $P_i = 0.7 \,^{\circ}\text{W}$

US units

Version with max. $T_m = 536 ^{\circ}F$								
T _a ¹⁾ [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]		
95 ²⁾	176	203	266	383	536	_		
122 ³⁾	-	203	266	383	536	-		
140	-	-	266	383	536	-		

Version with max. $T_m = 536 ^{\circ}F$								
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]		
149	-	-	266	383	536 ⁴⁾	-		
158	_	_	266	383 ⁵⁾	536 ⁵⁾	-		

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 104$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 131$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0.7$ W
- $T_a = 158 \,^{\circ}\text{F} \text{ for pulse/frequency/switch output P}_i = 0.7 \,^{\circ}\text{W}$

Order code for "Approval", options BC, BG, BK, B3, IC, IG, IK, I5, C3 $_{\rm CCSA_{\rm US}}$ XP

SI units

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
40	80	95	130	195	280	-			
55	-	95	130	195	280	-			
65	-	-	130	195	280 ¹⁾	-			
70	_	_	130	195 ²⁾	280 ²⁾	-			

- 1) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0.7$ W
- 2) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.7$ W

US units

Version	Version with max. $T_m = 536 ^{\circ}F$								
T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
104	176	203	266	383	536	-			
131	-	203	266	383	536	-			
149	-	-	266	383	536 ¹⁾	-			
158	-	-	266	383 ²⁾	536 ²⁾	-			

- 1) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0.7$ W
- 2) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0.7$ W

Order code for "Output", option C "4-20mA HART, 4-20mA" $\,$

Order code for "Approval", all options cCSA_{US} IS, cCSA_{US} XP, cCSA_{US} NI

SI units

Version with max. T_m = 280 °C								
T _a 1) [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]		
40	80	95	130	195	280	-		
55	-	95	130	195	280	-		
60	_	_	130	195	280	_		

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a 1) [°C]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 ℃]	T2 [300°C]	T1 [450 °C]			
65	-	-	130	195	280 ²⁾	-			
70	-	-	130	-	-	-			

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0$ W

US units

Version with max. $T_m = 536 ^{\circ}F$										
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]				
104	176	203	266	383	536	-				
131	-	203	266	383	536	-				
140	-	_	266	383	536	-				
149	-	_	266	383	536 ²⁾	_				
158	-	-	266	-	-	-				

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6 \,^{\circ}F$
- 2) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0$ W

Order code for "Output", option D "4-20 mA HART, PFS output; 4-20 mA input" Order code for "Approval", all options

CCSA{US} IS, _CCSA_{US} XP, _CCSA_{US} NI

SI units

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$									
T _a 1) [°C]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 ℃]	T2 [300°C]	T1 [450 ℃]				
35	80	95	130	195	280	-				
50	-	95	130	195	280	-				
55	-	-	-	195	280	-				
60	-	-	-	195	-	-				

1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C

US units

Version with max. $T_m = 536 ^{\circ}F$										
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]				
95	176	203	266	383	536	-				
122	-	203	266	383	536	-				
131	-	-	-	383	536	-				
140	_	-	-	383	-	-				

The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 35.6$ °F

Order code for "Output", option E "FOUNDATION Fieldbus, pulse/frequency/switch output" and option G "PROFIBUS PA, pulse/frequency/switch output"

Order code for "Approval", all options cCSA_{US} IS, cCSA_{US} XP, cCSA_{US} NI

SI units

Version w	Version with max. $T_m = 280 ^{\circ}\text{C}$									
T _a 1) [°C]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200°C]	T2 [300°C]	T1 [450 ℃]				
40	80	95	130	195	280	-				
50 ²⁾	_	95	130	195	280	-				
60	_	_	130	195	280	_				
65	-	-	130	195	280 ³⁾	-				
70	_	-	130	195 ⁴⁾	280 4)	_				

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 60$ °C for pulse/frequency/switch output $P_i = 0$ W
- 3) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0$ W
- 4) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0$ W

US units

Version wit	Version with max. $T_m = 536 ^{\circ}F$										
T _a ¹⁾ [°F]	T _a 1) T6 T5 T4 T3 T2 °F] [185 °F] [212 °F] [275 °F] [392 °F] [572 °F]										
104	176	203	266	383	536	-					
122 ²⁾	-	203	266	383	536	-					
140	-	-	266	383	536	-					
149	-	-	266	383	536 ³⁾	-					
158	_	-	266	383 ⁴⁾	536 ⁴⁾	-					

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 140$ °F for pulse/frequency/switch output $P_i = 0$ W
- 3) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0$ W
- 4) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0$ W

Remote version

Transmitter

Order code for "Housing", option J "GT20 two-chamber, remote G314, aluminum coated"; option K "GT20 two-chamber, remote G315, 316L"

SI units

Order code for "Output", option	Order code for "Approval", option	T6 [85 °C]	T5 [100°C]	T4 [135 °C]
A	All	40	60	75
В	BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2	35 ¹⁾	50 ²⁾	70 ³⁾
	BC, BG, BK, B3, IC, IG, IK, I5, C3	40	55	70 ³⁾
С	All	40	55	70 ⁴⁾

Order code for "Output", option	Order code for "Approval", option	T6 [85 °C]	T5 [100 ℃]	T4 [135 °C]
D	All	35 ⁵⁾	50 ⁵⁾	65
E G	All	40	55	70 ⁴⁾

- 1) $T_a = 40 \,^{\circ}\text{C}$ for pulse/frequency/switch output $P_i = 0.85 \,^{\circ}\text{W}$
- 2) $T_a = 60 \,^{\circ}\text{C}$ for pulse/frequency/switch output $P_i = 0.85 \,^{\circ}\text{W}$
- 3) $T_a = 75$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 75$ °C for pulse/frequency/switch output $P_i = 0$ W
- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C

US units

Order code for "Output", option	Order code for "Approval", option	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]
А	All	104	140	167
В	BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2	95 ¹⁾	122 ²⁾	158 ³⁾
	BC, BG, BK, B3, IC, IG, IK, I5, C3	104	131	158 ³⁾
С	All	104	131	158 ⁴⁾
D	All	95 ⁵⁾	122 ⁵⁾	149
E G	All	104	131	158 ⁴⁾

- 1) $T_a = 104$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 2) $T_a = 140$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 167$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 167$ °F for pulse/frequency/switch output $P_i = 0$ W
- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F

Sensor

Order code for "Sensor version", option 4 "Volume flow Alloy 718"; option 6 "Mass flow Alloy 718"

SI units

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$									
T _a [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]				
55	80	95	130	195	280	-				
70	-	95	130	195	280	-				
85	_	_	130	195	280	-				

US units

Version with max. T_m = 536 $^{\circ}F$									
Ta T6 T5 T4 T3 T2 [°F] [185 °F] [212 °F] [275 °F] [392 °F] [572 °F]						T1 [842 °F]			
104	176	203	266	383	536	-			
122	_	203	266	383	536	-			
149	_	_	266	383	536	-			

Storage temperature

All components apart from the display modules:

-50 to +80 °C (-58 to +176 °F)

Display modules:

-40 to +80 °C (-40 to +176 °F)

Climate class

DIN EN 60068-2-38 (test Z/AD)

Degree of protection

Transmitter

- As standard: IP66/67, type 4X enclosure
- When housing is open: IP20, type 1 enclosure
- Display module: IP20, type 1 enclosure

Sensor

IP66/67, type 4X enclosure

Device plug

IP67, only in screwed situation

Vibration resistance

- For compact/remote version made of coated aluminum and remote version made of stainless steel: Acceleration up to 2q (if gain set to factory setting), 10 to 500 Hz, following IEC 60068-2-6
- For the compact version made of stainless steel:
 Acceleration up to 1q (if gain set to factory setting), 10 to 500 Hz, following IEC 60068-2-6

Electromagnetic compatibility (EMC)

As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)



For details refer to the Declaration of Conformity.

Process

Medium temperature range

DSC sensor 2)

Order code for "Sensor version":

- Option 4 "Volume flow, Alloy 718":
 - -40 to +400 °C (-40 to +752 °F)
- Option 6 "Mass flow, Alloy 718":
 -40 to +400 °C (-40 to +752 °F)

Seals

- -200 to +400 °C (-328 to +752 °F) for graphite (standard)
- -15 to +175 °C (+5 to +347 °F) for Viton
- -20 to +275 °C (-4 to +527 °F) for Kalrez
- $-200 \text{ to } +260 \,^{\circ}\text{C} \, (-328 \text{ to } +500 \,^{\circ}\text{F}) \text{ for Gylon}$


Pressure-temperature ratings

The following pressure-temperature ratings refer to the entire device and not just the process connection.

The pressure-temperature rating for the specific measuring device is programmed into the software. If values exceed the curve range a warning is displayed. Depending on the system configuration and sensor version, the pressure and temperature are determined by entering, reading in or calculating values.

2) Capacitance sensor

Process connection: flange to ASME B16.5 ed. 2009, Group 1.1 materials



■ 17 Process connection material: carbon steel, multiple certifications, SA-105, SA-350 LF2 (1)

NOTICE

If the device is used for a prolonged period at a temperature of over 375 °C, it is the responsibility of the owner-operator to perform additional tests. These can include:

▶ Dimensional tests to monitor deformation caused by corrosion or creepage.

Pressure loss

For a precise calculation, use the Applicator $(\rightarrow \triangleq 65)$.


Thermal insulation

For optimum temperature measurement and mass calculation, heat transfer at the sensor must be avoided for some fluids. This can be ensured by installing thermal insulation. A wide range of materials can be used for the required insulation.

This applies for:

- Compact version
- Remote sensor version

The maximum insulation height permitted is illustrated in the diagram:



A0019212

- 1 Maximum insulation height
- When insulating, ensure that a sufficiently large area of the housing support remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Vibrations

The correct operation of the measuring system is not affected by plant vibrations up to $1\,\mathrm{g}$, $10\,\mathrm{to}$ 500 Hz. Therefore no special measures are needed to secure the sensors.


Mechanical construction

Design, dimensions

Compact version

Order code for "Housing", option C "GT20, two-chamber, aluminum coated"

Flanged version



1 Optional inspection ports: order code for "Sensor option", option CR "ERCB Dir. 017 inspection ports"

Dimensions in SI units

DN	A	B 1)	С	D ²⁾	E	F 2)	G ³⁾	L
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
50	162	102	60	165	75	90	310	4)
80	162	102	60	165	75	90	321	4)
100	162	102	60	165	75	90	331	4)
150	162	102	60	165	75	90	352	4)

- 1) For version without local display: values 7 mm
- 2) For version with overvoltage protection: values + 8 mm
- 3) For version without local display: values 10 mm
- 4) dependent on respective process connection


Dimensions in US units

DN	A	B 1)	С	D ²⁾	E	F 2)	G 3)	L
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
2	6.38	4.02	2.36	6.50	2.95	3.54	12.4	4)
3	6.38	4.02	2.36	6.50	2.95	3.54	12.64	4)
4	6.38	4.02	2.36	6.50	2.95	3.54	13.03	4)
6	6.38	4.02	2.36	6.50	2.95	3.54	13.86	4)

- 1) For version without local display: values 0.28 in
- 2) For version with overvoltage protection: values \pm 0.31 in
- 3) For version without local display: values 0.39 in
- 4) dependent on respective process connection

Butt-weld version

Order code for "Process connection", option CAC "ASME Cl. 600/Sch.80 butt-weld"; option CAD "ASME Cl. 900/Sch.160 butt-weld";



■ 18 Engineering unit mm (in)

- Groove type as per ASME B31.3 Inspection ports

Dimensions in SI units

Cl. 600	Cl. 600/Sch. 80: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAC)													
DN	Α	B 1)	С	D ²⁾	E	F	G ³⁾	H ³⁾	L	K	M	di		
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]		
50	162	102	60	165	75	90	310	354	288	60	172	49.3		
80	162	102	60	165	75	90	321	378	325	88	200	73.7		
100	162	102	60	165	75	90	331	402	394	114	226	97.1		
150	162	102	60	165	75	90	352	450	566	168	280	146.3		

- 1)
- For version without local display: values 7 mm For version with overvoltage protection: values + 8 mm $\,$ 2)
- For version without local display: values 10 mm

Cl. 900	/Sch. 16	0: SA-10	06 Gr. B,	SA-333	Gr. 6 (01	der code	e for "Pr	ocess co	nection	", option	CAD)	
DN	Α	B 1)	С	D 2)	E	F	G ³⁾	H ³⁾	L	K	M	di
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
50	162	102	60	165	75	90	310	354	288	60	172	42.9
80	162	102	60	165	75	90	321	378	325	88	200	66.7
100	162	102	60	165	75	90	331	402	394	114	226	87.3
150	162	102	60	165	75	90	352	450	566	168	280	131.7

- For version without local display: values 7 mm 1)
- For version with overvoltage protection: values + 8 mm For version without local display: values 10 mm 2)
- 3)

Dimensions in US units

Cl. 600	Cl. 600/Sch. 80: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAC)												
DN	Α	B 1)	С	D 2)	Е	F	G ³⁾	H ³⁾	L	K	M	di	
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	
2	6.38	4.02	2.36	6.50	2.95	3.54	12.4	13.94	11.34	2.36	6.77	1.94	
3	6.38	4.02	2.36	6.50	2.95	3.54	12.64	14.88	12.8	3.46	7.87	2.9	
4	6.38	4.02	2.36	6.50	2.95	3.54	13.03	15.83	15.51	4.49	8.90	3.82	
6	6.38	4.02	2.36	6.50	2.95	3.54	13.86	17.72	22.28	6.61	11.02	5.76	


- 1)
- For version without local display: values 0.28 in For version with overvoltage protection: values + 0.31 in 2)
- 3) For version without local display: values - 0.39 in

Cl. 900	Cl. 900/Sch. 160: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAD)													
DN	A	B 1)	С	D ²⁾	E	F	G ³⁾	H ³⁾	L	K	M	di		
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]		
2	6.38	4.02	2.36	6.50	2.95	3.54	12.4	13.94	11.34	2.36	6.77	1.69		
3	6.38	4.02	2.36	6.50	2.95	3.54	12.64	14.88	12.8	3.46	7.87	2.63		
4	6.38	4.02	2.36	6.50	2.95	3.54	13.03	15.83	15.51	4.49	8.90	3.44		
6	6.38	4.02	2.36	6.50	2.95	3.54	13.86	17.72	22.28	6.61	11.02	5.19		

- 1)
- For version without local display: values 0.28 in For version with overvoltage protection: values + 0.31 in 2)
- For version without local display: values 0.39 in

Transmitter remote version

Order code for "Housing", option J "GT20, remote, aluminum coated"



Dimensions in SI units

A 1)	В	С	D ²⁾	E	F	G ³⁾	Н
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
162	90	191	165	75	90	254	107

- For device version without local display: value 7 mm
- For device version with overvoltage protection (OVP): value + 8 mm 2)
- For device version without local operation: value 10 mm

Dimensions in US units


A 1)	В	С	D 2)	E	F	G ³⁾	Н
[in]	[in]						
6.38	3.54	7.52	6.5	2.75	3.54	10.0	4.21

- For device version without local display: value 0.28 in
- 2) For device version with overvoltage protection (OVP): value + 0.31 in
- 3) For device version without local operation: value - 0.39 in

Sensor remote version

Order code for "Housing", option J "GT20, remote, aluminum coated"

Flanged version



A0020233

Optional inspection ports: order code for "Sensor option", option CR "ERCB Dir. 017 inspection ports"

Dimensions in SI units

DN	A	В	С	D	E	L
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
50	94.3	134.3	107.3	131	282	1)
80	94.3	134.3	107.3	131	293	1)

DN	A	В	С	D	E	L
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
100	94.3	134.3	107.3	131	303	1)
150	94.3	134.3	107.3	131	324	1)

1) dependent on respective process connection


Dimensions in US units

DN	A	В	С	D	E	L
[in]	[in]	[in]	[in]	[in]	[in]	[in]
2	3.71	5.29	4.22	5.16	11.1	1)
3	3.71	5.29	4.22	5.16	11.54	1)
4	3.71	5.29	4.22	5.16	11.93	1)
6	3.71	5.29	4.22	5.16	12.76	1)

1) dependent on respective process connection

Butt-weld version

 $\label{lem:code_code_constraint} Order\ code\ for\ "Process\ connection",\ option\ CAC\ "ASME\ Cl.\ 600/Sch.80\ butt-weld";\ option\ CAD\ "ASME\ Cl.\ 900/Sch.160\ butt-weld";$



■ 19 Engineering unit mm (in)

1 Groove type as per ASME B31.3

2 Inspection ports

Dimensions in SI units

Cl. 600/5	Cl. 600/Sch. 80: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAC)											
DN	Α	В	С	D	E	F	L	G	Н	di		
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]		
50	94.3	134.3	107.3	131	310	354	288	60	172	49.2		
80	94.3	134.3	107.3	131	321	378	325	88	200	73.7		

Cl. 600/	Cl. 600/Sch. 80: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAC)											
DN	A	В	С	D	E	F	L	G	Н	di		
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]		
100	94.3	134.3	107.3	131	331	402	394	114	226	97.0		
150	94.3	134.3	107.3	131	352	450	566	168	280	146.3		

Cl. 900/S	Cl. 900/Sch. 160: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAD)													
DN	A	В	С	D	E	F	L	G	Н	di				
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]				
50	94.3	134.3	107.3	131	310	354	288	60	172	42.9				
80	94.3	134.3	107.3	131	321	378	325	88	200	66.7				
100	94.3	134.3	107.3	131	331	402	394	114	226	87.3				
150	94.3	134.3	107.3	131	352	450	566	168	280	131.7				


Dimensions in US units

Cl. 600/	Cl. 600/Sch. 80: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAC)									
DN	A	В	С	D	E	F	L	G	Н	di
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
2	3.71	5.29	4.22	5.16	12.4	13.94	11.34	2.36	6.77	1.94
3	3.71	5.29	4.22	5.16	12.64	14.88	12.8	3.46	7.87	2.9
4	3.71	5.29	4.22	5.16	13.03	15.83	15.51	4.49	8.90	3.82
6	3.71	5.29	4.22	5.16	13.86	17.72	22.28	6.61	11.02	5.76

Cl. 900/	Cl. 900/Sch. 160: SA-106 Gr. B, SA-333 Gr. 6 (order code for "Process connection", option CAD)									
DN	A	В	С	D	E	F	L	G	Н	di
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
2	3.71	5.29	4.22	5.16	12.4	13.94	11.34	2.36	6.77	1.69
3	3.71	5.29	4.22	5.16	12.64	14.88	12.8	3.46	7.87	2.63
4	3.71	5.29	4.22	5.16	13.03	15.83	15.51	4.49	8.90	3.44
6	3.71	5.29	4.22	5.16	13.86	17.72	22.28	6.61	11.02	5.19

Process connections in SI units

Flange connections ASME B16.5



■ 20 Engineering unit mm (in)


Flange according to ASME B16.5, Cl. 600/Sch. 80: SA-105, SA-350 LF2 (1), (order code for "Process connection", option CAA) Surface roughness (flange): ASME B16.5, Ra 3.2 to 6.3 μm Α D Е L [mm] [mm] [mm] [mm] [mm] [mm] [mm] 50 165.1 127.0 8×19.0 49.2 305 33 80 209.6 168.3 8 × 22.2 39 73.7 325 273.0 97.0 100 215.9 8×23.4 49 363 150 355.6 292.1 12 × 28.6 64 146.3 393

	Flange according to ASME B16.5, Cl. 600/Sch. 160: SA-105, SA-350 LF2 (1), (order code for "Process connection", option CAE)							
Surface rough	ness (flange): A	ASME B16.5, Ra	3.2 to 6.3 µm					
DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]		
50	165.1	127.0	8 × 19.0	33	42.9	305		
80	209.6	168.3	8 × 22.2	39	66.7	325		
100	273.0	215.9	8 × 23.4	49	87.3	363		
150	355.6	292.1	12 × 28.6	64	131.7	393		

Flange according to ASME B16.5, Cl. 900/Sch. 160: SA-105, SA-350 LF2 (1), (order code for "Process connection", option CAB)							
Surface rough	ness (flange): A	ASME B16.5, Ra	3.2 to 6.3 μm				
DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]	
50	60.3	165.1	8 × 31.7	44.5	42.9	363	
80	88.94	190.5	8 × 31.7	44.5	66.7	363	
100	292.1	234.9	8 × 25.4	50.8	87.3	387	
150	381.0	317.5	12 × 25.4	62.0	131.7	439	

Process connections in US units

Flange connections ASME B16.5



■ 21 Engineering unit mm (in)

	Flange according to ASME B16.5, Cl. 600/Sch. 80: SA-105, SA-350 LF2 (1), (order code for "Process connection", option CAA)							
Surface rough	nness (flange): A	SME B16.5, Ra	125 to 250µin					
DN [in]	A [in]	B [in]	Ø C [in]	D [in]	E [in]	L [in]		
2	6.50	5	8 × 0.75	1.30	1.94	12.0		
3	8.26	6.63	8 × 0.87	1.54	2.90	12.8		
4	10.7	8.5	8 × 0.92	1.93	3.82	14.29		
6	14.01	11.5	12 × 1.13	2.52	5.76	15.47		

	Flange according to ASME B16.5, Cl. 600/Sch. 160: SA-105, SA-350 LF2 (1), (order code for "Process connection", option CAE)							
Surface rough	nness (flange): A	ASME B16.5, Ra	125 to 250µin					
DN [in]	A [in]	B [in]	ø C [in]	D [in]	E [in]	L [in]		
2	6.50	5	8 × 0.75	1.30	1.69	12.0		
3	8.26	6.63	8 × 0.87	1.54	2.63	12.8		
4	10.7	8.5	8 × 0.92	1.93	3.44	14.29		
6	14.01	11.5	12 × 1.13	2.52	5.19	15.47		

connection",	Flange according to ASME B16.5, Cl. 900/Sch. 160: SA-105, SA-350 LF2 (1), (order code for "Process connection", option CAB) Surface roughness (flange): ASME B16.5, Ra 125 to 250µin							
DN [in]	DN A B ØC D E L							
2	2.37	6.5	8 × 1.25	1.75	1.69	14.29		
3	3.5	7.5	8 × 1.25	1.75	2.63	14.29		
4	11.5	9.25	8 × 1	2	3.44	15.24		
6	15	12.5	12 × 1	2.44	5.19	17.28		

Weight

Compact version

Weight data:

- Including the transmitter:
 Order code for "Housing", option C: 1.8 kg (4.0 lb)
- Excluding packaging material

Weight in SI units

All values (weight) refer to devices with ASME B16.5/Class 900 flanges. Weight information in [kg].

DN	Weight [kg]
[mm]	Order code for "Housing", option C Aluminum, AlSi10Mg, coated
50	26.8
80	34.1
100	53.9
150	112.7

Weight in US units

All values (weight) refer to devices with ASME B16.5/Class 900 flanges. Weight information in [lbs].

DN	Weight [lbs]
[in]	Order code for "Housing", option C Aluminum, AlSi10Mg, coated
2	59.1
3	75.2
4	118.8
6	248.5

Transmitter remote version

Wall-mount housing

Depends on the material of the wall-mount housing:

- Aluminum, AlSi10Mg, coated: 2.4 kg (5.2 lb)
- Stainless steel, 1.4404 (316L): 6.0 kg (13.2 lb)

Sensor remote version

Weight data:

- Including the connection housing: Aluminum, AlSi10Mg, coated: 0.8 kg (1.8 lb)
- Excluding the connecting cable
- Excluding packaging material

Weight in SI units

All values (weight) refer to devices with ASME B16.5/Class 900 flanges. Weight information in [kg].

DN	Weight [kg]
[mm]	Connection housing Aluminum, AlSi10Mg, coated
50	25.7
80	33.1

DN	Weight [kg]
[mm]	Connection housing Aluminum, AlSi10Mg, coated
100	52.8
150	111.6

Weight in US units

All values (weight) refer to devices with ASME B16.5/Class 900 flanges. Weight information in [lbs].

DN	Weight [lbs]
[in]	Connection housing Aluminum, AlSi10Mg, coated
2	56.7
3	73.0
4	116.4
6	246.0

Materials

Transmitter housing


Compact version

Order code for "Housing", option ${\bf C}$ "Compact, aluminum coated": Aluminum, AlSi10Mg, coated

Remote version

Order code for "Housing", option \boldsymbol{J} "Remote, aluminum coated": Aluminum, AlSi10Mg, coated

Cable entries/cable glands



A0020640

■ 22 Possible cable entries/cable glands

- 1 Cable entry in transmitter housing, wall-mount housing or connection housing with internal thread M20 x 1.5
- 2 Cable gland M20 x 1.5
- 3 Adapter for cable entry with internal thread G ½" or NPT ½"

Order code for "Housing": option C "Compact, aluminum coated", option J "Remote, aluminum coated"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	Non-ExEx iaEx ic	Plastic
	Adapter for cable entry with internal thread G ½"	Nickel-plated brass

Cable entry/cable gland	Type of protection	Material
Adapter for cable entry with internal thread NPT ½"	For non-Ex and Ex (except for CSA Ex d/XP)	Nickel-plated brass
Thread NPT ½" via adapter	For non-Ex and Ex	

Connecting cable for remote version

- Standard cable: PVC cable with copper shield
- Reinforced cable: PVC cable with copper shield and additional steel wire braided jacket

Sensor connection housing

Coated aluminum AlSi10Mg

Measuring tubes

Pressure ratings Class 600 to 900

Carbon steel, multiple certifications, SA-106 Grade B, SA-333 Grade 6

Bluff body

Carbon steel, multiple certifications, SA-105, SA-350 LF2 (1)

Inspection ports

Carbon steel, multiple certifications, SA-105, SA-350 LF2 (1)

DSC sensor

- Parts in contact with medium (marked as "wet" on the DSC sensor flange): UNS N07718 similar to Alloy 718/2.4668
- Parts not in contact with medium: Stainless steel 1.4301 (304)

Process connections

ASME B16.5

Carbon steel, multiple certifications, SA-105, SA-350 LF2 (1)



List of all available process connections ($\rightarrow \triangleq 56$)

Seals

- Graphite (standard)
- FPM (Viton) 3)
- Kalrez 6375³⁾
- Gylon 3504 (BAM-certified for oxygen applications, "high quality in terms of TA Luft (German Clean Air Act"))

Housing support

Stainless steel, 304

Accessories

Weather protection cover

Stainless steel 1.4404 (316L)

Process connections

ASME B16.5



For information on the materials of the process connections ($\Rightarrow \triangleq 56$)

³⁾ Only available for the DSC sensor, not for inspection ports.

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

Quick and safe commissioning

- Guided menus ("Make-it-run" wizards) for applications
- Menu guidance with brief explanations of the individual parameter functions

Reliable operation


- Operation in the following languages:
 - Via local display:
 - English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Swedish, Turkish, Chinese, Japanese, Korean, Bahasa (Indonesian), Vietnamese, Czech
 - Via "FieldCare" operating tool:
 English, German, French, Spanish, Italian, Chinese, Japanese
- Uniform operating philosophy applied to device and operating tools
- If replacing the electronic module, transfer the device configuration via the integrated memory (integrated HistoROM) which contains the process and measuring device data and the event logbook. No need to reconfigure.

Efficient diagnostics increase measurement availability

- Troubleshooting measures can be called up via the device and in the operating tools
- Diverse simulation options, logbook for events that occur and optional line recorder functions

Local operation

Via display module



Display elements

- 4-line display
- With order code for "Display; operation", option E:
 White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
 The readability of the display may be impaired at temperatures outside the temperature range.


Operating elements

- With order code for "Display; operation", option **C**: Local operation with 3 push buttons: [①], [①], [⑥]
- With order code for "Display; operation", option **E**: External operation via touch control; 3 optical keys: ③, ⑤, ⑤
- Operating elements also accessible in various hazardous areas

Additional functionality

- Data backup function
 - The device configuration can be saved in the display module.
- Data comparison function The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function
- The transmitter configuration can be transmitted to another device using the display module.

Via remote display and operating module FHX50




23 Operating options via FHX50

- Housing of remote display and operating module FHX50
- SD02 display and operating module, push buttons: cover must be opened for operation
- SD03 display and operating module, optical buttons: operation possible through cover glass

Remote operation

Via HART protocol




€ 24 Options for remote operation via HART protocol

- Control system (e.g. PLC) 1
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- Connection for Commubox FXA195 and Field Communicator 475 3
- 4 Field Communicator 475
- Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM) 5
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 VIATOR Bluetooth modem with connecting cable
- Transmitter

Via FOUNDATION Fieldbus network

This communication interface is present in the following device version: Order code for "Output", option E: FOUNDATION Fieldbus




A0023460

- Automation system
- Computer with FOUNDATION Fieldbus network card 2
- 3 Industry network
- High Speed Ethernet FF-HSE network Segment coupler FF-HSE/FF-H1
- FOUNDATION Fieldbus FF-H1 network
- Power supply FF-H1 network
- 8 T-box
- Measuring device

Via PROFIBUS PA network


This communication interface is present in the following device version: Order code for "Output", option **G**: PROFIBUS PA



- Automation system
- Segment coupler PROFIBUS DP/PA
- 2 3 Computer with PROFIBUS network card
- PROFIBUS DP network
- PROFIBUS PA network
- 6 Measuring device
- T-box

Service interface

Service interface (CDI)



A0020545

- 1 Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring device
- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

Certificates and approvals

C-Tick symbol

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

cCSAus

Currently, the following versions for use in hazardous areas are available:

ХP

Category	Type of protection	
Class I, II, III Division 1 Groups A-G	XP (Ex d Flameproof version)	

IS

Category	Type of protection	
Class I, II, III Division 1 Groups A-G	IS (Ex i Intrinsically safe version)	

NI

Category	Type of protection	
Class I Division 2 Groups ABCD	NI (Non-incentive version), NIFW-Parameter*	

^{*=} Entity- und NIFW-Parameter gemäß Control Drawings

60

Functional safety

The measuring device can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture) and SIL 3 (multichannel architecture with homogeneous redundancy) and is independently evaluated and certified by the TÜV in accordance with IEC 61508.

The following types of monitoring in safety equipment are possible: Volume flow



Functional Safety Manual with information on the SIL device ($\rightarrow \triangleq 66$)

FOUNDATION Fieldbus certification

FOUNDATION Fieldbus interface

The measuring device is certified and registered by the Fieldbus FOUNDATION. The measuring system meets all the requirements of the following specifications:

- Certified in accordance with FOUNDATION Fieldbus H1
- Interoperability Test Kit (ITK), revision version 6.1.1 (certificate available on request)
- Physical Layer Conformance Test
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with PROFIBUS PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

Experience

The Prowirl 200 measuring system is the official successor to Prowirl 72 and Prowirl 73.

Other standards and guidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ DIN ISO 13359

Measurement of conductive liquid flow in closed conduits - Flanged-type electromagnetic flowmeters - Overall length

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use

IEC/EN 61326

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

■ NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

■ NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

■ ASME BPVC Section VIII, Division 1

Rules for Construction of Pressure Vessels

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser web site: www.endress.com → Choose your $country \rightarrow Products \rightarrow Select\ measuring\ technology,\ software\ or\ components \rightarrow Select\ product$ (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product \rightarrow The Product Configurator for the selected product is opened.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered from Endress+Hauser either directly with the device or subsequently. Detailed information on the order code in question is available from your local Endress +Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.



Detailed information on the application packages: Special Documentation on the device $(\rightarrow \triangleq 67)$

Diagnostics functions

Package	Description	
HistoROM extended function	Comprises extended functions concerning the event log and the activation of the measured value memory.	
	Event log: Memory volume is extended from 20 message entries (basic version) to up to 100 entries.	
	 Data logging (line recorder): Memory capacity for up to 1000 measured values is activated. 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Data logging is visualized via the local display or FieldCare. 	

Heartbeat Technology

Package	Description
Heartbeat Verification	Heartbeat Verification: Makes it possible to check the device functionality on demand when the device is installed, without having to interrupt the process. Access via onsite operation or other operating interfaces, such as FieldCare for instance. Documentation of device functionality within the framework of manufacturer specifications, for proof testing for instance. End-to-end, traceable documentation of the verification results, including report. Makes it possible to extend calibration intervals in accordance with operator's risk assessment.

Air and industrial gases	Package	Description
	Air and industrial gases	This application package enables users to calculate the density and energy of air and industrial gases. The calculations are based on time-tested standard calculation methods. It is possible to automatically compensate for the effect of pressure and temperature via an external or constant value.
		With this application package it is possible to output the energy flow, standard volume flow and mass flow of the following fluids: Air Single gas
		Gas mixtureUser-specific gas

N	at	ural	a	as

Package	Description
Natural gas	This application package enables users to calculate the chemical properties (gross calorific value, net calorific value) of natural gases. The calculations are based on time-tested standard calculation methods. It is possible to automatically compensate for the effect of pressure and temperature via an external or constant value. With this application package it is possible to output the energy flow, standard volume flow and mass flow based on the following standard methods:
	Energy can be calculated based on the following standards: • AGA5 • ISO 6976 • GPA 2172
	Density can be calculated based on the following standards: ISO 12213-2 (AGA8-DC92) ISO 12213-3 AGA NX19 AGA8 Gross 1 SGERG 88

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the transmitter

Accessories	Description
Prowirl 200 transmitter	Transmitter for replacement or for stock. Use the order code to define the following specifications: Approvals Output Display / operation Housing Software For details, see Installation Instructions EA01056D

Remote display	FHX50 housing to accommodate a display module (→ 🗎 58).
FHX50	 FHX50 housing suitable for: SD02 display module (push buttons) SD03 display module (touch control) Housing material: Plastic PBT 316L Length of connecting cable: up to max. 60 m (196 ft) (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft))
	The measuring device can be ordered with the FHX50 housing and a display module. The following options must be selected in the separate order codes: Order code for measuring device, feature 030: Option L or M "Prepared for FHX50 display" Order code for FHX50 housing, feature 050 (device version): Option A "Prepared for FHX50 display" Order code for FHX50 housing, depends on the desired display module in feature 020 (display, operation): Option C: for an SD02 display module (push buttons) Option E: for an SD03 display module (touch control)
	The FHX50 housing can also be ordered as a retrofit kit. The measuring device display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing: Feature 050 (measuring device version): option B "Not prepared for FHX50 display" Feature 020 (display, operation): option A "None, existing displayed used" For details, see Special Documentation SD01007F
Overvoltage protection for 2-wire devices	Ideally, the overvoltage protection module should be ordered directly with the device. See product structure, characteristic 610 "Accessory mounted", option NA "Overvoltage protection". Separate order necessary only if retrofitting.
	 OVP10: For 1-channel devices (characteristic 020, option A): OVP20: For 2-channel devices (characteristic 020, options B, C, E or G) For details, see Special Documentation SD01090F.
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight or extreme cold in winter. For details, see Special Documentation SD00333F
Connecting cable for remote version	 Connecting cable available in various lengths: 5 m (16 ft) 10 m (32 ft) 20 m (65 ft) 30 m (98 ft) Reinforced cables available on request. Standard length: 5 m (16 ft)
Post mounting kit	Is always supplied if no other cable length has been ordered. Post mounting kit for transmitter. The post mounting kit can only be ordered together with a transmitter.

For the sensor

Accessories	Description
Inspection kit	The inspection kit comprises: 2 inspection centering sleeves 8 screws 2 inspection seals 2 inspection covers For details, see Installation Instructions EA01058D

Communication-specific accessories

Accessories	Description	
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F	
Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see the "Technical Information" document TI405C/07	
HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions BA00371F	
Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity.	
	For details, see Operating Instructions BA00061S	
Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00053S	
Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions	
	BA00051S	
Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area .	
	For details, see Operating Instructions BA01202S	
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area and the Ex area .	
	For details, see Operating Instructions BA01202S	

Service-specific accessories

Accessories	Description
Applicator	Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections. Graphic illustration of the calculation results
	Administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.
	Applicator is available: Via the Internet: https://wapps.endress.com/applicator On CD-ROM for local PC installation.

W@M	Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records. W@M is available: Via the Internet: www.endress.com/lifecyclemanagement On CD-ROM for local PC installation.
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.
	For details, see Operating Instructions BA00027S and BA00059S

System components

Accessories	Description		
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.		
	For details, see "Technical Information" TI00133R and Operating Instructions BA00247R		
RN221N	Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission.		
	For details, see "Technical Information" TI00073R and Operating Instructions BA00202R		
RNS221	Supply unit for powering two 2-wire measuring devices solely in the non-Ex area. Bidirectional communication is possible via the HART communication jacks.		
	For details, see "Technical Information" TI00081R and Brief Operating Instructions KA00110R		
Cerabar M	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.		
	For details, see "Technical Information" TI00426P, TI00436P and Operating Instructions BA00200P, BA00382P		
Cerabar S	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.		
	For details, see "Technical Information" TI00383P and Operating Instructions BA00271P		

Documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- The CD-ROM provided for the device (depending on the device version, the CD-ROM might not be part of the delivery!)
- The *W@M Device Viewer*: Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

Brief Operating Instructions

Measuring device	Documentation code
Prowirl C 200	KA01134D

Operating Instructions

Measuring device	Documentation code		
	HART	FOUNDATION Fieldbus	PROFIBUS PA
Prowirl C 200	BA01152D	BA01215D	BA01220D

Supplementary devicedependent documentation

Safety Instructions

Contents	Documentation code	
_C CSA _{US} XP	XA01153D	
_C CSA _{US} IS	XA01154D	

Special Documentation

Contents	Documentation code
Functional Safety Manual	SD01162D
Heartbeat Technology	SD01204D
Natural gas	SD01194D
Air + Industrial Gases (Single Gas + Gas Mixtures)	SD01195D
ERCB Dir. 017	SD01213D

Installation Instructions

Contents	Documentation code
Installation Instructions for spare part sets	Specified for each individual accessory (→ 🖺 63)

Registered trademarks

HART®

Registered trademark of the HART Communication Foundation, Austin, USA

PROFIBUS®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

$FOUNDATION^{TM}\ Fieldbus$

Registration-pending trademark of the Fieldbus Foundation, Austin, Texas, USA

KALREZ®, VITON®

Registered trademarks of DuPont Performance Elastomers L.L.C., Wilmington, DE USA

GYLON⁰

Registered trademark of Garlock Sealing Technologies, Palmyar, NY, USA

Applicator®, FieldCare®, Field XpertTM, HistoROM®, Heartbeat TechnologyTM Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

