

















Technical Information

Tankvision NXA820, NXA821, NXA822

Inventory Management System with completely integrated software for operation via standard web browser







Application

Tankvision is a dedicated tank inventory system which is operated by a standard web browser and does not require proprietary software or licensing costs.

Tankvision is based on a distributed architecture on a Local Area Network (LAN). Due to its modular structure it can be adjusted to any application. It is ideally suited for small tank farms with only a couple of tanks, but also for large refineries with hundreds of tanks.

Tankvision consists of the following components:

- Tankvision NXA820 (Tank Scanner) scans parameters from tank gauges and performs tank calculations
- Tankvision NXA821 (Data Concentrator) summarizes data from various Tank Scanners NXA820
- Tankvision NXA822 (Host Link)
 provides data to host systems (such as PLC or DCS) via
 Modbus

Your benefits

- License-free
- Approved for custody transfer applications according to NMI and PTB (in preparation)
- Global system engineering and service support
- A robust industrial operating system with embedded software ensures high stability and availability.
- Modular design; easily adjustable to any application; can be upgraded as required
- Configuration, commissioning and operation via web browser; no proprietary software required
- Access for up to 10 users per Tankvision component from any connected PC
- Common hardware platform for all components; no hard disc or fans no wearout
- Volume calculations and correction included according to international standards (API/ASTM/IP tables) in Tank Scanner NXA820
- Predefined or customized operator screens for typical operation of a tank farm



Table of Contents

Inventory control
Inventory calculations
Remote configuration of measuring equipment $\dots 3$
Application areas
Function and system design4
System design
System configuration
Features
Typical system configurations
Tankvision NXA820 (Tank Scanner)
Function
Number of tanks
LAN connections
Input NXA820
Output NXA820
Power supply NXA820
Terminals NXA820
Ambient conditions NXA820
Mechanical construction
Human interface
Certificates and approvals
Ordering information NXA820
Ordering iniormation NAAOZO
Tankvision NXA821 (Data Concentrator) 19
Function
Number of tanks
LAN connections
Output NXA821
Power supply
Terminals NXA821
Ambient conditions
Mechanical construction
Human interface
Human interface
Certificates and approvals
Certificates and approvals
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27
Certificates and approvals
Certificates and approvals24Ordering information NXA82125Tankvision NXA822 (Host Link)27Function27Number of tanks27
Certificates and approvals24Ordering information NXA82125Tankvision NXA822 (Host Link)27Function27Number of tanks27LAN connections27
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28
Certificates and approvals24Ordering information NXA82125Tankvision NXA822 (Host Link)27Function27Number of tanks27LAN connections27Output NXA82227Power supply28Terminals NXA82228Ambient conditions34
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35 Certificates and approvals 35
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35 Certificates and approvals 35 Ordering information NXA822 36
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35 Certificates and approvals 35 Ordering information NXA822 36 Human interface 37
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35 Certificates and approvals 35 Ordering information NXA822 36 Human interface 37 Operating concept 37
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35 Certificates and approvals 35 Ordering information NXA822 36 Human interface 37 Operating concept 37 Languages 37
Certificates and approvals 24 Ordering information NXA821 25 Tankvision NXA822 (Host Link) 27 Function 27 Number of tanks 27 LAN connections 27 Output NXA822 27 Power supply 28 Terminals NXA822 28 Ambient conditions 34 Mechanical construction 34 Human interface 35 Certificates and approvals 35 Ordering information NXA822 36 Human interface 37 Operating concept 37

Examples o	f operating p	pages			38
Suppleme	entary doc	cumentat	ion	• • • • • •	40
Operating I	nstructions				40
-			ns		
Trademai	rks				40
MODBUS					40
Windows .					40
Java					40
					41

Applications

Inventory control

By using Tankvision to monitor the tank level and stored volume of valuable liquids remotely, owners or operators of tank farms or terminals for petroleum products and chemicals (liquids) can visualize the volume of the stored medium in real time. The data can be used to plan the inventory and distribution. The data can also be used to manage tank farm operations like pumping or transferring products.

Tankvision has its unique concept using network technology. Without using proprietary software, the users can visualize and manage their valuable liquids stored in the tanks by a web browser.

Tankvision is a flexible and cost effective solution due to its scalable architecture. The application coverage goes from small depots with only a few tanks up to refineries.

Inventory calculations

Tankvision calculates gross, net volumes and mass, based on measured variables and tank capacity tables. Volumes and density of products like hydrocarbons, LPG's, asphalt are corrected according to international standards, including API/ASTM tables 5A, 5B/6, 53A, 53B/54, 23/24, LPG. This includes temperature corrections at 15C, 60F and alternative temperatures. Additionally, available pumpable volumes and water volume are calculated. Up to 3000 strapping points per tank are supported for vertical, spherical and bullet tanks.

Remote configuration of measuring equipment

Tankvision does not only acquire the current measured level or volume from the tanks. The configuration of device settings from the control room is also possible by using the corresponding HART operating software from Endress+Hauser (e.g. ToF Tool or FieldCare) for the connected Endress+Hauser devices. Tankvision passes on the device setting information transparently, so that all device functions for the respective operating software are available from the control room. Some on-site operations can be avoided using this feature during commissioning or maintenance. (The availability of this feature may depend on the system configuration.)

Application areas

- tank farms in refineries
- ship loading terminals
- marketing and distribution terminals
- pipeline terminals
- logistic terminals for tanks storing products like crude oils, refined white and black products, chemicals, LPGs

Function and system design

System design

Tank management visualization without proprietary software

Tankvision is the first tank management visualization system providing its functionality without the need to have proprietary software installed and maintained on a PC. The main functionality is realized by embedded web pages in the Tankvision components. Tankvision uses an industrial proven operating system and provides high availability. Tankvision is not based on a PC platform and runs independent of connected PCs. This eliminates the need to maintain a specialized PC with a Windows operating system and necessary updates and hot fixes. Tankvision web pages can be accessed from a standard PC with a web browser and the Java Runtime Environment only. Multiple users with different roles can simultaneously log in to each Tankvision component. Additional users can be added as required. There are no multi-user licence fees.

Distributed architecture and scalability

Tankvision is based on a distributed architecture on a Local Area Network (LAN). Coordinated components perform all inventory management tasks. The modular design makes it easy to enlarge the system whenever required and to add further tank areas.

Thus, Tankvision is fully scalable and is ideally suited for applications of any size – from small tank farms to large refineries.

Common hardware platform

The Tankvision components have dedicated tasks in a system, but have a common architecture, based on a 32 Bit processor. The embedded tank management software uses a multi-threaded real time operating system (RTOS), specifically designed for industrial applications. The hardware is designed without wear-out components like hard discs or fans. This guarantees high reliability.

System configuration

Configuration of the components

Each Tankvision component has its own data base and a web server. The components are connected and exchange data with time stamp and status information. Data is optionally encrypted and secured by a CRC checksum.

The Tankvision components are configured with static IP addresses, which are reserved on a DHCP network. The configuration pages are embedded in the Tankvision components and allow configuration of Tankvision via a connected web browser without configuration software. No Internet access is necessary, as all pages are loaded from the Tankvision system itself.

Configuration of the connected tank gauges/sensors (available for Windows XP SP1; in preparation for Windows XP SP2)

Tankvision supports connection of Endress+Hauser configuration tools (e.g. ToF Tool or FieldCare) via LAN. This enables configuration of the tank gauges if they support remote configuration (e.g. Tank Side Monitor NRF590 and the level radars Micropilot S FMR53x/FMR54x).

The tank gauges must be connected to the Tank Scanner NXA820 in one of the following ways:

- via a field protocol
- via HART to the Tank Side Monitor NRF590 (version 02.04) which in turn is connected via one of the following protocols to the Tank Scanner NXA820:
 - MODBUS
 - Sakura V1
 - Whessoematic WM550 (in preparation)

Features

■ Representation of tank data

Tank data can be represented graphically or in tables. The corresponding HTML pages are predefined.

■ Definition and management of tank groups

The total contents of static or dynamic tank groups (e.g. of tanks containing the same product) can be displayed.

■ Definition and management of products

Product characteristics can be defined. The defined product can be attributed to a number of tanks. Links to product safety sheets can be integrated.

■ Trend display

Real time and historical trends of the tank parameters can be displayed. The data is stored in the internal memory.

■ Archive

Tankvision stores measured and calculated data, log files and alarms on the internal flash memory.

■ Alarms

Limit alarms (high-high, high, low, low, low) can be defined for measured and calculated tank parameters. An alarm bar visualizes alarms in the browser window.

Alarms can be reported by an optional Alarm Popup¹⁾ window.

■ Products

A product database allows definition of 250 products per NXA or shared in the system.

Monitoring of transfers

Product transfers from and to tanks can be monitored. Pre-alarms can be generated before completion of the transfer. A report is issued after the transfer.

Auditing

An auditing table contains all events such as alarms or configuration changes.

■ Log-In roles

Log-In roles with different access rights (supervisor, operator, guest) can be assigned to users and user groups.

■ Reports

Reports are predefined as HTML pages. They can be sent to a printer connected to a computer at scheduled time intervals by an optional Printer Agent¹.

■ Volume calculation and correction

Available calculation tables according to API, ASTM and IP can be integrated.

Graphical User Interface (GUI)

Tankvision uses an intuitive and optimized user interface (e.g. automatic creation of dynamic tank groups).

■ Remote access


Any PC with the specified requirements which is connected to the Intranet can be connected with Tankvision.

■ Redundancy (in preparation)


Two Tankvision components of the same type can be interconnected via the SyncLink interface. Only the primary NXA has to be configured. The secondary NXA takes over the task if the master fails (see diagram on page 6).

¹⁾ available for Windows on the device to upload; other operating systems in preparation

Typical system configurations Small tank farm (up to 15 tanks)



Refinery (up to 225 tanks)



6

Tankvision NXA820 (Tank Scanner)

Function

- The Tank Scanner NXA820 connects multiple tank gauges from up to 15 tanks via one field-loop. The Tank Scanner NXA820 supports different field protocols (Modbus EIA485, Sakura V1, Whessoematic WM550).
- The measured values are transmitted by the network and visualized on HTML pages.
- The Tank Scanner NXA820 can be used stand-alone for small tank farms, but also be integrated into a large system for use in refineries.
- The Tank Scanner NXA820 is equipped with a full set of tank inventory calculations. The calculations are based on various international standards such as API, ASTM, IP and many others. Measured values are used to calculate volume and mass.

Number of tanks

Protocol	max. number of tanks per NXA820
MODBUS EIA485	15
Sakura V1	10
Whessoematic WM550 (in preparation)	15

LAN connections

System LAN port

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector Connects the NXA820 Tank Scanner to the Local Area Network (LAN)

Sync-Link LAN port (in preparation)

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector

Connects the NXA820 Tank Scanner (e.g. primary) to an optional redundant unit (e.g secondary), to make sure the two devices remain synchronized with each other. If the primary unit fails, the secondary NXA820 Tank Scanner takes over operation without system interruption (see diagram on page 6).

Service LAN port

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector

Connects the NXA820 Tank Scanner to a local computer **only** for local commissioning and service operations. The computer does not become part of the local area network the NXA820 Tank Scanner is connected to through the System LAN port.

This port has a fixed IP address and can also provide the connected computer automatically with a compatible IP address using a DHCP server built into the NXA820 Tank Scanner. For this automatic IP function to work the computer must be set to obtain its IP address using a DHCP server



Note!

All LAN ports support Auto-MDIX. This system automatically detects the type of cable connected (either straight or crossed) and adjusts itself to match. With this feature you do not need to obtain special crossed cables to interconnect Tankvision components.

Input NXA820

Fieldbus protocols

The Tank Scanner NXA820 is available with the following field protocols:

- MODBUS EIA485 master, max. 15 gauges
- Sakura V1, max. 10 gauges
- Whessoematic 550, max. 15 gauges (in preparation)

Output NXA820

NXA Status Relay

- potential free relay, SPDT
- normally-closed when NXA is operating normally, open when NXA is powered off or in fault status
- switching power:
 - 25 V_{DC}, 100 W
 - 250 V_{AC}, 4 A, 1000VA

Power supply NXA820


Instrument version	Supply voltage	Power consumption	Current consumption	Fuse
AC voltage NXA820 - ##1#######	90 - 250 V _{AC} (50/60Hz)	max. 23 VA	max. 100 mA at 230 VAC	400 mA T
DC voltage NXA820 - ##2########	10.5 - 32 V _{DC}	max. 14 W	max. 580 mA at 24 VDC	2 A T

Galvanic isolation

The following terminals are galvanically isolated from each other:
■ Alarm relay output
■ LAN interfaces

- Fieldbus interface

Terminals NXA820



A: Power supply; B: Fuse; C: Status relay; D: Fieldbus connection; E: Ground; F: System LAN port; G: Sync Link LAN port; H: Service LAN port; I: Endress+Hauser CDI port; J: Display port; K: USB port; L: Weights & Measures locking switch

Power supply (AC version)

Terminal	Meaning	Remarks
1	L	
2	N	90 - 250 V _{AC} Connector: Phoenix 7.62 GMSTB/GFKC
3	Potential equalization	
-	Fuse	400 mA T

Power supply (DC version)

Terminal	Meaning	Remarks
1	L+	
2	L-	10.5 - 32V _{DC} Connector: Phoenix 7.62 GMSTB/GFKC
3	Potential equalization	
-	Fuse	2 A T

Status Relay

Terminal	Meaning	Remarks
6	normally open contact	■ NXA operating normally:
7	normally closed contact	terminals 7 & 8 are interconnected NXA powered off or fault status condition:
8	switching contact	terminals 6 & 8 are interconnected

Connector: Phoenix FKC 2,5HC/3-St-5,08



Note!

The depicted switching state of the relay refers to the de-energized state.

Field connection: MODBUS Serial, EIA/TIA-485 (RS485)

Terminal	EIA/TIA-485 MODBUS	Meaning	Remarks
13	S	Capacitive Shield	
12	С	Signal Common	Connector: Phoenix FKIC 2.5/4-St-5,08
11	В	+ signal	Confidence: Filoenix FRIC 2,37 4-3(-3,00
10	A	- signal	
<u></u>	Ground		Must be independently connected directly to a primary grounding point using $4\ \mathrm{mm^2}$ cable.

Two-Wire MODBUS Definition

As described in the "MODBUS over serial line specification and implementation guide V1.02" published by the Modbus-IDA organisation (www.modbus.org) and based upon the EIA/TIA-485-A physical layer specification. MODBUS two-wire serial requires the following four electrical connections between each of the devices on the bus:

Signal	Purpose	Remarks
A	Data signal (-)	These signals must be connected using a balanced twisted pair cable.
В	Data signal (+)	
С	Signal Common	Must interconnect all devices on the bus.
Shield	EMC Protection	Copper braided or combined foil and braided shielding.

Additional EIA/TIA-485 bus settings

- Bus biasing resistors (must be present at one point on the bus) (always enabled inside NXA820)
- Bus termination resistor (must be present at each end of the bus) (software selectable inside NXA820)

MODBUS Cable Specification

Characteristic impedance	135 to 165 Ω at measuring frequency of 3 to 20 MHz
Cable capacitance	≤ 30 pF/m
Core cross-section	\geq 0.34 mm ² , corresponds to AWG 22, multi-strand cable is preferred
Cable type	Single twisted pair + third conductor (for common) or Dual twisted pair (common uses second pair with wire joined together)
Cable resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shielding	Copper braided shielding or combined foil and braided shielding

Field connection: V1

Terminal	V1	Meaning	Remarks
13	S	Capacitive Shield	
12		Not connected	Connector: Phoenix FKIC 2,5/4-St-5,08
11	A	- signal	Connector. Phoenix PKIC 2,37 4-31-3,00
10	В	+ signal	
=	Ground		Must be independently connected directly to a primary grounding point using 4 mm ² cable.

V1 Definition

V1 fieldbus is a voltage mode digital communication using up to $\pm 30~V_{DC}$, and requires the following three electrical connections between each of the devices on the bus:

Signal	Purpose	Remarks
A	Data signal (-)	These signals must be connected using a balanced twisted pair cable.
В	Data signal (+)	
Shield	EMC protection	Copper braided or combined foil and braided shielding

V1 Cable specification

Cable capacitance	≤ 50 nF/m
Core cross-section	\geq 0.9 mm ² , corresponds to AWG 17, multi-strand cable is preferred
Cable type	twisted pair
Cable resistance	≤ 30 Ω/km
Shielding	Copper braided shielding or combined foil and braided shielding
Insulation	≥ 60 V _{DC}

Field connection: Whessoematic 550 (WM550) (in preparation)

Terminal	WM550	Meaning	Remarks
13		Not connected	
12		Not connected	Connector: Phoenix FKIC 2,5/4-St-5,08
11	+	Loop Send	Connector. Price Pix Px C 2,37 4-31-3,00
10	-	Loop Return	
=	Ground		Must be independently connected directly to a primary grounding point using 4 mm ² cable.

WM550 Definition

WM550 fieldbus consists of a current loop which passes from the source device (e.g. NXA820) through all connected gauges before returning to the source device. Typically this is managed by a single multi-core cable which holds both the outgoing and returning current loop, and requires the following two electrical connections between each of the devices on the bus:

Signal	Purpose	Remarks
+	Current Loop (+)	Current always flows from positive to negative within the loop.
-	Current Loop (-)	



Caution!

WM550 loop signal voltages can be as high as 100 $\ensuremath{V_{DC}}\xspace$

WM550 Cable specification

Cable capacitance	≤ 75 nF/m
Core cross-section	\geq 0.5 mm ² , corresponds to AWG 20, multi-strand cable is preferred
Cable type	twisted pair
Cable resistance	\leq 40 Ω /km (total loop resistance \leq 250 Ω)
Shielding	None
Insulation	\geq 100 V _{DC}

Shielding and Grounding

When planning the shielding and grounding for a fieldbus system, there are three important points to consider:

- Electromagnetic compatibility (EMC)
- Explosion protection
- Safety of the personnel

To ensure the optimum electromagnetic compatibility of systems, it is important that the system components and above all cables, which connect the components, are shielded and that no portion of the system is unshielded. Ideally, the cable shields are connected to the normally metal housings of the connected field devices. Since these are generally connected to the protective earth, the shield of the bus cable is grounded many times. Keep the stripped and twisted lengths of cable shield to the terminals as short as possible. This approach, which provides the best electromagnetic compatibility and personnel safety, can be used without restriction in systems with good potential equalization.

In the case of systems without potential equalization, a power supply frequency (50/60 Hz) equalizing current can flow between two grounding points which, in unfavourable cases, e.g. when it exceeds the permissible shield current, may destroy the cable.

To suppress the low frequency equalizing currents on systems without potential equalization, it is therefore recommended to connect the cable shield directly to the building ground (or protective earth) at one end only and to use capacitive coupling to connect all other grounding points.

The NXA820 provides two grounding points for the shield, close to the fieldbus interface connector:

- The "\(\perp \)" terminal, which should already be connected directly to ground
- The "S" terminal (13), which provides capacitive connection to the " $\stackrel{\perp}{=}$ " terminal



Caution!

The legal EMC requirements are fulfilled only when the cable shield is grounded on both sides!

LAN connection

Socket	Meaning	Remarks
器	System LAN port	Connects the instrument to the network.
<u> </u>	Sync Link LAN port (in preparation)	Used for connection to redundant unit. If the primary unit fails, its task is taken over by the redundant unit.
4	Service LAN port	Connects the instrument to a computer locally for service purpose. Only this instrument can be configured. The Service LAN port does not allow access to the network.

LEDs

Symbol	Color	Meaning
0	Green	Power On
(1)	Yellow	Stand-by Indicates the box is a redundant secondary unit, and is ready to take over if the primary unit fails.
4	Red	Fault Indicates a Fault when lit or "Maintenance required" when flashing
\$	Yellow	Communication Flashes when the NXA820 Tank Scanner completes a successful fieldbus communication cycle (e.g. Sent a request and received a reply).
⇒	Yellow	Fieldbus Rx Flashes to indicate data bits are being received from the connected field devices.
♦	Yellow	Fieldbus Tx Flashes to indicate data bits are being sent to the connected field devices.
\leftrightarrow		Data Transfer
·	Green	Indicates data is being transferred on the LAN interface.
	Yellow	Indicates data is being transferred on the USB interface.
○ —○	Green	Linked
● √ [*]	Yellow	USB active (for future enhancements) When lit the connected USB device has been detected and is in use. Do not remove the device while this LED is lit.
Y	Yellow	Service Indicates a Service operation is currently active (e.g. during HART tunnelling).

Additional elements in the terminal compartment

Symbol	Meaning	Remarks
1	Endress+Hauser CDI port	Not used in the Tankvision instrument.
	Display port	For the connection of the local display in the housing cover. Is connected on delivery.
● ✓•	USB port	Reserved for future enhancements.
W&M	Weights & Measures Switch	■ ☐ :W&M parameters are unlocked and can be changed. ■ ☐ :W&M parameters are locked and cannot be changed.

Ambient conditions NXA820

Mounting location	Cabinet or protective housing
Ambient temperature	-40 +60 °C (-40 +140 °F)
Storage temperature	-40 +85 °C (-40 +185 °F)
Relative humidity	max. 90% at +25 °C (non-condensing)
Ingress protection	IP20

Electromagnetic compatibility (EMC)


The device complies with the requirements of the EMC Directive 89/336/EEC, "Electromagnetic Compatibility".

Installation

Tankvision NXA820 Tank Scanner is designed to be installed in a cabinet, using a standard 35 mm DIN (tophat) rail conforming to EN50022 (BS5584) (IEC 60715).

Mechanical construction

Dimensions



Dimensions in mm (inch)

Materials

Housing

Polycarbonate Colour: light grey


Front cover
Polyamide PA6
Colour: grey

Fixing slide (for fastening on the top-hat rail)

Polyamide PA6 Colour: black

Human interface

Display module



(a): IP address; (b): date and time; (c): instrument tag; (d): W&M switch status

LEDs

Symbol	Color	Meaning
\odot	Green/Red	Green = Power On Red = Indicates a Fault when lit or "Maintenance required" when flashing.
1	Yellow	Communication Flashes when the NXA820 Tank Scanner completes a successful fieldbus communication cycle (e.g. Sent a request and received a reply).
r	Yellow	Service Indicates a Service operation is currently active (e.g. during HART tunnelling).
•	Yellow	Stand-by Indicates the box is a redundant secondary unit, and is ready to take over if the primary unit fails.

Certificates and approvals

NMi

W&M approval according to OIML R 85 (in preparation)

PTB

Innerstaatliche Bauartzulassung (in preparation)

Ordering information NXA820

010	Ap	pro	val										
	Α	No	n-haza	rdo	us ar	ea							
020		Fie	Field Communication; Input										
		8			•		ol, max						
		1					,				nts (in preparation)		
		4 v	4 MODBUS EIA485 master, max. 15 instruments Y Special version, to be specified										
	1	Power supply											
030							50.446						
						VAC VD(50/60	HZ					
							n, to b	e spe	cifie	d			
040	İ	 	1	Inv	ont	OM7	calcu	latio	ne				
040				1		+gas	caicu	iauo	1113				
				9		-	version	, to b	e spe	ecified	ed		
050					Da	ta A	rchiv	e M	emo	orv S	Size		
					D	1					in; 90 days		
				Y Special version, to be specified									
060				Local Operation									
				1 status display									
						9	Special version, to be specified						
070						Operation language							
							A English						
	1						Y	Y Special version, to be specified					
080							Housing						
								1 9			l mounting PBT, IP20 version, to be specified		
	1	1						7			, .		
090										1	ndancy		
									1 2	w/o	o ivated (in preparation)		
								9 Special version, to be specified					
100											istody Transfer Approval		
100								O not selected					
										1	NMI + PTB type (in preparation)		
								9 Special version, to be specified					
110											Additional Option		
											A Basic version		
								l			Y Special version, to be specified		
NXA820 -											complete product designation		

Tankvision NXA821 (Data Concentrator)

Function

- The NXA821 Tankvision Data Concentrator is the enhanced solution for large tank farms and refineries. The Data Concentrator is required if:
 - the plant contains more than one field loop (each of which has its own Tank Scanner NXA820)
 - tanks of more than one Tank Scanner NXA820 are to be grouped
- The Data Concentrator collects the data of several Tank Scanner units and enables reconciliation and totalization of the tank data of many or all tanks in structured groups.
- Alarms and events from all connected Tank Scanners NXA820 can be shown in a common screen. Any tank of the system can be assigned to any tank group, regardless of the Tank Scanner it is linked to. This ensures the highest possible flexibility for the plant or tank farm.
- An alarm pop-up shows alarms of all connected Tank Scanners NXA820 even if the web browser is closed.
- A central log-in allows access to all Tank Scanners NXA820 in the network without having to access each unit via its IP address. Tank details of all units can be viewed from a central location.

Number of tanks

- 225 tanks² can be allocated to each Data Concentrator NXA821. Each of these tanks must have been allocated to a Tank Scanner NXA820 beforehand.
 - If more than 225 tanks are to be integrated in the system, multiple Data Concentrators NXA821 have to be used.
- Tanks from up to 15 different Tank Scanners NXA820 can be integrated in this way³. If more than 15 Tank Scanners NXA820 are involved, multiple Data Concentrators NXA821 have to be used.

LAN connections

System LAN port

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector Connects the NXA821 Data Concentrator to the Local Area Network (LAN)

Sync-Link LAN port (in preparation)

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector

Connects the NXA821 Data Concentrator (e.g. primary) to an optional redundant unit (e.g secondary), to make sure the two devices remain synchronized with each other. If the primary unit fails, the secondary NXA821 Data Concentrator takes over operation without system interruption (see diagram on page 6).

Service LAN port

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector

Connects the NXA821 Data Concentrator to a local computer only for local commissioning and service operations. The computer does not become part of the local area network the NXA821 Data Concentrator is connected to through the System LAN port.

This port has a fixed IP address and can also provide the connected computer automatically with a compatible IP address using a DHCP server built into the NXA821 Data Concentrator. For this automatic IP function to work the computer must be set to obtain its IP address using a DHCP server



Note!

All LAN ports support Auto-MDIX, this system automatically detects the type of cable connected (either straight or crossed) and adjusts itself to match. With this feature you do not need to obtain special crossed cables to interconnect Tankvision components.

Output NXA821

NXA Status relay

- potential free relay, SPDT
- normally-closed when NXA is operating normally, open when NXA is powered off or in fault status
- switching power:
 - $-25 V_{DC}$, 100 W
 - 250 V_{AC}, 4 A, 1000VA

on reguest: more than 45 tanks, up to 225 tanks

3) standard: 4 Tank Scanners;

on request: more than 4 Tank Scanners, up to 15 Tank Scanners

²⁾ standard: 45 tanks;


Power supply

Instrument version	Supply voltage	Power consumption	Current consumption	Fuse
AC voltage NXA821 - #1#######	90 - 250 V _{AC} (50/60Hz)	max. 23 VA	max. 100 mA at 230 VAC	400 mA T
DC voltage NXA821 - #2#######	10.5 - 32 V _{DC}	max. 14 W	max. 580 mA at 24 VDC	2 A T

Galvanic isolation

The following terminals are galvanically isolated from each other:
■ Alarm relay output
■ LAN interfaces

Terminals NXA821



A: Power supply; B: Fuse; C: Status relay; D: System LAN port; E: Sync Link LAN port; F: Service LAN port; G: Endress+Hauser CDI port; H: Display port; I: USB port; J: Weights & Measures locking switch

Power supply (AC version)

Terminal	Meaning	Remarks
1	L	
2	N	90 - 250 V _{AC} Connector: Phoenix 7.62 GMSTB/GFKC
3	Potential equalization	
-	Fuse	400 mA T

Power supply (DC version)

Terminal	Meaning	Remarks
1	L+	
2	L-	10.5 - 32V _{DC} Connector: Phoenix 7.62 GMSTB/GFKC
3	Potential equalization	
	Fuse	2 A T

NXA Status relay

Terminal	Meaning	Remarks		
6	normally open contact	Connector: Phoenix FKC 2,5HC/3-St-5,08		
7	normally closed contact	■ NXA operating normally: terminals 7 & 8 are interconnected		
8	switching contact	NXA powered off or fault status condition: terminals 6 & 8 are interconnected		

LAN connection

Socket	Meaning	Remarks
器	System LAN port	Connects the instrument to the network.
<u> </u>	Sync Link LAN port (in preparation)	Used for connection to redundant unit. If the primary unit fails, its task is taken over by the redundant unit.
4	Service LAN port	Connects the instrument to a computer locally for service purpose. Only this instrument can be configured. The Service LAN port does not allow access to the network.

LEDs

Symbol	Color	Meaning
•	Green	Power On
•	Yellow	Stand-by Indicates the box is a redundant secondary unit, and is ready to take over if the primary unit fails.
4	Red	Fault Indicates a Fault when lit or "Maintenance required" when flashing
1	Yellow	NXA Communication Flashes when the NXA821 Data Concentrator receives a new set of tank data from a connected NXA820 Tank Scanner, through the LAN interface.
\Leftrightarrow		Data Transfer
	Green	Indicates data is being transferred on the LAN interface.
	Yellow	Indicates data is being transferred on the USB interface.
0-0	Green	Linked
•<*	Yellow	USB active (for future enhancements) When lit the connected USB device has been detected and is in use, do not remove the device while this LED is lit.
Y	Yellow	Service Indicates a Service operation is currently active (e.g. during HART tunnelling).

Additional elements in the terminal compartment

Symbol	Meaning	Remarks
-	Endress+Hauser CDI port	Not used in the Tankvision instrument.
	Display port	For the connection of the local display in the housing cover. Is connected on delivery.
● √*	USB port	Reserved for future enhancements.
W&M	Weights & Measures Switch	■ ☐ :W&M parameters are unlocked and can be changed. ■ ☐ :W&M parameters are locked and cannot be changed.

Ambient conditions

Mounting location	Cabinet or protective housing
Ambient temperature	-40 +60 °C (-40 +140 °F)
Storage temperature	-40 +85 °C (-40 +185 °F)
Relative humidity	max. 90% at +25 °C (non-condensing)
Ingress protection	IP20

Electromagnetic compatibility (EMC)


The device complies with the requirements of the EMC Directive 89/336/EEC, "Electromagnetic Compatibility".

Installation

Tankvision NXA821 Data Concentrator is designed to be installed in a cabinet, using a standard 35 mm DIN (top-hat) rail conforming to EN50022 (BS5584) (IEC 60715).

Mechanical construction

Dimensions



Dimensions in mm (inch)

Materials

Housing

Polycarbonate Colour: light grey

Front cover


Polyamide PA6 Colour: grey

Fixing slide (for fastening on the top-hat rail)

Polyamide PA6 Colour: black

Human interface

Display module



(a): IP address; (b): date and time; (c): instrument tag; (d): W&M switch status

LEDs

Symbol	Color	Meaning	
\odot	Green/Red	Green = Power On Red = Indicates a Fault when lit or "Maintenance required" when flashing.	
1	Yellow	NXA Communication Flashes when the NXA821 Data Concentrator receives a new set of tank data from a connected NXA820 Tank Scanner, through the LAN interface.	
r	Yellow	Service Indicates a Service operation is currently active (e.g. during HART tunnelling).	
•	Yellow	Stand-by Indicates the box is a redundant secondary unit, and is ready to take over if the primary unit fails.	

Certificates and approvals

NMi

W&M approval according to OIML R 85 (in preparation)

PTB

Innerstaatliche Bauartzulassung (in preparation)

Ordering information NXA821

010	 Approval A Non-Hazardous area						
030	Pow 1 2	ver su 90-250 10.5-3	i pply O VAC 2 VDC	50/60		oified	
050		Data D 1	Archi GB; 15	ve M param	l em c	ory Size /min; 90 e specifie	days
060		1 9		ıs disp	olay	to be spe	ecified
070			Operation Language				
080				Housing I DIN rail mounting PBT, IP20 Special version, to be specified			
090					Redundancy		
100					Custody Transfer Approval 0 not selected 1 NMI + PTB type (in preparation) 9 Special version, to be specified		
110						A d	Basic version Special version, to be specified
NXA821 -							complete product designation

Tankvision NXA822 (Host Link)

Function

- The Host Link NXA822 collects data from all Tank Scanners NXA820 on a network and transfers them to the host system.
- The MODBUS option supports serial EIA-232(RS) and EIA-485(RS), as well as MODBUS TCP/IP. The NXA822 is configured as a MODBUS slave. Supported functions are:
 - Coil Status (#01)
 - Holding Registers (#03)
 - Input Registers (#04)
 - Write Modbus Values (#06)
- The MODBUS register map can be described via XML files and so easily adapted to individual MODBUS master requirements.

Number of tanks

- 225 tanks⁴ can be allocated to each Host Link NXA822. Each of these tanks must have been allocated to a Tank Scanner NXA820 before.
 - If more than 225 tanks are to be integrated in the system, multiple Host Links NXA822 have to be used.
- Tanks from up to 15 different Tank Scanners NXA820 can be integrated in this way⁵⁾.

 If more than 15 Tank Scanners NXA820 are involved, multiple Host Links NXA822 have to be used.

LAN connections

System LAN port

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector Connects the NXA822 Host Link to the Local Area Network (LAN)

SyncLink LAN port (in preparation)

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector

Connects the NXA822 Host Link (e.g. primary) to an optional redundant unit (e.g secondary), to make sure the two devices remain synchronized with each other. If the primary unit fails, the secondary NXA822 Host Link takes over operation without system interruption.

Service LAN port

100 BASE-TX, Full/Half Duplex, 100 Mbit, Shielded RJ45 connector

Connects the NXA822 Host Link to a local computer only for local commissioning and service operations. The computer does not become part of the local area network the NXA822 Host Link is connected to through the System LAN port.

This port has a fixed IP address and can also provide the connected computer automatically with a compatible IP address using a DHCP server built into the NXA822 Host Link. For this automatic IP function to work the computer must be set to obtain its IP address using a DHCP server.



Note!

All LAN ports support Auto-MDIX, this system automatically detects the type of cable connected (either straight or crossed) and adjusts itself to match. With this feature you do not need to obtain special crossed cables to interconnect Tankvision components.

Output NXA822

NXA Status Relay

- potential free relay, SPDT
- normally-closed when NXA is operating normally, open when NXA is powered off or fault status exists
- switching power:
 - $-25 V_{DC}$, 100 W
 - $-250\,\bar{V}_{AC}$, 4 A, 1000VA

Host connection

- EIA-232(RS)
- EIA-485(RS)
- TCP-IP on System LAN port

⁴⁾ standard: 45 tanks;

on request: more than 45 tanks; up to 225 tanks

⁵⁾ standard: 4 Tank Scanners;

on request: more than 4 Tank Scanners; up to 15 Tank Scanners

Power supply


Instrument version	Supply voltage	Power consumption	Current consumption	Fuse
AC voltage NXA822 - ##1######	90 - 250 V _{AC} (50/60Hz)	max. 23 VA	max. 100 mA at 230 VAC	400 mA T
DC voltage NXA822 - ##2##### (in preparation)	10.5 - 32 V _{DC}	max. 14 W	max. 580 mA at 24 VDC	2 A T

Galvanic isolation

The following terminals are galvanically isolated from each other:

- Alarm relay output
- LAN interfaces
- Host connection

Terminals NXA822



A: Power supply; B: Fuse; C: Status relay; D: System LAN port; E: Sync Link LAN port; F: Service LAN port; G: RS232 Host connection; H: RS485 Host connection; I: Endress+Hauser CDI port; J: Display port; K: USB port; L: Weights & Measures locking switch

Power supply (AC version)

Terminal	Meaning	Remarks	
1	L		
2	N	90 - 250 V _{AC} Connector: Phoenix 7.62 GMSTB/GFKC	
3	Potential equalization		
-	Fuse	400 mA T	

Power supply (DC version)

Terminal	Meaning	Remarks		
1	L+			
2	L-	10.5 - 32V _{DC} Connector: Phoenix 7.62 GMSTB/GFKC		
3	Potential equalization			
	Fuse	2 A T		

NXA Status Relay

Terminal	Meaning	Remarks		
6	normally open contact	Connector: Phoenix FKC 2,5HC/3-St-5,08		
7	normally closed contact	 NXA operating normally: terminals 7 & 8 are interconnected 		
8	switching contact	 NXA powered off or fault status condition: terminals 6 & 8 are interconnected 		

LAN connection

Socket	Meaning	Remarks
25	System LAN port	Connects the instrument to the network.
<u> </u>	Sync Link LAN port (in preparation)	Used for connection to redundant unit. If the primary unit fails, its task is taken over by the redundant unit.
Y	Service LAN port	Connects the instrument to a computer locally for service purpose. Only this instrument can be configured. The Service LAN port does not allow access to the network.

Field connection: MODBUS Serial, EIA/TIA-232 (RS232)

The NXA822 Data Concentrator is defined as a Data Terminal Equipment (DTE) device, and provides EIA/TIA-232 (RS232) interface through a male DB9 connector whose pin out complies with the EIA/TIA-574 standard:

Pin	RS232	Name	Remarks
1	CD	Carrier Detect	Signal from connected device
2	RxD	Receive Data	Signal from connected device
3	TxD	Transmit Data	Signal to connected device
4	DTR	Data Terminal Ready	Signal to connected device
5	G	Signal Ground	Common connection
6	DSR	Data Set Ready	Signal from connected device
7	RTS	Request To Send	Signal to connected device
8	CTS	Clear To Send	Signal from connected device
9	RI	Ring Indicator	Signal from connected device
Case	Shield	Shield	

Definition

EIA/TIA-232 (RS232) is a voltage mode digital communication using up to $\pm 12~V_{DC}$, and requires a variety of signals depending on the operating mode (software selectable):

Signal	Basic RS232	Fully RS232 with Hardware Handshaking (in preparation)	Remarks
Shield	Required	Required	Copper braided or combined foil and braided shielding
G	Required	Required	
RxD	Required	Required	
TxD	Required	Required	
RTS		Required	Null Modem connection, these two pins can be
CTS		Required	linked together
DTR		Required	Null Modem connection, these three pins can be
DSR		Required	linked together
CD		Required	
RI		Optional	Not required

RS-232 Cable Specification

Cable capacitance	≤ 50 pF/m
Core cross-section	\geq 0.34 mm ² , corresponds to AWG 22, multi-strand cable is preferred
Cable type	Single cable or twisted pair
Cable resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shielding	Copper braided shielding or combined foil and braided shielding

Field connection: MODBUS Serial, EIA/TIA-485 (RS485)

Tern	ninal	EIA/TIA-485 MODBUS	Meaning	Remarks
18		С	Signal Common	
17		В	+ signal	Connector: Phoenix FKC 2,5HC/3-St-5,08
16		A	- signal	

Two-Wire MODBUS Definition

As described in the "MODBUS over serial line specification and implementation guide V1.02" published by the Modbus-IDA organisation (www.modbus.org) and based upon the EIA/TIA-485-A physical layer specification, MODBUS two-wire serial requires the following four electrical connections between each of the devices on the bus:

Signal	Purpose	Remarks	
A	Data signal (-)	These signals must be connected using a balanced	
В	Data signal (+)	twisted pair cable.	
С	Signal Common	Must interconnect all devices on the bus.	
Shield	EMC Protection	Copper braided or combined foil and braided shielding	


Additional EIA/TIA-485 bus settings

- Bus biasing resistors (must be present at one point on the bus) (software selectable inside NXA822)
- Bus termination resistor (must be present at each end of the bus) (software selectable inside NXA822)

Cable Specification

Characteristic impedance	135 to 165 Ω at measuring frequency of 3 to 20 MHz
Cable capacitance	≤ 30 pF/m
Core cross-section	\geq 0.34 mm ² , corresponds to AWG 22, multi-strand cable is preferred
Cable type	Single twisted pair + third conductor (for common) Or Dual twisted pair (common uses second pair with wire joined together)
Cable resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shielding	Copper braided shielding or combined foil and braided shielding

Field connection: MODBUS TCP/IP



L00-NXA82xxx-04-00-00-yy-02

LEDs

Symbol	Color	Meaning
0	Green	Power On
(1)	Yellow	Stand-by Indicates the box is a redundant secondary unit, and is ready to take over if the primary unit fails.
4	Red	Fault Indicates a Fault when lit or "Maintenance required" when flashing
1	Yellow	Slave Communication (on base unit). Flashes when the NXA822 Host Link completes a successful fieldbus communication cycle (e.g. Receives a request and sends a reply).
	Yellow	NXA Communication (on local display) Flashes when the NXA822 Host Link receives a new set of tank data from a connected NXA820 Tank Scanner, through the LAN interface.
→	Yellow	Fieldbus Rx Flashes to indicate data bits are being received from the connected field devices.
♦	Yellow	Fieldbus Tx Flashes to indicate data bits are being sent to the connected field devices.
RTS	Yellow	Request to Send Flashes to indicate the RTS signal is being sent to the connected field device, only used when Full RS-232 mode is selected, otherwise off.
CTS	Yellow	Clear to Send Flashes to indicate the CTS signal is being received from the connected field device, only used when Full RS-232 mode is selected, otherwise off.
DTR	Yellow	Data Terminal Ready Flashes to indicate the DTR signal is being sent to the connected field device, only used when Full RS-232 mode is selected, otherwise off.
DSR	Yellow	Data Set Ready Flashes to indicate the DSR signal is being received from the connected field device, only used when Full RS-232 mode is selected, otherwise off.
\Leftrightarrow		Data Transfer
·	Green	Indicates data is being transferred on the LAN interface.
	Yellow	Indicates data is being transferred on the USB interface.
00		Linked Indicates that the LAN cable is both connected and functioning.
•<	Yellow	USB active (for future enhancements) When lit the connect USB device has been detected and is in use, do not remove the device while this LED is lit.
Y	Yellow	Service Indicates a Service operation is currently active (e.g. during HART tunnelling).

Additional elements in the terminal compartment

Symbol	Meaning	Remarks
1	Endress+Hauser CDI port	Not used in the Tankvision instruments.
	Display port	For the connection of the on-site display in the housing cover. Is connected on delivery.
● √ [*]	USB port	Reserved for future enhancements
W&M	Weights & Measures Locking	■ ☐ :W&M parameters are unlocked and can be changed. ■ ☐ :W&M parameters are locked and cannot be changed.

Shielding and Grounding

When planning the shielding and grounding for a fieldbus system, there are three important points to consider:

- Electromagnetic compatibility (EMC)
- Explosion protection
- Safety of the personnel

To ensure the optimum electromagnetic compatibility of systems, it is important that the system components and above all cables, which connect the components, are shielded and that no portion of the system is unshielded. Ideally, the cable shields are connected to the normally metal housings of the connected field devices. Since these are generally connected to the protective earth, the shield of the bus cable is grounded many times. Keep the stripped and twisted lengths of cable shield to the terminals as short as possible. This approach, which provides the best electromagnetic compatibility and personnel safety, can be used without restriction in systems with good potential equalization.

In the case of systems without potential equalization, a power supply frequency $(50/60 \, \text{Hz})$ equalizing current can flow between two grounding points which, in unfavourable cases, e.g. when it exceeds the permissible shield current, may destroy the cable.

To suppress the low frequency equalizing currents on systems without potential equalization, it is therefore recommended to connect the cable shield directly to the building ground (or protective earth) at one end only and to use capacitive coupling to connect all other grounding points.



Caution!

The legal EMC requirements are fulfilled **only** when the cable shield is grounded on both sides!

Ambient conditions

Mounting location	Cabinet or protective housing
Ambient temperature	-40 +60 °C (-40 +140 °F)
Storage temperature	-40 +85 °C (-40 +185 °F)
Relative humidity	max. 90% at +25 °C (non-condensing)

Electromagnetic compatibility (EMC)


The device complies with the requirements of the EMC Directive 89/336/EEC, "Electromagnetic Compatibility".

Installation

Tankvision NXA822 Host Link is designed to be installed in a cabinet, using a standard 35 mm DIN (top-hat) rail conforming to EN50022 (BS5584) (IEC 60715).

Mechanical construction

Dimensions



NXA82xxx-06-00-00-yy-003

Dimension in mm (inch)

Materials

Housing

Polycarbonate Colour: light grey

Front cover


Polyamide PA6 Colour: grey

Fixing slide (for fastening on the top-hat rail)

Polyamide PA6 Colour: black

Human interface

Display module



(a): IP address; (b): date and time; (c): instrument tag; (d): W&M switch status

LEDs

Symbol	Color	Meaning
· ·	Green/Red	Green = Power On Red = Indicates a Fault when lit or Maintenance required when flashing
1	Yellow	NXA Communication Flashes when the NXA822 Host Link receives a new set of tank data from a connected NXA820 Tank Scanner, through the LAN interface.
Y	Yellow	Service Indicates a Service operation is currently active (e.g. during HART tunnelling)
•	Yellow	Stand-by Indicates the box is a redundant secondary unit, and is ready to take over if the primary unit fails.

Certificates and approvals

NMi

W&M approval according to OIML R 85 (in preparation)

PTB

Innerstaatliche Bauartzulassung (in preparation)

Ordering information NXA822

010	Ap	Approval								
	Α	Not	Non-hazardous area							
020		Co	Communication; Output							
		1				,				nterface
		9	Spe	cial v	ersion/	, to b	e spe	cifie	d	
030			Po	wer	Supp	oly				
			1	90-	250 V	AC 5	0/60	Hz		
			2		5-32 V		, ,			,
			9	Spe	cial ve	rsion	, to b	e spe	cifie	d
060				Lo	cal O	pera	ition	1		
				1	status		,			
				9	Speci	al ve	rsion	, to b	e spe	ecified
070					Operating language					
					Α	Eng	glish			
					Y	Spe	cial v	rersio	n, to	be specified
080						Но	Housing			
						1	1 DIN rail mounting PBT, IP20			
						9	Special version, to be specified			
090							Re	dun	dan	су
							1	w/c	0	
							2			d (in preparation)
			ļ				9	Spe	cial v	version, to be specified
100								Cu	stoc	ly Transfer Approval
								0		selected
								1	l	II + PTB type (in preparation)
			ļ				ļ	9	Spe	cial version, to be specified
110									Ad	ditional Option
									Α	Basic version
									Y	Special version, to be specified
NXA822 -										complete product designation

Human interface

Operating concept

Tankvision is operated by a standard web browser (e.g. Microsoft Internet Explorer).

The Tankvision components contain predefined operating pages. If required, they can be adjusted by the user.

Languages

The operating pages are available in the following languages:

- English
- other languages in preparation

System requirements of user PC

Hardware

CPU	min. 1 GHz, P4
RAM	512 MB
Screen resolution	min. 1024x768; recommended 1280x1024

Software

Operating System	Microsoft Windows 2000 / XP
Web Browser	Microsoft Internet Explorer 6
Java Runtime Environment	1.5.0-upt.07

Network

Network switches **must** always be used to interconnect Tankvision components (Network hubs must **never** be used).

Only use screened Category 5 (or higher) cables.



Caution!

The legal EMC requirements are fulfilled **only** when screened LAN cable is used and the cable screen is properly terminated to screened RJ45 connectors.




Caution!

Most commercial and IT infrastructure networking switches (and components) are not designed to be used within harsh environments (e.g. temperatures below $+5^{\circ}$ C, dusty or with high levels of EMC or electrical noise), it is therefore recommended that **only** networking components specifically designed for industrial control purposes be used within the control room (or control cabinet) environment as part of the Tankvision system.


Examples of operating pages

Tank group



A: Internet Explorer menu and symbol bar; B: Navigation tree; C: Main window; D: Alarms and events viewer

Single tank



A: Internet Explorer menu and symbol bar; B: Navigation tree; C: Main window; D: Alarms and events viewer

Alarm Popup Agent



L00-NXA82xxx-20-00-00-en-005

Supplementary documentation

Operating Instructions	BA340F
	Operating Instructions for NXA820, NXA821 and NXA822 Describes installation, electrical connection and first setup.
Description of Instrument Functions	BA239F
	Description of Instrument Functions for NXA820, NXA821 and NXA822 Contains a detailed description of all instrument functions.
	Trademarks
MODBUS	MODBUS is a registered trademark of the MODBUS-IDA, Hopkinton, MA, USA
Windows	Windows is a registered trademark of the Microsoft Corporation
Java	Java is a registered trademark of Sun Microsystems, Inc.

Instruments International

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel. +41 61 715 81 00 Fax +41 61 715 25 00 www.endress.com info@ii.endress.com



People for Process Automation