Technical Information TI 189F/00/en

Operating Instructions 71075800

Ultrasonic Measurement prosonic FDU 80...86

Sensors for non-contact, continuous measurement of level and flow. Suitable for use in explosion hazardous areas.





















Application

Prosonic FDU is a series of nine ultrasonic sensors with different measuring ranges for continuous, noncontact measurement of level and flow.

- FDU 80, 80 F Liquids: 5 m (16 ft) Solids: 2 m (6.5 ft)
- FDU 81, 81 F Liquids: 10 m (32 ft) Solids: 5 m (16 ft)
- FDU 82 Liquids: 20 m (65 ft) Solids: 10 m (32 ft)
- FDU 83 Liquids: 25 m (82 ft) Solids: 15 m (49 ft)
 FDU 84
- Solids: 25 m (82 ft)
- FDU 85 Solids: 45 m (147 ft)
- FDU 86
- Solids: 70 m (230 ft)

The material to be measured can be aggressive liquids such as alkali or acid, or powdery and clumpy solids such as grain, coal, ore and gravel.

Features and Benefits

- Complete sensor programme for non-contact, continuous measurement of level and flow
- For use in flumes, weirs, tanks and silos
- Insensitive to dirt and build-up
- Optional integrated heating to protect against a build up of ice on the sensor
- Wide range of mountings using flange or thread
 - (with slip-on flange for flush mounting of the sensor)
- Weather resistant and safe against submersion (IP 68)
- Integrated temperature sensor

Please note: From January 2008, the sensors FDU80...86 are only available as spare part.



Measuring System

Measuring System

The complete measuring system consists of

- the Prosonic FDU 80, 80 F, 81, 81 F, 82, 83, 84, 85 or 86 ultrasonic sensor
- the transmitter
 - Prosonic FMU 860: 1-channel version for level measurement or
 - Prosonic FMU 861: 1-channel version for flow measurement or level measurement or
 - Prosonic FMU 862:
 2-channel version.

Sensor FDU 86 can be selected and operated by FMU 86x transmitters with software version 2.2 upwards.

Sensor Accessories

The accessories (see pages 9 and 10) ensure that the sensors can be adapted to special process conditions:

- Alignment unit FAU 40 for the sensor
- All-weather protective cover
- Mounting frame
- Wall bracket
- Sensor flanges (e.g. FAU 80)
- External temperature sensor FMT 131
- A separate power supply unit is available for heated sensors.





The emitter in the sensor is excited electrically and sends an ultrasonic pulse in the direction of the surface of the product which partially reflects the pulse. This echo is detected by the same sensor, now acting as a directional microphone, and then converted back into an electrical signal. The time between transmission and reception of the pulse (the sonic run time) is directly proportional to the distance between the sensor and the product surface. This distance is determined by the velocity of sound c and the run time t using the formula:



Blocking Distance

measured correctly.

Due to the ringing time of the sensor,

there is a zone immediately below the

sensor in which returning echoes

cannot be detected. This so-called

blocking distance BD determines the

diaphragm and the maximum level in

the silo. If the minimum distance is not

maintained, the level will not be

minimum distance between the sensor

Function

 $D = \frac{c \cdot t}{2}$

Operating principle of FDU ultrasonic sensors **BD** Blocking distance D Distance from sensor to surface of material Height in silo L (Level) Maximum level (100%, Full) F Zero point of measurement

(0%, Empty)

Planning Recommendations

Measuring

Maximum Measuring Range

The correct sensor for your particular application depends on the process and ambient conditions. When selecting the sensor, take into account that the maximum measuring range of the individual sensor is determined by the attenuation of the ultrasonic pulse by the air as well as by the reflecting characteristics of the product surface. Both the level of background noise (e.g. when filling) and the mounting point also can affect measurement.

Calculating the Range

The diagram shows ideal attenuation curves for the FDU 80...86 sensors:

- Check the factors affecting your
- Measurement in the table right.Add up their attenuation values.
- Take this sum and find the point where it intersects with the range limit line of the sensor you are using



Optimum conditions in tanks or silos are achieved if

- the lower edge of the sensor is below the silo roof
- the detection zone does not include any internal fixtures or the filling curtain
- the surface of the solid is hard and coarse-grained
- the surface of the liquid is calm and no vapour is formed
- operation is under normal atmospheric pressure
- the vessel is not being filled during measurement.

Less than optimum conditions reduce the measuring range of the sensors.

Factors	Attenuation (dB)
Temperature layering air temperature difference between sensor and surface of material up to 20°C (68°F) up to 40°C (104°F) up to 80°C (176°F) up to 150°C (302°F)	0 510 1020 2030
Filling curtain outside detection zone small amounts in detection zone large amounts in detection zone	0 510 1040
Dust none low amounts high amounts	0 5 520
Surface of solid hard, coarse (e.g. grit) soft (e.g. peat, dust-covered clinker)	40 4060
Surface of liquid calm ripples strong turbulence (e.g. agitator blades)	0 510 1020
Foam please contact Endress+Hauser	
Sensor installation lower edge free in silo on collar, lower edge slanted depending on diameter/length ratio on collar, lower edge horizontal depending on diameter/length ratio	0 1020 2040

Example for calculating range: range 70 • Silo with grit approx. 40 dB m • Little content approx. 5 dB approx. 5 dB Little dust FDU 86 Gives an attenuation of 50 dB. 40 The FDU 82 sensor measures up to 8 m under these conditions. FDU 85 30 FDU 84 FDU 83 20 **FDU 82** 10 FDU 81, 81 F FDU 80, 80 F 0 20 40 0 60 80 100 110 Attenuation dB

Dimensions 1 m = 3.28 ft 1 ft = 0.305 m

Echo attenuation as a function of range for various sensors (ideal reflection and atmospheric conditions)

Installation

Detection Limits and Interference Signals

If internal fixtures are present in the tank, then careful alignment of the sensor is critical in order to keep the interference echeos as low as possible. The ultrasonic pulse should travel unimpeded to the surface of the material. The signal leaves the sensor as a narrow beamwhich widens as the distance increases. Every objekt within this beam gives rise to an echo which is then received by the sensor. The radius of the beam can be easily estimated by using the 3 dB beam angle.

Operating Limits

 The sensors may not be used to measure aliphatic hydrocarbons (not applicable to FDU 80 F / FDU 81 F).

Estimation of the Detection Limits of the Detector

Please note:

- Edges, internal fixtures, etc. within the sound cone are of greatest importance in the first third of the range as the energy of the beam is highly concentrated.
- The energy in the last third of the range is distributed over a larger area, so that internal structures and edges are not as critical.

Accuracy

- A constant temperature and sound velocity within the measuring path enable a high degree of accuracy to be achieved. The effects of large temperature variations within the measuring path and changing gas mixtures must be calculated and the Prosonic programmed accordingly.
- With liquids having a high partial pressure, the gas composition must be determined to see if it remains constant.

		$r = tan \frac{\alpha}{2} \bullet L$		
		Liquids		
		α	L	r
	FDU 80, 80 F	8°	5 m (16 ft)	0.35 m (1.1 ft)
	FDU 81, 81 F	8°	10 m (32 ft)	0.69 m (2.3 ft)
	FDU 82	8°	20 m 65 ft)	1.4 m (4.6 ft)
	FDU 83	4°	25 m (82 ft)	0.87 m (2.8 ft)
		Solids		
	FDU 80	8°	2 m (6.6 ft)	0.14 m (0.46 ft)
	FDU 81	8°	5 m (16 ft)	0.35 m (1.1 ft)
	FDU 82	8°	10 m (32 ft)	0.7 m (2.3 ft)
	FDU 83	4°	15 m (49 ft)	0,52 m (1.7 ft)
	FDU 84	5°	25 m (82 ft)	1.1 m (3.6 ft)
x.	FDU 85	5°	45 m (147 ft)	1.9 m (6.2 ft)
	FDU 86	6°	70 m (230 ft)	3.6 m (11.8 ft)

 α 3 dB beam angle
 L length of beam (calculated from max measuring range of sensor)
 r radius of beam

Guidelines when Mounting

- · Check that the maximum level height does not come within the blocking distance of the sensor (see page 11, »Technical Data«).
- If possible, the face of the sensor should lie parallel to the surface of the product.
- The PE or PTFE coating on the diaphragm of the FDU 84, 85 and 86 is an integral part of the measuring system and must not be damaged during installation.
- Do not damage the funnel of the FDU 86 when mounting.
- The connecting cable of the FDU sensor is not designed as a supporting cable. Do not use it as a suspension wire.
- For dust explosion areas: The connecting cable of the FDU must be laid in piping. Local regulations for explosive athmospheres caused by dust must be observed.
- All national guidelines applicable must be observed in explosion hazardous areas.

Mounting in Vessels

- Install the sensor so that its lower edge projects into the vessel.
- Position the sensor so that neither the filling curtain nor any internal fittings, e.g. an additional limit switch, are within the detection zone.
- The sensor must be positioned at the centre of the outflow funnel so that an echo is received when the silo is empty.
- Accurate positioning of the sensor can be simplified using the FAU 40 alignment unit.
- The cable of the prosonic sensor is not designed as a supporting cable. Do not use it as a suspension wire.
- If the sensor is to be installed in tanks containing very aggressive media, check that the chemical and corrosion resistance of the sensor materials meet these requirements.

conduit seal



- a) Correct installation
- As far as possible from the silo wall, the material inflow and internal fixtures.
- The centre of the outflow funnel reflects an echo which is received by the sensor even when the silo is empty.
- b) Incorrect installation
- The detection zone includes the filling curtain. • The echo is reflected to one side when the silo is empty.





Mounting:

- above: FDU 84 on girder or angle bracket
- centre: FDU 84 with alignment unit FAU 40 near to a service access
- below: FDU 84 with a 1" sleeve welded to a grating



Sensor on a 1" pipe in combustible dust area (for FM, Class II)

1" pipe

hazardous area

conduit seal 1" threaded sleeve

Flush Mounting with Slip-on Flange FAU 80

The FDU 80 F and FDU 81 F sensors can be flush mounted using an FAU 80 slip-on flange.

FAU 80 - KAJ

FAU 80 - CHP

FAU 80 - CHJ FAU 80 - AHP

FAU 80 - AHJ FAU 80 - KHP

FAU 80 - KHJ

Flanges in polypropylene (PPs) should only be used with pressures up to 1.5 bar_{abs}, flanges in 1.4435 also above.

(JIS B 2210)

DN 100 PN 16 (DIN 2527)

ANSI 4" 150 psi

(ANSI B 16.5)

JIS 10 K 100



The internal diameter of the nozzle should be selected according to the valid allowable limits for 3A applications.

Usually, the internal diameter of the nozzle should be larger than or equal to the internal diameter of the sensor.

Dimensions 1 mm = 0.039 in

1 in = 25.4 mm			
	1	in =	25.4 mm



D



180

190.5

175

8

4

8

18

19.1

19

ote for 3A applications	;!
-------------------------	----

Ν

The internal diameter of the nozzle should be selected according to the valid allowable limits for 3A applications.

Usually, the internal diameter of the nozzle should be larger than or equal to the internal diameter of the sensor.

20

23.9

18

220

228.6

210

Mounting on a Mounting Pipe The sensor should be mounted on a pipe only when the maximum level comes within the blocking distance. Please note:

- No build-up of material should form in the pipe.
- Select a pipe with a diameter as large as possible (see figures and table).
 If there is a possibility of build-up in the pipe the diameter should be significantly larger.
- The inner surface of the pipe should be as smooth as possible (no edges or welding seams). When mounting in the open, the pipe should be insulated as the temperature within the pipe can differ significantly from that in the vessel.
- For other nozzles, fixed target suppression must be used.

Dimensions 1 mm = 0.039 in 1 in = 25.4 mm



Mounting above Flumes

To achieve the highest accuracy, the sensor should be situated immediately above the high water level (100%) plus the blocking distance BD (see page 11, »Technical Data«).

The sensor must always be mounted perpendicular to the surface of the water and be above the centre of the flume. The appropriate mounting distances with respect to the flume are to be maintained (see operating manual »Prosonic«, BA 100F/00/en). When mounted in the open, the sensor must be protected against the sun by a protective cover, so that temperature compensation works correctly. We recommend an all weather protection cover (see page 9, »Accessories«).



Electrical Connection

Connecting the FDU

The sensors are supplied with a fixed cable of 5 m (16.35 ft) in length as standard (30 m (98.1 ft) if required, cross section 0.75 mm² (AWG 18)). They can be connected:

- directly in the FMU connection compartment; the connecting terminals are designed for cross sections up to 2.5 mm² (AWG 13).
- via a terminal box: an additional cable is then required which may be up to 300 m (981 ft) in length, up to 6 Ω per core, maximum 60 nF (terminal box and cable not included in delivery). A two-wire, screened cable must be used (screening: metal braiding max. 6Ω). The screening serves as a return cable. Do not ground the screening and lay to the transmitter without any electrical break.

If the terminal box is to be installed in explosion hazardous areas, then all national guidelines applicable must be observed.

These measures ensure that the sensors correspond to industrial (NAMUR) and European EMC Standards EN 50 081-1 for interference emission and EN 50 082-2 for interference immunity. For general information on EMC (test methods, installation hints) see TI 241F/00/en.

Ultrasonic Sensor with Heating

The sensors FDU 80 and FDU 81 can be supplied with heating units. For heated sensors:

The connecting terminals for the heating unit are delivered with the sensor. They are to be mounted in the connection compartment of the transmitter.

 Technical data for an external power supply for heating the sensor 24 V_{DC} (10%)

for each heated sensor, 250 mA, 8 W

Ø mm ²	0.5 (AWG	0.75	1
	20)	(AWG 18)	(AWG 17)
max. length	150	250	300
m (ft)	(490.5)	(817.5)	(981)

Channel 1

FMU 862

Channel 2

90 91 92



Wire coding

BK	black
RD	red
YE	yellow
GNYE	green/yellow
BN	brown
BU	blue

Sensor extension

- cable: • FDU 80, 80F, 81, 81F, 82
- Ord. No. 938278-0120 • FDU 83, 84, 85
- Ord. No. 938278-1021
- FDU 86 Ord. No. 52000261

Connecting

- the sensors above left :
- FDU 80, 80F, 81, 81F, 82 above right:
- FDU 80, 81 with heating system
- below right: FDU 83, 84.85 (ground via the terminal box) below left;
- FDU 83, 84, 85, 86 (ground to FMU)

Screening

The screening acts as feedback and must be exhibit electrical continuity between sensor and transmitter.





Accessories

Mounting Frame

Material:	Order
number:	
700 mm, galvanised steel	919791-0000
700 mm, 1.4301 (AISI 304)	919791-0001
1400 mm, galv. steel	919791-0002
1400 mm,	
1.4301 (AISI 304)	919791-0003



Mounting frame with 1" pipe for cantilever and Prosonic FMU

Cantilever for Mounting Frame

For mounting Prosonic sensors FDU 80 and 81 over open channels

Material/version:	Order
number:	
500 mm, galv. steel	919790-0000
500 mm, 1.4301 (AISI 304)	919790-0001
1000 mm, galv. steel	919790-0002





Dimensions 1 mm = 0.039 in 1 in = 25.4 mm

frame

Cantilever for mounting

1000 mm, 1.4301 (AISI 304) 919790-0003

Wall Bracket

- Material: galvanised steel Order number: 919792-0000
- Material: 1.4301 (AISI 304) Order number: 919792-0001



Wall bracket for

cantilever

Accessories

All-Weather Protective Cover

For Prosonic sensors FDU 80 and 81 Material: PP-GF Order number: 919793-0000 The measurement point designation is fixed to the protective cover. Break off the fixing eyes on the sensor at the preformed positions – *beforehand*.



All-weather protective cover for FDU 80 and FDU 81

Flanges

Version, similar to:Order number:DN 80 PN 16 in PPs919789-0000DN 100 PN 16 in PPs919789-0002DN 150 PN 16 in PPs919789-0004DN 200 PN 16 in PPs919789-0006The maximum operating pressure of the
sensor applies.Other flanges on request.

Power Supply Unit for Sensor Heating of FDU 80 and FDU 81

Power unit (24 V DC) for sensor heating with IP 66 protective housing. Material: PT/ABS Order No.: 215095-0002

External Temperature Sensor FMT 131

Order code: • Standard version:

FMT 131-R7:

Application: for heated sensor and when temperature is not to be measured in the sensor. Housing: POM, IP 65 Sensor (NTC): 1.4571 stainless steel Thread: G $^{1}/_{2}$ A Two-core screened cabling, max. 25 Ω per core.

not certified.

always without cable

Dimensions 1 m = 3.28 ft







Dimensions 1 mm = 0.039 in

1 in = 25.4 mm

left: dimensions of temperature sensor FMT 131

right: electrical connection of standard temperature sensor FMT 131-R7 (FMT 131-J is delivered with cable connected)



Accessories

Protective Sleeve for Temperature Sensor FMT 131 Material: 1.4571 stainless steel (AISI 316 Ti) Order No.: 942046-0000



Dimensions 1 mm = 0.039 in

1 in = 25.4 mm

Alignment Unit FAU 40

For easy mounting and positioning of the FDU sensor (see Technical Information TI 179F/00/en).



Spare Parts for Sensor FDU 86

The following spare parts are available for the FDU 86 (Type FDU 86-R # #):

- Funnel with accessories Order number: 52002963
- Seals with accessories Order number: 52002964
- Cable with accessories
 Length Order number:
 5 m (16 ft) 52002957
 10 m (32 ft) 52002958
 15 m (49 ft) 52002959
 20 m (65 ft) 52002960
 25 m (82 ft) 52002961
 - 30 m (98 ft) 52002962

sleeve for temperature sensor

Dimension of protective

Dimensions of alignment unit FAU 40

left: with G 1 thread and Pg 11 cable gland

right:

with 1 NPT thread and $3/_4$ cable gland for pipe connection

* for use in Dust-Ex: Insert the seal which is supplied with the sensor here

Technical Data

General Information

Manufacturer	Endress+Hauser GmbH+Co.
Instrument	Ultrasonic sensor
Designation	Prosonic FDU 80, 80F, 81, 81F, 82, 83, 84, 85, 86
Technical documentation Version Technical data	TI 189F/00/en 06.99 according to DIN 19259

Application

Input

Operation and System Design

Non-contact continuous level measurement in liquids an	d solids		
Measuring principle	Ultrasonic echo level me	easurement, time-o	of-flight
Modularity	Ultrasonic sensor for various measuring ranges for connecting to the transmitters 860862, as standard with integrated temperature sensor and mounting accessories, FDU 80/81 with optional heating. Sensor FDU 86 can be selected and operated by FMX 86x transmitters with software version 2.2 unwards		
Construction	FDU 8086: Sensors with connecting cable, mounting via threaded boss on collar, FDU 80F/81F: Flush-mounted sensor with connecting cable, mounting via slip-on flange		
Signal transmission	Analogue voltages		
Measured variables	Level or flow, determine sensor (membrane) to the	d by the distance he surface of the p	from the ultrasonic product
Measuring ranges	FDU 80 FDU 80F FDU 81 FDU 81F FDU 82 FDU 83 FDU 83 FDU 85 FDU 86	in liquids 5 m (16 ft) 5 m (16 ft) 10 m (32 ft) 10 m (32 ft) 20 m (65 ft) 25 m (82 ft) - -	in solids 2 m (6.5 ft) - 5 m (16 ft) - 15 m (32 ft) 15 m (49 ft) 25 m (82 ft) 45 m (147 ft) 70 m (230 ft)
Blocking distance	FDU 80, 80F FDU 81, 81F FDU 82 FDU 83 FDU 84, 85 FDU 86	0.3 m (1.0 ft) 0.5 m (1.6 ft) 0.8 m (2.6 ft) 1.0 m (3.3 ft) 0.8 m (2.6 ft) 1.6 m (5.2 ft)	
Operating frequency (at 23°C)	FDU 80, 80F FDU 81, 81F FDU 82 FDU 83 FDU 84 FDU 85 FDU 86	58 kHz 44 kHz 29 kHz 30 kHz 21 kHz 17 kHz 11 kHz	
Pulse frequency	Dependent on measurin	ng range 1 Hz10	Hz
Attenuation due to conditions	Determining the detection	on limits with a 3 d	B beam angle
L = length of beam (calculated from max. measuring range of sensor) r = radius of beam	EDU 80, 80F FDU 81, 81F FDU 82 FDU 83 FDU 80 FDU 81 FDU 82 FDU 82 FDU 83 FDU 83 FDU 84	2 - quids 8° 5 m 8° 10 m 8° 20 m 8° 2 m colids 8° 8° 5 m 8° 10 m 8° 10 m 4° 15 m 5° 25 m	r 0.35 m 0.69 m 1.4 m 0.87 m 0.14 m 0.35 m 0.35 m 0.52 m 1.1 m
For feet see page 4	FDU 85 FDU 86	5° 45 m 6° 70 m	1.9 m 3.6 m
Transmitters	FMU 860: 1-channel ins	strument for level m	neasurement

FMU 861: 1-channel instrument for flow measurement FMU 862: 2-channel instrument for flow or level measurement

Output

L

Mounting conditions

Mounting position	Vertical to the surface of the material
-------------------	---

Ambient conditions

Storage temperature	FDU 80: FDU 80F FDU 81: FDU 81F: FDU 82, 83, 84, 85: FDU 86:	-40+60°C (-40+140°F) -40+95°C (-40+203°F) -40+80°C (-40+176°F) -40+95°C (-40+203°F) -40+80°C (-40+176°F) -40+150°C (-40+302°F)
Relative humidity	FDU 80, 80F, 81, 81F, 82, 83, 85, 86: 100% FDU 84: 100% (max. 60°C/140°F), 95% (max. 80°C/176°F)	
Protection	IP 68 (tested by immersing to 1 m for 24 h)	
Electromagnetic compatibility	Emitted interference to EN 61326, Class B equipment; immunity to interference resistance to EN 61326; Annex A (industry sector)	

Process temperature

FDU 80

Certificate (Version)	Sensor heating	Temperature class	Ambient temperature
standard (R) CSA GP (U)			- 20 °C + 60 °C [- 40 °C + 60 °C for limited range]
ATEX II 2 G (J) FM (Q) CSA (S)	nein	Т6	- 20 °C + 60 °C
	ја	Т6	- 20 °C + 40 °C

FDU 81

Certificate (Version)	Sensor heating	Temperature class	Ambient temperature
standard (R) CSA GP (U)	nein		- 20 °C + 80 °C [- 40 °C + 80 °C for limited range]
	ja		- 20 °C + 60 °C
ATEX II 2 G (J) FM (Q) CSA (S)	nein	T5	- 20 °C + 80 °C
	ја	T5	- 20 °C + 60 °C

FDU 80F / 81F

Certificate (Version)	Temperature class	Ambient temperature
standard (R) CSA GP (U)		- 40 °C + 95 °C
ATEX II 2 G (J) FM (Q) CSA (S)	Τ5	- 20 °C + 80 °C

FDU 82

Certificate (Version)	Temperature class	Ambient temperature
standard (R) CSA GP (U)		- 20 °C + 80 °C [- 40 °C + 80 °C for limited range]
ATEX II 2 G (J)	Τ5	- 20 °C + 80 °C
FM (Q) CSA (S)	Т6	- 20 °C + 60 °C

FDU 83 / 84 / 85

Certificate (Version)	Ambient temperature
standard (R) CSA GP (U)	- 20 °C + 80 °C [- 40 °C + 80 °C for limited range]
ATEX II 1/2 D (E) FM (P) CSA (T)	- 20 °C + 80 °C

FDU 86

Certificate (Version)	Temperature class	Ambient temperature
standard (R) CSA GP (U)		- 40 °C + 150 °C
ATEX 1/2 D (E) FM (P) CSA (S)	T3C	- 40 °C + 140 °C
ATEX 1/2 D (F) FM (K) CSA (L)	Τ5	- 40 °C + 80 °C
ATEX II 2 G	Т5	- 40 °C + 90 °C
	Тб	- 40 °C + 75 °C

Process pressure

Process pressure P _{abs}	FDU 80	2 bar (29 psi)
	FDU 80F	4 bar (58 psi)
* May be used at high pressures but only after first	FDU 81	2 bar (29 psi)
contacting Endress+Hauser	FDU 81F	4 bar (58 psi)
	FDU 82	2 bar (29 psi)
	FDU 83	1.5 bar (22 psi)
	FDU 84	1.5 bar (22 psi)
	FDU 85	1.5 bar (22 psi)
	FDU 86	3 bar (44 psi)
Housings	•	

Mechanical Construction





Materials

Thread FDU 80, 81, 82: PP-GF FDU 80, 81, 82: FDU 80, 81, 82: FTE FDU 83 1,4301 (AISI 304) or aluminium FDU 84 1,4301 (AISI 304) or aluminium FDU 85 UP FDU 85 UP FDU 85 UP *** 0.5 mm stainless steel 1.4571/SS 316Ti with a 4 mm closed-pore PE cover facing the material *** 1 mm aluminium with a 5 mm closed-pore PE cover facing the material *** 1 um aluminium diaphragm coated with PTFE Diaphragm seal FDU 8085: EPDM Connecting cable FDU 80.SGF. 81, 81F, 82: PVC FDU 80, 84, 85: PUR FDU 80, 80F, 81, 81F, 82: PVC FDU 80, 80F, 81, 81F, 82: PVC FDU 80, 80F, 81, 81F, 82: PVC FDU 80, 80F, 81, 81F, 82: PUR FDU 80, 80F, 81, 81F, 82: PUR FDU 80, 80F, 81, 81F, 82: PVC FDU 80, 80F, 81, 81F, 82: PUR FDU 80, 80F, 81, 81F, 82: PUR	Housing * A 1.4301/SS 304 stainless steel cover around the PA housing enables it to be used in Zone 10.	FDU 80, 81, 82: PP-GF FDU 80F, 81F: ETFE FDU 83 PA* FDU 84 PA* FDU 85 UP FDU 86 UP
Diaphragm FDU 83 1.4571 (AISI 316 Ti) * 0.5 mm stainless steel 1.4571/SS 316Ti with a 4 mm closed-pore PE cover facing the material FDU 84 1.4571 (AISI 316 Ti)/PE* *** 1 mm aluminium with a 5 mm closed-pore PE cover facing the material FDU 86 Al/PE** *** aluminium diaphragm coated with PTFE FDU 8085: EPDM FDU 86: silicone Connecting cable FDU 80, 80F, 81, 81F, 82: PVC FDU 83; 84, 85: PUR FDU 86: silicone Mounting accessories Alignment unit: flange 1.4301 (AISI 304), pipe galvanised steel Silp-on flange: PP (max. 1.5 bar) or 1.4435/1.4404 (AISI 304) (>1.5 bar) Power supply Via transmitters FMU 860862 Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Thread	FDU 80, 81, 82: PP-GF FDU 80F, 81F: ETFE FDU 83 1.4301 (AISI 304) or aluminium FDU 84 1.4301 (AISI 304) or aluminium FDU 85 UP FDU 86 UP or 1.4301
Diaphragm seal FDU 8085: EPDM FDU 86: silicone Connecting cable FDU 80, 80F, 81, 81F, 82: PVC FDU 83, 84, 85: PUR FDU 86: silicone Mounting accessories Alignment unit: flange 1.4301 (AISI 304), pipe galvanised steel Slip-on flange: PP (max. 1.5 bar) or 1.4435/1.4404 (AISI 304) (>1.5 bar) Power supply Via transmitters FMU 860862 Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Diaphragm * 0.5 mm stainless steel 1.4571/SS 316Ti with a 4 mm closed-pore PE cover facing the material ** 1 mm aluminium with a 5 mm closed-pore PE cover facing the material *** aluminium diaphragm coated with PTFE	FDU 83 1.4571 (AISI 316 Ti) FDU 84 1.4571 (AISI 316 Ti)/PE* FDU 85 AI/PE** FDU 86 AI/PTFE***
Connecting cable FDU 80, 80F, 81, 81F, 82: PVC FDU 83, 84, 85: PUR FDU 86: silicone Mounting accessories Alignment unit: flange 1.4301 (AISI 304), pipe galvanised steel Slip-on flange: PP (max. 1.5 bar) or 1.4435/1.4404 (AISI 304) (>1.5 bar) Power supply Via transmitters FMU 860862 Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Diaphragm seal	FDU 8085: EPDM FDU 86: silicone
Mounting accessories Alignment unit: flange 1.4301 (AISI 304), pipe galvanised steel Slip-on flange: PP (max. 1.5 bar) or 1.4435/1.4404 (AISI 304) (>1.5 bar) Power supply Via transmitters FMU 860862 Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Connecting cable	FDU 80, 80F, 81, 81F, 82: PVC FDU 83, 84, 85: PUR FDU 86: silicone
Power supply Via transmitters FMU 860862 Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Mounting accessories	Alignment unit: flange 1.4301 (AISI 304), pipe galvanised steel Slip-on flange: PP (max. 1.5 bar) or 1.4435/1.4404 (AISI 304) (>1.5 bar)
Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Power supply	Via transmitters FMU 860862
Ignition protection see section »Product Structure« CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.		·
CE mark By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.	Ignition protection	see section »Product Structure«
	CE mark	By attaching the CE mark, Endress+Hauser confirms that the instrument fulfils all the requirements of the relevant EC directives.
See Section »Produkt Structure«	see section »Produkt Structure«	

Power Supply

Certificates and Approvals

Order Code

Supplementary Documentation

Technical Information TI 190F/00/en Prosonic FMU 860...862 Operating Instructions BA 100F/00/en Prosonic FMU 860...862

Product Structure

FDU 80, 80F, 81, 81F, 82 Prosonic Sensors



FDU 83, 84, 85 Prosonic Sensors



Product Structure

FDU 86 P	rosonic Sensor
	Certificates
	R Version for non-hazardous area E DMT Dust-Ex ATEX II 1/2 D (-40140°C) F DMT Dust-Ex ATEX II 1/2 D (-4080°C) J DMT Gas-Ex ATEX II 2 G (-35140°C) K FM Class I/I/III, Div. 1/2 Groups AG, LT (-4080°C) L CSA Class II/III, Div. 1/2 Groups EG, NT (-4080°C) P FM Class I/I/III, Div. 1/2, Groups AG, HT (-40140°C) T CSA General Purpose W TIIS dust Ex DP12
	Process Connection / Material G Threaded connection G 1, UP N Threaded connection 1 NPT, UP S Threaded connection G 1, 1.4301 (AISI 304) V Threaded connection 1 NPT, 1.4301 (AISI 304) Cable Length 1 1 with 5 m (16 ft) connecting cable 2 with 10 m (32 ft) connecting cable 3 with 5 m (49 ft) connecting cable 4 with 20 m (65 ft) connecting cable 5 with 30 m (98 ft) connecting cable 6 with 30 m (98 ft) connecting cable 8 m (variable length, up to 300 m)
FDU 8	6 - Product designation

Endress+Hauser GmbH+Co. KG Instruments International P.O. Box 2222 D-79574 Weil am Rhein Germany

Tel. (07621) 975-02 Fax (07621) 975-345 http://www.endress.com info@ii.endress.com





05.02/PT1