Endress + Hauser GmbH	+ Co.	Inspection and test	plan		page 1 of 1
Product:	Monitoring station		Туре:	CE-26	
Measurement principle:					
Manufacturer:	Endress+Hauser Gm	bH+Co.	PC -	Wetzer	



Mode of testing	Test instructions	Inspection criteria	Frequency of testing	
Contract review	Internal test specification	Base of contract DIN EN ISO 9001:2000	100%	
Incoming inspection	Internal test specification	Verification of conformance to the specified requirements	Dynamic, CAQ – System	
Insulation test	Internal test specification	500V/DC	100%	
Function test/ final test Internal test specification		Verification of communication, digital outputs, digital inputs, relays, measuring accuracy, display, keys, function of integrated devices, check of conformity with order.	100%	
Outgoing check	Internal test specification	Visual check, verfication of type label. Completeness: accessories and correct packaging	100%	

Inspection mark	No special marking is provided on the instrument for standard instrument.	
Records	The serial number and manufacturing date are the indication by way of internal documentation, for the date of production as well the filed test results.	

Prepared:	TIP/EH	Checked:	TIP/EH	Release:	1.00
Date:	20.09.2002	Date:	20.09.2002	Date:	20.09.2002