

Hazardous (Classified) Location Class I / Division 1, 2 / Groups ABCD Class I. Zone 0, IIC Class II / Division 1, 2 / Groups EFG

Nonhazardous Locations



RID14 with electronic insert for Profibus PA/Foundation Fieldbus Concept FISCO Ui (Vmax) 17.5 V 24 V 500mA 250mA Ii (Ìmax) 5.5 W 1.2 W Pi (Pmax) Ci < 5nF Li < 10 tiH Leakage current ≤ 50 µA



### Installation Notes RID14

- CSA Approved Apparatus must be installed in accordance with manufacturer instructions.
- Install per National Canadian Electrical Code.
- Use supply wires suitable for 5°C above surroundings.
- Warning: Substitution of components may impair intrinsic safety or suitability for Class I, Division 2.

#### Temperature range

0

Class III

T4 -40°C ... +80°C

-40°C +70°C

-40°C ... +55°C

## DUST IGNITION PROOF

# Class II. III / Div. 1 / Groups EFG

- A dust tight seal must be used for conduit entries when the field indicator is used in a Class II or Class III location.

### **INTRINSICALLY SAFE**

### Class I / Div. 1 / Groups ABCD Ex ia IIC

N

- CSA approved associated apparatus must meet the following requirements:
- Uo or Voc or  $Vt \le Ui$  (Vmax) and Io or Isc or  $It \le Ii$  (Imax) and Po or Pmax  $\le Pi$  (Pmax)
- The maximum non-hazardous area voltage must not exceed 250 V.
- The Installation should be in accordance with the Canadian Electrical Code
- Be aware of multiple earthing of screen. The screen must be connected in accordance with Canadian Electrical Code.
- The polarity for connecting + and is of no importance due to an internal rectifier.

RID14 is suitable for the connection to a Profibus PA/Foundation Fieldbus system according to Entity- or FISCO Concept

#### FISCO-Concept

The FISCO Concept allows interconnection of intrinsically safe apparatus to associated apparatus not specifically examined in such combination. The criteria for interconnection is that the voltage (Ui or Vmax), the current (Ii or Imax) and the power (Pi or Pmax) which intrinsically safe apparatus can receive and remain intrinsically safe, considering faults, must be equal or greater than the voltage (Uo or Voc or Vt), the current (lo or Isc or It) and the power (Po or Pmax) levels which can be delivered by the associated apparatus, considering faults and applicable factors. In addition, the maximum unprotected capacitance (Ci) and inductance (Li) of each apparatus (other than the termination) connected to the fieldbus must be less than or equal to 5 nF and 10 µH respectively.

In each segment only one active device, normally the associated apparatus is allowed to provide the necessary energy for the fieldbus system. The voltage Uo (or Voc or Vt) of the associated apparatus has to be limited to the range of 14V to 24V d.c. All other equipment connected to the bus cable has to be passive, meaning that they are not allowed to provide energy to the system, except to a leakage current of 50 uA for each

Separately powered equipment needs a galvanic isolation to assure that the intrinsically safe fieldbus circuit remains passive.

The cable used to interconnect the devices has to meet the following values:

Loop resistance R': 15 ... 150  $\Omega$ /km, inductance L': 0.4 ... 1 mH/km

capacitance C': 80 ... 200 nF/km

C' = C' line/line + 0.5 C' line/screen, if both lines are floating or

C'= C'line/line + C'line/screen, if the screen is connected to one line

length of trunk cable: 1 km length of splice: 1 m Length of spur cable: 30 m

At each end of the trunk cable an approved infallible line termination with the following parameters is suitable:

 $R = 90 \dots 100 \Omega$   $C = 0 \dots 2.2 \mu F$ .

One of the allowed terminations might already be integrated in the associated apparatus.

The number of passive devices connected to the bus segment is not limited due to I.S. reasons. If the above rules are respected, up to a total length of 1000 m (sum of the length of trunk cable and all spur cables), the inductance and capacitance of the cable will not impair the intrinsic safety of the installation.

### NONINCENDIVE

Class I / Zone 2 / Ex nA IIC Class I / Div. 2 / Groups ABCD

- Intrinsic safety barrier not required. Vmax ≤ 35 V DC.
- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous.
- Nonincendive field wiring installation

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or Associated Apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations. when  $Voc \le Vmax$ ,  $Ca \ge Ci + Ccable$ ,  $La \ge Li + Lcable$ .

Field indicator Nonincendive Field Wiring parameters are as follows:

Ui or Vmax  $\leq 35$  V DC

 $Ci = \le 5 \text{ nF}$   $Li \le 10 \mu\text{F}$ 

For these current controlled circuits, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the Associated Nonincendive Field Wiring Apparatus or Associated Apparatus.

- Warning: Explosion Hazard- Do not disconnect equipment unless power has been switched off or the area is known to be non hazardous
- The field indicator is suitable to be installed according the FNICO concept.

|   | Approved Pfanzelt                  | Date (yyyy-mm-dd)<br>2009-07-06          | Drawing No. 12 08 00 112 | Dwg.rev.     | Revision no. | Revision date (yyyy-mm-dd) | Name   | Material 7<br>ZD 084R/09/ | 1116940<br>en/05.10 | Endress+Hauser 🖽  |
|---|------------------------------------|--|--------------------------|--------------|--------------|----------------------------|--------|---------------------------|---------------------|---|
| Volume (mm³)                            | Designed Pfanzelt                  | Date (yyyy-mm-dd)<br>2009-07-05          | RID14                    | Scale<br>1:1 | CONTRO       | L DRAWING                  | Series |                           |                     |   |
| Refer to protection notice<br>ISO 16016 | Edge of working parts<br>ISO 13715 | Geometrical tolerancing<br>ISO 2768-mH-E | Part No.                 | Format<br>A4 | IS/NI/DIP    |                            |        | Objekt version            |                     | Endress + Hauser Wetzer<br>GmbH+Co. KG Nesselwang / Germany |

ယ

4

CD

ω

0

O